

# **GB-15/GB-16 SERIES**

**GAS APPLIANCE BALL VALVES** 

Job Name:	Contractor:	
Job Location:	P.O. Number:	
Engineer:	Representative:	
Тад:	Wholesale Distributor:	

#### DESCRIPTION

The Apollo-International<sup>®</sup> GB-15 and GB-16 series forged brass ball valves are specifically designed and certified for natural gas, manufactured and mixed gas, liquefied petroleum gases and LP gas-air mixture applications.

## **FEATURES**

- Rated Gas Pressures of <sup>1</sup>/<sub>2</sub> and 5 psig
- Full port design ensures maximum capacity
- For natural gas, manufactured and mixed gases, LP gas and LP gas-air mixtures

### MATERIAL

Part Name	Material
Body	Forged Brass
Ball	Brass, Chrome Plated
Stem Packing	Dual O-Ring
Seat	PTFE
Retainer	Forged Brass
Handle	Die Cast

## CAPACITIES AND DIMENSIONS

Model Number	PART NUMBERS	SIZE AND END CONNECTION (in.)
GB-15	51GF301	1/2 FNPT x 1/2 FNPT
GB-15	51GF401	¾ FNPT x ¾ FNPT
GB-16	51GG201	1/2 FNPT x 3/8 Flare
GB-16	51GG301	1/2 FNPT x 1/2 Flare



## **APPROVALS**

- ANSI Z21.15, CGA 9.1 (1/2 psig service) gas shutoff
- ASME B16.44 (5 psig service)
- MSS SP-10; Ball Valves
- UL Guide YRBX
- UL Guide YSTD
- UL Guide YRPV
- UL Guide MHKZ

Conbraco Industries, Inc. 701 Matthews Mint Hill Rd. Matthews NC 28105 USA ; www.apollovalves.com ; 704-841-6000

Conbraco Industries can accept no responsibility for possible errors in this document and reserves the right to alter its product design or construction without notice and without incurring any obligation to make such changes on Conbraco products previously or subsequently sold. All product specifications are approximate and are provided for reference only.