

# 'Apollo' Valves

## SUBMITTAL SHEET

### 101T-PR

200 CWP Bronze RS Gate Valve

**APOLLOXPRESS®**



Job Name:	
Job Location:	
Engineer:	
Contractor:	
Tag:	
PO Number:	
Representative:	
Wholesale Distributor:	



### DESCRIPTION

The APOLLOXPRESS® Model 101T-PR (30 Series) Gate valve with Press connections is a proven combination that provides economical installation and reliable service. The valves are cast, machined, assembled, and tested in South Carolina using proven ASTM quality materials. The Apollo rising stem Gate valve can reliably be installed in most plumbing and heating systems including building service piping and OEM applications.

### FEATURES

- Fast, Reliable, Economical Press Installation
- Ridgid® XL Press Tool Compatible
- Leak Before Press® Technology
- Full Port Flow
- Guided Solid Bronze Disc
- Adjustable Graphite Stem Packing
- Rising Stem
- Screw-in Bonnet
- Rugged Malleable Iron Hand Wheel
- Back seat protection
- Made in U.S.A., ARRA Compliant

### PERFORMANCE RATING†

- Maximum Pressure: 200 psi (13.8 bar) non-shock
- Temperature Range: 0°F - 250°F (-18°C - 121°C)

†APOLLOXPRESS® connectors are designed for direct mechanical connection to ASTM B88-Type K, L, and M copper tubing in the hard drawn condition. Press connectors are not suitable for steam or flammable gas service.

### OPTIONS

- (101T-PR-LF) Lead Free APOLLOXPRESS®

### STANDARD MATERIALS LIST

Part Name	Material
Body	ASTM B62 –C83600 Bronze
Bonnet	ASTM B62 –C83600 Bronze
Connector Housing	ASTM B16 –C36000 Brass
Connector O-Ring	NSF grade EPDM
Stem	ASTM B371 C69400 Bronze
Disc	ASTM B62 –C83600 Bronze
Packing	Grafoil
Hand Wheel	Malleable Iron
Nameplate	Aluminum

### APPROVALS

- MSS SP-80, "Bronze Gate, Globe, Angle & Check Valves"
- Canadian Registration Number OC14667.5

**Not intended for potable water**

### ORDER INFORMATION

Model Number	Part Number	Size (in.)
101T-12-PR	30-003-01PR	1/2"
101T-34-PR	30-004-01PR	3/4"
101T-1-PR	30-005-01PR	1"
101T-114-PR	30-006-01PR	1-1/4"
101T-112-PR	30-007-01PR	1-1/2"
101T-2-PR	30-008-01PR	2"

### DIMENSIONS

Height open (in.)	Length (in.)	Weight (lbs)	Cv (gpm)
4.85	3.9	1.3	12.5
5.71	4.3	1.8	24.0
6.71	4.7	2.6	72.3
8.1	5.13	3.8	80.0
9.08	6.12	5.4	119.0
11.28	6.70	8.5	338.0

For liquids the flow coefficient - Cv - expresses the flow capacity in gallons per minute (GPM) of 60°F water with a pressure drop of 1 psi (lb/in<sup>2</sup>).

Apollo Valves, Manufactured by **Conbraco Industries, Inc.**  
701 Matthews Mint-Hill Road, Matthews, NC 28105 USA  
[www.apollovalves.com](http://www.apollovalves.com) | (704) 841-6000

This specification is provided for reference only. Conbraco Industries Inc. reserves the right to change any portion of this specification without notice and without incurring obligation to make such changes to Conbraco products previously or subsequently sold. Please visit our website @ [www.apollovalves.com](http://www.apollovalves.com) for the most current information.

