

S360 Safety Vest

General

ANSI/ISEA Classification:	Meets ANSI/ISEA 107-2015
Warning Markings:	Yes, on packaging and garment
Personalization:	Yes
Item Number:	Lime: M-61375, L-61376, XL-61377, 2X-61378, 3X-61379, 4X-61380, 5X-61381
Item Series:	Class 2 Vest
Case Pack:	50 ea.
Sell Pack:	Each
Case Dimensions:	15.75" x 11" x 19.70
Case Weight:	20-26 lbs



Description

- 100% polyester woven oxford
- Right interior waist pocket with hook & loop closure. 7" W x 7.75" D
- 2 exterior waist pockets with hook & loop closure. 7" W x 7.75" D
- Right exterior waist pen compartment
- Left exterior chest radio/phone pocket flapped with hook & loop closure. 3" W x 5" D with 1" gusset
- Microphone tabs on both sides

Materials

Material:	100% polyester woven oxford
Color:	Hi-Viz Lime
Size:	M-5XL

Sizing

Vest Type:	ANSI Class 2
Vest Dimensions:	M- 47x27" L-51x27" XL- 55x27" 2X- 59x27" 3X- 61x28" 4X- 63x28" 5X- 65x29"
Closure Type:	Hook and Loop
Binding Type:	Polyester

Customization Capabilities:

Screen Printing, Vinyl Transfer and 4 Color Transfer

Labeling

Vest Tag Info:	Aware Wear Conforms to ANSI/ISEA 107-2015 Class 2 Level 2 #S360 Made in China Care label
Poly Bag Info:	Class 2 Level 2 5 Pockets S360 (Item #) ANSI Class 2 (Color) (Size) ERB Industries
Carton Markings:	Style No: PO#: Color: Size: Quantity: N.W.: G.W.: C/No.: Made in China