WIDOS, LLC 1375 Highlands Ridge Rd. Ste A Smyrna,GA. 30082 www.widoswelding.com



Office: 678-766-1250 Fax:678-766-1249 info@widoswelding.com

EQUIPMENT SPECIFICATION SHEET



WIDOS W2500/315 Butt Fusion Machine - 110v

A handy, mobile, plastic welding machine capable of welding PE, PP, and PVDF materials, for use in the workshop and on the building site. This machine is particularly suitable for sanitary installations and wastepipe systems. The pipe size range, in diameters, are from an OD of 50 to 315 mm (1-1/2" – 10" IPS). Machine comes equipped with electrically operated planer and heating element, basic clamping tool divided into two parts, each side swiveling up to 15°, with clamping inserts and prismatic pipe supports. The transport crate provides safe, clean and protected storage, as well as serving as a portable working bench top for onsite fabrication. Versions also available in °C, or with kp-force display.

W2500 features:

- Optional Horizontal and Vertical adjustments for proper alignment
- Angular Master Clamps for site mitered fitting production
- Optional power supply requirements (110v or 230v)
- Electronically adjusted heating element, with indicator
- Easily installed Reducer Inserts for welding 50mm 280mm
- IPS Reducer Clamps available for easy conversion to IPS Pipe

| WIDOS W2500/315 Bench Butt Fusion Machine – 110v | |
|--|----------------------------------|
| WIDOS W2500/315 Bench Butt Welding Machine | |
| Size Range | 50mm - 315mm (1-1/2" to 10" IPS) |
| Material Range | HDPE, PP, PVDF |
| Material Construction | Steel, Aluminum |
| Power Requirement | 110v, 15amp |
| Planer Power Supply | 110v / 1050W |
| Heater Power Supply | 110v / 2100W |
| Base Tool Dimension | 32"L x 24"W x 20" H |
| Machine Weight* | 77 lbs. |
| Transport Case Weight | 68 lbs. |
| Transport Case Dimension | 38"L x 27"W x 28"H |
| Total Machine Weight, | 254 lbs. |
| with crate | |
| * Does not include Planer, Heater or Inserts. | |

