

# **Model ZW1070XL**

# **Aqua-Gard® Thermostatic Mixing Valve**

# **Application**

Ideal for use where Lead-Free\* valves are required. The Zurn Wilkins Model ZW1070XL Aqua-Gard® Thermostatic mixing valve is designed to be installed at the point of use to assist in the prevention of scalding. The valve's extremely rapid response rate make it most suitable for installation at plumbing fixtures and appliances for the final control of water temperature. The ZW1070XL is ASSE 1070 listed for fixtures, sinks, lavatories or bathtubs and will mix hot and cold water from the distribution system to a final safer temperature of 95-115°F (35-46°C). Multiple end configurations make this valve suitable for all residential and commercial installations.

# **Standards Compliance**

- ASSE® Listed 1070
- CSA® Certified
- Meets the requirements of NSF/ANSI 61-9\* \*(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

#### **Materials**

Body Low Lead Cast Bronze, ASTM B 584

W/Nickel Plating ASTM B 456

Service Condition #2

Low Lead Brass, ASTM B 927, Internal brass

UNS C27450

Piston Polysufone Guide Tube NorvI GFN2

Spring & Screen 300 Series Stainless Steel

Seals Viton

Checks Noryl GFN2





### **Features**

Sizes: 3/8", 1/2", 3/4", 1" Outlet Temp. Range Temperature Hot Supply

120-195°F max. (49-90.5°C) 40-75°F (4.4-23.8°C) +/- 3°F(1.78°C) 145 psi

95-115°F(35-46°C)

Max. Working Pressure (inlet) Temperature must be field set

Temperature Cold Supply

Set Temperature Accuracy

Max. Pressure Differential is 15 psi between Hot & Cold inlets

Flow rate @ 45 psi pressure loss 10 gpm Min. Flow Rate 0.35 gpm

CPVC tailpiece - Maximum Hot water Temperature of

180°F @ 100 psi.

- Cold water rated Temperature of

73.4°F @ 400 psi.

## **Options**

- with Z-Bite™ push fit tailpiece connections


(1/2" - 1" only)

PR - with Z-Press™ press fit tailpiece connections

(3/4" - 1" only)


# Dimensions & Weights (do not include pkg.)

	INLET & OUTLET	DIMENSIONS (approximate)						WEIGHT	
MODEL		Α.		В		С		WEIGHT	
		in.	mm	in.	mm	in.	mm	lbs.	kg
38-ZW1070XLCOMP	3/8" Compression	5 11/16	145	3 5/8	92	5 13/16	148	2	1
12-ZW1070XL	1/2" FNPT	5 7/16	138	3 3/8	86	5 1/4	133	2	1
12-ZW1070XLC	1/2" CU Sweat								
12-ZW1070XLCPVC	1/2" CPVC	5 7/8	149	3 13/16	97	6 3/16	157	2	1
12-ZW1070XLPEX	1/2" Barb	5 9/16	141	3 1/2	89	5 9/16	141	2	1
12-ZW1070XLPEXF1960	1/2" Barb	5 3/8	137	3 5/16	85	5 1/4	133	2	1
34-ZW1070XL	3/4" FNPT	5 1/2	140	3 1/2	89	5 7/16	138	2	1
34-ZW1070XLC	3/4" CU Sweat								
34-ZW1070XLCPVC	3/4" CPVC	5 7/16	138	3 3/8	86	5 5/16	135	2	1
34-ZW1070XLPEX	3/4" Barb	5 9/16	141	3 1/2	89	5 9/16	141	2	1
34-ZW1070XLPEXF1960	3/4" Barb	5 3/4	146	3 11/16	94	5 11/16	151	2	1
34-ZW1070XLM	3/4" MNPT	6 1/4	159	4 1/4	108	7	178	2	1
1-ZW1070XLC	1" CU Sweat	5 1/2	140	3 7/16	87	5 3/16	132	2	1



# Flow Characteristic

## MODEL ZW1070XL (STANDARD & METRIC)



Zurn Industries, LLC | Wilkins

1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766

In Canada | Zurn Industries Limited

3544 Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292

Document No. TMV-ZW1070XL Product No. Model ZW1070XL