



Measurements:

<u>Height</u>	<u>Width</u>
6.00"	13.50"
<u>Hanging Weight</u>	
2.45 lb	

Lamping:

Incandescent MB	1,344 Rated Lumens
2.00 60W MB	Color Temperature
120 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.80 lb	15.40"	6.30"	15.40"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209029255	Yes	

Finish:

Black BK

Glass:

Ice IC

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB (Not Included)



253 NORTH VINELAND AVE. | CITY OF INDUSTRY, CA 91746
T. 626.956.4200 | F. 626.956.4225

maximlighting.com
#Maximlighting

Always consult a qualified, licensed electrician before installation of any products....