

DECK-MOUNT GOOSENECK SPOUT

WITH LAMINAR FLOW IN BASE OF SPOUT




7522.180 Shown

MODEL NUMBER:

☐ 7522.180 Gooseneck Spout

Tubular brass gooseneck spout with 1.5 gpm pressure compensating laminar flow device in base. Plain spout end. Rigid. Deck-mounted. Chrome finish.



GENERAL DESCRIPTION:

Deck-mounted rigid, tubular brass gooseneck spout with laminar flow device in base. Plain spout end. Chrome finish. 1.5 gpm/5.7 L/min maximum flow rate.

PRODUCT FEATURES:

Laminar Flow Device in Base of Spout: Prevents mix of air and water. Ideal for hospital applications.

Plain Spout End: Eliminates area for lime and debris to collect.

Brass Construction: Durable - Excellent in high use applications. Ideal for prolonged contact with water.

Lead-Free: Faucet contains ≤ 0.25% total lead content by weighted average.

SUGGESTED SPECIFICATION

Tubular brass gooseneck spout with laminar flow device in base. Plain spout end. Polished Chrome finish. 1.5 gpm/5.7 L/min maximum flow rate. Fitting shall be American Standard Model # 7522.180.002.