

Class 125 Iron Body Check Valves

Twin disc • wafer style • bronze disc • rubber seat •
spring actuated • non slam • silent check

150 PSI/10.3 bar non-shock cold working pressure
Maximum temperature to 180°F/82°C

CONFORMS TO AWWA C518



W-920-W-LF
Wafer





C USA
COMPONENT LEAD-FREE

MATERIAL LIST — 30"

PART	SPECIFICATION
1. Body	Cast Iron ASTM A126 Class B w/Buna-N (Nitrile) resilient seat molded to body
2. Disc	Bronze ASTM A536 B584 UNS C87600
3. Torsion Spring	Stainless Steel ASTM A 313 UNS S31600 or UNS S17400
4. Disc Thrust Bearing	Stainless Steel ASTM A 240 UNS S31600
5. Stabilization Sphere	Nitrile ASTM D 2000
6. Hinge Pin Retainer	Steel
7. Stop Pin Retainer	Steel
8. Disc Stop Pin	Stainless Steel ASTM A 276 UNS S31600
9. Disc Hing Pin	Stainless Steel ASTM A 276 UNS S31600

MATERIAL LIST — 36"

PART	SPECIFICATION
1. Body	Cast Iron ASTM A126 Class B
2. Disc	Nickel Plated D.I. ASTM A536 Grade 65-45-12
3. Torsion Spring	Stainless Steel ASTM A 313 UNS S31600 or UNS S17400
4. Inner Thrust Bearing	Stainless Steel ASTM A 240 UNS S31600
5. Outer Thrust Bearing	Stainless Steel ASTM A 240 UNS S31600
6. Hinge Pin Retainer	Steel
7. Stop Pin Retainer	Steel
8. O-Ring	Nitrile ASTM D 2000
9. Shaft Collar	Stainless Steel ASTM A 240 UNS S31600
10. Stabilization Sphere	Nitrile ASTM D 2000
11. Stop Pin	Stainless Steel ASTM A 276 UNS S31600
12. Hinge Pin	Stainless Steel ASTM A 276 UNS S31600



DIMENSIONS—WEIGHTS—QUANTITIES

Size	Dimensions										Weight		
	A		B		C		D		E		Lbs.	Kg.	
In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.		
30	750	12.00	305	34.75	883	9.50	241	30.00	762	28.50	724	1112	504
36	900	14.50	368	41.25	1048	12.00	305	36.00	914	34.50	876	1864	846

NOTE: Twin Disc Check Valves can be installed horizontally or in the vertical position with flow up.

Install 5 pipe diameters minimum downstream from pump discharge or changes in direction to avoid flow turbulence. Flow straighteners may be required in extreme cases.

CAUTION:

For horizontal flow applications, the valve must be installed with disc hinge pin in the vertical position, to insure proper operation.

WARNING:

1. Seat end of valve must be mated to a standard flat faced metal flange. Rubber flanges not acceptable.
2. These are not to be used as steam valves.
3. Valves are not to be used near a reciprocating air compressor.

Note: On pump discharge, the preferred check valves are:

- inline, spring assisted, center-guided, lift checks
- spring assisted twin (double) disc
- swing design with lever and weight or lever and spring

*Weighted average lead content ≤ 0.25%

VISIT WWW.NIBCO.COM FOR CURRENT CHEM-GUIDE AND GALVANIC POTENTIAL IN PIPING SYSTEMS INFORMATION.

Visit our website for the most current information.