
# **SIEMENS**

# **Technical Instructions**

Document No. 155-180P25 EA 599-4 June 11, 2013

# Flowrite<sup>™</sup> 599 Series

# SKD6xU Electronic Valve Actuators 24 Vac Proportional Control





## **Description**

The Flowrite 599 Series SKD6xU Electronic Valve Actuators require a 24 Vac supply and receive a 0 to 10 Vdc or a 4 to 20 mA control signal to proportionally control a valve. These actuators are designed to work with Flowrite 599 Series valves with a 3/4-inch (20 mm) stroke.

#### **Features**

- Direct-coupled installation requires no special tools or adjustments
- Visual and electronic stroke indication
- Die-cast aluminum housing
- Manual override
- Spring return to fail-safe position or non-spring return fail-in-place
- Automatic stroke calibration
- Maintenance-free

## **Application**

These electronic actuators are designed to be used with Flowrite 599 Series valves and Siemens Industry standard valves with a 3/4-inch (20 mm) stroke in liquid service and steam service applications.

#### **Product Number**

SKD62U, Spring Return (Actuator Prefix Code 274) SKD60U, Non-Spring Return (Actuator Prefix Code 267)

# **Warning/Caution Notations**

| WARNING: | A | Personal injury or loss of life may occur if you do not perform a procedure as specified.  |
|----------|---|--|
| CAUTION: | A | Equipment damage or loss of data may occur if you do not perform a procedure as specified. |

| Specifications       |   |                                      |                  |
|----------------------|---|--------------------------------------|------------------|
| Power supply         | Operating voltage   | 24 Vac -20%                          | /+30%            |
| · onor ouppry        | Frequency   | 50/60 Hz                             |                  |
|                      | Power consumption   | 17 VA/12W                            |                  |
| Control signals      | Control input (Y)   |                                      |                  |
|                      | Voltage   | 0 to 10 Vdc or 4 to 20 mA            |                  |
|                      |   | (DIP switch selectable)              |                  |
|                      | Maximum Impedance   | 0 to 10 Vdc 100K ohms                |                  |
|                      | Signal resolution   | 4 to 20 mA; 240 ohm                  |                  |
|                      | Signal resolution   | <1%                                  |                  |
|                      | Hysteresis  | 1%                                   |                  |
|                      | Control input (Z)  Resistance                             | 0 to 1000 ob                         | mo               |
|                      |   | 0 to 1000 ohms                       |                  |
|                      | Voltage   | 0 to 1.6V                            |                  |
|                      | Control output (U) – position feedback                    | 0 to 0.9 V/do 1.29/                  |                  |
|                      | Voltage<br>Load Impedance                                 | 0 to 9.8 Vdc <u>+</u> 2%<br>>10K ohm |                  |
|                      | Current   |                                      |                  |
|                      | Load impedance  | 4 to 19.6 mA <u>+</u> 2% < 500 ohms  |                  |
|                      | Nominal stroke  | 3/4-inch (20 mm)                     |                  |
| Function             |   | 3/4-111011 (20                       | 111111)          |
|                      | Run time with control operation (full stroke)             | 20 accorde                           |                  |
|                      | Pushing stroke, 0 to 100%                                 | 30 seconds<br>15 seconds             |                  |
|                      | Pulling and Spring return stroke, 100 to 0% Nominal Force | Stroke Force                         |                  |
|                      | NC and 3-way upper  | 0%                                   | 225 lbs (1000 N) |
|                      | NO and 3-way by-pass                                      | 100%                                 | 258 lbs (1150 N) |
| Aganay Cartification | UL approval   | UL873                                |                  |
| Agency Certification | 5 - 5 F F 1 - 5 - 5 - 5 - 5 - 5 - 5 - 5 - 5 - 5 -         |                                      |                  |
|                      | cUL   | Certified to Canadian standard       |                  |
|                      |   | C22.2 No. 24-93                      |                  |
|                      | CE conformity per the EMC directive                       | 89/336/EEC                           |                  |
|                      | Low voltage directive                                     | 73/23/EEC                            |                  |
| Ambient conditions   | Ambient temperature (Operation)                           | 5°F to 122°F (-15°C to 50°C)         |                  |
| Ambient conditions   | Media temperature   | -13°F to 300°F (-25°C to 150°C)      |                  |
|                      | '   | <32°F (0°C) requires a Stem Heater   |                  |
| Housing              | NEMA Rating   | NEMA 1 (interior only) See           |                  |
|                      | <u> </u>  | Accessories                          |                  |
| Miscellaneous        | Dimensions  | See Figure 17                        |                  |
|                      | Conduit opening   | 1/2-inch NPSM                        |                  |
|                      | Weight  |                                      |                  |
|                      | SKD60U  | 7.9 lbs (3.6 kg                      | rα\              |

Page 2 Siemens Industry, Inc.

#### **Accessories**

**NOTE:** Installation instructions are included with each accessory.




Figure 1. Auxiliary Switch.

**ASC1.6** Auxiliary switch.

Sends a signal to indicate the valve is in the 0% stroke position. Switching point is fixed at the 0% stroke position.

Switching capacity 24 Vac

4A resistive 2A inductive

Lowest recommended

current 10 mA




Figure 2. Packing Heating Element.


**599-00417** Packing heating element.

Allows stem to move freely in valves controlling fluids at temperatures below 32°F (0°C). Reduces ice crystal formation on the stem which may damage the packing.

Operating Voltage

24 Vac

Heating Output 20 W



See Service Kits for replacement ultraviolet resistant cable ties.




Figure 3. Weather Shield.

#### **Service Kits**

The only field serviceable part is the circuit board.


Circuit board replacement 4-668-5748-8
Plastic wiring compartment cover 4-104 5634-8
Manual Override Kit for SKD 4-268 5504-8
Ultraviolet (UV) resistant cable ties (pkg. of 10) 538-996



#### **WARNING:**

This product contains a spring under high compression. Do not attempt to disassemble the actuator.

#### **SKD Details**



Legend

- 1 Pressure cylinder
- 2 Piston
- 3 Oscillating pump
- 4 Return spring
- 5 Bypass valve
- 6 Valve stem retainer
- 7 Manual override knob
- B Position indicator

Figure 4. SKD6xU Details.

# Operation

The actuator accepts a 0 to 10 Vdc or a 4 to 20 mA control signal. The actuator mounted on a valve, produces a stroke proportional to the input signal. When power is turned off or in the event of a power failure, the SKD62U Actuator spring returns the valve to its normal position, and the SKD60U Actuator fails in place.






Figure 5.

Figure 6.

Spring return: When power is turned off or in the event of a power failure, the actuator spring returns the valve to its normal position.

Non-spring return: When power is turned off or in the event of a power failure, the actuator maintains its position.




Figure 7. Valve Stem Travel Indication.

Page 4 Siemens Industry, Inc.

# Mounting and Installation




Figure 8. Acceptable Mounting Positions.

The vertical position is the recommended position for mounting. Other positions are allowed. When using the Weather Shield for NEMA 3R rating, the vertical position is required. See Weather Shield installation instructions and Figure 8.

Allow four inches (100 mm) around the sides and back of the actuator and eight inches (200 mm) above and to the front of the actuator.

See dimensions in Figure 17.

Detailed installation instructions for field mounting are shipped with the actuator.

## Start-up

Check the wiring for proper connections.

**NOTE:** The valve body assembly determines the complete assembly action.

#### **Stroke Calibration**

To determine the stroke positions 0% and 100% in the valve, calibration is required when the valve/actuator are commissioned for the first time.

The actuator must be mechanically connected to a valve and must have a 24 Vac power supply. The calibration procedure can be repeated as often as necessary.



#### **CAUTION:**

Before starting calibration, be sure the manual adjuster is set to **Automatic** to register the actual values.

There is a slot on the printed circuit boards of the actuators. To initiate the calibration procedure, the contacts inside this slot must be short-circuited, for example, with a screwdriver (see Figure 9).



Automatic calibration proceeds as follows (see Figure 10):

- Actuator runs to the 0 stroke position (1), green LED flashes.
- Actuator then runs to the 100 stroke position (2), green LED flashes.
- Measured values are stored in the EPROM.
- The actuator now moves to the position defined by control signal Y or Z (3), and the green LED now glows steadily (normal operation).
- Throughout this procedure, output U is inactive; meaning, the values only represent actual positions when the green LED stops flashing and remains on continuously.

Figure 9.




Figure 10.


# Stroke Calibration, Continued

Table 1. LED Status.

| LED   | Display  | Function   | Action   |
|-------|----------|--|--|
|       | ON       | Normal Operation   | Automatic operation  |
| Green | Flashing | Stroke calibration In Progress                               | Wait for calibration to be completed (LED stops flashing)  |
| Red   | ON       | Faulty stroke calibration  Internal Error                    | Check mounting     Restart stroke calibration (by short-circuiting calibration slot)     Replace electronics |
|       | Flashing | Inner valve jammed   | Check the valve  |
|       | OFF      | <ul><li>No power supply</li><li>Faulty electronics</li></ul> | -Check mains -Replace electronics  |

#### **Override Control**

The override control input (Z) has three modes of operation:



The Z-modes have a "direct acting" factory setting.

Page 6 Siemens Industry, Inc.

# Start-up, Continued




Figure 11. SKD Electronic Features.

| DIP Switches<br>(Left to right) | 1<br>Selection of<br>Control Signal | 2<br>Selection of<br>Flow Characteristic |
|---------------------------------|-------------------------------------|--|
| ON                              | 4 to 20 mA                          | Modified*                                |
| OFF<br>Factory Setting          | 0 to 10 Vdc                         | Default                                  |

<sup>\*</sup>Changing the default setting will modify an equal percentage valve to a linear flow characteristic. When set to default, the flow characteristic is determined by the valve body.

#### **Normally Closed Valve**

Actuator pressure cylinder moves:

- Outward (0 to 1): Valve opens.
- Inward (1 to 0): Valve closes.

#### **Normally Open Valve**

Actuator pressure cylinder moves:

- Outward (0 to 1): Valve closes.
- Inward (1 to 0): Valve opens.

### **Three-Way Valve**

Actuator pressure cylinder moves

- Outward (0 to 1): Valve opens between port NC and C.
- Inward (1 to 0): Valve opens between ports NO and C.

The measuring voltage at terminal U provides valve stem position feedback to an indicating instrument or building automation system.

# Manual Operation \*\*Sax360 \*\*CAUTO\*\*\* \*\*Figure 12. The Manual Setting Knob in Manual and Automatic Position. - Turn the manual setting knob clockwise for manual operation. - A red indicator becomes visible as you begin to crank. Each complete revolution.

- A red indicator becomes visible as you begin to crank. Each complete revolution (360°) is equal to 3/32-inch (2.5 mm) stroke.
- If a signal is sent to the actuator while it is in manual operation, the actuator will move but the control will not be accurate.
- The valve cannot be commanded to its 0% position while in manual operation.

#### **Automatic operation**

For automatic operation the manual override knob must be in the fully closed position.

Turn the manual override knob counterclockwise until the red indicator disappears.

## Wiring

Do not use autotransformers. Use earth ground isolating step-down Class 2 power supplies.

Determine supply transformer rating by summing total VA of all actuators used.

The maximum rating for Class 2 step-down transformer is 100 VA.

- Since SKD6xU actuators require ≈20 VA, a maximum of four actuators can be powered by one transformer (80% of transformer VA).
- Operating more than four SKD6xU actuators requires additional transformers or separate 100 VA power supplies.
- The position output signal U will switch from 0 to 10 Vdc to 4 to 20 mA when a 4 to 20 mA input signal is selected and used on the Y terminal.

Page 8 Siemens Industry, Inc.

# **Wiring Diagrams**





Figure 13. Connecting Terminals.

| 24 Vac |   |  |
|--------|---|--|
| G      | System Potential (SP)   |  |
| G0     | System Neutral (SN)   |  |
| Υ      | Control input 0 to 10 Vdc or 4 to 20 mA (DIP switch selectable) |  |
| М      | Measuring neutral   |  |
| U      | Position indication 0 to 10 Vdc or 4 to 20 mA, (see Table 2.    |  |
| Z      | Override control  |  |

Table 2.

|                       | Receiving Impedance |                 |  |
|-----------------------|---------------------|-----------------|--|
| Actuator input signal | Low (<500 Ohm)      | High (>10K Ohm) |  |
| 0 to 10 Vdc           | 0 to 20 mA          | 0 to 10 Vdc     |  |
| 4 to 20 mA            | 4 to 20 mA          | 2 to 10 Vdc     |  |






Figure 14. Auxiliary Switch ASC1.6.

Figure 15. Packing Heating Element 599-00417.


# **Troubleshooting**

Check that the wires are connected correctly and attached securely.

Check for adequate power supply.

Check that the actuator is set for automatic operation. See the *Start-Up* section.

## **Dimensions**






Figure 16. Dimensions of 599-10071 Weather Shield in Inches (Millimeters).

Page 10 Siemens Industry, Inc.




Figure 17. Dimensions of SKD6xU Actuators.

Information in this publication is based on current specifications. The company reserves the right to make changes in specifications and models as design improvements are introduced. Flowrite is a trademark of Siemens Industry, Inc. Other product or company names mentioned herein may be the trademarks of their respective owners. © 2013 Siemens Industry, Inc.