

PFXT



Thermal Expansion Tanks

Product Features

- Diaphragm-type
- Pre-pressurized expansion tank
- Designed for potable hot water systems
- Eliminates relief valve spills
- Controls pressure build-up
- Protects plumbing fixtures
- Extends water heater life
- Eliminates hot water waste
- Factory precharged to 40 PSI
- Made in USA
- Low lead compliant
- 3/4" SS NPTM connection


Product Specifications

Model No.	Total Volume Gals.	Max Accept. Factor	Diameter A	Height B	System Connection	Ship Weight Lbs.
PFXT5	2.0	.45	8"	12-5/8"	3/4" NPTM	5
PFXT12	4.4	.73	11"	15"	3/4" NPTM	9

Water Heater Size/Volume	130°F				140°F				160°F				180°F			
	130°F	140°F	160°F	180°F	130°F	140°F	160°F	180°F	130°F	140°F	160°F	180°F	130°F	140°F	160°F	180°F
30 gallons	PFXT5	PFXT5	PFXT5	PFXT5												
40 gallons	PFXT5	PFXT5	PFXT5	PFXT5												
50 gallons	PFXT5	PFXT5	PFXT5	PFXT12												
60 gallons	PFXT5	PFXT5	PFXT5	PFXT12												
80 gallons	PFXT5	PFXT12	PFXT12	PFXT12												
100 gallons	PFXT12	PFXT12	PFXT12	*												
120 gallons	PFXT12	PFXT12	PFXT12	*												
150 gallons	PFXT12	PFXT12	*	*												
175 gallons	PFXT12	*	*	*												



PFXT5



Maximum Operating Conditions

Operating Temperature - 200°F

Working Pressure - 150 psig (10.5 kg/cm²)

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO tanks carry a 1-year limited warranty. NSF 61 approved.

