Rinnai. SENSEI


RESIDENTIAL (WITH RECIRCULATION PUMP)



CIRC-LOGIC[™] RECIRCULATION TECHNOLOGY

Rinnai Circ-Logic[™] recirculation technology allows users to set recirculation patterns that coincide with their hot water usage patterns. Hot water is available when needed, without the expense of circulating it during times of inactivity. Two recirculation modes are available:

- **Dedicated Mode** With a dedicated return line, the integrated pump recirculates water from the tankless water heater through the return line and back to the heater.
- **Crossover Mode** In applications where a dedicated return line is not available or is difficult to install, ThermaCirc360[™] technology allows for the simple installation of a **Thermal Bypass Valve** (included with purchase) at the fixture farthest away from the water heater.



EASE OF INSTALLATION AND SERVICEABILITY

- Compact Design to Save Space
- Wi-Fi Technology for Remote Monitoring and Management
- Simple Gas Conversion

SUPER-HIGH-EFFICIENCY (CONDENSING) TANKLESS WATER HEATER		
Installation Type	External (Outdoor) Residential Applications	
Model Numbers	RUR199e (REU-NP3237W-US) RUR160e (REU-NP2530W-US)	
Approved Gas Types	Natural and Propane	
Uniform Energy Factor (UEF)	0.92	
Energy Factor (EF)	0.95	
High Altitude Approved	Up to 10,200 Ft (3,109 M)	
Water Flow Control	Water Flow Sensor, Electronic Water Control and Bypass Control	
Controller	Standard: MC-91-2US Required for Recirculation: MC-195T-US or Control-R™ Wi-Fi Module	
Certifications	AHRI, ANSI Z21.10.3, CSA 4.3, and Energy Star®	

Warranty

- Heat Exchanger: 15 years or 12,000 operation hours, whichever occurs first
- All Other Parts and Components: 5 Years
- Reasonable Labor: 1 Year

Safety Devices

Flame Failure - Flame Rod, Boiling Protection, Combustion Fan RPM Check, Over Current - Glass Fuse, Remaining Flame (OHS) and Automatic Frost Protection

Included with Purchase

Tankless Water Heater, Thermal Bypass Valve, Pressure Relief Valve and Adapter, Isolation Valve Kit, Integrated Controller, and Recirculation Pump Cable

Additional Features

- Complies with South Coast Air Quality Management District 14 ng/J or 20 ppm NOx Emission Levels
 - Ultra Low NOx
 - Tankless Rack System[™] Compatible
 - 1/2 in. (13 mm) Gas Line Compatible

OPTIONAL ACCESSORIES

Room Air Screen, Condensate Neutralizer, ScaleCutter, Drain Down Kit, Additional Controllers, Pipe Cover, Recirculation Pump, DPS/MIS Switch, EZ Connect Cables, Control-R[™] WI-FI Module, Wireless Accessories, and many more. Visit rinnai.us for a complete list of accessories.




CERTIFIED TO ANSI Z21.10.3 - CSA 4.3


SENSEI[™] TECHNICAL SPECIFICATIONS

SPECIFICATION		RUR199e	RUR160e	
Dimensions - w, h, d		18.5 in. x 26.4 in. x 11.4 in.	(470 mm x 670 mm x 290 mm)	
Minin Btu/h	num Gas Consumption	15,000		
Maximum Gas Consumption Btu/h		199,000	160,000	
Flow Rate ¹ (Min - Max)		0.26 - 9.8 GPM (1.0 - 37 L/min)	0.26 - 8.0 GPM (1.0 - 30 L/min)	
Max Flow Rate with Parameter Adjustment		11 GPM (42 L/min)	9 GPM (34 L/min)	
Weight		73 lb (33 kg)	71 lb (32 kg)	
Sound Level		53 dB	52 dB	
	Normal	81 W	49 W	
cal	Standby	1.3 W		
Electrical	Freeze Protection	198 W		
	Max Current	4 Amps		
	Fuse	10 Amps		
Temperature		 Minimum: 98° F (37° C) Default 120° F (49° C) Crossover Mode Maximum: 120° F (49° C) Default 140° F (60° C) With Parameter Adjustment 		
By-Pass Flow Control		Electronic		
Gas Supply Pressure ²		 Natural: 3.5 in. w.c 10.5 in. w.c. Propane: 8.0 in. w.c 13.5 in. w.c. 		
Ignition System		Direct Electronic Ignition		
Electr	 Appliance: AC 120 Volts, 60Hz. Temperature Controller: DC 12 Volts (Digital) 		Volts (Digital)	
Wate	r Supply Pressure	 Minimum: 50 PSI (Recommended 60-80 PSI for max performance) Maximum: 150 PSI 		
Contr	oller Cable	Cable Non-Polarized Two Core Cable (Minimum 22 AWG)		
 Gas Supply: 3/4 in. (19 mm) NPT Cold Water Inlet: 3/4 in. (19 mm) NPT Hot Water Outlet: 3/4 in. (19 mm) NPT Condensate Drain: 1/2 in. (13 mm) NPT 		m) NPT nm) NPT		
• Top: 2 in. (51 mm)* • Back: 0 in. Clearances • Bottom/Ground: 12 in. (305 mm) • Sides: 2 in. (51 mm)*** • Front: 0 in.** • Front Exhaust: 24 in. (6)				

SENSEI[™] DIMENSIONS

in. (mm)






0 in. from vent components

** Clearance for servicing is 24 in. (610 mm) in front of water heater *** Add 0.25 in. (6.35 mm) for recess box


¹ Minimum flow may vary slightly depending on the temperature setting and the inlet water temperature. Minimum activation flow is 0.4 GPM (1.5 L/min).
 ² The maximum gas supply pressure must not exceed the value specified by the manufacturer.


SENSEI[™] WATER FLOW CURVE

Flow curves apply only to incoming water temperatures of 70° F (21° C) or less. For incoming water temperatures greater than 70° F (21° C), please contact Rinnai.










Rinnai America Corporation • 103 International Drive, Peachtree City, GA 30269 • 1-800-621-9419 • rinnai.us ©2017 Rinnai America Corporation. Rinnai America Corporation continually updates materials, and as such, content is subject to change without notice.

SENSEI[™] PUMP PERFORMANCE AND PUMP + TANKLESS PERFORMANCE CURVE



The RUR pump has an operation range of 1.05 GPM to 5.30 GPM

Internal Recirculation Pump Control Internal Pump

Maximum Recirculation Pipe Lengths

Built-in Rinnai Circ-Logic™: Recirculation program cycles internal pump

Integrated pump and bypass technology allow for recirculation through a dedicated return line or thermal bypass valve.

- 400 equivalent feet for 3/4" pipe diameter
 - 100 equivalent feet for 1/2" pipe diameter

Take equivalent elbow lengths into consideration when calculating pipe length.

For dedicated return lines: Total length includes both hot water supply and dedicated return lines.

Cross-over mode: Total length includes both hot water supply and cold water piping length from the tankless water heater to the thermal bypass valve. Cross-over mode requires the use of a thermal bypass valve (included).