Electronic Exposed TECK® Flush Valve





□ 81T201HWA-DF

Exposed Hardwire Operated 1-1/2" Top Inlet Closet Fixture

- Polished chrome-plated vandal resistant metal cover with top mounted sensor operated H₂Oprics^o electronics
- Right or left-hand supply installation
- · ADA compliant, automatic operation hardwire powered infrared sensor
- Scratch resistant replaceable lens window
- Supplied with an advanced infrared sensor activated flush system that uses precise
 user distance measurements along with a bowl length setting to activate the correct
 flush for each usage
- Hardwire adaptor 24 VAC to 6.4 VDC converter (supplied)
- Vandal resistant copper tube conduit
- · Override button activation will always produce a full flush
- Optional 24 hour automatic flush factory set to OFF
- Set-up sensor range adjustment indicator lights
- · 24 VAC input, 6 second arming delay
- Electronic operated non-hold-open **metal** override button with 5 second lockout
- (110 to 24 VAC Transformer not included. See selection below for additional part number.)
- Quiet action, TECK® exposed diaphragm flush valve
- Chloramine resistant diaphragm
- · Forged brass diaphragm retainer
- Renewable seat
- · Polished chrome-plated body
- External water conserving flush adjustment, factory set to 6 litre (1.6 gal.)
- Optional dual flush setting capability factory set to on providing average 30% water reduced flush based on time and distance
- 1" FIP/Copper sweat inlet adaptor, angle check stop with protecting cap
- Adjustable 121mm (4-3/4") plus or minus 11mm (7/16") inlet/valve outlet centers
- · Vacuum breaker
- Cover tube, stainless steel wall flange, spud flange, concealed spud nut, and 292mm (11-1/2") outlet tube
- · Recommended water supply:

Minimum flowing pressure – 25 psi (172 kPa) Minimum flow rate – 25 gpm (95 L/min)

APPROVALS:

- IAPMO listed to ASSE 1037/ ASME A112.1037/CSA B125.37
- Landicates compliance to ICC/ANSI A117.1

(Contact Delta Representative for State and/or Local Approvals.)

Patented



Engineer/Architect Approval Model Specified: Approval: Date:




AVAILABLE OPTIONS FOR FIELD CONVERSION

☐ 061047A

Hardwire with Battery Backup

See **DSP-BB** for detailed specification.

V	TRANSFORMERS	
	060704A	110 to 24 VAC Class 2 20 VA (for up to 5 Electronic Valves)
	060771A	110 to 24 VAC Class 2 40 VA (for up to 10 Electronic Valves)



Note: For high and low pressure applications, please see page FEA-81T High Water Pressure note for more details.

Verify flow requirements with bowl manufacturer.

Note: Measurements may vary \pm 6mm (0.25")

Refer to www specselect com for individual models.

Note: Use this page as a product submittal sheet.

Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability