





Architect/Engineering Specifications:

Ledge mounted double pedal valve with chrome plated solid brass body, adjustable height aluminum pedals, self-closing valves, 1/2" NPT female inlets, 1/2" NPT female outlet and mounting screws. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372.





- Ledge mounted double pedal valve w/ polished chrome plated brass body
- Adjustable height hot and cold pedals
- Pedals flip up for floor cleaning
- Metering cartridges
- Adjustable metering cycle 10 to 30 seconds
- 1/2" NPT female inlets and outlet
- Includes mounting screws
- Material: Polished chrome brass body, satin finish aluminum pedals

Optional Cartridges

- Fast Self-Closing Cartridge
- □ Slow Self-Closing Cartridge (Standard)

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)

Warranty: One Year (Limited)

Performance Data:

- Pressure: 20 125 psi
- Temperature: 40 °F 140 °F
- Flow Rate: 6.92 GPM @ 60 psi
- Water Consumption: @ 10 sec = 1.2 gal
 @ 15 sec = 1.7 gal







