
INSTRUCTIONS FOR MODELS

S-4000 -E2 -E175 -E15 **S-4001** -E2 -E175 -E15 **S-4002** -E2 -E175 -E15



NEED HELP?

For additional assistance or service please contact:


SPEAKMAN® Company 400 Anchor Mill Road New Castle, DE 19720

ع 800-537-2107


customerservice@speakman.com

www.speakman.com







Apply Teflon Tape to the outlet side of shower arm in a clockwise direction.



ROUGH IN DIMENSIONS





DIMENSIONS SUBJECT TO CHANGE WITHOUT NOTICE.

Standard Model Flow Data:

Max Flow Rate: 2.5 gpm (9.5 L/min) FOR USE WITH AUTOMATIC COMPENSATING VALVES RATED AT 7.6 L/MIN (2.0 GPM) OR LESS.

E2 Model Flow Data:

Max. Flow Rate: 2.0 gpm (7.6 L/min) Min. Flow Rate: 1.5 gpm (5.7 L/min) @ 45psi FOR USE WITH AUTOMATIC COMPENSATING VALVES RATED AT 6.6 L/MIN (1.75 GPM) OR LESS.

E175 Model Flow Data:

Max. Flow Rate: 1.75 gpm (6.6 L/min) Min. Flow Rate: 1.3 gpm (4.9 L/min) @ 45psi FOR USE WITH AUTOMATIC COMPENSATING VALVES RATED AT 5.7 L/MIN (1.5 GPM) OR LESS.

E15 Model Flow Data:

Max. Flow Rate: 1.5 gpm (5.7 L/min) Min. Flow Rate: 1.1 gpm (4.2 L/min) @ 45psi FOR USE WITH AUTOMATIC COMPENSATING VALVES RATED AT 5.2 L/MIN (1.37 GPM) OR LESS.