Shark Bite Plumbing Solutions

SharkBite® Hose Bibbs

DESCRIPTION

SharkBite® hose bibbs are outdoor hose faucets for use in residential or commercial applications.

FEATURES AND BENEFITS

Instant push-fit connection for increased ease-of use:

No soldering, clamps, unions, or glue required.

Patent Pending:


One piece integrated flange and push-to-connect fitting

Integral tube liner for PEX installations:

Means no loose components and ensures a secure, reliable connection.

DIMENSIONAL DATA







SKU	Description	Α	В
24632LF	1/2" X 3/4" MHT - No Kink	3.12	3.45
24633LF	3/4" X 3/4" MHT - No Kink	3.12	3.45









SharkBite® Hose Bibbs

90º Multi Turn



SKU	Description	Α	В
24626LF	1/2" X 3/4" MHT	3.45	3.75
24627LF	3/4" X 3/4" MHT	3.45	3.75

45º 1/4 Turn




SKU	Description	Α	В
24630LF	1/2" X 3/4" MHT - No Kink	3.00	3.45
24631LF	3/4" X 3/4" MHT - No Kink	3.00	3.45





SharkBite® Hose Bibbs

90º 1/4 Turn




SKU	Description	Α	В
24620LF	1/2" X 3/4" MHT	3.00	3.45
24621LF	3/4" X 3/4" MHT	3.00	3.45

PERFORMANCE DATA

Pressure and Temperature Performance:

- Max working pressure 200 psi
- Max working temperature 200°F
- Min working temperature 33°F







SharkBite® Hose Bibbs

Washer.....EPDM Screw.....Brass

Material:

Hose bibbs are approved for potable water and glycol (up to 100% mix)


Valve Material:

•	Body	Lead Free DZR Brass
•	O-ring	EPDM
•	Grab Ring	Stainless Steel Grade 316
•	Tube Support Liner	Veradel
	1/4 Turn Hose Bibb:	
•	Ball	Chrome Plated DZR Lead Free Brass
•	Seat Seal	PTFE
•	O-Ring	EPDM
•	Stem	DZR Brass
	Multi-Turn:	
•	Stem	DZR Brass

Compatible pipes:

Hose bibbs are approved for use ASTM F876/CSA B137.5 PEX, ASTM B88 Type K, L and M and copper, ASTM D2846/CSA B137.6 CPVC, and ASTM F2769 PE-RT

TYPICAL INSTALLATION



CERTIFICATIONS

SharkBite hose bibbs are approved for use in all national and local codes in the US and Canada. Certified and listed to the following standards:

- ASME A112.18.1/CSA B125.1 Plumbing Supply Fittings
- ANSI/NSF 61 Drinking Water System Components Health Effects
- ASI/NSF 372 Drinking Water Components Lead Content

SPECIFICATION

The tube shall be inserted into the SharkBite® push-to-connect (PTC) fitting in the first stage through a release collar and then through a stainless steel grab ring. The grab ring has teeth that open out and grip onto the tube. At the second stage the tube shall be pushed through an O-ring protector which aligns the tube. A specially formulated EPDM O-ring shall be compressed between the wall of the fitting and the tube before the end of the tube reaches the tube stop. Only when the tube has passed through the O-ring and reached the tube stop shall a secure joint be created. The fitting shall be a SharkBite PTC fitting.

Job Name:	
Job Location:	
Engineer	
Contractor:	
Tag:	





www.sharkbite.com · 2727 Paces Ferry Road · Building 2 · Suite 1800 · Atlanta · Georgia 30339 · USA US Contact: 1-877-700-4242 · customerservice@sharkbite.com · Canadian Contact: 1-888-820-0120 · canadasales@rwc.com