# PCA® Perlator®

## Faucet Aerator - 1.2 gpm max

## Pressure Compensating Regular Size



flow, stop and go®

#### **Features and Benefits**

- Watercolours® design: Color coding to identify flow rate and stream pattern.
- Patented construction provides a splash-free stream, well-aerated and soft to the touch.
- Pressure compensating for constant flow from 20 to 80 psi.
- Integrated anti-liming honeycomb replaces conventional wire mesh screens prone to lime build up.
- Anti-clogging dome screen filters sediment and particles.
- Compatible with regular and vandal proof M22 & M24 metric housings.
- Available housing finishes: chrome, polished brass, brushed nickel, and oil rubbed bronze.
- Laser marked housings with statutory marks.

### Certifications


ANSI/NSF®-61-372

ASME A112.18.1M and CSA B125

Meets CALGreen requirements

WaterSense

Complies with CEC Amendment to CCR Title 20, section 1605.3




Thread & Part Number			
Part #	Designation Thread Size		
14 535	Insert only		
14 500	Regular male	15/16"-27	
14 510	Regular female	55/64"-27	
14 520	Regular dual thread	15/16"-27 x 55/64" -27	
14 504	Vandal proof regular male	15/16"-27	
14 514	Vandal proof regular female	55/64"-27	
14 526	Vandal proof regular dual thread	15/16"-27 x 55/64"-27	

Other product combinations available.


_								
P	a	^	k:	n	П	n	a	ė
	u	•	176	49	ш	ш	9	В

1 pc (bag), 6 pcs (tube), 50 pcs (bag) Inserts Reg. male/female/dual thread 1 pc (bag), 6 pcs (tube), 50 pcs (tray) Reg. vandal proof male/female/dual thread 1 pc (bag), 6 pcs (tube), 40 pcs (tray)

Color Code			
Dome	Flow Regulator	Basket	
Natural	Pink	Dark Gray	







Dimensions					
No	mm	In			
А	20.88	.822			
В	12.00	.472			
С	19.97	.786			
D	≈ 13	≈ 1/2			



Technical Data						
Materials: Body		Acetal				
	0-ring	EPDM				
Washer		EPDM				
Conti	nuous	Short-term (5 minutes max.) Per ASME A112.18.1 testing requirements.				
max. 120		70 max. 160				
°C 🔵 °F	80 psi = 5.5 bar max.	°C 🔵 °F	125 psi 8.5 bar max.			