



SUBMITTAL DATA - I-P UNITS Unit Designation: _____ Job Name:_____ Architect: _____ Engineer:_____ Contractor: PERFORMANCE DATA Cooling Capacity: _____ Btuh EER: Heating Capacity: _____ Btuh COP: _____ Ambient Air Temp: _____ °F Entering Water Temp (Clg): °F °F Entering Air Temp (Clg): Entering Water Temp (Htg): _____ °F Entering Air Temp (Htg): ____ °F Airflow: _____ CFM Fan Speed or Motor/RPM/Turns: Operating Weight: _____ (lb) ELECTRICAL DATA Power Supply: Volts Phase Hz Minimum Circuit Ampacity:_____ Maximum Overcurrent Protection:





SUBMITTAL DATA - S-I UNITS Unit Designation: _____ Job Name:_____ Architect: _____ Engineer:_____ Contractor: PERFORMANCE DATA Cooling Capacity: _____ kW EER: Heating Capacity: kW COP: _____ °C Ambient Air Temp: _____ Entering Water Temp (Clg): _____ °C °C Entering Air Temp (Clg): Entering Water Temp (Htg): _____ °C Entering Air Temp (Htg): °C Airflow: l/s Fan Speed or Motor/RPM/Turns:_____ Operating Weight: (kg) ELECTRICAL DATA Power Supply: Volts Phase Hz Minimum Circuit Ampacity:_____ Maximum Overcurrent Protection:

Table of Contents

| UNIT FEATURES |
|---|
| SELECTION PROCEDURE |
| TC Series Nomenclature |
| PERFORMANCE DATA - AHRI/ASHRAE/ISO 13256-18 |
| Performance Data - Selection Notes |
| PERFORMANCE DATA - TC H/V 006 |
| Performance Data - TC H/V 00911 |
| PERFORMANCE DATA - TC H/V 01212 |
| PERFORMANCE DATA - TC H/V 015 |
| Performance Data - TC H/V 018 |
| Performance Data - TC H/V 024 |
| Performance Data - TC H/V 030 |
| Performance Data - TC H/V 036 |
| Performance Data - TCV 041 |
| Performance Data - TC H/V 042 |
| Performance Data - TC H/V 048 |
| Performance Data - TC H/V 060 |
| AIR FLOW CORRECTION TABLE |
| ANTIFREEZE CORRECTION TABLE |
| BLOWER PERFORMANCE DATA - STANDARD UNIT |
| BLOWER PERFORMANCE DATA - HIGH STATIC |
| PHYSICAL DATA |
| TC - Horizontal - Dimensional Data |
| TC - Vertical Upflow - Dimensional Data |
| CORNER WEIGHTS FOR TCH SERIES UNITS |
| ELECTRICAL DATA - STANDARD UNIT |
| ELECTRICAL DATA - HIGH STATIC BLOWER |
| TC Series Wiring Diagram Matrix |
| TYPICAL WIRING DIAGRAM - SINGLE PHASE TO UNITS WITH CXM CONTROLLER |
| TYPICAL WIRING DIAGRAM - SINGLE PHASE TO UNITS WITH DXM CONTROLLER |
| TYPICAL WIRING DIAGRAM - THREE PHASE 208/230V TC UNITS WITH CXM CONTROLLER |
| TYPICAL WIRING DIAGRAM - THREE PHASE 208/230V TC UNITS WITH DXM CONTROLLER |
| TYPICAL WIRING DIAGRAM - THREE PHASE 460/575V TC UNITS WITH CXM CONTROLLER |
| TYPICAL WIRING DIAGRAM - THREE PHASE 460/575V TC UNITS WITH DXM CONTROLLER |
| TYPICAL WIRING DIAGRAM - THREE PHASE 460/575V TC UNITS WITH CXM AND LON CONTROLLER 41 |
| TYPICAL WIRING DIAGRAM - THREE PHASE 460/575V TC UNITS WITH DXM & LON CONTROLLER 42 |
| TYPICAL WIRING DIAGRAM - THREE PHASE 460/575V TC UNITS WITH CXM & MPC CONTROLLER 43 |
| TYPICAL WIRING DIAGRAM - THREE PHASE 460/575V TC UNITS WITH DXM & MPC CONTROLLER 44 |
| Engineering Specifications |
| REVISION HISTORY |
| |

*Document page number is shown next to part number (e.g. LC405 - 3 = page 3). Since not all pages are typically used in the submittals process, the page number in the lower right corner can still be used (page _____0f____).

Unit Features

THE TRANQUILITY® 16 COMPACT (TC) SERIES

The award winning Tranquility[®] 16 Series raises the bar for water-source heat pump efficiencies, features and application flexibility. Not only does the Tranquility[®] 16 exceed ASHRAE 90.1 efficiencies, but it also uses EarthPure[®] HFC-410A zero ozone depletion refrigerant, making it an extremely environmentally-friendly option. Tranquility[®] 16 is eligible for additional LEED[®] (Leadership in Energy and Environmental Design) points because of the "green" technology design. With one of the smallest cabinets in the industry, the Tranquility[®] 16 will easily fit into tight spaces. Designed to be backward compatible with thousands of older water-source heat pumps, the Tranquility[®] 16 Compact Series heat pump is packed full of the innovation you have come to expect from the experts at ClimateMaster.

Available in sizes from 1/2 ton (1.76 kW) through 5 tons (17.6 kW) with multiple cabinet options (vertical upflow and horizontal) the Tranquility[®] 16 offers a wide range of units for most anaxy powder painted front access panel, galvanized steel with epoxy powder painted drain pan and sound absorbing air handler insulation are just some of the features of the Tranquility[®] 16 Series.

ClimateMaster's exclusive double isolation compressor mounting system makes the Tranquility® 16 the quietest unit on the market. Compressors are mounted on specially engineered sound-tested EPDM grommets or spring vibration isolators to a heavy gauge mounting plate, which is further isolated from the cabinet base with rubber grommets for maximized vibration/sound attenuation. The easy access control box and large access panels make installing and maintaining the unit easier than other water-source heat pumps currently in production, proving that a small unit can be easy to service.

Options such as coated air coil, DDC controls, high efficiency pleated MERV 11 two-inch (51mm) air filter or one-inch (25mm) pleated MERV 8 air filters allow customized design solutions. Optional high static fan motor expands the operating range and helps overcome some of the challenges associated with ductwork for retrofit installations. A cupro-nickel water-coil and sound absorbing mute package are options that make a great unit even better.

The Tranquility[®] 16 (TC) Series Water-Source Heat Pumps are designed to meet the challenges of today's HVAC demands with one of the most innovative products available on the market.

UNIT FEATURES

- Sizes 006 (1/2 ton, 1.76 kW) through 060 (5 tons, 17.6 kW)
- EarthPure[®] HFC-410A refrigerant
- Exceeds ASHRAE 90.1 efficiencies
- Galvanized steel construction with attractive matte black epoxy powder coat paint front access panel
- Epoxy powder painted galvanized steel drain pan
- Sound absorbing glass fiber insulation
- Unique double isolation compressor mounting via vibration isolating rubber grommets for quiet operation
- Insulated divider and separate compressor/air handler compartments
- Copeland scroll compressors (rotary for size 018 and below)
- TXV metering device
- Microprocessor controls standard (optional DXM and/ or DDC controls)
- Field convertible discharge air arrangement for horizontal units
- PSC three-speed fan motor
- Internally trapped condensate drain line (vertical units only)
- Unit Performance Sentinel performance monitoring system
- Eight Safeties Standard
- Extended range (20 to 120°F, -6.7 to 48.9°C) capable
- High static blowers available
- LonWorks, BACnet, Modbus and Johnson N2 compatibility options for DDC controls
- Cupro-nickel water-coil
- Sound absorbing UltraQuiet package

AVAILABLE OPTIONS

- High static blowers
- LonWorks, BACnet, Modbus and Johnson N2 compatibility options for DDC controls
- Cupro-nickel water-coil
- Sound absorbing UltraQuiet package
- Coated air coil

Selection Procedure

Reference Calculations

| Heating | Cooling | |
|--|--|-----------------------|
| $LWT = EWT - \frac{HE}{GPM \times 500}$ | LWT = EWT + $\frac{\text{HR}}{\text{GPM x 500}}$ | LC = TC - SC |
| LAT = EAT + $\frac{HC}{CFM \times 1.08}$ | LAT (DB) = EAT (DB) - <u>SC</u> CFM x1.08 | $S/T = \frac{SC}{TC}$ |

Legend and Glossary of Abbreviations

| BTUH = BTU(British Thermal Unit) per hour CFM = airflow, cubic feet/minute COP = coefficient of performance = BTUH output/BTUH input DB = dry bulb temperature (°F) EAT = entering air temperature, Fahrenheit (dry bulb/wet bulb) EER = energy efficiency ratio = BTUH output/Watt input MPT = male pipe thread ESP = external static pressure (inches w.g.) EWT = entering water temperature GPM = water flow in U.S. gallons/minute HE = total heat of extraction, BTUH HC = air heating capacity, BTUH HR = total heat of rejection, BTUH | HWC = hot water generator (desuperheater) capacity, Mbtuh FPT = female pipe thread KW = total power unit input, kilowatts LAT = leaving air temperature, °F LC = latent cooling capacity, BTUH LWT = leaving water temperature, °F MBTUH = 1000 BTU per hour S/T = sensible to total cooling ratio SC = sensible cooling capacity, BTUH TC = total cooling capacity, BTUH WB = wet bulb temperature (°F) WPD = waterside pressure drop (psi & ft. of hd.) |
|--|--|
|--|--|

Conversion Table - to convert inch-pound (English) to S-I (Metric)

| Air Flow | Water Flow | Ext Static Pressure | Water Pressure Drop |
|-----------------------------|---------------------------------|---------------------------------|---------------------------------|
| Airflow (L/s) = CFM x 0.472 | Water Flow (L/s) = gpm x 0.0631 | ESP (Pa) = ESP (in of wg) x 249 | PD (kPa) = PD (ft of hd) x 2.99 |

Selection Procedure

- Step 1 Determine the actual heating and cooling loads at the desired dry bulb and wet bulb conditions.
- Step 2 Obtain the following design parameters: Entering water temperature, water flow rate in GPM, air flow in CFM, water flow pressure drop and design wet and dry bulb temperatures. Air flow CFM should be between 300 and 450 CFM per ton. Unit water pressure drop should be kept as close as possible to each other to make water balancing easier. Go to the appropriate tables and find the proper indicated water flow and water temperature.
- Step 3 Select a unit based on total and sensible cooling conditions. Select a unit which is closest to, but no larger than, the actual cooling load.
- Step 4 Enter tables at the design water flow and water temperature. Read the total and sensible cooling capacities (Note: interpolation is permissible, extrapolation is not).
- Step 5 Read the heating capacity. If it exceeds the design criteria it is acceptable. It is quite normal for Water-Source Heat Pumps to be selected on cooling capacity only since the heating output is usually greater than the cooling capacity.
- Step 6 Determine the correction factors associated with the variable factors of dry bulb, wet bulb and air flow.

Corrected Total Cooling = tabulated total cooling x wet bulb correction x air flow correction

Corrected Sensible Cooling = tabulated sensible cooling x dry bulb correction x air flow correction

- Step 7 Compare the corrected capacities to the load requirements. Normally if the capacities are within 10% of the loads, the equipment is acceptable. It is better to undersize than oversize, as undersizing improves humidity control, reduces sound levels and extends the life of the equipment.
- Step 8 When completed, calculate water temperature rise and assess the selection. If the units selected are not within 10% of the load calculations, then review what effect changing the GPM, water temperature and/or air flow and air temperature would have on the corrected capacities. If the desired capacity cannot be achieved, select the next larger or smaller unit and repeat the procedure. Remember, when in doubt, undersize slightly for best performance.

Example Equipment Selection For Cooling

Step 1 Load Determination:

Assume we have determined that the appropriate cooling load at the desired dry bulb 80°F and wet bulb 65°F conditions is as follows:

| Total Cooling | 23,700 BTUH |
|-------------------|-------------------------------|
| • | |
| Entering Air Temp | 80°F Dry Bulb / 65°F Wet Bulb |

Step 2 Design Conditions:

Similarly, we have also obtained the following design parameters:

| Entering Water Temp | 90°F |
|--|----------|
| Water Flow (Based upon 10°F rise in temp.) | |
| Air Flow | .800 CFM |

Step 3, 4 & 5 HP Selection:

After making our preliminary selection (TC024), we enter the tables at design water flow and water temperature and read Total Cooling, Sens. Cooling and Heat of Rej. capacities:

| Total Cooling | 23,400 BTUH |
|-------------------|-------------|
| Sensible Cooling | |
| Heat of Rejection | |

Step 6 & 7 Entering Air and Airflow Corrections:

Next, we determine our correction factors.

| | Table | Ent Air | Air Flow | Corrected |
|-----------------|-------------|------------|---------------|--------------|
| Corrected Total | Cooling = | 23,400 × 0 |).9681 x 1.00 | 050 = 22,767 |
| Corrected Sens | s Cooling : | = 17,500 x | 1.1213 x 0.9 | 820 = 19,270 |
| Corrected He | at of Rej. | = 30,200 x | 0.9747 x 1.0 | 434 = 30,713 |

Step 8 Water Temperature Rise Calculation & Assessment:


Actual Temperature Rise......10.2°F

When we compare the Corrected Total Cooling and Corrected Sensible Cooling figures with our load requirements stated in Step 1, we discover that our selection is within +/- 10% of our sensible load requirement. Furthermore, we see that our Corrected Total Cooling figure is within 1,000 Btuh the actual indicated load.

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

of _

TC Series Nomenclature



Performance Data – AHRI/ASHRAE/ISO 13256-1

| | Water Loop Heat Pump | | | | Ground Water Heat Pump | | | | Ground Loop Heat Pump | | | | |
|---------|----------------------|---------------|------------------|------|------------------------|---------------|------------------|------|-----------------------|---------------|------------------|-----|--|
| Model | Cooling | g 86°F | Heating | 68°F | Cooling | g 59°F | Heating | 50°F | Cooling | 77°F | Heating 32°F | | |
| | Capacity Btuh | EER Btuh/W | Capacity Btuh | СОР | Capacity Btuh | EER Btuh/W | Capacity Btuh | СОР | Capacity Btuh | EER Btuh/W | Capacity Btuh | СОР | |
| TC-006 | 5,800 | 13.2 | 7,500 | 4.7 | 6,900 | 21.1 | 6,200 | 4.0 | 6,200 | 15.4 | 4,900 | 3.4 | |
| TC-009 | 8,800 | 13.4 | 11,600 | 4.2 | 10,100 | 21.0 | 9,800 | 3.9 | 9,300 | 15.7 | 7,900 | 3.4 | |
| TC-012 | 11,700 | 13.5 | 15,200 | 4.3 | 13,700 | 20.8 | 12,500 | 3.8 | 12,000 | 14.9 | 9,900 | 3.2 | |
| TC-015 | 14,500 | 15.4 | 17,300 | 5.0 | 16,800 | 24.5 | 14,400 | 4.4 | 15,000 | 17.2 | 11,100 | 3.6 | |
| TC-018 | 17,300 | 14.3 | 21,500 | 5.0 | 20,600 | 24.2 | 17,200 | 4.4 | 18,400 | 16.3 | 13,900 | 3.4 | |
| TC-024 | 23,700 | 13.4 | 28,500 | 4.7 | 26,700 | 20.9 | 24,000 | 4.1 | 24,900 | 15.4 | 18,500 | 3.3 | |
| TC-030 | 28,100 | 13.4 | 35,100 | 4.6 | 31,700 | 20.1 | 29,600 | 4.1 | 28,900 | 15.1 | 23,400 | 3.4 | |
| TC-036 | 34,500 | 13.5 | 45,200 | 4.4 | 38,700 | 20.7 | 37,500 | 4.0 | 35,300 | 14.9 | 29,600 | 3.3 | |
| TCV-041 | 36,500 | 13.1 | 45,700 | 4.2 | 41,400 | 19.7 | 38,000 | 3.7 | 38,000 | 14.8 | 30,100 | 3.1 | |
| TC-042 | 40,100 | 13.1 | 52,700 | 4.3 | 45,900 | 19.6 | 44,000 | 3.8 | 40,500 | 14.4 | 34,300 | 3.2 | |
| TC-048 | 47,700 | 13.3 | 55,900 | 4.7 | 54,300 | 20.5 | 46,500 | 4.1 | 49,000 | 14.7 | 36,400 | 3.4 | |
| TC-060 | 59,400 | 13.4 | 77,000 | 4.3 | 66,600 | 19.9 | 64,000 | 3.8 | 60,100 | 14.8 | 50,500 | 3.1 | |

ASHRAE/AHRI/ISO 13256-1. English (I-P) Units

Cooling capacities based upon 80.6°F DB, 66.2°F WB entering air temperature Heating capacities based upon 68°F DB, 59°F WB entering air temperature

All ratings based upon operation at lower voltage of dual voltage rated models

ASHRAE/AHRI/ISO 13256-1. Metric (S-I) Units

| | Water Loop Heat Pump | | | | Ground Water Heat Pump | | | | Ground Loop Heat Pump | | | | |
|---------|----------------------|------------|----------------|------|------------------------|--------------|----------------|--------------|-----------------------|--------------|----------------|-------------|--|
| Model | Cooling | g 30°C | Heating | 20°C | Coolin | Cooling 15°C | | Heating 10°C | | Cooling 25°C | | Heating 0°C | |
| | Capacity kW | EER W/W | Capacity kW | СОР | Capacity kW | EER W/W | Capacity kW | СОР | Capacity kW | EER W/W | Capacity kW | СОР | |
| TC-006 | 1.70 | 3.9 | 2.20 | 4.7 | 2.02 | 6.2 | 1.82 | 4.0 | 1.82 | 4.5 | 1.44 | 3.4 | |
| TC-009 | 2.58 | 3.9 | 3.40 | 4.2 | 2.96 | 6.2 | 2.87 | 3.9 | 2.72 | 4.6 | 2.31 | 3.4 | |
| TC-012 | 3.43 | 4.0 | 4.45 | 4.3 | 4.01 | 6.1 | 3.66 | 3.8 | 3.52 | 4.4 | 2.90 | 3.2 | |
| TC-015 | 4.25 | 4.5 | 5.07 | 5.0 | 4.92 | 7.2 | 4.22 | 4.4 | 4.39 | 5.0 | 3.25 | 3.6 | |
| TC-018 | 5.07 | 4.2 | 6.30 | 5.0 | 6.04 | 7.1 | 5.04 | 4.4 | 5.39 | 4.8 | 4.07 | 3.4 | |
| TC-024 | 6.94 | 3.9 | 8.35 | 4.7 | 7.82 | 6.1 | 7.03 | 4.1 | 7.30 | 4.5 | 5.42 | 3.3 | |
| TC-030 | 8.23 | 3.9 | 10.28 | 4.6 | 9.29 | 5.9 | 8.67 | 4.1 | 8.47 | 4.4 | 6.86 | 3.4 | |
| TC-036 | 10.11 | 4.0 | 13.24 | 4.4 | 11.34 | 6.1 | 10.99 | 4.0 | 10.34 | 4.4 | 8.67 | 3.3 | |
| TCV-041 | 10.69 | 3.8 | 13.39 | 4.2 | 12.13 | 5.8 | 11.13 | 3.7 | 11.13 | 4.3 | 8.82 | 3.1 | |
| TC-042 | 11.75 | 3.8 | 15.44 | 4.3 | 13.45 | 5.7 | 12.89 | 3.8 | 11.87 | 4.2 | 10.05 | 3.2 | |
| TC-048 | 13.98 | 3.9 | 16.38 | 4.7 | 15.91 | 6.0 | 13.62 | 4.1 | 14.36 | 4.3 | 10.67 | 3.4 | |
| TC-060 | 17.40 | 3.9 | 22.56 | 4.3 | 19.51 | 5.8 | 18.75 | 3.8 | 17.61 | 4.3 | 14.80 | 3.1 | |

Cooling capacities based upon 27°C DB, 19°C WB entering air temperature Heating capacities based upon 20°C DB, 15°C WB entering air temperature All ratings based upon operation at lower voltage of dual voltage rated models

Performance Data – Selection Notes

For operation in the shaded area when water is used in lieu of an antifreeze solution, the LWT (Leaving Water Temperature) must be calculated. Flow must be maintained to a level such that the LWT is maintained above 40°F [4.4°C] when the JW3 jumper is not clipped (see example below). Otherwise, appropriate levels of a proper antifreeze solution should be used in systems with leaving water temperatures of 40°F or below and the JW3 jumper should be clipped. This is due to the potential of the refrigerant temperature being as low as 32°F [0°C] with 40°F [4.4°C] LWT, which may lead to a nuisance cutout due to the activation of the Low Temperature Protection. JW3 should never be clipped for standard range equipment or systems without antifreeze.

Example:

At 50°F EWT (Entering Water Temperature) and 2.25 gpm/ ton, a 3 ton unit has a HE of 27,300 Btuh. To calculate LWT, rearrange the formula for HE as follows:

 $HE = TD \times GPM \times 500$, where HE = Heat of Extraction (Btuh); TD = temperature difference (EWT - LWT) and GPM = U.S. Gallons per Minute.

TD = HE / (GPM x 500)

TD = 27,300 / (6.75 x 500)

 $TD = 8^{\circ}F$

LWT = EWT - TD

 $LWT = 50 - 8 = 42^{\circ}F$

In this example, as long as the EWT does not fall below 50°F, the system will operate as designed. For EWTs below 50°F, higher flow rates will be required (open loop systems, for example, require at least 2 gpm/ton when EWT is below 50°F).

| | | | | \sim | | | |
|-----|------|----------------|------|-----------|----------|-----|--------|
| | | \square | | Heating - | EAT 70°F | | \geq |
| | | Airflow CFM | нс | kW | HE | LAT | COP |
| | | 860 | 22.6 | 2.67 | 14.1 | 94 | 2.49 |
| | | 1150 | 23.2 | 2.39 | 15.1 | 89 | 2.84 |
| | 23.8 | 860 | 25.6 | 2.80 | 16.6 | 98 | 2.68 |
| | 23.8 | 1150 | 26.2 | 2.51 | 17.7 | 91 | 3.06 |
| þ | 24.7 | 860 | 26.8 | 2.85 | 17.6 | 99 | 2.76 |
| .4 | 24.7 | 1150 | 27.5 | 2.56 | 18.8 | 92 | 3.15 |
| 6.5 | 25.0 | 860 | 27.5 | 2.88 | 18.2 | 100 | 2.80 |
| 7.3 | 25.0 | 1150 | 28.2 | 2.59 | 19.4 | 93 | 3.19 |
| 5.3 | 21.8 | 860 | 30.1 | 2.98 | 20.3 | 102 | 2.95 |
| '.1 | 21.8 | 1150 | 30.8 | 2.68 | 21.7 | 95 | 3.37 |
| .5 | 23.3 | 860 | 31.6 | 3.05 | 21.6 | 104 | 3.04 |
| .4 | 23.3 | 1150 | 32.4 | 2.74 | 23.1 | 96 | 3.47 |
| .6 | 23.9 | 860 | 32.4 | 3.08 | 22.3 | 105 | 3.09 |
| .4 | 23.9 | 1150 | 33.2 | 2.77 | 23.8 | 97 | 3.52 |
| 7 | 19.2 | 860 | 34.5 | 3.16 | 24.1 | 107 | 3.20 |
| .5 | 19.2 | 1150 | 35.4 | 2.84 | 25.7 | 98 | 3.65 |
| 1 | 21.0 | 860 | 36.3 | 3.23 | 25.6 | 109 | 3.30 |
| 1 | 21.0 | 1150 | 37.2 | 2.90 | 27.3 | 100 | 3.76 |
| | 21.9 | 860 | 37.3 | 3.27 | 26.4 | 110 | 3.35 |
| | 21.9 | 1150 | 38.2 | 2.93 | 28.2 | 101 | 3.82 |
| | 16.4 | 860 | 38.9 | 3.32 | 27.8 | 112 | 3.43 |
| | 16.4 | 1150 | 39.8 | 2.99 | 29.7 | 102 | 3.91 |
| | ¥ | 860 | 40.9 | 3.40 | 29.5 | 114 | 3.53 |
| | | 1150 | 41.9 | 3.05 | 31.5 | 104 | 4.02 |
| | • | 860 | 42.0 | 3.44 | 30.4 | 115 | 2 |
| | | 150 | 43.0 | 3.09 | 32.5 | 105 | |
| | | | 43.1 | 3.47 | 31.4 | 110 | |
| | | | | 3.12 | 33.5 | | |

Performance Data – TC H/V 006

220 CFM Nominal (Rated) Airflow

Performance capacities shown in thousands of Btuh

| | | w | PD | | | Cooli | ng - EAT 80/ | 67°F | | | | He | ating - E | AT 70°F | = | |
|-----------|------------|------------|------------|----------------|------------|------------|-------------------|--------------|------------|--------------|----------------|------------|--------------|------------|----------------|------------|
| EWT °F | GPM | PSI | FT | Airflow CFM | тс | sc | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | нс | kW | HE | LAT | СОР |
| 20 | 1.5 1.5 | 1.7 1.7 | 4.0 4.0 | | Ope | ration | not recor | nmenc | ded | | 170 225 | 4.3 4.4 | 0.49 0.44 | 2.7 2.9 | 93.3 88.0 | 2.6 2.9 |
| | 0.8 | 0.5 | 1.2 | 170 | 7.4 | 4.2 | 0.57 | 0.28 | 8.4 | 26.4 | 170 | 4.6 | 0.50 | 3.0 | 95.2 | 2.7 |
| | 0.8 | 0.5 | 1.2 | 225 | 7.7 | 4.8 | 0.62 | 0.29 | 8.7 | 26.4 | 225 | 4.7 | 0.45 | 3.2 | 89.5 | 3.1 |
| 30 | 1.1 | 0.8 | 1.8 | 170 | 7.4 | 4.1 | 0.55 | 0.26 | 8.3 | 28.5 | 170 | 4.8 | 0.51 | 3.2 | 96.2 | 2.8 |
| | 1.1 | 0.8 | 1.8 | 225 | 7.7 | 4.6 | 0.60 | 0.27 | 8.6 | 28.5 | 225 | 4.9 | 0.46 | 3.4 | 90.3 | 3.2 |
| | 1.5 1.5 | 1.3 1.3 | 2.9 2.9 | 170 225 | 7.3 7.6 | 4.0 4.5 | 0.54 0.59 | 0.25 0.26 | 8.2 8.5 | 29.2 29.2 | 170 225 | 4.9 5.0 | 0.51 0.46 | 3.2 3.5 | 96.8 90.7 | 2.8 3.2 |
| | 0.8 | 0.4 | 0.9 | 170 | 7.3 | 4.3 | 0.59 | 0.20 | 8.3 | 23.2 | 170 | 5.3 | 0.40 | 3.6 | 98.8 | 3.0 |
| | 0.8 | 0.4 | 0.9 | 225 | 7.6 | 4.8 | 0.64 | 0.33 | 8.7 | 23.2 | 225 | 5.4 | 0.47 | 3.8 | 92.3 | 3.4 |
| 40 | 1.1 | 0.6 | 1.4 | 170 | 7.4 | 4.2 | 0.57 | 0.29 | 8.4 | 25.8 | 170 | 5.5 | 0.53 | 3.8 | 100.2 | 3.1 |
| 40 | 1.1 | 0.6 | 1.4 | 225 | 7.7 | 4.8 | 0.62 | 0.30 | 8.7 | 25.8 | 225 | 5.7 | 0.47 | 4.1 | 93.3 | 3.5 |
| | 1.5 | 1.0 | 2.4 | 170 | 7.4 | 4.2 | 0.56 | 0.28 | 8.4 | 26.9 | 170 | 5.7 | 0.53 | 3.9 | 100.9 | 3.1 |
| | 1.5 0.8 | 1.0 0.3 | 2.4 0.8 | 225 170 | 7.7 | 4.7 | 0.61 | 0.29 | 8.7 8.1 | 26.9 19.9 | 225 170 | 5.8 6.0 | 0.48 | 4.2 | 93.9 102.7 | 3.6 3.3 |
| | 0.8 | 0.3 | 0.8 | 225 | 7.2 | 4.8 | 0.66 | 0.36 | 8.5 | 19.9 | 225 | 6.1 | 0.48 | 4.5 | 95.3 | 3.7 |
| 50 | 1.1 | 0.5 | 1.2 | 170 | 7.2 | 4.3 | 0.59 | 0.32 | 8.3 | 22.5 | 170 | 6.3 | 0.55 | 4.5 | 104.4 | 3.4 |
| 50 | 1.1 | 0.5 | 1.2 | 225 | 7.5 | 4.8 | 0.64 | 0.33 | 8.6 | 22.5 | 225 | 6.5 | 0.49 | 4.8 | 96.6 | 3.9 |
| | 1.5 | 0.9 | 2.0 | 170 | 7.3 | 4.3 | 0.58 | 0.31 | 8.3 | 23.8 | 170 | 6.5 | 0.55 | 4.6 | 105.4 | 3.4 |
| | 1.5 0.8 | 0.9 | 2.0 0.6 | 225 170 | 7.6 6.5 | 4.8 | 0.63 | 0.32 | 8.7 7.9 | 23.8 16.8 | 225 170 | 6.7 6.7 | 0.50 | 5.0 4.9 | 97.4 106.7 | 3.9 3.5 |
| | 0.8 | 0.3 | 0.6 | 225 | 6.8 | 4.1 4.7 | 0.63 | 0.39 | 7.9 8.2 | 16.8 | 225 | 6.9 | 0.50 | 4.9 5.2 | 98.4 | 3.5 4.0 |
| | 1.1 | 0.5 | 1.0 | 170 | 6.9 | 4.2 | 0.61 | 0.36 | 8.1 | 19.1 | 170 | 7.1 | 0.57 | 5.2 | 108.6 | 3.7 |
| 60 | 1.1 | 0.5 | 1.0 | 225 | 7.1 | 4.8 | 0.67 | 0.37 | 8.4 | 19.1 | 225 | 7.3 | 0.51 | 5.5 | 99.9 | 4.2 |
| | 1.5 | 0.8 | 1.8 | 170 | 7.0 | 4.2 | 0.61 | 0.34 | 8.2 | 20.4 | 170 | 7.3 | 0.57 | 5.3 | 109.7 | 3.7 |
| | 1.5 | 0.8 | 1.8 | 225 | 7.3 | 4.8 | 0.66 | 0.36 | 8.5 | 20.4 | 225 | 7.5 | 0.51 | 5.7 | 100.7 | 4.3 |
| | 0.8 0.8 | 0.2 0.2 | 0.5 0.5 | 170 225 | 6.0 6.3 | 4.0 4.5 | 0.66 0.72 | 0.43 0.45 | 7.5 7.8 | 14.0 14.0 | 170 225 | 7.4 7.6 | 0.58 0.52 | 5.5 5.9 | 110.5 101.4 | 3.8 4.3 |
| | 1.1 | 0.2 | 0.9 | 170 | 6.4 | 4.1 | 0.64 | 0.40 | 7.8 | 14.0 | 170 | 7.8 | 0.52 | 5.8 | 112.4 | 4.5 3.9 |
| 70 | 1.1 | 0.4 | 0.9 | 225 | 6.7 | 4.6 | 0.70 | 0.42 | 8.1 | 16.0 | 225 | 8.0 | 0.53 | 6.2 | 102.8 | 4.5 |
| | 1.5 | 0.7 | 1.6 | 170 | 6.6 | 4.1 | 0.63 | 0.38 | 7.9 | 17.1 | 170 | 8.0 | 0.59 | 5.9 | 113.4 | 4.0 |
| | 1.5 | 0.7 | 1.6 | 225 | 6.8 | 4.7 | 0.69 | 0.40 | 8.2 | 17.1 | 225 | 8.2 | 0.53 | 6.4 | 103.6 | 4.5 |
| | 0.8 | 0.2 | 0.5 | 170 | 5.6 | 3.8 | 0.68 | 0.47 | 7.2 | 12.0 | 170 | 7.9 | 0.59 | 5.9 | 113.2 | 4.0 |
| | 0.8 | 0.2 0.4 | 0.5 0.8 | 225 170 | 5.8 5.9 | 4.3 3.9 | 0.74 0.67 | 0.49 0.45 | 7.5 7.4 | 12.0 13.2 | 225 170 | 8.1 8.3 | 0.53 0.60 | 6.3 6.3 | 103.5 115.4 | 4.5 4.1 |
| 80 | 1.1 | 0.4 | 0.8 | 225 | 6.1 | 4.4 | 0.73 | 0.46 | 7.7 | 13.2 | 225 | 8.5 | 0.54 | 6.7 | 105.1 | 4.6 |
| | 1.5 | 0.6 | 1.5 | 170 | 6.2 | 4.0 | 0.65 | 0.42 | 7.6 | 14.7 | 170 | 8.4 | 0.60 | 6.3 | 115.7 | 4.1 |
| | 1.5 | 0.6 | 1.5 | 225 | 6.4 | 4.6 | 0.71 | 0.44 | 7.9 | 14.7 | 225 | 8.6 | 0.54 | 6.7 | 105.3 | 4.6 |
| | 0.8 | 0.2 | 0.5 | 170 | 5.3 | 3.7 | 0.70 | 0.50 | 7.0 | 10.7 | 170 | 8.2 | 0.60 | 6.2 | 114.7 | 4.0 |
| | 0.8 | 0.2 0.3 | 0.5 0.8 | 225 170 | 5.5 5.6 | 4.2 3.8 | 0.76 0.68 | 0.52 0.47 | 7.3 7.2 | 10.7 11.9 | 225 170 | 8.4 8.5 | 0.50 0.60 | 6.6 6.4 | 104.6 116.2 | 4.6 4.1 |
| 85 | 1.1 | 0.3 | 0.8 | 225 | 5.8 | 4.3 | 0.74 | 0.49 | 7.5 | 11.9 | 225 | 8.7 | 0.50 | 6.8 | 105.8 | 4.7 |
| | 1.5 | 0.6 | 1.4 | 170 | 5.8 | 3.9 | 0.67 | 0.45 | 7.4 | 13.1 | 170 | 8.5 | 0.60 | 6.4 | 116.4 | 4.1 |
| | 1.5 | 0.6 | 1.4 | 225 | 6.1 | 4.4 | 0.73 | 0.47 | 7.7 | 13.1 | 225 | 8.7 | 0.50 | 6.8 | 105.9 | 4.7 |
| | 0.8 | 0.2 | 0.4 | 170 | 5.0 | 3.6 | 0.72 | 0.53 | 6.7 | 9.4 | 170 | 8.5 | 0.61 | 6.4 | 116.3 | 4.1 |
| | 0.8 | 0.2 0.3 | 0.4 0.7 | 225 170 | 5.2 5.3 | 4.1 3.7 | 0.79 0.70 | 0.55 0.49 | 7.0 7.0 | 9.4 10.7 | 225 170 | 8.7 8.6 | 0.55 0.62 | 6.8 6.5 | 105.8 117.0 | 4.7 4.1 |
| 90 | 1.1 | 0.3 | 0.7 | 225 | 5.5 | 4.2 | 0.76 | 0.49 | 7.3 | 10.7 | 225 | 8.8 | 0.55 | 7.0 | 106.4 | 4.7 |
| | 1.5 | 0.6 | 1.3 | 170 | 5.5 | 3.8 | 0.69 | 0.48 | 7.1 | 11.5 | 170 | 8.7 | 0.62 | 6.5 | 117.1 | 4.1 |
| | 1.5 | 0.6 | 1.3 | 225 | 5.7 | 4.3 | 0.75 | 0.50 | 7.4 | 11.5 | 225 | 8.9 | 0.56 | 7.0 | 106.5 | 4.7 |
| | 0.8 | 0.2 | 0.4 | 170 | 4.4 | 3.4 | 0.76 | 0.58 | 6.4 | 7.6 7.6 | | | | | | |
| | 0.8 | 0.2 0.3 | 0.4 0.7 | 225 170 | 4.6 4.7 | 3.8 3.5 | 0.83 0.74 | 0.60 0.55 | 6.6 6.6 | 7.6 8.7 | | | | | | |
| 100 | 1.1 | 0.3 | 0.7 | 225 | 4.9 | 4.0 | 0.80 | 0.55 | 6.9 | 8.7 | | | | | | |
| | 1.5 | 0.5 | 1.2 | 170 | 4.9 | 3.6 | 0.73 | 0.53 | 6.7 | 9.3 | | | | | | |
| | 1.5 | 0.5 | 1.2 | 225 | 5.1 | 4.0 | 0.79 | 0.55 | 7.0 | 9.3 | | | | | | |
| | 0.8 | 0.2 | 0.3 | 170 | 3.9 | 3.1 | 0.81 | 0.63 | 6.0 | 6.2 | | | | | | |
| | 0.8 | 0.2 0.3 | 0.3 0.6 | 225 170 | 4.1 4.2 | 3.6 3.3 | 0.87 0.78 | 0.66 0.60 | 6.3 6.2 | 6.2 7.0 | | | | | | |
| 110 | 1.1 | 0.3 | 0.6 | 225 | 4.2 | 3.3 3.7 | 0.78 | 0.60 | 6.5 | 7.0 | Ор | eratio | n not re | ecomn | nende | d |
| | 1.5 | 0.5 | 1.2 | 170 | 4.3 | 3.3 | 0.77 | 0.58 | 6.3 | 7.4 | | | | | | |
| | 1.5 | 0.5 | 1.2 | 225 | 4.5 | 3.8 | 0.83 | 0.61 | 6.6 | 7.4 | | | | | | |
| | 0.8 | 0.1 | 0.3 | 170 | 3.5 | 3.0 | 0.85 | 0.68 | 5.8 | 5.0 | | | | | | |
| | 0.8 | 0.1 | 0.3 | 225 | 3.6 | 3.3 | 0.93 | 0.71 | 6.0 | 5.0 | | | | | | |
| 120 | 1.1 | 0.3 0.3 | 0.6 0.6 | 170 225 | 3.7 3.8 | 3.0 3.4 | 0.83 0.90 | 0.65 0.68 | 5.9 6.2 | 5.6 5.6 | | | | | | |
| | 1.5 | 0.5 | 1.1 | 170 | 3.8 | 3.1 | 0.81 | 0.64 | 6.0 | 6.0 | | | | | | |
| | 1.5 | 0.5 | 1.1 | 225 | 4.0 | 3.5 | 0.88 | 0.67 | 6.2 | 6.0 | | | | | | |

Interpolation is permissible; extrapolation is not.

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/ISO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 40°F EVT is based upon a 15% methanol antifreeze solution. Operation below 60°F EVT requires optional insultated water/refigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 009

325 CFM Nominal (Rated) Airflow

Performance capacities shown in thousands of Btuh

| | | W | PD | | | Cool | ing - EAT 80 | /67°F | | | | H | eating - E | AT 70°F | | |
|-----------|------------|------------|-------------|----------------|--------------|------------|-------------------|--------------|--------------|--------------|----------------|-------------------|--------------|-------------|----------------|------------|
| EWT °F | GPM | PSI | FT | Airflow CFM | тс | sc | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | нс | kW | HE | LAT | СОР |
| 20 | 2.3 | 4.5 | 10.5 | | Op | eratior | not recor | nmend | ed | | 250 | 6.5 | 0.73 | 4.2 | 94.2 | 2.6 |
| | 2.3 1.1 | 4.5 1.3 | 10.5 3.0 | 250 | 10.2 | 6.0 | 0.59 | 0.39 | 11.6 | 26.6 | 330 250 | <u>6.7</u> 7.1 | 0.66 | 4.4 | 88.8 96.3 | 3.0 2.8 |
| | 1.1 | 1.3 | 3.0 | 330 | 10.7 | 6.8 | 0.64 | 0.40 | 12.0 | 26.6 | 330 | 7.3 | 0.67 | 5.0 | 90.4 | 3.2 |
| 30 | 1.7 | 1.9 | 4.4 | 250 | 10.5 | 6.0 | 0.57 | 0.36 | 11.7 | 29.5 | 250 | 7.4 | 0.75 | 4.9 | 97.4 | 2.9 |
| | 1.7 | 1.9 | 4.4 | 330 | 10.9 | 6.8 | 0.62 | 0.37 | 12.2 | 29.5 | 330 | 7.6 | 0.67 | 5.3 | 91.2 | 3.3 |
| | 2.3 2.3 | 3.5 3.5 | 8.1 8.1 | 250 330 | 10.6 11.0 | 6.0 6.8 | 0.56 0.61 | 0.34 0.36 | 11.8 12.3 | 31.1 31.1 | 250 330 | 7.5 7.7 | 0.75 0.68 | 5.1 5.4 | 97.9 91.7 | 2.9 3.4 |
| | 1.1 | 0.9 | 2.0 | 250 | 9.9 | 6.0 | 0.61 | 0.30 | 11.3 | 22.8 | 250 | 8.0 | 0.00 | 5.5 | 99.8 | 3.1 |
| | 1.1 | 0.9 | 2.0 | 330 | 10.3 | 6.8 | 0.66 | 0.45 | 11.8 | 22.8 | 330 | 8.2 | 0.69 | 5.9 | 93.1 | 3.5 |
| 40 | 1.7 | 1.5 | 3.5 | 250 | 10.1 | 6.0 | 0.59 | 0.40 | 11.5 | 25.4 | 250 | 8.4 | 0.77 | 5.8 | 101.1 | 3.2 |
| | 1.7 | 1.5 | 3.5 | 330 | 10.5 | 6.8 | 0.64 | 0.41 | 12.0 | 25.4 | 330 | 8.6 | 0.69 | 6.2 | 94.1 | 3.6 |
| | 2.3 2.3 | 3.0 3.0 | 6.8 6.8 | 250 330 | 10.3 10.7 | 6.0 6.8 | 0.59 0.64 | 0.38 0.40 | 11.6 12.0 | 26.8 26.9 | 250 330 | 8.6 8.8 | 0.78 0.70 | 6.0 6.4 | 101.8 94.7 | 3.2 3.7 |
| | 1.1 | 0.6 | 1.5 | 250 | 9.4 | 6.0 | 0.63 | 0.48 | 11.1 | 19.5 | 250 | 9.0 | 0.79 | 6.4 | 103.3 | 3.4 |
| | 1.1 | 0.6 | 1.5 | 330 | 9.8 | 6.7 | 0.69 | 0.50 | 11.6 | 19.5 | 330 | 9.2 | 0.71 | 6.8 | 95.8 | 3.8 |
| 50 | 1.7 | 1.3 | 2.9 | 250 | 9.7 | 6.0 | 0.62 | 0.45 | 11.3 | 21.7 | 250 | 9.4 | 0.80 | 6.7 | 104.8 | 3.5 |
| | 1.7 | 1.3 | 2.9 | 330 | 10.1 | 6.8 | 0.67 | 0.47 | 11.7 | 21.7 | 330 | 9.6 | 0.72 | 7.2 | 97.0 | 3.9 |
| | 2.3 2.3 | 2.6 2.6 | 6.0 6.0 | 250 330 | 9.9 10.3 | 6.0 6.8 | 0.61 0.66 | 0.43 0.45 | 11.3 11.8 | 23.0 23.0 | 250 330 | 9.6 9.8 | 0.80 0.72 | 6.9 7.4 | 105.6 97.6 | 3.5 4.0 |
| | 1.1 | 0.5 | 1.2 | 250 | 9.0 | 5.9 | 0.65 | 0.43 | 10.8 | 16.5 | 250 | 9.9 | 0.72 | 7.2 | 106.8 | 3.6 |
| | 1.1 | 0.5 | 1.2 | 330 | 9.4 | 6.7 | 0.71 | 0.57 | 11.3 | 16.5 | 330 | 10.2 | 0.73 | 7.7 | 98.5 | 4.1 |
| 60 | 1.7 | 1.1 | 2.5 | 250 | 9.3 | 5.9 | 0.64 | 0.50 | 11.0 | 18.5 | 250 | 10.4 | 0.82 | 7.6 | 108.4 | 3.7 |
| | 1.7 | 1.1 | 2.5 | 330 | 9.7 | 6.7 | 0.69 | 0.52 | 11.5 | 18.5 | 330 | 10.6 | 0.74 | 8.1 | 99.8 | 4.2 |
| | 2.3 2.3 | 2.3 2.3 | 5.4 5.4 | 250 330 | 9.5 9.8 | 6.0 6.7 | 0.63 0.69 | 0.48 0.50 | 11.1 11.6 | 19.6 19.6 | 250 330 | 10.6 10.9 | 0.83 0.75 | 7.8 8.3 | 109.3 100.5 | 3.7 4.3 |
| | 1.1 | 0.4 | 0.9 | 250 | 8.5 | 5.8 | 0.68 | 0.61 | 10.6 | 14.0 | 250 | 10.3 | 0.84 | 8.0 | 110.1 | 3.8 |
| | 1.1 | 0.4 | 0.9 | 330 | 8.8 | 6.5 | 0.74 | 0.63 | 11.0 | 14.0 | 330 | 11.1 | 0.75 | 8.5 | 101.1 | 4.3 |
| 70 | 1.7 | 1.0 | 2.3 | 250 | 8.8 | 5.8 | 0.66 | 0.56 | 10.7 | 15.6 | 250 | 11.3 | 0.85 | 8.4 | 111.9 | 3.9 |
| | 1.7 | 1.0 | 2.3 | 330 | 9.2 | 6.6 | 0.72 | 0.59 | 11.2 | 15.6 | 330 | 11.6 | 0.77 | 9.0 | 102.5 | 4.4 |
| | 2.3 2.3 | 2.1 2.1 | 4.9 4.9 | 250 330 | 9.1 9.5 | 5.9 6.7 | 0.65 0.71 | 0.53 0.55 | 10.9 11.3 | 17.1 17.1 | 250 330 | 11.4 11.6 | 0.85 0.77 | 8.5 9.0 | 112.1 102.7 | 3.9 4.4 |
| | 1.1 | 0.3 | 0.8 | 250 | 8.0 | 5.6 | 0.70 | 0.67 | 10.3 | 11.8 | 250 | 11.0 | 0.87 | 8.7 | 113.3 | 4.0 |
| | 1.1 | 0.3 | 0.8 | 330 | 8.3 | 6.3 | 0.77 | 0.70 | 10.7 | 11.8 | 330 | 12.0 | 0.78 | 9.3 | 103.6 | 4.5 |
| 80 | 1.7 | 0.9 | 2.1 | 250 | 8.3 | 5.7 | 0.69 | 0.63 | 10.5 | 13.2 | 250 | 12.2 | 0.88 | 9.1 | 115.1 | 4.0 |
| | 1.7 2.3 | 0.9 2.0 | 2.1 4.6 | 330 250 | 8.6 8.6 | 6.5 5.8 | 0.75 0.67 | 0.66 0.59 | 10.9 10.6 | 13.2 14.4 | 330 250 | 12.5 12.2 | 0.79 0.88 | 9.8 9.2 | 105.0 115.4 | 4.6 4.1 |
| | 2.3 | 2.0 | 4.6 | 330 | 8.9 | 5.8 6.5 | 0.07 | 0.62 | 10.0 | 14.4 | 330 | 12.2 | 0.88 | 9.2 9.8 | 105.2 | 4.1 |
| | 1.1 | 0.3 | 0.7 | 250 | 7.7 | 5.5 | 0.71 | 0.70 | 10.1 | 11.0 | 250 | 12.0 | 0.88 | 9.0 | 114.5 | 4.0 |
| | 1.1 | 0.3 | 0.7 | 330 | 8.0 | 6.2 | 0.78 | 0.73 | 10.5 | 11.0 | 330 | 12.3 | 0.80 | 9.6 | 104.6 | 4.6 |
| 85 | 1.7 | 0.9 | 2.0 | 250 | 8.0 | 5.6 | 0.70 | 0.67 | 10.3 | 12.1 | 250 | 12.6 | 0.90 | 9.5 | 116.5 | 4.1 |
| | 1.7 2.3 | 0.9 1.9 | 2.0 4.4 | 330 250 | 8.4 8.3 | 6.4 5.7 | 0.76 0.69 | 0.69 0.63 | 10.7 10.5 | 12.1 13.3 | 330 250 | 12.9 12.6 | 0.80 0.90 | 10.1 9.5 | 106.1 116.8 | 4.7 4.1 |
| | 2.3 | 1.9 | 4.4 | 330 | 8.7 | 6.5 | 0.05 | 0.65 | 10.5 | 13.3 | 330 | 12.0 | 0.80 | 10.2 | 106.3 | 4.1 |
| | 1.1 | 0.3 | 0.6 | 250 | 7.5 | 5.4 | 0.72 | 0.73 | 10.0 | 10.2 | 250 | 12.3 | 0.89 | 9.3 | 115.7 | 4.1 |
| | 1.1 | 0.3 | 0.6 | 330 | 7.8 | 6.2 | 0.79 | 0.76 | 10.4 | 10.2 | 330 | 12.6 | 0.80 | 9.9 | 105.5 | 4.6 |
| 90 | 1.7 | 0.8 | 1.9 | 250 | 7.7 | 5.5 | 0.71 | 0.70 | 10.1 | 11.1 | 250 | 12.9 | 0.91 | 9.8 | 117.9 | 4.2 |
| | 1.7 2.3 | 0.8 1.8 | 1.9 4.3 | 330 250 | 8.1 8.0 | 6.3 5.6 | 0.78 0.70 | 0.73 0.66 | 10.6 10.3 | 11.1 12.1 | 330 250 | 13.3 13.0 | 0.82 0.91 | 10.5 9.9 | 107.2 118.2 | 4.8 4.2 |
| | 2.3 | 1.8 | 4.3 | 330 | 8.4 | 6.4 | 0.76 | 0.69 | 10.3 | 12.1 | 330 | 13.3 | 0.82 | 10.5 | 107.4 | 4.8 |
| | 1.1 | 0.2 | 0.6 | 250 | 6.8 | 5.1 | 0.76 | 0.82 | 9.6 | 8.2 | | | | | | |
| | 1.1 | 0.2 | 0.6 | 330 | 7.0 | 5.8 | 0.82 | 0.86 | 10.0 | 8.2 | | | | | | |
| 100 | 1.7 | 0.8 | 1.7 | 250 | 7.1 | 5.3 | 0.74 | 0.78 | 9.8 | 9.2 | | | | | | |
| | 1.7 2.3 | 0.8 1.7 | 1.7 4.0 | 330 250 | 7.4 7.3 | 6.0 5.4 | 0.81 0.73 | 0.81 0.75 | 10.2 9.9 | 9.2 9.7 | | | | | | |
| | 2.3 | 1.7 | 4.0 | 330 | 7.6 | 6.1 | 0.80 | 0.78 | 10.3 | 9.7 | | | | | | |
| | 1.1 | 0.2 | 0.5 | 250 | 6.1 | 4.8 | 0.79 | 0.90 | 9.2 | 6.8 | | | | | | |
| | 1.1 | 0.2 | 0.5 | 330 | 6.3 | 5.4 | 0.85 | 0.94 | 9.5 | 6.8 | | | | | | |
| 110 | 1.7 1.7 | 0.7 0.7 | 1.6 1.6 | 250 330 | 6.5 6.8 | 5.0 5.6 | 0.77 0.84 | 0.86 0.89 | 9.4 9.8 | 7.6 7.6 | (| Operatic | on not r | ecomm | ended | |
| | 2.3 | 1.6 | 3.8 | 250 | 6.7 | 5.6 5.1 | 0.84 | 0.89 | 9.8 9.5 | 7.6 8.0 | | | | | | |
| | 2.3 | 1.6 | 3.8 | 330 | 7.0 | 5.8 | 0.83 | 0.87 | 9.9 | 8.0 | | | | | | |
| | 1.1 | 0.2 | 0.4 | 250 | 5.4 | 4.4 | 0.82 | 0.98 | 8.7 | 5.5 | | | | | | |
| | 1.1 | 0.2 | 0.4 | 330 | 5.6 | 5.0 | 0.89 | 1.02 | 9.1 | 5.5 | | | | | | |
| 120 | 1.7 1.7 | 0.7 0.7 | 1.6 1.6 | 250 330 | 5.8 6.0 | 4.6 5.2 | 0.80 0.87 | 0.94 0.98 | 9.0 9.4 | 6.2 6.2 | | | | | | |
| | 2.3 | 1.6 | 3.6 | 250 | 6.0 | 4.7 | 0.87 | 0.98 | 9.4 9.1 | 6.5 | | | | | | |
| | 2.3 | 1.6 | 3.6 | 330 | 6.2 | 5.4 | 0.86 | 0.95 | 9.5 | 6.5 | | | | | | |
| | | | | | | | | | | | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/ISO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units.

Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution.

Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above.

See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 012

400 CFM Nominal (Rated) Airflow

```
Performance capacities shown in thousands of Btuh
```

| EWT | | W | PD | | (| Cooling | g - EAT | 80/67° | F | | Heating - EAT 70°F Airflow CEM HC kW HE LAT COP | | | | | | | | |
|-----|------------|-------------------|--------------|----------------|--------------|------------|-------------------|--------------|---------------------|---------------------|--|--------------|---------------------|---------------------|----------------|------------|--|--|--|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | НС | kW | HE | LAT | СОР | | | |
| 20 | 3.0 3.0 | 8.5 8.5 | 19.6 19.6 | | 0 | peration | not reco | mmend | ed | | 300 400 | 8.5 8.7 | 0.98 0.88 | 5.3 5.7 | 96.2 90.2 | 2.5 2.9 | | | |
| | 1.5 | 1.9 | 4.3 | 300 | 14.2 | 8.2 | 0.58 | 0.55 | 16.1 | 25.8 | 300 | 9.3 | 1.00 | 6.0 | 98.6 | 2.7 | | | |
| | 1.5 2.3 | 1.9 3.6 | 4.3 8.4 | 400 300 | 14.8 14.3 | 9.3 8.2 | 0.63 0.58 | 0.57 0.51 | 16.8 16.1 | 25.8 27.9 | 400 300 | 9.5 9.6 | 0.90 1.01 | 6.4 6.3 | 91.9 99.7 | 3.1 2.8 | | | |
| 30 | 2.3 | 3.6 | 8.4 | 400 | 14.9 | 9.3 | 0.63 | 0.53 | 16.7 | 27.9 | 400 | 9.9 | 0.91 | 6.8 | 92.8 | 3.2 | | | |
| | 3.0 | 6.7 | 15.5 | 300 | 14.3 | 8.2 | 0.58 | 0.50 | 16.0 | 28.8 | 300 | 9.8 | 1.02 | 6.5 | 100.4 | 2.8 | | | |
| | 3.0 1.5 | 6.7 | 15.5 | 400 | 14.9 14.0 | 9.3 | 0.63 | 0.52 | 16.6 | 28.8 | 400 300 | 10.1 | 0.92 | 7.0 | 93.3 | 3.2 | | | |
| | 1.5 | 1.4 1.4 | 3.2 3.2 | 300 400 | 14.0 | 8.1 9.2 | 0.58 0.63 | 0.61 0.63 | 16.0 16.7 | 22.9 22.9 | 400 | 10.6 10.8 | 0.93 | 7.1 | 102.6 95.0 | 3.0 3.4 | | | |
| 40 | 2.3 | 3.0 | 6.9 | 300 | 14.2 | 8.2 | 0.58 | 0.57 | 16.1 | 25.1 | 300 | 11.0 | 1.05 | 7.6 | 104.1 | 3.1 | | | |
| 40 | 2.3 | 3.0 | 6.9 | 400 | 14.8 | 9.3 | 0.63 | 0.59 | 16.8 | 25.1 | 400 | 11.3 | 0.94 | 8.1 | 96.2 | 3.5 | | | |
| | 3.0 3.0 | 5.7 5.7 | 13.1 13.1 | 300 400 | 14.3 14.8 | 8.2 9.3 | 0.58 0.63 | 0.54 0.57 | 16.1 16.8 | 26.2 26.2 | 300 400 | 11.3 11.6 | 1.06 0.95 | 7.8 8.3 | 104.9 96.8 | 3.1 3.6 | | | |
| | 1.5 | 1.1 | 2.5 | 300 | 13.5 | 7.9 | 0.58 | 0.67 | 15.8 | 20.1 | 300 | 11.9 | 1.08 | 8.3 | 106.8 | 3.2 | | | |
| | 1.5 | 1.1 | 2.5 | 400 | 14.1 | 8.9 | 0.63 | 0.70 | 16.5 | 20.1 | 400 | 12.2 | 0.97 | 8.9 | 98.2 | 3.7 | | | |
| 50 | 2.3 2.3 | 2.6 2.6 | 6.0 6.0 | 300 400 | 13.9 14.4 | 8.0 9.1 | 0.58 0.63 | 0.62 0.65 | 16.0 16.7 | 22.2 22.2 | 300 400 | 12.5 12.8 | 1.09 0.98 | 8.9 9.5 | 108.6 99.6 | 3.4 3.8 | | | |
| | 3.0 | 2.0 5.0 | 11.5 | 300 | 14.4 | 8.1 | 0.63 | 0.60 | 16.1 | 23.3 | 300 | 12.8 | 1.10 | 9.5 | 109.6 | 3.8 | | | |
| | 3.0 | 5.0 | 11.5 | 400 | 14.6 | 9.2 | 0.63 | 0.63 | 16.7 | 23.3 | 400 | 13.1 | 0.99 | 9.8 | 100.4 | 3.9 | | | |
| | 1.5 1.5 | 0.9 0.9 | 2.1 2.1 | 300 400 | 12.9 13.5 | 7.6 8.6 | 0.59 0.64 | 0.74 0.77 | 15.5 16.1 | 17.4 17.4 | 300 400 | 13.3 13.6 | 1.11 1.00 | 9.6 10.2 | 111.1 101.5 | 3.5 4.0 | | | |
| ~~ | 2.3 | 2.3 | 5.3 | 300 | 13.5 | 7.8 | 0.64 | 0.69 | 15.7 | 19.3 | 300 | 14.0 | 1.13 | 10.2 | 113.1 | 3.6 | | | |
| 60 | 2.3 | 2.3 | 5.3 | 400 | 13.9 | 8.8 | 0.63 | 0.72 | 16.4 | 19.3 | 400 | 14.3 | 1.02 | 10.8 | 103.1 | 4.1 | | | |
| | 3.0 | 4.5 | 10.3 | 300 | 13.6 | 7.9 | 0.58 | 0.67 | 15.8 | 20.4 | 300 | 14.3 | 1.14 | 10.5 | 114.2 | 3.7 | | | |
| | 3.0 1.5 | 4.5 | 10.3 1.8 | 400 300 | 14.1 12.2 | 8.9 7.3 | 0.63 | 0.69 | <u>16.5</u> 15.0 | <u>20.4</u> 14.9 | 400 300 | 14.7 14.7 | <u>1.03</u> 1.15 | <u>11.2</u> 10.8 | 104.0 115.3 | 4.2 | | | |
| | 1.5 | 0.8 | 1.8 | 400 | 12.7 | 8.3 | 0.65 | 0.85 | 15.6 | 14.9 | 400 | 15.0 | 1.04 | 11.5 | 104.8 | 4.2 | | | |
| 70 | 2.3 | 2.1 | 4.8 | 300 | 12.5 | 7.4 | 0.59 | 0.77 | 15.2 | 16.3 | 300 | 15.4 | 1.18 | 11.4 | 117.6 | 3.8 | | | |
| | 2.3 3.0 | 2.1 4.1 | 4.8 9.5 | 400 300 | 13.1 12.7 | 8.4 7.5 | 0.64 0.59 | 0.80 0.75 | 15.8 15.3 | 16.3 17.0 | 400 300 | 15.8 15.8 | 1.06 1.19 | 12.2 11.7 | 106.5 118.8 | 4.4 3.9 | | | |
| | 3.0 | 4.1 | 9.5 | 400 | 13.3 | 8.5 | 0.55 | 0.78 | 15.9 | 17.0 | 400 | 16.2 | 1.07 | 12.5 | 107.5 | 4.4 | | | |
| | 1.5 | 0.7 | 1.5 | 300 | 11.4 | 7.0 | 0.61 | 0.90 | 14.5 | 12.7 | 300 | 16.0 | 1.20 | 11.9 | 119.4 | 3.9 | | | |
| | 1.5 2.3 | 0.7 1.9 | 1.5 | 400 300 | 11.9 | 7.9 | 0.67 0.60 | 0.94 0.85 | 15.1 14.7 | 12.7 13.9 | 400 300 | 16.4 16.8 | 1.08 1.22 | 12.7 12.6 | 108.0 121.7 | 4.5 | | | |
| 80 | 2.3 | 1.9 | 4.4 4.4 | 400 | 11.8 12.3 | 7.1 8.0 | 0.60 | 0.85 | 14.7 | 13.9 | 400 | 17.2 | 1.22 | 12.6 | 121.7 | 4.0 4.6 | | | |
| | 3.0 | 3.8 | 8.8 | 300 | 12.0 | 7.2 | 0.60 | 0.83 | 14.8 | 14.5 | 300 | 17.2 | 1.24 | 12.9 | 123.0 | 4.1 | | | |
| | 3.0 | 3.8 | 8.8 | 400 | 12.5 | 8.1 | 0.65 | 0.86 | 15.4 | 14.5 | 400 | 17.6 | 1.11 | 13.8 | 110.7 | 4.6 | | | |
| | 1.5 1.5 | 0.6 0.6 | 1.5 1.5 | 300 400 | 10.9 11.4 | 6.8 7.7 | 0.62 0.68 | 0.9 0.98 | 14.2 14.7 | 11.7 11.7 | 300 400 | 16.6 17.0 | 1.22 1.1 | 12.5 13.3 | 121.3 109.4 | 4.0 4.6 | | | |
| 05 | 2.3 | 1.8 | 4.2 | 300 | 11.4 | 6.9 | 0.61 | 0.89 | 14.4 | 12.8 | 300 | 17.4 | 1.3 | 13.1 | 123.6 | 4.1 | | | |
| 85 | 2.3 | 1.8 | 4.2 | 400 | 11.9 | 7.9 | 0.66 | 0.93 | 15.0 | 12.8 | 400 | 17.8 | 1.1 | 14.0 | 111.2 | 4.6 | | | |
| | 3.0 3.0 | 3.7 3.7 | 8.5 8.5 | 300 400 | 11.6 12.1 | 7.0 7.9 | 0.60 0.66 | 0.87 0.90 | 14.5 15.1 | 13.4 13.4 | 300 400 | 17.7 18.2 | 1.3 1.1 | 13.4 14.3 | 124.8 112.1 | 4.1 4.7 | | | |
| | 1.5 | 0.6 | 1.4 | 300 | 10.5 | 6.7 | 0.63 | 0.90 | 13.9 | 10.7 | 300 | 17.3 | 1.24 | 13.0 | 123.3 | 4.1 | | | |
| | 1.5 | 0.6 | 1.4 | 400 | 10.9 | 7.5 | 0.69 | 1.03 | 14.4 | 10.7 | 400 | 17.7 | 1.12 | 13.9 | 110.9 | 4.6 | | | |
| 90 | 2.3 2.3 | 1.8 1.8 | 4.1 4.1 | 300 400 | 11.0 11.4 | 6.8 7.7 | 0.62 0.67 | 0.93 0.97 | 14.1 14.7 | 11.7 11.7 | 300 400 | 18.0 18.4 | 1.28 1.15 | 13.6 14.5 | 125.5 112.6 | 4.1 4.7 | | | |
| | 3.0 | 3.6 | 8.2 | 300 | 11.4 | 6.8 | 0.61 | 0.97 | 14.7 | 12.3 | 300 | 18.3 | 1.15 | 14.5 | 126.6 | 4.7 | | | |
| | 3.0 | 3.6 | 8.2 | 400 | 11.6 | 7.7 | 0.67 | 0.95 | 14.8 | 12.3 | 400 | 18.8 | 1.16 | 14.8 | 113.5 | 4.7 | | | |
| | 1.5 | 0.5 | 1.2 | 300 | 9.5 | 6.4 | 0.67 | 1.07 | 13.2 | 8.9 | | | | | | | | | |
| | 1.5 2.3 | 0.5 1.7 | 1.2 3.8 | 400 300 | 9.9 10.1 | 7.2 6.5 | 0.72 0.65 | 1.12 1.02 | 13.8 13.5 | 8.9 9.8 | | | | | | | | | |
| 100 | 2.3 | 1.7 | 3.8 | 400 | 10.5 | 7.3 | 0.70 | 1.06 | 14.1 | 9.8 | | | | | | | | | |
| | 3.0 | 3.3 | 7.7 | 300 | 10.4 | 6.6 | 0.64 | 1.00 | 13.8 | 10.4 | | | | | | | | | |
| | 3.0 1.5 | <u>3.3</u> 0.5 | 7.7 | 400 300 | 10.8 8.5 | 7.5 | 0.69 | 1.04 1.17 | 14.3 12.5 | 10.4 7.3 | | | | | | | | | |
| | 1.5 | 0.5 | 1.1 | 400 | 8.9 | 6.8 | 0.77 | 1.22 | 13.1 | 7.3 | | | | | | | | | |
| 110 | 2.3 | 1.6 | 3.6 | 300 | 9.1 | 6.2 | 0.68 | 1.12 | 12.9 | 8.1 | | Opera | ation not | recomm | hended | | | | |
| | 2.3 3.0 | 1.6 3.2 | 3.6 7.3 | 400 300 | 9.4 9.4 | 7.0 6.3 | 0.74 0.67 | 1.16 1.09 | 13.4 13.1 | 8.1 8.6 | | opere | | | lonaca | | | | |
| | 3.0 | 3.2 | 7.3 | 400 | 9.4 9.8 | 7.1 | 0.07 | 1.14 | 13.7 | 8.6 | | | | | | | | | |
| | 1.5 | 0.4 | 1.0 | 300 | 7.5 | 5.7 | 0.76 | 1.27 | 11.8 | 5.9 | | | | | | | | | |
| | 1.5 | 0.4 | 1.0 | 400 | 7.8 | 6.4 | 0.82 | 1.32 | 12.3 | 5.9 | | | | | | | | | |
| 120 | 2.3 2.3 | 1.5 1.5 | 3.4 3.4 | 300 400 | 8.0 8.3 | 5.8 6.6 | 0.73 0.79 | 1.22 1.27 | 12.2 12.7 | 6.6 6.6 | | | | | | | | | |
| | 3.0 | 3.0 | 7.0 | 300 | 8.3 | 5.9 | 0.71 | 1.19 | 12.4 | 7.0 | | | | | | | | | |
| | 3.0 | 3.0 | 7.0 | 400 | 8.7 | 6.7 | 0.77 | 1.24 | 12.9 | 7.0 | | | | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/SO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/SO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 015

Performance capacities shown in thousands of Btuh

| EN4/T | | W | PD | | (| Cooling | J - EAT | 80/67°I | F | | | | | EAT 70 |)°F | as of Btun |
|-----------|---------------------|-------------------|-------------------|----------------|---------------------|--------------------|-------------------|---------------------|---------------------|---------------------|----------------|---------------------|---------------------|---------------------|-------------------|---------------------|
| EWT °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | HC | kW | HE | LAT | СОР |
| 20 | 3.8 3.8 | 4.1 4.1 | 9.5 9.5 | | O | peration | not reco | mmend | ed | | 395 525 | 9.5 9.8 | 1.07 0.96 | 6.1 6.5 | 92 87 | 2.62 2.98 |
| | 1.9 | 1.0 | 2.3 | 395 | 17.3 | 10.8 | 0.62 | 0.61 | 19.4 | 28.4 | 395 | 10.6 | 1.09 | 7.1 | 95 | 2.84 |
| | 1.9 | 1.0 | 2.3 | 525 | 18.1 | 12.2 | 0.67 | 0.64 | 20.2 | 28.4 | 525 | 10.9 | 0.98 | 7.5 | 89 | 3.24 |
| 30 | 2.8 2.8 | 1.8 1.8 | 4.3 4.3 | 395 525 | 17.5 18.2 | 10.8 12.2 | 0.62 0.67 | 0.56 0.59 | 19.4 20.2 | 31.1 31.1 | 395 525 | 11.1 11.4 | 1.11 0.99 | 7.5 8.0 | 96 90 | 2.94 3.35 |
| | 3.8 | 3.3 | 7.7 | 395 | 17.5 | 10.8 | 0.62 | 0.54 | 19.4 | 32.2 | 395 | 11.3 | 1.11 | 7.7 | 97 | 2.99 |
| | 3.8 | 3.3 | 7.7 | 525 | 18.3 | 12.2 | 0.67 | 0.57 | 20.2 | 32.2 | 525 | 11.6 | 1.00 | 8.2 | 90 | 3.41 |
| | 1.9 1.9 | 0.8 0.8 | 1.8 1.8 | 395 525 | 17.0 17.7 | 10.6 12.0 | 0.63 0.68 | 0.68 0.71 | 19.3 20.1 | 24.8 24.8 | 395 525 | 12.3 12.6 | 1.13 1.02 | 8.5 9.1 | 99 92 | 3.18 3.62 |
| 40 | 2.8 | 1.6 | 3.6 | 395 | 17.2 | 10.7 | 0.62 | 0.63 | 19.4 | 27.3 | 395 | 12.8 | 1.14 | 9.0 | 100 | 3.29 |
| 40 | 2.8 3.8 | 1.6 2.9 | 3.6 6.6 | 525 395 | 18.0 17.4 | 12.1 | 0.68 0.62 | 0.66 0.60 | 20.2 19.4 | 27.3 28.8 | 525 395 | 13.1 | 1.03 1.15 | 9.7 9.3 | 93 101 | 3.75 3.35 |
| | 3.8 | 2.9 | 6.6 6.6 | 525 | 17.4 | 10.8 12.2 | 0.62 | 0.60 | 20.2 | 28.8 | 525 | 13.1 13.5 | 1.03 | 9.3 | 94 | 3.82 |
| | 1.9 | 0.6 | 1.5 | 395 | 16.4 | 10.4 | 0.63 | 0.76 | 19.0 | 21.6 | 395 | 13.9 | 1.16 | 10.0 | 103 | 3.50 |
| | 1.9 | 0.6 | 1.5 | 525 | 17.1 | 11.8 | 0.69 | 0.79 | 19.8 | 21.6 | 525 | 14.2 | 1.05 | 10.7 | 95 | 3.99 |
| 50 | 2.8 2.8 | 1.4 1.4 | 3.1 3.1 | 395 525 | 16.8 17.5 | 10.6 12.0 | 0.63 0.68 | 0.71 0.74 | 19.2 20.0 | 23.8 23.8 | 395 525 | 14.6 14.9 | 1.18 1.06 | 10.6 11.3 | 104 96 | 3.63 4.13 |
| | 3.8 | 2.5 | 5.8 | 395 | 17.0 | 10.6 | 0.63 | 0.68 | 19.3 | 25.0 | 395 | 14.9 | 1.18 | 10.9 | 105 | 3.69 |
| | 3.8 | 2.5 | 5.8 | 525 | 17.7 | 12.0 | 0.68 | 0.71 | 20.1 | 25.0 | 525 | 15.3 | 1.06 | 11.7 | 97 | 4.21 |
| | 1.9 1.9 | 0.6 0.6 | 1.3 1.3 | 395 525 | 15.7 16.4 | 10.2 11.5 | 0.65 0.70 | 0.84 0.88 | 18.6 19.4 | 18.7 18.7 | 395 525 | 15.5 15.9 | 1.20 1.07 | 11.5 12.2 | 106 98 | 3.81 4.34 |
| 60 | 2.8 | 1.2 | 2.8 | 395 | 16.2 | 10.4 | 0.64 | 0.79 | 18.9 | 20.5 | 395 | 16.3 | 1.21 | 12.1 | 108 | 3.94 |
| 00 | 2.8 | 1.2 | 2.8 | 525 | 16.9 | 11.7 | 0.69 | 0.82 | 19.7 | 20.5 | 525 | 16.7 | 1.09 | 13.0 | 99 | 4.50 |
| | 3.8 3.8 | 2.3 2.3 | 5.3 5.3 | 395 525 | 16.4 17.1 | 10.4 11.8 | 0.63 0.69 | 0.76 0.79 | 19.0 19.8 | 21.6 21.6 | 395 525 | 16.7 17.1 | 1.22 1.09 | 12.5 13.3 | 109 100 | 4.02 4.58 |
| | 1.9 | 0.5 | 1.1 | 395 | 15.2 | 10.1 | 0.66 | 0.93 | 18.3 | 16.2 | 395 | 17.1 | 1.22 | 12.9 | 110 | 4.10 |
| | 1.9 | 0.5 | 1.1 | 525 | 15.8 | 11.4 | 0.72 | 0.97 | 19.1 | 16.3 | 525 | 17.5 | 1.10 | 13.8 | 101 | 4.68 |
| 70 | 2.8 2.8 | 1.1 1.1 | 2.5 2.5 | 395 525 | 15.5 16.1 | 10.1 11.4 | 0.65 0.71 | 0.88 0.91 | 18.5 19.2 | 17.6 17.6 | 395 525 | 18.0 18.4 | 1.24 1.11 | 13.7 14.6 | 112 102 | 4.25 4.85 |
| | 3.8 | 2.1 | 4.9 | 395 | 15.8 | 10.2 | 0.65 | 0.85 | 18.6 | 18.6 | 395 | 18.4 | 1.25 | 14.1 | 113 | 4.33 |
| | 3.8 1.9 | <u>2.1</u> 0.4 | <u>4.9</u> 1.0 | 525 395 | 16.4 | 11.5 | 0.70 | 0.88 | <u>19.4</u> 17.8 | 18.6 | 525 | 18.8 | 1.12 | 15.0 | 103 | 4.94 |
| | 1.9 | 0.4 | 1.0 | 525 | 14.3 14.9 | 9.8 11.1 | 0.68 0.74 | 1.03 | 17.8 | 13.9 13.9 | 395 525 | 18.7 19.2 | 1.25 1.12 | 14.3 15.3 | 114 104 | 4.38 5.00 |
| 80 | 2.8 | 1.0 | 2.4 | 395 | 14.7 | 9.8 | 0.67 | 0.97 | 18.0 | 15.1 | 395 | 19.6 | 1.27 | 15.1 | 116 | 4.54 |
| | 2.8 3.8 | 1.0 2.0 | 2.4 4.6 | 525 395 | 15.3 14.9 | 11.1 9.9 | 0.73 0.66 | 1.01 0.94 | 18.7 18.2 | 15.1 15.9 | 525 395 | 20.1 20.1 | 1.14 1.27 | 16.2 15.6 | 105 117 | 5.18 4.62 |
| | 3.8 | 2.0 | 4.6 | 525 | 15.6 | 9.9 11.2 | 0.00 | 0.94 | 18.2 | 15.9 | 525 | 20.1 | 1.14 | 16.6 | 106 | 4.02 5.27 |
| | 1.9 | 0.4 | 0.9 | 395 | 13.8 | 9.6 | 0.70 | 1.1 | 17.5 | 12.8 | 395 | 19.5 | 1.26 | 15.0 | 116 | 4.52 |
| | 1.9 2.8 | 0.4 1.0 | 0.9 2.3 | 525 395 | 14.4 14.2 | 10.9 9.7 | 0.76 0.68 | 1.13 1.02 | 18.2 17.7 | 12.8 13.9 | 525 395 | 19.9 20.4 | 1.13 1.28 | 16.0 15.9 | 105 118 | 5.15 4.68 |
| 85 | 2.8 | 1.0 | 2.3 | 525 | 14.8 | 11.0 | 0.74 | 1.02 | 18.4 | 13.9 | 525 | 20.9 | 1.15 | 16.9 | 107 | 5.34 |
| | 3.8 | 1.9 | 4.4 | 395 | 14.5 | 9.8 | 0.67 | 0.99 | 17.9 | 14.7 | 395 | 20.9 | 1.29 | 16.3 | 119 | 4.77 |
| | <u>3.8</u> 1.9 | <u>1.9</u> 0.4 | <u>4.4</u> 0.9 | 525 395 | <u>15.1</u> 13.3 | <u>11.1</u> 9.5 | 0.73 | <u>1.03</u> 1.14 | <u>18.6</u> 17.2 | <u>14.7</u> 11.7 | 525 395 | <u>21.4</u> 20.2 | <u>1.15</u> 1.28 | <u>17.4</u> 15.7 | <u>108</u> 117 | <u>5.43</u> 4.65 |
| | 1.9 | 0.4 | 0.9 | 525 | 13.9 | 10.7 | 0.77 | 1.19 | 18.0 | 11.7 | 525 | 20.2 | 1.15 | 16.8 | 107 | 5.30 |
| 90 | 2.8 | 1.0 | 2.2 | 395 | 13.7 | 9.5 | 0.69 | 1.08 | 17.4 | 12.8 | 395 | 21.2 | 1.29 | 16.6 | 120 | 4.82 |
| | 2.8 3.8 | 1.0 1.9 | 2.2 4.3 | 525 395 | 14.3 14.1 | 10.8 9.6 | 0.75 0.69 | 1.12 1.04 | 18.1 17.6 | 12.8 13.5 | 525 395 | 21.7 21.7 | 1.16 1.30 | 17.7 17.1 | 108 121 | 5.49 4.90 |
| | 3.8 | 1.9 | 4.3 | 525 | 14.6 | 10.9 | 0.00 | 1.04 | 18.3 | 13.5 | 525 | 22.2 | 1.17 | 18.2 | 109 | 5.59 |
| | 1.9 | 0.4 | 0.8 | 395 | 12.4 | 9.2 | 0.74 | 1.25 | 16.6 | 9.9 | | | | | | |
| | 1.9 2.8 | 0.4 0.9 | 0.8 2.1 | 525 395 | 12.9 12.8 | 10.4 9.2 | 0.80 0.72 | 1.31 1.19 | 17.3 16.8 | 9.9 10.8 | | | | | | |
| 100 | 2.8 | 0.9 | 2.1 | 525 | 13.3 | 10.4 | 0.78 | 1.23 | 17.5 | 10.8 | | | | | | |
| | 3.8 | 1.8 | 4.1 | 395 | 13.1 | 9.3 | 0.71 | 1.15 | 17.0 | 11.4 | | | | | | |
| | <u>3.8</u> 1.9 | <u>1.8</u> 0.3 | <u>4.1</u> 0.7 | 525 395 | <u>13.6</u> 11.3 | <u>10.5</u> 8.8 | <u> </u> | <u>1.20</u> 1.37 | <u>17.7</u> 16.0 | <u>11.4</u> 8.3 | | | | | | |
| | 1.9 | 0.3 | 0.7 | 525 | 11.8 | 10.0 | 0.84 | 1.43 | 16.7 | 8.3 | | | | | | |
| 110 | 2.8 | 0.8 | 1.9 | 395 | 11.8 | 8.9 | 0.75 | 1.30 | 16.2 | 9.0 | | Opera | tion not | recomm | ended | |
| | 2.8 3.8 | 0.8 1.7 | 1.9 3.9 | 525 395 | 12.2 12.1 | 10.0 9.0 | 0.82 0.74 | 1.36 1.27 | 16.9 16.4 | 9.0 9.5 | | | | | | |
| | 3.8 | 1.7 | 3.9 | 525 | 12.6 | 10.2 | 0.81 | 1.32 | 17.1 | 9.5 | | | | | | |
| | 1.9 | 0.3 | 0.7 | 395 | 10.3 | 8.5 | 0.82 | 1.50 | 15.5 | 6.9 | | | | | | |
| | 1.9 2.8 | 0.3 0.8 | 0.7 1.8 | 525 395 | 10.8 10.7 | 9.6 8.5 | 0.89 0.79 | 1.56 1.43 | 16.1 15.6 | 6.9 7.5 | | | | | | |
| 120 | 2.8 | 0.8 | 1.8 | 525 | 11.2 | 9.6 | 0.86 | 1.48 | 16.2 | 7.5 | | | | | | |
| | 3.8 | 1.6 | 3.7 | 395 | 11.0 | 8.6 | 0.78 | 1.39 | 15.8 | 7.9 | | | | | | |
| | 3.8 is permissit | 1.6 | 3.7 | 525 | 11.5 | 9.8 | 0.85 | 1.45 | 16.4 | 7.9 | | | | | | |

525 CFM Nominal (Rated) Airflow

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/ISO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance capacities shown in thousands of Btuh

Performance Data – TC H/V 018

600 CFM Nominal (Rated) Airflow

EW °F

20

30

40

50

60

70

80

85

90

100

110

120

| PSI FT Arribor (PM) TC SC Semiror (PM) W HR EER Arribor (PM) HC kW HE LAT COl (20) 1 4.5 7.2 16.7 Corration not recommended 450 11.2 1.26 7.2 88 93 2.61 2.3 2.1 4.9 450 22.1 14.2 0.64 0.72 24.5 30.7 450 12.4 1.28 8.2 98 2.83 3.4 3.4 7.9 450 22.9 14.4 0.68 0.67 2.21 3.53 650 13.7 13.8 89 3.33 4.5 5.9 13.7 400 2.33 14.4 0.62 2.34 3.00 600 13.2 1.31 9.0 97 2.97 3.39 2.3 1.7 3.8 460 2.15 7.0 0.64 2.44 2.03 460 1.32 1.05 99 3.12 <t< th=""><th>т</th><th></th><th>W</th><th>PD</th><th></th><th>C</th><th>cooling</th><th>g - EAT</th><th>80/67°</th><th>F</th><th></th><th></th><th>He</th><th>eating -</th><th>EAT 7</th><th>0°F</th><th></th></t<> | т | | W | PD | | C | cooling | g - EAT | 80/67° | F | | | He | eating - | EAT 7 | 0°F | |
|--|---|------------|-----|-----|-----|------|----------|----------|--------|------|------|-----|-------|----------|--------|--------|--------------|
| 4.5 7.2 16.7 CP28100/1011(2000) 600 11.4 11.3 7.6 88 288 23 21 24 43 600 23.3 16.1 0.77 23.5 30.6 600 12.4 12.8 28.9 90 32.3 3.4 3.4 3.4 7.0 400 23.3 16.1 0.77 23.5 30.8 600 13.3 11.9 8.9 90 32.3 4.5 5.9 13.7 460 22.3 14.4 0.62 26.4 90.0 600 15.5 11.7 90 91 33.8 2.3 1.7 3.3 640 22.8 16.0 0.70 0.76 23.9 15.5 11.8 10.0 10.6 13.3 13.8 99 99 31.5 2.3 1.4 3.3 600 22.6 14.5 0.64 0.77 24.9 14.9 12.8 12.4 12.8 13.3 10.8 1 | : | GPM | PSI | FT | | тс | SC | | kW | HR | EER | | нс | kW | HE | LAT | СОР |
| 23 24 140 400 221 142 046 077 255 056 127 156 62 63 64 62 62 63 64 62 64 63 64 63 64 63 64 63 64 63 64 63 64 63 64 63 64 63 64 63 64 63 64 63 64 <th64< th=""> 64 <th64< th=""></th64<></th64<> |) | | | | | Or | peration | not reco | mmend | ed | | | | | | | 2.61 |
| 2.3 2.1 4.9 600 22.0 16.1 0.70 0.75 25.5 30.8 600 12.7 13.6 8.8 90 32.2 3.4 3.4 7.7 600 22.3 16.4 0.88 0.67 27.3 35.8 600 13.7 19.9 97 33 4.5 5.5 17.7 3.9 600 22.3 16.4 0.88 23.9 25.6 490 13.3 99 98 31.5 2.3 17.7 3.9 600 22.0 16.7 0.72 0.86 24.9 25.6 490 14.7 12.0 10.8 93 35.9 3.4 2.0 6.7 45.0 21.8 14.2 0.66 0.79 24.4 23.3 450 16.0 13.8 10.67 13.8 10.67 13.8 10.67 13.8 10.67 13.8 10.67 13.8 10.67 13.8 11.7 10.3 40.3 < | | | | | 450 | | | | | | 30.7 | | | | | | |
| 3.4 3.4 3.4 7.9 600 23.9 16.3 0.68 0.67 26.1 35.8 600 13.2 13.1 17 9.3 90 33.3 90 33.3 90 93.3 90 33.3 90 93.3 | | 2.3 | 2.1 | 4.9 | 600 | 23.0 | 16.1 | 0.70 | 0.75 | 25.5 | 30.8 | 600 | 12.7 | 1.16 | 8.8 | 90 | 3.22 |
| 4.5 5.9 13.7 460 23.3 14.4 0.62 0.80 25.3 30.0 460 13.2 1.11 9.6 97 2.9 2.3 1.7 3.9 460 21.1 13.9 0.66 0.82 23.9 25.6 450 14.3 1.33 9.9 98 3.5 2.3 1.7 3.9 460 21.2 1.67 0.72 0.66 2.42 2.8 460 14.7 1.20 10.8 3.35 4.5 5.1 11.8 600 2.5 16.4 0.70 0.74 2.59 31.9 600 16.3 1.37 11.7 10.3 3.4 2.3 1.4 3.3 600 2.17 15.8 0.72 2.44 450 16.3 1.37 11.7 10.3 3.4 2.4 6.40 10.6 0.68 2.47 2.44 6.40 17.4 1.35 1.37 1.47 1.34 10.7 </th <th></th> | | | | | | | | | | | | | | | | | |
| 2 3 1.7 3.9 460 21.1 13.9 0.66 0.82 23.9 25.6 460 14.8 13.3 0.9 90 3.5 3.4 2.9 6.7 480 21.9 14.2 0.66 0.76 24.4 29.3 460 15.0 1.3 10.4 3.5 4.4 5.4 1.13 400 22.5 14.6 0.07 0.74 22.4 23.5 11.4 3.4 3.4 11.4 3.4 3.4 11.4 3.4 3.4 400 22.5 11.4 0.74 3.2 11.4 11.3 11.4 11.4 11.3 11.4 11.4 11.3 11.4 11.4 11.4 | | | | | | | | | | | | | | | | | 2.97 |
| 2.3 1.7 3.9 600 22.0 15.7 0.72 0.86 2.44 22.6 600 15.0 15.3 12.0 10.66 98 3.55 3.4 2.9 6.7 600 22.8 16.0 0.70 0.78 25.4 23.3 16.0 15.3 12.1 11.2 94 3.72 4.5 6.1 11.8 600 22.5 16.4 0.76 0.77 25.6 31.9 260 16.7 12.7 11.5 94 3.77 3.72 12.5 11.5 94 3.7 12.4 105 3.7 12.7 106 3.7 12.7 106 3.7 12.7 106 3.6 12.7 12.4 105 3.6 94 3.4 2.6 10.6 12.7 10.6 3.6 94 2.2 14.4 10.0 13.8 12.4 105 3.6 94 13.4 11.6 11.6 11.6 11.6 11.6 11.6 | | | | | | | | | | | | | | | | | 3.38 |
| 3.4 2.9 6.7 6.67 4.50 21.9 1.4.2 0.65 0.75 2.4.4 2.9.3 450 1.50 1.35 1.06 1.04 1.04 1.06 1.04 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.06 1.06 1.06 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 1.05 | | | | | | | | | | | | | | | | | |
| 4.5 5.1 11.8 450 22.5 14.5 0.64 0.71 24.9 31.9 450 15.3 1.35 10.8 10.2 13.3 2.3 14 3.3 450 22.4 13.7 0.67 0.33 22.5 21.9 450 16.3 1.37 11.7 10.3 3.47 2.3 14.4 3.3 450 22.6 15.6 0.60 15.7 12.4 10.5 3.67 3.4 2.6 5.9 4450 450 22.4 430 10.6 12.4 10.5 3.67 4.5 6.6 10.6 0.02 22.1 15.8 0.67 0.68 24.9 26.1 600 11.4 14.4 10.4 17.4 12.5 13.6 96 4.13 2.3 13.3 2.9 600 20.1 14.9 0.74 10.8 22.8 16.8 600 12.6 12.6 13.6 14.2 14.2 < | | 3.4 | 2.9 | 6.7 | 450 | 21.9 | 14.2 | 0.65 | 0.75 | 24.4 | 29.3 | 450 | 15.0 | 1.35 | 10.5 | 101 | 3.26 |
| 4.5 5.1 11.8 600 23.5 11.6 94.3 27.2 11.6 94.3 23.3 1.4 33.3 600 21.2 15.5 0.73 0.97 24.5 22.0 600 16.6 1.37 11.7 10.3 34.4 3.4 2.6 5.9 400 21.6 13.8 0.60 0.85 23.7 24.4 450 17.4 1.25 13.2 97 4.10 4.5 4.6 10.6 460 21.1 13.9 0.60 0.81 23.9 24.1 460 17.4 1.28 13.3 2.9 7.7 10.0 3.5 2.3 1.3 2.9 460 13.4 0.66 0.81 2.8 81.6 600 18.2 1.4 | | | | | | | | | | | | | | | | | |
| 2.3 1.4 3.3 600 21.2 15.5 0.73 0.97 24.5 22.0 600 16.6 1.23 12.5 986 386 3.4 2.6 5.9 600 21.7 15.6 0.72 0.88 24.7 24.4 450 17.4 1.25 13.2 97 4.10 4.5 4.6 10.6 600 22.1 15.8 0.72 0.88 24.7 24.4 450 17.4 1.38 12.7 10.6 3.6 2.3 1.3 2.9 600 22.1 15.8 0.72 0.88 1.04 22.8 1.84 450 17.4 1.39 12.4 1.04 1.07 3.7 1.39 22.8 1.44 1.43 1.42 1.42 1.42 1.42 1.42 1.42 1.42 1.42 1.03 3.3 1.3 2.6 1.33 1.25 1.01 4.34 1.7 1.28 1.07 1.23 1.10 | | | | | | | | | | | | | | | | | 3.78 |
| 1 3.4 2.6 5.9 450 20.8 13.8 0.66 0.85 23.7 24.4 460 17.0 13.8 12.4 1005 36.6 4.5 4.6 10.6 450 21.7 15.6 0.031 23.9 26.1 450 17.4 13.8 12.7 1006 36.7 2.3 1.3 2.9 450 19.3 13.2 0.08 1.04 22.8 18.6 600 18.2 14.4 13.4 107 3.7 3.4 2.3 5.3 450 19.8 13.4 0.68 0.99 23.0 20.6 650 19.1 1.42 14.2 109 3.3 3.4 2.3 5.3 650 19.8 13.4 0.68 10.3 20.0 660 19.1 12.2 10.4 43.4 4.5 4.2 9.6 600 19.7 0.90 22.3 17.4 650 22.1 13.4 13.4< | | | | | | | | | | | | | | | | | 3.47 |
| 3.4 2.6 5.9 600 21.7 15.6 0.72 0.89 24.7 24.4 600 17.4 1.28 13.2 97 4.10 4.5 4.6 10.6 600 22.1 15.8 0.72 0.85 24.9 26.1 600 17.4 1.28 13.4 19.7 4.10 2.3 1.3 2.9 600 20.1 14.9 0.74 1.08 23.8 18.6 650 18.6 14.2 14.4 19.9 4.33 3.4 2.3 6.3 600 20.1 15.1 0.73 100 24.0 20.6 450 11.1 14.2 14.2 100 44.3 4.5 4.2 6.6 0.00 10.7 100 24.0 20.6 115.8 600 116.2 117.7 103 24.6 600 116.7 117.4 128 117.7 103 24.6 600 116.7 117.7 14.7 14.8 | | | | | | | | | | | | | | | | | |
| 4.5 4.6 10.6 600 22.1 15.8 0.72 0.86 24.9 26.1 1800 17.9 1.25 13.4 10.7 3.7 2.3 1.3 2.9 600 20.1 14.9 0.74 1.06 23.8 18.6 450 18.5 14.2 10.9 3.3 3.4 2.3 6.3 600 20.6 15.1 0.73 1.00 24.0 20.6 450 19.1 14.2 10.9 3.3 4.5 4.2 9.6 6400 21.0 15.3 0.67 0.67 23.3 21.9 450 14.6 14.7 110 4.6 2.3 1.1 2.6 660 18.0 14.3 0.76 1.20 23.1 15.8 450 18.2 10.2 14.4 16.2 10.2 44.6 3.4 2.1 4.9 600 18.4 10.0 14.3 0.77 1.29 16.2 10.2 1 | | 3.4 | 2.6 | 5.9 | 600 | 21.7 | 15.6 | 0.72 | 0.89 | 24.7 | 24.4 | 600 | 17.4 | 1.25 | 13.2 | 97 | 4.10 |
| 2.3 1.3 2.9 450 19.3 13.2 0.68 1.04 22.8 18.6 600 18.6 1.41 13.4 107 3.79 3.4 2.3 5.3 450 19.8 13.4 0.68 2.0 2.06 660 19.6 11.42 14.2 109 3.33 3.4 2.3 5.3 450 2.06 15.1 0.77 0.92 2.33 21.9 660 1.43 14.7 110 4.01 4.5 4.2 9.6 450 18.2 1.7 0.69 1.15 22.1 15.8 660 20.7 1.29 15.2 12.4 4.51 1.14 4.52 1.12 4.51 1.14 4.52 1.12 4.51 1.11 1.2.6 1.11 1.2.1 1.12 2.2.1 1.45 1.46 1.14 4.27 3.4 2.1 4.9 450 18.7 1.28 0.76 1.22.3 1.74 4.60 | | | | | | | | | | | | | | | | | |
| 3.4 2.3 5.3 450 19.8 13.4 0.68 0.96 22.0 20.6 450 19.6 1.28 15.2 100 44.5 4.5 4.2 9.6 450 20.1 15.3 0.67 0.92 23.3 21.9 600 20.1 14.3 14.7 110 4.6 4.5 4.2 9.6 600 20.1 15.3 0.67 0.92 23.3 21.9 600 20.1 12.9 15.7 114 450 2.3 1.1 2.6 450 18.2 12.7 0.69 1.15 22.1 15.8 600 20.7 12.9 15.2 112 4.11 2.3 1.0 2.3 450 19.1 13.0 0.68 1.03 22.6 18.4 600 21.7 1.14 14.4 4.27 3.4 2.0 4.5 4.50 17.7 12.7 0.71 12.8 21.4 13.3 600< | | 2.3 | 1.3 | 2.9 | 450 | 19.3 | 13.2 | 0.68 | 1.04 | 22.8 | 18.6 | 450 | 18.2 | 1.41 | 13.4 | 107 | 3.79 |
| 3.4 2.3 5.3 600 20.6 15.1 0.73 1.00 24.0 20.6 600 19.6 1.28 15.2 100 4.40 4.5 4.2 9.6 600 21.0 15.3 0.73 0.96 24.2 21.9 450 10.6 12.9 15.7 101 4.66 2.3 1.1 2.6 600 19.0 14.3 0.77 0.82 17.1 15.8 4.65 0.20 1.44 15.2 112 4.14 10.7 22.3 17.4 4.60 21.7 1.31 17.2 10.3 4.66 4.5 3.9 8.9 600 19.1 13.0 0.68 10.3 22.6 18.4 4.60 22.7 1.32 17.4 4.60 22.3 1.32 17.7 13.3 4.50 22.3 13.3 4.60 22.7 1.32 14.4 10.3 6.00 22.3 1.32 13.5 10.7 13.5 11.7 <th></th> <th>4.32</th> | | | | | | | | | | | | | | | | | 4.32 |
| 4.5 4.2 9.6 600 21.0 15.3 0.73 0.96 24.2 21.9 600 20.1 1.29 15.7 10.1 4.6 2.3 1.1 2.6 600 19.0 14.3 0.76 1.20 23.1 15.8 650 20.2 1.24 15.2 10.2 4.66 3.4 2.1 4.9 600 18.7 12.8 0.69 10.7 2.3 17.4 450 21.2 1.46 16.1 11.4 4.27 4.5 3.9 8.9 600 19.4 14.5 0.75 1.12 22.3 13.2 1.7 1.31 17.7 1.03 4.66 15.4 4.50 22.3 1.32 17.4 4.50 22.3 1.32 1.74 14.6 16.4 14.4 600 22.3 1.32 17.8 10.4 4.96 2.3 1.34 10.0 2.3 10.0 2.3 10.0 1.4 10.0 1.6 | | 3.4 | 2.3 | | | | | | 1.00 | 24.0 | | | | | | | 4.49 |
| 2.3 1.1 2.6 450 18.2 12.7 0.69 1.16 22.1 15.8 450 20.2 1.44 15.2 11.2 4.11 2.3 4 2.1 4.9 450 18.7 12.8 0.69 1.07 22.3 17.4 450 21.2 1.46 16.1 11.4 4.27 3.4 2.1 4.9 600 19.4 14.5 0.75 11.2 22.3 17.4 450 21.7 1.46 16.1 11.4 4.27 4.5 3.8 8.9 450 19.1 13.0 0.68 10.3 22.6 18.4 450 21.7 1.46 16.6 11.5 4.50 2.3 10 2.3 460 17.7 13.7 0.77 13.3 22.2 13.3 450 22.3 13.3 450 22.3 13.4 450 22.3 13.4 450 22.3 13.4 450 22.3 13.4 | | | | | | | | | | | | | | | | | 4.01 |
| 3.4 2.1 4.9 650 18.7 12.8 0.69 1.07 22.3 17.4 450 21.2 1.46 16.1 114 4.27 4.5 3.9 8.9 450 19.1 13.0 0.68 10.3 22.6 18.4 450 21.7 1.31 17.4 16.6 115.4 4.5 2.3 1.0 2.3 450 17.0 12.1 0.71 12.8 21.4 13.3 450 22.1 1.47 17.4 4.90 2.3 1.0 2.3 600 17.7 1.37 0.77 1.33 22.3 1.34 4.0 4.6 3.4 2.0 4.5 450 1.75 1.23 0.70 1.20 21.6 1.47 450 23.3 1.49 1.80 107 52.3 3.4 2.0 4.5 4.5 600 18.7 1.41 0.76 1.20 21.6 1.47 450 22.3 1.49 | | | | | | | | | | | | | | | | | 4.56 |
| 3.4 2.1 4.9 600 19.4 14.5 0.75 1.12 23.2 17.4 600 21.7 1.131 17.2 103 4.86 4.5 3.9 8.9 600 19.8 14.7 0.74 108 23.5 18.4 600 22.3 1.32 17.8 104 4.96 2.3 1.0 2.3 600 17.7 1.37 0.77 1.33 22.1 1.47 1.06 4.45 2.3 1.0 2.3 600 17.7 1.37 0.77 1.33 22.1 1.47 1.06 4.45 3.4 2.0 4.5 600 17.5 12.0 0.16 1.47 4.50 22.3 1.49 18.0 118 4.50 4.5 3.6 8.3 600 18.7 12.3 0.70 12.2 22.8 15.5 450 23.9 1.34 19.3 10.7 52.3 4.5 3.6 8.3 </th <th></th> <th>4.68</th> | | | | | | | | | | | | | | | | | 4.68 |
| 4.5 3.9 8.9 450 19.1 13.0 0.68 10.03 22.6 18.4 450 21.7 1.46 16.6 115 4.35 2.3 1.0 2.3 450 17.0 12.1 0.71 12.8 21.4 13.3 450 22.1 1.32 17.8 104 4.96 2.3 1.0 2.3 600 17.7 13.3 0.70 12.2 3.31 450 22.1 1.47 17.0 116 4.95 3.4 2.0 4.5 600 17.9 12.0 0.70 12.0 22.16 14.7 600 23.3 1.49 18.0 118 4.5 4.5 3.6 8.3 600 17.9 1.35 0.77 1.33 1.14 1.9 1.35 1.9 1.84 1.9 4.4 1.9 4.4 1.9 1.36 1.9 1.26 1.55 600 2.47 1.33 1.91 107 5.20 |) | | | | | | | | | | | | | | | | |
| 2.3 1.0 2.3 450 17.0 12.1 0.71 1.28 21.4 13.3 450 22.1 1.47 17.0 116 4.41 2.3 1.0 2.3 600 17.7 13.3 0.77 1.33 22.3 13.3 600 22.7 1.32 18.2 105 5.03 3.4 2.0 4.5 600 18.3 13.9 0.76 1.25 2.6 14.7 600 23.9 1.34 19.3 107 5.23 4.5 3.6 8.3 450 16.4 11.8 0.72 1.35 21.9 1.55 600 23.9 1.50 18.6 119 4.66 2.3 1.0 2.2 450 16.4 11.8 0.72 1.35 21.0 12.2 450 23.1 1.49 17.9 118 4.56 3.4 1.9 4.4 450 17.3 12.2 0.70 1.22 453 450 2.0 1.60 2.43 1.50 1.86 2.0 1.7 1.33 | | 4.5 | 3.9 | 8.9 | 450 | 19.1 | 13.0 | 0.68 | 1.03 | 22.6 | 18.4 | 450 | 21.7 | 1.46 | 16.6 | 115 | 4.35 |
| 2.3 1.0 2.3 4.00 1.7.7 1.3.7 0.7.7 1.3.3 22.3 13.3 600 22.7 1.3.2 18.2 10.5 5.0 3.4 2.0 4.5 500 17.5 12.3 0.70 1.25 22.5 14.7 600 23.9 1.34 19.3 107 52.3 4.5 3.6 8.3 450 17.9 12.5 0.69 1.15 21.9 15.5 450 23.9 1.50 18.6 119 4.66 2.3 1.0 2.2 450 16.4 11.8 0.72 1.35 21.0 1.22 450 23.1 1.49 17.9 118 4.56 2.3 1.0 2.2 450 16.4 11.8 0.72 1.35 21.0 1.35 1.0 1.0 1.0 2.2 1.0 2.2 1.0 1.2 21.0 1.35 1.0 1.0 1.0 2.0 23.1 1.49 1 | | | | | | | | | | | | | | | | | |
| 3.4 2.0 4.5 600 18.3 13.9 0.76 1.25 22.5 14.7 600 23.9 1.34 19.3 107 5.23 4.5 3.6 8.3 450 17.9 12.5 0.69 1.15 21.9 15.5 450 23.9 1.34 19.3 107 5.23 2.3 1.0 2.2 450 16.4 11.8 0.72 1.35 21.0 12.2 450 23.1 1.49 17.9 118 4.56 2.3 1.0 2.2 450 17.3 10.7 13.3 0.78 1.40 21.9 12.2 450 23.1 1.49 17.9 118 4.56 3.4 1.9 4.4 450 16.9 12.0 0.71 1.26 21.2 13.5 600 24.3 15.5 20.3 108 5.41 4.5 3.5 8.1 450 15.8 11.5 0.77 1.31 22.1 13.5 600 24.3 15.5 20.3 108 5.41 4.50 | | 2.3 | 1.0 | 2.3 | 600 | 17.7 | 13.7 | 0.77 | 1.33 | 22.3 | 13.3 | 600 | 22.7 | 1.32 | 18.2 | 105 | 5.03 |
| 4.5 3.6 8.3 450 17.9 12.5 0.69 1.15 21.9 15.5 450 23.9 1.50 18.6 119 4.68 2.3 1.0 2.2 450 16.4 11.8 0.72 1.35 21.0 12.2 450 23.1 1.49 17.9 118 4.56 3.4 1.9 4.4 450 16.9 12.0 0.71 1.26 21.2 13.5 450 23.1 1.49 17.9 118 4.56 3.4 1.9 4.4 600 17.6 13.5 0.77 1.31 22.1 13.5 600 24.9 1.35 20.3 108 5.44 4.5 3.5 8.1 600 18.0 13.8 0.76 1.22 21.4 14.3 600 25.6 1.51 19.6 12.0 4.54 2.3 0.9 2.1 600 16.4 13.0 0.73 1.42 20.6 11.1 450 25.6 1.51 10.6 1.55 1.50 10.6 5.57 | | | | | | | | | | | | | | | | | 4.59 |
| 2.3 1.0 2.2 450 16.4 11.8 0.72 1.35 21.0 12.2 450 23.1 1.49 17.9 118 4.55 3.4 1.9 4.4 450 16.9 12.0 0.71 13.5 600 23.7 1.33 19.1 107 5.20 3.4 1.9 4.4 600 17.6 13.5 0.77 1.31 22.1 13.5 600 24.9 1.35 20.3 108 5.41 4.5 3.5 8.1 600 18.0 13.8 0.76 1.27 22.4 14.3 600 25.6 1.36 20.9 110 5.51 2.3 0.9 2.1 650 15.8 11.5 0.73 1.42 20.6 11.1 450 24.7 1.35 20.1 108 5.37 3.4 1.8 4.2 450 16.3 11.7 0.71 1.33 20.8 12.3 450 26.1 1.53 20.6 1.32 20.0 12.2 480 45.3 3.4 < | | 4.5 | | | 450 | 17.9 | | | 1.15 | 21.9 | 15.5 | 450 | 23.9 | 1.50 | | 119 | 4.68 |
| 2.3 1.0 2.2 600 17.1 13.3 0.78 1.40 21.9 12.2 600 23.7 1.33 19.1 107 5.20 3.4 1.9 4.4 450 16.9 12.0 0.71 1.26 21.2 13.5 450 24.3 1.50 19.0 12.0 4.74 4.5 3.5 8.1 450 17.3 12.2 0.70 1.22 21.5 14.3 450 25.0 1.51 19.6 12.1 4.54 4.5 3.5 8.1 600 18.0 13.8 0.76 1.27 22.4 14.3 600 25.6 1.36 20.9 110 5.51 2.3 0.9 2.1 450 16.8 11.5 0.73 1.42 20.6 11.1 450 24.1 1.50 18.8 12.0 4.71 3.4 1.8 4.2 450 16.3 11.7 0.71 13.3 20.8 12.3 450 25.4 1.52 20.0 122 4.88 4.5 3.4 | | | | | | | | | | | | | | | | | 5.34 |
| 3.4 1.9 4.4 600 17.6 13.5 0.77 1.31 22.1 13.5 600 24.9 1.35 20.3 108 5.41 4.5 3.5 8.1 450 17.3 12.2 0.70 1.22 21.5 14.3 450 25.0 1.51 19.6 121 4.84 4.5 3.5 8.1 600 16.0 13.8 0.76 1.22 22.4 14.3 600 25.6 1.36 20.9 110 5.51 2.3 0.9 2.1 600 16.4 13.0 0.79 1.48 21.5 11.1 600 24.7 1.35 20.1 108 5.37 3.4 1.8 4.2 600 17.0 13.2 0.78 1.38 21.7 12.3 600 26.0 1.37 21.3 110 5.58 4.5 3.4 7.9 600 17.4 13.4 0.77 1.38 21.1 13.0 450 26.1 1.53 20.6 12.4 4.99 4.5 3.4 < | | | | | | | | | | | | | | | | | 4.50 5.20 |
| 4.5 3.5 8.1 450 17.3 12.2 0.70 1.22 21.5 14.3 450 25.0 1.51 19.6 121 4.84 4.5 3.5 8.1 600 18.0 13.8 0.76 1.27 22.4 14.3 600 25.6 1.51 19.6 121 4.84 2.3 0.9 2.1 600 16.4 13.0 0.79 1.48 21.5 11.1 600 24.7 1.35 20.1 108 5.37 3.4 1.8 4.2 450 16.3 11.7 0.71 1.33 20.8 12.3 450 25.4 1.52 20.1 108 5.37 4.5 3.4 7.9 450 16.7 11.9 0.71 1.28 21.1 13.0 450 26.1 1.53 20.6 124 4.99 4.5 3.4 7.9 600 17.4 13.4 0.76 1.57 19.8 9.2 26.7 1.38 22.0 111 5.69 2.3 0.9 <td< th=""><th>;</th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th>4.74</th></td<> | ; | | | | | | | | | | | | | | | | 4.74 |
| 4.5 3.5 8.1 600 18.0 13.8 0.76 1.27 22.4 14.3 600 25.6 1.36 20.9 110 5.51 2.3 0.9 2.1 450 15.8 11.5 0.73 1.42 20.6 11.1 450 24.1 1.50 18.8 120 4.71 2.3 0.9 2.1 600 17.0 13.0 0.79 1.48 21.5 11.1 600 26.4 1.52 20.0 108 5.37 3.4 1.8 4.2 450 16.3 11.7 0.71 1.33 20.8 12.3 450 25.4 1.52 20.0 122 4.88 4.5 3.4 7.9 600 17.0 13.2 0.78 1.38 21.7 12.3 600 26.1 1.53 20.6 12.4 4.99 4.5 3.4 7.9 600 17.4 13.4 0.77 1.57 19.8 9.2 600 26.7 1.38 22.0 111 5.69 2.3 <t< th=""><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th></t<> | | | | | | | | | | | | | | | | | |
| 2.3 0.9 2.1 600 16.4 13.0 0.79 1.48 21.5 11.1 600 24.7 1.35 20.1 108 5.37 3.4 1.8 4.2 450 16.3 11.7 0.71 1.33 20.8 12.3 450 25.4 1.52 20.0 122 4.88 4.5 3.4 7.9 450 16.7 11.9 0.71 1.28 21.1 13.0 450 26.0 1.37 21.3 110 5.58 4.5 3.4 7.9 600 17.4 13.4 0.77 1.34 22.0 13.0 600 26.7 1.38 22.0 111 5.69 2.3 0.9 2.0 450 15.0 11.0 0.74 1.48 20.0 10.1 1.33 22.0 111 5.69 2.3 0.9 2.0 600 15.6 12.5 0.80 1.54 20.8 10.1 1.48 20.4 10.1 1.45 22.0 10.1 1.48 20.1 10.8 7.4 | | 4.5 | 3.5 | 8.1 | 600 | 18.0 | 13.8 | 0.76 | 1.27 | 22.4 | 14.3 | 600 | 25.6 | 1.36 | 20.9 | 110 | 5.51 |
| 3.4 1.8 4.2 450 16.3 11.7 0.71 1.33 20.8 12.3 450 25.4 1.52 20.0 122 4.89 4.5 3.4 7.9 600 17.0 13.2 0.78 1.38 21.7 12.3 600 26.0 1.37 21.3 110 5.58 4.5 3.4 7.9 600 17.4 13.4 0.77 1.34 22.0 13.0 600 26.1 1.53 20.6 124 4.99 2.3 0.9 2.0 450 14.4 10.8 0.75 1.57 19.8 9.2 26.7 1.38 22.0 111 5.69 2.3 0.9 2.0 600 15.0 12.2 0.82 1.63 20.6 9.2 3.4 1.7 4.0 600 15.6 12.5 0.80 1.54 20.3 10.1 1.83 20.0 10.1 1.43 20.3 10.8 1.45 3.2 7.4 450 13.5 10.3 0.76 1.64 19.1 8.2 | | | | | | | | | | | | | | | | | |
| 4.5 3.4 7.9 450 16.7 11.9 0.71 1.28 21.1 13.0 450 26.1 1.53 20.6 124 4.99 2.3 0.9 2.0 450 14.4 10.8 0.75 1.57 19.8 9.2 2.3 0.9 2.0 600 15.0 11.0 0.74 1.44 22.0 13.0 600 26.7 1.38 22.0 111 5.89 2.3 0.9 2.0 600 15.0 11.0 0.74 1.48 20.0 10.1 3.4 1.7 4.0 600 15.6 12.5 0.80 1.54 20.8 10.1 4.5 3.2 7.4 600 16.0 12.7 0.79 1.49 21.1 10.8 4.5 3.2 7.4 600 13.4 11.4 0.83 1.71 19.9 8.2 2.3 0.8 1.8 600 13.4 11.4 0.82 1.65 20.2 8.8 4.5 3.1 7.1 600 </th <th></th> <th>3.4</th> <th>1.8</th> <th>4.2</th> <th>450</th> <th>16.3</th> <th>11.7</th> <th>0.71</th> <th>1.33</th> <th>20.8</th> <th>12.3</th> <th>450</th> <th>25.4</th> <th>1.52</th> <th>20.0</th> <th>122</th> <th>4.89</th> | | 3.4 | 1.8 | 4.2 | 450 | 16.3 | 11.7 | 0.71 | 1.33 | 20.8 | 12.3 | 450 | 25.4 | 1.52 | 20.0 | 122 | 4.89 |
| 4.5 3.4 7.9 600 17.4 13.4 0.77 1.34 22.0 13.0 600 26.7 1.38 22.0 111 5.69 2.3 0.9 2.0 450 14.4 10.8 0.75 1.57 19.8 9.2 2.3 0.9 2.0 600 15.0 12.2 0.82 163 20.6 9.2 3.4 1.7 4.0 450 15.6 12.5 0.80 15.4 20.3 10.1 4.5 3.2 7.4 450 15.4 11.2 0.73 1.43 20.3 10.1 4.5 3.2 7.4 450 15.4 11.2 0.73 1.43 20.3 10.8 4.5 3.2 7.4 450 13.5 10.3 0.76 1.64 19.1 8.2 2.3 0.8 1.8 600 13.4 11.4 0.83 1.71 19.9 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 <th></th> | | | | | | | | | | | | | | | | | |
| 2.3 0.9 2.0 600 15.0 12.2 0.82 1.63 20.6 9.2 3.4 1.7 4.0 450 15.0 11.0 0.74 1.48 20.0 10.1 4.5 3.2 7.4 600 15.6 12.5 0.80 1.54 20.8 10.1 4.5 3.2 7.4 600 16.0 12.7 0.79 1.43 20.3 10.8 2.3 0.8 1.8 450 12.9 10.1 0.78 1.74 18.8 7.4 2.3 0.8 1.8 600 13.4 11.4 0.85 1.81 19.6 7.4 3.4 1.6 3.8 600 13.4 11.4 0.85 1.81 19.6 7.4 3.4 1.6 3.8 600 14.0 11.6 0.83 1.71 19.9 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 450 11.2 | | 4.5 | 3.4 | 7.9 | 600 | 17.4 | 13.4 | 0.77 | 1.34 | 22.0 | 13.0 | | | | | | 5.69 |
| 0 3.4 1.7 4.0 450 15.0 11.0 0.74 1.48 20.0 10.1 3.4 1.7 4.0 600 15.6 12.5 0.80 1.54 20.8 10.1 4.5 3.2 7.4 450 15.4 11.2 0.73 1.43 20.3 10.8 4.5 3.2 7.4 450 15.4 11.2 0.73 1.43 20.3 10.8 2.3 0.8 1.8 450 12.9 10.1 0.78 1.74 18.8 7.4 2.3 0.8 1.8 600 13.4 11.4 0.85 1.81 19.6 7.4 3.4 1.6 3.8 600 13.4 11.4 0.83 1.71 19.9 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 450 11.9 0.82 1.65 20.2 8.8 2.3 0.7 1.7 450 11.8 | | | | | | | | | | | | | | | | | |
| 4.5 3.2 7.4 450 15.4 11.2 0.73 1.43 20.3 10.8 4.5 3.2 7.4 600 16.0 12.7 0.79 1.49 21.1 10.8 2.3 0.8 1.8 450 12.9 10.1 0.78 1.74 18.8 7.4 2.3 0.8 1.8 600 13.4 11.4 0.85 18.1 19.6 7.4 2.3 0.8 1.8 600 13.4 11.4 0.85 18.1 19.6 7.4 3.4 1.6 3.8 450 13.5 10.3 0.76 1.64 19.1 8.2 3.4 1.6 3.8 600 14.0 11.6 0.83 1.71 19.9 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 600 11.6 10.4 0.89 2.00 18.5 5.8 2.3 0.7 1.7 600 11.6 | n | | | | | | | | | | | | | | | | |
| 4.5 3.2 7.4 600 16.0 12.7 0.79 1.49 21.1 10.8 2.3 0.8 1.8 450 12.9 10.1 0.78 1.74 18.8 7.4 2.3 0.8 1.8 600 13.4 11.4 0.85 1.81 19.6 7.4 3.4 1.6 3.8 600 13.4 11.4 0.85 1.81 19.6 7.4 3.4 1.6 3.8 600 14.0 11.6 0.83 1.71 19.9 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 600 14.5 11.9 0.82 1.65 20.2 8.8 2.3 0.7 1.7 450 11.2 9.2 0.78 5.8 2.3 0.7 1.7 600 11.6 10.4 0.89 2.00 18.5 5.8 2.3 0.7 1.7 600 11.8 9.5 0.80 | | | | | | | | | | | | | | | | | |
| 2.3 0.8 1.8 600 13.4 11.4 0.85 1.81 19.6 7.4 3.4 1.6 3.8 450 13.5 10.3 0.76 1.64 19.1 8.2 3.4 1.6 3.8 450 13.5 10.3 0.76 1.64 19.1 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 600 14.5 11.9 0.82 1.65 20.2 8.8 2.3 0.7 1.7 600 11.2 9.2 0.82 1.92 17.8 5.8 2.3 0.7 1.7 600 11.8 9.5 0.80 1.82 18.1 6.5 3.4 1.6 3.6 450 11.8 9.5 0.80 1.82 18.1 6.5 3.4 1.6 3.6 600 12.3 10.7 0.87 1.89 18.8 6.5 4.5 2.9 6.8 450 12.3 | | | | | | 16.0 | | | 1.49 | | | | | | | | |
| 0 3.4 1.6 3.8 450 13.5 10.3 0.76 1.64 19.1 8.2 3.4 1.6 3.8 600 14.0 11.6 0.83 1.71 19.9 8.2 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 600 14.5 11.9 0.82 1.65 20.2 8.8 2.3 0.7 1.7 450 11.2 9.2 0.82 1.92 17.8 5.8 2.3 0.7 1.7 450 11.6 0.4 0.89 2.00 18.5 5.8 3.4 1.6 3.6 450 11.8 9.5 0.80 182 18.1 6.5 3.4 1.6 3.6 450 12.3 9.7 0.79 1.77 18.4 7.0 0 3.4 1.6 3.6 450 12.3 9.7 0.79 1.77 18.4 7.0 <th></th> | | | | | | | | | | | | | | | | | |
| J 3.4 1.6 3.8 600 14.0 11.6 0.83 1.71 19.9 8.2 Operation not recommended 4.5 3.1 7.1 450 13.9 10.5 0.75 1.59 19.4 8.8 4.5 3.1 7.1 600 14.5 11.9 0.82 1.65 20.2 8.8 2.3 0.7 1.7 450 11.2 9.2 0.82 1.92 17.8 5.8 2.3 0.7 1.7 600 11.6 10.4 0.89 2.00 18.5 5.8 2.3 0.7 1.7 600 11.8 9.5 0.80 1.82 18.1 6.5 3.4 1.6 3.6 450 12.3 9.7 0.79 1.77 18.4 7.0 | | | | | | | | | | | | | 0 | | | | |
| 4.5 3.1 7.1 600 14.5 11.9 0.82 1.65 20.2 8.8 2.3 0.7 1.7 450 11.2 9.2 0.82 1.92 17.8 5.8 2.3 0.7 1.7 600 11.6 10.4 0.89 2.00 18.5 5.8 3.4 1.6 3.6 450 11.8 9.5 0.80 1.82 18.1 6.5 3.4 1.6 3.6 600 12.3 10.7 0.87 1.89 18.8 6.5 4.5 2.9 6.8 450 12.3 9.7 0.79 1.77 18.4 7.0 | | 3.4 | 1.6 | 3.8 | 600 | 14.0 | 11.6 | 0.83 | 1.71 | 19.9 | 8.2 | | Opera | mon not | recomm | lended | |
| 2.3 0.7 1.7 450 11.2 9.2 0.82 1.92 17.8 5.8 2.3 0.7 1.7 600 11.6 10.4 0.89 2.00 18.5 5.8 3.4 1.6 3.6 450 11.8 9.5 0.80 1.82 18.1 6.5 3.4 1.6 3.6 600 12.3 10.7 0.87 1.89 18.8 6.5 4.5 2.9 6.8 450 12.3 9.7 0.79 1.77 18.4 7.0 | | 4.5 4.5 | | | | | | | | | | | | | | | |
| 3.4 1.6 3.6 450 11.8 9.5 0.80 1.82 18.1 6.5 3.4 1.6 3.6 600 12.3 10.7 0.87 1.89 18.8 6.5 4.5 2.9 6.8 450 12.3 9.7 0.79 1.77 18.4 7.0 | | 2.3 | 0.7 | 1.7 | 450 | 11.2 | 9.2 | 0.82 | 1.92 | 17.8 | 5.8 | | | | | | |
| J 3.4 1.6 3.6 600 12.3 10.7 0.87 1.89 18.8 6.5 4.5 2.9 6.8 450 12.3 9.7 0.79 1.77 18.4 7.0 | | | | | | | | | | | | | | | | | |
| | U | 3.4 | 1.6 | 3.6 | 600 | 12.3 | 10.7 | 0.87 | 1.89 | 18.8 | 6.5 | | | | | | |
| | | 4.5 4.5 | | | | | | | | | | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/SO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/SO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply: performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 024

Performance capacities shown in thousands of Btuh

| EWT | | W | PD | | | Coolin | g - EAT | 80/67 ° | F | | | He | eating - | EAT 7 | 0°F | |
|-----|------------|-------------------|--------------------|----------------|---------------------|---------------------|-------------------|---------------------|---------------------|---------------------|----------------|---------------------|--------------|---------------------|-------------------|--------------|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | НС | kW | HE | LAT | СОР |
| 20 | 6.0 6.0 | 8.5 8.5 | 19.6 19.6 | | 0 | peration | not reco | mmend | ed | | 640 850 | 15.5 15.9 | 1.91 1.71 | 9.5 10.1 | 92 87 | 2.39 2.72 |
| | 3.0 | 2.2 | 5.2 | 640 | 27.7 | 17.4 | 0.63 | 1.12 | 31.5 | 24.8 | 640 | 17.2 | 1.93 | 11.0 | 95 | 2.61 |
| | 3.0 | 2.2 | 5.2 | 850 | 28.9 | 19.7 | 0.68 | 1.16 | 32.8 | 24.8 | 850 | 17.6 | 1.74 | 11.8 | 89 | 2.98 |
| 30 | 4.5 4.5 | 4.0 4.0 | 9.3 9.3 | 640 850 | 28.2 29.4 | 17.5 19.8 | 0.62 0.67 | 1.05 1.09 | 31.8 33.1 | 26.9 26.9 | 640 850 | 18.0 18.4 | 1.95 1.75 | 11.7 12.5 | 96 90 | 2.70 3.08 |
| | 6.0 | 7.2 | 16.7 | 640 | 28.5 | 17.5 | 0.62 | 1.02 | 31.9 | 28.0 | 640 | 18.4 | 1.95 | 12.1 | 97 | 2.76 |
| | 6.0 | 7.2 | 16.7 | 850 | 29.6 | 19.8 | 0.67 | 1.06 | 33.2 | 28.0 | 850 | 18.8 | 1.76 | 12.9 | 91 | 3.14 |
| | 3.0 3.0 | 1.9 1.9 | 4.4 4.4 | 640 850 | 26.9 28.0 | 17.1 19.4 | 0.64 0.69 | 1.23 1.28 | 31.1 32.4 | 21.9 21.9 | 640 850 | 19.9 20.4 | 1.98 1.78 | 13.4 14.4 | 99 92 | 2.94 3.36 |
| 40 | 4.5 | 3.6 | 8.2 | 640 | 28.0 | 19.4 | 0.63 | 1.20 | 31.4 | 21.9 | 640 | 20.4 | 2.00 | 14.4 | 100 | 3.06 |
| 40 | 4.5 | 3.6 | 8.2 | 850 | 28.7 | 19.6 | 0.68 | 1.19 | 32.7 | 24.0 | 850 | 21.3 | 1.79 | 15.3 | 93 | 3.49 |
| | 6.0 | 6.4 | 14.9 | 640 | 27.8 | 17.4 | 0.63 | 1.11 | 31.5 | 25.1 | 640 | 21.3 | 2.01 | 14.7 | 101 | 3.12 |
| | 6.0 3.0 | 6.4 1.7 | 14.9 3.9 | 850 640 | 28.9 26.2 | 19.7 16.9 | 0.68 | 1.16 1.36 | 32.8 30.8 | 25.1 19.3 | 850 640 | 21.9 22.6 | 1.80 2.03 | 15.7 15.9 | <u>94</u> 103 | 3.55 3.27 |
| | 3.0 | 1.7 | 3.9 | 850 | 20.2 | 10.5 | 0.00 | 1.42 | 32.1 | 19.3 | 850 | 23.2 | 1.82 | 17.0 | 95 | 3.72 |
| 50 | 4.5 | 3.2 | 7.4 | 640 | 26.7 | 17.0 | 0.64 | 1.26 | 31.0 | 21.1 | 640 | 23.7 | 2.05 | 16.9 | 104 | 3.39 |
| 50 | 4.5 | 3.2 | 7.4 | 850 | 27.8 | 19.3 | 0.69 | 1.32 | 32.2 | 21.1 | 850 | 24.3 | 1.84 | 18.0 | 96 | 3.87 |
| | 6.0 6.0 | 5.9 5.9 | 13.6 13.6 | 640 850 | 27.0 28.1 | 17.1 19.4 | 0.64 0.69 | 1.22 1.27 | 31.1 32.4 | 22.1 22.1 | 640 850 | 24.3 24.9 | 2.06 1.85 | 17.4 18.6 | 105 97 | 3.46 3.94 |
| | 3.0 | 1.5 | 3.5 | 640 | 25.3 | 16.6 | 0.66 | 1.52 | 30.4 | 16.7 | 640 | 25.3 | 2.08 | 18.3 | 107 | 3.57 |
| | 3.0 | 1.5 | 3.5 | 850 | 26.3 | 18.8 | 0.71 | 1.58 | 31.7 | 16.7 | 850 | 25.9 | 1.87 | 19.6 | 98 | 4.07 |
| 60 | 4.5 | 3.0 | 6.9 | 640 | 25.7 | 16.7 | 0.65 | 1.40 | 30.5 | 18.3 | 640 | 26.6 | 2.10 | 19.4 | 108 | 3.70 |
| | 4.5 6.0 | 3.0 5.5 | 6.9 12.6 | 850 640 | 26.8 26.1 | 18.9 | 0.70 0.64 | 1.46 1.35 | 31.7 30.6 | 18.3 19.3 | 850 640 | 27.2 27.2 | 1.89 2.12 | 20.7 20.0 | 100 109 | 4.22 3.77 |
| | 6.0 | 5.5 | 12.6 | 850 | 20.1 | 16.8 19.0 | 0.04 | 1.35 | 30.0 | 19.3 | 850 | 27.2 | 1.90 | 20.0 | 109 | 4.30 |
| | 3.0 | 1.4 | 3.2 | 640 | 24.1 | 16.2 | 0.67 | 1.70 | 29.9 | 14.2 | 640 | 27.9 | 2.13 | 20.7 | 110 | 3.84 |
| | 3.0 | 1.4 | 3.2 | 850 | 25.1 | 18.3 | 0.73 | 1.77 | 31.1 | 14.2 | 850 | 28.6 | 1.91 | 22.1 | 101 | 4.38 |
| 70 | 4.5 4.5 | 2.8 2.8 | 6.4 6.4 | 640 850 | 24.6 25.6 | 16.3 18.4 | 0.66 0.72 | 1.57 1.63 | 30.0 31.2 | 15.7 15.7 | 640 850 | 29.2 29.9 | 2.16 1.94 | 21.8 23.3 | 112 103 | 3.97 4.53 |
| | 6.0 | 2.8 5.2 | 0.4 11.9 | 640 | 25.0 | 16.4 | 0.72 | 1.51 | 30.1 | 16.6 | 640 | 29.9 | 2.17 | 23.5 | 103 | 4.04 |
| | 6.0 | 5.2 | 11.9 | 850 | 26.0 | 18.6 | 0.71 | 1.57 | 31.4 | 16.6 | 850 | 30.6 | 1.95 | 24.0 | 103 | 4.60 |
| | 3.0 | 1.3 | 3.0 | 640 | 22.9 | 15.7 | 0.69 | 1.91 | 29.4 | 12.0 | 640 | 30.4 | 2.18 | 22.9 | 114 | 4.08 |
| | 3.0 4.5 | 1.3 2.6 | 3.0 6.1 | 850 640 | 23.8 23.4 | 17.8 15.8 | 0.75 0.67 | 1.99 1.76 | 30.6 29.4 | 12.0 13.3 | 850 640 | 31.1 31.7 | 1.96 2.21 | 24.4 24.0 | 104 116 | 4.65 4.20 |
| 80 | 4.5 | 2.6 | 6.1 | 850 | 23.4 24.4 | 17.9 | 0.07 | 1.84 | 30.7 | 13.3 | 850 | 32.5 | 1.99 | 24.0 | 105 | 4.20 |
| | 6.0 | 4.9 | 11.3 | 640 | 23.8 | 16.0 | 0.67 | 1.70 | 29.6 | 14.1 | 640 | 32.4 | 2.23 | 24.6 | 117 | 4.26 |
| | 6.0 | 4.9 | 11.3 | 850 | 24.8 | 18.1 | 0.73 | 1.77 | 30.8 | 14.1 | 850 | 33.1 | 2.00 | 26.3 | 106 | 4.85 |
| | 3.0 3.0 | 1.3 1.3 | 2.9 2.9 | 640 850 | 22.2 23.1 | 15.5 17.5 | 0.70 0.76 | 2.03 2.12 | 29.2 30.4 | 11.0 11.0 | 640 850 | 31.5 32.3 | 2.21 1.98 | 23.8 25.5 | 116 105 | 4.18 4.77 |
| 05 | 4.5 | 2.6 | 5.9 | 640 | 22.8 | 15.6 | 0.68 | 1.88 | 29.2 | 12.2 | 640 | 32.7 | 2.24 | 25.0 | 103 | 4.29 |
| 85 | 4.5 | 2.6 | 5.9 | 850 | 23.7 | 17.6 | 0.74 | 1.95 | 30.4 | 12.2 | 850 | 33.5 | 2.01 | 26.7 | 107 | 4.89 |
| | 6.0 | 4.8 | 11.0 | 640 | 23.2 | 15.7 | 0.68 | 1.80 | 29.3 | 12.9 | 640 | 33.4 | 2.25 | 25.5 | 118 | 4.34 |
| | 6.0 3.0 | <u>4.8</u> 1.2 | <u>11.0</u> 2.8 | 850 640 | <u>24.1</u> 21.6 | <u>17.8</u> 15.3 | 0.74 | <u>1.88</u> 2.16 | <u>30.5</u> 28.9 | <u>12.9</u> 10.0 | 850 640 | <u>34.2</u> 32.6 | 2.02 | <u>27.2</u> 24.8 | <u>107</u> 117 | 4.95 4.28 |
| | 3.0 | 1.2 | 2.8 | 850 | 22.4 | 17.3 | 0.77 | 2.25 | 30.1 | 10.0 | 850 | 33.4 | 2.01 | 26.5 | 106 | 4.88 |
| 90 | 4.5 | 2.5 | 5.8 | 640 | 22.2 | 15.4 | 0.69 | 1.99 | 29.0 | 11.1 | 640 | 33.8 | 2.26 | 25.9 | 119 | 4.38 |
| 00 | 4.5 | 2.5 | 5.8 | 850 | 23.1 | 17.4 | 0.75 | 2.07 | 30.1 | 11.1 | 850 | 34.6 | 2.03 | 27.6 | 108 | 4.99 |
| | 6.0 6.0 | 4.7 4.7 | 10.7 10.7 | 640 850 | 22.5 23.4 | 15.4 17.5 | 0.69 0.75 | 1.91 1.99 | 29.0 30.2 | 11.8 11.8 | 640 850 | 34.4 35.2 | 2.28 2.05 | 26.4 28.2 | 120 108 | 4.42 5.04 |
| | 3.0 | 1.2 | 2.7 | 640 | 20.2 | 14.8 | 0.74 | 2.44 | 28.5 | 8.3 | | 00.2 | 2.00 | -9.2 | | 0.01 |
| | 3.0 | 1.2 | 2.7 | 850 | 21.0 | 16.8 | 0.80 | 2.54 | 29.7 | 8.3 | | | | | | |
| 100 | 4.5 | 2.4 | 5.5 | 640 | 20.8 | 14.9 | 0.72 | 2.25 | 28.5 | 9.2 | | | | | | |
| | 4.5 6.0 | 2.4 4.5 | 5.5 10.3 | 850 640 | 21.6 21.1 | 16.9 15.0 | 0.78 0.71 | 2.34 2.16 | 29.7 28.5 | 9.2 9.8 | | | | | | |
| | 6.0 | 4.5 | 10.3 | 850 | 22.0 | 17.0 | 0.77 | 2.25 | 29.7 | 9.8 | | | | | | |
| | 3.0 | 1.1 | 2.5 | 640 | 18.8 | 14.4 | 0.77 | 2.77 | 28.3 | 6.8 | | | | | | |
| | 3.0 4.5 | 1.1 | 2.5 5.3 | 850 640 | 19.5 19.3 | 16.3 | 0.84 0.75 | 2.88 2.55 | 29.4 28.1 | 6.8 7.6 | | | | | | |
| 110 | 4.5 | 2.3 2.3 | 5.3 5.3 | 850 | 20.1 | 14.4 16.3 | 0.75 | 2.55 2.66 | 20.1 | 7.6 7.6 | | Opera | ation not | recomm | nended | |
| | 6.0 | 4.3 | 9.9 | 640 | 19.7 | 14.5 | 0.74 | 2.45 | 28.1 | 8.0 | | | | | | |
| | 6.0 | 4.3 | 9.9 | 850 | 20.5 | 16.4 | 0.80 | 2.55 | 29.3 | 8.0 | | | | | | |
| | 3.0 | 1.0 | 2.4 | 640 | 17.1 | 13.9 | 0.81 | 3.13 | 27.9 | 5.5 | | | | | | |
| | 3.0 4.5 | 1.0 2.2 | 2.4 5.1 | 850 640 | 17.8 17.8 | 15.7 14.0 | 0.88 0.78 | 3.26 2.89 | 29.0 27.8 | 5.5 6.2 | | | | | | |
| 120 | 4.5 | 2.2 | 5.1 | 850 | 18.6 | 15.8 | 0.85 | 3.01 | 28.9 | 6.2 | | | | | | |
| | 6.0 | 4.2 | 9.6 | 640 | 18.3 | 14.1 | 0.77 | 2.78 | 27.9 | 6.6 | | | | | | |
| | 6.0 | 4.2 | 9.6 | 850 | 19.1 | 16.0 | 0.84 | 2.89 | 29.0 | 6.6 | | | | | | |

800 CFM Nominal (Rated) Airflow

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/SO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/SO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply: performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance Data Selection Notes for operating conditions of the rhan those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 030

1,000 CFM Nominal (Rated) Airflow

```
Performance capacities shown in thousands of Btuh
```

| EWT | | W | PD | | (| Cooling | g - EAT | 80/67 ° | F | | | He | eating - | EAT 7 | 0°F | |
|-----|------------|------------|--------------|----------------|--------------|--------------|-------------------|----------------|--------------|--------------|----------------|--------------|--------------|--------------|------------|--------------|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | HC | kW | HE | LAT | СОР |
| 20 | 7.5 7.5 | 5.0 5.0 | 11.6 11.6 | | 0 | peration | not reco | mmend | ed | | 750 1000 | 20.0 20.4 | 2.31 2.08 | 12.6 13.4 | 95 89 | 2.53 2.89 |
| | 3.8 | 1.3 | 2.9 | 750 | 33.3 | 20.3 | 0.61 | 1.38 | 38.0 | 24.0 | 750 | 21.6 | 2.37 | 14.0 | 97 | 2.67 |
| | 3.8 5.6 | 1.3 2.3 | 2.9 5.4 | 1000 750 | 34.7 33.5 | 22.9 20.2 | 0.66 0.60 | 1.44 1.31 | 39.5 37.9 | 24.0 25.7 | 1000 750 | 22.1 22.5 | 2.13 2.40 | 14.9 14.7 | 90 98 | 3.04 2.75 |
| 30 | 5.6 | 2.3 | 5.4 | 1000 | 34.9 | 20.2 | 0.65 | 1.36 | 39.5 | 25.7 | 1000 | 23.0 | 2.40 | 15.7 | 91 | 3.13 |
| | 7.5 | 4.2 | 9.7 | 750 | 33.6 | 20.0 | 0.60 | 1.27 | 37.9 | 26.5 | 750 | 22.9 | 2.41 | 15.1 | 98 | 2.79 |
| | 7.5 3.8 | 4.2 | 9.7 2.4 | 1000 750 | 35.0 32.6 | 22.7 | 0.65 | 1.32 1.51 | 39.4 37.7 | 26.5 21.6 | 1000 750 | 23.5 24.7 | 2.16 | 16.2 16.7 | 92 100 | 3.18 2.95 |
| | 3.8 | 1.0 | 2.4 | 1000 | 34.0 | 20.2 | 0.62 | 1.57 | 39.3 | 21.6 | 1000 | 24.7 | 2.45 | 17.8 | 93 | 3.36 |
| 40 | 5.6 | 2.0 | 4.7 | 750 | 33.1 | 20.3 | 0.61 | 1.42 | 37.9 | 23.3 | 750 | 25.7 | 2.48 | 17.6 | 102 | 3.04 |
| 40 | 5.6 7.5 | 2.0 3.7 | 4.7 8.6 | 1000 750 | 34.5 33.7 | 22.9 20.5 | 0.67 0.61 | 1.48 1.38 | 39.5 38.3 | 23.3 24.4 | 1000 750 | 26.4 26.3 | 2.23 2.49 | 18.8 18.1 | 94 102 | 3.47 3.10 |
| | 7.5 | 3.7 | 8.6 | 1000 | 35.1 | 20.5 | 0.66 | 1.44 | 39.9 | 24.4 | 1000 | 26.9 | 2.49 | 19.4 | 95 | 3.53 |
| | 3.8 | 0.9 | 2.1 | 750 | 31.6 | 19.9 | 0.63 | 1.65 | 37.2 | 19.2 | 750 | 27.8 | 2.52 | 19.5 | 104 | 3.24 |
| | 3.8 | 0.9 | 2.1 | 1000 | 32.9 | 22.5 | 0.68 | 1.72 | 38.8 | 19.2 | 1000 | 28.5 | 2.26 | 20.8 | 96 | 3.69 |
| 50 | 5.6 5.6 | 1.8 1.8 | 4.2 4.2 | 750 1000 | 32.3 33.7 | 20.1 22.8 | 0.62 0.68 | 1.55 1.61 | 37.6 39.1 | 20.9 20.9 | 750 1000 | 29.1 29.8 | 2.55 2.29 | 20.6 22.0 | 106 98 | 3.35 3.82 |
| | 7.5 | 3.4 | 7.8 | 750 | 32.6 | 20.2 | 0.62 | 1.50 | 37.7 | 21.7 | 750 | 29.8 | 2.56 | 21.3 | 107 | 3.41 |
| | 7.5 | 3.4 | 7.8 | 1000 | 34.0 | 22.9 | 0.67 | 1.57 | 39.3 | 21.7 | 1000 | 30.5 | 2.30 | 22.7 | 98 | 3.89 |
| | 3.8 3.8 | 0.8 0.8 | 1.8 1.8 | 750 1000 | 30.4 31.7 | 19.4 21.9 | 0.64 0.69 | 1.81 1.89 | 36.6 38.1 | 16.8 16.8 | 750 1000 | 31.0 31.8 | 2.58 2.32 | 22.4 23.9 | 108 99 | 3.52 4.02 |
| 60 | 5.6 | 1.7 | 3.8 | 750 | 31.1 | 19.6 | 0.63 | 1.70 | 36.9 | 18.3 | 750 | 32.5 | 2.61 | 23.7 | 110 | 3.65 |
| 00 | 5.6 | 1.7 | 3.8 | 1000 | 32.4 | 22.2 | 0.69 | 1.77 | 38.4 | 18.3 | 1000 | 33.3 | 2.34 | 25.3 | 101 | 4.16 |
| | 7.5 7.5 | 3.1 3.1 | 7.2 7.2 | 750 1000 | 31.4 32.7 | 19.7 22.3 | 0.63 0.68 | 1.65 1.71 | 37.0 38.5 | 19.0 19.1 | 750 1000 | 33.3 34.1 | 2.63 2.36 | 24.4 26.0 | 111 102 | 3.71 4.24 |
| | 3.8 | 0.7 | 1.6 | 750 | 29.0 | 18.8 | 0.65 | 2.00 | 35.8 | 14.5 | 750 | 34.2 | 2.64 | 25.2 | 112 | 3.79 |
| | 3.8 | 0.7 | 1.6 | 1000 | 30.2 | 21.2 | 0.70 | 2.08 | 37.3 | 14.5 | 1000 | 35.1 | 2.37 | 26.9 | 102 | 4.33 |
| 70 | 5.6 5.6 | 1.5 1.5 | 3.6 3.6 | 750 1000 | 30.0 31.2 | 19.2 21.7 | 0.64 0.70 | 1.87 1.95 | 36.3 37.8 | 16.0 16.0 | 750 1000 | 35.8 36.7 | 2.68 2.40 | 26.7 28.5 | 114 104 | 3.92 4.47 |
| | 7.5 | 2.9 | 6.7 | 750 | 30.4 | 19.4 | 0.64 | 1.81 | 36.6 | 16.8 | 750 | 36.7 | 2.40 | 20.3 | 115 | 3.99 |
| | 7.5 | 2.9 | 6.7 | 1000 | 31.7 | 21.9 | 0.69 | 1.89 | 38.1 | 16.8 | 1000 | 37.6 | 2.42 | 29.3 | 105 | 4.55 |
| | 3.8 3.8 | 0.7 0.7 | 1.5 1.5 | 750 1000 | 27.7 28.8 | 18.3 20.7 | 0.66 0.72 | 2.21 2.30 | 35.3 36.7 | 12.5 12.5 | 750 1000 | 37.3 38.2 | 2.71 2.43 | 28.0 29.9 | 116 105 | 4.04 4.60 |
| 80 | 5.6 | 1.4 | 3.3 | 750 | 28.5 | 18.5 | 0.65 | 2.07 | 35.5 | 13.7 | 750 | 39.0 | 2.75 | 29.5 | 118 | 4.15 |
| 00 | 5.6 | 1.4 | 3.3 | 1000 | 29.6 | 21.0 | 0.71 | 2.16 | 37.0 | 13.7 | 1000 | 40.0 | 2.47 | 31.5 | 107 | 4.74 |
| | 7.5 7.5 | 2.7 2.7 | 6.3 6.3 | 750 1000 | 29.0 30.2 | 18.7 21.2 | 0.65 0.70 | 2.00 2.08 | 35.8 37.3 | 14.5 14.5 | 750 1000 | 40.2 41.2 | 2.78 2.50 | 30.6 32.6 | 120 108 | 4.24 4.84 |
| | 3.8 | 0.6 | 1.4 | 750 | 26.7 | 17.8 | 0.67 | 2.34 | 34.7 | 11.5 | 750 | 38.8 | 2.75 | 29.3 | 118 | 4.14 |
| | 3.8 | 0.6 | 1.4 | 1000 | 27.8 | 20.1 | 0.72 | 2.43 | 36.1 | 11.5 | 1000 | 39.8 | 2.5 | 31.3 | 107 | 4.72 |
| 85 | 5.6 5.6 | 1.4 1.4 | 3.2 3.2 | 750 1000 | 27.6 28.8 | 18.2 20.6 | 0.66 0.71 | 2.18 2.27 | 35.1 36.5 | 12.7 12.7 | 750 1000 | 40.5 41.5 | 2.8 2.5 | 30.8 32.9 | 120 108 | 4.24 4.84 |
| | 7.5 | 2.7 | 6.2 | 750 | 28.2 | 18.4 | 0.65 | 2.11 | 35.4 | 13.4 | 750 | 41.6 | 2.8 | 31.7 | 121 | 4.30 |
| | 7.5 | 2.7 | 6.2 | 1000 | 29.3 | 20.8 | 0.71 | 2.20 | 36.8 | 13.4 | 1000 | 42.6 | 2.5 | 33.9 | 109 | 4.91 |
| | 3.8 3.8 | 0.6 0.6 | 1.4 1.4 | 750 1000 | 25.7 26.8 | 17.3 19.6 | 0.67 0.73 | 2.46 2.56 | 34.1 35.5 | 10.5 10.5 | 750 1000 | 40.3 41.3 | 2.79 2.51 | 30.6 32.7 | 120 108 | 4.23 4.83 |
| 90 | 5.6 | 1.4 | 3.1 | 750 | 26.8 | 17.8 | 0.66 | 2.30 | 34.7 | 11.7 | 750 | 42.0 | 2.85 | 32.1 | 122 | 4.33 |
| 30 | 5.6 | 1.4 | 3.1 | 1000 | 27.9 | 20.1 | 0.72 | 2.39 | 36.1 | 11.7 | 1000 | 43.0 | 2.56 | 34.3 | 110 | 4.93 |
| | 7.5 7.5 | 2.6 2.6 | 6.0 6.0 | 750 1000 | 27.3 28.5 | 18.0 20.4 | 0.66 0.72 | 2.22 2.31 | 34.9 36.4 | 12.3 12.3 | 750 1000 | 42.9 44.0 | 2.88 2.59 | 32.9 35.1 | 123 111 | 4.36 4.98 |
| | 3.8 | 0.6 | 1.3 | 750 | 24.0 | 16.6 | 0.69 | 2.74 | 33.3 | 8.7 | 1000 | 11.0 | 2.00 | 00.1 | | 4.00 |
| | 3.8 | 0.6 | 1.3 | 1000 | 24.9 | 18.8 | 0.75 | 2.85 | 34.7 | 8.7 | | | | | | |
| 100 | 5.6 5.6 | 1.3 1.3 | 3.0 3.0 | 750 1000 | 25.1 26.1 | 17.0 19.3 | 0.68 0.74 | 2.56 2.67 | 33.8 35.2 | 9.8 9.8 | | | | | | |
| | 7.5 | 2.5 | 5.7 | 750 | 25.6 | 17.3 | 0.67 | 2.48 | 34.1 | 10.3 | | | | | | |
| | 7.5 | 2.5 | 5.7 | 1000 | 26.7 | 19.6 | 0.73 | 2.58 | 35.5 | 10.3 | | | | | | |
| | 3.8 3.8 | 0.5 0.5 | 1.2 1.2 | 750 1000 | 22.5 23.5 | 16.1 18.2 | 0.72 0.78 | 3.07 3.19 | 33.0 34.4 | 7.4 7.4 | | | | | | |
| 110 | 5.6 | 1.2 | 2.8 | 750 | 23.2 | 16.3 | 0.70 | 2.86 | 33.1 | 8.1 | | Onore | ation not | rocomm | ondod | |
| 110 | 5.6 | 1.2 | 2.8 | 1000 | 24.2 | 18.4 | 0.76 | 2.98 | 34.4 | 8.1 | | Opera | | recomm | lended | |
| | 7.5 7.5 | 2.4 2.4 | 5.5 5.5 | 750 1000 | 23.8 24.8 | 16.5 18.7 | 0.69 0.75 | 2.77 2.88 | 33.3 34.6 | 8.6 8.6 | | | | | | |
| | 3.8 | 0.5 | 1.1 | 750 | 20.4 | 15.2 | 0.74 | 3.44 | 32.2 | 5.9 | | | | | | |
| | 3.8 | 0.5 | 1.1 | 1000 | 21.2 | 17.2 | 0.81 | 3.58 | 33.5 | 5.9 | | | | | | |
| 120 | 5.6 5.6 | 1.2 1.2 | 2.7 2.7 | 750 1000 | 21.4 22.3 | 15.6 17.6 | 0.73 0.79 | 3.21 3.34 | 32.4 33.8 | 6.7 6.7 | | | | | | |
| | 7.5 | 2.3 | 5.3 | 750 | 22.0 | 15.8 | 0.72 | 3.10 | 32.6 | 7.1 | | | | | | |
| | 7.5 | 2.3 | 5.3 | 1000 | 22.9 | 17.8 | 0.78 | 3.23 | 33.9 | 7.1 | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/SO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 036

Performance capacities shown in thousands of Btuh

1,200 CFM Nominal (Rated) Airflow

| EWT | | W | PD | | (| Cooling | g - EAT | 80/67 ° | F | | | He | ating - | EAT 7 | 0°F | |
|---------------|-------------------|-------------------|--------------|----------------|---------------------|---------------------|-------------------|---------------------|---------------------|---------------------|----------------|---------------------|---------------------|---------------------|-------------------|--------------|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | HC | kW | HE | LAT | СОР |
| 20 | 9.0 9.0 | 6.4 6.4 | 14.8 14.8 | | 0 | peration | not reco | mmend | ed | | 860 1150 | 22.6 23.2 | 2.67 2.39 | 14.1 15.1 | 94 89 | 2.49 2.84 |
| | 4.5 | 1.8 | 4.3 | 860 | 39.9 | 24.2 | 0.61 | 1.67 | 45.6 | 23.8 | 860 | 25.6 | 2.80 | 16.6 | 98 | 2.68 |
| | 4.5 6.8 | 1.8 3.1 | 4.3 7.1 | 1150 860 | 41.5 40.1 | 27.4 24.3 | 0.66 0.61 | 1.74 1.62 | 47.4 45.5 | 23.8 24.7 | 1150 860 | 26.2 26.8 | 2.51 2.85 | 17.7 17.6 | 91 99 | 3.06 2.76 |
| 30 | 6.8 | 3.1 | 7.1 | 1150 | 41.7 | 27.5 | 0.66 | 1.69 | 47.4 | 24.7 | 1150 | 27.5 | 2.56 | 18.8 | 92 | 3.15 |
| | 9.0 | 5.4 | 12.5 | 860 | 40.0 | 24.3 | 0.61 | 1.60 | 45.5 | 25.0 | 860 | 27.5 | 2.88 | 18.2 | 100 | 2.80 |
| | 9.0 4.5 | 5.4 1.6 | 12.5 3.6 | 1150 860 | 41.7 39.2 | 27.5 24.0 | 0.66 | 1.67 1.80 | 47.3 45.3 | 25.0 21.8 | 1150 860 | 28.2 30.1 | 2.59 2.98 | 19.4 20.3 | 93 102 | 3.19 2.95 |
| | 4.5 | 1.6 | 3.6 | 1150 | 40.8 | 27.2 | 0.67 | 1.87 | 47.1 | 21.8 | 1150 | 30.8 | 2.68 | 21.7 | 95 | 3.37 |
| 40 | 6.8 | 2.7 2.7 | 6.2 6.2 | 860 | 39.7 | 24.2 | 0.61 | 1.71 | 45.5 | 23.3 | 860 | 31.6 | 3.05 | 21.6 23.1 | 104 | 3.04 |
| | 6.8 9.0 | 2.7 4.8 | 6.2 11.1 | 1150 860 | 41.4 39.9 | 27.4 24.3 | 0.66 0.61 | 1.78 1.67 | 47.4 45.6 | 23.3 23.9 | 1150 860 | 32.4 32.4 | 2.74 3.08 | 23.1 | 96 105 | 3.47 3.09 |
| | 9.0 | 4.8 | 11.1 | 1150 | 41.6 | 27.4 | 0.66 | 1.74 | 47.4 | 23.9 | 1150 | 33.2 | 2.77 | 23.8 | 97 | 3.52 |
| | 4.5 4.5 | 1.4 | 3.2 3.2 | 860 | 38.0 | 23.6 | 0.62 | 1.98 | 44.7 | 19.2 | 860 | 34.5 | 3.16 | 24.1 | 107 | 3.20 |
| 50 | 4.5 6.8 | 1.4 2.4 | 3.2 5.6 | 1150 860 | 39.5 38.8 | 26.7 23.9 | 0.68 0.62 | 2.06 1.85 | 46.5 45.1 | 19.2 21.0 | 1150 860 | 35.4 36.3 | 2.84 3.23 | 25.7 25.6 | 98 109 | 3.65 3.30 |
| 50 | 6.8 | 2.4 | 5.6 | 1150 | 40.4 | 27.0 | 0.67 | 1.92 | 47.0 | 21.0 | 1150 | 37.2 | 2.90 | 27.3 | 100 | 3.76 |
| | 9.0 9.0 | 4.4 4.4 | 10.1 10.1 | 860 1150 | 39.2 40.8 | 24.0 | 0.61 0.67 | 1.79 | 45.3 47.2 | 21.9 | 860 1150 | 37.3 | 3.27 | 26.4 | 110 101 | 3.35 |
| | <u>9.0</u> 4.5 | 1.3 | 2.9 | 860 | <u>40.8</u> 36.1 | <u>27.2</u> 22.9 | 0.63 | <u>1.87</u> 2.20 | 47.2 | <u>21.9</u> 16.4 | 860 | <u>38.2</u> 38.9 | 2.93 3.32 | <u>28.2</u> 27.8 | 112 | 3.82 3.43 |
| | 4.5 | 1.3 | 2.9 | 1150 | 37.6 | 25.9 | 0.69 | 2.29 | 45.4 | 16.4 | 1150 | 39.8 | 2.99 | 29.7 | 102 | 3.91 |
| 60 | 6.8 6.8 | 2.3 2.3 | 5.2 5.2 | 860 1150 | 37.5 39.1 | 23.5 26.5 | 0.63 0.68 | 2.04 2.13 | 44.4 46.3 | 18.4 18.4 | 860 1150 | 40.9 41.9 | 3.40 3.05 | 29.5 31.5 | 114 104 | 3.53 4.02 |
| | 9.0 | 4.0 | 9.3 | 860 | 38.0 | 20.5 | 0.68 | 1.97 | 40.3 | 19.3 | 860 | 41.9 | 3.05 | 30.4 | 115 | 3.58 |
| | 9.0 | 4.0 | 9.3 | 1150 | 39.6 | 26.7 | 0.68 | 2.05 | 46.5 | 19.3 | 1150 | 43.0 | 3.09 | 32.5 | 105 | 4.08 |
| | 4.5 4.5 | 1.2 1.2 | 2.7 2.7 | 860 1150 | 34.6 36.0 | 22.5 25.5 | 0.65 0.71 | 2.46 2.56 | 42.9 44.7 | 14.0 14.0 | 860 1150 | 43.1 44.1 | 3.47 3.12 | 31.4 33.5 | 116 106 | 3.64 4.15 |
| 70 | 6.8 | 2.1 | 4.9 | 860 | 35.8 | 22.9 | 0.64 | 2.28 | 43.6 | 15.7 | 860 | 45.2 | 3.55 | 33.2 | 119 | 3.74 |
| 70 | 6.8 | 2.1 | 4.9 | 1150 | 37.3 | 25.9 | 0.70 | 2.38 | 45.4 | 15.7 | 1150 | 46.3 | 3.19 | 35.4 | 107 | 4.26 |
| | 9.0 9.0 | 3.8 3.8 | 8.7 8.7 | 860 1150 | 36.4 37.9 | 23.1 26.1 | 0.63 0.69 | 2.20 2.29 | 43.9 45.7 | 16.6 16.6 | 860 1150 | 46.4 47.5 | 3.59 3.22 | 34.2 36.5 | 120 108 | 3.79 4.32 |
| | 4.5 | 1.1 | 2.5 | 860 | 32.5 | 21.8 | 0.67 | 2.76 | 41.9 | 11.8 | 860 | 47.0 | 3.61 | 34.8 | 121 | 3.82 |
| | 4.5 | 1.1 | 2.5 | 1150 | 33.8 | 24.7 | 0.73 | 2.88 | 43.7 | 11.8 | 1150 | 48.2 | 3.24 | 37.1 | 109 | 4.36 |
| 80 | 6.8 6.8 | 2.0 2.0 | 4.6 4.6 | 860 1150 | 33.9 35.3 | 22.3 25.2 | 0.66 0.72 | 2.56 2.67 | 42.6 44.4 | 13.2 13.2 | 860 1150 | 49.2 50.4 | 3.68 3.30 | 36.6 39.1 | 123 111 | 3.92 4.47 |
| | 9.0 | 3.6 | 8.3 | 860 | 34.5 | 22.5 | 0.65 | 2.47 | 42.9 | 14.0 | 860 | 50.3 | 3.71 | 37.6 | 124 | 3.97 |
| | 9.0 4.5 | <u>3.6</u> 1.0 | 8.3 2.4 | 1150 860 | <u>35.9</u> 31.5 | <u>25.5</u> 21.5 | 0.71 | <u>2.57</u> 2.9 | <u>44.7</u> 41.5 | <u>14.0</u> 10.8 | 1150 860 | <u>51.5</u> 48.8 | <u>3.34</u> 3.67 | <u>40.1</u> 36.3 | <u>111</u> 123 | 4.53 3.90 |
| | 4.5 | 1.0 | 2.4 | 1150 | 32.8 | 21.5 | 0.08 | 3.05 | 41.5 | 10.8 | 1150 | 40.0 50.0 | 3.29 | 38.8 | 123 | 3.90 4.45 |
| 85 | 6.8 | 1.9 | 4.4 | 860 | 32.8 | 21.9 | 0.67 | 2.72 | 42.1 | 12.1 | 860 | 50.9 | 3.73 | 38.1 | 125 | 4.00 |
| | 6.8 9.0 | 1.9 3.5 | 4.4 8.1 | 1150 860 | 34.1 33.4 | 24.8 22.1 | 0.73 0.66 | 2.84 2.62 | 43.8 42.3 | 12.1 12.8 | 1150 860 | 52.2 52.0 | 3.35 3.76 | 40.7 39.0 | 112 126 | 4.56 4.05 |
| | 9.0 | 3.5 | 8.1 | 1150 | 34.7 | 25.0 | 0.00 | 2.02 | 42.3 | 12.8 | 1150 | 53.2 | 3.38 | 39.0 41.7 | 113 | 4.03 |
| | 4.5 | 1.0 | 2.3 | 860 | 30.5 | 21.2 | 0.70 | 3.10 | 41.1 | 9.8 | 860 | 50.6 | 3.72 | 37.9 | 125 | 3.99 |
| | 4.5 6.8 | 1.0 1.9 | 2.3 4.3 | 1150 860 | 31.8 31.7 | 24.0 21.6 | 0.76 0.68 | 3.23 2.88 | 42.8 41.6 | 9.8 11.0 | 1150 860 | 51.9 52.7 | 3.34 3.79 | 40.4 39.6 | 112 127 | 4.54 4.08 |
| 90 | 6.8 | 1.9 | 4.3 | 1150 | 33.0 | 24.4 | 0.74 | 3.00 | 43.3 | 11.0 | 1150 | 54.0 | 3.40 | 42.3 | 113 | 4.65 |
| | 9.0 | 3.4 | 7.9 | 860 | 32.2 | 21.7 | 0.67 | 2.78 | 41.7 | 11.6 | 860 | 53.7 | 3.82 | 40.5 | 128 | 4.12 |
| | 9.0 4.5 | <u>3.4</u> 0.9 | 7.9 | 1150 860 | <u>33.5</u> 28.3 | 24.5 20.5 | 0.73 | <u>2.89</u> 3.47 | <u>43.4</u> 40.2 | <u>11.6</u> 8.1 | 1150 | 55.0 | 3.43 | 43.2 | 114 | 4.70 |
| | 4.5 | 0.9 | 2.2 | 1150 | 29.5 | 20.5 | 0.79 | 3.62 | 41.9 | 8.2 | | | | | | |
| 100 | 6.8 | 1.8 | 4.1 | 860 | 29.5 | 20.8 | 0.71 | 3.24 | 40.6 | 9.1 | | | | | | |
| | 6.8 9.0 | 1.8 3.3 | 4.1 7.5 | 1150 860 | 30.7 30.1 | 23.5 21.0 | 0.77 0.70 | 3.37 3.13 | 42.2 40.8 | 9.1 9.6 | | | | | | |
| | 9.0 | 3.3 | 7.5 | 1150 | 31.3 | 23.7 | 0.76 | 3.25 | 42.5 | 9.6 | | | | | | |
| | 4.5 | 0.9 | 2.1 | 860 | 26.2 | 19.8 | 0.75 | 3.88 | 39.5 | 6.8 | | | | | | |
| 110 | 4.5 6.8 | 0.9 1.7 | 2.1 4.0 | 1150 860 | 27.3 27.2 | 22.4 20.0 | 0.82 0.73 | 4.04 3.63 | 41.1 39.7 | 6.8 7.5 | | ~ | | | | |
| 110 | 6.8 | 1.7 | 4.0 | 1150 | 28.4 | 22.6 | 0.80 | 3.78 | 41.3 | 7.5 | | Opera | tion not | recomm | lended | |
| | 9.0 9.0 | 3.1 3.1 | 7.2 7.2 | 860 1150 | 27.6 28.8 | 20.0 22.7 | 0.72 0.79 | 3.51 3.65 | 39.6 41.3 | 7.9 7.9 | | | | | | |
| | 4.5 | 0.9 | 2.0 | 860 | 20.0 | 19.0 | 0.79 | 4.31 | 38.9 | 5.6 | | | | | | |
| | 4.5 | 0.9 | 2.0 | 1150 | 25.1 | 21.4 | 0.86 | 4.49 | 40.4 | 5.6 | | | | | | |
| 120 | 6.8 6.8 | 1.6 1.6 | 3.8 3.8 | 860 1150 | 25.1 26.1 | 19.2 21.8 | 0.77 0.83 | 4.05 4.21 | 39.0 40.6 | 6.2 6.2 | | | | | | |
| | 9.0 | 3.0 | 7.0 | 860 | 25.4 | 19.2 | 0.76 | 3.92 | 38.9 | 6.5 | | | | | | |
| | 9.0 | 3.0 | 7.0 | 1150 | 26.5 | 21.8 | 0.82 | 4.08 | 40.5 | 6.5 | | | | | | |
| Internolation | | | | | | | | | | | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/SO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply. performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TCV 041

| wT | | W | PD | | | Cooling - | EAT 80/67 | ۳°F | | | | Heating - | EAT 70°F | | |
|-----|------------|------------|------------|----------------|--------------|--------------|--------------|--------------|--------------|----------------|--------------|--------------|--------------|----------------|------------|
| °F | GPM | PSI | FT | Airflow CFM | тс | sc | kW | HR | EER | Airflow CFM | нс | kW | HE | LAT | COF |
| 20 | 10.0 | 0.0 | 0.0 | 845 | | Operatio | n not reco | mmended | | 845 | 26.6 | 3.17 | 16.5 | 99.1 | 2.5 |
| 20 | 10.0 | 0.0 | 0.0 | 1125 | 45.0 | | | | 07.4 | 1125 | 27.2 | 2.85 | 17.6 | 92.4 | 2.8 |
| | 5.0 5.0 | 0.0 0.0 | 0.0 0.0 | 845 1125 | 45.0 46.8 | 25.2 28.5 | 1.64 1.71 | 50.5 52.6 | 27.4 27.4 | 845 1125 | 28.8 29.5 | 3.23 2.90 | 18.4 19.7 | 101.6 94.3 | 2.6 |
| | 7.5 | 0.0 | 0.0 | 845 | 45.8 | 25.3 | 1.51 | 50.8 | 30.4 | 845 | 29.9 | 3.26 | 19.4 | 102.8 | 2.7 |
| 30 | 7.5 | 0.0 | 0.0 | 1125 | 47.6 | 28.6 | 1.57 | 52.9 | 30.4 | 1125 | 30.7 | 2.93 | 20.7 | 95.2 | 3.1 |
| | 10.0 | 0.0 | 0.0 | 845 | 46.1 | 25.3 | 1.44 | 50.9 | 32.1 | 845 | 30.5 | 3.28 | 20.0 | 103.5 | 2.7 |
| | 10.0 | 0.0 | 0.0 | 1125 | 48.0 | 28.6 | 1.50 | 53.0 | 32.1 | 1125 | 31.3 | 2.94 | 21.3 | 95.7 | 3.1 |
| | 5.0 | 0.0 | 0.0 | 845 | 43.8 | 24.9 | 1.81 | 50.0 | 24.2 | 845 | 32.4 | 3.33 | 21.6 | 105.6 | 2.9 |
| | 5.0 | 0.0 | 0.0 | 1125 | 45.6 | 28.1 | 1.89 | 52.0 | 24.2 | 1125 | 33.2 | 2.99 | 23.1 | 97.4 | 3.3 |
| 40 | 7.5 | 0.0 | 0.0 | 845 | 44.3 | 25.0 | 1.75 | 50.2 | 25.3 | 845 | 33.8 | 3.37 | 22.8 | 107.0 | 2.9 |
| | 7.5 | 0.0 0.0 | 0.0 0.0 | 1125 845 | 46.1 44.6 | 28.3 25.1 | 1.82 1.70 | 52.3 50.4 | 25.3 26.2 | 1125 845 | 34.6 34.5 | 3.02 3.39 | 24.3 23.4 | 98.5 107.8 | 3.4 3.0 |
| | 10.0 | 0.0 | 0.0 | 1125 | 44.0 | 23.1 | 1.70 | 50.4 52.4 | 26.2 | 1125 | 35.3 | 3.04 | 23.4 25.0 | 99.1 | 3.4 |
| | 5.0 | 0.0 | 0.0 | 845 | 40.3 | 20.4 | 1.99 | 49.2 | 20.2 | 845 | 36.1 | 3.43 | 23.0 | 109.6 | 3.1 |
| | 5.0 | 0.0 | 0.0 | 1125 | 44.2 | 27.6 | 2.07 | 51.2 | 21.3 | 1125 | 37.0 | 3.08 | 26.5 | 100.4 | 3.5 |
| 50 | 7.5 | 0.0 | 0.0 | 845 | 43.5 | 24.8 | 1.86 | 49.8 | 23.4 | 845 | 37.6 | 3.47 | 26.2 | 111.2 | 3.2 |
| 50 | 7.5 | 0.0 | 0.0 | 1125 | 45.3 | 28.0 | 1.93 | 51.8 | 23.4 | 1125 | 38.5 | 3.12 | 27.9 | 101.7 | 3.6 |
| | 10.0 | 0.0 | 0.0 | 845 | 44.0 | 24.9 | 1.79 | 50.1 | 24.6 | 845 | 38.4 | 3.50 | 26.9 | 112.1 | 3.2 |
| | 10.0 | 0.0 | 0.0 | 1125 | 45.8 | 28.2 | 1.86 | 52.1 | 24.6 | 1125 | 39.4 | 3.14 | 28.7 | 102.4 | 3.7 |
| | 5.0 | 0.0 | 0.0 | 845 | 40.9 | 23.8 | 2.18 | 48.3 | 18.8 | 845 | 39.7 | 3.53 | 28.0 | 113.5 | 3.3 |
| | 5.0 | 0.0 | 0.0 | 1125 | 42.6 | 27.0 | 2.27 | 50.3 | 18.8 | 1125 | 40.7 | 3.17 | 29.9 | 103.5 | 3.8 |
| 60 | 7.5 | 0.0 | 0.0 | 845 | 42.1 | 24.3 | 2.04 | 49.0 | 20.6 | 845 | 41.5 | 3.58 | 29.5 | 115.4 | 3.4 |
| | 7.5 | 0.0 0.0 | 0.0 0.0 | 1125 845 | 43.8 42.6 | 27.4 24.5 | 2.12 1.97 | 51.0 49.3 | 20.6 21.7 | 1125 845 | 42.5 42.4 | 3.22 3.61 | 31.5 30.3 | 104.9 116.4 | 3.9 3.4 |
| | 10.0 | 0.0 | 0.0 | 1125 | 44.4 | 24.5 | 2.05 | 49.3 51.3 | 21.7 | 1125 | 43.4 | 3.24 | 32.4 | 105.7 | 3.9 |
| | 5.0 | 0.0 | 0.0 | 845 | 39.2 | 23.2 | 2.39 | 47.3 | 16.4 | 845 | 43.4 | 3.64 | 31.2 | 117.5 | 3.5 |
| | 5.0 | 0.0 | 0.0 | 1125 | 40.8 | 26.2 | 2.49 | 49.3 | 16.4 | 1125 | 44.4 | 3.27 | 33.3 | 106.6 | 4.0 |
| | 7.5 | 0.0 | 0.0 | 845 | 40.5 | 23.6 | 2.23 | 48.1 | 18.1 | 845 | 45.3 | 3.69 | 32.8 | 119.6 | 3.6 |
| 70 | 7.5 | 0.0 | 0.0 | 1125 | 42.1 | 26.8 | 2.33 | 50.0 | 18.1 | 1125 | 46.4 | 3.32 | 35.1 | 108.2 | 4.1 |
| | 10.0 | 0.0 | 0.0 | 845 | 41.1 | 23.9 | 2.16 | 48.4 | 19.0 | 845 | 46.3 | 3.73 | 33.7 | 120.7 | 3.6 |
| | 10.0 | 0.0 | 0.0 | 1125 | 42.8 | 27.0 | 2.25 | 50.4 | 19.0 | 1125 | 47.4 | 3.35 | 36.0 | 109.0 | 4.2 |
| | 5.0 | 0.0 | 0.0 | 845 | 37.4 | 22.5 | 2.63 | 46.4 | 14.2 | 845 | 47.0 | 3.75 | 34.3 | 121.5 | 3.7 |
| | 5.0 | 0.0 | 0.0 | 1125 | 38.9 | 25.4 | 2.74 | 48.3 | 14.2 | 1125 | 48.1 | 3.37 | 36.7 | 109.6 | 4.2 |
| 80 | 7.5 | 0.0 0.0 | 0.0 0.0 | 845 1125 | 38.7 40.3 | 23.0 26.0 | 2.46 2.56 | 47.1 49.0 | 15.8 15.8 | 845 1125 | 49.1 50.3 | 3.81 3.43 | 36.1 38.6 | 123.8 111.4 | 3.8 4.3 |
| | 10.0 | 0.0 | 0.0 | 845 | 39.4 | 20.0 | 2.30 | 45.0 | 16.6 | 845 | 50.5 50.2 | 3.85 | 37.1 | 125.0 | 3.8 |
| | 10.0 | 0.0 | 0.0 | 1125 | 41.0 | 26.3 | 2.47 | 49.4 | 16.6 | 1125 | 51.4 | 3.46 | 39.6 | 112.3 | 4.4 |
| | 5.0 | 0.0 | 0.0 | 845 | 36.4 | 22.1 | 2.8 | 45.9 | 13.2 | 845 | 48.8 | 3.81 | 35.9 | 123.5 | 3.8 |
| | 5.0 | 0.0 | 0.0 | 1125 | 37.9 | 25.0 | 2.88 | 47.8 | 13.2 | 1125 | 50.0 | 3.4 | 38.3 | 111.1 | 4.3 |
| 85 | 7.5 | 0.0 | 0.0 | 845 | 37.8 | 22.6 | 2.58 | 46.6 | 14.7 | 845 | 51.0 | 3.9 | 37.8 | 125.9 | 3.9 |
| 00 | 7.5 | 0.0 | 0.0 | 1125 | 39.3 | 25.6 | 2.69 | 48.5 | 14.7 | 1125 | 52.2 | 3.5 | 40.3 | 113.0 | 4.4 |
| | 10.0 | 0.0 | 0.0 | 845 | 38.4 | 22.9 | 2.49 | 46.9 | 15.5 | 845 | 52.1 | 3.9 | 38.8 | 127.1 | 3.9 |
| | 10.0 | 0.0 | 0.0 | 1125 | 40.0 | 25.9 | 2.60 | 48.9 | 15.5 | 1125 | 53.4 | 3.5 | 41.4 | 114.0 | 4.4 |
| | 5.0 | 0.0 0.0 | 0.0 | 845 | 35.5 | 21.8 | 2.91 | 45.4 | 12.2 | 845 | 50.6 | 3.86 | 37.4 | 125.5 | 3.8 |
| | 5.0 7.5 | 0.0 | 0.0 0.0 | 1125 845 | 36.9 36.8 | 24.6 22.3 | 3.03 2.71 | 47.3 46.1 | 12.2 13.6 | 1125 845 | 51.8 52.9 | 3.47 3.94 | 40.0 39.4 | 112.7 127.9 | 4.4 3.9 |
| 90 | 7.5 | 0.0 | 0.0 | 1125 | 38.3 | 25.2 | 2.82 | 48.0 | 13.6 | 1125 | 54.1 | 3.54 | 42.0 | 114.6 | 4.5 |
| | 10.0 | 0.0 | 0.0 | 845 | 37.5 | 22.5 | 2.62 | 46.4 | 14.3 | 845 | 54.1 | 3.99 | 40.4 | 129.3 | 4.0 |
| | 10.0 | 0.0 | 0.0 | 1125 | 39.0 | 25.5 | 2.72 | 48.3 | 14.3 | 1125 | 55.4 | 3.58 | 43.2 | 115.6 | 4.5 |
| | 5.0 | 0.0 | 0.0 | 845 | 31.4 | 20.4 | 3.61 | 43.7 | 8.7 | | | | | | |
| | 5.0 | 0.0 | 0.0 | 1125 | 32.7 | 23.0 | 3.76 | 45.5 | 8.7 | | | | | | |
| 00 | 7.5 | 0.0 | 0.0 | 845 | 32.8 | 20.8 | 3.35 | 44.2 | 9.8 | | | | | | |
| | 7.5 | 0.0 | 0.0 | 1125 | 34.1 | 23.6 | 3.49 | 46.1 | 9.8 | | | | | | |
| | 10.0 | 0.0 | 0.0 | 845 1125 | 33.5 34.9 | 21.1 | 3.23 | 44.5 | 10.4 | | | | | | |
| | 5.0 | 0.0 | 0.0 | 845 | 29.3 | 23.8 19.7 | 3.36 4.05 | 46.4 43.2 | 10.4 7.2 | | | | | | |
| | 5.0 | 0.0 | 0.0 | 1125 | 29.3 30.5 | 22.3 | 4.03 | 43.2 44.9 | 7.2 | | | | | | |
| | 7.5 | 0.0 | 0.0 | 845 | 30.5 | 22.3 | 3.75 | 44.5 | 8.2 | | | | | | |
| 110 | 7.5 | 0.0 | 0.0 | 1125 | 31.9 | 22.8 | 3.91 | 45.3 | 8.2 | | Ope | eration not | recommen | nded | |
| | 10.0 | 0.0 | 0.0 | 845 | 31.4 | 20.4 | 3.61 | 43.7 | 8.7 | | | | | | |
| | 10.0 | 0.0 | 0.0 | 1125 | 32.7 | 23.0 | 3.76 | 45.5 | 8.7 | | | | | | |
| | 5.0 | 0.0 | 0.0 | 845 | 27.6 | 19.2 | 4.45 | 42.9 | 6.2 | | | | | | |
| | 5.0 | 0.0 | 0.0 | 1125 | 28.7 | 21.7 | 4.63 | 44.6 | 6.2 | | | | | | |
| 120 | 7.5 | 0.0 | 0.0 | 845 | 29.0 | 19.6 | 4.11 | 43.1 | 7.1 | | | | | | |
| | 7.5 | 0.0 | 0.0 | 1125 | 30.2 | 22.2 | 4.28 | 44.9 | 7.1 | | | | | | |
| | 10.0 | 0.0 | 0.0 | 845 | 29.7 | 19.8 | 3.95 | 43.3 | 7.5 | | | | | | |

Interpolation is permissible, extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling and 70°F DB in heating. ARI/ISO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for ARI/ISO conditions. All performance is based upon the lower value of dual voltage rated units. Performance stated is at the rated power supply: performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance orrection tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 042

1,350 CFM Nominal (Rated) Airflow

Performance capacities shown in thousands of Btuh

| EWT | | w | PD | | | Coolin | g - EAT 8 | 30/67°F | | | | н | eating - | EAT 70 | ۴F | |
|-----|--|---|---|--|--|--|--|--|--|--|--|--|--|--|---|--|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | НС | kW | HE | LAT | СОР |
| 20 | 10.5 10.5 | 9.2 9.2 | 21.3 21.3 | | 0 | peration | not reco | mmend | ed | | 1050 1400 | 28.8 29.5 | 3.37 3.03 | 18.1 19.3 | 95 90 | 2.51 2.86 |
| 30 | 5.3 5.3 7.9 7.9 | 2.3 2.3 4.3 4.3 | 5.3 5.3 10.0 10.0 | 1050 1400 1050 1400 | 47.4 49.3 48.4 50.4 | 30.6 34.7 31.1 35.2 | 0.65 0.70 0.64 0.70 | 1.87 1.95 1.76 1.83 | 53.7 55.9 54.4 56.6 | 25.4 25.4 27.5 27.5 | 1050 1400 1050 1400 | 31.6 32.4 32.9 33.7 | 3.45 3.10 3.49 3.14 | 20.5 21.9 21.6 23.1 | 98 91 99 92 | 2.68 3.06 2.76 3.15 |
| | 10.5 10.5 | 7.9 7.9 | 18.2 18.2 | 1050 1400 | 48.9 50.9 | 31.3 35.5 | 0.64 0.70 | 1.71 1.78 | 54.7 57.0 | 28.6 28.6 | 1050 1400 | 33.6 34.5 | 3.52 3.16 | 22.3 23.8 | 100 93 | 2.80 3.20 |
| 40 | 5.3 5.3 7.9 7.9 10.5 | 2.0 2.0 3.9 3.9 7.1 | 4.6 4.6 8.9 8.9 16.4 | 1050 1400 1050 1400 1050 | 45.9 47.8 47.0 48.9 47.5 | 29.9 33.9 30.4 34.4 30.7 | 0.65 0.71 0.65 0.70 0.65 | 2.05 2.13 1.92 2.00 1.86 | 52.8 55.0 53.4 55.6 53.8 | 22.4 22.4 24.5 24.5 25.5 | 1050 1400 1050 1400 1050 | 36.1 37.0 37.8 38.7 38.7 | 3.59 3.23 3.64 3.27 3.67 | 24.4 26.1 25.8 27.6 26.6 | 102 94 103 96 104 | 2.95 3.36 3.04 3.46 3.09 |
| 50 | 10.5 5.3 7.9 7.9 10.5 | 7.1 1.8 1.8 3.5 3.5 6.5 | 16.4 4.1 4.1 8.1 8.1 15.0 | 1400 1050 1400 1050 1400 1050 | 49.4 44.4 46.2 45.4 47.3 46.0 | 34.7 29.2 33.1 29.7 33.6 30.0 | 0.70 0.66 0.72 0.65 0.71 0.65 | 1.94 2.26 2.35 2.11 2.20 2.04 | 56.0 52.0 54.2 52.6 54.8 52.9 | 25.5 19.6 21.5 21.5 22.5 | 1400 1050 1400 1050 1400 1050 | 39.6 40.8 41.8 42.8 43.8 43.9 | 3.30 3.74 3.36 3.80 3.41 3.83 | 28.4 28.5 30.4 30.2 32.2 31.1 | 96 106 98 108 99 109 | 3.52 3.20 3.65 3.30 3.76 3.35 |
| 60 | 10.5 5.3 5.3 7.9 7.9 10.5 | 6.5 1.6 3.3 3.3 6.1 | 15.0 3.7 3.7 7.5 7.5 14.0 | 1400 1050 1400 1050 1400 1050 | 47.9 43.1 44.9 43.9 45.7 44.4 | 33.9 28.8 32.6 29.0 32.8 29.2 | 0.71 0.67 0.73 0.66 0.72 0.66 | 2.12 2.51 2.61 2.34 2.43 2.25 | 55.1 51.7 53.8 51.8 53.9 52.1 | 22.5 17.2 17.2 18.8 18.8 19.7 | 1400 1050 1400 1050 1400 1050 | 44.9 45.6 46.7 47.8 49.0 49.0 | 3.44 3.89 3.49 3.96 3.56 4.00 | 33.2 32.6 34.8 34.5 36.9 35.6 | 100 110 101 112 102 113 | 3.82 3.44 3.92 3.54 4.04 3.60 |
| 70 | 10.5 5.3 5.3 7.9 7.9 10.5 10.5 | 6.1 1.5 1.5 3.1 3.1 5.7 5.7 | 14.0 3.4 7.1 7.1 13.2 13.2 | 1400 1050 1400 1050 1400 1050 1400 | 46.2 41.3 43.0 42.2 43.9 42.8 44.5 | 33.1 28.1 31.8 28.3 32.0 28.5 32.3 | 0.72 0.68 0.74 0.67 0.73 0.67 0.73 | 2.35 2.80 2.91 2.60 2.71 2.51 2.61 | 54.2 50.9 52.9 51.0 53.1 51.3 53.4 | 19.7 14.8 14.8 16.2 16.2 17.1 17.1 | 1400 1050 1400 1050 1400 1050 1400 | 50.2 50.3 51.5 52.8 54.1 54.1 55.4 | 3.59 4.04 3.63 4.11 3.70 4.16 3.73 | 38.0 36.7 39.2 38.8 41.5 40.0 42.7 | 103 114 104 117 106 118 107 | 4.10 3.65 4.16 3.76 4.29 3.82 4.35 |
| 80 | 5.3 5.3 7.9 7.9 10.5 10.5 | 1.4 1.4 2.9 2.9 5.4 5.4 | 3.2 3.2 6.7 6.7 12.6 12.6 | 1050 1400 1050 1400 1050 1400 1400 | 39.5 41.1 40.4 42.1 41.0 42.7 | 27.4 31.0 27.6 31.3 27.9 31.5 | 0.70 0.76 0.68 0.74 0.68 0.74 | 3.13 3.26 2.91 3.03 2.80 2.92 | 50.1 52.2 50.3 52.4 50.6 52.6 | 12.6 12.6 13.9 13.9 14.6 14.6 | 1050 1400 1050 1400 1050 1400 | 54.9 56.3 57.6 59.0 59.0 60.4 | 4.18 3.76 4.27 3.83 4.31 3.87 | 40.7 43.4 43.0 45.9 44.2 47.2 | 118 107 121 109 122 110 | 3.85 4.39 3.96 4.51 4.01 4.58 |
| 85 | 5.3 5.3 7.9 7.9 10.5 10.5 | 1.3 1.3 2.8 2.8 5.3 5.3 | 3.1 3.1 6.5 6.5 12.3 12.3 | 1050 1400 1050 1400 1050 1400 | 38.4 40.0 39.4 41.1 40.1 41.7 | 27.1 30.7 27.3 30.9 27.5 31.2 | 0.71 0.77 0.69 0.75 0.69 0.75 | 3.32 3.46 3.08 3.21 2.97 3.09 | 49.8 51.8 50.0 52.0 50.2 52.3 | 11.6 11.6 12.8 12.9 13.5 13.6 | 1050 1400 1050 1400 1050 1400 1400 | 57.2 58.6 59.9 61.3 61.3 62.7 | 4.25 3.82 4.34 3.89 4.38 3.93 | 42.6 45.5 44.9 48.0 46.2 49.3 | 120 109 123 111 124 111 | 3.94 4.49 4.05 4.61 4.10 4.68 |
| 90 | 5.3 5.3 7.9 7.9 10.5 10.5 | 1.3 1.3 2.8 2.8 5.2 5.2 | 3.0 3.0 6.4 6.4 12.0 12.0 | 1050 1400 1050 1400 1400 1050 1400 | 37.4 39.0 38.5 40.1 39.1 40.7 | 26.8 30.3 27.0 30.6 27.2 30.8 | 0.73 0.72 0.78 0.70 0.76 0.70 0.76 | 3.51 3.65 3.26 3.39 3.14 3.27 | 49.4 51.5 49.6 51.6 49.8 51.9 | 10.7 10.7 11.8 11.8 12.5 12.5 | 1050 1400 1050 1400 1050 1400 1400 | 59.4 60.8 62.1 63.6 63.5 65.1 | 4.32 3.88 4.40 3.96 4.45 3.99 | 49.5 44.6 47.6 46.9 50.1 48.1 51.4 | 122 110 125 112 126 113 | 4.08 4.03 4.59 4.13 4.71 4.19 4.77 |
| 100 | 5.3 5.3 7.9 7.9 10.5 | 1.2 1.2 2.7 2.7 5.0 | 2.8 2.8 6.1 6.1 11.6 | 1050 1400 1050 1400 1050 | 35.2 36.7 36.4 37.9 37.1 | 26.2 29.6 26.4 29.9 26.6 | 0.74 0.81 0.73 0.79 0.72 | 3.94 4.10 3.66 3.81 3.52 | 48.7 50.7 48.9 50.9 49.1 | 8.9 8.9 9.9 9.9 10.5 | 1400 | 05.1 | 3.99 | 51.4 | 113 | 4.77 |
| 110 | 10.5 5.3 5.3 7.9 7.9 10.5 | 5.0 1.2 2.6 2.6 4.8 | 11.6 2.7 2.7 5.9 5.9 11.2 | 1400 1050 1400 1050 1400 1050 | 38.6 32.8 34.2 34.1 35.5 34.8 26.2 | 30.1 25.5 28.9 25.7 29.1 25.9 | 0.78 0.78 0.85 0.76 0.82 0.75 | 3.67 4.41 4.60 4.11 4.28 3.96 4.12 | 51.1 47.9 49.9 48.1 50.1 48.4 | 10.5 7.4 7.4 8.3 8.3 8.8 | | Opera | ation not | recomm | nended | |
| 120 | 10.5 5.3 5.3 7.9 7.9 10.5 10.5 | 4.8 1.1 1.1 2.5 2.5 4.7 4.7 | 11.2 2.6 2.6 5.7 5.7 10.8 | 1400 1050 1400 1050 1400 1050 1400 | 36.2 30.2 31.4 31.5 32.8 32.3 33.7 | 29.4 24.8 28.0 25.0 28.3 25.3 | 0.81 0.82 0.89 0.79 0.86 0.78 | 4.12 4.95 5.15 4.61 4.80 4.45 | 50.4 47.1 49.1 47.3 49.3 47.6 49.5 | 8.8 6.1 6.8 6.8 7.3 7.3 | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80° F DB and 67° F WB in cooling, and 70° F DB in heating. AHRI/ISO certified conditions are 80.6° F DB and 66.2° F WB in cooling and 68° F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 80°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 048

1,600 CFM Nominal (Rated) Airflow

Performance capacities shown in thousands of Btuh

| EWT | | W | PD | | (| Cooling | g - EAT | 80/67° | F | | | He | eating - | EAT 7 | 0°F | |
|-----|--------------|-------------------|--------------------|----------------|---------------------|---------------------|-------------------|--------------|---------------------|--------------|----------------|---------------------|---------------------|--------------|------------------|--------------|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | НС | kW | HE | LAT | СОР |
| 20 | 12.0 12.0 | 6.8 6.8 | 15.6 15.6 | | 0 | peration | not reco | mmend | ed | | 1200 1600 | 30.9 31.6 | 3.54 3.18 | 19.6 20.9 | 94 88 | 2.56 2.92 |
| | 6.0 | 1.8 | 4.1 | 1200 | 56.4 | 34.4 | 0.61 | 2.25 | 64.0 | 25.1 | 1200 | 33.9 | 3.60 | 22.3 | 96 | 2.76 |
| | 6.0 | 1.8 | 4.1 7.8 | 1600 1200 | 58.8 | 39.0 | 0.66 | 2.34 2.11 | 66.7 64.6 | 25.1 27.2 | 1600 1200 | 34.7 | 3.24 | 23.8 22.7 | 90 97 | 3.14 |
| 30 | 9.0 9.0 | 3.4 3.4 | 7.8 | 1600 | 57.5 59.8 | 34.6 39.1 | 0.60 0.65 | 2.11 | 67.2 | 27.2 | 1200 | 34.4 35.3 | 3.63 3.26 | 24.2 | 97 | 2.78 3.17 |
| | 12.0 | 6.2 | 14.3 | 1200 | 57.9 | 34.5 | 0.60 | 2.05 | 64.8 | 28.2 | 1200 | 35.1 | 3.65 | 23.3 | 97 | 2.82 |
| | 12.0 6.0 | <u>6.2</u> 1.6 | 14.3 3.7 | 1600 1200 | 60.3 54.8 | <u>39.1</u> 34.0 | 0.65 | 2.14 2.47 | 67.5 63.2 | 28.2 22.2 | 1600 1200 | <u>36.0</u> 37.9 | <u>3.27</u> 3.70 | 24.9 25.8 | <u>91</u> 99 | 3.22 3.00 |
| | 6.0 | 1.6 | 3.7 | 1600 | 57.1 | 38.5 | 0.67 | 2.57 | 65.8 | 22.2 | 1600 | 38.8 | 3.33 | 27.5 | 92 | 3.42 |
| 40 | 9.0 | 3.1 | 7.2 | 1200 | 56.0 | 34.3 | 0.61 | 2.31 | 63.8 | 24.3 | 1200 | 39.5 | 3.74 | 27.2 | 100 | 3.10 |
| 40 | 9.0 12.0 | 3.1 5.8 | 7.2 13.4 | 1600 1200 | 58.3 56.6 | 38.9 34.5 | 0.67 0.61 | 2.40 2.23 | 66.4 64.1 | 24.3 25.4 | 1600 1200 | 40.5 40.7 | 3.36 3.76 | 29.1 28.3 | 93 101 | 3.53 3.18 |
| | 12.0 | 5.8 | 13.4 | 1600 | 58.9 | 39.0 | 0.66 | 2.32 | 66.8 | 25.4 | 1600 | 41.7 | 3.37 | 30.2 | 94 | 3.62 |
| | 6.0 | 1.5 | 3.4 | 1200 | 52.9 | 33.3 | 0.63 | 2.72 | 62.1 | 19.4 | 1200 | 43.6 | 3.81 | 31.0 | 104 | 3.36 |
| | 6.0 9.0 | 1.5 3.0 | 3.4 6.8 | 1600 1200 | 55.1 54.3 | 37.7 33.8 | 0.68 0.62 | 2.83 2.53 | 64.7 62.9 | 19.4 21.4 | 1600 1200 | 44.7 44.9 | 3.42 3.85 | 33.0 32.1 | 96 105 | 3.83 3.42 |
| 50 | 9.0 | 3.0 | 6.8 | 1600 | 56.5 | 38.3 | 0.62 | 2.53 | 65.5 | 21.4 | 1600 | 44.9 | 3.46 | 34.3 | 97 | 3.42 |
| | 12.0 | 5.5 | 12.7 | 1200 | 55.0 | 34.0 | 0.62 | 2.45 | 63.2 | 22.5 | 1200 | 46.0 | 3.87 | 33.1 | 106 | 3.49 |
| | 12.0 6.0 | <u>5.5</u> 1.4 | <u>12.7</u> 3.2 | 1600 1200 | <u>57.2</u> 50.7 | 38.5 32.5 | 0.67 | 2.55 3.02 | <u>65.8</u> 61.0 | 22.5 16.8 | 1600 1200 | 47.1 48.2 | <u>3.48</u> 3.91 | 35.3 35.0 | <u>97</u> 107 | 3.98 3.61 |
| | 6.0 | 1.4 | 3.2 3.2 | 1200 | 50.7 52.8 | 32.5 36.8 | 0.64 | 3.02 | 63.5 | 16.8 | 1200 | 40.2 49.3 | 3.91 | 35.0 37.4 | 99 | 3.01 4.11 |
| 60 | 9.0 | 2.8 | 6.5 | 1200 | 52.3 | 33.1 | 0.63 | 2.81 | 61.8 | 18.6 | 1200 | 50.5 | 3.96 | 37.1 | 109 | 3.74 |
| 00 | 9.0 | 2.8 | 6.5 | 1600 | 54.5 | 37.5 | 0.69 | 2.92 | 64.4 62.2 | 18.6 | 1600 | 51.8 | 3.56 | 39.6 | 100 | 4.26 |
| | 12.0 12.0 | 5.3 5.3 | 12.2 12.2 | 1200 1600 | 53.0 55.2 | 33.4 37.8 | 0.63 0.68 | 2.70 2.81 | 62.2 64.8 | 19.6 19.6 | 1200 1600 | 51.8 53.1 | 3.99 3.58 | 38.3 40.9 | 110 101 | 3.81 4.34 |
| | 6.0 | 1.3 | 3.0 | 1200 | 48.3 | 31.5 | 0.65 | 3.38 | 59.9 | 14.3 | 1200 | 53.5 | 4.02 | 39.8 | 111 | 3.90 |
| | 6.0 | 1.3 | 3.0 | 1600 | 50.3 | 35.7 | 0.71 | 3.52 | 62.3 | 14.3 | 1600 | 54.8 | 3.61 | 42.4 | 102 | 4.44 |
| 70 | 9.0 9.0 | 2.7 2.7 | 6.3 6.3 | 1200 1600 | 50.0 52.1 | 32.2 36.4 | 0.64 0.70 | 3.13 3.25 | 60.7 63.2 | 16.0 16.0 | 1200 1600 | 56.2 57.5 | 4.08 3.67 | 42.2 45.0 | 113 103 | 4.03 4.60 |
| | 12.0 | 5.1 | 11.8 | 1200 | 50.9 | 32.5 | 0.64 | 3.01 | 61.1 | 16.9 | 1200 | 57.6 | 4.12 | 43.4 | 114 | 4.10 |
| | 12.0 6.0 | <u>5.1</u> 1.3 | 11.8 | 1600 | 53.0 | 36.8 | 0.70 | 3.13 | 63.6 | 16.9 | 1600 | 59.0 | 3.70 | 46.4 | 104 115 | 4.68 |
| | 6.0 | 1.3 | 2.9 2.9 | 1200 1600 | 45.7 47.6 | 30.5 34.5 | 0.67 0.72 | 3.79 3.94 | 58.6 61.0 | 12.1 12.1 | 1200 1600 | 58.8 60.2 | 4.14 3.72 | 44.5 47.5 | 105 | 4.16 4.74 |
| 80 | 9.0 | 2.6 | 6.1 | 1200 | 47.5 | 31.2 | 0.66 | 3.50 | 59.5 | 13.6 | 1200 | 61.7 | 4.21 | 47.1 | 118 | 4.29 |
| 00 | 9.0 | 2.6 | 6.1 | 1600 | 49.5 | 35.3 | 0.71 | 3.64 | 61.9 | 13.6 | 1600 | 63.2 | 3.78 | 50.2 | 107 | 4.90 |
| | 12.0 12.0 | 4.9 4.9 | 11.4 11.4 | 1200 1600 | 48.4 50.4 | 31.6 35.7 | 0.65 0.71 | 3.37 3.50 | 59.9 62.4 | 14.4 14.4 | 1200 1600 | 63.3 64.8 | 4.25 3.82 | 48.4 51.7 | 119 107 | 4.36 4.97 |
| | 6.0 | 1.2 | 2.8 | 1200 | 44.3 | 29.9 | 0.68 | 4.02 | 58.0 | 11.1 | 1200 | 61.3 | 4.20 | 46.7 | 117 | 4.28 |
| | 6.0 | 1.2 | 2.8 | 1600 | 46.1 | 33.8 | 0.73 | 4.19 | 60.4 | 11.1 | 1600 | 62.8 | 3.78 | 49.9 | 106 | 4.88 |
| 85 | 9.0 9.0 | 2.6 2.6 | 6.0 6.0 | 1200 1600 | 46.2 48.1 | 30.6 34.7 | 0.66 0.72 | 3.72 3.87 | 58.8 61.3 | 12.5 12.5 | 1200 1600 | 64.3 65.9 | 4.28 3.84 | 49.4 52.7 | 120 108 | 4.40 5.02 |
| | 12.0 | 4.9 | 11.3 | 1200 | 47.1 | 31.0 | 0.66 | 3.57 | 59.3 | 13.2 | 1200 | 65.9 | 4.32 | 50.7 | 121 | 4.47 |
| | 12.0 | 4.9 | 11.3 | 1600 | 49.0 | 35.1 | 0.72 | 3.72 | 61.7 | 13.2 | 1600 | 67.5 | 3.88 | 54.1 | 109 | 5.09 |
| | 6.0 6.0 | 1.2 1.2 | 2.8 2.8 | 1200 1600 | 42.9 44.6 | 29.3 33.2 | 0.68 0.74 | 4.26 4.43 | 57.4 59.8 | 10.1 10.1 | 1200 1600 | 63.9 65.5 | 4.27 3.83 | 49.0 52.3 | 119 108 | 4.39 5.01 |
| 90 | 9.0 | 2.6 | 5.9 | 1200 | 44.8 | 30.1 | 0.67 | 3.93 | 58.2 | 11.4 | 1200 | 66.9 | 4.35 | 51.7 | 122 | 4.51 |
| 30 | 9.0 | 2.6 | 5.9 | 1600 | 46.6 | 34.1 | 0.73 | 4.10 | 60.6 | 11.4 | 1600 | 68.6 | 3.91 | 55.1 | 110 | 5.14 |
| | 12.0 12.0 | 4.8 4.8 | 11.1 11.1 | 1200 1600 | 45.7 47.6 | 30.5 34.5 | 0.67 0.72 | 3.78 3.94 | 58.6 61.1 | 12.1 12.1 | 1200 1600 | 68.5 70.2 | 4.39 3.95 | 53.0 56.6 | 123 111 | 4.57 5.21 |
| | 6.0 | 1.2 | 2.7 | 1200 | 39.8 | 28.2 | 0.71 | 4.79 | 56.2 | 8.3 | | | | | | |
| | 6.0 | 1.2 | 2.7 | 1600 | 41.4 | 31.9 | 0.77 | 4.99 | 58.5 | 8.3 | | | | | | |
| 100 | 9.0 9.0 | 2.5 2.5 | 5.8 5.8 | 1200 1600 | 41.8 43.5 | 28.9 32.7 | 0.69 0.75 | 4.43 4.62 | 57.0 59.3 | 9.4 9.4 | | | | | | |
| | 12.0 | 4.7 | 10.9 | 1200 | 42.8 | 29.3 | 0.69 | 4.26 | 57.4 | 10.0 | | | | | | |
| | 12.0 | 4.7 | 10.9 | 1600 | 44.6 | 33.2 | 0.74 | 4.44 | 59.7 | 10.0 | | | | | | |
| | 6.0 6.0 | 1.1 1.1 | 2.6 2.6 | 1200 1600 | 36.5 38.0 | 26.9 30.4 | 0.74 0.80 | 5.40 5.62 | 55.0 57.3 | 6.8 6.8 | | | | | | |
| 110 | 9.0 | 2.4 | 5.6 | 1200 | 38.6 | 27.7 | 0.72 | 5.00 | 55.8 | 7.7 | | Operation | ation not | rocome | onded | |
| 110 | 9.0 | 2.4 | 5.6 | 1600 | 40.2 | 31.4 | 0.78 | 5.21 | 58.0 | 7.7 | | Opera | | recomm | lended | |
| | 12.0 12.0 | 4.6 4.6 | 10.6 10.6 | 1200 1600 | 39.7 41.3 | 28.1 31.8 | 0.71 0.77 | 4.81 5.01 | 56.1 58.5 | 8.2 8.2 | | | | | | |
| | 6.0 | 1.1 | 2.5 | 1200 | 33.0 | 25.5 | 0.77 | 6.09 | 53.9 | 5.4 | | | | | | |
| | 6.0 | 1.1 | 2.5 | 1600 | 34.4 | 28.9 | 0.84 | 6.34 | 56.1 | 5.4 | | | | | | |
| 120 | 9.0 9.0 | 2.4 2.4 | 5.5 5.5 | 1200 1600 | 35.2 36.7 | 26.4 29.9 | 0.75 0.81 | 5.65 5.88 | 54.6 56.8 | 6.2 6.2 | | | | | | |
| | 12.0 | 4.5 | 10.4 | 1200 | 36.3 | 26.8 | 0.74 | 5.44 | 55.0 | 6.7 | | | | | | |
| | 12.0 | 4.5 | 10.4 | 1600 | 37.8 | 30.3 | 0.80 | 5.66 | 57.2 | 6.7 | | | | | | |

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/SO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/SO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply: performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. Operation below 60°F EWT requires optional insulated water/refrigerant circuit. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Performance Data – TC H/V 060

| EWT | | W | PD | | C | Cooling | g - EAT | 80/67°I | F | | | He | ating - | EAT 7 | 0°F | |
|-----|--------------|--------------|--------------|----------------|--------------|--------------|-------------------|--------------|--------------|---------------------|----------------|--------------|--------------|---------------------|-----------------|--------------|
| °F | GPM | PSI | FT | Airflow CFM | тс | SC | Sens/Tot Ratio | kW | HR | EER | Airflow CFM | HC | kW | HE | LAT | СОР |
| 20 | 15.0 | 14.0 | 32.2 | | O | peration | not reco | mmend | ed | | 1460 | 41.6 | 4.98 | 25.8 | 96 | 2.45 |
| | 15.0 7.5 | 14.0 3.4 | 32.2 7.9 | 1460 | 68.2 | 41.6 | 0.61 | 3.00 | 78.3 | 22.8 | 1950 1460 | 42.6 45.5 | 4.48 5.08 | 27.5 29.2 | <u>90</u> 99 | 2.79 2.62 |
| | 7.5 | 3.4 | 7.9 | 1950 | 71.0 | 47.0 | 0.66 | 3.12 | 81.6 | 22.8 | 1950 | 46.6 | 4.56 | 31.1 | 92 | 2.99 |
| 30 | 11.3 11.3 | 6.8 6.8 | 15.8 15.8 | 1460 1950 | 69.0 71.8 | 41.5 47.0 | 0.60 0.65 | 2.87 2.99 | 78.7 82.0 | 24.0 24.0 | 1460 1950 | 47.4 48.6 | 5.13 4.61 | 30.9 33.0 | 100 93 | 2.71 3.09 |
| | 15.0 | 12.6 | 29.2 | 1460 | 69.3 | 41.3 | 0.60 | 2.82 | 78.8 | 24.6 | 1460 | 48.5 | 5.16 | 31.8 | 101 | 2.75 |
| | 15.0 | 12.6 | 29.2 | 1950 | 72.1 | 46.8 | 0.65 | 2.94 | 82.1 | 24.6 | 1950 | 49.7 | 4.64 | 34.0 | 94 | 3.14 |
| | 7.5 7.5 | 3.1 3.1 | 7.0 7.0 | 1460 1950 | 66.6 69.3 | 41.1 46.5 | 0.62 0.67 | 3.21 3.34 | 77.4 80.6 | 20.8 20.8 | 1460 1950 | 52.2 53.5 | 5.27 4.73 | 35.1 37.5 | 103 95 | 2.91 3.31 |
| 40 | 11.3 | 6.3 | 14.6 | 1460 | 67.8 | 41.5 | 0.61 | 3.05 | 78.1 | 22.2 | 1460 | 54.8 | 5.34 | 37.3 | 105 | 3.01 |
| 40 | 11.3 15.0 | 6.3 11.8 | 14.6 27.2 | 1950 1460 | 70.6 68.3 | 47.0 41.6 | 0.67 0.61 | 3.18 2.98 | 81.3 78.4 | 22.2 22.9 | 1950 1460 | 56.1 56.2 | 4.80 5.38 | 39.8 38.5 | 97 106 | 3.43 3.06 |
| | 15.0 | 11.8 | 27.2 | 1950 | 71.1 | 47.0 | 0.66 | 3.10 | 81.6 | 22.9 | 1950 | 57.5 | 4.83 | 41.1 | 97 | 3.49 |
| | 7.5 | 2.8 | 6.4 | 1460 | 64.7 | 40.3 | 0.62 | 3.47 | 76.4 | 18.7 | 1460 | 59.5 | 5.48 | 41.4 | 108 | 3.18 |
| 50 | 7.5 11.3 | 2.8 5.9 | 6.4 13.7 | 1950 1460 | 67.3 66.0 | 45.6 40.9 | 0.68 0.62 | 3.61 3.28 | 79.6 77.1 | 18.7 20.1 | 1950 1460 | 60.9 62.6 | 4.92 5.57 | 44.2 44.1 | 99 110 | 3.63 3.29 |
| 50 | 11.3 | 5.9 | 13.7 | 1950 | 68.7 | 46.3 | 0.67 | 3.41 | 80.3 | 20.1 | 1950 | 64.1 | 5.01 | 47.1 | 100 | 3.75 |
| | 15.0 15.0 | 11.1 11.1 | 25.7 25.7 | 1460 1950 | 66.7 69.4 | 41.2 46.6 | 0.62 0.67 | 3.19 3.32 | 77.5 80.7 | 20.9 20.9 | 1460 1950 | 64.3 65.9 | 5.63 5.05 | 45.6 48.7 | 111 101 | 3.35 3.82 |
| | 7.5 | 2.6 | 6.0 | 1460 | 62.4 | 39.3 | 0.63 | 3.78 | 75.3 | 16.5 | 1460 | 66.9 | 5.70 | 47.8 | 112 | 3.44 |
| | 7.5 | 2.6 | 6.0 | 1950 | 65.0 | 44.5 | 0.69 | 3.93 | 78.4 | 16.5 | 1950 | 68.5 | 5.12 | 51.0 | 103 | 3.92 |
| 60 | 11.3 11.3 | 5.6 5.6 | 13.0 13.0 | 1460 1950 | 63.7 66.3 | 39.9 45.1 | 0.63 0.68 | 3.56 3.70 | 75.8 78.9 | 17.9 17.9 | 1460 1950 | 70.4 72.1 | 5.82 5.22 | 50.9 54.4 | 115 104 | 3.55 4.05 |
| | 15.0 | 10.7 | 24.6 | 1460 | 64.2 | 40.0 | 0.62 | 3.45 | 75.9 | 18.6 | 1460 | 72.4 | 5.88 | 52.6 | 116 | 3.61 |
| | 15.0 7.5 | 10.7 2.4 | 24.6 5.6 | 1950 1460 | 66.8 59.6 | 45.3 38.0 | 0.68 | 3.59 4.15 | 79.0 73.7 | <u>18.6</u> 14.3 | 1950 1460 | 74.1 74.2 | 5.28 5.93 | <u>56.2</u> 54.1 | 105 117 | 4.12 3.66 |
| | 7.5 | 2.4 | 5.6 | 1950 | 62.0 | 43.0 | 0.69 | 4.32 | 76.7 | 14.3 | 1950 | 75.9 | 5.33 | 57.8 | 106 | 4.18 |
| 70 | 11.3 11.3 | 5.4 5.4 | 12.5 12.5 | 1460 1950 | 61.1 63.6 | 38.6 43.7 | 0.63 0.69 | 3.89 4.05 | 74.3 77.4 | 15.7 15.7 | 1460 1950 | 78.0 79.9 | 6.05 5.44 | 57.5 61.4 | 119 108 | 3.78 4.31 |
| | 15.0 | 10.3 | 23.7 | 1460 | 61.6 | 38.8 | 0.63 | 3.77 | 74.4 | 16.3 | 1460 | 80.1 | 6.12 | 59.2 | 108 | 3.84 |
| | 15.0 | 10.3 | 23.7 | 1950 | 64.2 | 43.9 | 0.68 | 3.92 | 77.5 | 16.3 | 1950 | 82.0 | 5.50 | 63.2 | 109 | 4.37 |
| | 7.5 7.5 | 2.3 2.3 | 5.4 5.4 | 1460 1950 | 56.4 58.8 | 36.7 41.5 | 0.65 0.71 | 4.59 4.78 | 72.1 75.1 | 12.3 12.3 | 1460 1950 | 81.1 83.0 | 6.15 5.52 | 60.1 64.2 | 121 109 | 3.86 4.41 |
| 80 | 11.3 | 5.2 | 12.0 | 1460 | 58.1 | 37.3 | 0.64 | 4.29 | 72.7 | 13.5 | 1460 | 84.9 | 6.27 | 63.4 | 124 | 3.97 |
| | 11.3 15.0 | 5.2 9.9 | 12.0 22.9 | 1950 1460 | 60.4 58.7 | 42.2 37.5 | 0.70 0.64 | 4.47 4.15 | 75.7 72.8 | 13.5 14.1 | 1950 1460 | 87.0 86.9 | 5.63 6.33 | 67.7 65.1 | 111 125 | 4.52 4.02 |
| | 15.0 | 9.9 | 22.9 | 1950 | 61.1 | 42.4 | 0.69 | 4.32 | 75.8 | 14.1 | 1950 | 89.0 | 5.69 | 69.5 | 112 | 4.58 |
| | 7.5 7.5 | 2.3 2.3 | 5.2 5.2 | 1460 1950 | 54.8 57.0 | 36.1 40.8 | 0.66 0.72 | 4.84 5.04 | 71.3 74.2 | 11.4 | 1460 1950 | 84.1 86.2 | 6.25 5.6 | 62.8 67.0 | 123 111 | 3.95 4.50 |
| 05 | 11.3 | 2.3 5.1 | 11.8 | 1460 | 56.4 | 36.6 | 0.72 | 4.52 | 74.2 | 11.4 12.5 | 1460 | 87.8 | 6.4 | 65.9 | 126 | 4.04 |
| 85 | 11.3 | 5.1 | 11.8 | 1950 | 58.7 | 41.4 | 0.70 | 4.71 | 74.8 | 12.5 | 1950 | 89.9 | 5.7 | 70.4 | 113 | 4.61 |
| | 15.0 15.0 | 9.8 9.8 | 22.6 22.6 | 1460 1950 | 57.1 59.5 | 36.8 41.6 | 0.64 0.70 | 4.37 4.55 | 72.0 75.0 | 13.1 13.1 | 1460 1950 | 89.6 91.8 | 6.4 5.8 | 67.5 72.0 | 127 114 | 4.09 4.66 |
| | 7.5 | 2.2 | 5.1 | 1460 | 53.1 | 35.4 | 0.67 | 5.09 | 70.5 | 10.4 | 1460 | 87.2 | 6.35 | 65.4 | 125 | 4.03 |
| | 7.5 11.3 | 2.2 5.0 | 5.1 11.6 | 1950 1460 | 55.3 54.8 | 40.1 35.9 | 0.73 0.66 | 5.30 4.76 | 73.4 71.0 | 10.4 11.5 | 1950 1460 | 89.3 90.7 | 5.70 6.45 | 69.9 68.4 | 112 128 | 4.59 4.12 |
| 90 | 11.3 | 5.0 | 11.6 | 1950 | 57.1 | 40.7 | 0.71 | 4.95 | 74.0 | 11.5 | 1950 | 92.9 | 5.80 | 73.1 | 114 | 4.70 |
| | 15.0 15.0 | 9.6 9.6 | 22.2 22.2 | 1460 1950 | 55.5 57.8 | 36.1 40.9 | 0.65 0.71 | 4.60 4.78 | 71.2 74.1 | 12.1 12.1 | 1460 1950 | 92.3 94.5 | 6.50 5.84 | 69.8 74.5 | 129 115 | 4.16 4.74 |
| | 7.5 | 2.1 | 4.9 | 1460 | 49.6 | 34.3 | 0.69 | 5.67 | 69.0 | 8.8 | 1930 | 94.0 | 5.04 | 74.5 | 115 | 4./4 |
| | 7.5 | 2.1 | 4.9 | 1950 | 51.7 | 38.9 | 0.75 | 5.90 | 71.9 | 8.8 | | | | | | |
| 100 | 11.3 11.3 | 4.9 4.9 | 11.3 11.3 | 1460 1950 | 51.4 53.5 | 34.7 39.3 | 0.68 0.73 | 5.29 5.51 | 69.5 72.3 | 9.7 9.7 | | | | | | |
| | 15.0 | 9.4 | 21.7 | 1460 | 52.1 | 34.8 | 0.67 | 5.11 | 69.6 | 10.2 | | | | | | |
| | 15.0 | 9.4 | 21.7 | 1950 1460 | 54.2 | 39.4 | 0.73 | 5.32 | 72.4 68.2 | 10.2 | | | | | | |
| | 7.5 | 2.0 2.0 | 4.7 4.7 | 1460 | 46.6 48.5 | 33.8 38.2 | 0.73 | 6.33 6.59 | 71.0 | 7.4 | | | | | | |
| 110 | 11.3 | 4.8 | 11.0 | 1460 | 47.8 | 33.6 | 0.70 | 5.91 | 68.0 | 8.1 | | Opera | ition not | recomm | nended | |
| | 11.3 15.0 | 4.8 9.2 | 11.0 21.2 | 1950 1460 | 49.8 48.6 | 38.1 33.7 | 0.76 0.69 | 6.15 5.71 | 70.8 68.2 | 8.1 8.5 | | 000.0 | | | | |
| | 15.0 | 9.2 | 21.2 | 1950 | 50.6 | 38.2 | 0.75 | 5.94 | 71.0 | 8.5 | | | | | | |
| | 7.5 7.5 | 2.0 2.0 | 4.6 4.6 | 1460 1950 | 43.0 44.7 | 33.1 37.5 | 0.77 0.84 | 7.07 7.36 | 67.2 70.0 | 6.1 6.1 | | | | | | |
| 120 | 11.3 | 4.7 | 10.7 | 1460 | 44.2 | 32.8 | 0.74 | 6.61 | 66.8 | 6.7 | | | | | | |
| 120 | 11.3 15.0 | 4.7 | 10.7 20.7 | 1950 1460 | 46.0 44.9 | 37.1 32.7 | 0.81 0.73 | 6.88 6.38 | 69.6 66.8 | 6.7 7.0 | | | | | | |
| | 15.0 | 9.0 9.0 | 20.7 | 1460 1950 | 44.9 46.8 | 32.7 37.0 | 0.73 | 6.64 | 69.5 | 7.0 | | | | | | |

2,000 CFM Nominal (Rated) Airflow

Performance capacities shown in thousands of Btuh

Interpolation is permissible; extrapolation is not. All entering air conditions are 80°F DB and 67°F WB in cooling, and 70°F DB in heating. AHRI/ISO certified conditions are 80.6°F DB and 66.2°F WB in cooling and 68°F DB in heating. Table does not reflect fan or pump power corrections for AHRI/ISO conditions. All performance is based upon the lower voltage of dual voltage rated units. Performance stated is at the rated power supply; performance may vary as the power supply varies from the rated. Operation below 40°F EWT is based upon a 15% methanol antifreeze solution. See performance correction tables for operating conditions other than those listed above. See Performance Data Selection Notes for operation in the shaded areas.

Air Flow Correction Table

| | Cooling Corrections | | | | | | | | | | | | |
|---------|---------------------|---------|------------------|--------|--------|--------|--------|--------|--------|--------|-----------|--|--|
| Ent Air | Total Clg | • | | | | | | | | | | | |
| WB °F | Сар | 65 | 70 | 75 | 80 | 80.6 | 85 | 90 | 95 | Power | Rejection | | |
| 50 | 0.7800 | 0.9778 | * | * | * | * | * | * | * | 0.9972 | 0.8243 | | |
| 55 | 0.8327 | 0.8966 | 1.0556 | * | * | * | * | * | * | 0.9980 | 0.8667 | | |
| 60 | 0.8954 | 0.7505 | 0.9184 | 1.1056 | * | * | * | * | * | 0.9988 | 0.9169 | | |
| 65 | 0.9681 | | 0.6778 | 0.8992 | 1.1213 | 1.1480 | 1.3439 | * | * | 0.9996 | 0.9747 | | |
| 66.2 | 0.9871 | | 0.6103 | 0.8420 | 1.0698 | 1.0969 | 1.2938 | * | * | 0.9999 | 0.9897 | | |
| 67 | 1.0000 | | 0.5507 | 0.7782 | 1.0000 | 1.0262 | 1.2161 | 1.4266 | * | 1.0000 | 1.0000 | | |
| 70 | 1.0508 | | | 0.6408 | 0.8856 | 0.9135 | 1.1082 | 1.3087 | 1.4869 | 1.0005 | 1.0403 | | |
| 75 | 1.1435 | Operati | ion not recommer | nded | 0.6085 | 0.6403 | 0.8566 | 1.0663 | 1.2376 | 1.0014 | 1.1135 | | |

* Sensible capacity equals total capacity. AHRI/ISO/ASHRAE 13256-1 uses entering air conditions of Cooling - 80.6°F DB/ 66.2°F WB, and Heating -68°F DB/ 59°F WB entering air temperature.

| | Heating C | Corrections | |
|------------------|---------------------|------------------|-----------------------|
| Ent Air DB °F | Heating Capacity | Heating Power | Heat of Extraction |
| 45 | 1.0507 | 0.7802 | 1.1314 |
| 50 | 1.0327 | 0.8227 | 1.0953 |
| 55 | 1.0195 | 0.8683 | 1.0646 |
| 60 | 1.0102 | 0.9168 | 1.0380 |
| 65 | 1.0033 | 0.9680 | 1.0139 |
| 68 | 1.0000 | 1.0000 | 1.0000 |
| 70 | 0.9979 | 1.0218 | 0.9908 |
| 75 | 0.9928 | 1.0781 | 0.9673 |
| 80 | 0.9866 | 1.1367 | 0.9419 |

Air Flow Correction Table

| Airflow | | Heating | | | | Cooling | | |
|---------------|---------------------|------------------|-----------------------|-------------------|----------------------|---------------------|--------|----------------------|
| % of Rated | Heating Capacity | Heating Power | Heat of Extraction | Total Capacity | Sensible Capacity | Sens/Total Ratio | Power | Heat of Rejection |
| 75 | 0.9764 | 1.1134 | 0.9368 | 0.9605 | 0.8837 | 0.9200 | 0.9606 | 0.9605 |
| 81.25 | 0.9829 | 1.0789 | 0.9551 | 0.9730 | 0.9130 | 0.9384 | 0.9691 | 0.9722 |
| 87.5 | 0.9889 | 1.0484 | 0.9717 | 0.9837 | 0.9393 | 0.9548 | 0.9784 | 0.9826 |
| 93.75 | 0.9947 | 1.0222 | 0.9867 | 0.9927 | 0.9668 | 0.9739 | 0.9887 | 0.9919 |
| 100 | 1.0000 | 1.0000 | 1.0000 | 1.0000 | 1.0000 | 1.0000 | 1.0000 | 1.0000 |
| 106.25 | 1.0050 | 0.9820 | 1.0116 | 1.0055 | 1.0434 | 1.0377 | 1.0122 | 1.0069 |
| 112.5 | 1.0096 | 0.9681 | 1.0216 | 1.0093 | 1.1016 | 1.0915 | 1.0253 | 1.0126 |
| 118.75 | 1.0138 | 0.9583 | 1.0299 | 1.0113 | 1.1790 | 1.1658 | 1.0394 | 1.0171 |
| 125 | 1.0177 | 0.9527 | 1.0365 | 1.0116 | 1.2798 | 1.2652 | 1.0544 | 1.0204 |

Antifreeze Correction Table

| | | | Cooling | | Hea | ting | WPD |
|------------------|-----------------|-----------|----------|-------|---------|-------|------------|
| Antifreeze Type | Antifreeze % | | EWT 90°F | | EWT | 30°F | Corr. Fct. |
| | | Total Cap | Sens Cap | Power | Htg Cap | Power | EWT 30°F |
| Water | 0 | 1.000 | 1.000 | 1.000 | 1.000 | 1.000 | 1.000 |
| | 5 | 0.995 | 0.995 | 1.003 | 0.989 | 0.997 | 1.070 |
| Propylene Glycol | 15 | 0.986 | 0.986 | 1.009 | 0.968 | 0.990 | 1.210 |
| | 25 | 0.978 | 0.978 | 1.014 | 0.947 | 0.983 | 1.360 |
| | 5 | 0.997 | 0.997 | 1.002 | 0.989 | 0.997 | 1.070 |
| Methanol | 15 | 0.990 | 0.990 | 1.007 | 0.968 | 0.990 | 1.160 |
| | 25 | 0.982 | 0.982 | 1.012 | 0.949 | 0.984 | 1.220 |
| | 5 | 0.998 | 0.998 | 1.002 | 0.981 | 0.994 | 1.140 |
| Ethanol | 15 | 0.994 | 0.994 | 1.005 | 0.944 | 0.983 | 1.300 |
| | 25 | 0.986 | 0.986 | 1.009 | 0.917 | 0.974 | 1.360 |
| | 5 | 0.998 | 0.998 | 1.002 | 0.993 | 0.998 | 1.040 |
| Ethylene Glycol | 15 | 0.994 | 0.994 | 1.004 | 0.980 | 0.994 | 1.120 |
| | 25 | 0.988 | 0.988 | 1.008 | 0.966 | 0.990 | 1.200 |

Blower Performance Data – Standard Unit

Airflow in CFM with wet coil and clean air filter

| Model | Fan | Rated | Min | Airflow (cfm) at External Static Pressure (in. wg) | | | | | | | | | | | | | | | |
|--------------|-------|---------|------|--|------|------|------|------|------|------|------|------|------|------|------|----------|-----------|-------|------|
| Model | Speed | Airflow | CFM | 0.00 | 0.05 | 0.10 | 0.15 | 0.20 | 0.25 | 0.30 | 0.35 | 0.40 | 0.45 | 0.50 | 0.60 | 0.70 | 0.80 | 0.90 | 1.00 |
| | н | | | | 1 | 310 | 300 | 290 | 280 | 270 | 250 | 230 | 210 | 180 | 0 | peratior | n not rea | comme | nded |
| TCH/V 006 | MED | 220 | 150 | | | 260 | 250 | 240 | 230 | 210 | 200 | 190 | 150 | | | | | | |
| 000 | LOW | | | | | 210 | 200 | 190 | 180 | 160 | 150 | | | | | | | | |
| | н | | | | | 410 | 400 | 380 | 360 | 350 | 330 | 320 | 300 | 280 | | | | | |
| TCH/V 009 | MED | 325 | 225 | | | 390 | 370 | 360 | 340 | 320 | 310 | 290 | 280 | 260 | | | | | |
| 005 | LOW |] | | | | 340 | 330 | 322 | 310 | 300 | 280 | 260 | 250 | | | | | | |
| TOUR | н | | | | | 470 | 460 | 450 | 440 | 430 | 420 | 400 | 390 | 380 | 320 | | | | |
| TCH/V 012 | MED | 400 | 300 | | | 420 | 410 | 400 | 390 | 380 | 370 | 360 | 350 | 340 | | | | | |
| 012 | LOW | | | | | 360 | 360 | 350 | 340 | 320 | 320 | 310 | 300 | | | | | | |
| TOUR | н | | | | | 745 | 725 | 706 | 696 | 686 | 666 | 637 | 588 | 539 | 451 | | | | |
| TCH/V 015 | MED | 525 | 375 | 686 | 676 | 666 | 657 | 647 | 637 | 617 | 608 | 588 | 549 | 510 | | | | | |
| 010 | LOW | | | 608 | 598 | 588 | 578 | 568 | 559 | 549 | 529 | 510 | 480 | 451 | | | | | |
| TOUR | н | | | | | 745 | 725 | 706 | 696 | 686 | 666 | 637 | 588 | 539 | 451 | | | | |
| TCH/V 018 | MED | 600 | 450 | 686 | 676 | 666 | 657 | 647 | 637 | 617 | 608 | 588 | 549 | 510 | | | | | |
| 010 | LOW | | | 608 | 598 | 588 | 578 | 568 | 559 | 549 | 529 | 510 | 480 | 451 | | | | | |
| TOUR | н | | | | | | | | | | | 950 | 922 | 884 | 827 | 732 | 656 | | |
| TCH/V 024 | MED | 800 | 600 | 960 | 950 | 941 | 931 | 912 | 893 | 874 | 855 | 836 | 817 | 789 | 732 | 665 | | | |
| 024 | LOW | | | 779 | 770 | 760 | 751 | 741 | 732 | 722 | 713 | 694 | 684 | 665 | 618 | | | | |
| тенал | н | | | | | | | | | 1102 | 1074 | 1045 | 1017 | 979 | 903 | 798 | | | |
| TCH/V 030 | MED | 1000 | 750 | 1188 | 1169 | 1140 | 1121 | 1093 | 1064 | 1036 | 1017 | 988 | 960 | 922 | 846 | | | | |
| | LOW | | | 1064 | 1045 | 1017 | 998 | 979 | 960 | 931 | 912 | 884 | 855 | 827 | 751 | | | | |
| тенал | н | | | 1474 | 1455 | 1436 | 1416 | 1387 | 1358 | 1329 | 1310 | 1280 | 1232 | 1174 | 1077 | 931 | | | |
| TCH/V 036 | MED | 1200 | 900 | 1174 | 1164 | 1106 | 1106 | 1096 | 1096 | 1086 | 1077 | 1067 | 1038 | 1009 | 912 | | | | |
| | LOW | | | 980 | 980 | 970 | 970 | 960 | 960 | 951 | 951 | 941 | 922 | 902 | | | | | |
| тсу | н | | | 1328 | 1300 | 1269 | 1235 | 1198 | 1157 | 1114 | 1067 | 1018 | 965 | | | | | | |
| 041 | MED | 1325 | 950 | 1181 | 1164 | 1142 | 1118 | 1090 | 1058 | 1023 | 985 | | | | | | | | |
| | LOW | | | 1031 | 1021 | 1008 | 991 | 971 | 947 | | | | | | | | | | |
| TCH/V | н | | | 1558 | 1530 | 1501 | 1473 | 1444 | 1416 | 1378 | 1340 | 1302 | 1264 | 1226 | 1131 | | | | |
| 042 | MED | 1350 | 1050 | 1416 | 1397 | 1368 | 1349 | 1321 | 1302 | 1273 | 1245 | 1207 | 1169 | 1131 | 1064 | | | | |
| | LOW | | | 1083 | 1083 | 1074 | 1074 | 1064 | 1055 | | | | | | | | | | |
| TCH/V | н | | | | | | | 1881 | 1853 | 1815 | 1767 | 1710 | 1653 | 1596 | 1416 | 1216 | 1216 | | |
| 048 | MED | 1600 | 1200 | 1843 | 1824 | 1805 | 1786 | 1767 | 1729 | 1682 | 1653 | 1625 | 1577 | 1520 | 1340 | | | | |
| | LOW | | | 1682 | 1663 | 1644 | 1625 | 1606 | 1587 | 1568 | 1530 | 1492 | 1435 | 1378 | 1264 | | | | |
| тсн/у | н | | | 2195 | 2195 | 2185 | 2176 | 2156 | 2117 | 2078 | 2048 | 2019 | 1999 | 1970 | 1921 | 1842 | 1754 | 1627 | |
| 060 | MED | 2000 | 1500 | 2009 | 2009 | 1999 | 1980 | 1950 | 1931 | 1901 | 1882 | 1852 | 1823 | 1793 | 1744 | 1676 | 1588 | | |
| | LOW | | | 1813 | 1813 | 1803 | 1793 | 1774 | 1764 | 1744 | 1725 | 1695 | 1666 | 1637 | 1568 | | | | |

Black areas denote ESP where operation is not recommended.

Units factory shipped on medium speed. Other speeds require field selection.

All airflow is rated and shown above at the lower voltage if unit is dual voltage rated, e.g. 208V for 208-230V units.

Only two speed fan (H & M) available on 575V units.

Performance stated is at the rated power supply, performance may vary as the power supply varies from the rated.

Blower Performance Data – High Static

| | Fan | Rated | Min | | | | | Airflo | ow (cfm |) at Ext | ernal St | atic Pre | essure | (in. wg |) | | | | |
|--------------|--------|---------|------|-------|-------------|--------|------|--------|---------|----------|----------|----------|--------|---------|------|------|------|------|------|
| Model | Speed | Airflow | CFM | 0.00 | 0.05 | 0.10 | 0.15 | 0.20 | 0.25 | 0.30 | 0.35 | 0.40 | 0.45 | 0.50 | 0.60 | 0.70 | 0.80 | 0.90 | 1.00 |
| | HS HI | | | | | | 774 | 764 | 755 | 745 | 735 | 715 | 696 | 676 | 637 | 519 | | | |
| TCH/V 015 | HS MED | 525 | 375 | 735 | 725 | 706 | 696 | 686 | 676 | 657 | 657 | 647 | 637 | 617 | 588 | 480 | | | |
| 0.0 | HS LOW | | | 657 | 647 | 627 | 617 | 608 | 598 | 588 | 578 | 568 | 568 | 559 | 519 | | | | |
| | HS HI | | | | | | 774 | 764 | 755 | 745 | 735 | 715 | 696 | 676 | 637 | 519 | | | |
| TCH/V 018 | HS MED | 600 | 450 | 735 | 725 | 706 | 696 | 686 | 676 | 657 | 657 | 647 | 637 | 617 | 588 | 480 | | | |
| 010 | HS LOW | | | 657 | 647 | 627 | 617 | 608 | 598 | 588 | 578 | 568 | 568 | 559 | 519 | | | | |
| | HS HI | | | Opera | tion not re | acommo | ndod | | | | | | | 979 | 903 | 798 | 665 | | |
| TCH/V 024 | HS MED | 800 | 600 | Орега | | ecomme | nueu | | | | | 988 | 960 | 922 | 846 | 713 | | | |
| 024 | HS LOW | | | | | | | 979 | 960 | 931 | 912 | 884 | 855 | 827 | 751 | 675 | | | |
| | HS HI | | | | | | | | | | | | | 1102 | 988 | 874 | 760 | | |
| TCH/V 030 | HS MED | 1000 | 750 | | | | | | | | | 1074 | 1026 | 979 | 884 | 779 | | | |
| 000 | HS LOW | | | 998 | 988 | 979 | 960 | 941 | 931 | 912 | 893 | 865 | 836 | 798 | | | | | |
| | HS HI | | | | | | | | | | | 1484 | 1455 | 1426 | 1358 | 1251 | 1135 | 931 | |
| TCH/V 036 | HS MED | 1200 | 900 | 1319 | 1310 | 1300 | 1290 | 1280 | 1271 | 1261 | 1242 | 1222 | 1213 | 1193 | 1116 | 1038 | | | |
| | HS LOW | | | 999 | 989 | 980 | 980 | 970 | 970 | 960 | 951 | 931 | 922 | 902 | | | | | |
| | HS HI | | | | | | | 1473 | 1463 | 1444 | 1425 | 1397 | 1387 | 1378 | 1311 | 1178 | | | |
| TCH/V 042 | HS MED | 1350 | 1050 | 1321 | 1311 | 1302 | 1292 | 1283 | 1273 | 1254 | 1245 | 1235 | 1216 | 1188 | 1121 | | | | |
| 042 | HS LOW | | | | | | | | | | | | | | | | | | |
| | HS HI | | | | | | | | | | | 1957 | 1938 | 1910 | 1862 | 1786 | 1701 | 1577 | 1435 |
| TCH/V 048 | HS MED | 1600 | 1200 | 1948 | 1948 | 1938 | 1919 | 1891 | 1872 | 1843 | 1824 | 1796 | 1767 | 1739 | 1691 | 1625 | 1539 | 1416 | 1254 |
| 040 | HS LOW | | | 1758 | 1758 | 1748 | 1739 | 1720 | 1710 | 1691 | 1672 | 1644 | 1615 | 1587 | 1520 | 1435 | 1311 | | أهم |
| | HS HI | | | 2352 | 2352 | 2342 | 2332 | 2323 | 2313 | 2293 | 2274 | 2254 | 2225 | 2195 | 2156 | 2087 | 2019 | 1940 | 1852 |
| TCH/V 060 | HS MED | 2000 | 1500 | 2117 | 2117 | 2107 | 2107 | 2097 | 2068 | 2038 | 2019 | 1999 | 1989 | 1980 | 1940 | 1891 | 1842 | 1460 | 1715 |
| | HS LOW | | | 1891 | 1891 | 1882 | 1882 | 1872 | 1862 | 1852 | 1852 | 1842 | 1833 | 1813 | 1793 | 1764 | 1715 | 1666 | 1588 |

Black areas denote ESP where operation is not recommended.

Units factory shipped on medium speed. Other speeds require field selection. All airflow is rated and shown above at the lower voltage if unit is dual voltage rated, e.g. 208V for 208-230V units. Only two speed fan (H & M) available on 575V units. Performance stated is at the rated power supply, performance may vary as the power supply varies from the rated.

Physical Data

| TC Series | 006 | 009 | 012 | 015 | 018 | 024 | 030 | 036 | 041 | 042 | 048 | 060 |
|--------------------------------|-------|-------|--------|----------|----------|----------|----------|---------------------|----------|---------------------|---------------------|---------------------|
| Compressor (1 Each) | | | Rotary | | | | | | Scroll | | | |
| Factory Charge HFC-410A (oz) | 17 | 18.5 | 23 | 32 | 43 | 43 | 47 | 50 | 70 | 70 | 74 | 82 |
| PSC Fan Motor & Blowe | r | | | | | | | | | | | |
| Fan Motor Type/Speeds | PSC/3 | PSC/3 | PSC-3 | PSC/3 | PSC/3 | PSC/3 | PSC/3 | PSC/3 | PSC/3 | PSC/3 | PSC/3 | PSC/3 |
| Fan Motor (hp) | 1/25 | 1/10 | 1/10 | 1/6 | 1/6 | 1/4 | 3/4 | 1/2 | 3/4 | 3/4 | 3/4 | 1 |
| Blower Wheel Size (Dia x w) | 5x5 | 5x5 | 6x5 | 8x7 | 8x7 | 9x7 | 9x7 | 9x8 | 9x8 | 9x8 | 10x10 | 11x10 |
| Water Connection Size | | | | | | | | | | | | |
| FPT | 1/2" | 1/2" | 1/2" | 1/2" | 1/2" | 3/4" | 3/4" | 3/4" | 3/4" | 3/4" | 1" | 1" |
| Coax Volume (gallons) | 0.123 | 0.143 | 0.167 | 0.286 | 0.450 | 0.286 | 0.323 | 0.323 | 0.890 | 0.890 | 0.738 | 0.939 |
| Vertical | | | | | | | | | | | • | |
| Air Coil Dimensions (H x W) | 10x15 | 10x15 | 10x15 | 20x17.25 | 20x17.25 | 20x17.25 | 20x17.25 | 24x21.75 | 20x17.25 | 24x21.76 | 24x28.25 | 24x28.25 |
| Filter Standard - 1" Throwaway | 10x18 | 10x18 | 10x18 | 20x20 | 20x20 | 20x20 | 20x20 | 24x24 | 20x20 | 24x24 | 1-14x24, 1-18x24 | 1-14x24, 1-18x24 |
| Weight - Operating (lbs.) | 103 | 105 | 114 | 153 | 158 | 189 | 197 | 203 | 210 | 218 | 263 | 278 |
| Weight - Packaged (lbs.) | 113 | 115 | 124 | 158 | 163 | 194 | 202 | 209 | 217 | 224 | 270 | 285 |
| Horizontal | | | | | | | | | | | | |
| Air Coil Dimensions (H x W) | 10x15 | 10x15 | 10x15 | 16x22 | 16x22 | 16x22 | 16x22 | 20x25 | N/A | 20x25 | 20x35 | 20x35 |
| Filter Standard - 1" Throwaway | 10x18 | 10x18 | 10x18 | 16x25 | 16x25 | 18x25 | 18x25 | 20x28 or 2-20x14 | N/A | 20x28 or 2-20x14 | 1-20x24, 1-20x14 | 1-20x24, 1-20x14 |
| Weight - Operating (lbs.) | 103 | 105 | 114 | 153 | 158 | 174 | 182 | 203 | N/A | 218 | 263 | 278 |
| Weight - Packaged (lbs.) | 113 | 115 | 124 | 158 | 163 | 179 | 187 | 209 | N/A | 224 | 270 | 285 |

Notes:

All units have TXV expansion device, and 1/2" & 3/4" electrical knockouts.

FPT = Female Pipe Thread

Condensate Drain Connection is 3/4" FPT.

575 volt fan motors are two speed.

| Unit Maximum Water Working Pressure | Max Pressure PSIG [kPa] |
|-------------------------------------|-------------------------|
| Base Unit | 300 [2,068] |


TC - Horizontal – Dimensional Data

| Horiz | ontol | Ov | erall Cabi | net | | | Electrical Knockouts | | | |
|-----------|----------|--------------|---------------|--------------|-----------|---------------------|----------------------|----------------|-----------------|--|
| Mo | | A Width | B Length | C Height | | Horizontal Model | | J 1/2" | K 3/4" | |
| 006 - 012 | in cm | 19.1 48.5 | 34.1 86.6 | 11.1 28.2 | | uei | Low Voltage | Low Voltage | Power Supply | |
| 015 - 018 | in cm | 20.1 51.1 | 43.1 109.5 | 17.0 43.2 | 006 - 012 | in cm | 8.1 20.6 | 5.1 13.0 | 2.1 5.4 | |
| 024 - 030 | in cm | 20.1 51.1 | 43.1 109.5 | 18.3 46.5 | 015 - 030 | in cm | 12.1 30.8 | 9.1 23.2 | 6.1 15.6 | |
| 036 - 042 | in cm | 20.1 51.1 | 47.1 119.6 | 21.0 53.3 | 036 - 060 | in cm | 16.1 41.0 | 13.1 33.3 | 10.1 25.7 | |
| 048 - 060 | in cm | 24.1 61.2 | 54.1 137.4 | 21.0 53.3 | | 0.11 | | 00.0 | _3.1 | |

| | | | | Wa | ater Connec | tions | | |
|-----------|----------|--------------|----------------|-------------|-------------|------------|------------|--------------------|
| Horiz | ontal | (1 | $\overline{)}$ | | 2) | | 3) | |
| Мо | del | Loop In | Loop In | Loop Out | Loop Out | Cond. 3 | 3/4" FPT | Loop In/Out FPT |
| | | D | E | F | G | AA | BB | |
| 006 - 012 | in cm | 9.6 24.3 | 1.1 2.7 | 1.5 3.8 | 1.1 2.7 | 3.3 8.4 | 0.7 1.8 | 1/2" |
| 015 | in cm | 15.1 38.4 | 1.4 3.4 | 3.2 8.1 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 1/2" |
| 018 | in cm | 15.1 38.4 | 1.4 3.4 | 4.1 10.4 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 1/2" |
| 024 | in cm | 16.4 41.7 | 1.4 3.4 | 4.4 11.3 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 3/4" |
| 030 | in cm | 16.4 41.7 | 1.4 3.4 | 3.1 7.8 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 3/4" |
| 036 | in cm | 19.1 48.5 | 1.4 3.4 | 5.3 13.4 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 3/4" |
| 042 | in cm | 19.1 48.5 | 1.4 3.4 | 4.4 11.3 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 3/4" |
| 048 | in cm | 19.1 48.5 | 1.4 3.4 | 4.4 11.1 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 1" |
| 060 | in cm | 19.1 48.5 | 1.4 3.4 | 3.8 9.7 | 1.4 3.5 | 3.3 8.4 | 0.7 1.8 | 1" |

| Horiz | ontol | D | Discha uct Flange Insta | rge Connectio Illed (+/- 0.10 ir | Return Connection Using Return Air Opening | | | | | |
|-----------|-------|-----|----------------------------|-------------------------------------|---|-----|----------------------|-----------------------|-----|-----|
| Mo | | L | M Supply Height | N Supply Width | о | Ρ | Q Return Width | R Return Height | s | т |
| 006 - 012 | in | 0.8 | 8.9 | 6.7 | 5.2 | 1.3 | 16.1 | 9.8 | 1.1 | 0.6 |
| | cm | 1.9 | 22.7 | 17.0 | 13.3 | 3.3 | 41.0 | 25.0 | 2.7 | 1.5 |
| 015 - 018 | in | 2.6 | 13.3 | 9.9 | 4.1 | 1.3 | 23.0 | 15.0 | 1.1 | 1.0 |
| | cm | 6.6 | 33.8 | 25.1 | 10.5 | 3.3 | 58.4 | 38.1 | 2.8 | 2.5 |
| 024 - 030 | in | 2.6 | 13.3 | 9.9 | 4.1 | 1.3 | 23.0 | 16.3 | 1.1 | 1.0 |
| | cm | 6.6 | 33.8 | 25.1 | 10.5 | 3.3 | 58.4 | 41.4 | 2.8 | 2.5 |
| 036 - 042 | in | 2.5 | 16.1 | 11.0 | 3.0 | 2.5 | 25.9 | 19.0 | 1.1 | 1.0 |
| | cm | 6.3 | 40.9 | 27.9 | 7.7 | 6.4 | 65.8 | 48.3 | 2.8 | 2.5 |
| 048 | in | 3.7 | 16.1 | 13.7 | 4.1 | 1.3 | 35.9 | 19.0 | 1.1 | 1.0 |
| | cm | 9.5 | 41.0 | 34.8 | 10.3 | 3.2 | 91.2 | 48.3 | 2.8 | 2.5 |
| 060 | in | 1.7 | 18.1 | 13.7 | 4.1 | 1.3 | 35.9 | 19.0 | 1.1 | 1.0 |
| | cm | 4.4 | 46.0 | 34.8 | 10.3 | 3.2 | 91.2 | 48.3 | 2.8 | 2.5 |

TC - Horizontal – Dimensional Data



Legend:

CAP = Control Access Panel

BSP = Blower Service Panel

CSP = Compressor Access Panel

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

_ of _

TC - Vertical Upflow – Dimensional Data

Water Connections - Standard Units

| Vertic | al | 0\ | verall Cabi | net |
|------------|----|-------|-------------|--------|
| Upflo | | A | B | C |
| Mode | | Width | Depth | Height |
| 006 - 012 | in | 19.1 | 19.1 | 22.0 |
| | cm | 48.5 | 48.5 | 55.9 |
| 015 - 018 | in | 21.5 | 21.5 | 39.0 |
| | cm | 54.6 | 54.6 | 99.1 |
| 024 - 030, | in | 21.5 | 21.5 | 40.0 |
| 041 | cm | 54.6 | 54.6 | 101.6 |
| 036 - 042 | in | 21.5 | 26.0 | 45.0 |
| | cm | 54.6 | 66.0 | 114.3 |
| 048 - 060 | in | 24.0 | 32.5 | 46.0 |
| | cm | 61.0 | 82.6 | 116.8 |

| Vertical Upflow Model | | 1 | | | 2 | | | |
|-----------------------------|----------|------------|------------|--------------|-------------|-------------------|------------|----------------|
| | | Loop In | Loop In | Loop Out | Loop Out | Cond. 3/4" FPT | | Loop In/Out |
| | | D | E | F | G | н | I | FPT |
| 006 - 012 | in cm | 1.4 3.6 | 1.6 4.1 | 9.5 24.1 | 1.6 4.3 | 6.1 15.6 | 1.6 4.1 | 1/2" |
| 015 | in cm | 1.9 4.8 | 1.4 3.6 | 13.8 35.1 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 1/2" |
| 018 | in cm | 1.9 4.8 | 1.4 3.6 | 12.9 32.8 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 1/2" |
| 024 | in cm | 1.9 4.8 | 1.4 3.6 | 13.8 35.1 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 3/4" |
| 030 | in cm | 1.9 4.8 | 1.4 3.6 | 15.2 38.6 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 3/4" |
| 036 | in cm | 1.9 4.8 | 1.4 3.6 | 15.7 39.9 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 3/4" |
| 041 | in cm | 3.6 4.8 | 2.3 5.8 | 14.0 35.6 | 2.3 5.8 | 8.1 20.6 | 2.3 5.8 | 3/4" |
| 042 | in cm | 1.9 4.8 | 1.4 3.6 | 16.6 42.0 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 3/4" |
| 048 | in cm | 1.9 4.8 | 1.4 3.6 | 16.6 42.2 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 1" |
| 060 | in cm | 1.9 4.8 | 1.4 3.6 | 17.2 43.7 | 1.4 3.6 | 8.1 20.6 | 1.4 3.6 | 1" |

| | | Electrical Knockouts | | | | | | |
|--------------|-----------|----------------------|----------------|-----------------|--|--|--|--|
| Vert Mo | 1/2" 1/2" | | L 3/4" | | | | | |
| Woder | | Low Voltage | Low Voltage | Power Supply | | | | |
| 006 - 012 | in cm | 2.9 7.3 | 5.9 14.9 | 8.9 22.5 | | | | |
| 015 - 060 | in cm | 4.1 10.5 | 7.1 18.1 | 10.1 25.7 | | | | |
| 041 in cm | | 3.1 7.9 | 7.1 18.0 | 11.1 28.2 | | | | |

Notes:

- While clear access to all removable panels is not required, installer should take care to comply with all building codes and allow adequate clearance for future field service.
- Front & Side access is preferred for service access. However, all components may be serviced from the front access panel if side access is not available. (Except on TCV 009-030 with front return)
- 3. Discharge flange is field installed.
- 4. Condensate is 3/4" FPT.
- 5. Units shipped with filter rails. These rails should be removed for return duct connection. See Aff---- for accessory air filter frame with duct collar.

| R | Recommended Minimum Installation Clearances for Vertical Units* | | | | | | | |
|----|---|--|--|--|--|--|--|--|
| 1" | Back of unit | | | | | | | |
| | Side opposite return air | | | | | | | |
| 6" | Front if hard piped | | | | | | | |
| | Return Air Side | | | | | | | |
| 1" | Ducted return - ‡ Add for duct width - † Add 2" for 1" filter frame/rail or 3" for 2" filter frame/rail | | | | | | | |
| | Free (open) return - calculate required dimension for a maximum velocity of 600 fpm | | | | | | | |

*Field installed accessories (hoses, air cleaners, etc.) may require additional space.


Legend:

CAP = Control Access Panel

BSP = Blower Service Panel

CSP = Compressor Access Panel

ASP = Alternative Service Panel



TC - Vertical Upflow – Dimensional Data


| Vertical Model | | Duct F | | scharge Connection nstalled (+/- 0.10 in, +/- 2.5mm) | | | | Return Connection Using Return Air Opening | | | |
|-------------------|----|--------|------|---|----------------------|------|-----|---|-----------------------|-----|--|
| | | м | N | O Supply Width | P Supply Depth | Q | R | S Return Depth | T Return Height | U | |
| 006 - 012 | in | 8.9 | 5.1 | 9.0 | 9.0 | 5.5 | 2.1 | 16.2 | 9.9 | 0.7 | |
| | cm | 22.7 | 12.9 | 22.9 | 22.9 | 14.0 | 5.3 | 41.1 | 25.1 | 1.9 | |
| 015 - 018 | in | 6.4 | 3.8 | 14.0 | 14.0 | 5.3 | 2.3 | 18.3 | 20.9 | 0.7 | |
| | cm | 16.1 | 9.5 | 35.6 | 35.6 | 13.6 | 5.8 | 46.5 | 53.1 | 1.9 | |
| 024 - 030, *041 | in | 6.4 | 5.0 | 14.0 | 14.0 | 5.8 | 2.0 | 18.5 | 19.3 | 0.9 | |
| | cm | 16.3 | 12.7 | 35.6 | 35.6 | 14.7 | 5.1 | 47.0 | 49.0 | 2.3 | |
| 036 - 042 | in | 6.4 | 3.8 | 14.0 | 14.0 | 5.1 | 2.3 | 22.8 | 23.9 | 0.7 | |
| | cm | 16.1 | 9.5 | 35.6 | 35.6 | 13.1 | 5.8 | 57.9 | 60.7 | 1.9 | |
| 048 - 060 | in | 6.9 | 7.3 | 16.0 | 18.0 | 5.1 | 2.3 | 29.3 | 22.5 | 0.7 | |
| | cm | 17.4 | 18.4 | 40.6 | 45.7 | 13.1 | 5.8 | 74.4 | 57.0 | 1.9 | |

*Size 041 units have unique M, N, Q dimensions due to the position of the blower assembly.

Front Return - N = 4.8 in (12.2 cm), Q = 6.4 in (16.3 cm).

Right Return - N = 3.8 in (9.7 cm), Q = 5.5 in (14.0 cm).

Left Return - M = 6.4 in (16.3 cm), N = 2.8 in (7.1 cm).



Units shipped with filter rails. These rails should be removed for return duct connection. See Aff---- for accessory air filter frame with duct collar.

Corner Weights for TCH Series Units

| Model | | Total | Left-Front* | Right-Front* | Left-Back* | Right-Back* |
|---------|------|-------|-------------|--------------|------------|-------------|
| TCH006 | Lbs | 103 | 37 | 24 | 23 | 19 |
| TCHUU | kg | 46.72 | 16.78 | 10.89 | 10.43 | 8.62 |
| ТСН009 | Lbs | 105 | 38 | 24 | 23 | 20 |
| 101009 | kg | 47.63 | 17.24 | 10.89 | 10.43 | 9.07 |
| TCH012 | Lbs | 114 | 42 | 26 | 25 | 21 |
| TCHUIZ | kg | 51.71 | 19.05 | 11.79 | 11.34 | 9.53 |
| TCH015 | Lbs | 153 | 53 | 36 | 34 | 30 |
| TCHUIS | kg | 69 | 24 | 16 | 15 | 14 |
| TCH018 | Lbs | 158 | 55 | 37 | 35 | 31 |
| TCHOID | kg | 72 | 25 | 17 | 16 | 14 |
| TCH024 | Lbs | 174 | 62 | 40 | 39 | 33 |
| 101024 | kg | 79 | 28 | 18 | 18 | 15 |
| ТСН030 | Lbs | 182 | 67 | 41 | 40 | 34 |
| TCH050 | kg | 83 | 30 | 19 | 18 | 15 |
| TCH036 | Lbs | 203 | 75 | 47 | 44 | 37 |
| 101030 | kg | 92 | 34 | 21 | 20 | 17 |
| TCH042 | Lbs | 218 | 81 | 50 | 48 | 39 |
| 1011042 | kg | 99 | 37 | 23 | 22 | 18 |
| TCH048 | Lbs. | 263 | 98 | 60 | 58 | 47 |
| 101040 | kg | 119 | 44 | 27 | 26 | 21 |
| ТСН060 | Lbs. | 278 | 94 | 59 | 56 | 69 |
| 101060 | kg | 126 | 43 | 27 | 25 | 31 |

*Front is control box end.

Electrical Data – Standard Unit

| Model | Voltage | Rated | Voltage Min/ Max | Co | mpres | sor | Fan Motor | Total | Min Circuit | Max Fuse/ |
|-------|---------|--------------|------------------------|-----|-------|-------|--------------|-------------|----------------|--------------|
| woder | Code | Voltage | | QTY | RLA | LRA | FLA | Unit FLA | Amp | HACR |
| 006 | G | 208-230/60/1 | 197/254 | 1 | 3.3 | 17.7 | 0.40 | 3.7 | 4.5 | 15 |
| 000 | E | 265/60/1 | 239/292 | 1 | 2.9 | 13.5 | 0.40 | 3.3 | 4.0 | 15 |
| 009 | G | 208-230/60/1 | 197/254 | 1 | 4.5 | 22.2 | 0.92 | 5.4 | 6.5 | 15 |
| 009 | E | 265/60/1 | 239/292 | 1 | 3.8 | 18.8 | 0.70 | 4.5 | 5.5 | 15 |
| 012 | G | 208-230/60/1 | 197/254 | 1 | 5.1 | 32.5 | 0.92 | 6.0 | 7.3 | 15 |
| 012 | E | 265/60/1 | 239/292 | 1 | 4.0 | 31.5 | 0.70 | 4.7 | 5.7 | 15 |
| 015 | G | 208-230/60/1 | 197/254 | 1 | 6.0 | 29.0 | 1.20 | 7.2 | 8.7 | 15 |
| 015 | Е | 265/60/1 | 239/292 | 1 | 5.4 | 28.0 | 0.86 | 6.8 | 8.2 | 15 |
| 018 | G | 208-230/60/1 | 197/254 | 1 | 7.2 | 33.0 | 1.20 | 8.4 | 10.2 | 15 |
| 010 | E | 265/60/1 | 239/292 | 1 | 5.9 | 28.0 | 0.86 | 6.8 | 8.2 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 12.8 | 58.3 | 1.50 | 14.3 | 17.5 | 30 |
| 024 | E | 265/60/1 | 239/292 | 1 | 9.6 | 54.0 | 1.30 | 10.9 | 13.3 | 20 |
| 024 | Н | 208-230/60/3 | 197/254 | 1 | 7.7 | 55.4 | 1.50 | 9.2 | 11.1 | 15 |
| | F | 460/60/3 | 414/506 | 1 | 3.6 | 28.0 | 0.76 | 4.4 | 5.3 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 14.1 | 73.0 | 3.00 | 17.1 | 20.6 | 30 |
| 030 | E | 265/60/1 | 239/292 | 1 | 11.2 | 60.0 | 2.70 | 13.9 | 16.7 | 25 |
| 030 | Н | 208-230/60/3 | 197/254 | 1 | 8.9 | 58.0 | 3.00 | 11.9 | 14.1 | 20 |
| | F | 460/60/3 | 414/506 | 1 | 4.2 | 28.0 | 1.70 | 5.9 | 7.0 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 16.7 | 79.0 | 1.80 | 18.5 | 22.7 | 35 |
| 036 | E | 265/60/1 | 239/292 | 1 | 13.5 | 72.0 | 2.00 | 15.5 | 18.9 | 30 |
| 036 | Н | 208-230/60/3 | 197/254 | 1 | 10.4 | 73.0 | 1.80 | 12.2 | 14.8 | 25 |
| | F | 460/60/3 | 414/506 | 1 | 5.8 | 38.0 | 1.24 | 7.0 | 8.5 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 17.9 | 112.0 | 3.00 | 20.9 | 25.4 | 40 |
| 041 | Н | 208-230/60/3 | 197/254 | 1 | 13.2 | 88.0 | 3.00 | 16.2 | 19.5 | 30 |
| 041 | F | 460/60/3 | 414/506 | 1 | 6.0 | 44.0 | 1.70 | 7.7 | 9.2 | 15 |
| | Ν | 575/60/3 | 518/633 | 1 | 4.2 | 30.0 | 1.40 | 5.6 | 6.7 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 17.9 | 112.0 | 3.00 | 20.9 | 25.4 | 40 |
| 042 | Н | 208-230/60/3 | 197/254 | 1 | 13.5 | 88.0 | 3.00 | 16.5 | 19.9 | 30 |
| 042 | F | 460/60/3 | 414/506 | 1 | 6.0 | 44.0 | 1.70 | 7.7 | 9.2 | 15 |
| | Ν | 575/60/3 | 518/633 | 1 | 4.9 | 34.0 | 1.40 | 6.3 | 7.5 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 21.8 | 117.0 | 3.40 | 25.2 | 30.7 | 50 |
| 048 | Н | 208-230/60/3 | 197/254 | 1 | 13.7 | 83.1 | 3.40 | 17.1 | 20.5 | 30 |
| 040 | F | 460/60/3 | 414/506 | 1 | 6.2 | 41.0 | 1.80 | 8.0 | 9.6 | 15 |
| | N | 575/60/3 | 518/633 | 1 | 4.8 | 33.0 | 1.40 | 6.2 | 7.4 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 26.3 | 134.0 | 4.90 | 31.2 | 37.8 | 60 |
| 060 | Н | 208-230/60/3 | 197/254 | 1 | 15.6 | 110.0 | 4.90 | 20.5 | 24.4 | 40 |
| 060 | F | 460/60/3 | 414/506 | 1 | 7.8 | 52.0 | 2.50 | 10.3 | 12.3 | 20 |
| | N | 575/60/3 | 518/633 | 1 | 5.8 | 38.9 | 1.90 | 7.7 | 9.2 | 15 |

HACR circuit breaker in USA only All fuses Class RK-5

Electrical Data – High Static Blower


| тс | Voltage | Rated | Voltage | Compressor | | | Fan | Total | Min | Max |
|-------|---------|--------------|---------|------------|------|-------|--------------|-------------|----------------|---------------|
| Model | Code | Voltage | Min/Max | QTY | RLA | LRA | Motor FLA | Unit FLA | Circuit Amp | Fuse/ HACR |
| 015 | G | 208-230/60/1 | 197/254 | 1 | 6.0 | 29.0 | 1.20 | 7.2 | 8.7 | 15 |
| | E | 265/60/1 | 239/292 | 1 | 5.4 | 28.0 | 0.86 | 6.3 | 7.6 | 15 |
| 018 | G | 208-230/60/1 | 197/254 | 1 | 7.2 | 33.0 | 1.50 | 8.7 | 10.5 | 15 |
| 010 | E | 265/60/1 | 239/292 | 1 | 5.9 | 28.0 | 1.30 | 7.2 | 8.7 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 12.8 | 58.3 | 1.50 | 14.3 | 17.5 | 30 |
| 024 | E | 265/60/1 | 239/292 | 1 | 9.6 | 54.0 | 1.30 | 10.9 | 13.3 | 20 |
| 024 | н | 208-230/60/3 | 197/254 | 1 | 7.7 | 55.4 | 1.50 | 9.2 | 11.1 | 15 |
| | F | 460/60/3 | 414/506 | 1 | 3.6 | 28.0 | 0.76 | 4.4 | 5.3 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 14.1 | 73.0 | 3.00 | 17.1 | 20.6 | 30 |
| 030 | E | 265/60/1 | 239/292 | 1 | 11.2 | 60.0 | 2.70 | 13.9 | 16.7 | 25 |
| 030 | н | 208-230/60/3 | 197/254 | 1 | 8.9 | 58.0 | 3.00 | 11.9 | 14.1 | 20 |
| | F | 460/60/3 | 414/506 | 1 | 4.2 | 28.0 | 1.70 | 5.9 | 7.0 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 16.7 | 79.0 | 3.00 | 19.7 | 23.9 | 40 |
| 000 | E | 265/60/1 | 239/292 | 1 | 13.5 | 72.0 | 2.70 | 16.2 | 19.6 | 30 |
| 036 | н | 208-230/60/3 | 197/254 | 1 | 10.4 | 73.0 | 3.00 | 13.4 | 16.0 | 25 |
| | F | 460/60/3 | 414/506 | 1 | 5.8 | 38.0 | 1.70 | 7.5 | 9.0 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 17.9 | 112.0 | 3.00 | 20.9 | 25.4 | 40 |
| 042 | н | 208-230/60/3 | 197/254 | 1 | 13.5 | 88.0 | 3.00 | 16.5 | 19.9 | 30 |
| 042 | F | 460/60/3 | 414/506 | 1 | 6.0 | 44.0 | 1.70 | 7.7 | 9.2 | 15 |
| | N | 575/60/3 | 518/633 | 1 | 4.9 | 34.0 | 1.40 | 6.3 | 7.5 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 21.8 | 117.0 | 4.90 | 26.7 | 32.2 | 50 |
| 0.40 | н | 208-230/60/3 | 197/254 | 1 | 13.7 | 83.1 | 4.90 | 18.6 | 22.0 | 35 |
| 048 | F | 460/60/3 | 414/506 | 1 | 6.2 | 41.0 | 2.50 | 8.7 | 10.3 | 15 |
| | N | 575/60/3 | 518/633 | 1 | 4.8 | 33.0 | 1.90 | 6.7 | 7.9 | 15 |
| | G | 208-230/60/1 | 197/254 | 1 | 26.3 | 134.0 | 5.80 | 32.1 | 38.7 | 60 |
| 060 | н | 208-230/60/3 | 197/254 | 1 | 15.6 | 110.0 | 5.80 | 21.4 | 25.3 | 40 |
| 060 | F | 460/60/3 | 414/506 | 1 | 7.8 | 52.0 | 2.60 | 10.4 | 12.4 | 20 |
| | N | 575/60/3 | 518/633 | 1 | 5.8 | 38.9 | 2.30 | 8.1 | 9.6 | 15 |

HACR circuit breaker in USA only All fuses Class RK-5

TC Series Wiring Diagram Matrix

| Model | Wiring Diagram Part Number | Electrical | Control | DDC | Agency |
|---------------------|-------------------------------|--------------------|---------|-----|--------|
| | 96B0006N01 | | | - | ETL |
| | 96B0006N03 | | СХМ | LON | ETL |
| TC Series Single | 96B0006N09 | 208-230/60/1, | | MPC | ETL |
| Phase | 96B0006N02 | 265/60/1 | | - | ETL |
| | 96B0006N04 | | DXM | LON | ETL |
| | 96B0006N10 | | | MPC | ETL |
| | 96B0007N01 | | | - | ETL |
| TC Series | 96B0007N03 | | СХМ | LON | ETL |
| Three Phase | 96B0007N06 | 208-230/60/3 | | MPC | ETL |
| (230V | 96B0007N02 | 206-230/00/3 | DXM | - | ETL |
| Style) | 96B0007N04 | | | LON | ETL |
| | 96B0007N07 | | | MPC | ETL |
| | 96B0008N01 | | | - | ETL |
| TC Series | 96B0008N03 | | СХМ | LON | ETL |
| Three Phase | 96B0008N08 | 460/60/3, 575/60/3 | | MPC | ETL |
| (460V | 96B0008N02 | 400/00/3, 575/00/3 | | - | ETL |
| Style) | 96B0008N04 | | DXM | LON | ETL |
| | 96B0008N09 | | | MPC | ETL |

Typical Wiring Diagram – Single Phase TC Units with CXM Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

LC405 - 35

of

Q Ø 96B0006N02 COMPONENT SIZES: 006 . . TE WIRING 208/230V BRN BLU ų ALTERNAT SIZE 60: 2 WATER Ę Ē Ð Σ ٦ * 0 20 BLK THA В YEL Þ ЯĞ HOT WATER GENERATOR* POWER SUPPLY USE OPPER CONDUCTORS ONLY SEE NOTES 2 AND STATUS LED (G Stow Flash = 1 Slow Flash = 1 Fault LED (RE CYCLES APROM ALARM RELAY C 0 BRN (265V) į 1 D 230V AL2. RED 208V) POWER SUPPLY REFER TO DATA PLATE USE COPPER CONDUCTORS ONLY. ALI AND JUMPER. SEE NOTE 3 TRANS THE TWO DESIRED SPEED FPI THERNISTER PROVIDES LOW TEMPERATURE FROTECTION FOR WATER. WHEN USING ANTI-FREEZE SOLUTIONS, CUT JW3. REFER TO PMC, LON, OR TSTAT INSTALLEND, APPLICATION, AND OFENATION MANULL FOR CONTROL WIRING TO THE UNIT. TO THE STATI TO THE TOTAL APPLICATION, AND OFENATION MANULL FOR CONTROL WIRING TO THE UNIT. TOTAL TO THE WIRING WORT BE "CLASSI" I FOR DOWLARE FE EQUAL OR GRAFTER THAN UNIT SUPPLY VOLTAGE. LOW VOLTAGE WIRING WORT BE "CLASSI" I FOR UND VOLTAGE FEE EQUAL OR GRAFTER THAN UNIT SUPPLY VOLTAGE. 24V ALARM SIGNAL SHOWN. FOR DRY ALARM CONTACT, CUT JW4 JUMPER AND DRY CONTACT WILL BE AVAILABLE BETWEEN ິສ (Ч BLOWER MOTOR IS FACTORY WIRED FOR MEDIUM AND HICH SPEEDS. FOR ANY OTHER COMBINITION OF SPEEDS AT THE MOTOR ATTACH BLACK WIRE TO THE HIORER OF THE TWO DESIRED SPEED TARS, AND THE BLUE WIRE TO THE LOWER TRANSFORMER SECONDARY GROUND VIA GRN/YEL WIRE TO CONTROL BOX FROM "C" TERMINAL. ° └╵ ┝╴╴ AQUA STAT IS SUPPLIED WITH UNIT AND MUST BE WIRED IN SERIES WITH THE HOT LEG TO THE PUMP. AQUA STAT IS RATED FOR VOLTAGES UP TO 277V. THE REPORT OF ALL AND 7/2/10 # • 2. ALL WIRING TO THE UNIT MUST COMPLY WITH NEC AND LOCAL CODES. IO CAP TUBE BRN-0j 10-0290 COMPRESSOR THERMALLY PROTECTED INTERNALLY. 0 EH2 COMPR AE Sea 24V DC Ŧ FP2 8 ā. 2 Ø H: HI FAN/D Not Used SNO 006-070 208-230/60/1, 265/60/1 & 220-240/50/1 DXM COMMERCIAL DXM MICROPROCESSOR CONTROL LOGIC ≥∃**₹** ACC2 FUNCT ACCI SEE NOTE 4 Low N.O. UPS: DISABLE/ENABLE UPS: DISABLE/ENABLE 31 TSTAT: HEAT COOL/HEAT PUMF 21 VO 18 JKV ON O 21 PEUMPIO/NORMAL 21 BOULENLESS: ENABLL/DISABLE 21 BOULENLESS: 40 TF/50 'F Low < COMI COMI 202 Notes 7MC ۰. τώ DIP SWITCH S S SENSOR, LOW TEMP PRETECTION, WATER COLL SENSOR, LOW TEMP PREDTECTION, WATER COLL HIGH PRESSURE SWITCH 5 HIGH PRESSURE WATER SWITCH 5 HIGH (LEAVING) WATER TEMP SWITCH COMPRESSOR CONTACTOR CRANKCASE HEATER SENSOR, CONDENSATE OVERFLOW ALARM RELAY CLIPPABEL FIELD SELECTION JUMPER LOSS OF CHARGE PRESSURE SWITCH MOTORIZED VALVE MOTORIZED VALVE END SWITCH FIELD WIRING TERMINAL BLOCK REVERSING VALVE SOLENDID SLOWER MOTOR CAPACITOR 1 RELAY CONTACTS FER RELAY ER MOTOR ALI 8 P2 AL2 , B ₽Ş Ò BREAKER SEE -ALARM BLOWE COMPONENT LOCATION #□□ SEE NOTE \Box 000 000 0000 (*<u>₹</u>) FIELD LINE VOLTAGE WIRING FIELD LOW VOLTAGE WIRING PRINTED CIRCUIT TRACE OPTIONAL WIRING RELAY / CONTACTOR COIL Ш TEMPERATURE SWITCH Solenoid Coil Relay contacts - N.O. COMPRESSOR ・ OPTIONAL シーク SOLENDID CUL アレクト RELAY CONTACTS - N. クーク TENPERATTURE SWITT クーレ STROPG-LOWING GROUND の WIE NUT MIRE NUT CIRCUIT BREAKER CONDENSATE PAN COOLING EAN 24 VAC COMMON TYPICAL HEAT PUMP T-STAT SEE NOTE 5 CONTAC THERMISTOR ø 6 60 LED H Ś LEGEND ĵ∰∭(¦∅


Typical Wiring Diagram – Single Phase TC Units with DXM Controller

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMastetrs ophinon or commendation of its products. The latest version of this document is available at **climatemaster.com**.

LC405 - 36


of

Typical Wiring Diagram – Three Phase 208/230V TC Units with CXM Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.


Typical Wiring Diagram – Three Phase 208/230V TC Units with DXM Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and on to form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.


LC405 - 38

Typical Wiring Diagram – Three Phase 460/575V TC Units with CXM Controller




ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Typical Wiring Diagram – Three Phase 460/575V TC Units with DXM Controller




ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's Opinion or dis products. The latest version of this document is available at **climatemaster.cm**.

Typical Wiring Diagram – Three Phase 460/575V TC Units with CXM And LON Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.


Typical Wiring Diagram - Three Phase 460/575V TC Units with DXM & LON Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's ophion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

LC405 - 42


Typical Wiring Diagram – Three Phase 460/575V TC Units with CXM & MPC Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

of _

Typical Wiring Diagram – Three Phase 460/575V TC Units with DXM & MPC Controller



ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 1

General:

Furnish and install ClimateMaster Tranquility[®] "TC" Water Source Heat Pumps, as indicated on the plans. Equipment shall be completely assembled, piped and internally wired. Capacities and characteristics as listed in the schedule and the specifications that follow.

Units shall be supplied completely factory built capable of operating over an entering water temperature range from 20° to 120°F (-6.7° to 48.9°C) as standard. Equivalent units from other manufacturers may be proposed provided approval to bid is given 10 days prior to bid closing. All equipment listed in this section must be rated and <u>certified</u> in accordance with Air-Conditioning, Heating and Refrigeration Institute/International Standards Organization (AHRI/ISO 13256-1). All equipment must be tested, investigated, and determined to comply with the requirements of the standards for Heating and Cooling Equipment UL-1995 for the United States and CAN/CSA-C22.2 NO.236 for Canada, by Intertek Testing Laboratories (ETL). The units shall have AHRI/ISO and ETL-US-C labels.

All units shall be fully quality tested by factory run testing under normal operating conditions as described herein. Quality control system shall automatically perform via computer: triple leak check, pressure tests, evacuation and accurately charge system, perform detailed heating and cooling mode tests, and quality cross check all operational and test conditions to pass/fail criteria. Detailed report card will ship with each unit displaying status for critical tests and components. **Note: If unit fails on any cross check, it shall not be allowed to ship. Serial numbers will be recorded by factory and furnished to contractor on report card for ease of unit warranty status. Units tested without water flow are not acceptable.**

Basic Construction:

Horizontal units shall have one of the following air flow arrangements: Left Inlet/Straight (Right) Discharge; Right Inlet/Straight (Left) Discharge; Left Inlet/Back Discharge; or Right Inlet/Back Discharge as shown on the plans. Units must have the ability to be field convertible from straight to back or back to straight discharge with no additional parts or unit structure modification. Horizontal units will have factory installed hanger brackets with rubber isolation grommets packaged separately.

Vertical units shall have one of the following airflow arrangements: Left Return/Top Discharge, Right Return/Top Discharge, as shown on the plans.

If units with these arrangements are not used, the contractor is responsible for any extra costs incurred by other trades. All units (horizontal and vertical) must have a minimum of two access panels for serviceability of compressor compartment. Units having only one access panel to compressor/heat exchangers/expansion device/refrigerant piping shall not be acceptable.

All interior surfaces shall be lined with 1/2 inch (12.7mm) thick, 1-1/2 lb/ft3 (24 kg/m3) acoustic type glass fiber insulation. Insulation placement shall be designed in a manner that will eliminate any exposed edges to prevent the introduction of glass fibers into the air stream.

The heat pumps shall be fabricated from heavy gauge galvanized steel with powder coat paint finish on the front access panels.

Standard cabinet panel insulation must meet NFPA 90A requirements, air erosion and mold growth limits of UL-181, stringent fungal resistance test per ASTM-C1071 and ASTM G21, and shall meet zero level bacteria growth per ASTM G22. **Unit insulation must meet these stringent requirements or unit(s) will not be accepted.**

All horizontal units to have factory installed 1" (25.4mm) discharge air duct collars, 1" (25.4mm) filter rails with 1" (25.4mm) filters factory installed, and factory installed unit-mounting brackets. Vertical units to have field installed discharge air duct collar, shipped loose and 1" (25.4mm) filter rails with 1" (25.4mm) filters factory installed. If units with these factory installed provisions are not used, the contractor is responsible for any extra costs to field install these provisions, and/or the extra costs for his sub-contractor to install these provisions.

All units must have an insulated panel separating the fan compartment from the compressor compartment. Units with the compressor in the air stream are not acceptable. Units shall have factory installed 1 inch (25.4mm) wide filter rails for filter removal from either side. Units shall have a 1 inch (25.4mm) thick throwaway type glass fiber filter. The contractor shall purchase one spare set of filters and replace factory shipped filters on completion of start-up. Filters shall be standard sizes. If units utilize non-standard filter sizes then the contractor shall provide 12 spare filters for each unit.

Cabinets shall have separate holes and knockouts for entrance of line voltage and low voltage control wiring. All factory-installed wiring passing through factory knockouts and openings shall be protected from sheet metal edges at openings by plastic ferrules. Supply and return water connections shall be copper FPT fittings. All water connections and electrical knockouts must be in the compressor compartment corner post as to not interfere with the serviceability of unit. Contractor shall be responsible for any extra costs involved in the installation of units that do not have this feature. Contractor must ensure that units can be easily removed for servicing and coordinate locations of electrical conduit and lights with the electrical contractor.

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's ophion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 2

Option: Contractor shall install 2-inch (50.8mm) filter frame with removable access door and 2 inch (50.8mm) Glass Fiber throwaway filters on all units.

Option: The unit shall be supplied with extended range insulation option, which adds closed cell insulation to internal water lines, and provides insulation on suction side refrigeration tubing including refrigerant to water heat exchanger.

Fan and Motor Assembly:

Blower shall have inlet rings to allow removal of wheel and motor from one side without removing housing. Units shall have a direct-drive centrifugal fan. The fan motor shall be 3-speed (2-speed for 575V), permanently lubricated, PSC type, with internal thermal overload protection. Units supplied without permanently lubricated motors must provide external oilers for easy service. The fan motor on small and medium size units (006-042) shall be isolated from the fan housing by a torsionally flexible motor mounting system with rubber type grommets to inhibit vibration induced high noise levels associated with "hard wire belly band" motor mounting. The fan motor on larger units (048 & 060) shall be isolated with flexible rubber type isolation grommets only. The fan and motor assembly must be capable of overcoming the external static pressures as shown on the schedule. Airflow/Static pressure rating of the unit shall be based on a wet coil and a clean filter in place.

Option: High static motors (015-060)

Refrigerant Circuit:

All units shall contain an EarthPure[®] (HFC-410A) sealed refrigerant circuit including a high efficiency scroll or rotary compressor designed for heat pump operation, a thermostatic expansion valve for refrigerant metering, an enhanced corrugated aluminum lanced fin and rifled copper tube refrigerant to air heat exchanger, reversing valve, coaxial (tube in tube) refrigerant to water heat exchanger, and safety controls including a high pressure switch, low pressure (loss of charge) switch, water coil low temperature sensor, and air coil low temperature sensor. Access fittings shall be factory installed on high and low pressure refrigerant lines to facilitate field service. Activation of any safety device shall prevent compressor operation via a microprocessor lockout circuit. The lockout circuit shall be reset at the thermostat or at the contractor supplied disconnect switch. **Units that cannot be reset at the thermostat shall not be acceptable.**

Hermetic compressors shall be internally sprung. The compressor shall have a dual level vibration isolation system. The compressor will be mounted on specially engineered sound-tested EPDM vibration isolation grommets or springs to a large heavy gauge compressor mounting plate, which is then isolated from the cabinet base with rubber grommets for maximized vibration attenuation. Compressor shall have thermal overload protection. Compressor shall be located in an insulated compartment away from air stream to minimize sound transmission.

Refrigerant to air heat exchangers shall utilize enhanced corrugated lanced aluminum fins and rifled copper tube construction rated to withstand 625 PSIG (4309 kPa) refrigerant working pressure. Refrigerant to water heat exchangers shall be of copper inner water tube and steel refrigerant outer tube design, rated to withstand 625 PSIG (4309 kPa) working refrigerant pressure and 500 PSIG (3445 kPa) working water pressure. The refrigerant to water heat exchanger shall be "electro-coated" with a low cure cathodic epoxy material a minimum of 0.4 mils thick (0.4 – 1.5 mils range) on all surfaces. The black colored coating shall provide a minimum of 1000 hours salt spray protection per ASTM B117-97 on all external steel and copper tubing. The material shall be formulated without the inclusion of any heavy metals and shall exhibit a pencil hardness of 2H (ASTM D3363-92A), crosshatch adhesion of 4B-5B (ASTM D3359-95), and impact resistance of 160 in-lbs (184 kg-cm) direct (ASTM D2794-93).

Refrigerant metering shall be accomplished by thermostatic expansion valve only. Expansion valves shall be dual port balanced type with external equalizer for optimum refrigerant metering. Units shall be designed and tested for operating ranges of entering water temperatures from 20° to 120°F (-6.7° to 48.9°C). Reversing valve shall be four-way solenoid activated refrigerant valve, which shall default to heating mode should the solenoid fail to function. If the reversing valve solenoid defaults to cooling mode, an additional low temperature thermostat must be provided to prevent over-cooling an already cold room.

Option: The unit will be supplied with cupro-nickel coaxial water to refrigerant heat exchanger.

Option: The refrigerant to air heat exchanger shall be coated.

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's option or commendation of its products. The latest version of this document is available at **climatemaster.com**.

<u>Option: UltraQuiet package shall consist of spring isolation under compressor; discharge muffler (except rotary compressors); and</u> sound attenuating material applied to the fan housing.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 3

Drain Pan:

The drain pan shall be constructed of galvanized steel and have a powder coat paint application to further inhibit corrosion. This corrosion protection system shall meet the stringent 1000 hour salt spray test per ASTM B117. If plastic type material is used, it must be HDPE (High Density Polyethylene) to avoid thermal cycling shock stress failure over the lifetime of the unit. Drain pan shall be fully insulated. Drain outlet shall be located at pan as to allow complete and unobstructed drainage of condensate. Drain outlet for horizontal units shall be connected from pan directly to FPT fitting. No hidden internal tubing extensions from pan outlet extending to unit casing (that can create drainage problems) will be accepted. The unit as standard will be supplied with solid-state electronic condensate overflow protection. Mechanical float switches will NOT be accepted.

Vertical units shall be furnished with a PVC FPT condensate drain connection and an internal factory installed condensate trap. If units without an internal trap are used, the contractor is responsible for any extra costs to field install these provisions, and/or the extra costs for his sub-contractor to install these provisions.

Option: The unit shall be supplied with stainless steel drain pan.

Electrical:

A control box shall be located within the unit compressor compartment and shall contain a 50VA transformer, 24 volt activated, 2 or 3 pole compressor contactor, terminal block for thermostat wiring and solid-state controller for complete unit operation. Reversing valve and fan motor wiring shall be routed through this electronic controller. Units shall be name-plated for use with time delay fuses or HACR circuit breakers. Unit controls shall be 24 Volt and provide heating or cooling as required by the remote thermostat/sensor.

Solid State Control System (CXM):

Units shall have a solid-state control system. **Units utilizing electro-mechanical control shall not be acceptable.** The control system microprocessor board shall be specifically designed to protect against building electrical system noise contamination, EMI, and RFI interference. The control system shall interface with a heat pump type thermostat. The control system shall have the following features:

- a Anti-short cycle time delay on compressor operation.
- b. Random start on power up mode.
- c. Low voltage protection.
- d. High voltage protection.
- e. Unit shutdown on high or low refrigerant pressures.
- f. Unit shutdown on low water temperature.
- g. Condensate overflow electronic protection.
- h. Option to reset unit at thermostat or disconnect.
- i. Automatic intelligent reset. Unit shall automatically reset the unit 5 minutes after trip if the fault has cleared. If a fault occurs 3 times sequentially without thermostat meeting temperature, then lockout requiring manual reset will occur.
- j. Ability to defeat time delays for servicing.
- k. Light emitting diode (LED) on circuit board to indicate high pressure, low pressure, low voltage, high voltage, low water/air temperature cut-out, condensate overflow, and control voltage status.
- I. The low-pressure switch shall not be monitored for the first 120 seconds after a compressor start command to prevent nuisance safety trips.
- m. 24V output to cycle a motorized water valve or other device with compressor contactor.
- n. Unit Performance Sentinel (UPS). The UPS warns when the heat pump is running inefficiently.
- o. Water coil low temperature sensing (selectable for water or anti-freeze).
- p. Air coil low temperature sensing.

NOTE: Units not providing the 8 safety protections of anti-short cycle, low voltage, high voltage, high refrigerant pressure, low pressure (loss of charge), air coil low temperature cut-out, water coil low temperature cut-out, and condensate overflow protections will not be accepted.

Option: Enhanced solid state control system (DXM):

This control system features two stage control of cooling and two stage control of heating modes for exacting temperature and dehumidification purposes.

This control system coupled with a multi-stage thermostat will better dehumidify room air by automatically running the heat pump's fan at lower speed on the first stage of cooling thereby implementing low sensible heat ratio cooling. On the need for higher cooling performance the system will activate the second stage of cooling and automatically switch the fan to the higher fan speed setting. This system may be further enhanced with a humidistat. **Units not having automatic low sensible heat ratio cooling will not be accepted; as an alternate a hot gas reheat coil may be provided with control system for automatic activation.**

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's ophion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 4

Control shall have all of the above mentioned features of the CXM control system along with the following expanded features:

- a. Removable thermostat connector.
- b. Night setback control.
- c. Random start on return from night setback.
- d. Minimized reversing value operation (Unit control logic shall only switch the reversing value when cooling is demanded for the first time. The reversing value shall be held in this position until the first call for heating, ensuring quiet operation and increased value life.).
- e. Override temperature control with 2-hour timer for room occupant to override setback temperature at the thermostat.
- f. Dry contact night setback output for digital night setback thermostats.
- g. Ability to work with heat pump or heat/cool (Y, W) type thermostats.
- h. Ability to work with heat pump thermostats using O or B reversing valve control.
- i. Emergency shutdown contacts.
- j. Boilerless system heat control at low loop water temperature.
- k. Ability to allow up to 3 units to be controlled by one thermostat.
- I. Relay to operate an external damper.
- m. Ability to automatically change fan speed from multistage thermostat.
- n. Relay to start system pump.
- o. 75 VA control transformer. Control transformer shall have load side short circuit and overload protection via a built in circuit breaker.

Digital Night Setback with Pump Restart (DXM w/ ATP32U03/04)

The unit will be provided with a Digital Night Setback feature using an accessory relay on the DXM controller with an ATP32U03/04 thermostat and an external, field-provided time clock. The external time clock will initiate and terminate the night setback period. The thermostat will have a night setback override feature with a programmable override time period.

An additional accessory relay on the unit DXM controller will energize the building loop pump control for the duration of the override period. (Note: this feature requires additional low voltage wiring. Consult Application Drawings for details.)

Remote Service Sentinel (CXM/DXM)

Solid state control system shall communicate with thermostat to display (at the thermostat) the unit status, fault status, and specific fault condition, as well as retrieve previously stored fault that caused unit shutdown. The Remote Service Sentinel allows building maintenance personnel or service personnel to diagnose unit from the wall thermostat. The control board shall provide a signal to the thermostat fault light, indicating a lockout. Upon cycling the G (fan) input 3 times within a 60 second time period, the fault light shall display the specific code as indicated by a sequence of flashes. A detailed flashing code shall be provided at the thermostat LED to display unit status and specific fault status such as over/under voltage fault, high pressure fault, low pressure fault, low water temperature fault, condensate overflow fault, etc. **Units that do not provide this remote service sentinel shall not be acceptable.**

Option: Lonworks interface system

Units shall have all the features listed above (either CXM or DXM) and the control board will be supplied with a LONWORKS interface board, which is LONMark certified. This will permit all units to be daisy chained via a 2-wire twisted pair shielded cable. The following points must be available at a central or remote computer location:

- a. Space temperature
- b. Leaving water temperature
- c. Discharge air temperature
- d. Command of space temperature setpoint
- e. Cooling status
- f. Heating status
- g. Low temperature sensor alarm
- h. Low pressure sensor alarm
- i. High pressure switch alarm
- j. Condensate sensor alarm
- k. Hi/low voltage alarm
- I. Fan "ON/AUTO" position of space thermostat as specified above
- m. Unoccupied/occupied command
- n. Cooling command
- o. Heating command
- p. Fan "ON/AUTO" command
- q. Fault reset command
- r. Itemized fault code revealing reason for specific shutdown fault (any one of 7)

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 5

This option also provides the upgraded 75VA control transformer with load side short circuit and overload protection via a built in circuit breaker.

Option: MPC (Multiple Protocol Control) interface system

Units shall have all the features listed above (either CXM or DXM) and the control board will be supplied with a Multiple Protocol interface board. Available protocols are BACnet MS/TP, Modbus, or Johnson Controls N2. The choice of protocol shall be field selectable/changeable via the use of a simple selector switch. **Protocol selection shall not require any additional programming or special external hardware or software tools.** This will permit all units to be daisy chain connected by a 2-wire twisted pair shielded cable. The following points must be available at a central or remote computer location:

- a. Space temperature
- b. Leaving water temperature
- c. Discharge air temperature
- d. Command of space temperature setpoint
- e. Cooling status
- f. Heating status
- g. Low temperature sensor alarm
- h. Low pressure sensor alarm
- i. High pressure switch alarm
- j. Condensate overflow alarm
- k. Hi/low voltage alarm
- I. Fan "ON/AUTO" position of space thermostat as specified above
- m. Unoccupied/occupied command
- n. Cooling command
- o. Heating command
- p. Fan "ON/AUTO" command
- q. Fault reset command
- r. Itemized fault code revealing reason for specific shutdown fault (any one of 7)

This option also provides the upgraded 75VA control transformer with load side short circuit and overload protection via a built in circuit breaker.

Warranty:

ClimateMaster shall warranty equipment for a period of 12 months from start up or 18 months from shipping (which ever occurs first).

Option: Extended 4-year compressor warranty covers compressor for a total of 5 years.

Option: Extended 4-year refrigeration circuit warranty covers coils, reversing valve, expansion valve and compressor for a total of 5 years.

Option: Extended 4-year control board warranty covers the CXM/DXM control board for a total of 5 years.

FIELD INSTALLED OPTIONS

Hose Kits:

All units shall be connected with hoses. The hoses shall be 2 feet (61cm) long, braided stainless steel; fire rated hoses complete with adapters. Only fire rated hoses will be accepted.

Valves:

The following valves are available and will be shipped loose:

- a. Ball valve; bronze material, standard port full flow design, FPT connections.
- b. Ball valve with memory stop and PT port.
- c. "Y" strainer with blowdown valve; bronze material, FPT connections.
- d. Motorized water valve; slow acting, 24v, FPT connections.

Hose Kit Assemblies:

The following assemblies ship with the valves already assembled to the hose described:

- a. Supply and return hoses having ball valve with PT port.
- b. Supply hose having ball valve with PT port; return hose having automatic flow regulator valve with PT ports, and ball valve.
- c. Supply hose having "Y" strainer with blowdown valve, and ball valve with PT port; return hose having automatic flow regulator with PT ports, and ball valve.
- d. Supply hose having "Y" strainer with blowdown valve, and ball valve with PT port; return hose having ball valve with PT port.

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's ophion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 6

Thermostats:

The thermostat shall be a ClimateMaster mechanical or electronic type thermostat as selected below with the described features: a. <u>Single Stage Standard Manual Changeover (ATM11C11)</u>

Thermostat shall be a single-stage, horizontal mount, manual changeover with HEAT-OFF-COOL system switch and fan ON-AUTO switch. Thermostat shall have a mechanical temperature setpoint indicator. Thermostat shall only require 4 wires for connection. Mercury bulb thermostats are not acceptable.

b. Single Stage Digital Auto or Manual Changeover (ATA11U01)

Thermostat shall be a single-stage, digital, auto or manual changeover with HEAT-OFF-COOL-AUTO system switch and fan ON-AUTO switch. Thermostat shall have an LCD display with temperature and setpoint(s) in °F or °C. The Thermostat shall provide permanent memory of setpoint(s) without batteries. A fault LED shall be provided to display specific fault condition. Thermostat shall provide temperature display offset for custom applications.

- c. <u>Single Stage Digital Automatic or Manual Changeover with Two-Speed Fan Control (ATA11C04) DXM and PSC Fan required</u> Thermostat shall be a single-stage, digital, auto or manual changeover with HEAT-OFF-COOL-AUTO system switch, fan ON-AUTO switch, and fan LO-HI switch. Thermostat shall have an LCD display with temperature and setpoint(s) in °F or °C. A fault LED shall be provided to display specific fault condition. Thermostat shall allow use of an accessory remote temperature sensor (AST009), but may be operated with internal sensor via orientation of a jumper.
- d. Multistage Digital Automatic Changeover (ATA22U01)

Thermostat shall be multi-stage (2H/2C), manual or automatic changeover with HEAT-OFF-COOL-AUTO-EM HEAT system settings and fan ON-AUTO settings. Thermostat shall have an LCD display with temperature, setpoint(s), mode, and status indication. The temperature indication shall be selectable for °F or °C. The thermostat shall provide permanent memory of setpoint(s) without batteries. A fault LED shall be provided to indicate specific fault condition(s). Thermostat shall provide temperature display offset for custom applications. Thermostat shall allow unit to provide better dehumidification with optional DXM controller by automatically using lower fan speed on stage 1 cooling (higher latent cooling) as main cooling mode, and automatically shifting to high speed fan on stage 2 cooling.

e. Multistage Manual Changeover Programmable 5/2 Day (ATP21U01)

Thermostat shall be 5 day/2 day programmable (with up to 4 setpoints per day), multi-stage (2H/1C), manual changeover with HEAT-OFF-COOL-EM HEAT system settings and fan ON-AUTO settings. Thermostat shall have an LCD display with temperature, setpoint(s), mode, and status indication. The temperature indication shall be selectable for °F or °C. The thermostat shall provide permanent memory of setpoint(s) without batteries. Thermostat shall provide convenient override feature to temporarily change setpoint.

f. Multistage Automatic or Manual Changeover Programmable 7 Day (ATP32U03)

Thermostat shall be 7 day programmable (with up to 4 setpoints per day), multi-stage (3H/2C), automatic or manual changeover with HEAT-OFF-COOL-AUTO-EM HEAT system settings and fan ON-AUTO settings. Thermostat shall have a blue backlit dot matrix LCD display with temperature, setpoints, mode, and status indication. The temperature indication shall be selectable for °F or °C. Time display shall be selectable for 12 or 24-hour clock. Fault identification shall be provided (when used with ClimateMaster CXM or DXM controls) to simplify troubleshooting by providing specific unit fault at the thermostat with red backlit LCD during unit lockout. The thermostat shall provide permanent memory of setpoints without batteries. Thermostat shall provide heating setpoint range limit, cooling setpoint range limit, temperature display offset, keypad lockout, dead-band range setting, and inter-stage differential settings. Thermostat shall provide progressive recovery to anticipate time required to bring space temperature to the next programmed event. Thermostat shall provide an installer setup for configuring options and for setup of servicing contractor name and contact information. Thermostat shall allow the use of an accessory remote and/or outdoor temperature sensor (AST008). Thermostat navigation shall be accomplished via five buttons (up/down/right/left/select) with menu-driven selections for ease of use and programming.

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Tranquility[®] 16 (TC) Series 60Hz Engineering Specifications – Page 7

g. Multistage Automatic or Manual Changeover Programmable 7 Day with Humidity Control (ATP32U04) Thermostat shall be 7 day programmable (with up to 4 setpoints per day), multi-stage (3H/2C), automatic or manual changeover with HEAT-OFF-COOL-AUTO-EM HEAT system settings and fan ON-AUTO settings. Separate dehumidification and humidification setpoints shall be configurable for discreet outputs to a dehumidification option and/or an external humidifier. Installer configuration mode shall allow thermostat dehumidification mode to operate with ClimaDry® reheat or with ECM fan dehumidification mode via settings changes. Thermostat shall have a blue backlit dot matrix LCD display with temperature, relative humidity, setpoints, mode, and status indication. The temperature indication shall be selectable for °F or °C. Time display shall be selectable for 12 or 24 hour clock. Fault identification shall be provided (when used with ClimateMaster CXM or DXM controls) to simplify troubleshooting by providing specific unit fault at the thermostat with red backlit LCD during unit lockout. The thermostat shall provide permanent memory of setpoints without batteries. Thermostat shall provide heating setpoint range limit, cooling setpoint range limit, temperature display offset, keypad lockout, dead-band range setting, and inter-stage differential settings. Thermostat shall provide progressive recovery to anticipate time required to bring space temperature to the next programmed event. Thermostat shall provide an installer setup for configuring options and for setup of servicing contractor name and contact information. Thermostat shall allow the use of an accessory remote and/or outdoor temperature sensor (AST008). Thermostat navigation shall be accomplished via five buttons (up/down/right/ left/select) with menu-driven selections for ease of use and programming.

DDC Sensors:

ClimateMaster wall mounted DDC sensor to monitor room temperature and interfaces with optional interface system described above. Several types as described below:

- a. Sensor only with no display (LON and MPC).
- b. Sensor with override (LON only).
- c. Sensor with setpoint adjustment and override (MPC only).
- d. Sensor with setpoint adjustment and override, LCD display, status/fault indication (LON and MPC).

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.

Revision History

| Date: | Item: | Action: |
|----------|---|---|
| 02/11/13 | Unit Features | Updated |
| 02/06/13 | TCV041 M, N, Q Dimensions page 30 | Updated |
| 02/04/13 | TCV Right Return Electrical Tables | Updated Blower Orientation Miscellaneous Edits |
| 09/27/12 | TCH060 Corner Weights Recommended Minimum Installation Clearances for Vertical Units * | Corrected Added |
| 05/02/12 | Size 041 | ISO Table Updated |
| 04/30/12 | Horizontal Dimensional Data Table | Updated |
| 02/20/12 | Engineering Specifications | Updated |
| 01/23/12 | Size 041 | Added |
| 09/19/11 | Size 024 | Added "H" and "F" Voltage |
| 08/09/11 | Unit Maximum Working Water Pressure | Updated to Reflect New Safeties |
| 08/03/11 | Engineering Specifiations | Added Digital Night Setback with Pump Restart (DXM w/ ATP32U03/04) |
| 06/17/11 | Coated Air Coil Option | Changed Description |
| 04/07/11 | Engineering Specification NOTICE | Updated |
| 02/11/11 | Performance Data Selection Notes | Updated |
| 01/03/11 | Format - All Pages | Updated |
| 09/28/10 | Engineering Specifications | Updated |
| 09/28/10 | Physical Data Table | Updated-Added Coax Volume Data |
| 09/01/10 | 012 'E' Airflow Correction Table | Added/Corrected |
| 07/26/10 | Wiring Diagrams | Updated |
| 07/26/10 | Compressor Mounting Information and Graphics Engineering Specifications | Updated to Reflect Spring/Grommet Change |
| 06/11/10 | Format - All Pages | Updated |
| 06/11/10 | Engineering Specifiations | Updated |
| 04/23/10 | Updated (Page 1) of Engineering Specifications | Paragraph edit to update ARI to AHRI |
| 04/22/10 | LEED [®] , Tranquility [®] 16, EarthPure [®] | Updated format ([®] ™ etc) |
| 09/25/09 | Performance Data Selection Notes | Example Updated |
| 09/09/09 | Engineering Specification - Fan 2 Motor Assembly | Changed 'dry' to 'wet' |
| 09/09/09 | Engineering Specification - Thermostat | Changed ATP32U01, 02 to 03, 04 |
| 09/03/09 | Fan and Motor Assembly Engineering Spec. | Changed 'dry' to 'wet' |
| 09/03/09 | Thermostat Engineering Spec. | Removed ATP11N01, Changed ATP32U01, 02 to 03, 04 |
| 05/27/09 | Stand-Alone and Big Book Submittals | Consolidated |
| 05/06/09 | Dimensional Data Tables | Condensate Column Added to Water Connections Table, Rows Consoli- dated in Cabinet, Knockoutand Discharge Tables |
| 04/14/09 | 006-012 unit data added | |
| 02/25/09 | First Published | |

ClimateMaster works continually to improve its products. As a result, the design and specifications of each product at the time of order may be changed without notice and may not be as described herein. Please contact ClimateMaster's Customer Service Department at 1-405-745-6000 for specific information on the current design and specifications. Statements and other information contained herein are not express warranties and do not form the basis of any bargain between the parties, but are merely ClimateMaster's opinion or commendation of its products. The latest version of this document is available at **climatemaster.com**.