

# 36" Single Speed



**36", 1/2 h.p. Single-Speed Motor  
Cools 2,500 sq. ft.**

- **High Volume 9,600 CFM**
- **32 Gallon Water Capacity**
- **Best Value Unit**

- Lowers temperatures up to 30 degrees F
- Energy efficient 10.8 amps for pump and motor
- 3/4" garden hose connection for longer running
- Durable one-piece, rust-free, leak-proof molded polyethylene housing
- Environmentally friendly efficient and effective resource use
- Cools for a fraction of the cost of air conditioning
- Cools without chemicals or refrigerants
- Long-term dependability—near maintenance-free operation
- Shipped completely assembled—ready to operate out of the box
- UL Listed (electric models) in U.S. and Canada

## 36" One Speed Unit Specification

Speeds	One
Air Delivery CFM	9,600
Total Amps	10.8
Water reservoir	32 gallons
Dimensions	67"h x 62"w x 32"d
Unit weight	195 lbs.
Shipping weight	235 lbs.
Box Size	68"h x 64"w x 33"d
Cooling Capacity	2,500 sq. ft.

**STOCK NUMBER PAC2K361S**

**Port-A-Cool, LLC**

**936-598-5651 • 1-800-695-2942 • FAX 936-598-8901**