



# **Comfortmaker® Variable-Speed Inverter Heat Pumps**







## **Built with strength**

When you choose Comfortmaker<sup>®</sup> heating and cooling equipment, it means your home comfort is backed by superior engineering and quality manufacturing so you can enjoy more important things. Each unit is 100% run tested, and we design our products to give you the best in quality, energy efficiency and reliability. We deliver products that give you the most in home comfort so you can enjoy comfort with confidence.







#### CVH8 SoftSound<sup>®</sup> Deluxe 18 Heat Pump with SmartSense<sup>™</sup> Technology

- Up to 19 SEER cooling efficiency
- Up to 11 HSPF heating efficiency
- Variable-speed compressor for the ultimate in quiet and efficient operation
- Superior summer dehumidification
- High leaving temperatures in the cold months for increased efficiency
- Multi-speed fan motor for even temperatures
- Communicating capability
- 10-year No Hassle Replacement<sup>™</sup> limited warranty
- 10-year parts limited warranty (upon timely registration)


# SOFTSOUND® DELUXE 18

#### WITH SMARTSENSE<sup>™</sup> TECHNOLOGY

The SoftSound<sup>®</sup> Deluxe 18 Heat Pump with SmartSense<sup>™</sup> Technology offers superior heating and cooling comfort. The SmartSense Technology quietly delivers high efficiency heating and cooling, superior humidity control and even comfort levels, all in a smaller package. When it's installed as part of a complete Observer<sup>®</sup> communicating system, your home will operate at optimal comfort levels no matter the temperature outside.

#### Savings

This product is designed for our best energy-saving operation at a cost comparable to a two-stage unit. It can save you money over traditional twostage units with continuous and efficient performance. Operating much like adaptive cruise control, Comfortmaker variable-speed inverter products with SmartSense Technology make many small variations to speed in order to work more efficiently and keep temperatures and humidity in your home steady. When installed as part of an Observer communicating system the heat pump will optimize itself to run at the most efficient level, which can save you money.



#### Steady, Quiet Comfort

Whether it's quiet summer days on the patio or fall evenings under the stars, your comfort will stay uninterrupted with SmartSense Technology. It runs much quieter than traditional twostage units, so your time outside is peaceful. During warmer months it runs at lower, more efficient speeds in between cooling cycles, providing your home with superior humidity control and comfort And during cooler months you'll experience higher leaving air temperatures for a steady, warming comfort—all at a lower sound level than two-stage heat pumps.

#### Easy

The SoftSound Deluxe 18 Heat Pump with SmartSense Technology can be matched with a compatible indoor unit and works with most two-stage units. When installed as part of a complete Observer communicating system with the Observer communicating control



featuring Wi-Fi<sup>®</sup> capability, your home will not only run at optimal levels but you

can also adjust your preferred home temperatures remotely. That means when you come home from vacation, you can change your home temperature from your remote device so that it will be at the perfect comfort level when you walk through the door.

### Efficiency ratings—what do they mean?

#### Seasonal Energy Efficiency Ratio (SEER)

Measures the cooling efficiency of air conditioners and heat pumps during an average cooling season. The higher the SEER, the greater the energy economy.

#### Energy Efficiency Rating (EER)

Measures the cooling efficiency of air conditioners and heat pumps during a set temperature (95° F).

#### Heating Seasonal Performance Factor (HSPF)

Measures the heating efficiency of heat pumps. The higher the HSPF, the greater the efficiency and energy savings potential during heat pump heating.




SEER

#### ENERGY STAR®

A U.S. Environmental Protection Agency program to identify and promote energy-efficient products in order to reduce energy consumption.

**SEER vs. Cooling Cost Savings** 



Percentage based on national averages at 10 SEER; may vary according to efficiency of current unit and installation.

	SOFTSOUND <sup>®</sup> DELUXE		<b>SOFTSOUND</b> <sup>®</sup>
Comfortmaker® Split System Heat Pump Options	CVH8	CCH6	CSH5
Comfort Features			
Summer Dehumidification	Best	Best	Better
Temperature Control	Best	Best	Better
Efficiency			
Cooling SEER	Up to 19	Up to 17.5	Up to 16
Electric Heating HSPF	Up to 11	Up to 9.5	Up to 9
Design Features			
Observer <sup>®</sup> Communicating System compatible (when installed with Observer Wall Control with Wi-Fi <sup>®</sup> )	•	•	•
Compressor Stages	Variable	2	1
Compressor Sound Jacket	•	•	•
Multi-speed Fan Motor	•		
Peace of Mind			
10-Year Parts Limited Warranty	•	•	•
No Hassle Replacement <sup>™</sup> Limited Warranty	10-yr	10-yr	5-yr

Many models are ENERGY STAR® qualified. Ask your contractor for details or visit www.energystar.gov.

Timely registration required for 10 year parts limited warranty. Limited warranty period is 5 years for parts if not registered within 90 days of installation. Jurisdictions where warranty benefits cannot be conditioned on registration will receive the registered limited warranty periods. Please see warranty certificate for further details and restrictions.

All systems tested and listed by the appropriate agencies.



ISO 9001: 2000 Registered



As part of its commitment to quality, International Comfort Products reserves the right to change specifications on its products without notice. Illustrations and photographs in this brochure are only representative. Some product models may vary. Wi-Fi® is a registered trademark of the Wi-Fi Alliance Corporation.

CVH8 Series © 2015 International Comfort Products

#### **Backed by** exceptional warranties

The only No Hassle Replacement<sup>™</sup> limited warranty that you'll find in the industry backs every Comfortmaker SoftSound product. It means comfort with no questions. We'll replace your unit if the compressor or coil fails within the covered period. We give you extra coverage in addition to a 10-year parts and compressor limited warranty.\*



\*To the original owner, Comfortmaker products are covered by a 10-year parts limited warranty upon timely registration. The limited warranty period is 5 years if not registered within 90 days of installation. Jurisdictions where warranty benefits cannot be conditioned on registration will automatically receive a 10-year parts limited warranty. See warranty certificate for complete details.



PO Box 128 Lewisburg, TN 37091 Comfortmaker.com

> Part No. 428-42-5405-00 Printed 06/15