

Foot & Check - Plastic



HARVARD Four in One Plastic Foot Valve

- · Positive sealing spring loaded valve poppet closes against a smooth tapered seat.
- Corrosion resistant nylon body and internals.
- · Self cleaning design for continuous positive sealing.
- · Large screen designed to assure smooth water passage and better suction.
- Tapered screen eliminates pipe joint hang-ups during installation.
- Fits four pipe sizes., 3/4" through 1 1/2".
- Third party certified to NSF/ANSI 372.





Part Number	Size	Ctn Qty	List Price
FV441	3/4" through 1 1/2"	100	\$ 15.54

FV441



FV Series



LC Series



FV SN Series

Brady Plastic Foot & Check Valve Features:

- "Nose Cone" diffuser reduces friction.
- 50% greater water flow.
- Acetal copolymer construction.
- Non-electrolytic, non-corrosive.
- Spring loaded, 316 stainless steel
- BUNA-N seal
- Pressure max: 175 psi
- Temperature max: 180 F
- LC check valve, FPT x FPT
- Third party certified to NSF/ANSI 372.

Part Number	Size	Ctn Qty	List Price			
Brady Foot Valve - Spring Loaded						
FV75	3/4"	12	\$ 25.95			
FV100	1"	30	29.77			
FV125	1-1/4"	32	42.34			
FV150	1-1/2"	21	51.41			
Brady Check Valve- Spring Loaded						
LC75	3/4"	24	22.36			
LC100	1"	24	24.71			
LC125	1-1/4"	24	36.36			
LC150	1-1/2"	12	43.53			
Brady Foot Valve Strainer						
FV75SN	3/4"	50	2.35			
FV100SN	1"	50	3.25			
FV125SN	1-1/4"	50	3.79			
FV150SN	1-1/2"	50	3.65			



In Canada:

www.americangranby.com In the United States: Phone (800) 776-2266 Fax (800) 729-3299 Phone (800) 268-7570 Fax (905) 629-3204

