



Representative drawing only.  
Some models may vary in appearance.



### WARRANTY

Standard warranty or Extended warranty available with product registration.

See warranty document for details or visit [www.marsdelivers.com](http://www.marsdelivers.com)

# CCG Series

## Uncased Upflow/Downflow Coils

### STANDARD SPECIFICATIONS

- Rifled copper tubing, enhanced aluminum fins
- Immersion-tested at 500 psi, then nitrogen-pressurized and sealed
- Right-hand refrigerant and plumbing connections
- Liquid line - 3/8" ODS, suction line - 3/4" ODS on 1-1/2 - 3 ton & 7/8" ODS on 3-1/2 - 5 ton
- Externally mounted flowrator body with Schrader valve for hiss-testing
- Heavy duty plastic drain pans on most models
- Upflow without field modification. Downflow applications require plate kit, included
- AHRI certifiable with all brands of A/C and heat pump systems
- ETL listed for use with both R-22 and R-410a when proper metering device is used

TXV for 1.5 - 3 Ton 4200

TXV for 3.5 - 5 Ton 4202

### SPECIFICATIONS

Coil Model	Flowrator		Dimensions						Shipping Information	
	Size		Pan Widths (W)"				Pan Depth (D)"	Slab Height (H)"	Shipping Weight (LBS.)	
	R22	R410A	13	16	19-1/2	23			2 ROW	3 ROW
CCG18PA1M	0.059	0.055	X				19-3/8	13-1/2		27
CCG18PB1M	0.059	0.055		X			19-3/8	13-1/2		27
CCG18PC1M	0.059	0.055			X		19-3/8	13-1/2		27
CCG24/30PA1M	0.068	0.059	X				19-3/8	17-1/2	23	
CCG24/30PB1M	0.068	0.059		X			19-3/8	17-1/2	23	
CCG24/30PC1M	0.068	0.059			X		19-3/8	17-1/2	23	
CCG24PA2M	0.068	0.059	X				19-3/8	19-1/2	25	
CCG24PB2M	0.068	0.059		X			19-3/8	19-1/2	25	
CCG24PC2M	0.068	0.059			X		19-3/8	19-1/2	25	
CCG30PA2M	0.068	0.059	X				19-3/8	17-1/2		36
CCG30PB2M	0.068	0.059		X			19-3/8	17-1/2		36
CCG30PC2M	0.068	0.059			X		19-3/8	17-1/2		36
CCG36PA1M	0.074	0.068	X				19-3/8	19-1/2		40
CCG36PB1M	0.074	0.068		X			19-3/8	19-1/2		40
CCG36PC1M	0.074	0.068			X		19-3/8	19-1/2		40
CCG42PB1M	0.080	0.074		X			19-3/8	23-1/2	31	
CCG42PC1M	0.080	0.074			X		19-3/8	23-1/2	31	
CCG42PD1M	0.080	0.074				X	19-3/8	23-1/2	31	
CCG42PB2M	0.080	0.074		X			19-3/8	23-1/2		49
CCG42PC2M	0.080	0.074			X		19-3/8	23-1/2		49
CCG42PD2M	0.080	0.074				X	19-3/8	23-1/2		49
CCG48PB1M	0.084	0.080		X			19-3/8	25-1/2		54
CCG48PC1M	0.084	0.080			X		19-3/8	25-1/2		54
CCG48PD1M	0.084	0.080				X	19-3/8	25-1/2		54
CCG60PC1M	0.092	0.089			X		19-3/8	27-1/2		58
CCG60PD1M	0.092	0.089				X	19-3/8	27-1/2		58



Representative drawing only.  
Some models may vary in appearance.



# VCG Series

## Cased Upflow/Downflow Coils

### STANDARD SPECIFICATIONS

- Rifled copper tubing, enhanced aluminum fins
- Immersion-tested at 500 psi, then nitrogen-pressurized and sealed
- Right-hand refrigerant and plumbing connections
- Liquid line - 3/8" ODS, suction line - 3/4" ODS on 1-1/2- 3 ton & 7/8" ODS on 3-1/2 - 5 ton
- Externally mounted flowrator body with Schrader valve for hiss-testing
- Heavy duty plastic drain pans on most models
- Upflow without field modification. Downflow applications require plate kit, included
- Painted cabinets feature furnace connectors
- Fully insulated cabinets with faced insulation
- Split access doors in front for easy service
- AHRI certifiable with all brands of A/C and heat pump systems
- ETL listed for use with both R-22 and R-410a when proper metering device is used

### WARRANTY

Standard warranty or Extended warranty available with product registration.

See warranty document for details or visit [www.marsdelivers.com](http://www.marsdelivers.com)

TXV for 1.5 - 3 Ton 4200

TXV for 3.5 - 5 Ton 4202

### SPECIFICATIONS

Coil Model	Flowrator		Dimensions						Shipping Information	
	Size		Cabinet Widths (W)"				Cabinet Depth (D)"	Cabinet Height (H)"	Shipping Weight (LBS.)	
	R22	R410A	14-1/2	17-1/2	21	24-1/2			2 ROW	3 ROW
VCG18PA1M	0.059	0.055	X				21-1/2	16		37
VCG18PB1M	0.059	0.055		X			21-1/2	16		37
VCG18PC1M	0.059	0.055			X		21-1/2	16		37
VCG24/30PA1M	0.068	0.059	X				21-1/2	20	39	
VCG24/30PB1M	0.068	0.059		X			21-1/2	20	39	
VCG24/30PC1M	0.068	0.059			X		21-1/2	20	39	
VCG24PA2M	0.068	0.059	X				21-1/2	20	44	
VCG24PB2M	0.068	0.059		X			21-1/2	20	44	
VCG24PC2M	0.068	0.059			X		21-1/2	20	44	
VCG30PA2M	0.068	0.059	X				21-1/2	20		50
VCG30PB2M	0.068	0.059		X			21-1/2	20		50
VCG30PC2M	0.068	0.059			X		21-1/2	20		50
VCG36PA1M	0.074	0.068	X				21-1/2	20		56
VCG36PB1M	0.074	0.068		X			21-1/2	20		56
VCG36PC1M	0.074	0.068			X		21-1/2	20		56
VCG42PB1M	0.080	0.074		X			21-1/2	24	54	
VCG42PC1M	0.080	0.074			X		21-1/2	24	54	
VCG42PD1M	0.080	0.074				X	21-1/2	24	54	
VCG42PB2M	0.080	0.074		X			21-1/2	24		69
VCG42PC2M	0.080	0.074			X		21-1/2	24		69
VCG42PD2M	0.080	0.074				X	21-1/2	24		69
VCG48PB1M	0.084	0.080		X			21-1/2	28		75
VCG48PC1M	0.084	0.080			X		21-1/2	28		75
VCG48PD1M	0.084	0.080				X	21-1/2	28		75
VCG60PC1M	0.092	0.089			X		21-1/2	28		81
VCG60PD1M	0.092	0.089				X	21-1/2	28		81

Supply plenum opening size is cabinet width -1" x cabinet depth -1".



Representative drawing only.  
Some models may vary in appearance.



# MCG Series

## Cased Multi-Position Coils

### STANDARD SPECIFICATIONS

- Rifled copper tubing, enhanced aluminum fins
- Immersion-tested at 500 psi, then nitrogen-pressurized and sealed
- Right-hand refrigerant and plumbing connections
- Liquid line - 3/8" ODS, suction line - 3/4" ODS on 1-1/2- 3 ton & 7/8" ODS on 3-1/2 - 5 ton
- Externally mounted flowrater body with Schrader valve for hiss-testing
- Heavy duty plastic drain pans on most models
- Upflow, horizontal right, or horizontal left without field model modification. Downflow application require plate kit, included.
- Painted cabinets feature furnace connectors
- Fully insulated cabinets with faced insulation
- Split access doors in front for easy service
- AHRI certifiable with all brands of A/C and heat pump systems
- ETL listed for use with both R-22 and R-410a when proper metering device is used

### WARRANTY

Standard warranty or Extended warranty available with product registration.

See warranty document for details or visit [www.marsdelivers.com](http://www.marsdelivers.com)

TXV for 1.5 - 3 Ton 4200

TXV for 3.5 - 5 Ton 4202

### SPECIFICATIONS

Coil Model	Fluorator		Dimensions						Shipping Information	
	Size		Cabinet Widths (W)"				Cabinet Depth (D)"	Cabinet Height (H)"	Shipping Weight (LBS.)	
	R22	R410A	14-1/2	17-1/2	21	24-1/2			2 ROW	3 ROW
MCG18PA1M	0.059	0.055	X				21-1/2	19		39
MCG18PB1M	0.059	0.055		X			21-1/2	19		39
MCG18PC1M	0.059	0.055			X		21-1/2	19		39
MCG24/30PA1M	0.068	0.059	X				21-1/2	23	41	
MCG24/30PB1M	0.068	0.059		X			21-1/2	23	41	
MCG24/30PC1M	0.068	0.059			X		21-1/2	23	41	
MCG24PA2M	0.068	0.059	X				21-1/2	23	46	
MCG24PB2M	0.068	0.059		X			21-1/2	23	46	
MCG24PC2M	0.068	0.059			X		21-1/2	23	46	
MCG24TA2M	Factory installed TXV		X				21-1/2	23	46	
MCG24TB2M	Factory installed TXV			X			21-1/2	23	46	
MCG24TC2M	Factory installed TXV				X		21-1/2	23	46	
MCG30PA2M	0.068	0.059	X				21-1/2	23		52
MCG30PB2M	0.068	0.059		X			21-1/2	23		52
MCG30PC2M	0.068	0.059			X		21-1/2	23		52
MCG36PA1M	0.074	0.068	X				21-1/2	23		58
MCG36PB1M	0.074	0.068		X			21-1/2	23		58
MCG36PC1M	0.074	0.068			X		21-1/2	23		58
MCG36TA2M	Factory installed TXV		X				21-1/2	23		52
MCG36TB2M	Factory installed TXV			X			21-1/2	23		52
MCG36TC2M	Factory installed TXV				X		21-1/2	23		52

Supply plenum opening size is cabinet width -1" x cabinet depth -1".

CONTINUED ON NEXT PAGE



Representative drawing only.  
Some models may vary in appearance.



# MCG Series

## Cased Multi-Position Coils

### STANDARD SPECIFICATIONS

- Rifled copper tubing, enhanced aluminum fins
- Immersion-tested at 500 psi, then nitrogen-pressurized and sealed
- Right-hand refrigerant and plumbing connections
- Liquid line - 3/8" ODS, suction line - 3/4" ODS on 1-1/2- 3 ton & 7/8" ODS on 3-1/2 - 5 ton
- Externally mounted flowrator body with Schrader valve for hiss-testing
- Heavy duty plastic drain pans on most models
- Upflow, horizontal right, or horizontal left without field model modification. Downflow application require plate kit, included.
- Painted cabinets feature furnace connectors
- Fully insulated cabinets with faced insulation
- Split access doors in front for easy service
- AHRI certifiable with all brands of A/C and heat pump systems
- ETL listed for use with both R-22 and R-410a when proper metering device is used

### WARRANTY

Standard warranty or Extended warranty available with product registration.

See warranty document for details or visit [www.marsdelivers.com](http://www.marsdelivers.com)

TXV for 1.5 - 3 Ton 4200

TXV for 3.5 - 5 Ton 4202

### SPECIFICATIONS

Coil Model	Flowrator		Dimensions						Shipping Information	
	Size		Cabinet Widths (W)"				Cabinet Depth (D)"	Cabinet Height (H)"	Shipping Weight (LBS.)	
	R22	R410A	14-1/2	17-1/2	21	24-1/2			2 ROW	3 ROW
MCG42PB1M	0.080	0.074		X			21-1/2	27	57	
MCG42PC1M	0.080	0.074			X		21-1/2	27	57	
MCG42PD1M	0.080	0.074				X	21-1/2	27	57	
MCG42PB2M	0.080	0.074		X			21-1/2	27		71
MCG42PC2M	0.080	0.074			X		21-1/2	27		71
MCG42PD2M	0.080	0.074				X	21-1/2	27		71
MCG48PB1M	0.084	0.080		X			21-1/2	30		78
MCG48PC1M	0.084	0.080			X		21-1/2	30		78
MCG48PD1M	0.084	0.080				X	21-1/2	30		78
MCG48TC2M	Factory installed TXV				X		21-1/2	30		78
MCG48TD2M	Factory installed TXV					X	21-1/2	30		78
MCG60PC1M	0.092	0.089			X		21-1/2	30		84
MCG60PD1M	0.092	0.089				X	21-1/2	30		84
MCG60TC2M	Factory installed TXV				X		21-1/2	30		84
MCG60TD2M	Factory installed TXV					X	21-1/2	30		84

**Supply plenum opening size is cabinet width -1" x cabinet depth -1".**

*Due to ongoing product improvements, specifications and dimensions are subject to change and correction without notice or incurring obligations. Determining the application and suitability for use of any product is the responsibility of the installer. Additionally, the installer is responsible for verifying dimensional data on the actual product prior to beginning any installation preparations.*

*Third party incentive and rebate programs have precise requirements as to product performance and certification.*

*All products meet applicable regulations in effect on date of manufacture; however, certifications are not necessarily granted for the life of a product. Therefore, it is the responsibility of the applicant to determine whether a specific model qualifies for these incentive/rebate programs.*