Port-A-Cool 16" Vertical Tank





16", 1/2 h.p. Three-Speed Motor Cools 900 sq. ft.

- 42 Gallon Water Capacity
- Water Level Sight Tube
 - Cord Wrap
- Lowers temperatures up to 30 degrees F
- New cord-wrap storage
- 42-gallon water reservoir for longer operation
- Energy efficient 5.1 amps for pump and motor
- Water level sight tube and sump drain
- Durable one-piece, rust-free, leak-proof molded polyethylene housing
- Environmentally friendly efficient and effective resource use
- Cools for a fraction of the cost of air conditioning
- Cools without chemicals or refrigerants
- Long-term dependability—near maintenance-free operation
- Shipped completely assembled—ready to operate out of the box
- UL Listed (electric models) in U.S. and Canada

Port-A-Cool 16" Vertical Tank

Speeds	Three
Air Delivery CFM	2,500 / 3,300 / 3,900
Total Amps	5.1
Water reservoir	42 gallons
Dimensions	59"h x 37.5"w x 23"d
Unit weight	130 lbs.
Shipping weight	145 lbs.
Box Size	60"h x 38"w x 25"d
Cooling Capacity	900 sq. ft.

STOCK NUMBER PAC163SVT