



# Description

QuietR<sup>®</sup> Textile Duct Liner is a bonded blanket of long glass fibers designed to be installed inside sheet metal ductwork and plenums with metal fasteners and adhesives.

# **Key Features**

- Absorbs fan and air turbulence noise and reduces popping noises within sheet metal ducts.
- Outstanding thermal and acoustical performance.
- Bacterial and fungal growth resistant with an EPA registered biocide that protects the airstream surface from microbial growth.

### **Product Applications/** Installation

All portions of duct designated to receive QuietR® Textile Duct Liner shall be completely covered with duct liner, adhered to the sheet metal with 90% coverage of adhesive complying with ASTM C 916. Transverse joints shall be neatly butted and there shall be no interruptions or gaps. All transverse joints shall be edgecoated. Metal nosing on leading edges must be used where duct liner is preceded by unlined metal, and on all upstream edges when velocity exceeds 4,000 fpm (20.3 m/s). The black mat faced surface of the duct liner shall face the airstream.

# Product Data Sheet

### Availability

Quiet $R^{\otimes}$  Textile Duct Liner is available in the following combinations of thicknesses and types: R-values, hr•ft<sup>2</sup>•°F/Btu (RSI, m<sup>2</sup>•°C/W)

Product Type and Thickness	0.5 in (I3mm)	1.0 in (25mm)	1.5 in (38mm)	2.0 in (51mm)
Туре 150	_	3.8 (0.67)	5.8 (1.02)	7.7 (1.36)
Туре 200	2.0 (0.35)	4.1 (0.72)	6.0 (1.06)	8.0 (1.41)
Туре 300	2.2 (0.38)	4.3 (0.76)	-	-

Popular roll widths are standard products. Other widths can be made to order.

. Actual finished thickness is 1.06" thick (nominal 1.0")

# **Typical Physical Properties**

Property	Test Method	Test Method Value				
Operating Temperature	ASTM C 411	250°F (1	21°C)			
Maximum Air Velocity	UL 181 Erosion Test ASTM C 1071	6,000 fpm (30.5 m/sec)				
Water Vapor Sorption (By Weight)	ASTM C 1104	<3% at 120°F (49°C), 95% R.H.				
Fungi Resistance	ASTM C 1338	Meets requirements				
Fungi Resistance	ASTM G 21	Meets requirements				
Bacteria Resistance	ASTM G 22	Meets requirements				
Corrosiveness	ASTM C 665 (Corrosiveness Test)	Will not cause corrosion greater than caused b sterile cotton on aluminum or steel <sup>2</sup>				
<b>Thermal Conductivity</b> <b>k at 75°F (λ at 24°C mean)</b> Type 150 Type 200 Type 300	ASTM C 518	Btu•in/hr•ft²•°F 0.26 0.25 0.23	(W/m•°C) (0.038) (0.036) (0.034)			
Surface Burning Characteristics <sup>3</sup> Flame Spread Smoke Developed	UL 723, or CAN/ULC-SI02	25 50				

2. When wet, coated surfaces of QuietR® Textile Duct Liner in contact with galvanized steel may cause discoloration of the sheet metal.

3. The surface burning characteristics of these products have been determined in accordance with UL 723 or CAN/ULC-SI02. This standard should be used to measure and describe the properties of materials, products or assemblies in response to heat and flame under controlled laboratory conditions and should not be used to describe or appraise the fire hazard or fire risk of materials, products or assemblies under actual fire conditions. However, results of this test may be used as elements of a fire risk assessment which takes into account all of the factors which are pertinent to an assessment of the fire hazard of a particular end use. Values are reported to the nearest 5 rating. UL 723 and ASTM E 84 are the same test methods.

QuietR<sup>®</sup> Textile Duct Liner shall also be secured with mechanical fasteners, either impact-driven or weld-secured, which shall compress the duct liner sufficiently to hold it firmly in place. For fastener spacing, see illustration.

Duct liner shall be cut to assure over-lapped and compressed longitudinal corner joints. For details, refer to NAIMA Publication AH124, Fibrous Glass Duct Liner Standard. Minor damage and small tears may be repaired by coating with adhesive.

After installation, and prior to occupancy, blow out duct system to remove any cutting scraps or foreign material remaining in the duct.

Installing two layers of material to meet a specific liner thickness is not recommended. If the specification forces the use of multiple layers, the following steps must be taken:



0.40

0.65

0.84

0.90



- I. Adhere bottom layer of duct liner to duct in normal manner.
- 2. Adhere top layer to bottom layer of liner using a minimum of 90% adhesive coverage.
- 3. Treat all leading edges with metal nosings to prevent separation of the two layers.
- 4. Use mechanical fasteners of the proper length for double layer.

### Limitations

Use of OuietR<sup>®</sup> Textile Duct Liner is not recommended for the following applications:

- With wood or coal fired equipment, or equipment of any type which does not include automatic maximum temperature controls and where operating temperatures of 250°F (121°C) may be exceeded.
- In kitchen or fume exhaust ducts, or ducts conveying solids or corrosive gases.
- In any application where the duct liner may come in direct contact with liquid water (such as cooling coils, humidifiers, and evaporative coolers) unless protected from the water source.
- Inside fire damper sleeves.
- Immediately adjacent to high temperature heating coils without radiation protection.

#### **Tips to Avoid Mold Growth in Ducts**

 Mold in duct systems occurs when moisture comes into contact with dirt or dust collected on the duct system

# Product Data Sheet

### Acoustic Performance

0.5 (13)

1.0 (25)

Type 300

	Thickness,	Sound Absorption coefficients at octave band center frequencies (Hz)									
Product	in. (mm)	125	250	500	1000	2000	4000	NRC			
Гуре 150	1.0 (25)	0.15	0.25	0.45	0.68	0.79	0.81	0.55			
	1.5 (38)	0.16	0.36	0.61	0.83	0.90	0.92	0.70			
	2.0 (51)	0.20	0.53	0.79	0.94	0.95	0.97	0.80			
уре 200	0.5 (13)	0.10	0.15	0.27	0.49	0.66	0.77	0.40			
	1.0 (25)	0.11	0.28	0.49	0.70	0.81	0.86	0.55			
	1.5 (38)	0.16	0.41	0.71	0.90	1.01	0.93	0.75			
	20. (51)	0.20	0.55	0.87	1.00	0.95	0.95	0.85			

0.16

0.26

These data were collected using a limited sample size and are not absolute values. Reasonable tolerances must therefore be applied. All tests were conducted in accordance with ASTM C 423, Mounting A (material placed against a solid backing such as a block wall). For more information, call your Owens Corning Representative.

0.30

0.54

0.51

0.85

0.69

0.96

# Insertion Loss, dB per ft. of Lined Duct

0.08

0.07

	Octave band center frequencies, Hz													
P/A,	P/A. I" Liner							2" Liner						
ft./ft. <sup>2</sup>	125	250	500	1000	2000	4000		125	250	500	1000	2000	4000	
8	0.6	1.5	2.7	5.8	7.4	4.3		0.8	2.9	4.9	7.2	7.4	4.3	
6	0.5	1.2	2.3	5.0	5.8	3.6		0.6	2.3	4.2	6.2	5.8	3.6	
4	0.4	0.8	1.9	4.0	4.1	2.8		0.5	1.6	3.5	5.0	4.1	2.8	
2	0.2	0.5	1.4	2.8	2.2	1.8		0.3	0.8	2.3	3.3	2.0	1.7	
I	0.1	0.1	1.0	2.0	1.2	1.2		0.2	0.5	1.8	2.3	1.1	1.1	

Duct Liner Insertion Loss – Data extracted from ASHRAE Handbook, HVAC Applications, Chapter 43, 1999 P/A = duct perimeter, ft/duct cross sectional area (ft<sup>2</sup>). Example: 12" × 12", P/A = 4 (1/ft.). For more information, call your Owens Corning Representative.



# QuietR® Textile Duct Liner



surfaces. Proper filters will minimize the collection of dust and dirt, but care needs to be exercised to prevent water formation in the duct. A properly sized and operated air conditioning unit will minimize the likelihood of water formation.

• The system must be maintained and operated to insure that sufficient dehumidification is occurring and that filters are installed and changed as recommended by the equipment manufacturer.

# Standards, Codes Compliance

- ASTM C 1071, Type I, Flexible (replaces obsolete Federal Specification HH-1-545B.)
- NFPA 90A/90B
- ICC Compliant
- California Title 24
- SMACNA Application Standard for Duct Liners
- NAIMA Fibrous Glass Duct Liner Installation Standard
- Conforms to ASHRAE 62-2001
- Meets requirements of ASTM C 1338, ASTM G 21 (fungi test) and ASTM G 22 (bacteria test).

# Product Data Sheet

#### Certifications and Sustainable Features of QuietR<sup>®</sup> Textile Duct Liner

- Certified by Scientific Certification Systems to contain a minimum of 57% recycled glass content
- Certified to meet indoor air quality standards under the stringent GREENGUARD Indoor Air Quality Certification Program<sup>SM</sup>, and the GREENGUARD Children & Schools Certification Program<sup>SM</sup>

# Environmental and Sustainability

Owens Corning is a worldwide leader in building material systems, insulation and composite solutions, delivering a broad range of highquality products and services. Owens Corning is committed to driving sustainability by delivering solutions, transforming markets and enhancing lives. More information can be found at www. sustainability.owenscorning.com.



# QuietR® Textile Duct Liner

# Product Data Sheet

#### Disclaimer of Liability

Technical information contained herein is furnished without charge or obligation and is given and accepted at recipient's sole risk. Because conditions of use may vary and are beyond our control, Owens Corning makes no representation about, and is not responsible or liable for the accuracy or reliability of data associated with particular uses of any product described herein. Nothing contained in this bulletin shall be considered a recommendation.

The GREENGUARD Indoor Air Quality Certified mark is a registered certification mark used under license through the GREENGUARD Envronmental Institute.

Scientific Certification Systems (SCS) provides independent verification of recycled content in building materials and verifies recycled content claims made by manufacturers. For more information, visit www.scscertified.com.









OWENS CORNING INSULATING SYSTEMS, LLC ONE OWENS CORNING PARKWAY TOLEDO, OHIO 43659 1-800-GET-PINK®

### INNOVATIONS FOR LIVING® www.owenscorningcommercial.com

Pub. No.59362-J. Printed in U.S.A. June 2012. THE PINK PANTHER<sup>™</sup> & ©1964-2012 Metro-Goldwyn-Mayer Studios Inc. All Rights Reserved. The color PINK is a registered trademark of Owens Corning. ©2012 Owens Corning. All Rights Reserved.

