


DIMENSIONS AND SPECIFICATIONS

Aspen Manufactured Home Coils

Designed to Fit Inside Mobile Home Furnaces



GENERAL SPECIFICATIONS

- Standard refrigerant connections: liquid line - 3/8" ODS, suction line - 7/8" ODS
- Left-hand refrigerant and plumbing connections.
- One 3/4" FPT condensate drain.
- Plastic drain pan engineered for downflow application only.
- Five-year warranty.
- Flowrater standard. Factory or field-installable TXV available.
- Every coil immersion-tested at 500 psi, then nitrogen-pressurized and sealed.
- Rifled copper tubing, enhanced aluminum fins.
- ARI certifiable with all brands of A/C and heat pump systems.
- HUD certified and listed by ETL per Federal Register 24CFR Section 3280, subsection 714 (5).

COIL MODEL	COIL HEIGHT	DRAIN PAN WIDTH	DRAIN PAN DEPTH	CFM RANGE	LIQUID ODS	SUCTION ODS	DRAIN CONN.	APPROX. SHIP WT.
MV1** 30	14	17-3/4	19-5/8	800-1000	3/8	7/8	3/4" FPT	25
MVR** 30	12	17-3/4	19-5/8	800-1000	3/8	7/8	3/4" FPT	23
MV5** 36	16	17-3/4	19-5/8	1000-1200	3/8	7/8	3/4" FPT	27
MVR** 36	14	17-3/4	19-5/8	1000-1200	3/8	7/8	3/4" FPT	25
MV5** 42	18	17-3/4	19-5/8	1200-1400	3/8	7/8	3/4" FPT	32
MVR** 42	16	17-3/4	19-5/8	1200-1400	3/8	7/8	3/4" FPT	29
MV7** 48	16	17-3/4	19-5/8	1400-1600	3/8	7/8	3/4" FPT	29
MVR** 48	18	17-3/4	19-5/8	1400-1600	3/8	7/8	3/4" FPT	35
MVR44 48A	18	17-3/4	19-5/8	1400-1600	3/8	7/8	3/4" FPT	35
†MVR44 48B	18	19-1/4	19-5/8	1400-1600	3/8	7/8	3/4" FPT	35
MVR** 60	18	17-3/4	19-5/8	1600-2000	3/8	7/8	3/4" FPT	35
† MVA** 60	18	19-1/4	20	1600-2000	3/8	7/8	3/4" FPT	36
# MVB** 60	26	19-1/2	19-5/8	1600-2000	3/8	7/8	3/4" FPT	41

† Fits inside electric furnace only. Utilizes powder-painted galvanized steel pan.

5T coil with plastic drain pan. Designed to fit top of electric furnace.