


Product Catalog

Roofing Metals • Roof Drainage • Metal Concrete Accessories

Ventilation • Pipe and Fittings • Drywall Metal Trims



Aluminum-Zinc Coated Steel coating consists of an alloy of nominally 55% aluminum, 1.6% silicon, and the remainder zinc by weight, as listed in ASTM designation A792.

Based on long-term atmospheric corrosion test results, it is estimated that **Aluminum-Zinc Coated Steel** sheet will outlast G90 galvanized by two to four times in marine, industrial and rural atmospheres.

In salt spray tests with cut edges exposed, the corrosion resistance is typically three to four times that of G90 Galvanized.





Aluminum-Zinc Coated Steel

More Corrosion Resistant

The unique combination of aluminum and zinc can outlast galvanized steel by two to four times, depending on the environment.

Formability

Equivalent formability to conventional galvanized products allows for a wide range of applications.

Attractive Appearance

Aluminum-Zinc Coated Steel's smooth surface is architecturally pleasing and makes for a superior surface for pre-painting and post-painting.

No Primer Required

No primer required when field painting, provided a water based acrylic finish coat is used.

Pre-painted

Aluminum-Zinc Coated Steel is available in pre-painted Award colors.

High Temperature Resistance

Operating conditions resulting in surface temperatures up to 600 degrees are easily withstood without surface discoloration.

Thermal Reflectivity

Aluminum-Zinc Coated Steel sheet reflects a high percentage of heat and light. In roofing, it acts as a heat shield and thermal barrier.

Distributed by: BEST MATERIALS LLC Ph: 800-474-7570, 602-272-8128 Fax: 602-272-8014 www.BestMaterials.com Email: Sales@BestMaterials.com

Introducing New Products

Not all products are stocked at all of our locations, call for availability.

Visit our online catalog: www.awardmetals.com

Painted Steel Products

For The Seamless Gutter Industry

Coils - Downspouts - Elbows - End Caps

12 Coil Colors

- 50° White
- Musket
- 30° White
- 80° White
- Almond
- Old Town Gray
- Classic Cream
- Pebblestone Clay
- Heritage Cream
- Raffia Beige
- Beaver Brown
- Buckskin Brown

Four Coil Widths

- 19" E grade (all colors)
- 15" D grade (all colors)
- 13" D grade (all colors)
- 11%" D grade (50° White and Musket)

Why Steel?

- Easier to install
- Fewer warranty concerns
- Far stronger than aluminum
- Less expensive than aluminum (per foot)



Round Elbows by Award Metals



2" & 3" Round Elbows

45°, 60°, 75°, 90°

Rolled Seam

20 per box

Galvanized in 2" & 3"

Bonderized in 3" only

More Elbows on Page 16

Attic Ventilation



™Nifty-fifty



Hood: 12" x 12" Base: 15" x 18" Height: 4"



Colors:

NORTHWEST BROWN,
WEATHERED GRAY,
LIGHT GRAY,
EMERALD,
BLACK OR TAN

♦ Designed by and for the roofing contractor

Made of high impact resins to achieve both the rigorous demands required for jobsite installation and the long-lasting durability to withstand harsh weather.

♦ Matte Finish

A matte finish that provides a uniform contoured surface that resists scratches and dents while giving the finished roof more of a blended appearance eliminating the shiny, "blistered" effect.

◆ 50 square inches of net free air flow

50 square inches of net free air for excellent air flow and op-

timum ventilation.

♦ Unique nailer strip

Unique nailer strip designed for ease of installation that dramatically reduces the risk of base fractures during fastening.

Ultraviolet inhibitors

Made with ultraviolet inhibitors to retain long-lasting strength, color and durability.

♦ Double fencing

True-38 Roof Vent




Regular Base
Height: 4" Base to top of Bonnet
Flange: 4½" from Throat
Hood: 10½" x 10½"
Base: 17" x 17"
Collar: 3"

Also available in:

5" High Collar - Shake or Tile 8" High Collar - Hot Mop



- **♦** Galvanized
- Pre-painted
- **◆** Award Stonecoat
- **♦** Copper by Special Order
- **♦** Aluminum Zinc Coated Steel
- ◆ 38 square inches of net free air flow



Jumbo Aluminum Base
Height: 6" Base to top of Bonnet
Flange: 81/4" from Throat
Hood: 101/2" x 101/2"
Base: 24" x 24"
Collar: 5"



STEALTH

Low Profile Vent

ICC Evaluation: ER-5463



Composition



"S" Tile



Flat Tile



Deck Opening Sizes

Net Free Air Flow

24" = 40 sq. in. 36" = 66 sq. in.

30" = 53 sq. in. 48" = 90 sq. in.



Available In

Paint-ready aluminum zinc **Pre-painted AWARD Colors** AWARD STONECOAT TM **Copper by Special Order**

Four Widths

24", 30", 36", 48"

Dade County Tested for Wind and Wind Driven Rain Resistance to 80 M.P.H. under an 8.8 inch per hour rainstorm. MD# CAE 00048




Ridge Cap Metal

- Saves You Money!
- Hurricane Tested*
- Easy To Install
- **Superior Protection**
- Natural Ventilation

Sub-flashing Metal

Virtually Invisible



* Dade County Tested for Wind and Wind Driven Rain Resistance to 110 M.P.H. under an 8.8 inch per hour rainstorm. MD# CAE 00048

STEALTH Ridge Vent: U.S.Patent 6,662,509 B2

Metal Ridge Vent ICC Evaluation: ER-6171



AWARD STONECOAT™







Award Metals has developed the unique *AWARD STONECOAT* $^{\text{TM}}$ process to eliminate the common drawback to all standard roof vents . . . they are visually unattractive. Some are bare metal, some are bright plastic. Bare metal, even galvanized metal, rusts long before the roofing surface needs to be replaced. A painted roof vent usually results in a poor match to the roofing surface and will likely eventually fade or peel. By using *AWARD STONECOAT* $^{\text{TM}}$ products for your roof venting, both longevity and appearance are greatly enhanced.

	Weathered Wood	Onyx	Blends of Brown	Wood Shake	Slate	Rustic Wood	White	Emerald	Pewter	Pacific Blue
CELOTEX	Weathered Wood	Charcoal Black	Dark Brown	Wood Tone	Slate	Autumn Blend	Artic White	Yosemite		
GAF Grand Sequoia	Weathered Wood	Charcoal Blend	Mesa Brown	Cedar Blend	Slate Blend	Barkwood				
GAF Timberline	Weathered Wood	Charcoal Blend	Burnt Sienna	Cedar Blend	Slate Blend		Birchwood Blend			
PABCO	Weathered Wood	Antique Black	Harvest Brown	Buckskin Tan	Driftwood	Prarrie Wood	Weathered White	Sherwood Green	Pewter Gray	Blue Slate
TAMCO	Weathered Wood	Rustic Black	Autumn Brown	Rustic Cedar	Antique Slate	Rustic Slate	Coastal Sand	Rustic Green		
ELK	Weathered Wood	Sablewood	Hickory	Shake Wood	Antique Slate	Barkwood	Aspen White	Forest Green		
O.C.	Driftwood	Onyx Black	Brownwood	Desert Tan	Coastal Gray	Teak	Sierra Gray	Chateau Green	Estate Gray	Harbour Blue
CERTAINTEED Independence	Weathered Wood	Charcoal Black	Burnt Sienna							
CERTAINTEED Haiteras	Weathered Stone		Sandpiper		Windswept Gray					Regatta Blue
CERTAINTEED Arc-80	Weathered Wood	Ebony Wood	Oakwood	Cypress Wood	Driftwood		Birchwood	Fernwood		
MALARKEY	Weathered Wood	Charcoal	Antique Brown	Sienna Blend		Natural Wood	Silverwood	Rain Forest	Oxford Gray	
IKO	Weathered Wood	Dual Black	Bark Brown	Earthtone Cedar	Castle Gray	NW Driftwood	Dual Gray	Forest Green	Harvard Gray	Blue Slate

© 2007 Award Metals - Vancouver, WA

AWARD STONECOAT[™] is available in other colors upon your request. Color variance may occur from different production runs. If any manufacturer or shingle color is not represented, please let us know.









AWARD STONECOAT™

Ask About The Price

It's Less Than You Think!



AWARD STONECOATTM is priced to *save you money* and make you look good at the same time! Impress your customers and your accountant.



Developed with the unique *AWARD STONECOAT*[™] process to eliminate the unattractiveness of galvanized roof vents. Available in a **wide range of colors** to match most roofing products including: Celotex, Certainteed, Elk, GAF, Pabco, Tamko, and Ownens Corning.

Durable and Builder Friendly

AWARD STONECOAT[™] helps to increase the longevity of all your roof venting needs, and eliminates painting problems while creating a wonderful accent color to the roof. We stand behind this durability by offering a 25-year limited warranty on all AWARD STONECOAT[™] products.

Ask Your Supplier For A Quote






























Rain Diverter

A 13"

B 2"

Lap Joint




A 11/8", 11/2" or 2"

B %"

C Variable

Eave Starter #230




A 3"

B 1"

C 1/4"


Anti Ponding Metal



A 11/2" or 2"

B 6", 8" or 10"

Water Table




A 21/2"

B 21/4"

C ½"

Rake Trim Metal




A 41/2"

B 5" or 61/4"

Special Order Product

Pipe Flashing - Standard Base



1/2" - 4"

Aluminum Zinc Coated,
Galvanized or Copper

Flat to 12:12 Pitch

Pipe Flashing - FHA Base

Aluminum Pipe Flashing



1/2" to 7"

Aluminum Zinc Coated

Steel, Galvanized or Copper

FHA Approved "Wide Base"

Pipe Flashing - Dead Soft Base



1/2" to 4"

Dead Soft Aluminum Base

Dead Soft Copper Base

Dead Soft Base 1100 - 0 Temper

1½" or 2" Pipe Diameter Flat Base Only Aluminum Base Only



Multiflex - Regular Base

Metal Products For The Construction Industry

Multiflex - Shake base



11/2" - 2"

Aluminum Zinc Coated, **Galvanized or Copper**

5:12 maximum




11/2" - 2"

Aluminum Zinc Coated, Galvanized or Copper

5:12 maximum

Multiflex - Dead Soft Base



11/2" - 2"

Deadsoft Aluminum Base For Tile Applications

> **Dead Soft Base** 1100 - 0 Temper

5:12 maximum

Multiflex - Regular Base High Boot



11/2" - 2"

Aluminum Zinc Coated, **Galvanized or Copper**

5:12 maximum

1 Rib "W" Valley



With or Without **Closed Hem or Open Hem**

18" or 24" 1" Rise **Aluminum Zinc Coated** or Galvanized * Copper by Special Order

1 Rib Tile Valley

3 Rib Valley

5 Rib Valley - Cedar Lite



3/4" Open Hem

24" 1" Rise **Aluminum Zinc Coated** or Galvanized * **Copper by Special Order**

2 Rib Open Valley



With or Without **Closed Hem or Open Hem**

24" 1" Rise 4" Between Rise **Aluminum Zinc Coated** or Galvanized *

Copper by Special Order



With or Without **Closed Hem or Open Hem**

24" **Aluminum Zinc Coated** or Galvanized * **Copper by Special Order**

4 Rib Valley



With or Without **Closed Hem or Open Hem**

24"

Aluminum Zinc Coated or Galvanized * Copper by Special Order



With or Without **Closed Hem or Open Hem**

24" or 283/4" **Aluminum Zinc Coated** or Galvanized * Copper by Special Order


31" Tall Rib (Not Pictured)



Gerard	"W" Valley	Bird Stop Eave Closure		
	7" 1" Rise Bonderized		Major Styles Available Weep & Nail Holes Provided Charcoal, Terra Cotta or Bare Metal	
Ro	ll Valley	Roo	of Outlet	
Pre-Painted, Galvanized or Aluminum	6" x 50" 7" x 50" 8" x 50" 12" x 50' 14" x 50' 20" x 50'		2" Round With 5" Long Tube 2" Round With 10" Long Tube Galvanized Call for other sizes. 5" - 50 per Box 10" - 25 per Box	
SI	ningles	Step Shingles		
	5" x 7" - 100/Bundle 6" x 8" - 100/Bundle 8" x 12" - 50/Bundle 10" x 14" - 50/Bundle Galvanized & Pre-Painted	Galvanized & Pre-Painted 50 per Bundle	3" x 5" x 7" 3" x 5" x 8" 4" x 6" x 14" 4" x 4" x 8" 4" x 4" x 12" 4" x 4" x 14"	
Zinc Mo	ss Roof Strip			
Contact us for more information on the Zinc Moss Roof Strip.	Zinc Moss Roof Strip is the long term solution to moss build-up on roofs. With each rainfall, moss killing zinc is released. Zinc is a proven agent for controlling moss and fungus. Just apply the rolled zinc to each side of the ridge cap along all roof peaks. Works on composition or shake roofs and is designed to last more than 25 years! Stocked at Vancouver & Seattle Facilities.			



Fascia Plain Face



Copper 10' Length Only

51/4" or 71/4"
Galvanized
or Bonderized
Copper by Special Order

Tile Plain Face



71/4"
Galvanized
or Bonderized
Copper by Special Order

Fascia Deco Face - 5 & 7 Rib



51/4" or 71/4" Galvanized or Bonderized

Tile Deco Face - 7 Rib



71/4"
Galvanized
or Bonderized

Fascia Curved Face - 1" Wing



Copper 10' Length Only

51/4" Standard
71/4" Standard or Tile
Galvanized
or Bonderized
Copper by Special Order


Half Round Single Bead



4", 5", or 6" Galvanized, Bonderized, or Copper

10' in 4", 5" & 6" 20' in 5" & 6"

"K" Style - No Wing



4" & 6" Copper 10' Only 5K Copper 10' or 20' 4" NA in Bonderized

4", 5", or 6" Galvanized, Bonderized, or Copper

10', 20', 25', or 30' 6" NA in Galvanized

Half Round Single Bead - 1" Wing


Half Round Double Bead



4", 5", or 6" Galvanized, Bonderized, or Copper

10' in 4", 5" & 6" 20' in 5" & 6"

"K" Style - 1" Wing



4" & 6" Copper 10' Only 5K & 6K Copper 10' or 20'

4", 5", or 6" Galvanized, Bonderized, or Copper



4", 5", or 6" Galvanized, Bonderized, or Copper

> 10' in 4", 5" & 6" 20' in 5" & 6"



Miter - Half Round Miter - "K" Style 5", or 6" 4", 5", or 6" Galvanized Galvanized or Copper 5" or 6" Copper **Half Round Drop Outlets Tapered Drop Outlets** 2" 3" or 4" Galvanized Galvanized or Copper or Copper **Oval Drop Outlets Rectangular Drop Outlets** 13/4" x 23/4" 3" or 4" 2" x 3", 3" x 4" Galvanized or Copper Copper 2" x 3" Only **Curved Fascia End Cap** Fascia Tap On End Cap 51/4" 51/4" or 71/4" Gal-Galvanized vanized or Copper or Copper "K" Style Tap On End Cap Half Round Tap On End Cap 4", 5", or 6" 4", 5", or 6" Galvanized Galvanized or Copper or Copper



		Metal Prod	lucts For The Construction Industry
Fo	errules	S	pikes
	4", 5", or 6" Galvanized or Copper 100 per Box	•	7" or 8" Gal- vanized or Copper Copper 100 per Box Galvanized 926 per Box
Square	Pipe Straps	Round	Pipe Straps
	13/4" x 23/4" 2" x 3" 3" x 4" 4" x 6" Galvanized or Copper		2" thru 4" Galvanized or Copper
Lead	ler Heads	Outlet B	Box - Scupper
Regular Ornate	Regular Ornate 13/4" x 23/4" 3", 4", 5", 6" 2" x 3" Round with 3" x 4" Male Extension 4" x 6" Special Order Galvanized or Copper	Left, Center, Right	2" x 3" 3" x 4" 4" x 6"
Round Do	ownspout - 10'	Sauare Dow	nspout - 10' & 20'
Notified by	2" thru 6" 26 GA Galvanized or 16 oz Copper	oquire bow	1¾" x 2¾" 2" x 3", 3" x 4", 4" x 6" 26ga Galvanized or Bonderized 16 oz Copper - 2" x 3" or 3" x 4"

50° White Pre-Painted Downspout

PACKAGED TO ELIMINATE SCRATCHING!



28ga or 26ga



Pre-painted Pipe Straps 1¾" x 2¾"




4" x 6" Special

Musket Brown Pre-Painted Downspout

28ga





Gutter Hanger Usage for Northern California

Award Metals Factory Produced Gutter

Profile

51/4" Curved

51/4" Fascia

71/4" Fascia & Curved Regular Profile

71/4" Fascia & Curved Tile Profile

4" K-type (also known as 4" OG)

5" K-type (also known as 5" OG)

6" K-type (also known as 6" OG)

1			
	20		

Hanger Spread

4 Inch	4.5 Inch	5 Inch	6 Inch	5 Inch Tile*
X				
Х				
	х			
				х
Х				
		Х		7
			Х	

^{*} Tile gutter uses a special dropped 5" spread.

Pre-painted Coil Gutter (produced in the field)

51/4" Curved

51/4" Fascia (differs from production gutter)

71/4" Fascia

5" K-type (also known as 5" OG)

6" K-type (also known as 6" OG)

Hanger Spread

4 Inch	4.5 Inch	<u>5 Inch</u>	<u>6 Inch</u>
X	167		
	Х		
	Х		
		Х	
	17		X

This information, while deemed to be accurate, is not guaranteed.



Nail Tv	pe Half Ro	ound Cross	bar
		, errer C 1 0 0 0	~~~

Imperial Hanger



4", 5", or 6" **Galvanized or Copper**

Single Bead



4" thru 6" Galvanized or Copper

#10 Circle & Shank Hanger

Half Round Strap Hanger



4", 5", or 6" Galvanized or Copper

50 per Box



5" or 6" Galvanized or Copper

Half Round Slip Connector



50 per Box

4", 5", or 6" Galvanized or Copper

20 per Box

Square Elbows - Style "A"

Square Elbows - Style "B"



Galvanized 28ga Rolled Seam Non-Mitered

3" x 4"

13/4" x 23/4" 2" x 3"

45°, 60°, 75°, 90°

"K" Style Slip Connector



50 per Box

Galvanized

or Copper



20 per Box

13/4" x 23/4" 2" x 3"

3" x 4"

Galvanized 28ga

Rolled Seam Non-Mitered

45°, 60°, 75°, 90°

Wire Strainer



2", 3", or 4" Galvanized or Copper

Round Elbows




20 per Box


2" or 3" **Rolled Seam** 20 per Box Galvanized in 2" & 3" Bonderized in 3"

Copper and other sizes by **Special Order**




Gutter Profiles






Tile Fascia - Plain or Deco



Plain Fascia or Deco




Curved Fascia



STEALTH *Metal Ridge Vent

STEALTH * Low Profile Vent





Ridge Cap

Sub-flashing

ICC Evaluation: ER-6171

Dade County Tested for Wind and Wind Driven Rain Resistance to 110 M.P.H. under an 8.8 inch per hour rainstorm. MD# CAE 00048

STEALTH * Ridge Vent: U.S.Patent 6,662,509 B2

See page 3 for more specifications.



ICC Evaluation: ER-5463 Four Widths 24", 30", 36" 48" Aluminum-Zinc coated steel, Pre-painted, copper or Award STONECOAT

Net Free Air Flow

24" = 40 sq. in. 36" = 66 sq. in.

30" = 53 sq. in. 48" = 90 sq. in.

STEALTH * Sub-base flashing Page 21

See page 3 for more specifications.

Nifty-fifty



50 sq. inches net free air See Page 2

High Impact Resins

Hood: 12" x 12"

Base: 15" x 18"

Height: 4"

True 38



38 sq. inches net free air See Page 2

Hood: 101/2" x 101/2"

Base: 17" x 17" Height: 4"

Gravity Vent



133.00 sq. inches net free air

22" Cap 10" High

6" Flange

26 Gauge

12" x 12" Opening

Half Round Dormer

Half Round Dormer - Pointed Back



28.47 and 50.19 sq. inches net free air

9" x 18"

Regular, Deadsoft Aluminum or Copper

12" x 24"

Regular, Tile, Deadsoft **Aluminum or Copper**

Pentagon Dormer



68.00 sq. inches net free air

13" x 19" "S" Tile, Flat Tile or Composition



28.47 and 50.19 sq. inches net free air

9" x 18"

Regular, Deadsoft Aluminum or Copper

12" x 24"

Regular, Tile, Deadsoft **Aluminum or Copper**



Round Aluminum Code Cap





3" to 10" Round ICBO RPT. 3728 CLIS AA-513

Regular, Shake Base or Tile Hem Deadsoft Base up to 8"

Oval Aluminum Code Cap





4" Horizontal or Vertical ICBO RPT. 3728 CLIS AA-513

Regular, Shake Base or Tile Hem Deadsoft Base up to 8"

Vent Cap



3", 4", 5", 6", 7", 8" 4" Oval Cap By Special Order



China Cap

4" to 24" Galvanized

Rectangular Gable End Vent



14" x 8"
14" x 12"
14" x 18"
14" x 24"

F.O.F., F.O.B., P.G.

Round Gable End Vent



14" or Larger 2" Flange F.O.F., F.O.B., P.G.

Foundation Vents



Foundation Vent 1/4" Screen



Stamped Foundation 1/4" Mesh Vent



Stamped Foundation Louver Vent

6" x 14" Galvanized Plaster Ground

6" x 14"
Bonderized
Plaster Ground

6" x 14" Bonderized Plaster Ground

Eave Vent



3-1/2" x 14" Ear Out 3-1/2" x 22" Ear Out 5" x 22" Ear Out 1/4" Screen

Ready-Vent®



U.S. Patent #6,165,066

8" x 16"
Poured-in-place foundation vent, with or without doors.
For wall sizes:
6". 8". 10" or 12"

6", 8", 10" or 12" Gray Plastic

See your Local Building Code for installation requirements.



Eyebrow Dormer - Gerard Hem



48.75 sq. inches net free air

4" x 19"

Aluminum Zinc Coated, Regular, Shake Base, Galvanized or Aluminum Base

Sub-Base Flashing Page 21

Eyebrow Dormer



48.75 sq. inches net free air

4" x 19"

Aluminum Zinc Coated, Regular, Shake Base, Galvanized or Aluminum Base

Sub-Base Flashing Page 21

Roof Jack



4", 6", 8"
Aluminum Zinc Coated
Regular Base
Flat or Pitched
4/12, 5/15, 6/12

Roof Jack - 2 Piece



3"- 4" 5"- 6" 7"- 8"
10", 12"
Regular, Shake Base
or Tile Hem
Adjustable Pitch
Sub-Base Flashing Available

T-Top



4" & 7" Round 6" x 6" Square

Open End or with End Caps Aluminum Zinc Coated, Galvanized or Copper Regular, Shake Base or Tile Hem

T-Top - Deadsoft Aluminum Base



4" or 7" Round Dead Soft Aluminum Dead Soft Copper

Horizontal Combo Vent



4" x 10"

4" x 12"

4" x 14"

Regular or Shake Base

Vertical Combo Vent



4" x 10"

4" x 12"

4" x 14"

Regular or Shake Base

Rotary Vent & Base



8" to 48" Galvanized

Special Order

Base Made To Pitch

Snow Splitter Vent



1" to 2" 3" to 4" Galvanized



Wall Cap

Wall Mount Dryer Vent



4" or 7" Wall Cap With Screen 2" Flange Copper by Special Order



4" or 5" Dryer Vent Galvanized 2" Flange **Copper by Special Order**

Tub Access Door

Roof Mounted Dryer Vent



14" x 14" Piano or Strap Hinge 1/2", 3/4" or 7/8" **Plaster Ground** Galvanized



4" or 5" **Round Dryer Vent** with Flapper

Available in Copper

Sub-Base Flashings

Stem Vent - ABS Plastic



Square Sub-Base Flashing 9" x 18" - Opening 10" x 10" 12" x 24" - Opening 14" x 14"



4" to 5" **Attached Plastic Bathroom Vent** With Flapper



STEALTH* & Eyebrow Sub-Base Flashing

DBX1000 Dryer Vent Receptacle



For the STEALTH® Vent 24", 30", 36" or 48"

> For 4" x 19" **Eyebrow Dormer**



Durable High Impact Polystyrene

RECOUPS UP TO 5 SQ. FT. OF SPACE.

Eliminates kinks in connection which reduces electrical/gas costs from improper venting and potential fire hazard from lint buildup.

Storm Collar

Access Able® Access Panel



3" to 6" Fixed or Adjustable Galvanized



4" x 6"

6" x 9"

8" x 8"

14" x 14"


14" x 29"

Bare Metal Drywall Trims



Metal Products For The Construction Industry





11/4" Corner Bead

Award Drywall Corner Bead special coating insures the best compound bonding and corrosion resistance. It provides lasting protection to exposed interior edges of wallboard and smooth, straight corners. It can be nailed, screwed or clinched onto wallboard.


Length/Ft	Pcs/Ctn	Ft/Ct
6'	100	600'
7'	86	600'
8'	75	600'
9'	67	600'
10'	60	600'
12'	50	600'

Other sizes available by special order.



Open Angle Corner Bead

Award Open Angle Corner Bead provides a straight, smooth finish for interior wall angles greater than 135°.



Length/Ft	Pcs/Ctn	Ft/Ctn
8'	63	504'
9'	56	504'
10'	50	500'

40 Cartons Per Skid



A B B 1/2 1 1 5/8 1

L-Bead

Award L-Bead is used for wallboard stops where speed and economy are important. Joint compound is required to finish. Available in both ½" and 5%" sizes.

Length/Ft	Pcs/Ctn	Ft/Ct
8'	75	600
10'	60	600

48 Cartons Per Skid



3/4" Bullnose Corner Bead

Award Bullnose Corner Bead provides the soft look of rounded interior corners. The ³/₄" radius is the popular choice of architects and builders. It can be nail, screw or staple applied.

Length/Ft	Pcs/Ctn	Ft/Ctn
7'	57	400'
8'	50	400'
9"	45	400'
10'	40	400'
12'	34	400

Other sizes available by special order.



A		_
	← c -	
A	В	\mathbf{C}
1/2	1/2	11/16
5/8	⁷ / ₁₆	¹⁵ ⁄16

U-Bead

Award U-Bead provides a smooth, square, finished edge for wallboard stops around door and window openings. Joint compound is required to finish. Back flange allows for tight fit against wood or steel stud. Available in both ½" and 5%" sizes.

Length/Ft	Pcs/Ctn	Ft/Ctn
8'	50	400'
10'	50	500'


30 Cartons Per Skid



32 Cartons Per Skid

3/4

3/4



Bullnose Open Angle

Award Open Angle Bullnose Corner Bead allows the soft look to continue on wall angles greater that 135°.

Length/Ft	Pcs/Ctn	Ft/Ctn
7'	57	400'
8'	50	400'
9'	45	400'
10'	40	400'
12'	34	400



	A.	— c	→
4		В	(
/		1/	44

_ B

A	В	C
1/2	1/2	1 ½16
5/8	⁷ / ₁₆	¹⁵ ⁄16

J-Bead


Award J-Bead J-Bead provides a finished edge at wallboard stops and can be used where wallboard panels intersect or abut dissimilar surfaces. Joint compound can not be used with J-Bead as the hemmed surface is generally painted. J-Bead is available in both ½" and 5%" sizes.

Length/Ft	Pcs/Ctn	Ft/Ctn
8'	50	400'
10'	50	500'

30 Cartons Per Skid



Bare Metal Drywall Trims




Cornerbead, J-Bead, U-Bead and L-Bead produced by Award Metals are manufactured from aluminum-zinc coated steel that is further coated for additional corrosion resistance and joint compound adhesion. Our products meet the ASTM specifications for hot-dipped galvanized contained in ASTM Specification C-1047-94 except for Section 4.1 (ASTM C-1047 is the specification for accessories for gypsum wallboard).

Bullnose Cornerbead produced by Award Metals is manufactured from aluminum-zinc coated steel that is further coated for additional corrosion resistance and joint compound adhesion. Our product meets the ASTM specification for hot-dipped galvanized contained in ASTM Specification C-1047-94. (ASTM C-1047 is the specification for accessories for gypsum wallboard).

Tape-On & Paperfaced Nail-On Trims






Award Metals tape-on and paperfaced trims are produced to meet or exceed specifications set forth in ASTM C-1047.

Tape-On Corner Bead for use on 90° Outside Corners

A1W, A1W NB, A1XW, A1XW NB, A1XW EL, A1XW EL NB

> Taper's Bead™ T1W EL, T1XW EL



Even Leg Beaded Even Leg No Bead

13/16 3/4 3/4 9/16 A1W 13/16 9/16 3/4 3/4 A1W NB 11/16 11/16 3/4 A1W EL 3/₄ 3/₄ 5/₈ 11/16 11/16 T1W EL 11/16 11/16 A1W EL NB ¹⁵/₁₆ 11/16 A1XW 5/8 13/16 13/16 5/8 A1XW EL ¹³/₁₆ 13/16 5/8 5/8 T1XW EL ¹⁵/₁₆ 11/16 5/8 A1XW NB ¹³/₁₆ 5/8 ¹³/₁₆ A1XW EL NB





METAL

Mini-Bead™ Tape-On Outside Corner

A₁MB


Tape-On outside corner designed with 1" legs to cover damaged edges and lower bead height that requires less fill.

A B C D

15/16 15/16 3/4 3/4

Stock Lengths: 8' & 10'

Stock Lengths: 8' & 10'
Custom lengths available upon request.



TAPE

METAL

A10A

Tape-On 135° Outside Open Angle

Tape-On 135° outside corners Open Angle bead to give a true offset corner.

> A B C D 23/32 15/32 5/8 5/8 Stock Lengths: 8', 9', 10'

Custom lengths available upon request.




Tape-On Inside Corner Bead

A2

Designed to provide a straight inside corner.

A B C D
3/8 3/8 5/8 5/8
Stock Lengths: 8' & 10'
Custom lengths available upon request.



Tape-On 135° Open Angle

A₂O_A

Product is designed for 135° open angle inside corners.

A B C D
5/8 5/8 5/8 5/8
Stock Lengths: 8' 9' & 1



Stock Lengths: 8', 9' & 10' Custom lengths available upon request.



Tape-On "L" Trim Corner Bead for use on 90° Outside Corners

METAL METAL	B METAL B
TAPE	C TAPE
Read	

METAL

A4

	A	В	C		A	В	C
A4 3/8	3/8	7/8	1	A4 3⁄8 NB	3/8	7/8	1
$A4\frac{1}{2}$	1/2	¹⁵ / ₁₆	1 5⁄ ₁₆	A4½ NB	1/2	¹⁵ ⁄ ₁₆	1 5⁄16
A4 5/8	5/8	¹³ / ₁₆	15/16	A4	5/8	¹³ / ₁₆	1 5⁄16
$A4\frac{3}{4}$	3/4	¹⁵ / ₁₆	¹⁵ / ₁₆	A4 3⁄4 NB	3/4	¹⁵ ⁄ ₁₆	¹⁵ / ₁₆
A4 1	1	¹⁵ / ₁₆	1 5⁄ ₁₆	A4 1 NB	1	¹⁵ ⁄ ₁₆	1 5⁄16
A4 1 1/8	11/8	1 ½16	11/16	A4 1 1/8 NB	11/8	1 ½16	1 ½16
A4 1 1⁄4	11/4	¹⁵ / ₁₆	11/16	A4 1 ½ NB	11/4	¹⁵ / ₁₆	1 ½16

Stock Lengths: 8', 9', 10'
Custom lengths available upon request.



Tape-On & Paperfaced Nail-On Trims


TAPE

Metal Products For The Construction Industry




Tape-On Bullnose 3/4" Radius

ABN



Bullnose is designed to provide an attractive 3/4" radius outside corner. The 3/4" radius Bullnose can be applied to all standard drywall sizes.

Stock Lengths: 7, 8', 9' & 10' Custom lengths available upon request.




Tape-On U and J-Trim Outside Corner

A9 1/2" A9 5/8"

Tape-On U and J Trim Provides a finished edge at wallboard stops. Can be used to finish closet drops as well as door window encasements.

	A	В	С	D
1/2	9/16	1/2	5/8	1 ½16
5/8	21/32	1/2	17/32	11/16

Stock Lengths: 7', 8', 10' Custom lengths available upon request.



METAL

Tape-On Reveal Trim Outside Corner

ART 1/2" ART 5/8"

Tape-on no bead reveal trim features an additional paper flange that eliminates the need for caulking.

	9 ·			
	A	В	С	D
1/2	1/2	1/2	¹⁵ / ₁₆	²⁵ / ₃₂
5/8	5/8	5/8	¹⁵ / ₁₆	21/32
	Standar	d Lens	gths: 8',	10'

Custom lengths available upon request.



Tape-On Shadow Trim Outside Corner

AST 1/2" AST 5/8"

Tape-On Shadow trim (Reveal) designed to be used where wallboard abuts suspended ceilings.

	Α	В	C	D
1/2	1/2	1/2	¹⁵ / ₁₆	1 5/16
5/8	5/8	5/8	¹⁵ / ₁₆	1 ½16

Standard Lengths: 8', 10 Custom lengths available upon request.



METAL


Tape-On Bullnose 3/4" For 135°

ABN OA

Product is designed for 135° open angle 3/4" radius outside corners.

> В C 3/4 3/4 3/4


Stock Lengths: 8', 9' & 10' Custom lengths available upon request.



METAL


Nail-On Bullnose 3/4" Radius

ABN N **ABN NXW**



C 3/4 5/8 5/8

Stock Lengths: 7, 8', 9' & 10' Custom lengths available upon request.



METAL

TAPE


Nail-On Bullnose 3/4" For 135°

ABN NOA

Nail-On paperfaced bullnose 3/4" for 135° open angle Outside Corner. Nail-on version of bullnose designed for 135° open angle 3/4" radius outside corners.

11/16 11/16

Stock Lengths: 8' & 10 Custom lengths available upon request.



- B -


MFTAL

TAPE

Nail-On Paperfaced J-Round

AJR 1/2" AJR 5/8"

Nail-On version of J-Round is ideal for ceating rounded edges at door and window (cased) openings.



All products packaged 50 pieces per carton, 60 cartons per pallet except:




SUN LINE

Tape-On & Nail-On Paperfaced Trims







TAPE

METAL


Mini Bull™ Tape-On 1/2" Radius Bullnose

SMB

Tape-On 1/2" radius bullnose outside corner.

A B C 1/2 5/8 5/8

Stock Lengths: 8', 9', 10'




Mini Bull™ Nail-On 1/2" Radius Bullnose

SMBN

Nail-On Paperfaced 1/2" radius bullnose outside corner.

A B C 1/2 3/4 3/4

Stock Lengths: 8', 9', 10'




Tape-On 3/4" Radius Bullnose

SBN

Tape-on 3/4" radius bullnose designed to provide an attractive radius outside corner.

A B C 3/4 5/8 5/8

Stock Lengths: 8', 9', 10'



TAPE

TAPE

METAL


Nail-On 3/4" Radius Bullnose

SBN N

Nail-On 3/4" radius bullnose designed to provide an attractive radius outside corner.

A B C 3/4 5/8 5/8

Stock Lengths: 8', 9', 10'




Tape-On 90° Extra Wide Outside Corner

S1XW

Tape-On 90° outside corner bead with 1-1/16" extra wide legs.

A B C D 11/16 11/16 5/8 5/8

Stock Lengths: 8', 9', 10'



METAL


Nail-On 3/4" Radius Extra Wide Bullnose

SBN NXW

Nail-On Paperfaced 3/4" radius bullnose with extra long legs designed to provide an attractive outside corner.

A B C 7/8 7/8

Stock Lengths: 8', 9', 10'



Tape-On 90° Extra Extra Wide Outside Corner

S1XXW

Tape-on 90° outside corner with 1-1/4" extra extra wide legs designed to cover damaged edges of wallboard and problem corners.

A B C D 11/4 11/4 3/4 3/4

Stock Lengths: 8', 9', 10'



METAL TAPE


Nail-On 90° Extra Extra Wide Outside Corner

S1XXWN

Nail-on 90° outside corner with 1-1/4" extra extra wide legs designed to cover damaged edges of wallboard and problem corners.

A B 11/4 11/4

Stock Lengths: 8', 9', 10'



Award Metals SUN LINETM trims are produced to meet ASTM C-1047 except for Section 4.1.





#34 Stucco Stop - No Holes

#36 Stucco Stop - With Holes



Award #34L Stucco Stop is generally used for exterior 3 coat stucco wall applications. Manufactured with a full 3½" wall flange to meet current codes. The wall flange also has 2 stiffeners that can be used to align stucco stop for 13/16" or 5/16" coverage at the mud sill. Available in 7/8" ground only.

10' Lengths Packaged 100' Per Bundle



Award #36L Stucco Stop is generally used for exterior 3 coat stucco wall applications. Manufactured with a full 3½" wall flange to meet current codes. The wall flange also has 2 stiffeners that can be used to align stucco stop for 13/16" or 5/16" coverage at the mud sill. Available in 7/8" ground only. Available with weep holes.

10' Lengths Packaged 100' Per Bundle

J-8 Drip Mold Metal

J-33 One Coat Screed



Award J-8 Drip Mold Metal is generally used as plaster or stucco stop at the mud sill. Manufactured with 3½" wall flange to meet current codes. The ½" base is available with or without weep holes.

10' Lengths Packaged 100' Per Bundle




Award J-33 One Coat Screed is generally used with foam board for one coat stucco applications. Manufactured with a full 3½" wall flange to meet current codes. The 1¾" base is available with or without weep holes.

10' Lengths Packaged 100' Per Bundle

#7 Sill Screed

#66 Casing Bead



Award #7 Sill Screed is generally used for exterior 3 coat stucco wall applications. Manufactured in 4", 5" and 5½" dimensions. Available with or without weep holes.

Available in Copper

10' Lengths Packaged 100' Per Bundle



Award #66 Casing Bead is for the use on window and door frames.

3/4" or 7/8"

10' Lengths Packaged 300' Per Carton




Metal Products For The Construction Industry

RAP-I-FACTS


The RAP-I-FORM® system eliminates the need to drill panels, fabricate inside and outside corners, or the labor of handling forming lumber such as walers and base plates.

RAP-I-FORM® Monolithic Straps

For single-pour, inverted "T" foundations.



Stocked in sizes: 15", 17", 19" & 23"





Cost Savings: The RAP-I-FORM® system costs a fraction of other concrete forming systems. Plus, you'll also save time on setting and stripping our forms. You'll be using the most cost effective system on the market.

Versatility: You can use the RAP-I-FORM® system to form anything from slab on-grade foundations to complete basements, and all without purchasing extra hardware.

Flexibility: The RAP-I-FORM® system can be used with 1½" HDO plywood, 3/4" HDO plywood, or regular dimension lumber. Hardware is readily available for all three types of forming materials. Change your elevations, wall heights and wall thicknesses quickly and easily.


Simplicity: You and your crew won't need extensive training to use the RAP-I-FORM® system. Most contractors can learn to use the system in less than a day.

Availability: The RAP-I-FORM® has an extensive dealer network throughout the United States. For a dealer near you, please call one of our offices.

Accuracy: The RAP-I-FORM® clips and Flat Snaptie Ties are fabricated to exact wall sizes. This ensures you of a consistent wall size throughout the pour.

Durability: Most HDO plywood panels, when used with reasonable care, will give you up to 300 pours with the RAP-I-FORM® system.





RAP-I-FORM® 11/8"

Walerless Plywood Form System

This is the only forming system that is specifically designed to meet the needs of the foundation wall contractor. It is the HDO plywood's strength, stability and hard smooth surface that provides a durable foundation wall system that makes it so appealing to builders throughout the country. In addition, all of the materials and hardware used in this




system can be worked with ordinary hand tools and standard carpentry skills.

The nature of HDO plywood is such that on site preparation is possible without the complicated re-working of the basic forming system. In effect, RAP-I-FORM® has taken the labor cost of form preparation and handling out of foundation wall construction.

The key to the RAP-I-FORM® system is a spreader type clip that fits over the top of, and under the bottom of, the forming plywood. On the job, form clips are laid out on a pre-poured footing and spaced approximately two feet apart. HDO plywood, cut into 2'x8' sheets, is then set into the form clip. Top clips are then applied to hold the top of the form in place, and the foundation wall is poured.





RAP-I-FACTS


The initial cost of RAP-I-FORM® forming system is 50% less than competitive systems when used with 11/8" HDO plywood.












W = Wall Thickness
P = Panel Thickness



- 1. Chalk building line on footing
- 2. Place clips on building line.
- 3. Set panels A & B and secure at corner. Then set panels C, D, & E, and continue along building line, make sure to place clips top and bottom 4-8" from end of each panel as shown. If desired, clips on joints may be nailed after placement of panel. (Exact spacing is not necessary.)

CAUTION: Always make certain there is a clip to hold the end of each panel regardless of where the panel joint may be.

PRE-NAILING OF CLIPS: will cause incorrect spacing and loss of time.

NOTE: With the Rap-I-Form® system a level footing is not necessary, however, a flat footing surface will speed the setting of forms and simplify alignment.

It is also imperative that the form clip be fully engaged to the bottom of the panel. An un-level footing could allow the form clip to drop below the edge of the panel restricting the ability of the form clip to capture the form panel. To correct the form clip alignment, nail form clips securely to the bottom of the form panel.

Rap-l-Form[®] clips are available for virtually any wall thickness and can be used with either plywood or dimension lumber. The table below shows the most common combinations of wall and panel thicknesses which are stocked for immediate shipment.

IIV	STOCKED FOR IMEDIATE SHIPPING	MAXIMUM CLIP SPACING

W. Wall Thickness	P. Panel Thickness					Pours to 36" Height	Shipping Weight Per Box of 100 Clips			
(inches)		(inch			_ : ::o:g.:c	l co morgine	3/4	11/8	1%	21/4
4	3/4	11/8			24" Maximum	16" Maximum	26#	31#		
55%		11/8			24" Maximum	16" Maximum		41#		
6	3/4	11/8	15⁄8		24" Maximum	16" Maximum	36#	41#		
75/8	3/4	11/8	1%	21/4	24" Maximum	16" Maximum	46#	49#		61#
8	3/4	11/8	1%	21/4	24" Maximum	16" Maximum	46#	51#		61#
9	3/4	11/8	1%	21/4	24" Maximum	16" Maximum	51#	56#		66#
10	3/4	11/8	1%	21/4	24" Maximum	16" Maximum	51#	58#		68#
11%		11/8		21/4	24" Maximum	16" Maximum		66#		76#
12	3/4	11/8	1%	21/4	24" Maximum	16" Maximum	66#	68#	76#	81#
14	3/4	11/8	15⁄8		24" Maximum		75#	77#	86#	
15	3/4	11/8	1%		24" Maximum		80#	84#	96#	
16	3/4	11/8	15⁄8		24" Maximum		85#	106#	106#	

3/4" and 1-1/8" panel size is for reversible plywood panels.


Rap-l-Form® shall not be responsible or liable for form failures where maximum clip spacing or recommended rate of pour has been exceeded. The clip spacings and rates of pour listed are the maximum permissible for each size clip.


^{1-5/8&}quot; size is for dimensional lumber.


^{2-1/4&}quot; size is for 5/8" plywood on a 2 x 4 frame.




Metal Products For The Construction Industry
















POURING TEMPERATURES			50°F	AHR.					70° F	AHR.		
Rate of pour ft. of height per hour	2 Ft.	3 Ft.	4 Ft.	5 Ft.	6 Ft.	8 Ft.	2 Ft.	3 Ft.	4 Ft.	5 Ft.	6 Ft.	8 Ft.
Concrete pressure per sq. ft. of forms	450#	600#	750#	900#	1050#	1350#	350#	450#	550#	650#	750#	950#
Tie Spacing	24*	20"	16"	14"	12"	12"	24"	20"	18"	16"	12"	12"

^{*}These tables are based on Hand Spading of Concrete; if mechanical vibration is used, decrease rate of pour or increase number of ties,

^{*}Note: The tie spacings listed are the maximum permissible spacings for the listed temperatures and rates of pour. Rap-t-Form shall not be responsible or liable for form failures where the maximum Tie Spacing or recommended rate of pour listed above has been exceeded.





Metal Products For The Construction Industry

Round Stakes

3/4" Round Std. Length Weight

ota. Length	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
12"	1.5#
18"	2.2#
24"	2.9#
30"	3.6#
36"	4.3#
42"	5.0#
48"	5.7#



10 stakes p	er bundle
-------------	-----------

7//8" R	ound
Std. Length	Weight
12"	2.6#
18"	3.9#
24"	5.2#
30"	6.5#
36"	7.8#
42"	9.1#
48"	10.4#

Stiffback Tie



Used to stiffen and align the walls by utilizing 2" x 4" vertical stiffbacks where applicable. Used in conjunction with our standard wedges.



Award Rap-I-Form® Form Clip is used to spread and hold the top and bottom of form set-up during the pour. The top clips are removed during stripping and saved for the next job. The clips are available in 1" increments from 4" to 24".

Flat Stacking Tie



The flat snaptie provides support through the horizontal joints between the plywood panels. Breakback after stripping is accomplished with a horizontal hammer blow.



Galvanized filler sheets are used on the interior of walls to compensate for odd wall lengths and eliminate the cutting of panels. The outside panels are allowed to run by at the corners.

Metal Key Way



With interlocking stakes. Meets both ACI and PCA recommendations for the design of tongue and groove key joint.

31/2", 51/2" or 71/2"

Key Way Stakes

Form Clip - 4" to 24"

Filler Pan



12", 15", 18" & 24"

Sold separately - 100 per box

Stake Puller



Pull all our round, square or flat stakes without adjustments. Our puller has easy-to-use three position base and three position handle.







Metal Washer & Plastic Cone Snaptie



Note: 2250 lbs. allowable with 2.0 safety factor, short end or long end. Rap-I-Form® Metal Washer and Plastic Cone Snap Ties are now available in wall sizes 6" through 24".

"Short End"

3/4" Plywood = **43/4" Ends**

11/8" Plywood = 51/8" Ends

"Long End"

3/4" Plywood = 81/4" Ends

"Stubbie"

3/4" Plywood = 11/4" Ends

11/8" Plywood = 15/8" Ends

100 Ties Per Box

Round Snaptie Wedge



Award Rap-I-Form® Round Snaptie Wedge is used to take up and secure round snapties to the panels. The wedge is secured with a vertical hammer blow and is released during stripping with a reverse hammer action.

100 per Box

Flat Snaptie Wedge



Award Rap-I-Form® Flat Snaptie Wedge is used to take up and secure flat snaptie ties to the panels. The wedge is secured with a vertical hammer blow and is released during stripping with a reverse hammer action.

50 per Box

Cardboard Pier Pad Boxes



Designed for forming concrete pier pads used in residential post & beam construction. Available in:

18" x 18" x 8"

24" x 24" x 8"

24" x 24" x 12"

Ready-Vent®



U.S. Patent #6,165,066

8" x 16"
Poured-in-place foundation

vent, with or without doors.

For wall sizes: 6", 8", 10" or 12" Gray Plastic

See your Local Building Code for installation requirements.

Conductor Pipe & Fittings



Half Round & Full Round Cut Off - 3" to 14"





Cast aluminum cut-offs with galvanized steel slide gates. Cut-offs are used to balance systems, or save air, heat and power when a machine is not in use. All cut-offs are furnished with set screws so blade may be firmly placed for volume control. To install, cut slot in pipe and sheet metal screw collar to pipe. Full cut-offs are used the same as half cut-offs, except to install. The pipe will fit over the collar of the cut-off on both ends. They are also furnished with set screws so blade may be firmly placed for volume control.

Ball Joint - 3" to 12"



Spun steel galvanized ball joints provide flexibility in ducts serving moving cutter heads or other moving equipment. Thus, duct can swing through on arc while maintaining exhaust flow in the line.

Floor Sweep



Floor sweeps are available as shown. Sweeps have tight fitting doors, conveniently opened by foot, installed near drills, benches, etc., for floor cleanup use. Made of 18 Gauge Galvanized, with 6" diameter connection.

Angle Rings - 3" to 50"



Pressed and rolled steel angle rings are used widely in jointing ductwork together in dust and fume control work. All stock rings have bolt holes and are made from black steel, unpainted. Stainless Steel rings available upon request.

One Piece Elbow



45°, 60°, 75°, 90°

Not Airtight: One-piece elbow is fabricated from a single piece of galvanized sheet steel formed by a special machine.

Airtight: Airtight elbows and short radius elbows upon request.

Round Conductor Pipe



2" to 26"

Contact your Award Metals Distributor for more Conductor Pipe Specifications.

Available in 26GA, 24GA, 22GA & 20GA (Not all gauges available in all diameters.)



Net Free Air Flow

STEALTH® Ridge Vent - ICC Evaluation ER-6171

8 sq. inches Net Free Air per lineal foot

STFALTH®	Attic Vents -	ICC Evaluation	FR-5463

24" wide	40 sq. inches
30" wide	53 sq. inches
36" wide	66 sq. inches
48" wide	90 sq. inches

TRUE-38

10-1/2" x 10-1/2" 38 sq. inches

NIFTY-fifty

12" x 12" 50 sq. inches

EYEBROW VENT

4" x 19" 50 sq. inches

PENTAGON DORMER

13" x 19" 68 sq. inches

HALF ROUND DORMERS

_ 9" x 18"	28.47 sq. inches
12" x 24"	50.19 sq. inches

GABLE LOUVERS

14" x 6"	17.24 sq. inches
14" x 9"	31.84 sq. inches
14" x 12"	46.43 sq. inches
14" x 18"	75.62 sq. inches
14" x 24"	104.80 sq. inches

READY-VENT®

8" x 16"	73 sq. inches
----------	---------------

Net Free Air is calculated according to AMCA Standard 500

Base Sizes

	REGULAR	SHINGLE	SHAKE	DEAD SOFT	FHA
1/2" to 2" Plumbers Flashing	14 x 12	17½ x 17½	17½ x 24	24 x 24	15 x 191/4
3" Plumbers Flashing	20 x 20	20 x 20	20 x 26	24 x 24	18 x 22½
4" Plumbers Flashing	20 x 20	20 x 20	20 x 26	24 x 24	18 x 22½
4" Oval Plumbers Flashing				24 x 26	22 x 17½
1-1/2" to 2" Multiflex	12½ x 16		15 x 23½	20 x 26	
3" Code Cap	20 x 20		20 x 26	24 x 24	
4" Code Cap	20 x 20		20 x 26	24 x 24	
5" Code Cap	22 x 22		22 x 28	24 x 24	
6" Code Cap	23 x 23		23 x 29	24 x 26	
7" Code Cap	24 x 24		24 x 30	24 x 26	
8" Code Cap	24 x 24		24 x 30	24 x 26	
4" Oval Code Cap Vert	17½ x 22½		17½ x 28	24 x 24	
4" Oval Code Cap Horz	17½ x 22½		22 x 24	24 x 26	
4" x 19" Eyebrow Vent	22 x 30		26½ x 30		
9" x 18" Half Rnd Dormer	30½ x 33½		30½ x 37½	36 x 38½	30 x 31
12" x 24" Half Rnd Dormer	39½ x 39½			43 x 41	35 x 35
<u>4" T-Top</u>	17½ x 17½		17½ x 24	22 x 23	22½ x 18
7" T-Top	21 x 20½		20 x 26	24 x 27	20 x 18
4" Fan Jack	17½ x 17½		18½ x 24		
6" Fan Jack	20 x 21		20 x 26		
8" Fan Jack	22 x 22		22 x 28		

Index of Products

* Product Availability



Roofing Metals

Rooming Mctais	
2-Way Edge No Grip or Drip	6
3-Way Edge Recover	6
Anti Ponding Metal	9
Bird Stop - Eave Closure	11
Brick Flashing	7
Coping - Drip, Grip, Plain	6
Counter Flashing	7
D-Metal	6
Diatto Leg Type	8
Diatto Regular Type	8
Eave Riser Strip T-Style	7
Eave Starter #230	9
Fabry Crown Gravel Stop	6
Eave Strip	6
Fascia Cap	6
Goodbye Moss Roof Strip	11
Gravel Stop: Drip or Grip	6
Lap Joint: Drip or Grip	9
Multiflex	10
Nosing With Grip	6
Pipe Flashings	
Aluminum	9
FHA Base	9
Shake Base	9
Standard Base	9
Rake Trim Metal	9
Rain Diverter	9
Roof Outlet	11
Roof-To-Wall Head Flashing	8
Roll Valley	11
Saddle Stock	7
Shingles	11
Step Shingles	11
T-Metal	7
Termite Flashing	8
Tile Pan	8
Tile Pan - Ribbed	8
Tile Riser	8
Tucker Flashing	7
U-Channel	8
Valley Metals	
1-Rib Tile Valley	10
1-Rib W-Valley	10
2-Rib Open Valley	10
3-Rib Valley	10
4-Rib Valley	10
5-Rib Cedar-Lite Valley	10
Gerard W-Valley	11
Vertical Flashing	8
Water Table	9
Z-Bar	7
	
Roof Drainage	
Coil for Seamless Gutter	1
Downspout/Leader Pipe	
Elbows	1 & 16
Pipe Strap - Round	14
Pipe Strap - Round Pipe Strap - Square	14
Round Leader Pipe	14
Round Leader 1 ipc	14

Square Leader Pipe			14
Drop Outlets			13
Gutter			
End Caps			13
Fascia Gutter			12
Half Round Gutter			12
Hangers	15	&	16
"K" Style Gutter			12
Miters - Inside & Outside			13
Profiles			17
Slip Connectors			16
Spikes & Ferrules			14
Leader Heads			14
Painted Steel - Coils, Downspout			1
Scuppers (Outlet Boxes)			14
Wire Strainers			16
Wa w411 -41 a a Dua da -44			
Ventilation Products			
Access Able® Access Panel			21
DBX1000 Dryer Vent Receptacle			21
China Caps			19
Code Caps - Round & Oval			19
Combo Vents Horizontal & Vertical			20
Dormer Vents			
Eyebrow			18
Half Round			18
Pentagon			18
Dryer Vents			21
Eave Vent			19
Foundation Vents			19
Free Air Calculations			35
Gable End Louvers			19
Gravity Vent			18
Nifty-fifty Vent	2	&	18
Roof Jacks - 1 & 2 Piece			20
Rotary Vents			20
Ready-Vent®			19
Snow Splitter Vents			20
Stamped Louver Vents			19
Stamped Mesh Vents			19
STEALTH * Low Profile Vent			18
STEALTH * Ridge Vent	3	&	18
Stem Vent			21
Storm Collar			21
Sub Base Flashings			21
T-Tops			20
True-38 Roof Vent	2	&	18
Tub Access Door			21
Vent Caps			19
Wall Cap			21
Daywoll Taims			
Drywall Trims			
Bare Metal			22
2-Way Corner Caps			23
3-Way Corner Caps			23
Bullnose Cornerbead			22
Bullnose Kerf			23
Construction L			23
Cornerbead			22

Hat Channel/Furring Channel	23
J-Bead	22
L-Bead	22
Resilient Furring Channel	23
U-Bead	22
Paperfaced Nail-On	
Bullnose	25
Bullnose Extra Wide	25
Bullnose Open Angle	25
J-Round Bullnose	25
Paperfaced Tape-On	
Bullnose Outside Corner	25
Bullnose Open Angle	25
Inside Corner	25
Inside Open Angle	24
"L" Trim	24
Mini-Bead [™]	24
	24
Outside Open Angle	
Outside Corner	24
U and J-Trim	25
Sun Line™	26
Bullnose 3/4" Extra Wide	26
Bullnose 3/4" Nail-On	26
Bullnose 3/4" Tape-On	26
Mini Bull TM 1/2" Nail-On	26
Mini Bull TM 1/2" Tape-On	26
Outside Corner Nail-On	26
Outside Corner Tape-On	26
Stucco Metals	
	27
#7 Sill Screed	27
#34L Stucco Stop	27
#36L Stucco Stop	27
#66 Casing Bead	27
J-8 Drip Mold Metal	27
J-33 One Coat Screed	27
Rap-I-Form - Concrete	
Construction Stakes	32
Filler Pan	32
Flat Snap Tie Wedge	33
Flat Stacking Tie	32
Form Clips	32
	32
Metal Wesher Span Tie	
Metal Washer Snap Tie	33
Monolithic Straps	32
Pier Pad Boxes	33
Plastic Cone Snap Tie	33
Ready-Vent®	33
Round Snaptie Wedge	33
Screed Bracket	32
Stiffback Tie	32
STEALTH® Attic & Ridge Vents	3
Nifty-fifty and True-38 Vents	2
AWARD STONECOAT™	4 & 5
Conductor Pipe & Fittings	34
oonauctor ripe & rittings	- 54

Net Free Air & Base Sizes

35

^{*} Not all products are stocked at all of our locations, call for availability.



Metal Products For The Construction Industry

The Elegance and Durability of Copper From Award Metals

