



**PRODUCT FEATURES:**

- **Flexible Selectronic® Platform** with programmable, multi-function sensor.
- **Hygienic, touch-free operation**
- **Easy Installation:** Simple integrated design; sensor, solenoid valve and electronics are enclosed in the spout. No control box below deck.
- **Above-Deck Mixing:** Allows user to manually adjust temperature. Leak-free ceramic disc valve. Hot limit safety stop to reduce the risk of accidental scalding. Installer can set temperature and remove handle to prevent user adjustment.
- **Dual Inlets:** For hot and cold water. Inlet hoses include check valves to prevent cross flow and filter screens to protect the solenoid valve.
- **Seamless Cast Brass Body:** No crevices. Easy to clean. Vandal-resistant.
- **Optional Auto Purge Feature:** Faucet can be programmed to open at a pre-determined time after last use to purge the faucet and water lines.
- **Safety Timer:** Helps prevent vandalism by turning off the faucet if the sensor is covered for 55 seconds or more. Timing is adjustable with optional remote control.
- **Adjustable Range:** Detection zone can be adjusted manually or with optional remote control.
- **Fail-Safe:** Faucet automatically shuts off upon loss of power or dead battery. Prevents costly excess water usage and potential flooding.
- **Lead-Free:** Faucet contains  $\leq 0.25\%$  total lead content by weighted average.

**GENERAL DESCRIPTION:**

Electronic faucet with proximity operation. Integrated design with sensor, solenoid valve and electronics enclosed in the spout. Includes Above-Deck Mixing option with ceramic disc valve, hot limit safety stop and removable handle. Vandal-resistant seamless, cast brass spout with single post mounting. Water pressure range from 20 to 125 psi. Dual inlets to spout: 18" flexible stainless steel inlet hoses with check valves, filter screens and 3/8" compression fittings.

**MODEL NUMBER:**

- **BASE UNIT (Does not include power supply)**
  - **705B.205** 0.5 GPM pressure compensating, vandal-resistant multi-laminar spray.
  - **705B.215** 1.5 GPM pressure compensating, vandal-resistant laminar flow outlet with adjustable face.

■ **POWER KITS (Must be purchased separately)**

- **PK00.PAC** Includes universal Plug-In AC power supply.
- **PK00.MAC** Includes Y-splitter and 10' extension cable.
- **PK00.HAC** Includes universal Hard-Wired AC transformer and 10' extension cable.
- **PK00.WRK** Includes 10-Year battery pack and holder.

■ **OPTIONAL Battery Back-Up**

- **PK00.BBU** Allows faucet to continuously operate during a power failure.

■ **OPTIONAL 4" or 8" Deck plates**

- **705P.400** 4" brass deck plate with 1/4" fixation studs and quick spin nuts. Includes fixation pin that prevents the faucet spout from rotating.

■ **OPTIONAL Mixing Valve**

- **605XTMV1070** Thermostatic mixing valve. 20" flexible stainless steel inlet hoses with 3/8" compression fittings. ASSE 1070 certified down to 0.35 gpm.

**POWER OPTIONS:**

- **Universal Voltage:** 100 - 240 VAC, 50/60 Hz
- **Plug-In AC:** Includes Class 2 UL certified universal Plug-In AC power supply with 6' long power cord.
- **Hard-Wired AC:** Includes Class 2 UL certified universal Hard-Wired AC transformer (electrical box by others).
- **Multi-AC:** One AC transformer can power up to 15 faucets and/or flush valves in a daisy chain configuration. **POWER SUPPLY NOT INCLUDED.**

**RECOMMENDED SPECIFICATION:**

Electronic, sensor-operated lavatory faucet shall feature a programmable, multi-function sensor and an electronically operated solenoid valve. Features a vandal resistant cast brass body with dual inlets with check valves and in-line filter screens. Single post mounting. Integrated design with sensor, solenoid valve and all electronics enclosed in the spout. Shall also feature above-decking mixing option using ceramic disc valve with hot limit safety stop. Shall meet ANSI A112.18.1 and ANSI 117.1 codes. Fitting shall be American Standard Model # 705B .2 5.

## CODES AND STANDARDS

These products meet or exceed the following codes and standards:

**ANSI A117.1**

**ASME A112.18.1**

**CSA B125.1**


**NSF 372**

### Other Aerators Available:

Part Suffix	Description
V035**	0.35 gpm (1.3 Lpm) PCA Vandal-Resistant Multi-Laminar Spray

\*PCA - PRESSURE COMPENSATING

\*\*MEETS CAL GREEN CODE



## NOT RECOMMENDED FOR INSTALLATION ON LUCERNE SINKS



Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for accessible and usable building facilities - check local codes

PART OF **LIXIL**