


Rheem *Commercial Value Series* Package Gas Electric Unit



RKKL-B Standard Efficiency Series

Nominal Sizes 15 & 20 Tons [52.8 & 70.3 kW]








TABLE OF CONTENTS

Unit Features & Benefits	3-7
Model Number Identification	8
Options	9
Selection Procedure	10
General Data	
RKKL-B Series	11-17
General Data Notes	18
Gross Systems Performance Data	
RKKL-B Series	19
Indoor Airflow Performance	
RKKL-B Series	20-21
Electrical Data	
RKKL-B Series	
Dimensional Data	24-26
Slab Installation	27
Accessories	28-39
Mechanical Specifications	40-45
Wiring Diagrams	46-49
Limited Warranty	50

Rheem Package Gas Electric Unit Features:




RKKL-B STANDARD FEATURES INCLUDE:

- R-410A HFC refrigerant.
- Complete factory charged, wired and run tested.
- Scroll compressors with internal line break overload and high-pressure protection.
- Two independent refrigerant circuits each with a scroll compressor provide two stage cooling operation.
- Convertible airflow vertical downflow or horizontal sideflow.
- Capillary tube refrigerant metering system on each circuit.
- High Pressure and Low Pressure/Loss of charge protection standard on all models.
- Solid Core liquid line filter drier on each circuit.
- Single slab, single pass designed evaporator and condenser coils facilitate easy cleaning for maintaining high efficiencies.
- · Cooling operation up to 125 degree F ambient.
- Foil faced insulation encapsulated throughout entire unit minimizes airborne fibers from the air stream.
- Hinged major access door with heavy-duty gasketing.
- Slide Out Indoor fan assembly for added service convenience.
- Powder Paint Finish meets ASTMB117 steel coated on each side for maximum protection. G90 galvanized.
- Base pan with drawn supply and return opening for superior water management.

- Forkable base rails for easy handling and lifting.
- Single point electrical connections.
- Internally sloped slide out condensate pan conforms to ASHRAE 62 standards.
- High performance belt drive motor with variable pitch pulleys and quick adjust belt system.
- Permanently lubricated evaporator, condenser and gas heat inducer motors.
- Condenser motors are internally protected, totally enclosed with shaft down design.
- 2 inch filter standard with slide out design.
- Two stage gas valve, direct spark ignition, and induced draft for efficiency and reliability.
- Tubular heat exchange for long life and induced draft for efficiency and reliability.
- · Solid state furnace control with on board diagnostics.
- 24 volt control system with resettable circuit breakers.
- Colored and labeled wiring.
- Copper tube/Aluminum Fin indoor coil.
- Aluminum MicroChannel outdoor coil(s).





Rheem Package equipment is designed from the ground up with the latest features and benefits required to compete in today's market. The clean design stands alone in the industry and is a testament to the quality, reliability, ease of installation and serviceability that goes into each unit. Outwardly, the large Rheem Commercial Series™ label (1) identifies the brand to the customer.

The sheet-metal cabinet (2) uses nothing less than 20-gauge material for structural components with an underlying coat of G90. To ensure the leak-proof integrity of these units, the design utilizes a top with a 1/8" drip lip (3), gasket-protected panels and screws. The (optional) hail guard protects the coil from hail damage (4). Every Rheem package unit uses the toughest finish in the industry, using electro deposition baked-on enamel tested to withstand a rigorous 1000-hour salt spray test, per ASTM B117.

Anything built to last must start with the right foundation. In this case, the foundation is 14-gauge, commercial-grade, full-perimeter base rails (5), which integrate fork slots and rigging holes to save set-up time on the job site. The base pan is stamped, which forms a 1-1/8" flange around the supply and return opening and has eliminated the worry of water entering the conditioned space (6). The drainpan (7) is made of material that resists the growth of harmful bacteria and is sloped for the latest IAQ benefits. Furthermore, the drainpan slides out for easy cleaning. The insulation has been placed on the underside of the basepan, removing areas that would allow for potential moisture accumulation, which can facilitate growth of harmful bacteria. All insulation is secured with both adhesive and mechanical fasteners, and all edges are hidden.



During development, each unit was tested to U.L. 1995, ANSI 21.47, AHRI 340-360 and other Rheem-required reliability tests. Rheem adheres to stringent ISO 9002 quality procedures, and each unit bears the U.L. and AHRI certification labels located on the unit nameplate (8). Contractors can rest assured that when a Rheem package unit arrives at the job, it is ready to go with a factory charge and quality checks.

Access to all major compartments is from the front of the unit, including the filter and electrical compartment, blower compartment, furnace section, and outdoor section. Each panel is permanently embossed with the compartment name (control/filter access, blower access and furnace access).

Electrical and filter compartment access is through a large, hinged-access panel. On the outside of the panel is the unit nameplate, which contains the model and serial number, electrical data and other important unit information.

The unit charging chart is located on the inside of the electrical and filter compartment door. Electrical wiring diagrams are found on the control box cover, which allows contractors to move them to more readable locations. To the right of the

control box the model and serial number can be found. Having this information on the inside will assure model identification for the life of the product. The production line quality test assurance label is also placed in this location (9). The two-inch throwaway filters (10) are easily removed on a tracked system for easy replacement.





Inside the control box ([11]), each electrical component is clearly identified with a label that matches the component to the wire diagram for ease of trouble shooting. All wiring is numbered on each end of the termination and color-coded to match the wiring diagram. The integrated furnace control, used to control furnace operation. incorporates a flashing LED troubleshooting device. Flash codes are clearly outlined on the unit wiring diagram. The control transformer has a low voltage circuit breaker that trips if a low voltage electrical short occurs. There is a blower contactor and a contactor for each compressor.



For added convenience in the field, a factory-installed convenience outlet and disconnect (12) are available. Low and High voltage can enter either from the side or through the base. Low-voltage connections are made through the low-voltage terminal strip. For ease of access, the U.L.-required low voltage barrier can be temporarily removed for low-voltage termination and then reinstalled. The high-voltage connection is terminated at the high-voltage




terminal block. The suggested mounting for the field-installed disconnect is on the exterior side of the electrical control box.

In the outdoor section are the external gauge ports. (13). With gauge ports mounted externally, an accurate diagnostic of system operation can be performed quickly and easily.



The blower compartment is to the right of the control box. To allow easy maintenance of the blower assembly, the entire assembly easily slides out by removing four #10 screws from the blower assembly. The adjustable motor pulley (14) can easily be adjusted by loosening the bolts on either side of the motor mount. Removing the bolts allows for easy removal of the blower pulley by pushing the blower assembly up to loosen the belt. Once the belt is removed, the motor sheave can be adjusted to the desired number of turns, ranging from 0 to 6 turns open. Where the demands for the job require high static, Rheem has high-static drives available that deliver nominal airflow up to 2" of static. By referring to the airflow performance tables listed in the installation instructions, proper static pressure and CFM requirements can be dialed in. The scroll housing (15) and blower scroll provide quiet and efficient airflow. The blower sheave is secured by an "H" bushing which firmly secures the

pulley to the blower shaft for years of troublefree operation. The "H" bushing allows for easy removal of the blower pulley from the shaft, as opposed to the use of a set screw, which can score the shaft, creating burrs that make blower-pulley removal difficult.



Also inside the blower compartment are the optional low-ambient controls ([16]). The low-ambient controls allow for operation of the compressor down to 0 degrees ambient temperature by cycling the outdoor fans on high pressure. Use of polarized plugs and schrader fittings allow for easy field or factory installation.


Inside the blower compartment the interlaced evaporator can also be viewed. The evaporator uses enhanced fin technology for maximum heat transfer. The capillary tube metering device assures even distribution of refrigerant throughout the evaporator.

Wiring throughout the unit is neatly bundled and routed. Where wire harnesses go through the condenser bulkhead or blower deck, a molded wire harness assembly (17) provides an air-tight and water-tight seal, and provides strain relief. Care is also taken to tuck raw



edges of insulation behind sheet metal to improve indoor air quality.


The furnace compartment contains the latest furnace technology on the market. The draft inducers (18) draw the flame from the Rheem exclusive in-shot burners (19) into the aluminized tubular heat exchanger (20) for clean, efficient gas heat. Stainless steel heat exchangers can be factory installed for those applications that have high fresh-air requirements, or applications in corrosive environments. Each furnace is equipment with a two-stage gas valve (21), which provides two stages of gas heat input. The first stage operates at 50% of the second stage (full fire). 81% steady state efficiency is maintained on both first and second stage by staging the multiple inducers to optimize the combustion airflow and maintain a near stoichiometric burn at each stage.




The direct spark igniter (22) assures reliable ignition in the most adverse conditions. This is coupled with remote flame sense (23) to assure that the flame has carried across the entire length of the burner assembly. Gas supply can be routed from the side or up through the base.

Each furnace has the following safety devices to assure consistent and reliable operation after ignition:

- Pressures switches (24) to assure adequate combustion airflow before ignition.
- Rollout switches (25) to assure no obstruction or cracks in the heat exchanger.
- A limit device that protects the furnace from over-temperature problems.






The compressor compartment houses the heartbeat of the unit. The scroll compressor (26) is known for its long life, and for reliable, quiet, and efficient operation. The suction and discharge lines are designed with shock loops (27) to absorb the strain and stress that the starting torque, steady state operation, and shut down cycle impose on the refrigerant tubing. Each compressor and circuit is independent for built-in redundancy, and each circuit is clearly marked throughout the system. Each unit has two stages of efficient cooling operation, first stage is approximately 50% of second stage.

The low-pressure switches (28) and high-pressure switches (29) are mounted on the appropriate refrigerant lines in the condenser section. The high-pressure switch will shut off the compressors if pressures exceeding 610 PSIG are detected as may occur if the outdoor fan motor fails. The low-pressure switches shut off the compressors if low pressure is detected due to loss of refrigerant charge. The optional freeze stats clip on the suction line above the compressor and wires into the low voltage plugs after removing a prewired jumper. The freeze stat protects the compressor if the evaporator coil gets too cold (below freezing) due to low airflow. Each factory-installed option is brazed into the appropriate high or low side and wired appropriately. Use of polarized plugs and schrader fittings allow for easy field installation.

The condenser fan motor (30) can easily be accessed and maintained by removing the protective fan grille. The polarized plug connection allows the motor to be changed quickly and eliminates the need to snake wires through the unit. The aluminum MicroChannel outdoor coil uses the latest enhanced fin design (31) for the most effective method of heat transfer with a reduction in refrigerant charge and unit weight. The outdoor coil is protected by optional louvered panels, which allow unobstructed airflow while protecting the unit from both Mother Nature and vandalism.



Each unit is designed for both downflow or horizontal applications (32) for job configuration flexibility. The return air com-




Each unit is pre-wired for the economizer to allow quick plug-in installation. The downflow economizer is also available as a factory-installed option. Power Exhaust is easily field-installed. The economizer, which provides free cooling when outdoor conditions are suitable and also provides fresh air to meet local requirements, comes standard with single enthalpy controls. The controls can be upgraded to dual enthalpy easily in the field. The direct drive actuator combined with gear drive dampers has eliminated the need for linkage adjustment in the field. The economizer control has a minimum position setpoint,


an outdoor-air setpoint, a mix-air setpoint, and a CO2 setpoint. Barometric relief is standard on all economizers. The power exhaust is housed in the barometric relief opening and is easily slipped in with a plug-in assembly.



The Rheem roofcurb (34) is made for toolless

assembly at the jobsite by inserting a pin into a hinge in each corner of the adjacent curb sides (35), which makes the assembly process quick and easy.





FACTORY INSTALLED OPTION CODES FOR RKKL-B 180/240

Option Code	Hail Guard	Stainless Steel Heat Exchanger	Non-Powered Convenience Outlet/ Unfused Service Disconnect	Low Ambient / Freeze Stat
AD	Х			
AJ		x		
AH			X	
AP				X
BF	X		X	
BG	X	X		
BY	X			X
JB		X	X	
CR	Х	X		X
DN	Х	Х	X	Х

[&]quot;x" indicates factory installed option.

ECONOMIZER SELECTION FOR RKKL-B 180/240

Option Code	No Economizer	Single Enthalpy Economizer* With Barometric Relief	Single Enthalpy Economizer* With Barometric Relief and Smoke Detector
A	Х		
F		х	
G			X

[&]quot;x" indicates factory installed option.

Instructions for Factory Installed Option(s) Selection

Note: Three characters following the model number will be utilized to designate a factory-installed option or combination of options. If no factory option(s) is required, nothing follows the model number.

Step 1. After a basic rooftop model is selected, choose a *two-character* option code from the FACTORY INSTALLED OPTION SELECTION TABLE.

Proceed to Step 2.

Step 2. The last option code character is utilized for factory-installed economizers. Choose a character from the FACTORY INSTALLED ECONOMIZER SELECTION TABLE.

Example: RKKL-B240CL40EXXX (where XX is factory installed option)

Example: No Options RKKL-B240CL40E

Example: No option with factory installed economizer

RKKL-B240CL40EAAF

Example: Options with low ambient and freeze stat, unwired convenience outlet, unfused service disconnect, hail guard, and stainless steel heat exchanger with no factory installed economizer

RKKL-B240CL40EDNA

Example: Options same as above with factory installed economizer

RKKL-B240CL40EDNF

^{*}Downflow economizer only.

To select an RKKL-B Cooling and Heating unit to meet a job requirement, follow this procedure, with example, using data supplied in this specification sheet.

DETERMINE COOLING AND HEATING REQUIREMENTS AND SPECIFIC OPERATING CONDITIONS FROM PLANS AND SPECS.

Example: Voltage-208/240V-3 Phase-60 Hz Total Cooling Capacity— 205,000 BTUH [60.0 kW] Sensible Cooling Capacity-155,000 BTUH [45.4 kW] 235,000 BTUH [68.8 kW] Heating Capacity-*Condenser Entering Air-95°F [35.0°C] DB *Evaporator Mixed Air Entering--65°F [18.3°C] WB; 78°F [25.6°C] DB *Indoor Air Flow (vertical)— 7200 CFM [3398 L/s] *External Static Pressure— .70 in. WG [.17 kPa]

2. SELECT UNIT TO MEET COOLING REQUIREMENTS.

Since total cooling is within the range of a nominal 20 ton [70.3 kW] unit, enter cooling performance table at 95°F [35.0 °C] DB condenser inlet air. Interpolate between 63°F [17.2 °C] WB and 67°F [19.4 °C] WB to determine total and sensible capacity and power input for 65°F [18.3 °C] WB evaporator inlet air at 7825 CFM [3692 L/s] indoor air flow (table basis):

Total Cooling Capacity = 245,500 BTUH [71.88 kW] Sensible Cooling Capacity = 201,150 BTUH [58.90 kW] Power Input (Compressor and Cond. Fans) = 19,750 watts

Use formula in note (1) to determine sensible capacity at 78°F [25.6 °C] DB evaporator entering air:

201,150 + (1.10 x 7,200 x (1 - 0.11) x (78 - 80)) Sensible Cooling Capacity = 187,052 BTUH [54.77 kW]

3. CORRECT CAPACITIES OF STEP 2 FOR ACTUAL AIR FLOW.

Select factors from airflow correction table at 7200 CFM [3398 L/s] and apply to data obtained in step 2 to obtain gross capacity:

Total Capacity = $245,500 \times 0.99 = 243,045$ BTUH [71.17 kW] Sensible Capacity = $187,052 \times 0.95 = 177,699$ BTUH [52.03 kW] Power Input = $19,750 \times 0.99 = 19,553$ Watts

These are Gross Capacities, not corrected for blower motor heat or power.

4. DETERMINE BLOWER SPEED AND WATTS TO MEET SYSTEM DESIGN.

Enter Indoor Blower performance table at 7200 CFM [3398 L/s]. Total ESP (external static pressure) per the spec of 0.70 in. WG [.17 kPa] includes the system duct and grilles. Add from the table "Component Air Resistance", 0.01 in. WG [.00 kPa]for wet coil, 0.08 in. WG [.02 kPa] for downflow air flow, for a total selection static pressure of 0.79 (0.8) in. WG [.20 kPa], and determine:

RPM = 741 WATTS = 2,895 DRIVE = L (standard 5 H.P. motor)

5. CALCULATE INDOOR BLOWER BTUH HEAT EFFECT FROM MOTOR WATTS, STEP 4.

 $2,895 \times 3.412 = 9,878 BTUH [2.89 kW]$

6. CALCULATE NET COOLING CAPACITIES, EQUAL TO GROSS CAPACITY, STEP 3, MINUS INDOOR BLOWER MOTOR HEAT.

Net Total Capacity = 243,045-9,878 = 233,167 BTUH [68.27 kW] Net Sensible Capacity = 177,699 - 9,878 = 167,821 BTUH [49.14 kW]

7. CALCULATE UNIT INPUT AND JOB EER.

Total Power Input = 19,553 (step 3) + 2,895 (step 4) = 22,448 Watts

EER = $\frac{\text{Net Total BTUH [kW] (step 6)}}{\text{Power Input, Watts (above)}} = \frac{233,167}{22,448} = 10.39$

8. SELECT UNIT HEATING CAPACITY.

From Physical Data Table read that gas heating output (input rating x efficiency) is:

Heating Capacity = 243,000 BTUH [71.2 kW]

9. CHOOSE MODEL RKKL-B240CL30E

*NOTE: These operating conditions are typical of a commercial application in a 95°F/79°F [35°C/26°C] design area with indoor design of 76°F [24°C] DB and 50% RH and 10% ventilation air, with the unit roof mounted and centered on the zone it conditions by ducts.

Model RKKL- Series	B180CL25E	B180CL35E	B180CM25E	B180CM35E
Cooling Performance ¹				CONTINUED ──➤
Gross Cooling Capacity Btu [kW]	174,000 [50.98]	174,000 [50.98]	174,000 [50.98]	174,000 [50.98]
EER/SEER2	10.9/NA	10.9/NA	10.9/NA	10.9/NA
Nominal CFM/AHRI Rated CFM [L/s]	6000/5500 [2831/2595]	6000/5500 [2831/2595]	6000/5500 [2831/2595]	6000/5500 [2831/2595]
AHRI Net Cooling Capacity Btu [kW]	170,000 [49.81]	170,000 [49.81]	170,000 [49.81]	170,000 [49.81]
Net Sensible Capacity Btu [kW]	125,400 [36.74]	125,400 [36.74]	125,400 [36.74]	125,400 [36.74]
Net Latent Capacity Btu [kW]	44,600 [13.07]	44,600 [13.07]	44,600 [13.07]	44,600 [13.07]
IEER3	11.1	11.1	11.1	11.1
Net System Power kW	15.6	15.6	15.6	15.6
Heating Performance (Gas) ⁴				
Heating Input Btu [kW] (1st Stage / 2nd Stage)	125,000/250,000 [36.62/73.25]	175,000/350,000 [51.27/102.55]] 125,000/250,000 [36.62/73.25]	175,000/350,000 [51.27/102.55]
Heating Output Btu [kW] (1st Stage / 2nd Stage)	101,500/203,000 [29.74/59.48]	142,000/284,000 [41.61/83.21]	101,500/203,000 [29.74/59.48]	142,000/284,000 [41.61/83.21]
Temperature Rise Range °F [°C] (1st / 2nd Stage)	15-45 [8.3-25] / 15-45 [8.3-25]	30-60 [16.7-33.3] / 30-60 [16.7-33.3]	15-45 [8.3-25] / 15-45 [8.3-25]	30-60 [16.7-33.3] / 30-60 [16.7-33.3]
Steady State Efficiency (%)	81	81	81	81
No. Burners	10	14	10	14
No. Stages	2	2	2	2
Gas Connection Pipe Size in. [mm]	0.75 [19]	0.75 [19]	0.75 [19]	0.75 [19]
Compressor	0.75 [18]	0.75 [18]	0.73 [18]	0.73 [18]
No./Type	2/Scroll	2/Scroll	2/Scroll	2/Scroll
Outdoor Sound Rating (dB) ⁵	91	91	91	91
Outdoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	MicroChannel	MicroChannel	MicroChannel	MicroChannel
MicroChannel Depth in. [mm]	1 [25.4]	1 [25.4]	1 [25.4]	1 [25.4]
Face Area sq. ft. [sq. m]	27.46 [2.55]	27.46 [2.55]	27.46 [2.55]	27.46 [2.55]
Rows / FPI [FPcm]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]
Indoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	Rifled	Rifled	Rifled	Rifled
Tube Size in. [mm]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]
Face Area sq. ft. [sq. m]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]
Rows / FPI [FPcm]	2 / 18 [7]	2 / 18 [7]	2 / 18 [7]	2 / 18 [7]
Refrigerant Control	Capillary Tubes	Capillary Tubes	Capillary Tubes	Capillary Tubes
Drain Connection No./Size in. [mm]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]
Outdoor Fan—Type	Propeller	Propeller	Propeller	Propeller
No. Used/Diameter in. [mm]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]
Drive Type/No. Speeds	Direct/1	Direct/1	Direct/1	Direct/1
CFM [L/s]	10000 [4719]	10000 [4719]	10000 [4719]	10000 [4719]
No. Motors/HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP
Motor RPM	1075	1075	1075	1075
Indoor Fan—Type	FC Centrifugal	FC Centrifugal	FC Centrifugal	FC Centrifugal
No. Used/Diameter in. [mm]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]
Drive Type/No. Speeds	Belt/Variable	Belt/Variable	Belt/Variable	Belt/Variable
No. Motors	1	1	1	1
Motor HP	3	3	5	5
Motor RPM	1725	1725	1725	1725
Motor Frame Size	56	56	184	184
Filter—Type	Disposable	Disposable	Disposable	Disposable
Furnished	Yes	Yes	Yes	Yes
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]
Refrigerant Charge Oz. [g]	115/119 [3260/3374]	115/119 [3260/3374]	115/119 [3260/3374]	115/119 [3260/3374]
Weights			· · ·	
Net Weight Ibs. [kg]	1799 [816]	1812 [822]	1828 [829]	1841 [835]
Ship Weight lbs. [kg]	1926 [874]	1939 [880]	1955 [887]	1968 [893]
See Page 18 for Notes.				nates Metric Conversions

See Page 18 for Notes.





Model RKKL- Series	B180DL25E	B180DL35E	B180DM25E	B180DM35E
Cooling Performance ¹	510052202	510052002	BIOGRAFICE	CONTINUED>
Gross Cooling Capacity Btu [kW]	174,000 [50.98]	174,000 [50.98]	174,000 [50.98]	174,000 [50.98]
EER/SEER2	174,000 [30.90] 10.9/NA	174,000 [30.90] 10.9/NA	174,000 [30.90] 10.9/NA	174,000 [30.30] 10.9/NA
Nominal CFM/AHRI Rated CFM [L/s]	6000/5500 [2831/2595]	6000/5500 [2831/2595]	6000/5500 [2831/2595]	6000/5500 [2831/2595]
AHRI Net Cooling Capacity Btu [kW]	170,000 [49.81]	170,000 [49.81]	170,000 [49.81]	170,000 [49.81]
Net Sensible Capacity Btu [kW]	125,400 [36.74]	125,400 [36.74]	125,400 [36.74]	125,400 [36.74]
Net Latent Capacity Btu [kW]	44,600 [13.07]	44,600 [13.07]	44,600 [13.07]	44,600 [13.07]
IEER3	11.1	11.1	11.1	11.1
Net System Power kW	15.6	15.6	15.6	15.6
Heating Performance (Gas) ⁴				
Heating Input Btu [kW] (1st Stage / 2nd Stage)			125,000/250,000 [36.62/73.25]	
Heating Output Btu [kW] (1st Stage / 2nd Stage)	101,500/203,000 [29.74/59.48]	142,000/284,000 [41.61/83.21]	101,500/203,000 [29.74/59.48]	142,000/284,000 [41.61/83.21]
Temperature Rise Range °F [°C] (1st / 2nd Stage)	15-45 [8.3-25] / 15-45 [8.3-25]	30-60 [16.7-33.3] / 30-60 [16.7-33.3]	15-45 [8.3-25] / 15-45 [8.3-25]	30-60 [16.7-33.3] / 30-60 [16.7-33.3]
Steady State Efficiency (%)	81	81	81	81
No. Burners	10	14	10	14
No. Stages	2	2	2	2
Gas Connection Pipe Size in. [mm]	0.75 [19]	0.75 [19]	0.75 [19]	0.75 [19]
Compressor	[.]	[.]	[.]	
No./Type	2/Scroll	2/Scroll	2/Scroll	2/Scroll
Outdoor Sound Rating (dB) ⁵	91	91	91	91
Outdoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	MicroChannel	MicroChannel	MicroChannel	MicroChannel
MicroChannel Depth in. [mm]	1 [25.4]	1 [25.4]	1 [25.4]	1 [25.4]
Face Area sq. ft. [sq. m]	27.46 [2.55]	27.46 [2.55]	27.46 [2.55]	27.46 [2.55]
Rows / FPI [FPcm]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]
Indoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	Rifled	Rifled	Rifled	Rifled
Tube Size in. [mm]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]
Face Area sq. ft. [sq. m]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]
Rows / FPI [FPcm]	2 / 18 [7]	2 / 18 [7]	2 / 18 [7]	2 / 18 [7]
Refrigerant Control	Capillary Tubes	Capillary Tubes	Capillary Tubes	Capillary Tubes
Drain Connection No./Size in. [mm]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]
Outdoor Fan—Type	Propeller	Propeller	Propeller	Propeller
No. Used/Diameter in. [mm]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]
Drive Type/No. Speeds	Direct/1	Direct/1	Direct/1	Direct/1
CFM [L/s]	10000 [4719]	10000 [4719]	10000 [4719]	10000 [4719]
No. Motors/HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP
Motor RPM	1075	1075	1075	1075
Indoor Fan—Type	FC Centrifugal	FC Centrifugal	FC Centrifugal	FC Centrifugal
No. Used/Diameter in. [mm]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]
Drive Type/No. Speeds	Belt/Variable	Belt/Variable	Belt/Variable	Belt/Variable
No. Motors	1	1	1	1
Motor HP	3	3	5	5
Motor RPM	1725	1725	1725	1725
Motor Frame Size	56	56	184	184
Filter—Type	Disposable	Disposable	Disposable	Disposable
Furnished	Yes	Yes	Yes	Yes
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]
Refrigerant Charge Oz. [g]	115/119 [3260/3374]	115/119 [3260/3374]	115/119 [3260/3374]	115/119 [3260/3374]
Weights				
Net Weight lbs. [kg]	1799 [816]	1812 [882]	1828 [829]	1841 [835]
Ship Weight lbs. [kg]	1926 [874]	1939 [880]	1955 [887]	1968 [893]
See Page 18 for Notes.			[] Design	nates Metric Conversions

See Page 18 for Notes.



Model RKKL- Series	B180YL35E	B180YM35E	B240CL30E	B240CL40E
Cooling Performance ¹				CONTINUED
Gross Cooling Capacity Btu [kW]	174,000 [50.98]	174,000 [50.98]	250,000 [73.25]	250,000 [73.25]
EER/SEER ²	10.9/NA	10.9/NA	10.5/NA	10.5/NA
Nominal CFM/AHRI Rated CFM [L/s]	6000/5500 [2831/2595]	6000/5500 [2831/2595]	8000/7825 [3775/3693]	8000/7825 [3775/3693]
AHRI Net Cooling Capacity Btu [kW]	170,000 [49.81]	170,000 [49.81]	240,000 [70.32]	240,000 [70.32]
Net Sensible Capacity Btu [kW]	125,400 [36.74]	125,400 [36.74]	175,000 [51.27]	175,000 [51.27]
Net Latent Capacity Btu [kW]	44,600 [13.07]	44,600 [13.07]	65,000 [19.04]	65,000 [19.04]
IEER3	11.1	11.1	10.5	10.5
Net System Power kW	15.6	15.6	22.88	22.88
Heating Performance (Gas)4	13.0	13.0	22.00	22.00
Heating Input Btu [kW] (1st Stage / 2nd Stage)	175 000/250 000 (51 27/102 55)	175 000/250 000 [51 27/102 55]	150 000/200 000 [42 05/97 0]	200 000/400 000 [59 6/117 2]
Heating Output Btu [kW] (1st Stage / 2nd Stage)				
Temperature Rise Range °F [°C]	30-60 [16.7-33.3] /	30-60 [16.7-33.3] /	15-45 [8.3-25] /	25-55 [13.9-30.6] /
(1st / 2nd Stage)	30-60 [16.7-33.3]	30-60 [16.7-33.3]	15-45 [8.3-25]	25-55 [13.9-30.6]
Steady State Efficiency (%)	81	81	81	81
No. Burners	14	14	12	14
No. Stages	2	2	2	2
Gas Connection Pipe Size in. [mm]	0.75 [19]	0.75 [19]	0.75 [19]	0.75 [19]
Compressor				
No./Type	2/Scroll	2/Scroll	2/Scroll	2/Scroll
Outdoor Sound Rating (dB) ⁵	91	91	91	91
Outdoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	MicroChannel	MicroChannel	MicroChannel	MicroChannel
MicroChannel Depth in. [mm]	1 [25.4]	1 [25.4]	1 [25.4]	1 [25.4]
Face Area sq. ft. [sq. m]	27.46 [2.55]	27.46 [2.55]	50.8 [4.72]	50.8 [4.72]
Rows / FPI [FPcm]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]
Indoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	Rifled	Rifled	Rifled	Rifled
Tube Size in. [mm]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]
Face Area sq. ft. [sq. m]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]
Rows / FPI [FPcm]	2 / 18 [7]	2 / 18 [7]	3 / 13 [5]	3 / 13 [5]
Refrigerant Control	Capillary Tubes	Capillary Tubes	Capillary Tubes	Capillary Tubes
Drain Connection No./Size in. [mm]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]
Outdoor Fan—Type	Propeller	Propeller	Propeller	Propeller
No. Used/Diameter in. [mm]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]
Drive Type/No. Speeds	Direct/1	Direct/1	Direct/1	Direct/1
CFM [L/s]	10000 [4719]	10000 [4719]	10000 [4719]	10000 [4719]
No. Motors/HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP
Motor RPM	1075	1075	1075	1075
Indoor Fan—Type	FC Centrifugal	FC Centrifugal	FC Centrifugal	FC Centrifugal
No. Used/Diameter in. [mm]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]
Drive Type/No. Speeds	Belt/Variable	Belt/Variable	Belt/Variable	Belt/Variable
No. Motors	1	1	1	1
Motor HP	3	5	5	5
Motor RPM	1725	1725	1725	1725
Motor Frame Size	56	184	184	184
Filter—Type	Disposable	Disposable	Disposable	Disposable
Furnished	Yes	Yes	Yes	Yes
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]
Refrigerant Charge Oz. [g]	115/119 [3260/3374]	115/119 [3260/3374]	200/219 [5670/6209]	200/219 [5670/6209]
Weights	[3230,007 1]		200,2.0 [0010,0200]	200,2.0 [00/0/0200]
Net Weight lbs. [kg]	1827 [829]	1856 [841]	2021 [917]	2035 [923]
Ship Weight lbs. [kg]	1954 [886]	1983 [899]	2021 [917]	2162 [981]
See Page 18 for Notes.	1000]	1000 [000]		anates Metric Conversions

See Page 18 for Notes.





Model RKKL- Series	B240CM30E	B240CM40E	B240CN30E	B240CN40E
Cooling Performance ¹				CONTINUED
Gross Cooling Capacity Btu [kW]	250,000 [73.25]	250,000 [73.25]	250,000 [73.25]	250,000 [73.25]
EER/SEER2	10.5/NA	10.5/NA	10.5/NA	10.5/NA
Nominal CFM/AHRI Rated CFM [L/s]	8000/7825 [3775/3693]	8000/7825 [3775/3693]	8000/7825 [3775/3693]	8000/7825 [3775/3693]
AHRI Net Cooling Capacity Btu [kW]	240,000 [70.32]	240,000 [70.32]	240,000 [70.32]	240,000 [70.32]
Net Sensible Capacity Btu [kW]	175,000 [51.27]	175,000 [51.27]	175,000 [51.27]	175,000 [51.27]
Net Latent Capacity Btu [kW]	65,000 [19.04]	65,000 [19.04]	65,000 [19.04]	65,000 [19.04]
IEER3	10.5	10.5	10.5	10.5
Net System Power kW	22.88	22.88	22.88	22.88
leating Performance (Gas) ⁴	22.00	22.00	22.00	22.00
Heating Input Btu [kW] (1st Stage / 2nd Stage)	150 000/300 000 [/3 05/87 0]	200,000/400,000 [58.6/117.2]	150 000/300 000 [//3 05/87 0]	200,000/400,000 [58.6/117.2
Heating Output Btu [kW] (1st Stage / 2nd Stage)				•
Temperature Rise Range °F [°C]	15-45 [8.3-25] /	25-55 [13.9-30.6] /	15-45 [8.3-25] /	25-55 [13.9-30.6] /
(1st / 2nd Stage)	15-45 [8.3-25]	25-55 [13.9-30.6]	15-45 [8.3-25]	25-55 [13.9-30.6]
Steady State Efficiency (%)	81	81	81	81
No. Burners	12	14	12	14
No. Stages	2	2	2	2
Gas Connection Pipe Size in. [mm]	0.75 [19]	0.75 [19]	0.75 [19]	0.75 [19]
ompressor				
No./Type	2/Scroll	2/Scroll	2/Scroll	2/Scroll
utdoor Sound Rating (dB) ⁵	91	91	91	91
utdoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	MicroChannel	MicroChannel	MicroChannel	MicroChannel
MicroChannel Depth in. [mm]	1 [25.4]	1 [25.4]	1 [25.4]	1 [25.4]
Face Area sq. ft. [sq. m]	50.8 [4.72]	50.8 [4.72]	50.8 [4.72]	50.8 [4.72]
Rows / FPI [FPcm]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]
door Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	Rifled	Rifled	Rifled	Rifled
Tube Size in. [mm]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]
Face Area sq. ft. [sq. m]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]
Rows / FPI [FPcm]	3 / 13 [5]	3 / 13 [5]	3 / 13 [5]	3 / 13 [5]
Refrigerant Control	Capillary Tubes	Capillary Tubes	Capillary Tubes	Capillary Tubes
Drain Connection No./Size in. [mm]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]
utdoor Fan—Type	Propeller	Propeller	Propeller	Propeller
No. Used/Diameter in. [mm]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]
Drive Type/No. Speeds	Direct/1	Direct/1	Direct/1	Direct/1
CFM [L/s]	10000 [4719]	10000 [4719]	10000 [4719]	10000 [4719]
No. Motors/HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP
Motor RPM	1075	1075	1075	1075
idoor Fan—Type	FC Centrifugal	FC Centrifugal	FC Centrifugal	FC Centrifugal
No. Used/Diameter in. [mm]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]
Drive Type/No. Speeds	Belt/Variable	Belt/Variable	Belt/Variable	Belt/Variable
No. Motors	1	1	1	1
Motor HP	7 1/2	7 1/2	7 1/2	7 1/2
Motor RPM	1725	1725	1725	1725
	213	213	213	213
Motor Frame Size	Z13 Disposable			
ilter—Type	•	Disposable	Disposable	Disposable
Furnished (NO.) Size Recommended in [mm v mm v mm]	Yes (9)2y25y20 (51y625y509)	Yes (9)2y25y20 [51y625y509]	Yes (8)2y25y20 [51y625y508]	Yes (8)2y25y20 [51y625y508]
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]
Refrigerant Charge Oz. [g]	200/219 [5670/6209]	200/219 [5670/6209]	200/219 [5670/6209]	200/219 [5670/6209]
Veights	0050 500 5	0070 1010	0057	0070 70 70
Net Weight lbs. [kg]	2059 [934]	2073 [940]	2057 [933]	2072 [940]
Ship Weight lbs. [kg]	2185 [991]	2200 [998]	2184 [991]	2198 [997]

See Page 18 for Notes.



Model RKKL- Series	B240DL30E	B240DL40E	B240DM30E	B240DM40E
Cooling Performance ¹				CONTINUED -
Gross Cooling Capacity Btu [kW]	250,000 [73.25]	250,000 [73.25]	250,000 [73.25]	250,000 [73.25]
EER/SEER2	10.5/NA	10.5/NA	10.5/NA	10.5/NA
Nominal CFM/AHRI Rated CFM [L/s]	8000/7825 [3775/3693]	8000/7825 [3775/3693]	8000/7825 [3775/3693]	8000/7825 [3775/3693]
AHRI Net Cooling Capacity Btu [kW]	240,000 [70.32]	240,000 [70.32]	240,000 [70.32]	240,000 [70.32]
Net Sensible Capacity Btu [kW]	175,000 [51.27]	175,000 [51.27]	175,000 [51.27]	175,000 [51.27]
Net Latent Capacity Btu [kW]	65,000 [19.04]	65,000 [19.04]	65,000 [19.04]	65,000 [19.04]
IEER3	10.5	10.5	10.5	10.5
Net System Power kW	22.88	22.88	22.88	22.88
leating Performance (Gas) ⁴				
-	150.000/300.000 [43.95/87.9]	200,000/400,000 [58.6/117.2]	150.000/300.000 [43.95/87.9]	200,000/400,000 [58.6/117.
Heating Output Btu [kW] (1st Stage / 2nd Stage)		-	121,500/243,000 [35.6/71.2]	
Temperature Rise Range °F [°C] (1st / 2nd Stage)	15-45 [8.3-25] / 15-45 [8.3-25]	25-55 [13.9-30.6] / 25-55 [13.9-30.6]	15-45 [8.3-25] / 15-45 [8.3-25]	25-55 [13.9-30.6] / 25-55 [13.9-30.6]
Steady State Efficiency (%)	81	81	81	81
No. Burners	12	14	12	14
No. Stages	2	2	2	2
Gas Connection Pipe Size in. [mm]	0.75 [19]	0.75 [19]	0.75 [19]	0.75 [19]
Compressor	0.70 [10]	0.70 [10]	0.70 [10]	0.70 [10]
No./Type	2/Scroll	2/Scroll	2/Scroll	2/Scroll
Outdoor Sound Rating (dB)5	91	91	91	91
Outdoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	MicroChannel	MicroChannel	MicroChannel	MicroChannel
MicroChannel Depth in. [mm]	1 [25.4]	1 [25.4]	1 [25.4]	1 [25.4]
Face Area sq. ft. [sq. m]	50.8 [4.72]	50.8 [4.72]	50.8 [4.72]	50.8 [4.72]
Rows / FPI [FPcm]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]
ndoor Coil—Fin Type Tube Type	Louvered Rifled	Louvered Rifled	Louvered Rifled	Louvered Rifled
Tube Size in. [mm]		0.375 [9.5]		
Face Area sq. ft. [sq. m]	0.375 [9.5]		0.375 [9.5]	0.375 [9.5]
	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]
Rows / FPI [FPcm]	3 / 13 [5] Capillary Tubes	3 / 13 [5]	3 / 13 [5]	3 / 13 [5]
Refrigerant Control	' '	Capillary Tubes	Capillary Tubes	Capillary Tubes
Drain Connection No./Size in. [mm]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]
Outdoor Fan—Type	Propeller	Propeller	Propeller	Propeller
No. Used/Diameter in. [mm]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]
Drive Type/No. Speeds	Direct/1	Direct/1	Direct/1	Direct/1
CFM [L/s]	10000 [4719]	10000 [4719]	10000 [4719]	10000 [4719]
No. Motors/HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP
Motor RPM	1075	1075	1075	1075
ndoor Fan—Type	FC Centrifugal	FC Centrifugal	FC Centrifugal	FC Centrifugal
No. Used/Diameter in. [mm]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]
Drive Type/No. Speeds	Belt/Variable	Belt/Variable	Belt/Variable	Belt/Variable
No. Motors	1	1	1	1
Motor HP	5	5	7 1/2	7 1/2
Motor RPM	1725	1725	1725	1725
Motor Frame Size	184	184	184	213
Filter—Type	Disposable	Disposable	Disposable	Disposable
Furnished	Yes	Yes	Yes	Yes
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]
Refrigerant Charge Oz. [g]	200/219 [5670/6209]	200/219 [5670/6209]	200/219 [5670/6209]	200/219 [5670/6209]
Weights				
Net Weight lbs. [kg]	2021 [917]	2073 [940]	2059 [934]	2073 [940]
Ship Weight lbs. [kg]	2147 [974]	2200 [998]	2185 [991]	2200 [998]

See Page 18 for Notes.





Model RKKL- Series	B240DN30E	B240DN40E	B240YL40E	B240YM40E
Cooling Performance ¹				CONTINUED
Gross Cooling Capacity Btu [kW]	250,000 [73.25]	250,000 [73.25]	250,000 [73.25]	250,000 [73.25]
EER/SEER2	10.5/NA	10.5/NA	10.5/NA	10.5/NA
Nominal CFM/AHRI Rated CFM [L/s]	8000/7825 [3775/3693]	8000/7825 [3775/3693]	8000/7825 [3775/3693]	8000/7825 [3775/3693]
AHRI Net Cooling Capacity Btu [kW]	240,000 [70.32]	240,000 [70.32]	240,000 [70.32]	240,000 [70.32]
Net Sensible Capacity Btu [kW]	175,000 [51.27]	175,000 [51.27]	175,000 [51.27]	175,000 [51.27]
Net Latent Capacity Btu [kW]	65,000 [19.04]	65,000 [19.04]	65,000 [19.04]	65,000 [19.04]
IEER3	10.5	10.5	10.5	10.5
Net System Power kW	22.88	22.88	22.88	22.88
Heating Performance (Gas) ⁴				
- , ,	150 000/300 000 [43 95/87 9]	200 000/400 000 [58 6/117 2]	200,000/400,000 [58.6/117.2]	200 000/400 000 [58 6/117
Heating Output Btu [kW] (1st Stage / 2nd Stage)				· · · · ·
Temperature Rise Range °F [°C] (1st / 2nd Stage)	15-45 [8.3-25] / 15-45 [8.3-25]	25-55 [13.9-30.6] / 25-55 [13.9-30.6]	25-55 [13.9-30.6] / 25-55 [13.9-30.6]	25-55 [13.9-30.6] / 25-55 [13.9-30.6]
Steady State Efficiency (%)	81	81	81	81
No. Burners	12	14	14	14
No. Stages	2	2	2	2
Gas Connection Pipe Size in. [mm]	0.75 [19]	0.75 [19]	0.75 [19]	0.75 [19]
ompressor No (Time	0/01	0/0	0/0	0/0
No./Type	2/Scroll 91	2/Scroll	2/Scroll	2/Scroll
Outdoor Sound Rating (dB) ⁵		91	91	91
outdoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	MicroChannel	MicroChannel	MicroChannel	MicroChannel
MicroChannel Depth in. [mm]	1 [25.4]	1 [25.4]	1 [25.4]	1 [25.4]
Face Area sq. ft. [sq. m]	50.8 [4.72]	50.8 [4.72]	50.8 [4.72]	50.8 [4.72]
Rows / FPI [FPcm]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]	1 / 23 [9]
ndoor Coil—Fin Type	Louvered	Louvered	Louvered	Louvered
Tube Type	Rifled	Rifled	Rifled	Rifled
Tube Size in. [mm]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]	0.375 [9.5]
Face Area sq. ft. [sq. m]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]	26.67 [2.48]
Rows / FPI [FPcm]	3 / 13 [5]	3 / 13 [5]	3 / 13 [5]	3 / 13 [5]
Refrigerant Control	Capillary Tubes	Capillary Tubes	Capillary Tubes	Capillary Tubes
Drain Connection No./Size in. [mm]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]	1/1 [25.4]
Outdoor Fan—Type	Propeller	Propeller	Propeller	Propeller
No. Used/Diameter in. [mm]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]	3/24 [609.6]
Drive Type/No. Speeds	Direct/1	Direct/1	Direct/1	Direct/1
CFM [L/s]	10000 [4719]	10000 [4719]	10000 [4719]	10000 [4719]
No. Motors/HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP	3 at 1/2 HP
Motor RPM	1075	1075	1075	1075
ndoor Fan—Type	FC Centrifugal	FC Centrifugal	FC Centrifugal	FC Centrifugal
No. Used/Diameter in. [mm]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]	2/18x9 [457x229]
Drive Type/No. Speeds	Belt/Variable	Belt/Variable	Belt/Variable	Belt/Variable
No. Motors	1	1	1	1
Motor HP	7 1/2	7 1/2	5	7 1/2
Motor RPM	1725	1725	1725	1725
Motor Frame Size	184	213	184	213
ilter—Type	Disposable	Disposable	Disposable	Disposable
Furnished	Yes	Yes	Yes	Yes
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]	(8)2x25x20 [51x635x508]
Refrigerant Charge Oz. [g]	200/219 [5670/6209]	200/219 [5670/6209]	200/219 [5670/6209]	200/219 [5670/6209]
Weights	200/213 [30/0/0203]	200/213 [30/0/0203]	200/213 [30/0/0203]	200/213 [30/0/0203]
-	2057 [022]	2072 [040]	2022 [022]	2002 10401
Net Weight lbs. [kg]	2057 [933]	2072 [940]	2055 [932]	2093 [949]
Ship Weight lbs. [kg]	2184 [991]	2198 [997]	2182 [990]	2220 [1007]

See Page 18 for Notes.



Model RKKL- Series	B240YN40E	
Cooling Performance ¹		
Gross Cooling Capacity Btu [kW]	250,000 [73.25]	
EER/SEER2	10.5/NA	
Nominal CFM/AHRI Rated CFM [L/s]	8000/7825 [3775/3693]	
AHRI Net Cooling Capacity Btu [kW]	240,000 [70.32]	
Net Sensible Capacity Btu [kW]	175,000 [51.27]	
Net Latent Capacity Btu [kW]	65,000 [19.04]	
IEER3	10.5	
Net System Power kW	22.88	
Heating Performance (Gas) ⁴		
Heating Input Btu [kW] (1st Stage / 2nd Stage)	200,000/400,000 [58.6/117.2]	
Heating Output Btu [kW] (1st Stage / 2nd Stage)		
Temperature Rise Range °F [°C]	25-55 [13.9-30.6] /	
(1st / 2nd Stage)	25-55 [13.9-30.6]	
Steady State Efficiency (%)	81	
No. Burners	14	
No. Stages	2	
Gas Connection Pipe Size in. [mm]	0.75 [19]	
Compressor		
No./Type	2/Scroll	
Outdoor Sound Rating (dB) ⁵	91	
Outdoor Coil—Fin Type	Louvered	
Tube Type	MicroChannel	
MicroChannel Depth in. [mm]	1 [25.4]	
Face Area sq. ft. [sq. m]	50.8 [4.72]	
Rows / FPI [FPcm]	1 / 23 [9]	
Indoor Coil—Fin Type	Louvered	
Tube Type	Rifled	
Tube Size in. [mm]	0.375 [9.5]	
Face Area sq. ft. [sq. m]	26.67 [2.48]	
Rows / FPI [FPcm]	3 / 13 [5]	
Refrigerant Control	Capillary Tubes	
Drain Connection No./Size in. [mm]	1/1 [25.4]	
Outdoor Fan—Type	Propeller	
No. Used/Diameter in. [mm]	3/24 [609.6]	
Drive Type/No. Speeds	Direct/1	
CFM [L/s]	10000 [4719]	
No. Motors/HP	3 at 1/2 HP	
Motor RPM	1075	
Indoor Fan—Type	FC Centrifugal	
No. Used/Diameter in. [mm]	2/18x9 [457x229]	
Drive Type/No. Speeds	Belt/Variable	
No. Motors	1	
Motor HP	7 1/2	
Motor RPM	1725	
Motor Frame Size	213	
Filter—Type	Disposable	
Furnished	Yes	
(NO.) Size Recommended in. [mm x mm x mm]	(8)2x25x20 [51x635x508]	
Refrigerant Charge Oz. [g]	200/219 [5670/6209]	
Weights	200,2.0 [0010,0200]	
ar organia		
Net Weight Ihs [kg]	2002 [040]	
Net Weight lbs. [kg] Ship Weight lbs. [kg]	2092 [949] 2218 [1006]	





NOTES:

- 1. Cooling Performance is rated at 95° F ambient, 80° F entering dry bulb, 67° F entering wet bulb. Gross capacity does not include the effect of fan motor heat. AHRI capacity is net and includes the effect of fan motor heat. Units are suitable for operation to ±20% of nominal cfm. Units are certified in accordance with the Unitary Air Conditioner Equipment certification program, which is based on AHRI Standard 210/240 or 340/360.
- 2. EER and/or SEER are rated at AHRI conditions and in accordance with DOE test procedures.
- 3. IEER is rated in accordance with AHRI Standard 340/360.
- 4. Heating Performance limit settings and rating data were established and approved under laboratory test conditions using American National Standard Institute standards. Ratings shown are for elevations up to 2000 feet. For elevations above 2000 feet, ratings should be reduced at the rate of 4% for each 1000 feet above sea level.
- 5. Outdoor Sound Rating shown is tested in accordance with AHRI Standard 270.

GROSS SYSTEMS PERFORMANCE DATA—B180

	ENTERING INDOOR AIR @ 80°F [26.7°C] dbe ①										
	wbE 71°F [21.7°C] 67°F [19.4°C] 63°F [17.2°C]			63°F [17.2°C]							
		FM [L/s]	7200 [3398]	5500 [2596]	4800 [2265]	7200 [3398]	5500 [2596]	4800 [2265]	7200 [3398]	5500 [2596]	4800 [2265]
		DR ①	0.04	0.1	0.13	0.04	0.1	0.13	0.04	0.1	0.13
0	75 [23.9]	Total BTUH [kW] Sens BTUH [kW] Power	205.5 [60.2] 133.5 [39.1] 12.1	194.6 [57.0] 105.8 [31.0] 11.8	190.1 [55.7] 95.3 [27.9] 11.7	197.3 [57.8] 162.0 [47.5] 12.0	186.8 [54.7] 131.1 [38.4] 11.6	182.5 [53.5] 119.3 [35.0] 11.5	190.6 [55.9] 184.8 [54.2] 11.8	180.5 [52.9] 151.4 [44.4] 11.5	176.3 [51.7] 138.5 [40.6] 11.3
U T D	80 [26.7]	Total BTUH [kW] Sens BTUH [kW] Power	203.2 [59.6] 134.3 [39.4] 12.7	192.4 [56.4] 106.6 [31.3] 12.4	187.9 [55.1] 96.0 [28.1] 12.2	194.9 [57.1] 162.7 [47.7] 12.5	184.6 [54.1] 131.9 [38.7] 12.2	180.3 [52.8] 120.0 [35.2] 12.1	188.3 [55.2] 185.6 [54.4] 12.4	178.3 [52.3] 152.2 [44.6] 12.0	174.1 [51.0] 139.2 [40.8] 11.9
O R D	85 [29.4]	Total BTUH [kW] Sens BTUH [kW] Power	200.3 [58.7] 134.3 [39.4] 13.4	189.7 [55.6] 106.8 [31.3] 13.0	185.3 [54.3] 96.3 [28.2] 12.9	192.1 [56.3] 162.8 [47.7] 13.2	181.8 [53.3] 132.0 [38.7] 12.8	177.6 [52.0] 120.2 [35.2] 12.7	185.4 [54.3] 185.4 [54.3] 13.0	175.5 [51.4] 152.3 [44.6] 12.7	171.5 [50.3] 139.5 [40.9] 12.5
R Y B	90 [32.2]	Total BTUH [kW] Sens BTUH [kW] Power	196.9 [57.7] 133.5 [39.1] 14.0	186.4 [54.6] 106.2 [31.1] 13.7	182.1 [53.4] 95.8 [28.1] 13.5	188.6 [55.3] 161.9 [47.5] 13.9	178.6 [52.3] 131.5 [38.5] 13.5	174.5 [51.1] 119.8 [35.1] 13.3	182.0 [53.3] 182.0 [53.3] 13.7	172.3 [50.5] 151.8 [44.5] 13.3	168.3 [49.3] 139.0 [40.7] 13.2
U L B	95 [35]	Total BTUH [kW] Sens BTUH [kW] Power	192.9 [56.5] 131.8 [38.6] 14.8	182.6 [53.5] 104.9 [30.8] 14.4	178.4 [52.3] 94.7 [27.8] 14.2	184.6 [54.1] 160.2 [47.0] 14.6	174.8 [51.2] 130.2 [38.2] 14.2	170.8 [50.1] 118.7 [34.8] 14.0	178.0 [52.2] 178.0 [52.2] 14.4	168.5 [49.4] 150.5 [44.1] 14.0	164.6 [48.2] 137.9 [40.4] 13.9
E M P E	100 [37.8]	Total BTUH [kW] Sens BTUH [kW] Power	188.4 [55.2] 129.3 [37.9] 15.5	178.3 [52.3] 102.9 [30.2] 15.1	174.2 [51.1] 92.9 [27.2] 14.9	180.1 [52.8] 157.8 [46.3] 15.3	170.5 [50.0] 128.3 [37.6] 14.9	166.6 [48.8] 117.0 [34.3] 14.8	173.4 [50.8] 173.4 [50.8] 15.2	164.2 [48.1] 148.6 [43.6] 14.8	160.4 [47.0] 136.2 [39.9] 14.6
R A T U	105 [40.6]	Total BTUH [kW] Sens BTUH [kW] Power	183.3 [53.7] 126.0 [36.9] 16.3	173.5 [50.8] 100.3 [29.4] 15.9	169.5 [49.7] 90.6 [26.6] 15.7	175.0 [51.3] 154.5 [45.3] 16.1	165.7 [48.6] 125.7 [36.8] 15.7	161.9 [47.4] 114.7 [33.6] 15.5	168.3 [49.3] 168.3 [49.3] 16.0	159.4 [46.7] 146.0 [42.8] 15.5	155.7 [45.6] 133.8 [39.2] 15.4
R E °F [°C]	110 [43.3]	Total BTUH [kW] Sens BTUH [kW] Power	177.6 [52.0] 121.9 [35.7] 17.1	168.2 [49.3] 97.1 [28.5] 16.7	164.3 [48.2] 87.7 [25.7] 16.5	169.4 [49.6] 150.4 [44.1] 17.0	160.4 [47.0] 122.4 [35.9] 16.5	156.6 [45.9] 111.6 [32.7] 16.3	162.7 [47.7] 162.7 [47.7] 16.8	154.0 [45.1] 142.6 [41.8] 16.4	150.5 [44.1] 130.8 [38.3] 16.2
[O	115 [46.1]	Total BTUH [kW] Sens BTUH [kW] Power	171.4 [50.2] 116.8 [34.2] 18.0	162.3 [47.6] 93.0 [27.3] 17.5	158.6 [46.5] 84.0 [24.6] 17.4	163.2 [47.8] 145.3 [42.6] 17.9	154.5 [45.3] 118.3 [34.7] 17.4	150.9 [44.2] 107.9 [31.6] 17.2	156.5 [45.9] 156.5 [45.9] 17.7	148.2 [43.4] 138.6 [40.6] 17.2	144.8 [42.4] 127.2 [37.3] 17.0

GROSS SYSTEMS PERFORMANCE DATA—B240

	ENTERING INDOOR AIR @ 80°F [26.7°C] dbE ①										
		wbE		71°F [21.7°C]			67°F [19.4°C]		63°F [17.2°C]		
		M [L/s]	9600 [4531]	7825 [3693]	6400 [3020]	9600 [4531]	7825 [3693]	6400 [3020]	9600 [4531]	7825 [3693]	6400 [3020]
		DR ①	0.06	0.11	0.15	0.06	0.11	0.15	0.06	0.11	0.15
	75 [23.9]	Total BTUH [kW] Sens BTUH [kW] Power	295.2 [86.5] 188.5 [55.3] 17.0	283.5 [83.1] 158.8 [46.5] 16.6	274.1 [80.3] 136.7 [40.1] 16.4	281.3 [82.4] 226.4 [66.4] 16.7	270.2 [79.2] 193.6 [56.7] 16.4	261.3 [76.6] 169.0 [49.5] 16.1	271.4 [79.5] 261.1 [76.5] 16.4	260.6 [76.4] 225.3 [66.0] 16.1	252.0 [73.9] 198.3 [58.1] 15.8
0 U	80 [26.7]	Total BTUH [kW] Sens BTUH [kW] Power	291.1 [85.3] 186.7 [54.7] 17.8	279.6 [81.9] 157.3 [46.1] 17.4	270.4 [79.2] 135.5 [39.7] 17.2	277.3 [81.3] 224.6 [65.8] 17.5	266.3 [78.0] 192.1 [56.3] 17.2	257.5 [75.5] 167.7 [49.2] 16.9	267.3 [78.3] 259.2 [76.0] 17.2	256.7 [75.2] 223.8 [65.6] 16.9	248.2 [72.7] 197.0 [57.7] 16.6
D 0 0 R	85 [29.4]	Total BTUH [kW] Sens BTUH [kW] Power	286.3 [83.9] 184.3 [54.0] 18.7	275.0 [80.6] 155.4 [45.6] 18.3	265.9 [77.9] 133.9 [39.3] 18.0	272.5 [79.9] 222.3 [65.2] 18.4	261.7 [76.7] 190.2 [55.8] 18.0	253.0 [74.1] 166.1 [48.7] 17.7	262.5 [76.9] 256.9 [75.3] 18.1	252.1 [73.9] 221.9 [65.0] 17.7	243.7 [71.4] 195.4 [57.3] 17.4
D R Y B	90 [32.2]	Total BTUH [kW] Sens BTUH [kW] Power	280.8 [82.3] 181.7 [53.3] 19.6	269.6 [79.0] 153.1 [44.9] 19.2	260.7 [76.4] 131.9 [38.7] 18.9	266.9 [78.2] 219.5 [64.3] 19.3	256.3 [75.1] 187.9 [55.1] 18.9	247.8 [72.6] 164.2 [48.1] 18.6	256.9 [75.3] 254.1 [74.5] 19.0	246.7 [72.3] 219.6 [64.4] 18.6	238.6 [69.9] 193.5 [56.7] 18.3
U L B T E	95 [35]	Total BTUH [kW] Sens BTUH [kW] Power	274.4 [80.4] 178.4 [52.3] 20.6	263.6 [77.3] 150.5 [44.1] 20.2	254.9 [74.7] 129.7 [38.0] 19.8	260.6 [76.4] 216.3 [63.4] 20.3	250.3 [73.4] 185.3 [54.3] 19.9	242.0 [70.9] 162.0 [47.5] 19.6	250.6 [73.4] 250.6 [73.5] 20.0	240.7 [70.5] 217.0 [63.6] 19.6	232.7 [68.2] 191.2 [56.0] 19.3
M P E R	100 [37.8]	Total BTUH [kW] Sens BTUH [kW] Power	267.4 [78.4] 174.7 [51.2] 21.6	256.8 [75.3] 147.4 [43.2] 21.2	248.3 [72.8] 127.1 [37.3] 20.8	253.5 [74.3] 212.5 [62.3] 21.3	243.5 [71.4] 182.2 [53.4] 20.9	235.4 [69.0] 159.3 [46.7] 20.5	243.5 [71.4] 243.5 [71.4] 21.0	233.9 [68.5] 214.0 [62.7] 20.6	226.1 [66.3] 188.7 [55.3] 20.3
A T U R E	105 [40.6]	Total BTUH [kW] Sens BTUH [kW] Power	259.6 [76.1] 170.6 [50.0] 22.7	249.3 [73.1] 144.0 [42.2] 22.2	241.0 [70.6] 124.2 [36.4] 21.9	245.7 [72.0] 208.5 [61.1] 22.4	236.0 [69.2] 178.8 [52.4] 21.9	228.2 [66.9] 156.5 [45.9] 21.6	235.7 [69.1] 235.7 [69.1] 22.1	226.4 [66.4] 210.5 [61.7] 21.7	218.9 [64.2] 185.7 [54.4] 21.3
°F.	110 [43.3]	Total BTUH [kW] Sens BTUH [kW] Power	251.0 [73.6] 166.1 [48.7] 23.8	241.1 [70.7] 140.3 [41.1] 23.3	233.1 [68.3] 121.1 [35.5] 22.9	237.1 [69.5] 203.9 [59.8] 23.5	227.7 [66.7] 175.0 [51.3] 23.0	220.2 [64.5] 153.3 [44.9] 22.7	227.1 [66.6] 227.1 [66.6] 23.2	218.1 [63.9] 206.7 [60.6] 22.8	210.9 [61.8] 182.5 [53.5] 22.4
	115 [46.1]	Total BTUH [kW] Sens BTUH [kW] Power	241.7 [70.8] 161.0 [47.2] 25.0	232.1 [68.0] 136.0 [39.9] 24.5	224.4 [65.8] 117.4 [34.4] 24.1	227.8 [66.8] 198.8 [58.3] 24.7	218.8 [64.1] 170.8 [50.1] 24.2	211.5 [62.0] 149.6 [43.9] 23.8	217.8 [63.8] 217.8 [63.8] 24.4	209.2 [61.3] 202.5 [59.4] 23.9	202.3 [59.3] 179.0 [52.5] 23.5

DR —Depression ratio
dbE —Entering air dry bulb wbE—Entering air wet bulb Total —Total capacity x 1000 BTUH
Sens —Sensible capacity x 1000 BTUH Power —KW input

NOTES: ① When the entering air dry bulb is other than $80^{\circ}F$ [27°C], adjust the sensible capacity from the table by adding [1.10 x CFM x (1 – DR) x (dbE – 80)].

AIRFLOW PERFORMANCE—15 TON [52.8 kW]-SIDEFLOW

::	Mo	Model RKKL-B180 Voltage 208/230, 460, 575 — 3 Phase 60 Hz	KKL-E	3180	٥	tage ;	208/2.	30, 4	60, 57	5	3 Pha	se 60	Hz																										
AIL I																Exte	rmal (Static	Press	Sure	External Static Pressure—Inches of Water [kPa]	s of V	Vater	[kPa]															
FIUW CEM II /61 0.1 [.02] 0.2 [.05] 0.3 [.07] 0.4 [.10] 0.5 [.12] 0.6 [.15] 0.7	0.1	.02]	0.2[.05	0.3	.07]	0.4 [.10]	0.5 [.12]	0.6	.15]	0.7 [[.17]	0.8	.20]	0.9	.22]	1.0[.25]	$0.8 [.20] \left 0.9 [.22] \right 1.0 [.25] \left 1.1 [.27] \right 1.2 [.30] \left 1.3 [.32] \right 1.4 [.35]$	[72]	1.2 [30]	.3[.	32] 1	.4[.3		1.5 [.37]	7]	1.6 [.40]	-	1.7 [.42] 1.8 [.45] 1.9 [.47]	1.8	[.45]	1.9	.47]	2.0 [.	.50]
	RPM	×	RPM	8	RPM	M	RPM	×	RPM	8	RPM	×		W	RPM	×	RPM W	8	RPM	8	W RPM W	×	3PM	RPM W RPM W	PM	W	RPM 1	WRF	RPM W		RPM W		RPM W		RPM W	RPM	M	RPM	×
4800 [2265]	Ι	1	Ι	Ι	ı	ı	ı	_	-	_	589	589 1395 613		1488	989	1584	629	1681	681	1781	203	1883	725 1	188	746	2093 7	766 22	2202	787 23	2313 80	806 2426	26 826	6 2541	1 845	5 2658	863	8212	881 2	2900
5000 [2359]	-	ı	-	1	Ι	1	-	_	574	1376	598 1469		621	1565	644	1663	299	1763	689	1866	710	1971	732 2	2078 7	752 2	2187 7	773 22	12 6677	793 24	2412 81	812 2528	28 831	1 2647	.7 850	2767	898	2890	886 3	3014
5200 [2454]	ı	ı	ı	I	I	ı	I	_	583	1452	607 1549		930	1647	652	1748	675	1852	969	1957	718	2065	739 2	2175 7	759 2	2287 7	779 2	2401 79	799 25	2518 81	818 2637	37 837	7 2758	8 856	3 2881	874	3007	891 3	3134
5400 [2548]	1	1	1	Ι	ı	1	Ι	_	265	1534	615 1634		638	1735	661	1839	683	1945	704	2054	725	2164	746 2	7272	766 2	2392 7	786 25	2509 80	806 2629		825 2751	51 843	3 2875	2 862	3001	879	3129	897 3	3260
5600 [2643]	1	Ι	-	1	I	Ι	218	578 1522		601 1622	624 1724		647	1829	699	1936	691	2045	712	2156	733	2270	753 2	2385 7	773 2	2 2097	793 26	2623 8	812 2746	46 831	31 2870	70 849	9 2997	1 867	3126	885	3258	902 3	3391
5800 [2737]	ı	1	ı	ı	ı	ı	287	1612	610	587 1612 610 1715	633 1821	_	655	1928	229	2038	669	2150	720	2264	741	2380	761	2499 7	781 2	2620 8	800 27	2743 8	819 2868		837 2996	96 856	6 3126	6 873	3 3258	891	3392	907	3528
6000 [2831]	1	1	-	1	573	573 1605 597 1709 620 1815 642 1923	265	1709	620	1815	642	1923	664	2033	989	2146	707	2261	728	2378	748	2497	768	2618 7	788 2	2742 8	807 28	2868 8	826 2996		844 3127	27 862	2 3260	628 0	3334	968	3532	913 3	3671
6200 [2926]	Ι	Ι	1	I	583	583 1704 606 1811 629 1919 651 2030	909	1811	629	1919	651	2030	673	2144	695	2259	715	2377	736	2497	756	2619	2 922	2744 7	795 2	2870 8	814 29	2999 8	832 3130	30 851	51 3264	64 868	8 3399	9 885	3537	905	3677	918 3	3819
6400 [3020]	ı	1	. 0/9	1701	593	593 1809 616 1918 639 2030 661 2144	919	1918	639	2030	991	2144	682	2260	703	2378	724	2499	744	2622	764	2747	784 2	2874 8	803 3	3004 8	821 3-	3136 8	839 3270		857 3406	06 875	5 3544	4 892	3685	806	3828	924 3	3973
6600 [3114]	-	1	. 089	1809	603	603 1919 626 2031	979	2031	648	2146	648 2146 670 2263		691	2382	712	2503	732	2627	753	2753	772	2881	791 3	3011 8	810 3	3143 8	829 32	3278 8	846 34	3415 86	864 3554	54 881	1 3695	2 898	3 3839	914	3985	930 4	4133
6800 [3209]	1	1	291	1922	614	614 2035 636 2150 658 2268	636	2150	658	2268	679 2388		200	2510	721	2634	741	2760	761	2889	780	3020	799 3	3153 8	818	3288 8	836 3	3426 8	854 3566	66 871	71 3708	08 888	8 3852	2 904	1 3999	920	4147	Ī	Ι
7000 [3303] 578 1927	278	1927	601	2041	624	601 2041 624 2157 646 2275 667 2395 689 2518	646	2275	299	2395	689	2518	709	2643	730	2770	750	2899	769	3031	788	3165	807	3301	825 3	3439 8	843 35	3579 86	861 3722		878 3867	67 894	4 4014	4 911	4164	926	4315	ı	1
[7200 [3398]] 589 [2049] 612 [2165] 634 [2284] 656 [2405] 677 [2528] 698 [2654] 719	289	2049	612	2165	634	2284	929	2405	229	2528	869	2654		2782	739	2912	759	3044	778	778 3178	797	3315	815 3	3454 8	833 3	3595 8	851 37	3739 86	868 38	3884 88	885 4032	32 901	1 4182	2 917	7 4335	1	I	1	1
MOTE: 1 Drive loft of hold line M Drive right of hold line	40	1 200	, v	2	tdoir	4	2																																

NOTE: L-Drive left of bold line, M-Drive right of bold line.

				9	775
				2	808
	28.5]	5H	26	7	840
Σ	5.0 [3728.5]	BK105H	1VP-56	3	873
				2	903
				1	927
				9	572
				9	909
	237.1]	BK105H	1VL-44	4	640
	3.0 [2237.1]	BK1	1VL	3	699
				7	701
				1	733
Drive Package	Motor H.P. [W]	Blower Sheave	Motor Sheave	Turns Open	RPM

NOTES: 1. Factory sheave settings are shown in bold type.
2. Do not set motor sheave below minimum turns open shown.

Re-adjustment of sheave required to achieve rated airflow at AHRI minimum External Static Pressure.
 Drive data shown is for horizontal airflow with dry coil. Add component resistance (below) to duct resistance to determine total External Static Pressure.

COMPONENT AIR RESISTANCE—15 TON [52.8 kW]

	4800	2000	5200	5400	2600	2800	0009	6200	6400	0099	0089	2000	7200
Č L M	[2265]	[2359]	[2454]	[2548]	[2643]	[2737]	[2831]	[2926]	[3020]	[3114]	[3209]	[3303]	[3398]
[۲/3]					Res	istance —	Resistance — Inches of Water [kPa]	f Water [k	Pa]				
Wet Coil	0.03	0.04	0.05	90.0	90.0	0.07	0.08	60.0	0.10	0.10	0.11	0.12	0.13
Welcoll	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.02]	[0.02]	[0.02]	[0.02]	[0.02]	[0.03]	[0.03]	[0.03]
Donnellour	90'0	90'0	0.05	0.05	0.05	0.05	0.05	90.0	90.0	90'0	0.07	80.0	80.0
DOWIIIOW	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.02]	[0.02]	[0.02]
Downflow Economizer	60'0	0.10	0.10	0.11	0.12	0.13	0.13	0.14	0.15	0.16	0.16	0.17	0.18
R.A. Damper Open	[0.02]	[0.02]	[0.02]	[0.03]	[0.03]	[0.03]	[0.03]	[0.03]	[0.04]	[0.04]	[0.04]	[0.04]	[0.04]
Horizontal Economizer	00'0	0.01	0.01	0.05	0.02	0.03	0.03	0.04	0.04	0.05	0.05	90.0	90.0
R.A. Damper Open	[0.00]	[00.0]	[00.0]	[00.00]	[00.00]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]	[0.01]
Concentric Grill RXRN-AD80 or	0.21	0.25	0.28	0.32	0.35	0.39	0.43	0.46	0.50	0.54	0.57	0.61	0.64
RXRN-AD81 & Transition RXMC-CJ07	[0.02]	[90:0]	[0.0]	[0.08]	[0.09]	[0.10]	[0.11]	[0.11]	[0.12]	[0.13]	[0.14]	[0.15]	[0.16]
LECIN	to the state of	and the first terms	1	100									

NOTE: Add component resistance to duct resistance to determine total external static pressure.

AIRFLOW CORRECTION FACTORS—15 TON [52.8 kW]

						•							
ACTUAL—CFM	4800	2000	5200	5400	2600	2800	0009	6200	6400	0099	0089	2000	7200
[L/s]	[2265]	[2359]	[2454]	[2548]	[2643]	[2737]	[2831]	[2926]	[3020]	[3114]	[3209]	[3303]	[3398]
TOTAL MBH	0.98	86.0	0.99	1.00	1.00	1.01	1.02	1.02	1.03	1.04	1.04	1.05	1.06
SENSIBLE MBH	0.91	0.94	96.0	0.99	1.02	1.04	1.07	1.10	1.12	1.15	1.18	1.20	1.23
POWER KW	0.99	0.99	0.99	1.00	1.00	1.00	1.01	1.01	1.01	1.02	1.02	1.02	1.03
NOTES: Multiply correction factor times gross performance data-resulting sensible capacity car	ctor times gross pe	÷rformance data–re	esulting sensible ca	apacity cannot exc	eed total capacity.						[] Design	Designates Metric Conversions	Conversions

AIRFLOW PERFORMANCE—20 TON [70.3 kW]-SIDEFLOW

		1.4[.35] 1.5[.37] 1.6[.40] 1.7[.42] 1.8[.45] 1.9[.47] 2.0[.50]	W RPM W RPM W RPM W RPM W	3453 887 3595 906 3761 923 3902 937 4121	3604 894 3750 912 3912 930 4056 944 4271	3763 901 3913 919 4072 933 4283 950 4432	3931 908 4085 926 4240 940 4448 957 4603	4108 916 4265 932 4417 947 4624 964 4784	4293 923 4454 938 4650 954 4810 971 4976	4487 931 4651 945 4841 962 5007 978 5179	4689 936 4878 953 5043 969 5214 986 5392	4900 944 5084 961 5255 977 5432 993 5616	5130 952 5300 969 5477 985 5660 1001 5850	5352 961 5528 977 5710 993 5899 1008 6094	5584 969 5765 985 5954 1001 6148 — —	5826 978 6013 993 6208 1009 6408		6079 986 6272 1002 6472 — — — —	995 6541 1010 6747 — — —	986 6272 1002 6472 — — — — 995 6541 1010 6747 — — — — 1004 6821 — — — — — —
		35] 1.5[.37] 1.6[W RPM W RPM	3170 848 3311 868	3314 856 3458 875	3467 864 3614 883	3628 872 3779 891	3797 880 3952 898	3975 889 4134 906	4162 897 4324 914	4357 906 4522 923	4560 914 4729 931	4772 923 4945 936	4993 932 5169 944	5222 937 5408 953	5434 946 5645 962	5712 955 5892 971		964 6149 980	964 6149 980 973 6418 989
	Pa]	1.2 [.30] 1.3 [.32] 1.4 [.3	RPM W RPM	808 3031 829	817 3172 837	825 3321 845	834 3478 853	843 3644 862	852 3818 871	861 4001 879	870 4192 888	880 4392 897	889 4601 906	899 4818 915	908 5043 925	918 5277 933	928 5519 939		933 5784 949	933 5784 949 942 6040 958
	External Static Pressure—Inches of Water [kPa	1.1 [.27] 1.2 [.30	RPM W RPM W	766 2756 788 2893	775 2890 796 3030	785 3031 805 3175	794 3182 814 3329	804 3340 824 3492	813 3508 833 3662	823 3683 842 3842	833 3868 852 4029	843 4060 861 4226	853 4262 871 4431	863 4471 881 4644	874 4690 891 4866	884 4916 901 5096	895 5151 912 5335		905 5395 922 5582	905 5395 922 916 5647 932
	al Static Pressure-	0.9 [.22] 1.0 [.25]	W RPM W	22 2487 745 2621	32 2613 754 2751	12 2747 764 2889	52 2890 773 3035	32 3042 783 3191	73 3202 793 3354	33 3371 803 3526	3548 814 3707	3733 824 3896	5 3927 834 4094	26 4130 845 4300	37 4341 856 4515	18 4561 866 4738	9 4789 877 4969	2007	6075 888 5706 L	5025 888 5270 899
	Extern	.17] 0.8 [.20] 0.	W RPM W RPM	2222 699 2354 722	2341 710 2476 732	2468 720 2607 742	2604 730 2747 752	2749 741 2895 762	2902 752 3051 773	3063 762 3216 783	3233 773 3390 794	3411 784 3572 804	3598 795 3762 815	3794 807 3961 826	3997 818 4169 837	4210 829 4385 848	4431 841 4609 859	1660 253 1810 271	24047	865 5083
- 3 rnase bu riz		2] 0.6 [.15] 0.7 [W RPM W RPM	— 652 2091 676	2074 663 2207 687	2194 674 2331 697	2323 685 2463 708	2460 697 2604 719	2606 708 2753 730	2760 719 2911 741	2923 731 3077 752	3094 743 3252 764	3435 775	3462 766 3627 787	3659 778 3827 798	3864 790 4036 810	803 4254 822	00 815 4479 834		828 4714
208/230, 400, 575		0.4[.10] 0.5[.1	RPM W RPM W	1	— — 639 Z0	— — 651 21	638 2184 662 23	650 2318 674 24	662 2460 685	674 2611 697	687 2770 709	699 2937 721	2954 711 3114 733 3274 754	724 3298 745 34	737 3491 758	750 3693 770	763 3903 783 40	776 4122 796 4300	771	789 4349 808
Model RKKL-B240 Voltage 208/230, 460, 575 — 3 Phase 60 Hz		0.1 [.02] 0.2 [.05] 0.3 [.07] 0.4 [.10] 0.5 [.12]	RPM W RPM W RPM W	 	 	 	 	 	— — 639 2315	— — 651 2462	640 2467 664 2618	630 2475 653 2628 676 2782	366 2797 689 2954	380 2974 702 3136	671 2996 693 3160 715 3325	3187 707 3355 728 3523	720 3558 742 3730	734 3769 755 3945		748 3989 769 4168
	All	CEM II (c) 0.1 [.02] 0	RPM W	- — — e400 [30Z0] — —	6600 [3114] — — -	- — — (- 800 3208)	- — — [£0££] 0002	- — — [8688] 0074	7400 [3492] — — -	- — — [98 2] — — — — — — — — — — — — — — — — — — —	7800 [3681] — 6	8000 [3775] 630 2475 6	8200 [3869] 643 2640 666 2797 689	8400 [3964] 657 2814 680 2974 702 3136 724 3298 745	8600 [4058] 671 2996 6	8800 [4153] 684 3187 7	9000 [4247] 698 3387 720 3558 742 3730 763 3903 783 4078	9200 [4341] 713 [3595] 734 [3769] 755	10000	9400 [4436] 727 3811 748 3989 769

NOTE: L-Drive left of bold line, M-Drive right of bold line.

				9	028
(/				5	899
lled only	32.7]	Н	71	4	876
N (field installed only)	7.5 [5592.7]	BK120H	1VP-71	3	922
N (f				2	981
				1	1009
				9	793
				9	820
	32.7]	H	71	4	847
M	7.5 [5592.7]	BK130H	1VP-71	3	874
				2	905
				1	928
				9	631
				2	658
	5.0 [3728.5]	BK130H	IVP-56	4	200 683
	5.0 [3	BK1	1VF	3	209
				2	734
				1	756
Drive Package	Motor H.P. [W]	Blower Sheave	Motor Sheave	Turns Open	RPM

NOTES: 1. Factory sheave settings are shown in bold type.
2. Do not set motor sheave below minimum turns open shown.

NOTES: 1. Factory sheave settings are shown in bold type.

2. Do not set motor sheave below minimum turns open shown.

4. Drive data shown is for horizontal airflow with dry coil. Add component resistance (below) to duct resistance to determine total External Static Pressure.

COMPONENT AIRFLOW RESISTANCE—20 TON [70.3 kW]


23	6400	0099	-			_		7800	8000	_	8400	8600	8800			_	0096
	[3020]	[3114]	[3209]	[3303]	[3398]	[3492]	[3586]	[3681]	[3775]	[3869]	[3964]	[4058]	[4153]	[4247]	[4341]	[4436]	[4530]
[6/3]							Resista	Resistance —	lnches (Inches of Water	[kPa]						
WetCoil	0.00	00'0	0.00	0.01	0.01	0.02	0.02	0.03	0.03	0.04	0.04	0.05	0.05	90.0	90'0	0.07	0.07
Met coll	[.00]	[.00]	[.00]	[.00]	[.00]	[.00]	[.00]	[.01]	[.01]	[.01]	[.01]	[.01]	[.01]	[.01]	[.01]	[.02]	[.02]
Dount	90.0	90'0	0.07	0.08	0.08	0.09	0.10	0.11	0.12	0.13	0.14	0.15	0.16	0.18	0.19	0.20	0.22
Downling	[.01]	[.01]	[.02]	[.02]	[.02]	[.02]	[.02]	[.03]	[.03]	[.03]	[.03]	[.04]	[.04]	[.04]	[:05]	[.05]	[:05]
Downflow Economizer	0.15	0.16	0.16	0.17	0.18	0.19	0.20	0.21	0.22	0.23	0.24	0.25	0.26	0.27	0.28	0.29	0.30
R.A. Damper Open	[.04]	[.04]	[.04]	[.04]	[.04]	[.05]	[.05]	[.05]	[.05]	[.06]	[.06]	[.06]	[.06]	[.07]	[.07]	[.07]	[.07]
Horizontal Economizer	0.04	0.05	0.05	90.0	90.0	0.07	0.07	0.08	0.09	0.09	0.10	0.10	0.11	0.11	0.12	0.12	0.13
R.A. Damper Open	[.01]	[.01]	[.01]	[.01]	[.01]	[.02]	[.02]	[.02]	[.02]	[.02]	[.02]	[.02]	[.03]	[:03]	[:03]	[:03]	[:03]
Concentric Grill RXRN-AD86	0.26	0.29	0.32	0.35	0.38	0.41	0.44	0.47	0.5	0.53	0.56	0.59	0.62	0.65	69.0	0.72	0.75
& Transition RXMC-CK08	[90.]	[.07]	[80.]	[60:]	[.09]	[10]	Ξ	[.12]	[.12]	[13]	[14]	[15]	[15]	[16]	[.17]	[.18]	[.19]
	[.00]	[.6.]	[00:]	[00:]	[00:]	[5]		[-1-]	[-1-]	[0]		[0]	-		-	[]	[]

AIRFLOW CORRECTION FACTORS—20 TON [70.3 kW]


					7												
ACTUAL—CFM	6400	0099	0089	2000	7200	7400	7600	7800	8000	8200	8400	8600	8800	0006	9200	9400	0096
[L/s]	[3020]	[3114]	[3209]	[3303]	[3398]	[3492]	[3286]	[3681]	[3775]	[3869]	[3964]	[4058]	[4153]	[4247]	[4341]	[4436]	[4530]
TOTAL MBH	0.97	0.97	0.98	0.98	0.99	0.99	0.99	1.00	1.00	1.01	1.01	1.02	1.02	1.03	1.03	1.04	1.04
SENSIBLE MBH	0.87	0.89	0.91	0.93	0.95	0.97	0.98	1.00	1.02	1.04	1.06	1.08	1.09	1.11	1.13	1.15	1.17
POWER KW	0.98	0.99	0.99	0.99	0.99	1.00	1.00	1.00	1.00	1.00	1.01	1.01	1.01	1.01	1.02	1.02	1.02
NOTES: Multiply correction factor times gross performance data-resulting sensible capacity can	ion factor times	s gross perforn	nance data–res	sulting sensible	capacity cann	nnot exceed total capacity.	। capacity.							[] Det	Designates N	Metric Conversions	versions

		ELECTR	ICAL DATA –	RKKL- SERIE	S		
		B180CL	B180CM	B180DL	B180DM	B180YL	B180YM
	Unit Operating Voltage Range	187-253	187-253	414-506	414-506	518-633	518-633
<u>.</u>	Volts	208/230	208/230	460	460	575	575
mat	Minimum Circuit Ampacity	75/75	78/78	38	40	28	30
Unit Information	Minimum Overcurrent Protection Device Size	90/90	90/90	45	45	30	35
'n	Maximum Overcurrent Protection Device Size	90/90	100/100	50	50	35	35
	No.	2	2	2	2	2	2
	Volts	200/230	200/230	460	460	575	575
- I	Phase	3	3	3	3	3	3
Mot	RPM	3450	3450	3450	3450	3450	3450
l i	HP, Compressor 1	7	7	7	7	7	7
ress	Amps (RLA), Comp. 1	25/25	25/25	12.2	12.2	9	9
Compressor Motor	Amps (LRA), Comp. 1	164/164	164/164	100	100	78	78
3	HP, Compressor 2	6	6	6	6	6	6
	Amps (RLA), Comp. 2	25/25	25/25	12.8	12.8	9.6	9.6
	Amps (LRA), Comp. 2	164/164	164/164	100	100	78	78
o.	No.	3	3	3	3	3	3
Mot	Volts	208/230	208/230	460	460	575	575
Compressor Motor	Phase	1	1	1	1	1	1
res	HP	1/2	1/2	1/2	1/2	1/2	1/2
Ē.	Amps (FLA, each)	2.3/2.3	2.3/2.3	1.5	1.5	1	1
3	Amps (LRA, each)	5.6/5.6	5.6/5.6	3.1	3.1	2.2	2.2
	No.	1	1	1	1	1	1
Fan	Volts	208/230	208/230	460	460	575	575
草	Phase	3	3	3	3	3	3
ora	HP	3	5	3	5	3	5
Evaporator Fan	Amps (FLA, each)	11.5/11.5	14.9/14.9	4.6	6.6	3.5	5.3
_	Amps (LRA, each)	74.5/74.5	82.6/82.6	38.1	46.3	20	39.4

			ELECTRIC	CAL DATA	– RKKL-	SERIES				
		B240CL	B240CM	B240CN	B240DL	B240DM	B240DN	B240YL	B240YM	B240YN
	Unit Operating Voltage Range	187-253	187-253	187-253	414-506	414-506	414-506	518-632	518-632	518-632
ioi	Volts	208/230	208/230	208/230	460	460	460	575	575	575
l ma	Minimum Circuit Ampacity	94/94	102/102	102/102	51	54	54	37	39	39
Unit Information	Minimum Overcurrent Protection Device Size	110/110	110/110	110/110	60	60	60	40	45	45
5	Maximum Overcurrent Protection Device Size	125/125	125/125	125/125	60	70	70	45	50	50
	No.	2	2	2	2	2	2	2	2	2
	Volts	200/230	200/230	200/230	460	460	460	575	575	575
=	Phase	3	3	3	3	3	3	3	3	3
Mot	RPM	3450	3450	3450	3450	3450	3450	3450	3450	3450
ĕ	HP, Compressor 1	10	10	10	10	10	10	10	10	10
ress	Amps (RLA), Comp. 1	33.6/33.6	33.6/33.6	33.6/33.6	17.9	17.9	17.9	12.8	12.8	12.8
Compressor Motor	Amps (LRA), Comp. 1	239/239	239/239	239/239	125	125	125	80	80	80
ت	HP, Compressor 2	8 1/2	8 1/2	8 1/2	8 1/2	8 1/2	8 1/2	8 1/2	8 1/2	8 1/2
	Amps (RLA), Comp. 2	30.1/30.1	30.1/30.1	30.1/30.1	16.7	16.7	16.7	12.2	12.2	12.2
Compressor Motor	Amps (LRA), Comp. 2	225/225	225/225	225/225	114	114	114	80	80	80
	No.	3	3	3	3	3	3	3	3	3
	Volts	208/230	208/230	208/230	460	460	460	575	575	575
sor	Phase	1	1	1	1	1	1	1	1	1
les	HP	1/2	1/2	1/2	1/2	1/2	1/2	1/2	1/2	1/2
🗑	Amps (FLA, each)	2.3/2.3	2.3/2.3	2.3/2.3	1.5	1.5	1.5	1	1	1
ت	Amps (LRA, each)	5.6/5.6	5.6/5.6	5.6/5.6	3.1	3.1	3.1	2.2	2.2	2.2
	No.	1	1	1	1	1	1	1	1	1
Far	Volts	208/230	208/230	208/230	460	460	460	575	575	575
Evaporator Fan	Phase	3	3	3	3	3	3	3	3	3
por:	HP	5	7 1/2	7 1/2	5	7 1/2	7 1/2	5	7 1/2	7 1/2
Eva	Amps (FLA, each)	14.7/14.7	23.1/23.1	23.1/23.1	6.6	9.6	9.6	5.3	7.8	7.8
	Amps (LRA, each)	82.6/82.6	136/136	136/136	46.3	67	67	39.4	53.8	53.8




SUPPLY AND RETURN DIMENSIONS FOR HORIZONTAL APPLICATIONS





DUCT SIDE VIEW (REAR)

SUPPLY AND RETURN DIMENSIONS FOR DOWNFLOW APPLICATIONS



BOTTOM VIEW





WEIGHTS


26

Accessory	Shipping—lbs [kg]	Operating—lbs [kg]
Downflow Economizer	277 [125.6]	168 [76.2]
Horizontal Economizer	333 [151.0]	301 [136.5]
Power Exhaust	119 [54.0]	59 [26.8]
Manual Fresh Air Damper*	61 [27.7]	52 [23.6]
Motor Kit for Fresh Air Damper*	42 [19.1]	35 [15.9]
Roofcurb, 14"	184 [83.5]	176 [79.8]
Hail Guard	50 [22.7]	45 [20.4]

NOTES: *Motorized Kit and Manual Fresh Air Damper must be combined for a complete Motorized Outside Air Damper Selection.

Capacity Tons [kW]	Corner	Weights	by Perc	entage
	Α	В	С	D
15-25 [52.8-87.9]	32%	27%	16%	24%


Corner weights measured at base of unit.



CLEARANCES

Recommended

The following minimum clearances are recommended for proper unit performance and serviceability.



THERMOSTAT WIRE

Clearance In. [mm] 80 [2032] A - Front 18 [457] B - Condenser Coil +18 [457] +C - Duct Side *18 [457] *D - Evaporator End 60 [1524] E - Above *Without Economizer. 48" [1219 mm] With Economizer

Location

+Without Horizontal Economizer, 42" [1067 mm] with Horizontal Economizer

[] Designates Metric Conversions

ST-A1182-27-00

FIELD INSTALLED ACCESSORY EQUIPMENT

Accessory Description	Model Number	Shipping Weight Lbs. [kg]	Installed Weight Lbs. [kg]	Factory Installation Available?	
Thermostat or Room Sensor	See The	No			
Downflow Economizer w/ Single Enthalpy	AXRD-PGCM3	277 [125.6]	168 [76.2]	Yes	
Downflow Economizer w/ Smoke Detector	AXRD-SGCM3	280 [127.0]	171 [77.6]	Yes	
Dual Enthalpy Kit	RXRX-AV02	1 [0.5]	0.5 [0.2]	No	
Horizontal Economizer w/ Single Enthalpy	AXRD-RGCM3	333 [151.0]	301 [136.5]	No	
Carbon Dioxide Sensor (Wall Mount)	RXRX-AR02	3 [1.4]	2 [0.9]	No	
Power Exhaust (208/230V)	RXRX-BGF05C	119 [54.0]	59 [26.8]	No	
Power Exhaust (460V)	RXRX-BGF05D	119 [54.0]	59 [26.8]	No	
Power Exhaust (575V)	RXRX-BGF05Y	119 [54.0]	59 [26.8]	No	
Manual Fresh Air Damper*	AXRF-KFA1	61 [27.7]	52 [23.6]	No	
Motorized Kit for Manual Fresh Air Damper*	RXRX-AW03	42 [19.1]	35 [15.9]	No	
Roofcurb, 14"	RXKG-CBH14	184 [83.5]	176 [79.8]	No	
Roofcurb Adapter to RXRK-E56	RXRX-CJCE56	465 [210.9]	415 [188.2]	No	
Roofcurb Adapter to RXKG-CAF14	RXRX-CJCF14	555 [251.7]	505 [229.1]	No	
Concentric Diffuser (Step-Down 18" x 36")	RXRN-AD81	310 [140.6]	157 [71.2]	No	
Concentric Diffuser (Step-Down 24" x 48")	RXRN-AD86	367 [166.5]	212 [96.2]	No	
Concentric Diffuser (Flush, 18" x 36")	RXRN-AD80	213 [96.6]	115 [52.2]	No	
Downflow Transition (Rect. To Rect. 18" x 36")	RXMC-CJ07 ¹	81 [36.7]	74 [33.6]	No	
Downflow Transition (Rect. To Rect. 24" x 48")	RXMC-CK08 ²	81 [36.7]	74 [33.6]	No	
Compressor Time-Delay Relay Kit	RXMD-A04	2 [0.9]	1 [0.5]	No	
Low-Ambient Control Kit (1 Per Compressor)	RXRZ-C02	3 [1.4]	2 [0.9]	Yes	
Freeze Stat	RXRX-AM03	1 [0.5]	0.5 [0.2]	Yes	
Non-Powered Convenience Outlet	RXRX-AN01	2 [0.9]	1.5 [0.7]	Yes	
Unfused Service Disconnect	RXRX-AP01	10 [4.5]	9 [4.1]	Yes	
Hail Guard	AXRX-AAD01K	50 [22.7]	45 [20.4]	Yes	

NOTES: *Motorized Kit and Manual Fresh Air Damper must be combined for a complete Motorized Outside Air Damper Selection

- 1. Used with RXRN-AD81 and RXRN-AD80 concentric diffusers
- 2. Used with RXRN-AD86 concentric diffusers

NOTICE: Please refer to conversion kit index provided with the unit for selecting the LP conversion kit model number.

[] Designates Metric Conversions

THERMOSTATS



200-Series *
Programmable



300-Series *
Deluxe
Programmable
400-Series *
Special Applications/

Programmable



500-Series * Communicating/ Programmable

Brand		Descripter (3 Characters)	Series (3 Characters)	System (2 Characters)	Type (2 Characters)	
RHC	-	TST	213	UN	MS	
RHC=Rheem		TST=Thermostat	200=Programmable 300=Deltuxe Programmable 400=Special Applications/ Programmable 500=Communicating/ Programmable	GE=Gas/Electric UN=Universal (AC/HP/GE) MD=Modulating Furnace DF=Dual Fuel CM=Communicating	SS=Single-Stage MS=Multi-Stage	

^{*} Photos are representative. Actual models may vary.

For detailed thermostat match-up information, see specification sheet form number T11-001.

ECONOMIZERS


■ Field Installed Power Exhaust Available

Use to Select Factory Installed Options Only [254 mm] AXRD-PGCM3—Single Enthalpy (Outdoor) AXRD-SGCM3—Single Enthalpy (Outdoor) with Smoke Detector RXRX-AV02—Dual Enthalpy Upgrade Kit RXRX-AR02—Optional Wall-Mounted CO, Sensor ■ Features **Honeywell** Controls Available Factory Installed or Field Accessory 52" [1321 mm] ■ Gear Driven Direct Drive Actuator ■ Fully Modulating (0-100%) **ECONOMIZER ACTUATOR** ■ Low Leakage Dampers ■ Slip-In Design for Easy Installation ■ Plug-In Polarized 12-pin Electrical Connections ■ Pre-Configured—No Field Adjustments DISCHARGE SENSOR (STRAPPED TO WIRE Necessary HARNESS) ■ Standard Barometric Relief Damper Single Enthalpy with Dual Enthalpy Upgrade Kit Available BAROMETRIC RELIEF ■ CO₂ Input Sensor Available 583/4[′] [1493 mm] ■ Field Assembled Hood Ships with Economizer 241/8" ■ Economizer Ships Complete for Downflow Duct **ENTHALPY SENSOR** [613 mm] Application. **ECONOMIZER CONTROLLER** Optional Remote Minimum Position Potentiometer (Honeywell #S963B1128) is Available from Prostock. Illustration

ST-A1125-19

TOLERANCE ±.125

SMOKE DETECTOR LOCATION




ECONOMIZER FOR HORIZONTAL DUCT INSTALLATION


Field Installed Only AXRD-RGCM3—Single Enthalpy (Outdoor)

RXRX-AV02—Dual Enthalpy Upgrade Kit RXRX-AR02—Wall-mounted CO₂ Sensor

- Features Honeywell Controls
- Available as a Field Installed Accessory Only
- Gear Driven Direct Drive Actuator
- Fully Modulating (0-100%)
- Low Leakage Dampers
- Slip-In Design for Easy Installation
- Plug-In Polarized 12-pin Electrical Connections
- Pre-Configured—No Field Adjustments Necessary
- Standard Barometric Relief Damper
- Single Enthalpy with Dual Enthalpy Upgrade Kit Available
- CO₂ Input Sensor Available
- Field Assembled Hood Ships with Economizer
- Economizer Ships Complete for Horizontal Duct Application
- Optional Remote Minimum Position Potentiometer (Honeywell #S963B1128) is Available from Prostock
- Field Installed Power Exhaust Available




TOLERANCE ± .125



POWER EXHAUST KIT FOR AXRD-PGCM3 & SGCM3 ECONOMIZERS

RXRX-BGF05 (C, D, or Y*)




Model No. No. of Fans	No.	Volts	Phase	HP (ea.)	Low Speed		High Speed ①		FLA	LRA
	of Fans	VUIIS			CFM [L/s] ②	RPM	CFM [L/s] ②	RPM	(ea.)	(ea.)
RXRX-BGF05C	2	208-230	1	0.75	4100 [1935]	850	5200 [2454]	1050	5	4.97
RXRX-BGF05D	2	460	1	0.75	4100 [1935]	850	5200 [2454]	1050	2.2	3.4
RXRX-BGF05Y	2	575	1	0.75	4100 [1935]	850	5200 [2454]	1050	1.5	2.84

NOTES: ① Power exhaust is factory set on high speed motor tap.
② CFM is per fan at 0" w.c. external static pressure.




FRESH AIR DAMPER

MOTORIZED DAMPER KIT RXRX-AWO3 (Motor Kit for AXRF-KFA1)




AXRF-KFA1 (Manual)
AXRX-AWO3 (Motorized damper kit for manual fresh air damper)





ROOFCURBS (Full Perimeter)

- Rheem's new roofcurb designs can be utilized on 15 & 20 ton [52.8 & 70.3 kW] models.
- One available height (14" [356 mm]).
- Quick assembly corners for simple and fast assembly.
- 1" [25.4 mm] x 4" [102 mm] Nailer provided.
- Insulating panels not required because of insulated outdoor base pan.
- Sealing gasket (28" [711 mm]) provided with Roofcurb.
- Packaged for easy field assembly.

ROOFCURB ASSEMBLY









DETAIL A

TYPICAL INSTALLATION





* BY CONTRACTOR


RETURN DUCT

FOR INSTALLATION OF DUCT AS SHOWN, USE RECOMMENDED DUCT SIZES FROM ROOFCURB INSTALLATION INSTRUCTIONS. FOR DUCT FLANGE ATTACHMENT TO UNIT, SEE UNIT INSTALLATION INSTRUCTIONS FOR RECOMMENDED DUCT SIZES.

[] Designates Metric Conversions

Illustration ST-A1125-14 Illustration

ROOFCURB ADAPTER



[] Designates Metric Conversions

[3048 mm]

Illustration

2901604

49⁵/₁₆" [1253 mm]

14115/16"

[3605 mm]

[829 mm]


[497 mm]

[332 mm]

[2048 mm]

53³/8" -[1381 mm]


CONCENTRIC DIFFUSER APPLICATION



DOWNFLOW TRANSITION DRAWINGS

RXMC-CJ07 (15 Ton) [52.8 kW]

■ Used with RXRN-AD80 and RXRN-AD81 Concentric Diffusers.






DOWNFLOW TRANSITION DRAWINGS (Cont.)


RXMC-CK08 (20 Ton) [70.3 kW]


■ Used with RXRN-AD86 Concentric Diffusers.




CONCENTRIC DIFFUSER RXRN-AD80 SERIES 15 TON [52.8 kW] FLUSH

- All aluminum diffuser with aluminum return air eggcrate.
- Built-in anti-sweat gasket.
- Molded fiberglass supports.
- Built-in hanging supports.
- Diffuser box constructed of sheetmetal insulated with 1" [25.4 mm] 1.5 lbs. [.7 kg] duct liner.







CONCENTRIC DIFFUSER SPECIFICATIONS

PART Number	CFM [L/s]	STATIC Pressure	THROW FEET	NECK Velocity	JET Velocity
RXRN-AD80	5600 [2643]	0.36	28-37	1000	2082
	5800 [2737]	0.39	29-38	1036	2156
	6000 [2832]	0.42	40-50	1071	2230
	6200 [2926]	0.46	42-51	1107	2308
	6400 [3020]	0.50	43-52	1143	2379
	6600 [3115]	0.54	45-56	1179	2454

[] Designates Metric Conversions

CONCENTRIC DIFFUSER RXRN-AD81 SERIES 15 TON [52.8 kW] STEP DOWN

 All aluminum diffuser with aluminum return air eggcrate.


■ Built-in anti-sweat gasket.


■ Molded fiberglass supports.


■ Built-in hanging supports.

 Diffuser box constructed of sheetmetal insulated with 1" [25.4 mm] 1.5 lbs.
 [.7 kg] duct liner.

 Double deflection diffuser with the blades secured by spring steel.








CONCENTRIC DIFFUSER SPECIFICATIONS


PART Number	CFM [L/s]	STATIC Pressure	THROW Feet	NECK Velocity	JET Velocity
RXRN-AD81	5600 [2643]	0.36	39-49	920	920
	5800 [2737]	0.39	42-51	954	954
	6000 [2832]	0.42	44-54	1022	1022
	6200 [2926]	0.46	45-55	1056	1056
	6400 [3020]	0.50	46-55	1090	1090
	6600 [3115]	0.54	47-56	1124	1124


[] Designates Metric Conversions

CONCENTRIC DIFFUSER RXRN-AD86 SERIES 20 TON [70.3 kW] STEP DOWN

- All aluminum diffuser with aluminum return air eggcrate.
- Built-in anti-sweat gasket.
- Molded fiberglass supports.
- Built-in hanging supports.
- Diffuser box constructed of sheetmetal insulated with 1" [25.4 mm] 1.5 lbs. [.7 kg] duct liner.
- Double deflection diffuser with the blades secured by spring steel.







CONCENTRIC DIFFUSER SPECIFICATIONS

PART Number	CFM [L/s]	STATIC Pressure	THROW FEET	NECK Velocity	JET Velocity
RXRN-AD86	7200 [3398]	0.39	33-38	827	827
	7400 [3492]	0.41	35-40	850	850
	7600 [3587]	0.43	36-41	873	873
	7800 [3681]	0.47	38-43	896	896
	8000 [3776]	0.50	39-44	918	918
	8200 [3870]	0.53	41-46	941	941
	8400 [3964]	0.56	43-49	964	964
	8600 [4059]	0.59	44-50	987	987
	8800 [4153]	0.63	47-55	1010	1010

[] Designates Metric Conversions

Guide Specifications RKKL-B180 thru B240

Note about this specification: Please feel free to copy this specification directly into your building spec. This specification is written to comply with the 2004 version of the "mask-format" as published by the Construction Specification Institute. www.csinet.org.

GAS HEAT PACKAGED ROOFTOP

HVAC Guide Specifications

Size Range: 15 to 20 Nominal Tons

Section Description

23 06 80 Schedules for Decentralized HVAC Equipment

23 06 80.13 Decentralized Unitary HVAC Equipment Schedule

23 06 80.13.A. Rooftop unit schedule

1. Schedule is per the project specification requirements.

23 07 16 HVAC Equipment Insulation

23 07 16.13 Decentralized, Rooftop Units:

- 1. Interior cabinet surfaces shall be insulated with a minimum 3/4-in. thick, minimum 1-1/2 lb density, flexible fiberglass insulation bonded with a phenolic binder, with aluminum foil facing on the air side.
- 2. Insulation and adhesive shall meet NFPA 90A requirements for flame spread and smoke generation.

23 09 13 Instrumentation and Control Devices for HVAC

23 09 13.23 Sensors and Transmitters:

23 09 13.23.A. Thermostats

- 1. Thermostat must
 - a. energize "G" when calling for heat.
 - b. have capability to energize 2 different stages of cooling, and 2 different stages of heating.
 - c. must include capability for occupancy scheduling.

23 09 33 Electric and Electronic Control System for HVAC

23 09 33.13 Decentralized, Rooftop Units:

23 09 93.13.A. General:

- 1. Shall be complete with self-contained low-voltage control circuit protected by a resettable circuit breaker on the 24-v transformer side.
- 2. Shall utilize color-coded wiring.
- The heat exchanger shall be controlled by an integrated furnace controller (IFC) microprocessor. See heat exchanger section of this specification.
- 4. Unit shall include a minimum of one 9-pin screw terminal connection board for connection of control wiring.

23 09 33.23.B. Safeties:

- 1. Compressor over-temperature, over current.
- 2. Low-pressure switch.
- 3. High-pressure switch.
- 4. Automatic reset, motor thermal overload protector.
- 5. Heating section shall be provided with the following minimum protections.
 - a. High-temperature limit switches.
 - b. Induced draft motor pressure switch.
 - c. Flame rollout switch.
 - d. Flame proving controls.

23 09 93 Sequence of Operations for HVAC Controls

23 09 93.13 Decentralized, Rooftop Units:

23 09 93.13 INSERT SEQUENCE OF OPERATION

23 40 13 Panel Air Filters

23 40 13.13 Decentralized, Rooftop Units:

23 40 13.13.A. Standard filter section shall

- 1. Shall consist of factory-installed, low velocity, throwaway 2-in. thick fiberglass filters of commercially available sizes.
- 2. Unit shall use only one filter size. Multiple sizes are not acceptable.
- 3. Filter face velocity shall not exceed 365 fpm at nominal airflows.
- 4. Filters shall be accessible through an access panel as described in the unit cabinet section of the specification (23 81 19.13.H).

23 81 19 Self-Contained Air Conditioners

23 81 19.13 Small-Capacity Self-Contained Air Conditioners

23 81 19.13.A. General

- 1. Outdoor, rooftop mounted, electrically controlled, heating and cooling unit utilizing a(n) hermetic scroll compressor(s) for cooling duty and gas combustion for heating duty.
- 2. Factory assembled, single-piece heating and cooling rooftop unit. Contained within the unit enclosure shall be all factory wiring, piping, controls, and special features required prior to field start-up.
- 3. Unit shall use environmentally safe, R-410A refrigerant.
- 4. Unit shall be installed in accordance with the manufacturer's instructions.
- 5. Unit must be selected and installed in compliance with local, state, and federal codes.

23 81 19.13.B. Quality Assurance

- 1. Unit meets ASHRAE 90.1-2004 minimum efficiency requirements.
- 2. 3 phase units are Energy Star qualified.
- 3. Unit shall be rated in accordance with AHRI Standards 210 and 360.
- 4. Unit shall be designed to conform to ASHRAE 15, 2001.
- 5. Unit shall be UL-tested and certified in accordance with ANSI Z21.47 Standards and UL-listed and certified under Canadian standards as a total package for safety requirements.
- 6. Insulation and adhesive shall meet NFPA 90A requirements for flame spread and smoke generation.
- 7. Unit casing shall be capable of withstanding 500-hour salt spray exposure per ASTM B117 (scribed specimen).
- 8. Unit casing shall be capable of withstanding Federal Test Method Standard No. 141 (Method 6061) 5000-hour salt spray.
- 9. Unit shall be designed in accordance with ISO 9001:2000, and shall be manufactured in a facility registered by ISO 9001:2000.
- 10. Roof curb shall be designed to conform to NRCA Standards.
- 11. Unit shall be subjected to a completely automated run test on the assembly line. The data for each unit will be stored at the factory, and must be available upon request.
- 12. Unit shall be designed in accordance with UL Standard 1995, including tested to withstand rain.
- 13. Unit shall be constructed to prevent intrusion of snow and tested to prevent snow intrusion into the control box up to 40 mph.

23 81 19.13.C. Delivery, Storage, and Handling

- 1. Unit shall be stored and handled per manufacturer's recommendations.
- 2. Lifted by crane requires either shipping top panel or spreader bars.
- 3. Unit shall only be stored or positioned in the upright position.

23 81 19.13.E. Project Conditions

1. As specified in the contract.

23 81 19.13.F. Operating Characteristics

- 1. Unit shall be capable of starting and running at 115°F (46°C) ambient outdoor temperature, meeting maximum load criteria of AHRI Standard 210/240 or 360 at ± 10% voltage.
- 2. Compressor with standard controls shall be capable of operation down to 40°F (4°C), ambient outdoor temperatures. Accessory low ambient kit is necessary if mechanically cooling at ambient temperatures below 40°F (4°C).
- 3. Unit shall discharge supply air vertically or horizontally as shown on contract drawings.
- 4. Unit shall be factory configured for vertical supply & return configurations.
- 5. Unit shall be field convertible from vertical to horizontal configuration.

23 81 19.13.G. Electrical Requirements

1. Main power supply voltage, phase, and frequency must match those required by the manufacturer.

23 81 19.13.H. Unit Cabinet

- 1. Unit cabinet shall be constructed of galvanized steel, and shall be bonderized and coated with a baked enamel finish on all externally exposed surfaces.
- 2. Unit cabinet exterior paint shall be: film thickness, (dry) 0.003 inches minimum, gloss (per ASTM D523, 60°F / 16°C): 60, Hardness: H-2H Pencil hardness.
- 3. Evaporator fan compartment interior cabinet insulation shall conform to AHRI Standards 210 or 360 minimum exterior sweat criteria. Interior surfaces shall be insulated with a minimum 3/4-in. thick, 1 lb. density, flexible fiberglass insulation, aluminum foil-face coated on the air side.
- 4. Base of unit shall have locations for thru-the-base gas and electrical connections (factory installed or field installed), standard.

5. Base Rail

- a. Unit shall have base rails on all sides.
- b. Holes shall be provided in the base rails for rigging shackles to facilitate maneuvering and overhead rigging.
- c. Holes shall be provided in the base rail for moving the rooftop by fork truck.
- d. Base rail shall be a minimum of 14 gauge thickness.
- 6. Condensate pan and connections:
 - a. Shall be a sloped condensate drain pan made of a non-corrosive material.
 - b. Shall comply with ASHRAE Standard 62.
 - c. Shall use a 1" x 11-1/2 NPT drain connection through the side of the drain pan. Connection shall be made per manufacturer's recommendations.

7. Gas Connections:

- a. All gas piping connecting to unit gas valve shall enter the unit cabinet at a single location on side of unit (horizontal plane).
- b. Thru-the-base capability
 - i. Standard unit shall have a thru-the-base gas-line location using a raised, embossed portion of the unit basepan.
 - ii. No basepan penetration, other than those authorized by the manufacturer, is permitted.

8. Electrical Connections

- a. All unit power wiring shall enter unit cabinet at a single, factory-prepared, knockout location.
- b. Thru-the-base capability
 - i. Standard unit shall have a thru-the-base electrical location(s) using a raised, embossed portion of the unit basepan.
 - ii. No basepan penetration, other than those authorized by the manufacturer, is permitted.
- 9. Component access panels (standard)
 - a. Cabinet panels shall be easily removable for servicing.
 - b. Stainless steel metal hinges are standard on all doors.

23 81 19.13.I. Gas Heat

1. General

- a. Heat exchanger shall be an induced draft design. Positive pressure heat exchanger designs shall not be allowed.
- b. Shall incorporate a direct-spark ignition system and redundant main gas valve.
- Heat exchanger design shall allow combustion process condensate to gravity drain; maintenance to drain the gas heat exchanger shall not be required.
- d. Gas supply pressure at the inlet to the rooftop unit gas valve must match that required by the manufacturer.
- 2. The heat exchanger shall be controlled by an integrated furnace controller (IFC) microprocessor.
 - a. IFC board shall notify users of fault using an LED (light-emitting diode).
- 3. Standard Heat Exchanger construction
 - Heat exchanger shall be of the tubular-section type constructed of a minimum of 20-gauge aluminum coated steel for corrosion resistance.
 - b. Burners shall be of the in-shot type constructed of aluminum-coated steel.
 - c. Burners shall incorporate orifices for rated heat output up to 2000 ft (610m) elevation. Additional accessory kits may be required for applications above 2000 ft (610m) elevation, depending on local gas supply conditions.
- 4. Optional Stainless Steel Heat Exchanger construction
 - a. Use energy saving, direct-spark ignition system.
 - b. Use a redundant main gas valve.
 - c. Burners shall be of the in-shot type constructed of aluminum-coated steel.
 - d. All gas piping shall enter the unit cabinet at a single location on side of unit (horizontal plane).
 - e. The optional stainless steel heat exchanger shall be of the tubular-section type, constructed of a minimum of 20-gauge type 409 stainless steel.
 - f. Type 409 stainless steel shall be used in heat exchanger tubes and vestibule plate.
 - g. Complete stainless steel heat exchanger allows for greater application flexibility.
- 5. Induced draft combustion motors and blowers
 - a. Shall be a direct-drive, single inlet, forward-curved centrifugal type.
 - b. Shall be made from steel with a corrosion-resistant finish.
 - c. Shall have permanently lubricated sealed bearings.
 - d. Shall have inherent thermal overload protection.
 - e. Shall have an automatic reset feature.



23 81 19.13.J. Coils

- 1. Standard Aluminum/Copper Coils:
 - a. Standard evaporator shall have aluminum lanced plate fins mechanically bonded to seamless internally grooved copper tubes with all joints brazed.
 - b. Evaporator and condenser coils shall be leak tested to 150 psig, pressure tested to 550 psig, and qualified to UL 1995 burst test at 2,200 psi.
 - c. Condenser coils shall be aluminum MicroChannel coils

23 81 19.13.K. Refrigerant Components

- 1. Refrigerant circuit shall include the following control, safety, and maintenance features:
 - a. Capillary tubes.
 - b. Refrigerant filter drier.
 - c. Service gauge connections on suction and discharge lines.
 - d. Pressure gauge access through an access port in the front and rear panel of the unit.

2. Compressors

- a. Unit shall use one fully hermetic, scroll compressor for each independent refrigeration circuit.
- b. Compressor motors shall be cooled by refrigerant gas passing through motor windings.
- Compressors shall be internally protected from high discharge temperature conditions. Advanced Scroll Temperature Protection on 240 size.
- d. Compressors shall be protected from an over-temperature and over-amperage conditions by an internal, motor overload device.
- e. Compressor shall be factory mounted on rubber grommets.
- f. Compressor motors shall have internal line break thermal and current overload protection.
- g. Crankcase heaters shall not be required for normal operating range.

23 81 19.13.L. Filter Section

- 1. Filters access is specified in the unit cabinet section of this specification.
- 2. Filters shall be held in place by filter tray, facilitating easy removal and installation.
- 3. Shall consist of factory-installed, low velocity, throw-away 2-in. thick fiberglass filters.
- 4. Filter face velocity shall not exceed 365 fpm at nominal airflows.
- 5. Filters shall be standard, commercially available sizes.
- 6. Only one size filter per unit is allowed.

23 81 19.13.M. Evaporator Fan and Motor

- 1. Evaporator fan motor:
 - a. Shall have permanently lubricated bearings.
 - b. Shall have inherent automatic-reset thermal overload protection.
 - c. Shall have a maximum continuous bhp rating for continuous duty operation; no safety factors above that rating shall be required.
- 2. Belt-driven Evaporator Fan:
 - a. Belt drive shall include an adjustable-pitch motor pulley.
 - b. Shall use sealed, permanently lubricated ball-bearing type.
 - c. Blower fan shall be double-inlet type with forward-curved blades.
 - d. Shall be constructed from steel with a corrosion resistant finish and dynamically balanced.

23 81 19.13.N. Condenser Fans and Motors

- 1. Condenser fan motors:
 - a. Shall be a totally enclosed motor.
 - b. Shall use permanently lubricated bearings.
 - c. Shall have inherent thermal overload protection with an automatic reset feature.
 - d. Shall use a shaft-down design. Shaft-up designs including those with "rain-slinger devices" shall not be allowed.
- 2. Condenser Fans shall:
 - a. Shall be a direct-driven propeller type fan
 - b. Shall have aluminum blades riveted to corrosion-resistant steel spiders and shall be dynamically balanced.

23 81 19.13.O. Special Features

- 1. Integrated Economizers:
 - a. Integrated, gear-driven parallel modulating blade design type capable of simultaneous economizer and compressor operation.
 - b. Independent modules for vertical or horizontal return configurations shall be available. Vertical return modules shall be available as a factory installed option.
 - c. Damper blades shall be galvanized steel with metal gears. Plastic or composite blades on intake or return shall not be acceptable.
 - d. Shall include all hardware and controls to provide free cooling with outdoor air when temperature and/or humidity are below setpoints.
 - e. Shall be equipped with gear driven dampers for both the outdoor ventilation air and the return air for positive air stream control.
 - f. Shall be capable of introducing up to 100% outdoor air.
 - g. Shall be equipped with a barometric relief damper capable of relieving up to 100% return air. The barometric relief damper shall include seals, hardware and hoods to relieve building pressure. Damper shall gravity close upon unit shut down.
 - h. Shall be designed to close damper(s) during loss-of-power situations with spring return built into motor.
 - i. An outdoor single-enthalpy sensor shall be provided as standard. Outdoor air enthalpy set point shall be adjustable and shall range from the enthalpy equivalent of 63°F @ 50% rh to 73°F @ 50% rh. Additional sensor options shall be available as accessories.
 - j. The economizer controller shall also provide control of an accessory power exhaust unit function. Factory set at 70%, with a range of 0% to 100%.
 - k. The economizer shall maintain minimum airflow into the building during occupied period and provide design ventilation rate for full occupancy. A remote potentiometer may be used to override the damper set point.
 - I. Economizer controller shall accept a 2-10Vdc CO2 sensor input for IAQ/DCV control. In this mode, dampers shall modulate the outdoor-air damper to provide ventilation based on the sensor input.
 - m. Actuator shall be direct coupled to economizer gear. No linkage arms or control rods shall be acceptable.
 - n. Economizer controller shall provide indications when in free cooling mode, in the DCV mode, or the exhaust fan contact is closed.

2. Two-Position Damper

- a. Damper shall be a Two-Position Damper. Damper travel shall be from the full closed position to the field adjustable %open setpoint.
- b. Damper shall include adjustable damper travel from 25% to 100% (full open).
- c. Damper shall include single or dual blade, gear driven damper and actuator motor.
- d. Actuator shall be direct coupled to economizer gear. No linkage arms or control rods shall be acceptable.
- e. Damper will admit up to 100% outdoor air for applicable rooftop units.
- f. Damper shall close upon indoor (evaporator) fan shutoff and/or loss of power.
- g. The damper actuator shall plug into the rooftop unit's wiring harness plug. No hard wiring shall be required.
- h. Outside air hood shall include aluminum water entrainment filter.
- 3. Manual damper
 - a. Manual damper package shall consist of damper, air inlet screen, and rain hood which can be preset to admit up to 50% outdoor air for year round ventilation.
- 4. Head Pressure Control Package
 - a. Controller shall control coil head pressure by condenser-fan cycling.
- 5. Liquid Propane (LP) Conversion Kit
 - a. Package shall contain all the necessary hardware and instructions to convert a standard natural gas unit for use with liquefied propane, up to 2000 ft (610m) elevation.
- 6. Unit-Mounted, Non-Fused Disconnect Switch:
 - a. Switch shall be factory-installed, internally mounted.
 - b. National Electric Code (NEC) and UL approved non-fused switch shall provide unit power shutoff.
 - c. Shall be accessible from outside the unit.
 - d. Shall provide local shutdown and lockout capability.



- e. Non-Powered convenience outlet.
- f. Outlet shall be powered from a separate 115-120v power source.
- g. A transformer shall not be included.
- h. Outlet shall be field-installed and internally mounted with easily accessible 115-v female receptacle.
- i. Outlet shall include 15 amp GFI receptacle.
- j. Outlet shall be accessible from outside the unit.

7. Flue Discharge Deflector:

- a. Flue discharge deflector shall direct unit exhaust vertically instead of horizontally.
- b. Deflector shall be defined as a "natural draft" device by the National Fuel and Gas (NFG) code.

8. Thru-the-Base Connectors:

a. Kits shall provide connectors to permit gas and electrical connections to be brought to the unit through the unit basepan.

9. Propeller Power Exhaust:

- a. Power exhaust shall be used in conjunction with an integrated economizer.
- b. Independent modules for vertical or horizontal return configurations shall be available.
- c. Horizontal power exhaust is shall be mounted in return ductwork.
- d. Power exhaust shall be controlled by economizer controller operation. Exhaust fans shall be energized when dampers open past the 0-100% adjustable setpoint on the economizer control.

10. Roof Curbs (Vertical):

- a. Full perimeter roof curb with exhaust capability providing separate airstreams for energy recovery from the exhaust air without supply air contamination.
- b. Formed galvanized steel with wood nailer strip and shall be capable of supporting entire unit weight.
- c. Permits installation and securing of ductwork to curb prior to mounting unit on the curb.

11. Universal Gas Conversion Kit:

a. Package shall contain all the necessary hardware and instructions to convert a standard natural gas unit to operate from 2000-7000 ft (610 to 2134m) elevation with natural gas or from 0-7000 ft (90-2134m) elevation with liquefied propane.

12. Outdoor Air Enthalpy Sensor:

a. The outdoor air enthalpy sensor shall be used to provide single enthalpy control. When used in conjunction with a return air enthalpy sensor, the unit will provide differential enthalpy control. The sensor allows the unit to determine if outside air is suitable for free cooling.

13. Return Air Enthalpy Sensor:

a. The return air enthalpy sensor shall be used in conjunction with an outdoor air enthalpy sensor to provide differential enthalpy control.

14. Indoor Air Quality (CO2) Sensor:


- a. Shall be able to provide demand ventilation indoor air quality (IAQ) control.
- b. The IAQ sensor shall be available in wall mount with LED display. The set point shall have adjustment capability.


15. Smoke detectors:


- a. Shall be a Four-Wire Controller and Detector.
- b. Shall be environmental compensated with differential sensing for reliable, stable, and drift-free sensitivity.
- c. Shall use magnet-activated test/reset sensor switches.
- d. Shall have tool-less connection terminal access.
- e. Shall have a recessed momentary switch for testing and resetting the detector.


f. Controller shall include:

- i. One set of normally open alarm initiation contacts for connection to an initiating device circuit on a fire alarm control panel
- ii. Two Form-C auxiliary alarm relays for interface with rooftop unit or other equipment.
- iii. One Form-C supervision (trouble) relay to control the operation of the Trouble LED on a remote test/reset station.
- iv. Capable of direct connection to two individual detector modules.
- v. Can be wired to up to 14 other duct smoke detectors for multiple fan shutdown applications.









BEFORE PURCHASING THIS APPLIANCE, READ IMPORTANT ENERGY COST AND EFFICIENCY INFORMATION AVAILABLE FROM YOUR RETAILER.

GENERAL TERMS OF LIMITED WARRANTY*

Rheem will furnish a replacement for any part of this product which fails in normal use and service within the applicable periods stated, in accordance with the terms of the limited warranty.

Compressor

3 Phase, Commercial ApplicationsFive (5) Years **Parts**

3 Phase, Commercial Applications.....One (1) Year

*For complete details of the Limited and Conditional Warranties, including applicable terms and conditions, contact your local contractor or the Manufacturer for a copy of the product warranty certificate.

Stainless Steel Heat Exchanger

3 Phase, Commercial ApplicationsTwenty (20) Years Standard Heat Exchanger

3 Phase, Commercial ApplicationsTen (10) Years



In keeping with its policy of continuous progress and product improvement, Rheem reserves the right to make changes without notice.

