



Air Conditioning & Heating

PRODUCT SPECIFICATIONS



1½ TO 2½ TON

ACNF SERIES

CEILING-MOUNT

AIR HANDLERS

The Goodman® ACNF Electric Heat Air Handler is designed to be ceiling-mounted. Its quiet operation and high performance makes the ACNF series a good choice for multi-family or lodging applications.

Standard Features

- Suitable for use with refrigerants R-410A (-16 models only) and R-22 (-16 & -1 models)
- Check flowrate for heat pump and cooling-only applications
- Direct-drive, resilient-mount, multi-speed motor
- Sequence-controlled and rust-resistant nickel chromium heating elements of 5, 6, 8 and 10 kW
- High-efficiency evaporator coil
- Quiet operation
- Available with and without heat
- ARI Certified
- ETL Certified

Cabinet Features

- Primary/secondary drain connection in a high-temperature plastic drain pan
- Suitable for free-return installation (non-ducted return air)
- Galvanized-steel construction
- Factory-installed pull-type disconnect
- Easy service access

Accessories

- Heat Pump Shut-off Relay Kit: HPSK-01
- Ceiling Access Panels:
 - CAP-1/ 1L (louvered) fits ACNF18
 - CAP-2/ 2L (louvered) fits ACNF24
 - CAP-3/ 3L (louvered) fits ACNF30



NOMENCLATURE

	A	C	N	F	3642	1	6	AA	
	1	2	3	4	5,6,7,8	9	10	11,12	
Brand					Engineering *				
A	Single-piece								Major/ Minor Revisions
	Air Handler								* Not used for inventory management
Unit Application					Refrigerant Compatability				
C	Ceiling Mount PSC Motor								No Digit = R-22 only
D	Downflow PSC Motor								6 = R-410A or R-22
E	Multi-Position Variable-Speed Motor								
R	Multi-Position PSC Motor								
S	Multi-Position EEM Motor								
W	Wall Mount PSC Motor								
Cabinet Finish					Electrical				
U	Unpainted								1 208/240 V, 1 Phase, 60 Hz
P	Painted								
N	Uncased								
Expansion Device					Nominal Capacity Range @ 13 SEER				
F	Flowrater								& Nominal Factory-Installed Electric Heat kW
T	Expansion Valve								1805 1½ Tons Cooling/ 5 kW Electric Heat
									2405 2 Tons Cooling/ 5 kW Electric Heat

SPECIFICATIONS

	ACNF 18001/16	ACNF 18051/16	ACNF 18061/16	ACNF 18081/16	ACNF 24001/16	ACNF 24051/16	ACNF 24061/16
Blower							
Diameter	5.75	5.75	5.75	5.75	6.31	6.31	6.31
Width	6.75	6.75	6.75	6.75	8.25	8.25	8.25
Coil Drain Connection FPT	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"
Service Valve							
Liquid	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Suction	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"
Electrical Data							
Min Circuit Ampacity @ 230V	0.9	27	33.5	40.5	1.68	27.8	34.3
Min Circuit Ampacity @ 208V	0.9	24.5	30.5	36.8	1.68	25.3	31.3
Max. Overcurrent Device @ 230V	15	30	40	50	15	30	40
Max. Overcurrent Device @ 208V	15	30	40	40	15	30	40
Minimum VAC	197	197	197	197	197	197	197
Maximum VAC	253	253	253	253	253	253	253
Electric Heat							
kW @ 230 Volts	0	4.8	6.0	7.3	0	4.8	6.0
BTU/h @ 230 Volts	0	16,392	20,490	24,930	0	16,392	20,490
Blower Motor							
FLA	0.72	0.72	0.72	0.72	1.34	1.34	1.34
HP	1/8	1/8	1/8	1/8	1/4	1/4	1/4
Ship Weight (lbs)	59	59	59	59	69	69	69

SPECIFICATIONS (CONT.)

	ACNF 24081/16	ACNF 24101/16	ACNF 30001/16	ACNF 30051/16	ACNF 30061/16	ACNF 30081/16	ACNF 30101/16
Blower							
Diameter	6.31	6.31	6.75	6.75	6.75	6.75	6.75
Width	8.25	8.25	8.25	8.25	8.25	8.25	8.25
Coil Drain Connection FPT	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"
Service Valve							
Liquid	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Suction	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"
Electrical Data							
Min Circuit Ampacity @ 230V	41.3	54.9	1.68	27.8	34.3	41.3	54.9
Min Circuit Ampacity @ 208V	37.6	49.8	1.68	25.3	31.3	37.6	49.8
Max. Overcurrent Device @ 230V	50	60	15	30	40	50	60
Max. Overcurrent Device @ 208V	40	50	15	30	40	40	50
Minimum VAC	197	197	197	197	197	197	197
Maximum VAC	253	253	253	253	253	253	253
Electric Heat							
kW @ 230 Volts	7.3	9.8	0	4.8	6.0	7.3	9.8
BTU/h @ 230 Volts	24,930	33,467	0	16,392	20,490	24,930	33,467
Blower Motor							
FLA	1.34	1.34	1.34	1.34	1.34	1.34	1.34
HP	1/4	1/4	1/4	1/4	1/4	1/4	1/4
Ship Weight (lbs)	69	69	79	79	79	79	79

Note:

When the room thermostat calls for second stage heat, the first stage (heat pump) operation must be locked out. When matching the "AC" unit that has electric heat with a heat pump, order "HEAT PUMP SHUT OFF KIT HPSK-01." The ACXX-00 units do not require this kit.

BLOWER PERFORMANCE

Model	Speed	CFM delivered against External Static Pressure				
		0.1"	0.2"	0.3"	0.4"	0.5"
ACNF18001/16	High	780	710	625	520	440
	Low	675	585	510	460	400
ACNF18051/16	High	780	710	625	520	440
	Low	675	585	510	460	400
ACNF18061/16	High	780	710	625	520	440
	Low	675	585	510	460	400
ACNF18081/16	High	780	710	625	520	440
	Low	675	585	510	460	400
ACNF24001/16	High	935	880	810	735	675
	Low	720	680	630	565	490
ACNF24051/16	High	935	880	810	735	675
	Low	720	680	630	565	490
ACNF24061/16	High	935	880	810	735	675
	Low	720	680	630	565	490

Model	Speed	CFM delivered against External Static Pressure				
		0.1"	0.2"	0.3"	0.4"	0.5"
ACNF24081/16	High	935	880	810	735	675
	Low	720	680	630	565	490
ACNF24101/16	High	935	880	810	735	675
	Low	720	680	630	565	490
ACNF30001/16	High	1,075	1,015	945	865	770
	Low	830	785	720	665	605
ACNF30051/16	High	1,075	1,015	945	865	770
	Low	830	785	720	665	605
ACNF30061/16	High	1,075	1,015	945	865	770
	Low	830	785	720	665	605
ACNF30081/16	High	1,075	1,015	945	865	770
	Low	830	785	720	665	605
ACNF30101/16	High	1,075	1,015	945	865	770
	Low	830	785	720	665	605




Note: Assumes dry coil with filter in place; 208-volt operation x .96

HEATING CAPACITY/kW CORRECTION FACTOR

Supply Voltage	240	230	220	210	208
Correction Factor	1.08	1.00	.92	.84	.82


(Multiply the 230-volt capacity by factors)

DIMENSIONS



Model	A	B	C	D
ACNF18	37 1/4"	34 11/16"	30"	6 1/2"
ACNF24	43 1/4"	40 11/16"	36"	6 1/2"
ACNF30	49 1/4"	46 11/16"	42"	6 1/2"

ACNF WIRING DIAGRAM



Wiring is subject to change. Always refer to the wiring diagram on the unit for the most up-to-date information.



WARNING

High Voltage:

Disconnect all power before servicing or installing this unit. Multiple power sources may be present. Failure to do so may cause property damage, personal injury, or death.



PRODUCT SPECIFICATIONS

NOTES

