




PRODUCT DIMENSIONS & SPECIFICATIONS

DX-TREME CR SERIES DEDICATED HORIZONTAL PLENUM COIL WITH BUILT-IN AUXILIARY DRAIN PAN



Representative image only. Some models may vary in appearance. Due to continuous product improvement, specifications are subject to change without notice.

STANDARD SPECIFICATIONS

- Rifled copper tubing, enhanced aluminum fins
- Immersion-tested at 500 psi, then nitrogen-pressurized and sealed
- Liquid line - 3/8" ODS, suction line - 3/4" ODS on 1-1/2-3 ton & 7/8" ODS on 3-1/2 - 5 ton.
- Externally mounted flowrater body or internally mounted factory-installed TXV
- Schrader valve on liquid line for hiss-testing
- Refrigerant lines exit top of coil
- Split access doors on top of coil for easy service
- Plastic drain pans (primary and secondary)
- Built-in auxiliary drain pan with 3/4" FPT
- Plenum sides and end constructed of foil-backed faced fiberglass ductboard. Plenum top and bottom constructed of galvanized steel
- AHRI certifiable with all brands of A/C and heat pump systems
- ETL listed for use with R-22 and R-410a when proper metering device is used
- Patented design (Patent No. 8,869,548 B2)
- Ten-year limited warranty with registration

COIL MODEL	R410a PISTON SIZE	DIMENSIONS			SHIPPING INFORMATION			
		CABINET WIDTH [W]"	CABINET DEPTH [D]"	CABINET HEIGHT [H]"	SHIPPING WEIGHT (LBS)			SKID QTY
					2 ROW	3 ROW	4 ROW	
CR24A*	0.055	20-1/2	31	15-1/2	42	51	N/A	8
CR24B*	0.055	20-1/2	31	19-1/2	47	56	N/A	8
CR24C*	0.055	20-1/2	31	23-1/2	57	69	N/A	8
CR30A*	0.059	20-1/2	31	15-1/2	48	58	N/A	8
CR30B*	0.059	20-1/2	31	19-1/2	47	56	N/A	8
CR30C*	0.059	20-1/2	31	23-1/2	57	69	N/A	8
CR36A*	0.068	20-1/2	31	15-1/2	55	66	N/A	8
CR36B*	0.068	20-1/2	31	19-1/2	55	66	N/A	8
CR36C*	0.068	20-1/2	31	23-1/2	57	69	N/A	8
CR36D*	0.068	20-1/2	40	19-1/2	93	112	N/A	8
CR42A*	0.074	20-1/2	40	19-1/2	62	75	N/A	8
CR42B*	0.074	20-1/2	40	23-1/2	67	80	N/A	8
CR42C*	0.074	20-1/2	40	25-1/2	62	75	N/A	8
CR48A*	0.08	20-1/2	40	23-1/2	76	92	N/A	8
CR48B*	0.08	20-1/2	40	25-1/2	73	87	N/A	8
CR48C*	0.08	20-1/2	40	25-1/2	93	112	135	8
CR60A*	0.089	20-1/2	40	23-1/2	124	149	N/A	8
CR60B*	0.089	20-1/2	40	25-1/2	125	150	180	8

Phone: 281.441.6500
Toll Free: 800.423.9007
Fax: 281.441.6510
www.aspenmfg.com



* For complete warranty details visit www.aspenmfg.com.

Revised 02/23/17. In keeping with its policy of continuous progress and product improvement, Aspen reserves the right to make changes without notice and incurring obligation. © 2015