

1/8 GPF Urinal EcoPower® Flushometer Valve

FEATURES

- Electronic flushometer valve, neutral rough-in, complete with 3/4" angle stop and 3/4" vacuum breaker set
- Hydropower self-generating system
- 1/8 GPF or less
- Manual override button
- 12 hour automatic flush for trap seal protection

MODELS

- TEU1UN#CP
Valve only, Left and right rough, Chrome plated finish
- TEU1UN12#CP (3/4" Vacuum breaker)
Left and right rough, Polished Chrome finish
Complete set supplied with:
Vacuum breaker & angle stop set - VB9CP-12
 - 3/4" Angle stop - 10077t4
 - 3/4" Vacuum breaker - 10075t2
 - Spud nut & escutcheon - 71051Nt5
 - Sweat solder kit - TH559EDVSJ1
- Optional Part:
Z-4000-J - Adapter for ground joint angle stops



COLORS/FINISHES

- #CP Chrome

CODES/STANDARDS (to be listed)

- Meets or exceeds ASSE 1037, CSA B125.3
- Certifications: IAPMO(cUPC), ASSE, State of Massachusetts, and others
- Code Compliance: UPC, IPC, NSPC, NPC Canada, California AB715, California Green Building Code and others
- ADA compliant

PRODUCT SPECIFICATION

TOTO® Model No. _____
Automatic infrared sensor activated, urinal flush valve. Heavy-duty zinc die cast cover with nickel chrome finish. Vandal resistant hex head screws. Automatic sensor adjustment on installation. Manual override button incorporated. Solenoid with self-cleaning mechanism. Automatic flush every twelve hours if not used. Angle stop and vacuum breaker included with accessories.



TEU1UN Series


1/8 GPF Urinal EcoPower® Flushometer Valve

SPECIFICATIONS

- Warranty Three Year Warranty
- Material Bronze casting
- Power Supply Hydro-Power Charge
- Water Supply 3/4" NPT
- Detection time Factory setting at six (6) seconds minimum
- Detection range Self-adjusting to environment
- Discharge quantity Preset to 1/8 gpf / 0.47 lpf
- Operating temperature 32°-104°F (0°-40°C)
- Supply water pressure 15 psi - 125 psi*
- Trap seal protection Automatically flushes once after twelve (12) hours of non-use

These specifications are subject to change without notice.

*Water pressures over 80 psi are not recommended for most plumbing fixtures.
Check your local plumbing code for details.



TOTO®

These dimensions and specifications are subject to change without notice