

60A-100 Steel & 60A-700 Stainless Steel Barstock Globe Valve



Job Name:	
Job Location:	
Engineer:	
Contractor:	
Tag:	
PO Number:	
Representative:	
Wholesale Distributor:	

Valve built to U.S. customary units. Reference metric units also shown.



DESCRIPTION

The Apollo® 60A Series Steel & Stainless Steel Barstock Globe Valves are ideally suited for use in instrumentation, sampling lines and flow control applications.

FEATURES

- Backseat stem design reduces pressure exerted on the packing, prolonging packing life. Design also prevents stem from being accidentally turned out of the valve.
- Integral metal-to-metal seat design.
- Externally adjustable PTFE packing is standard, graphoil available as an option.
- Malleable iron handle for long lasting, reliable service.
- All valves 100% pressure tested
- Fully threaded bonnet to accommodate optional panel mounting nut.
- Locking bonnet option available.
- All pressure retaining parts constructed of ASTM materials.
- Meets the requirements of MSS SP-99 & SP-105.
- Meets the requirements of NACE MR-01-75.

PERFORMANCE RATING

- Max Operating Pressure: 5000 psig @ 100°F 345 bar @ 38°C
- Temperature Range: -50°F to 1000°F (-46°C to 538°C)

OPTIONS & SIZES

- -01 Standard Configuration
- -07 Tee Handle (SS)
- -09 Lock Bonnet
- -24 Graphoil Packing
- -57 Oxygen Cleaned
- -88 Panel Mount
- 07 Tee Handle (SS) not available on 3/4" (DN 20) and 1" (DN 25) sizes
- Female x Female NPT end connections are standard.
- Socket weld end connections also available.

STANDARD MATERIALS LIST

Part Name	Material 60A-100	Material 60A-700							
Podu	ASTM A108	ASTM A276							
Body	Carbon Steel	316 Stainless Steel							
Hub	ASTM A108	ASTM A276							
пир	Carbon Steel	316 Stainless Steel							
Stem	ASTM A276 Stainless Steel								
Stem Packing	PTFE								
Gland	ASTM B484 ASTM B525								
Gland Nut	ASTM A108	ASTM A276							
GIANG NUL	Carbon Steel	316 Stainless Steel							
Handle ¹	ASTM A47 Malleable Iron,								
naliule	Zinc Phosphate Finish								
Handle Nut	Carbon Steel, Zinc Plated								

NOTE 1:


- 1/2" (DN 15) and smaller come standard with Cross Handle
- 3/4" (DN 20) and 1" (DN 25) sizes come standard with Tee Handle

Apollo Valves, Manufactured by Conbraco Industries, Inc.

701 Matthews Mint-Hill Road, Matthews, NC 28105 USA

www.apollovalves.com | (704) 841-6000

PRESSURE TEMPERATURE CURVE



538) (10) (27) (27) (27) (27) (27) (27) (27)

This specification is provided for reference only. Conbraco Industries Inc. reserves the right to change any portion of this specification without notice and without incurring obligation to make such changes to Conbraco products previously or subsequently sold. Please visit our website @www.apollovalves.com for the most current information.






60A-100 Steel & 60A-700 Stainless Steel Barstock Globe Valve

PRODUCT NUMBERING GUIDE

60	X	- X	Х	Х	- XX
SERIES	PRESSURE RATING	STYLE & MATERIAL	END CONNECTIONS	SIZE	OPTIONS
Conbraco Barstock Globe Valves	A = 5000 PSI (345 bar)	1 = Carbon Steel Globe	0 = FNPT x FNPT	1 = 1/4'' (DN 8)	01 = Standard
		7 = 316 Stainless Steel Globe	2 = Socket Weld	2 = 3/8" (DN 10) 07 = Tee Handle (SS)
			(Not Available on Angle Valves)	3 = 1/2'' (DN 15) 09 = Lock Bonnet
				4 = 3/4'' (DN 20) $24 =$ Grafoil Packing
				5 = 1'' (DN 25) $57 = 0xygen Cleaned$
					88 = Panel Mount

DIMENSIONS



Size		А			D		C C		D		F				Weight		
		Min.		Max.		D		Ľ		D		E		Cv	Kv	weight	
		In.	(mm)	In.	(mm)	ln.	(mm)	ln.	(mm)	ln.	(mm)	ln.	(mm)			lb.	(kg)
1/4″	(DN 8)	3.8	(96.5)	4.1	(104.1)	1.38	(35.1)	2.25	(57.2)	1.13	(28.7)	0.69	(17.5)	0.6	(0.5)	1.23	(0.6)
3/8″	(DN 10)	3.8	(96.5)	4.1	(104.1)	1.38	(35.1)	2.25	(57.2)	1.13	(28.7)	0.69	(17.5)	0.9	(0.8)	1.19	(0.5)
1/2″	(DN 15)	3.8	(96.5)	4.1	(104.1)	1.38	(35.1)	2.75	(69.9)	1.38	(35.1)	0.69	(17.5)	0.8	(0.7)	1.64	(0.7)
3/4"	(DN 20)	4.9	(124.5)	5.4	(137.2)	2.00	(50.8)	3.19	(81.0)	1.60	(40.6)	1.00	(25.4)	2.7	(2.3)	3.34	(1.5)
1″	(DN 25)	4.9	(124.5)	5.4	(137.2)	2.00	(50.8)	3.62	(92.0)	1.81	(46.0)	1.00	(25.4)	2.6	(2.2)	4.24	(1.9)

Apollo Valves, Manufactured by **Conbraco Industries, Inc.** 701 Matthews Mint-Hill Road, Matthews, NC 28105 USA www.**apollovalves**.com | (704) 841-6000

This specification is provided for reference only. Conbraco Industries Inc. reserves the right to change any portion of this specification without notice and without incurring obligation to make such changes to Conbraco products previously or subsequently sold. Please visit our website @ www.apollovalves.com for the most current information.

