

TRIPSAVER[®] Motors. A perfect name to describe the trustworthy advantages of three unique motors designed by PROTECH with the service technician in mind. TRIPSAVER[®] Motors single-handedly fulfill many requirements for replacements furnace, air handler and condenser fan motors.

Versatile, Dependable, Easy to Install

Wide-spread adaptability and convenience have made the **TRIPSAVER** name a legend in the industry.

TRIPSAVER Motors earned their outstanding distinction not only for their versatility, however. The qualities of reliability, dependability, and ease-of-installation helped establish their reputation too.

Saves Time and Money

TRIPSAVER Motors can save you time and money.

While no one motor can handle all of your motor service needs, **TRIPSAVER** Motors can easily fulfill the vast majority of your demands.

With the three **TRIPSAVER** Motors along on service calls, you'll never have to leave the job site for another motor.

Take a look at the features of the **TRIPSAVER** Motors inside and you'll know why.



PO Box 17010, Fort Smith, AR, 72917 3900 South Zero Street, Fort Smith, AR, 72908 Phone: (479) 646-4311 • Fax: (479) 648-4792



One Reliable Name. Three Great Motors

 Versatile, Dependable, Easy to Install
Saves Time and Money
Ideal Truck Stock

Professional Quality HVAC Parts and Suppl

51-23012-41



FURNACE MOTOR

The **TRIPSAVER** 115 Volt Furnace Motor will replace most gas furnace motors used today. Following are the features that make it so versatile:

- 1/2, 1/3, 1/4, 1/5 & 1/6 horsepower
- 115 volts
- 4 speed taps
- Reversible rotation
- Runs with 5, 7.5, and 10 mfd/370 vac capacitors (see motor label or PROTECH Master Catalog)
- 48 frame, 5.5-inch diameter
- 36-inch leads with easy-to-use flag QC terminals
- Operates in all positions
- Ports for re-oiling
- Mounts by belly band, thrubolts, or shell holes
- · Easy-to-follow installation instructions



CONDENSER FAN MOTOR

51-23053-21

The **TRIPSAVER** Condenser Fan Motor will replace most condenser fan motors used today. Following are the features that make it so versatile:

- 1/3 and 1/5 horsepower
- 208-230 volts
- 2 speeds
- Reversible rotation
- Runs with 5 and 7.5 mfd/370 vac capacitors (see motor label or PROTECH Master Catalog)
- 48 frame, 5.5-inch diameter
- 36-inch leads with easy-to-use flag QC terminals
- Operates in all positions
- Ports for re-oiling
- · Mounts by belly band, thrubolts, or shell holes
- Easy-to-follow installation instructions



ELECTRIC FURNACE-AIR HANDLER MOTOR

The **TRIPSAVER** 208-230 Volt Furnace Motor will replace most electric furnace and air handler motors used today. Following are the features that make it so versatile:

51-23022-41

- 1/2, 1/3, 1/4, 1/5 & 1/6 horsepower
- 208 230 volts
- 4 speed taps
- Reversible rotation
- Runs with 5, 7.5, and 10 mfd/370 vac capacitors (see motor label or PROTECH Master Catalog)
- 48 frame, 5.5-inch diameter
- 36-inch leads with easy-to-use flag QC terminals
- Operates in all positions
- Ports for re-oiling
- Mounts by belly band or thrubolts
- · Easy-to-follow installation instructions