

# **Product Catalog**

# Packaged Rooftop Air Conditioners Voyager™ Light Commercial – Heat Pump

12.5 to 20 Tons - 60 Hz







### Introduction

### **Packaged Rooftop Air Conditioners**

Through the years, American Standard has designed and developed the most complete line of Packaged Rooftop products available in the market today. American Standard was the first to introduce the Micro-microelectronic unit controls—and has continued to improve and revolutionize this design concept.

The ReliaTel control platform offers the same great features and functionality as the original Micro, with additional benefits for greater application flexibility.

Voyager continues to provide the highest standards in quality and reliability, comfort, ease of service, and the performance of American Standard light commercial products.

American Standard customers demand products that provide exceptional reliability, meet stringent performance requirements, and are competitively priced. American Standard delivers all of this with Voyager.

Voyager features cutting edge technologies: reliable compressors, American Standard engineered ReliaTel controls, computer-aided run testing, and Integrated Comfort™ Systems. So whether you're the contractor, the engineer or the owner, you can be certain Voyager Products are built to meet your needs.

### Copyright

This document and the information in it are the property of Trane, and may not be used or reproduced in whole or in part without written permission. Trane reserves the right to revise this publication at any time, and to make changes to its content without obligation to notify any person of such revision or change.

### **Trademarks**

American Standard and the American Standard logo, Frostat, Integrated Comfort, ReliaTel, Tracer, are trademarks of American Standard in the United States and other countries. All trademarks referenced in this document are the trademarks of their respective owners.

### **Revision Summary**

Updated Features & Benefits, Model Number Description, General Data, Electrical Data, Dimensional Data, Weights, and Mechanical Specifications sections.

©2017 Ingersoll Rand PKGP-PRC015R-EN



### **Table of Contents**

Features and Benefits
Standard Features and Available Options 4
Outstanding Standard Features 6
Variety of Options
Other Benefits
Application Considerations
Selection Procedure
Cooling Capacity
Heating Capacity
Model Number Description
General Data
Performance Data
Controls
Field Installed Control Options
Electrical Data
Dimensional Data
Weights
Jobsite Connections
Mechanical Specifications
General
Factory Installed Options
Factory or Field Installed Options 50
Field Installed Options



### **Features and Benefits**

**Note:** Packaged Rooftop units cooling, heating capacities, and efficiencies are AHRI certified within scope of AHRI Standard 340/360 (I-P) and ANSIZ21.47.

### **Standard Features and Available Options**

Table 1. Voyager™ Light Commercial control options — standard and optional

			Options <sup>(a)</sup>	
	Standard Features	Factory Installed	Factory or Field Installed	Field Installed
BACnet® Communications Interface (BCI)			Х	
LonTalk® Communications Interface (LCI)			Х	
ReliaTel™ Microprocessor Controls	Х			
ReliaTel™ Options Module			Х	
Trane® Communications Interface (TCI)			Х	
Zone Sensors and Remote Zone Sensors				Х

<sup>(</sup>a) Refer to model number description for option availability

Table 2. Voyager™ Light Commercial features - standard and optional

			Options <sup>(a)</sup>	
	Standard Features	Factory Installed	Factory or Field Installed	Field Installed
1-year Limited Parts Warranty	Х			
5-year Limited Compressor Warranty	Х			
2" MERV 8 Filters or 2" MERV 13 Filters with Filter Removal Tool		X		
2" throwaway filters	Х			
Anti-Short Cycle Timer	Х			
Barometric Relief			Х	
Belt Drive Motors	Х			
Black Epoxy Pre-Coated Coils		Х		
Clogged Filter/Fan Failure Switch			Х	
CO <sub>2</sub> Sensor				Х
CO <sub>2</sub> Sensor Wiring (Wiring Only)		Х		
Colored and Numbered Wiring	Х			
Condensate Overflow Switch		Х		
Crankcase Heaters	Х			
Dedicated Airflow	Х			
Digital Display Zone Sensor				Х
Discharge Air Temperature Sensing Kit			Х	
Easy Access Low Voltage Terminal Board (LTB)	Х			
Economizer - Standard, Downflow			Х	
Economizer - Standard, Horizontal				Х
Electric Heaters			Х	
Fault Detection Diagnostics (FDD)		Х		
Foil-Faced and Edge Captured Insulation	Х			
Frostat™			Х	



Table 2. Voyager™ Light Commercial features - standard and optional

			Options <sup>(a)</sup>	
	Standard Features	Factory Installed	Factory or Field Installed	Field Installed
High Efficiency Motors		Х		
High Pressure Cutout	Х			
High Short Circuit Current Rated (SCCR) Electrical Subsystem		Х		
High Static Drive				Х
Hinged Access Doors		Х		
Human Interface - 5 inch Color Touchscreen		Х		
IAQ Sloped Condensate Drain Pan	Х			
Indoor Fan Motor Shaft Grounding Ring			Х	
Liquid Line Refrigerant Drier	Х			
Low Ambient Cooling to 0°F	Х			
Low Leak Economizer - Downflow			Х	
Low Leak Economizer - Downflow and Horizontal				Х
Manual Outside Air Dampers				Х
Motorized Outside Air Dampers				Х
Multi-Speed Indoor Fans		Х		
Operating Charge of R-410A	Х			
Oversized Motors			Х	
Phase Monitor	Х			
Powered Exhaust				Х
Powered or Unpowered Convenience Outlet		Х		
Quick Access Panels	Х			
Quick Adjust Idler Arm Pulley	Х			
Reference or Comparative Enthalpy			Х	
Remote Potentiometer				Х
Roof Curb (Downflow Only)				Х
Single Point Power	Х			
Single Side Service	Х			
Single Zone Variable Air Volume (SZ VAV)		Х		
Stainless Steel Drain Pan		Х		
Standardized Components	Х			
Supply and/or Return Air Smoke Detector		Х		
Through the Base Electrical Access		Х		
Through the Base Electrical with Circuit Breaker		Х		
Through the Base Electrical with Disconnect Switch		Х		
Tool-less Hail Guards			Х	
U-shaped Airflow Pattern	Х			
Variable Frequency Drive (Multispeed Indoor Fan and Single Zone VAV)	Х			
Ventilation Override Accessory				Х

<sup>(</sup>a) Refer to model number description for option availability.

**Note:** Most Factory Installed Options (FIOPS) available for Downflow Air Discharge units only. Please verify with ordering system for availability.

### **Features and Benefits**

### **Outstanding Standard Features**

### **Anti-Short Cycle Timer**

Provides a 3 minute minimum "ON" time and 3 minute "OFF" time for compressors to enhance compressor reliability by assuring proper oil return.

### **Colored and Numbered Wiring**

Save time and money tracing wires and diagnosing the unit.

### Compressors

Voyager™ contains the best compressor technology available to achieve the highest possible performance. Dual compressors are outstanding for humidity control, light load cooling conditions and system back-up applications. Dual compressors are available on all models.

### **Condenser Coil**

Voyager boasts a patent-pending 1+1+1 condenser coil (pictured right), permanently gapped for easy cleaning.



### Controls - ReliaTel™

ReliaTel microprocessor controls provide unit control for heating, cooling and ventilating utilizing input from sensors that measure indoor and outdoor temperature and other zone sensors. ReliaTel also provides outputs for building automation systems and expanded diagnostics. For a complete list of ReliaTel offerings, refer to "Other Benefits," p. 13.

### **Conversion-less Units**

The dedicated design units (either downflow or horizontal) require no panel removal or alteration time to convert in the field — a major cost savings during installation. Horizontal units come complete with duct flanges so the contractor doesn't have to field fabricate them. These duct flanges are a time and cost saver.

#### Crankcase Heaters

These band or insertion heaters provide improved compressor reliability by warming the oil to prevent migration during off-cycles or low ambient conditions. These are standard on all Voyager models.

### **Discharge Line Thermostat**

A bi-metal element discharge line thermostats installed as a standard feature on the discharge line of each system. This standard feature provides extra protection to the compressors against high discharge temperatures in case of loss of charge, extremely high ambient and other conditions which could drive the discharge temperature higher.

### **Easy Access Low Voltage Terminal Board**



Voyager's Low Voltage Terminal Board is external to the electrical control cabinet. It is extremely easy to locate and attach the thermostat wire and test operation of all unit functions. This is another cost and time saving installation feature.

### **Foil Faced Insulation**



All panels in the evaporator section of the unit have cleanable foil-faced insulation. All edges are either captured or sealed to ensure no insulation fibers get into the airstream.

### **Low Ambient Cooling**


All Voyager microprocessor units have cooling capabilities down to 0°F as standard.

### **Low Voltage Connections**

The wiring of the low voltage connections to the unit and the zone sensors is as simple as 1-1, 2-2, and 3-3. This simplified system makes it easy for the installer to wire.

#### **Motors**

All indoor fan motors are belt drive as standard.



### **Pressure Cutouts**

Low and high pressure cutouts are standard on all Voyager models.

### **Phase Monitor**

The phase monitor provides 100% protection for motors and compressors against problems caused by phase loss, phase imbalance, and phase reversal. It is also equipped with an LED that provides an ON or FAULT indicator.

#### **Quick-Access Panels**

Remove three or fewer screws for access to the standardized internal components and wiring.

### Quick-Adjust Idler Arm

With the Quick-Adjust Idler Arm (pictured right), the belt and sheaves can be quickly adjusted without moving the mounted fan motor. The result is a major savings in time and money.

### **Single Point Power**

A single electrical connection powers the unit.





#### **Features and Benefits**

### Single Side Service

Single side service is standard on all units.

### **Sloped Drain Pans**

Standard on every unit.

### **Standardized Components**

Components are placed in the same location on all Voyager units. Familiarize yourself with one Voyager and you are familiar with every Voyager. Due to standardized components throughout the Voyager line, contractors/owners can stock fewer parts.

### **U-Shaped Airflow Pattern**

The U-shaped airflow allows for improved static capabilities.

### Variable Frequency Drives - VFD (Multispeed Indoor Fan and SZ VAV Only)

Variable Frequency Drives are factory installed and tested to provide supply fan motor speed modulation, as well as modulating gas heat. VFDs on the supply fan, as compared to inlet guide vanes or discharge dampers, are quieter, more efficient, and are eligible for utility rebates. All VFDs are designed to allow bypass if required. Bypass control will simply provide full nominal airflow in the event of drive failure. Modulating gas heat models with VFDs allow tighter space temperature control with less temperature swing.

### **Variety of Options**

### **Factory Installed Options**

### **Black Epoxy Pre-Coated Coils**

The pre-coated coils are an economical option for protection in mildly corrosive environments.

### CO<sub>2</sub> Sensor Wiring

This unit wiring for field installed C0<sub>2</sub> sensors. Factory-installed C0<sub>2</sub> sensor wiring saves time and ensures proper unit connections for the field installed C0<sub>2</sub> sensor kits.

### **Condensate Overflow Switch**

A condensate overflow switch is available to shut the unit down in the event that the condensate drain line becomes clogged. This option protects the unit from water overflowing from the drain pan and entering the base of the units.

### Fault Detection & Diagnostics (FDD)

This offering meets the mandatory requirement of CA Title 24 of fully configurable diagnostics allowing fault history and reading fault codes at the unit. This option provides detection of the following faults: Air temperature sensor failure/fault and notification of acceptable economizer mode. The FDD system shall be certified by the Energy Commission as meeting the requirements.

### **High Efficiency Filtration**

Voyager units offer a variety of high efficiency filtration options. MERV 8 and MERV 13 filters provide additional filtration beyond the capabilities of typical 2" throwaway filters. Also, when MERV 8 or MERV 13 filters are ordered, units come equipped with a filter removal tool.

### **High Efficiency Motors**

This option is available with efficiency ratings from 86.5 up to 91.0. It is not available for all models.



### **High Short Circuit Current Rating (SCCR)**

Voyager rooftop units now have an optional high short circuit current rated electrical subsystem for units with an MOP above 60A. This option is a perfect fit for applications that need protection against high potential fault currents. This option also includes individual over current protection for each compressor and the indoor fan, as well as a dedicated over current protection to the condenser fan motor(s). When the high SCCR is ordered, the control box will have components separated into two sections - high and low voltage components.

### **Hinged Access Doors**

These doors permit easy access to the filter, fan/heat, and compressor/control sections. They reduce the potential roof damage from screws or sharp access door corners.

#### **Human Interface**

The 5 inch Color Touchscreen Human Interface provides an intuitive user interface to the rooftop unit that speeds up unit commissioning, shortens unit troubleshooting times, and enhances preventative maintenance measures. The human interface includes several features such as:

- Data trending capabilities by means of time series graphs
- Historical alarm messages
- Real-time sensor measurements
- On board system setpoints
- USB port that enables the downloading of component runtime information as well as trended historical sensor data
- Customizable reports

### Multi-Speed Indoor Fan System

Multi-speed indoor fan system is designed for use in applications for meeting the minimum requirement of CA Title 24. This system incorporates a multi-speed fan control to change the speed of the fan to 67% of full airflow based off compressor stages.

### **Powered or Unpowered Convenience Outlet**

This option is a GFCI, 120V/15amp, 2-plug, convenience outlet, either powered or unpowered. This option can only be ordered when Through the Base Electrical with either the Disconnect Switch or Circuit Breaker option is ordered. This option is available on all models.

### Single Zone VAV - One Zone Variable Air Volume Mode

**Note:** Single Zone VAV is designed to be used with a zone sensor. If a unit is configured for Single Zone VAV operation but is connected to a thermostat, the control will revert to multi-speed (2-Speed) indoor fan control. (See "Multi-Speed Indoor Fan System" above.)

Single Zone VAV is designed for use in single zone applications like gymnasiums, auditoriums, manufacturing facilities, retail box stores, and any large open spaces, where there is a lot of diversity in the load profile. Single Zone VAV (SZ VAV) is an ideal replacement to "yesterday's" constant volume (CV) systems, by reducing operating costs while improving occupant comfort. SZ VAV systems combine Trane application, control and system integration knowledge to exactly match fan speed with cooling and heating loads, regardless of the operating condition. Trane algorithms meet/exceed ASHRAE 90.1- 2010, SZ VAV energy-saving recommendations, and those of CA Title 24. The result is an optimized balance between zone temperature control and system energy savings. Depending on your specific application, energy savings can be as much as 20%.





#### **Features and Benefits**

**Note:** Building system modeling in energy simulation software like TRACE is recommended to evaluate performance improvements for your application.

SZ VAV is fully integrated into the ReliaTel Control system and is available today. It provides the simplest and fastest commissioning in the industry through proven factory-installed, wired, and tested system controllers. All control modules, logic and sensors are factory installed, and tested to assure the highest quality and most reliable system available. This means no special programming of algorithms, or hunting at the jobsite for sensors, boards, etc. that need to be installed in the field.

#### Stainless Steel Drain Pan

For excellent corrosion and oxidation resistance, the optional stainless steel drain pan provides a cleanable surface that complement other IAQ solutions such as high efficiency filtration (MERV 8 or 13), and demand control ventilation (CO<sub>2</sub>).

### Supply, Return, and Plenum Air Smoke Detector

With this option (pictured right) installed, if smoke is detected, all unit operation will be shut down. Reset will be manual at the unit. Return Air Smoke Detectors require minimum allowable airflow when used with certain models.

Supply and/or Return Smoke Detectors may not be used with the Plenum Smoke Detector.



### Through the Base Electrical/Horizontal Side Access with Circuit Breaker

This option is a factory installed thermal-magnetic, molded case, HACR Circuit Breaker with provisions for through the base electrical connections.

### Through the Base Electrical/Horizontal Side Access with Disconnect Switch

Factory installed 3-pole, molded case, disconnect switch with provisions for through the base electrical connections are available.

### Through the Base Utilities Access

An electrical service entrance shall be provided allowing electrical access for both control and main power connections inside the curb and through the base of the unit. This option will allow for field installation of liquid-tight conduit and an external, field-installed disconnect switch.

### **Factory or Field Installed Options**

### **BACnet™ Communications Interface**

The BACnet communications interface allows the unit to communicate directly with a generic open protocol BACnet MS/TP Network Building Automation System Controls.

#### **Barometric Relief**

Designed to be used on downflow units, barometric relief is an unpowered means of relieving excess building pressure.

### Clogged Filter/Fan Failure Switch

A dedicated differential pressure switch is available to achieve active fan failure indication and/or clogged filter indication.

### **Discharge Air Sensing Kit**

Provides true discharge air sensing in heating models. The kit is functional only with the ReliaTel $^{\text{TM}}$  Options Module.



### **Economizer - Standard, Downflow**

Economizers are equipped with either dry bulb, reference, or comparative enthalpy sensing. These economizers provide free cooling as the outdoor temperature and/or humidity decreases. Correctly installed, they offer a valuable energy savings. Factory-installed economizers save time and ensure proper installation.

**Note:** Factory-installed economizers require some field set-up.

### **Economizer - Low Leak, Downflow**

This accessory meets low leak requirements for ASHRAE 90.1, IECC, and CA Title 24 standards (3 cfm/ft^2@1" wg exterior air, 4 cfm/ft^2@1" wg return air). This option allows 100% outdoor air supply from 0-100% modulating dampers and is standard with barometric relief. It can be paired with powered exhaust for additional building pressure relief. This option can be paired with or without Fault Detection & Diagnostics (FDD) to meet current mandatory CA Title 24 requirements. Available on downflow units only. The economizers come with three control options, dry bulb and reference or comparative enthalpy (optional).

#### **Electric Heaters**

Electric heat modules are available within the basic unit. If ordering the Through the Base Electrical option with an Electrical Heater, the heater must be factory installed.

#### Frostat™

This capillary bulb embedded in the face of the evaporator coil monitors coil temperature to prevent evaporator icing and protect the compressor. Recommended for applications with low leaving air temperatures, low airflow and/or high latent load applications.

### Indoor Fan Motor Shaft Grounding Ring

Shaft grounding rings are used on all VFD driven motors to provide a conductive discharge path away from the motor bearings to ground. Bearing Protection Rings shall be maintenance free circumferential rings of conductive micro fibers that discharge voltages to ground.

### **Oversized Motors**

Factory or field installed oversized motors are available for high static applications.

### **Reference or Comparative Enthalpy**

Measures and communicates humidity while maximizing comfort control.

### ReliaTel Options Module (RTOM)

The RTOM monitors the supply fan proving, clogged filter, supply air temperature, exhaust fan setpoint, dehumidification setpoint, supply air tempering, Frostat™ and smoke detector.

### **Tool-less Hail Guards**

Tool-less, hail protection quality coil guards (pictured right) shall be either factory or field-installed for condenser coil protection. This option protects the condenser coil from vandalism and/or hail damage.



### **Field Installed Options**

### CO<sub>2</sub> Sensor - Demand Control Ventilation (DCV)

Demand-controlled ventilation (DCV) is a control strategy that responds to the actual demand (need) for ventilation by regulating the rate at which the HVAC system brings outdoor air into the



#### **Features and Benefits**

building. A CO<sub>2</sub> sensor measures the concentration (parts per million, ppm) of CO<sub>2</sub> (Carbon Dioxide) in the air. As the CO<sub>2</sub> concentration changes, the outside air damper modulates to meet the current ventilation needs of the zone. The CO<sub>2</sub> sensor kit is available as a field installed accessory. Two field installed kits are offered; CO<sub>2</sub> sensor and wiring or CO<sub>2</sub> sensor only. The CO<sub>2</sub> Sensor only kit should be ordered with factory installed CO<sub>2</sub> sensor wiring. Factory installed CO<sub>2</sub> sensor wiring saves set-up time and ensures proper unit connections for the CO<sub>2</sub> sensor.

### **Dampers**

0-25 percent manual or 0-50 percent motorized outside air dampers are available.

### **Digital Display Zone Sensor**

The Digital LCD (Liquid Crystal Display) zone sensor has the look and functionality of standard zone sensors.

#### **Economizer - Standard, Horizontal**

Economizers are equipped with either dry bulb or reference or comparative enthalpy sensing. These economizers provide free cooling as the outdoor temperature and/or humidity decreases. Correctly installed, they offer a valuable energy savings.

### **Economizer - Low Leak, Downflow & Horizontal**

This accessory meets low leak requirements for ASHRAE 90.1, IECC, and CA Title 24 standards (3 cfm/ft^2@1" wg exterior air, 4 cfm/ft^2@1" wg return air). This option allows 100% outdoor air supply from 0-100% modulating dampers and is standard with barometric relief. It can be paired with powered exhaust for additional building pressure relief.

### **High Static Drive Accessory**

Available on many models, this high static drive accessory extends the capability of the standard motor. Avoid expensive motors and operating costs by installing this optimized sheave accessory.

### **Powered Exhaust**

This option is available on downflow units and provides exhaust of the return air, when using a downflow economizer, to maintain proper building pressurization. Great for relieving most building overpressurization problems.

#### **Remote Potentiometer**

When properly installed in the economizer control circuitry, this accessory provides a remote variable resistance to enable the operator to adjust the minimum damper position.

#### Roof Curbs

Available for downflow units. Only two roof curbs for the entire Voyager line simplifies curb selection.

### **Ventilation Override Accessory**

With the Ventilation Override Accessory installed, the unit can be set to transition to up to 3 different pre-programmed sequences for Smoke Purge, Pressurization and Exhaust. The transition occurs when a binary input on the RTOM is closed (shorted). This would typically be a hard wired relay output from a smoke detector or fire control panel. The ventilation override kit is available as a field installed accessory.

### **Zone Sensors/Thermostats**

Available in programmable, automatic and manual styles.

**Note:** Zone sensors required for units configured for Single Zone VAV indoor fan system control to enable Single Zone VAV functionality.



### Other Benefits

### **Cabinet Integrity**

For added water integrity, Voyager has a raised 1-1/8" lip around the supply and return of the downflow units to prevent water from blowing into the ductwork.

### Easy to Install, Service and Maintain

Because today's owners are very cost-conscious when it comes to service and maintenance, Voyager was designed with direct input from service contractors. This valuable information helped to design a product that would get the serviceman off the job quicker and save the owner money. Voyager does this by offering outstanding standard features enhanced by a variety of factory and field installed options, multiple control options, rigorously tested proven designs and superior product and technical support.

### **Outstanding Airflow Distribution**


Airflow is outstanding. The Voyager can replace an older machine with old ductwork and, in many cases, improve the comfort through better air distribution.

### **ReliaTel™ Controls Benefits**

ReliaTel controls provide unit control for heating, cooling and ventilating by utilizing input from sensors that measure outdoor and indoor temperature.

Quality and Reliability are enhanced through ReliaTel control and logic:

- Prevents the unit from short cycling, considerably improving compressor life.
- Ensures the compressor will run for a specific amount of time which allows oil to return for better lubrication, enhancing the reliability of the compressor.



Voyager with ReliaTel reduces the number of components required to operate the unit, thereby reducing possibilities for component failure.

### ReliaTel Makes Installing and Servicing Easy

ReliaTel eliminates the need for field installed anti-short cycle timer and time delay relays.

ReliaTel controls provide these functions as an integral part of the unit. The contractor no longer has to purchase these controls as options and pay to install them. The wiring of the low voltage connections to the unit and the zone sensors is as easy as 1-1, 2-2, and 3-3. This simplified system makes wiring easier for the installer.

### ReliaTel Makes Testing Easy

ReliaTel requires no special tools to run Voyager unit through its paces. Simply place a jumper between Test 1 and Test 2 terminals on the Low Voltage Terminal Board and the unit will walk through its operational steps automatically.

The unit automatically returns control to the zone sensor after stepping through the test mode a single time, even if the jumper is left on the unit.

As long as the unit has power and the "system on" LED is lit, ReliaTel is operational. The light indicates that the controls are functioning properly.

Some zone sensor options have central control panel lights which indicate the mode the unit is in and possible diagnostic information (dirty filters for example).



#### **Features and Benefits**

#### Other ReliaTel Benefits

The ReliaTel built-in anti-shortcycle timer, time delay relay and minimum "on" time control functions are factory tested to assure proper operation. ReliaTel softens electrical "spikes" by staging on fans, compressors and heaters. Intelligent Fallback is a benefit to the building occupant. If a component goes astray, the unit will continue to operate at predetermined temperature setpoint.

Intelligent Anticipation is a standard ReliaTel feature. It functions continuously as ReliaTel and zone sensor(s) work together in harmony to provide much tighter comfort control than conventional electro-mechanical thermostats.

The same ReliaTel Board fits all Packaged Gas/Electric, Cooling, and Heat Pump models. This provides standardization of parts for contractors. Less money is tied up in inventory with ReliaTel.

### **Rigorous Testing**

All of Voyager's designs were rigorously rain tested at the factory to ensure water integrity. Each part of the top (either two or three pieces) overlaps in such a way that water cannot leak into the unit. These overlapped edges are gasketed and sealed to ensure superior water integrity.

Actual shipping tests were performed to determine packaging requirements. Units were test shipped around the country to determine the best packaging. Factory shake and drop tests were used as part of the package design process to help assure that the unit arrives at the job site in top condition.

Rigging tests include lifting a unit into the air and letting it drop one foot, assuring that the lifting lugs and rails hold up under stress.

We perform a 100% coil leak test at the factory. All coils are pressure and leak tested at a minimum of 450 psig. The completely assembled refrigerant system is leak tested at a minimum of 240 psig with a refrigerant and nitrogen mixture.

All parts are inspected at the point of final assembly. Sub-standard parts are identified and rejected immediately. Every unit receives a 100 percent unit run test before leaving the production line to make sure it lives up to rigorous American Standard requirements.

### **Unmatched Support**

American Standard Sales Representatives are a Support Group that can assist you with:

Product

- Special Applications
- Application
- Specifications

Service

Computer Programs and much more

Training



### **Application Considerations**

Application of this product should be within the catalogued airflow and cooling considerations.

### Low Ambient Cooling

This Packaged Rooftop line features, as a standard, low ambient cooling down to 0°F. Contact your local American Standard Representative for more assistance with low ambient cooling applications.

### **Barometric Relief**

This product line offers an optional barometric relief damper included in the downflow economizer accessory. This accessory consists of gravity dampers which open with increased pressure. As the building air pressure increases, the pressure in the unit return air section also increases, opening the dampers and relieving the conditioned space.

Important: THE EFFECTIVENESS OF BAROMETRIC RELIEF DAMPER DURING ECONOMIZING OPERATION IS SYSTEM RELATED. PRESSURE DROP OF THE RETURN AIR SYSTEM SHOULD BE CONSIDERED TO CONTROL BUILDING PRESSURIZATION.

### **Power Exhaust Accessory**

The power exhaust accessory is available on all downflow units. This accessory can be field installed and will assist in relieving a building's pressurization.

### **Condensate Trap**

The evaporator is a draw-thru configuration. A trap must be field provided prior to start-up on the cooling cycle.

### **Clearance Requirements**

The recommended clearances identified with unit dimensions should be maintained to assure adequate serviceability, maximum capacity and peak operating efficiency. Actual clearances which appear inadequate should be reviewed with the local American Standard sales personnel.

#### **Unit Pitch**

These units have sloped condensate drain pans. Units must be installed level, any unit slope must be toward access side of unit.



### **Selection Procedure**

### **Cooling Capacity**

### Step 1

Calculate the building's total and sensible cooling loads at design conditions. Use the American Standard calculation form or any other standard accepted method.

### Step 2

Given the following building requirements:

A. Electrical Characteristics: 460/60/3

B. Summer Design Conditions: Entering Evaporator Coil: 80 DB/ 67 WB

Outdoor Ambient: 95 DB

C. Total Cooling Load: 172 MBh

D. Sensible Cooling Load: 122 MBh

E. Airflow: 6000 cfm

F. External Static Pressure: 0.50 in. w.g.

G. Rooftop - downflow configuration.

H. Accessories, Economizer, Supplementary Electric Heat

I. Heating Capacity 100 MBh

460 volt/3 phase Electric Supplemental Heat - at 6000 cfm

Size the equipment using Table 5, p. 23. As a starting point, a rough determination of the size of the unit must be made. This selection will then be confirmed after examining the performance at the given conditions. Divide the total cooling load by nominal BTUH per ton (12 MBh per ton); then round up to the nearest unit size. 172 MBh/12 MBh = 14.33 (approx. 15 tons.)

#### Step 3

Table 5, p. 23 shows that a WSD180E4 has a gross cooling capacity of 186.2 MBh and 138.9 MBh sensible capacity at 95°F ambient and 6000 cfm with 80 DB/67 WB air entering the evaporator.

### To Find Capacity at Intermediate Conditions

When the design conditions are between two numbers that are in the capacity table, interpolation is required to approximate the capacity.

**Note:** Extrapolation outside of the table conditions is not recommended.

### Step 4

Verify that there will be enough capacity by determining net capacity. In order to select the correct unit which meets the building's requirements, the fan motor heat must be deducted from the gross cooling capacity. The amount of heat that the fan motor generates is dependent on the effort by the motor CFM and static pressure. To determine the total unit static pressure, add the following:

External Static: 0.50 in.

Standard Filter 1 in: 0.05 in. (from Table 14, p. 28) Economizer Return Air: 0.04 in. (from Table 14, p. 28)

Electric Heater Size 18 kW: 0.06 in.

Total Static Pressure: 0.65 in.

**Note:** The Evaporator Fan Performance Table 8, p. 26 has already accounted for the pressure drop for standard filters and wet coils.



Therefore, the actual Total Static Pressure is 0.65 - 0.05 = 0.6. With 6000 CFM and 0.60 inches, Table 8, p. 26 shows 2.17 Bhp.

The note below Table 8, p. 26 gives a formula to calculate Fan Motor Heat:

```
3.15 \times bhp = MBh
3.15 \times 2.17 = 6.835 MBh
```

Now subtracting the fan motor heat from the gross cooling capacity of the unit:

```
Net Total Cooling Capacity =

186.2 - 6.835 = 179.36 MBh

Net Sensible Cooling Capacity =

138.9 - 6.385 = 132.065 MBh
```

### Step 5

If the performance will not meet the required load of the building, try a selection at the next higher size unit.

### **Heating Capacity**

### Step 1

Calculate the building heating load using the American Standard calculation form or other standard accepted method.

### Step 2

Size the equipment using Table 16, p. 30 to match the heating loads at design conditions.

A. Total Heating Load: 100 MBh

B. Outdoor Ambient (Winter) 17 DB

C. Indoor Return Temperature: 70 DB

D. Airflow: 6000 CFM

Use the integrated portion of Table 16, p. 30 for the WSD180E4 to determine capacity at winter design conditions. The mechanical heating portion of the heat pump will provide 85.4 MBh.

#### Step 3

Because 45 MBh is less than the building's required heating capacity at winter design conditions, a supplementary heater must be selected.

```
100.0 - 85.54 = 14.46 MBh
```

From Table 19, p. 31, at 480 volts, the 18 kW Heater will be adequate to do the job.

18 kW 61 MBh

From Table 19, p. 31 select heater AYDHTRK418A (18 kW 460/60/3).



### **Model Number Description**

 W
 S
 D

 1
 5
 0

 2
 3

 4
 5

 6
 7

 8
 9

### Digit 1 - Unit Type

W = Packaged Heat Pump, Electric Heat

### Digit 2 - Efficiency

S = Standard Efficiency

#### **Digit 3 – Airflow Configuration**

D = Downflow H = Horizontal

### Digit 4, 5, 6 — Nominal Gross Cooling Capacity (MBh)

 $150 = 12\frac{1}{2}$  Tons 180 = 15 Tons 240 = 20 Tons

### Digit 7 — Major Design Sequence

E = R-410A Refrigerant

### Digit 8 - Voltage Selection

3 = 208-230/60/3 4 = 460/60/3W = 575/60/3

#### Digit 9 - Unit Controls

R = Reliatel

### Digit 10 - Heating Capacity

0 = No Heat
G = 18 kW Electric Heat
N = 36 kW Electric Heat
P = 54 kW Electric Heat
R = 72 kW Electric Heat

### Digit 11 — Minor Design Sequence

### Digit 12, 13 — Service Sequence

#### Digit 14 - Fresh Air Selection

0 = No Fresh Air

D = Econ Dry Bulb w/ Barometric Relief<sup>1</sup>

F = Econ Reference Enthaply w/ Barometric Relief<sup>1</sup>

H = Econ Comparative Enthaply w/ Barometric Relief<sup>1</sup>

K = Low Leak Econ w/ Barometric Relief<sup>1</sup>

M = Low Leak Econ Reference Enthalpy w/ Barometric Relief<sup>1</sup>

P = Low Leak Econ Comparative Enthalpy w/ Barometric Relief<sup>1</sup>

### Digit 15 — Supply Fan/Drive Type/Motor

0 = Standard Motor 1 = Oversized Motor<sup>5</sup>

3 = High Efficiency Motor<sup>5</sup>

6 = Single Zone Variable Air Volume Standard Motor

7 = Multi-Speed Standard Motor

8 = Single Zone Variable Air Volume Oversized Motor

9 = Multi-Speed Oversized Motor

A = Single Zone Variable Air Volume Standard Motor w/ Shaft Ground Ring

B = Multi-Speed Standard Motor w/ Shaft Ground Ring

S = Single Zone Variable Air Volume Oversized Motor w/ Shaft Ground Ring

D = Multi-Speed Oversized Motor w/ Shaft Ground Ring

### Digit 16 — Hinged Service Access / Filters<sup>5</sup>

= Standard Panels/Standard Filters<sup>16</sup>

A = Hinged Access/Standard Filters<sup>16</sup>
B = Standard Panels/2" MERV 8 Filters
C = Hinged Access/2" MERV 8 Filters
D = Standard Panels/MERV 13 Filters
E = Hinged Access/MERV 13 Filters

### Digit 17 — Condenser Coil Protection

0 = Standard Coil

1 = Standard Coil With Hail Guard 2 = Black Epoxy Pre-Coated Coil 3 = Black Epoxy Pre-Coated Coil w

3 = Black Epoxy Pre-Coated Coil with Hail Guard

### Digit 18 — Through The Base Provisions

0 = No Through The Base Provisions A = Through The Base Electric<sup>11</sup>

D = Through The Base Utilities Access

### Digit 19 — Disconnect Switch/ Circuit Breaker<sup>10</sup>

0 = No Disconnect/circuit break 1 = Unit Mounted Non-Fused Disconnect Switch

2 = Unit Mounted Circuit Breaker

### Digit 20 — Convenience Outlet Option

O = Without Convenience Outlet A = Unpowered Convenience Outlet<sup>4</sup>

B = Powered Convenience Outlet<sup>4</sup>

### Digit 21 — Communications Options

O = Without Communications Options

6 = Building Automation Control Network Communications Interface

# 10 11 12 13 Digit 22 — Refrigeration System

0 = Standard refrigeration system

### Digit 23 — Refrigeration Controls

0 = Without Refrigeration Controls

1 = Frostat™

### Digit 24 - Smoke Detector<sup>2,9</sup>

0 = Without Smoke Detector
A = Return Air Smoke Detector
B = Supply Air Smoke Detector
C = Return/Supply Air Smoke
Detector

D = Plenum Smoke Detector

### Digit 25 — System Monitoring Controls<sup>2</sup>

0 = No Monitoring Controls 1 = Clogged Filter Switch

2 = Fan Failure Switch

3 = Discharge Air Sensing

4 = Clogged Filter Switch and Fan Failure

5 = Clogged Switch and Discharge Air Sensing

5 = Fan Failure Switch and Discharge Air Sensing 7 = Clogged Filter Switch, Fan Failure

Switch and Discharge Air Sensing

A = Condensate Drain Pan Overflow Switch

B = Clogged Filter Switch and Condensate Drain Pan Overflow Switch

C = Fan Failure Switch and Condensate Drain Pan Overflow Switch

D = Discharge Air Sensing and Condensate Drain Pan Overflow Switch

E = Clogged Filter Switch, Fan Failure Switch and Condensate Drain Pan Overflow Switch

F = Clogged Filter Switch, Discharge Air Sensing Tube and Condensate Drain Pan Overflow Switch

G = Fan Failure Switch, Discharge Air Sensing Tube and Condensate Drain Pan Overflow Switch

 H = Clogged Filter Switch, Fan Failure Switch, Discharge Air Sensing and Condensate Drain Pan Overflow Switch

### Digit 26 - System Monitoring Controls

0 = No Monitoring Controls

A = Demand Control Ventilation (CO<sub>2</sub>)<sup>14</sup>

B = FDD (Fault Detection and Diagnostics)

C = FDD (Fault Detection Diagnostics) & Demand Control Ventilation (CO<sub>2</sub>)<sup>14</sup>

### Digit 27 - Unit Hardware Enhancements

0 = No Enhancements

I = Stainless Steel Drain Pan

### **Digit 28 - Short Circuit Current Rating**

0 = Standard SCCR A = 65kA SCCR Option<sup>15</sup>

### Digit 31 - Advanced Unit Controls

0 = Standard Unit Controls

1 = Human Interface<sup>17</sup>

Note: Most Factory Installed Options available for Downflow Air Discharge units only. Please verify with ordering system for availability.

### **Model Number Notes**

- 1. Some field set up required.
- 2. Requires ReliaTel Options Module.
- 3. Requires Economizer.
- Must be ordered with Throughthe-Base Electrical option or Horizontal-Side Access and either Unit Mounted Disconnect or Circuit Breaker.
- 5. Available factory installed on downflow AND horizontal units. Verify with ordering system.
- 6. Cannot be fused.
- Must be factory installed when using Through-the-Base Options.
- ReliaTel Options Module is required when ordering the following accessories: Clogged Filter Switch, Fan Fail Switch, Condensate Overflow Switch, Discharge Air Sensing Kit, Frostat, Ventilation Override, and Smoke Detector.
- Option cannot be ordered in conjunction with field installed economizer on downflow units.
   Must be factory installed. The return air smoke detector may not fit up or work properly on the Voyager units when used in conjunction with 3<sup>rd</sup> party

- accessories (such as bolt on heat wheels, economizers, and power exhaust). Do not order the return air smoke detectors when using this type of accessory.
- Unit mounted disconnect and circuit breakers are mutually exclusive of each other.
- Through-the-base electrical option or Horizontal-Side Access must be ordered with either unit mounted disconnect or circuit breaker. When adding heat, you must order American Standard Electric Heat.
- All Factory Installed Options are Built-to-Order. Check order services for estimated production cycle.
- 13. For use with multi-speed and SZVAV units only.
- Demand Control Ventilation
   Option includes wiring only. The C0<sub>2</sub> sensor is a field-installed only option.
- 15. 575 VAC option is 25kA.
- 16. Standard filters are not available with Low Leak Economizers.
- 17. Human Interface is standard with FDD (Fault Detection Diagnostics).

18.



### **General Data**

Table 3. General data  $-12\frac{1}{2}$  - 20 tons

	12½ Tons Downflow & Horizontal Units	15 Tons Downflow & Horizontal Units	20 Tons Downflow & Horizontal Units
	WS*150E3,4,W	WS*180E3,4,W	WS*240E3,4,W
Cooling Performance <sup>(a)</sup>			
Gross Cooling Capacity	148,000	177,000	249,000
EER <sup>(b)</sup>	10.6	10.6	9.7
Nominal Airflow/ARI Rated Airflow (CFM)	5000	6000 / 5300	8000 / 6400
ARI Net Cooling Capacity	146,000	170,000	240,000
IEER <sup>(c)</sup> (One Speed Fan / Two or Variable Speed Fan)	12/13.5	12/13.5	11.5/12.0
System Power (kW)	13.77	16.04	25.47
Heating Performance <sup>(a)</sup>			
High Temp. Btuh Rating	136,000	170,000	210,000
COP	3.2	3.2	3.2
System Power (kW)	12.46	15.57	19.23
Low Temp. Btuh Rating	75,000	90,000	120,000
COP	2.1	2.1	2.1
System Power (kW)	10.47	12.56	16.75
Compressor			
Number/Type	2 / Scrolls	2 / Scrolls	2 / Scrolls
ARI Sound Rating (BELS)(d)	9.2	9.2	9.4
Outdoor Coil — Type	Hi-Performance	Hi-Performance	Hi-Performance
Refrigerant Control	Expansion Valve	Expansion Valve	Expansion Valve
Tube Size (in.) OD	0.3125	0.3125	0.3125
Face Area (sq. ft.)	35.20	35.20	42.53
Rows/FPI	3 / 16	3 / 16	3 / 16
Indoor Coil — Type	Hi-Performance	Hi-Performance	Hi-Performance
Tube Size (in.) ID	0.3125	0.3125	0.3125
Face Area (sq. ft.)	26.00	26.00	31.42
Rows/FPI	3 / 15	4 / 15	4 / 15
Refrigerant Control	Short Orifice	Short Orifice	Short Orifice
Drain Connection Number/Size (in.)	1/1.00 NPT	1/1.00 NPT	1/1.00 NPT
Outdoor Fan — Type	Propeller	Propeller	Propeller
Number Used/Diameter (in.)	2 / 26	2 / 26	2 / 28
Drive Type/No. Speeds	Direct / 1	Direct / 1	Direct / 1
CFM	11,100	10,800	14,800
Number Motors/HP	2 / 0.5	2 / 0.5	2 / 1.0
Motor RPM	1,100	1,100	1,125

American Standard

Table 3. General data  $-12\frac{1}{2}$  - 20 tons (continued)

	12½ Tons Downflow & Horizontal Units	15 Tons Downflow & Horizontal Units	20 Tons Downflow & Horizontal Units
	WS*150E3,4,W	WS*180E3,4,W	WS*240E3,4,W
Indoor Fan - Type	FC Centrifugal	FC Centrifugal	FC Centrifugal
Number Used/Diameter (in.)	1 / 18x18	1 / 18x18	1 / 18x18
Drive Type/No. Speeds	Belt / 1	Belt / 1	Belt / 1
Number Motors	1	1	1
Motor HP (Standard/Oversized)	3.0 / 5.0	3.0 / 5.0 or 7.5 <sup>(e)</sup>	5.0 / 7.5
Motor RPM (Standard/Oversized)	1740 / 3,450	1740 / 3,450	3450 / 3,470
Motor Frame Size (Standard/Oversized)	56HZ / 56HZ	184TZ / 56HZ or 184TZ	56HZ / 184T
Filters - Type Furnished	Throwaway	Throwaway	Throwaway
Number Size Recommended			
Downflow	(4)20x20x2 (4)20x25x2	(4)20x20x2 (4)20x25x2	(8)20x20x2 (4)20x16x2
Horizontal	(8)20x25x2	(8)20x25x2	(12)20x20x2
Refrigerant Charge Pounds of R-410A <sup>(f)</sup>			
Downflow	14 / 14.5	16.5 / 15.9	20.0 / 20.7
Horizontal	13.2 / 13.3	17 / 15.9	

<sup>(</sup>a) Cooling Performance is rated at 35°C (95°F) ambient, 26.7°C (80°F) entering dry bulb, 19.4°C (67°F) entering wet bulb. Heating Performance is rated at 20°C (68°F) ambient, 8.3°C (47°F) entering dry bulb, 6.1°C (43°F) entering wet bulb. Gross capacity does not include the effect of fan motor heat. ARI capacity is net and includes the effect of fan motor heat. Units are suitable for operation to ±20% of nominal airflow. Rated in accordance with ARI Standard 210/240 or 340/360.

<sup>(</sup>b) EER is rated at ARI conditions and in accordance with DOE test procedures.

(c) Integrated Energy Efficiency Ratio (IEER) is rated in accordance with AHRI standard 210/240 or 360.

(d) Sound Rating shown is tested in accordance with ARI Standard 270 or 370.

(e) Offered only as a field installed accessory.

(f) Refrigerant charge is an approximate value. For a more precise value, see unit nameplate and service instructions.



### **Performance Data**

Table 4. Gross cooling capacities (MBh) 12½ tons three phase WS\*150E

75 140.4 110.8 152.3 74.7 156.2 39.1 131.7 108.1 146.6 75.2 153.1 35.5 118.1 103.1 138 4000 80 146.6 139.5 156.7 99.7 160.5 60.9 135.0 131.4 148.6 98.4 155.7 59.5 123.4 123.4 140	105 67 SH SHC	73
Air Flow CFM         °F         MBH         SHC         MBH         SHC <t< th=""><th>67</th><th>73</th></t<>	67	73
Flow   DB   61   67   73   61   67   73   61   67   73   61   67   67   73   61   67   73   61   67   74   75   75   75   75   75   75   7		73
CFM °F MBH SHC		
4000 80 146.6 139.5 156.7 99.7 160.5 60.9 135.0 131.4 148.6 98.4 155.7 59.5 123.4 123.4 140		MBH SHC
4000	.7 73.6	148.3 33.9
4000	.6 97.0	150.9 58.0
85   148.1 148.1 156.5 121.3 161.4 85.3   141.9 141.9 150.7 121.6 158.5 83.4   135.0 135.0 142	.6 120.3	153.1 81.9
90   155.8 155.8 159.4 144.5 163.7 106.3   150.5 150.5 153.8 145.1 160.6 107.3   144.0 144.0 146	.2 143.6	156.0 105.8
75 144.5 117.5 156.4 77.9 157.1 37.5 136.4 115.5 149.0 77.1 154.1 36.7 125.1 111.9 141	.7 76.3	149.6 33.1
4500 80 147.8 143.2 158.8 103.5 159.8 61.1 139.9 139.6 151.2 102.9 157.1 63.3 131.5 131.5 143	.7 102.3	152.3 60.1
85   153.8 153.8 158.8 127.9 162.4 85.0   148.2 148.2 153.8 128.8 159.9 89.0   141.3 141.3 146		
90 160.1 160.1 161.6 152.9 165.3 108.6 156.0 156.0 157.4 153.7 162.5 113.9 150.0 150.0 150		
75   147.7   123.7   154.9   78.7   157.8   33.9   139.8   122.3   150.7   78.4   154.7   36.9   129.6   119.6   143		
5000 80 151.6 150.4 160.1 107.3 160.2 60.0 144.2 144.2 153.1 107.3 158.0 64.7 136.9 136.9 146		
85   157.3 157.3 160.3 135.3 162.7 86.8   152.6 152.6 156.4 136.0 160.8 91.1   146.2 146.2 149		
90 162.3 162.3 163.0 158.0 165.4 112.7 159.4 159.9 159.1 163.6 116.5 154.2 154.2 154.2		-
75   149.9   129.7   155.6   82.5   158.0   31.8   142.5   128.7   151.9   80.6   155.5   34.1   133.3   126.6   145.8   154.1   154.0   158.4   112.6   160.5   62.6   148.3   148.3   154.5   111.6   158.7   63.3   141.2   141.2   148.3   148.3   154.5   111.6   158.7   63.3   141.2   141.2   148.3   148.3   154.5   111.6   158.7   63.3   141.2   141.2   148.3   148.3   148.3   154.5   111.6   158.7   163.3   1		
5500 80 154.1 154.0 158.4 112.6 160.5 62.6 148.3 148.3 154.5 111.6 158.7 63.3 141.2 141.2 148.5 159.4 159.4 159.4 161.0 140.5 163.3 91.2 155.8 155.8 157.9 142.7 160.9 90.9 150.0 150.0 151		
90 163.8 163.8 164.2 160.8 165.7 118.4 161.1 161.1 161.4 161.2 164.1 119.0 157.1 157.1 157		
75   153.7   136.6   156.6   85.7   159.3   32.9   145.0   134.8   152.1   83.2   155.8   31.7   136.2   132.9   147.0		-
80   156.4   159.2   116.6   161.8   65.1   151.2   151.2   155.4   116.6   159.2   63.2   144.6   144.6   149		
6000 85 160.3 161.9 143.5 163.7 95.1 157.8 157.8 159.0 148.8 164.6 97.9 152.7 152.7 156		
90   164.7   164.9   162.7   166.3   122.2   162.7   164.7   164.7   164.5   123.4   158.7   158.7   158		
Ambient Temperature (°F)		
115		
Air Ent Entering Wet Bulb (F)		
Flow DB 61 67 73		
CFM °F MBH SHC MBH SHC		
75 104.6 98.2 129.1 71.4 141.4 33.8		
4000 80 114.1 114.1 130.8 94.5 143.9 58.3		
85   127.1 127.1 132.8 118.1 145.8 82.1		
90   136.7   136.7   136.9   136.9   148.1   105.6		
75 111.4 107.2 132.2 74.6 143.0 32.2		
80   122.5 122.5 134.1 100.7 145.4 59.5   4500   0.5   100.7 140.7 0.40.		
85   133.6 133.6 137.3 127.3 147.8 85.6		
90 142.8 142.8 142.9 150.6 112.4		
75   116.2   114.7   134.8   77.8   144.4   31.3   80   128.8   128.8   136.9   106.9   146.7   60.7		
5000 85 138.6 138.6 140.6 135.6 149.5 90.1		
90 147.3 147.5 147.5 152.6 119.3		
75   121.4   121.1   136.7   80.5   144.9   32.0		
80 133.0 139.2 112.5 148.0 63.8 <b>Notes</b> :		
5500 85 142 5 143 5 143 5 143 0 150 0 05 4 1. Dry Coil Condition. Total Gross Cooling Capacity (MBh) shown		
applicable. In this case the Sensible Heat Capacity (SHC) is the		
90 150.4 150.4 150.5 150.5 153.8 126.7 <b>2.</b> All capacities shown are gross and have not considered indoor		
75 125 5 128 4 83 4 145 6 32 6 cooling subtract indoor fan heat.		
75 125.5 125.5 138.4 83.4 145.6 32.6 cooling subtract indoor fan heat.  3. MBH = Total Gross Capacity  136.5 136.5 141.1 117.9 148.8 66.6 4 SHC = Sepsible Heat Capacity		
75 125.5 125.5 138.4 83.4 145.6 32.6 cooling subtract indoor fan heat.  3. MBH = Total Gross Capacity		



Table 5. Gross cooling capacities (MBh) 15 tons three phase WS\*180E

85

								P	Mbier	nt Tem	perat	ure (°	F)						
				8	5					9	5					10	05		
Air	Ent								Ente	ring W	et Bul	b (F)							
Flow	DB	61		6	7	7	3	6	1	6	7	7	3	6	1	6	7	7	3
CFM	°F	MBH	SHC	MBH	SHC	MBH	SHC	MBH	SHC	MBH	SHC	MBH	SHC	MBH	SHC	MBH	SHC	MBH	SHC
	75	172.4	137.8	185.0	97.2	190.7	51.2	157.4	132.2	181.5	98.1	189.5	52.1	141.1	123.6	169.8	95.1	185.3	54.1
4000	80	175.2	164.2	185.9	124.4	191.5	73.3	165.6	159.0	182.5	125.2	190.5	80.5	151.3	150.2	179.0	126.0	186.2	82.1
4800	85	182.7	182.4	204.9	161.7	192.5	98.7	176.3	176.3	183.4	152.4	190.9	107.9	167.0	167.0	161.9	143.1	187.8	110.5
	90	186.4	187.2	188.2	173.6	192.9	123.3	185.2	185.2	186.8	175.9	191.9	134.5	178.6	178.6	180.1	173.1	188.8	137.3
	75	176.7	146.7	186.4	97.4	192.2	43.3	163.9	141.3	183.8	102.8	190.8	53.1	148.9	134.8	174.0	99.6	187.4	51.8
5400	80	185.0	177.6	187.1	128.6	192.7	68.8	173.2	169.4	185.4	133.4	191.9	82.7	161.4	161.2	175.2	130.2	188.4	82.7
3400	85	185.9	186.3	188.2	157.9	193.7	99.4	183.4	183.4	186.4	163.3	192.8	110.9	171.2	171.2	178.2	160.1	188.9	112.5
	90	189.2	190.2	189.9	181.4	193.9	129.3	188.2	188.7	188.9	182.3	193.7	138.7	183.8	183.8	185.0	181.5	190.0	143.1
	75	180.7	154.7	186.9	103.2	193.2	37.0	169.6	151.6	186.2	105.9	192.0	51.1	154.9	143.9	177.5	103.9	189.4	51.7
6000	80	184.3	179.0	193.7	140.1	193.9	70.8	179.0	177.4	186.2	138.9	193.4	81.3	163.3	163.3	178.8	137.7	190.0	85.0
0000	85	187.7	188.5	189.9	165.8	194.6	104.4	186.5	186.5	188.1	168.9	194.3	111.2	171.3	172.9	182.7	169.1	190.4	119.4
	90	191.3								190.7						187.4			
	75	189.8	168.9	188.4	106.3	193.8	36.5	175.1	160.4	186.7	106.8	193.3	46.9			180.2			
6600	80	185.9	182.8	189.6	140.4	194.2	73.1			195.4						181.8			
	85	188.8	189.7	190.9	168.8	195.1	108.9			189.2						185.1			
	90	192.3								192.4						189.5			158.2
	75	184.1					36.2			187.4						185.2			51.1
7200	80	187.8								188.5						183.6			
	85	190.2								190.4						187.3			
	90	193.5						193.2	194.0	194.0	193.4	196.2	152.3	191.5	192.2	191.4	192.1	194.0	161.4
		Aı	mbier		•	ure (°I	=)	_											
					15			-											
Air	Ent			_	et Bul		_												
Flow	DB	61			7	7		-											
CFM	°F	MBH			SHC	MBH		_											
	75	125.9																	
4000	80	137.6																	
	85	154.5																	
	90	168.6																	
	75	132.7																	
4500	80	147.7																	
	85	164.1																	
	90	176.1						=											
	75	139.5 155.6																	
5000	80																		
	85	170.4																	
	90 75	180.9 145.6						-											
								Notes											
5500	80	162.2 175.2						<ol> <li>Dry</li> </ol>					oling Ca						
	85 90	184.1											le Heat						n not
	75	150.4					51.5			es snow tract ind			i nave n	ot consi	uerea Ir	iuoor ia	п пеат.	เบ บมเสเ	ппес
	80	167.2						<ol><li>MB</li></ol>	H = Tota	al Gross	Capacit	y							
6000	8U 85	170.5								sible He		-	izontol	unit					

PKGP-PRC015R-EN 23

179.5 179.5 179.9 177.1 186.0 132.8 \* stands for both downflow and horizontal unit.

185.5 185.7 186.3 186.4 187.8 168.8



### **Performance Data**

Table 6. Gross cooling capacities (MBh) 20 tons three phase WS\*240E

lable	J. J	ross co	omig	vapac	Jitios (	1410117	20 101		•				ΕV						
				0	5			,	Ambier		iperati 5	ure (	r)			1/	05		
				۰	· ວ				Ento	ring W		h (E)				- 10	Jo		
Air	Ent	61	ı	6	7	7	3		1	_	7		3	6	1	6	7	7	3
Flow CFM	DB °F	MBH		MBH			SHC		SHC		SHC	MBH			SHC		SHC		SHC
6400	75	231.1							173.6							232.4			
0.00	80	235.6														233.8			
	85	247.9														236.3			
	90	266.0 2																	
7200	75	242.5	197.1	274.8	142.3	292.9	73.3	219.0	187.9	259.9	138.5	283.2	74.2	194.4	178.4	239.9	132.8	269.1	72.5
	80	247.6	238.6	277.5	183.8	297.1	115.8	227.3	226.2	261.8	179.8	286.4	115.6	209.7	209.7	241.8	174.2	271.7	114.5
	85	262.8	262.8	280.9	225.7	301.5	158.1	248.8	248.8	265.0	221.7	290.1	158.4	233.0	233.0	245.7	216.1	274.7	156.5
	90	279.8	279.8	286.0	268.1	305.8	200.4	267.3	267.3	270.9	263.1	294.0	200.7	253.1	253.1	254.3	253.2	278.1	199.5
8000	75	251.1	209.8	279.7	146.5	295.4	70.6	229.7	202.0	265.1	143.6	285.9	70.7	204.3	192.2	247.0	139.0	272.5	70.2
	80	258.3	254.4	283.0	192.7	299.9	117.4	240.8	240.6	267.8	189.7	289.8	117.8	222.4	222.4	249.6	185.1	275.6	117.0
	85	274.0 2	274.0	287.2	239.1	304.5	164.0	260.7	260.7	271.9	236.4	294.0	164.5	245.2	245.2	253.4	231.5	279.0	163.6
	90	290.9	290.9	293.8	284.4	309.4	210.2	278.4	278.4	279.8	277.3	298.5	210.9	263.8	263.8	264.2	264.2	283.2	210.9
8800	75	258.4	222.0	283.4	150.7	297.2	69.0	237.8	214.9	269.4	148.5	288.1	69.4			251.4			
	80	266.2														254.5			
	85	283.3																	
	90	298.9 2																	
9600	75	263.4														255.4			
	80	273.7 2																	
	85 90	290.4 2 304.8 3																	
	70					ure (°I		274.2	274.2	274.4	274.4	304.7	232.0	200.3	200.5	200.0	200.0	270.7	234.1
		- 71			15	<u></u>		-											
Λ:	F4		Ente	ring W		b (F)		-											
Air Flow	Ent DB	61		6	7	7	3												
CFM	°F	MBH	SHC	MBH	SHC	MBH	SHC	-											
6400	75	158.5	152.9	206.9	118.1	246.1	71.0	-											
	80	177.1	177.1	208.6	154.5	247.1	108.6												
	85	201.1	201.1	212.3	192.1	249.1	144.9												
	90	222.0	222.0	223.1	223.0	251.3	182.3												
7200	75	168.6	165.4	216.4	125.7	251.0	70.1	•											
	80	191.7	191.7	218.4	166.8	252.7	111.5												
	85	214.8 2	214.8	223.1	209.0	255.1	153.3												
	90	236.2	236.2	236.5	236.5	257.9	195.5	_											
8000	75	179.2																	
	80	204.0 2																	
	85	227.3																	
0000	90	247.3						-											
8800	75	188.7						Notes											
	80 85	214.2						<ol> <li>Dry</li> </ol>	Coil Co										
	85 90	237.3 2 256.1 2						app	olicable.	In this	case the	Sensib	le Heat	Capacity	y (SHC)	is the to	otal cap	acity.	n net
9600	75	197.1						COC	oling sub	tract ind	door far	heat.	паve n	ot consi	uerea Ir	iuoor iai	пеат.	เบ บมเสโ	nnet
7000	80	223.4						3. MB	H = Tota	al Gross	Capacit	y city							
	85	245.1	245 1	246.0	245.3	266.7	178.3	* stand	ds for b	oth dov	vnflow	and hor	izontal	unit.					
	90	263.4																	
	70	200.7 2	_00.4	200.0	200.0	۷, ۱./	204.0												



Table 7. Evaporator fan performance 12½ tons WS\*150E downflow or horizontal

						Ex	ternal	Stati	c Pres	sure	(Inche	es of \	<b>Nater</b>	)						
	0.	10	0.	20	0.	30	0.	40	0.	50	0.0	60	0.	70	0.8	80	0.9	90	1.0	00
CFM	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP
		3HP S	Standa	ard Mo	otor &	Low	Static	Drive	Acce	ssory				3HP S	tanda	rd Mo	otor &	Drive	)	
4000	_	_	382	0.56	420	0.66	459	0.79	496	0.91	531	1.05	564	1.19	595	1.34	625	1.50	654	1.67
4500	_	_	410	0.73	446	0.85	479	0.97	514	1.11	548	1.26	578	1.40	610	1.56	639	1.72	666	1.89
5000	400	0.80	440	0.95	473	1.07	504	1.20	534	1.34	566	1.50	597	1.66	625	1.81	653	1.98	681	2.16
5500	431	1.03	470	1.19	502	1.34	531	1.48	559	1.62	586	1.77	615	1.95	643	2.12	670	2.30	695	2.47
6000	463	1.30	500	1.48	531	1.65	559	1.80	585	1.95	611	2.11	636	2.28	662	2.46	689	2.66	714	2.85
			J								3H	P Star	ndard	Moto	r & Hi	gh Sta	atic D	rive A	ccess	ory
Continu	ued										I									
-																				
							Exte	rnal S	tatic I	Pressi	ıre (I	nches	of Wa	ater)						
	1.	10	1.	20	1.	30		rnal S 40		Pressi 50	ure (I			ater) 70	1.8	80	1.	90	2.	00
CFM		10 BHP					1.	40	1.	50	1.	60	1.	70 <sup>°</sup>	1.8 RPM					
СҒМ	RPM	ВНР	RPM		RPM	ВНР	1. RPM	40 BHP	1.I RPM	50 BHP	1.0 RPM	60 BHP	1.° RPM	70 BHP		ВНР	RPM	ВНР	RPM	ВНР
<b>CFM</b> 4000	RPM	ВНР	RPM	ВНР	RPM	ВНР	1. RPM	40 BHP	1.I RPM ssory	50 BHP	1.0 RPM	60 BHP	1.° RPM	70 BHP	RPM	ВНР	RPM	ВНР	RPM	ВНР
	RPM 3HP S	BHP Standa	RPM ard Mo	BHP otor &	RPM Low	BHP Static	1. RPM Drive	40 BHP Acce	1.I RPM ssory	50 BHP	1.0 RPM 3HP S	60 BHP Standa	1. RPM ard Mo 826	70 BHP otor &	RPM High	BHP Statio	RPM Drive	BHP Acce	RPM essory	ВНР
4000	<b>3HP</b> \$	BHP Standa 1.83	<b>RPM</b> ard <b>M</b> 0 708	BHP otor &	RPM Low 734	BHP Static	1. RPM Drive	40 BHP Acce 2.32	RPM ssory	50 BHP 2.49	1.6 RPM 3HP S 804	60 BHP Standa 2.66	1. RPM ard Mo 826	70 BHP otor & 2.83	RPM High 847	BHP Statio	RPM Drive	BHP Acce 3.19	RPM essory	3.38
4000 4500	82 693	BHP Standa 1.83 2.07	<b>RPM</b> ard <b>M</b> 708 719	BHP otor & 1.99 2.25	<b>RPM Low</b> 734 745	2.16 2.44	758 769	40 BHP Acce 2.32 2.62	1.8 RPM ssory 782 793	50 BHP 2.49 2.80	1.6 RPM 3HP S 804 815	60 BHP Standa 2.66 2.99	1.7 RPM ard Mo 826 838	70 BHP otor & 2.83 3.17	<b>RPM High</b> 847	3.01 3.36	867 880	3.19 3.55	RPM essory 886 900	3.38 3.74
4000 4500 5000	8PM 3HP 9 682 693 707	BHP 5tanda 1.83 2.07 2.34	708 719 732	BHP otor & 1.99 2.25 2.53	RPM 10w 734 745 757	BHP Static 2.16 2.44 2.72	1. RPM Drive 758 769 780	40 BHP 2.32 2.62 2.92	1.1 RPM ssory 782 793 804	2.49 2.80 3.13	1.6 RPM 3HP S 804 815 826	60 BHP 5tanda 2.66 2.99 3.33	1. RPM ard Mo 826 838 848	70 BHP otor & 2.83 3.17 3.54	RPM High 847 859 870	3.01 3.36 3.74	RPM Drive 867 880 891	3.19 3.55 3.95	886 900 911	3.38 3.74 4.15

#### Notes:

- Fan motor heat (MBH) = 3.15 x Fan BHP.
   Data includes pressure drop due to wet coils and filters.
   No accessories or options are included in pressure drop data.
   Refer to Table 14, p. 28 to determine add¹l static pressure drop due to other options/accessories.
   Factory supplied motors, in commercial equipment, are definite purpose motors, specifically designed and tested to operate reliably and continuously at all cataloged conditions. Using the full horsepower range of our fan motors as shown in our tabulated data will not result in nuisance tripping or premature motor failure. Our product's warranty will not be affected.



### **Performance Data**

Table 8. Evaporator fan performance 15 tons WS\*180E downflow or horizontal

						E	kterna	I Stat	ic Pre	ssure	(Inch	es of \	<b>Vater</b>	)						
	0.	10	0.	20	0.	30	0.	40	0.	50	0.	60	0.	70	0.8	80	0.	90	1.	.00
CFM	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP
	3H	IP Sta	ndard	Moto	r & Lo	w Sta	atic Dr	ive A	ccesso	ory				3	HP Sta	andar	d Mot	or Dri	ve	
4800	397	0.75	435	0.88	469	1.00	501	1.13	533	1.28	566	1.43	596	1.59	625	1.74	655	1.92	682	2.09
5400	435	1.02	473	1.18	504	1.32	533	1.46	562	1.60	590	1.76	620	1.94	648	2.11	674	2.28	700	2.46
6000	475	1.36	510	1.53	541	1.70	568	1.85	594	2.01	620	2.17	645	2.34	672	2.53	698	2.73	723	2.92 <sup>(a)</sup>
6600	514	1.76	549	1.96	578	2.15	604	2.33	629	2.49	653	2.66	676	2.84	699	3.02	722	3.23	747	3.44
7200	555	2.25	588	2.46	616	2.68	641	2.89	665	3.06	687	3.24 <sup>(b)</sup>	709	3.43	730	3.62	751	3.82	772	4.02
														5H	P Ove	rsized	Moto	r & D	rive	
Contin	ued																			
							Exte	ernal	Static	Press	ure (l	Inches	of Wa	ater)						
	1.	10	1.	20	1.	30	1.	40	1.	50	1.	60	1.	70	1.8	80	1.	90	2.	.00
CFM	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP	RPM	BHP
	3H	P Sta	ndard	Moto	r & Hi	gh Sta	atic Di	rive A	ccess	ory			5HI	P Ove	rsized	Moto	r & Dı	ive		
4800	708	2.27	734	2.46	758	2.66	782	2.86	806	3.06	829	3.25	850	3.45	872	3.65	893	3.85	913	4.04
5400	727	2.65	752	2.85	776	3.05	799	3.25	821	3.47	843	3.69	865	3.91	886	4.13	907	4.36	927	4.58
6000	747	3.11	770	3.30	794	3.51	817	3.73	839	3.95	861	4.17	881	4.40	902	4.63	922	4.87	942	5.12
6600	770	3.66	793	3.87	815	4.08	835	4.28	857	4.51	879	4.74	900	4.98	_	_	_	_	_	_
7200	794	4.25	817	4.49	839	4.73	860	4.96	_	_	_	_	_	_	_	_	_	_	_	_

#### Notes:

- Fan motor heat (MBH) = 3.15 x Fan BHP.
   Data includes pressure drop due to wet coils and filters.
   No accessories or options are included in pressure drop data.
   Refer to Table 14, p. 28 to determine add'l static pressure drop due to other options/accessories.
- 5. Factory supplied motors, in commercial equipment, are definite purpose motors, specifically designed and tested to operate reliably and continuously at all cataloged conditions. Using the full horsepower range of our fan motors as shown in our tabulated data will not result in nuisance tripping or premature motor failure. Our product's warranty will not be affected.
- (a) 3HP Standard Motor & High Static Drive Accessory (b) 5-hp Oversized Motor & Field Supplied Fan Sheave BK160 x 1 3/16 with BX75 (DF) or BX90 (HZ) Belt Required.

Table 9. Evaporator fan performance 20 tons WS\*240E downflow or horizontal

						Ex	terna	l Stati	c Pres	sure	(Inch	es of	Water	)						
	0.	10	0.	20	0.		0.4		0.		•	60	0.	•	0.	80	0.9	90	1.	00
CFM	RPM	ВНР	RPM	ВНР	RPM	ВНР	RPM	ВНР	RPM	ВНР	RPM	ВНР	RPM	внр	RPM	ВНР	RPM	ВНР	RPM	ВНР
		5HP	Stand	ard M	otor D	rive 8	low	Static	Drive	Acce	ssory			5	HP St	andar	d Mot	or Dri	ve	
6400	_	_	_	_	507	1.72	535	1.88	560	2.07	584	2.27	607	2.46	631	2.66	654	2.86	677	3.07
7200	_	_	519	2.10	549	2.30	576	2.48	600	2.67	623	2.88	644	3.10	665	3.32	686	3.54	707	3.76
8000	531	2.50	563	2.77	592	3.00	617	3.21	641	3.41	663	3.62	684	3.86	704	4.10	723	4.34	742	4.58
8800	578	3.26	607	3.56	634	3.83	659	4.08	683	4.31	704	4.54	724	4.77	744	5.01	762	5.27	779	5.54
9600	626	4.19	653	4.51	679	4.81	703	5.10	725	5.36	746	5.62	765	5.85	784	6.11	802	6.36	819	6.64
											7.5H	HP Ov	ersize	d Mot	or & [	Orive				
Contin	ued						L													
							Exte	rnal S	Static	Press	ure (I	nches	of W	ater)						
	1.	10	1.	20	1.	30		rnal S 40		Press 50	•	nches 60	of W.	•	1.	80	1.9	90	2.	00
CFM							1.	40	1.	50	1.	60	1.	70 <sup>′</sup>					2. RPM	
CFM						ВНР	1.	40 BHP	1.I RPM	50 BHP	1.	60	1.	70 <sup>′</sup>						
<b>CFM</b> 6400						ВНР	1.4 RPM	40 BHP	1.I RPM	50 BHP	1.	60	1.	70 <sup>′</sup>			RPM			
	RPM	ВНР	RPM	ВНР	RPM	BHP 51	1.4 RPM HP Sta	40 BHP indar	1.I RPM d Moto	50 BHP or Driv	1. RPM ve 798	60 BHP	1. <sup>°</sup> RPM	70 BHP	RPM	ВНР	RPM	ВНР	RPM	ВНР
6400	<b>RPM</b> 699	<b>BHP</b> 3.30	<b>RPM</b> 721	<b>BHP</b> 3.52	<b>RPM</b> 742	<b>51</b> 3.75	1.4 RPM HP Sta 762	40 BHP andard	1.1 RPM d Moto 780	50 BHP or Driv 4.20	1. RPM ve 798	60 BHP 4.42	1.7 <b>RPM</b> 815	70 BHP 4.66	<b>RPM</b> 832	<b>BHP</b> 4.89	<b>RPM</b> 849	<b>BHP</b> 5.12	<b>RPM</b> 866 893	<b>BHP</b> 5.36
6400 7200	<b>RPM</b> 699 727	3.30 3.98	721 748	3.52 4.22	742 768	<b>51</b> 3.75 4.46	1.4 RPM HP Sta 762 789	40 BHP andard 3.98 4.71	1.8 RPM d Moto 780 808	50 BHP or Driv 4.20 4.97	1.4 RPM ve 798 827	60 BHP 4.42 5.22	1.7 RPM 815 845	70 BHP 4.66 5.48	832 861	<b>BHP</b> 4.89 5.73	<b>RPM</b> 849 878	5.12 5.98	<b>RPM</b> 866 893	5.36 6.24
6400 7200 8000	699 727 760	3.30 3.98 4.82	721 748 779	3.52 4.22 5.07	742 768 798	51 3.75 4.46 5.32	1.4 RPM HP Sta 762 789 816	40 BHP andard 3.98 4.71 5.57	1.8 RPM d Moto 780 808 834	50 BHP or Driv 4.20 4.97 5.83	1.4 RPM ve 798 827 853	4.42 5.22 6.11	1.7 RPM 815 845 871	4.66 5.48 6.38	832 861	<b>BHP</b> 4.89 5.73	<b>RPM</b> 849 878	5.12 5.98	<b>RPM</b> 866 893	5.36 6.24

#### Notes:

- 1. Fan motor heat (MBH) =  $3.15 \times \text{Fan BHP}$ .
- 2. Data includes pressure drop due to wet coils and filters.

- Data includes pressure drop due to wet coils and filters.
   No accessories or options are included in pressure drop data.
   Refer to Table 14, p. 28 to determine add'l static pressure drop due to other options/accessories.
   Factory supplied motors, in commercial equipment, are definite purpose motors, specifically designed and tested to operate reliably and continuously at all cataloged conditions. Using the full horsepower range of our fan motors as shown in our tabulated data will not result in nuisance tripping or premature motor failure. Our product's warranty will not be affected.
   For multi-speed or single zone VAV applications, minimum "full" speed airflow must be set to 6800 cfm or higher to prevent VFD overheating during
- heating operation.
- (a) 7.5-hp Oversized Motor & Field Supplied Motor Sheave 1VP50 x 1 1/8 Required.

Table 10. Standard motor & drive/fan speed (Rpm)

Tons	Unit Model No.	6 Turns Open	5 Turns Open	4 Turns Open	3 Turns Open	2 Turns Open	1Turn Open	Closed
121/2	WS*150E3,4,W	500	537	574	611	648	685	N/A
15	WS*180E3,4,W	500	537	574	611	648	685	N/A
20	WS*240E3,4,W	605	650	695	739	784	829	N/A

Note: Factory set at 3 turns open.

Table 11. Standard motor & low static fan drive

Tons	Unit Model No.	6 Turns Open	5 Turns Open	4 Turns Open	3 Turns Open	2 Turns Open	1Turn Open	Closed
121/2	WS*150E3,4,W	379	407	435	463	491	519	N/A
15	WS*180E3,4,W	379	407	435	463	491	519	N/A
20	WS*240E3,4,W	506	544	581	619	656	694	N/A

### **Performance Data**

Table 12. Standard motor & high static drive accessory/fan speed (rpm)

Tons	Unit Model No.	6 Turns Open	5 Turns Open	4 Turns Open	3 Turns Open	2 Turns Open	1Turn Open	Closed
121/2	WS*150E3,4,W	685	722	759	796	833	870	N/A
15	WS*180E3,4,W	685	722	759	796	833	870	N/A

Table 13. Oversized motor & drive/fan speed (rpm)

Tons	Unit Model No.	6 Turns Open	5 Turns Open	4 Turns Open	3 Turns Open	2 Turns Open	1Turn Open	Closed
121/2	WS*150E3,4,W	695	747	798	850	901	953	N/A
15	WS*180E3,4,W	695	747	798	850	901	953	N/A
20	WS*240E3,4,W	694	739	784	829	874	919	N/A

Table 14. Static pressure drops through accessories (inches water column)

				2"	2"	Econo with C	Standard Economizer with OA/RA Dampers <sup>(c)</sup>		Leak omizer OA/RA ers <sup>(d)</sup>	Electric Heater Accessory (KW) <sup>(e)</sup>				
Tons	Unit Model No.	CFM	Standard Filters <sup>(a)</sup>	MERV 8 Filters <sup>(b)</sup>	MERV 13 Filters <sup>(b)</sup>	100% OA	100% RA	100% OA	100% RA	5-12	14- 23	36	54	72
		4000	0.02	0.04	0.08	0.20	0.02	0.25	0.04	_	0.03	0.03	0.04	_
	WSH150E	5000	0.03	0.05	0.11	0.26	0.03	0.39	0.07	_	0.04	0.05	0.06	_
12½		6000	0.05	0.07	0.14	0.35	0.04	0.57	0.10	_	0.06	0.07	0.09	_
1 2 72		4000	0.02	0.04	0.08	0.20	0.02	0.16	0.10	_	0.03	0.03	0.04	_
	WSD150E	5000	0.03	0.05	0.11	0.26	0.03	0.24	0.16	_	0.04	0.05	0.06	_
		6000	0.05	0.07	0.14	0.35	0.04	0.33	0.24	_	0.06	0.07	0.09	_
		4800	0.03	0.05	0.10	0.24	0.03	0.36	0.06	_	0.04	0.04	0.05	_
	WSH180E	6000	0.05	0.07	0.14	0.35	0.04	0.57	0.10	_	0.06	0.07	0.08	_
15		7200	0.07	0.09	0.17	0.42	0.05	0.81	0.14	_	0.09	0.10	0.12	_
15		4800	0.03	0.05	0.10	0.24	0.03	0.22	0.15	_	0.04	0.04	0.05	_
	WSD180E	6000	0.05	0.07	0.14	0.35	0.04	0.33	0.24	_	0.06	0.07	0.08	_
		7200	0.07	0.09	0.17	0.42	0.05	0.45	0.35	_	0.09	0.10	0.12	_
		6400	0.04	0.01	0.11	0.22	0.04	0.64	0.11	_	_	0.06	0.08	0.09
	WSH240E	8000	0.06	0.09	0.14	0.31	0.05	1.00	0.17	_	_	0.10	0.12	0.14
20		9600	0.09	0.12	0.18	0.44	0.07	1.44	0.24	_	_	0.14	0.17	0.20
20		6400	0.05	0.08	0.12	0.22	0.04	0.37	0.27	_	_	0.06	0.08	0.09
	WSD240E	8000	0.08	0.10	0.15	0.31	0.05	0.54	0.43	_	_	0.10	0.12	0.14
		9600	0.11	0.14	0.19	0.44	0.07	0.75	0.62	_	_	0.14	0.17	0.20

<sup>(</sup>a) Tested with: 2" filters 12 - 20 tons.
(b) Difference in pressure drop should be considered when utilizing optional 2" pleated filters.
(c) OA = Outside Air and RA = Return Air.
(d) OA = Outside Air and RA = Return Air.
(e) Nominal KW ratings at 240, 480, 600 volts.



Table 15. 12½ tons three phase heating capacities (net) WS\*150E3, E4, EW at 5000 CFM

Outdoor Temp (°F)	_	ed Heating ( ndicated Dry		•	Total F		owatts at Ind Temp (°F)	dicated
70% RH	60	70	75	80	60	70	75	80
-8	50.9	48.5	47.2	45.9	9.6	10.3	10.8	11.3
-3	56.9	54.5	53.4	52.1	9.7	10.4	10.9	11.4
2	63.3	60.6	59.3	58.0	9.7	10.5	10.9	11.4
7	69.7	66.6	65.5	64.0	9.8	10.6	11.0	11.5
12	76.1	72.5	71.7	70.2	9.9	10.7	11.1	11.6
17	82.0	79.0	77.3	76.9	10.0	10.8	11.3	11.8
22	89.7	86.5	84.8	83.5	10.1	10.9	11.3	11.9
27	96.8	93.5	91.8	90.2	10.1	11.0	11.5	12.0
32	104.6	100.8	99.1	97.2	10.2	11.1	11.6	12.1
37	112.0	108.1	106.1	104.3	10.3	11.2	11.7	12.2
42	129.1	124.4	122.2	120.0	10.5	11.4	11.9	12.5
47	148.4	142.8	140.1	137.4	10.7	11.6	12.1	12.7
52	156.7	151.0	148.0	145.2	10.8	11.7	12.2	12.8
57	166.0	159.8	156.8	153.6	10.9	11.9	12.4	12.9
62	175.5	168.6	165.3	162.0	11.0	12.0	12.5	13.1
67	185.2	177.6	174.5	170.0	11.2	12.1	12.7	13.2
72	193.6	185.7	181.6	177.6	11.3	12.3	12.8	13.4

For other airflow conditions, see heating capacity correction factor Net Heating Capacity and Power Input include indoor fan heat at nominal CFM and 0.35 inch ESP. To obtain net heating at other conditions, subtract fan heat at this condition and add fan heat at new condition.

Heating capacities and powers are integrated to include the effects of defrost in the frost region.
 All heating capacities and power (kW) are at 70% OD relative humidity.



### **Performance Data**

Table 16. 15 tons three phase heating capacities (net) WS\*180E3, E4, EW at 6000 CFM

Outdoor Temp (°F)	•	ed Heating ( ndicated Dry			Total Power in Kilowatts at Indicated Dry Bulb Temp (°F)				
70% RH	60	70	75	80	60	70	75	80	
-8	56.3	54.8	54.0	53.2	10.5	11.5	12.0	12.5	
-3	62.8	61.1	60.2	59.4	10.7	11.7	12.1	12.7	
2	69.5	67.6	66.7	65.7	10.9	11.8	12.4	12.9	
7	76.2	71.1	69.9	70.8	11.1	12.0	12.5	14.0	
12	82.9	73.0	76.9	77.0	12.0	12.1	12.7	13.7	
17	88.2	85.4	84.0	82.7	11.4	12.4	12.9	13.5	
22	95.9	92.8	91.4	89.9	11.6	12.5	13.1	13.7	
27	103.8	100.6	98.9	97.3	11.8	12.7	13.3	13.9	
32	112.3	109.0	107.1	105.5	11.9	13.0	13.5	14.1	
37	120.8	117.1	115.4	113.7	12.1	13.2	13.8	14.4	
42	148.0	143.6	141.4	139.1	12.2	13.3	13.9	14.5	
47	179.2	173.8	170.8	168.0	12.6	13.6	14.2	14.8	
52	190.8	185.3	182.3	179.0	12.8	13.9	14.4	15.0	
57	204.1	197.7	194.2	191.5	13.1	14.1	14.7	15.3	
62	217.8	210.6	207.5	203.7	13.4	14.4	15.0	15.6	
67	233.5	225.5	221.1	217.0	13.7	14.8	15.4	16.0	
72	247.8	239.7	235.5	231.2	14.1	15.2	15.8	16.4	

For other airflow conditions, see heating capacity correction factor Net Heating Capacity and Power Input include indoor fan heat at nominal CFM and 0.35 inch ESP. To obtain net heating at other conditions, subtract fan heat at this condition and add fan heat at new condition.
 Heating capacities and powers are integrated to include the effects of defrost in the frost region.
 All heating capacities and power (kW) are at 70% OD relative humidity.



Table 17. 20 tons three phase heating capacities (Net) WS\*240E3, E4, EW at 8000 CFM

Outdoor Temp (°F)	_	ed Heating ( ndicated Dry		-	Total F		watts at Ind Temp (°F)	dicated
70% RH	60	70	75	80	60	70	75	80
-8	80.6	78.4	77.6	76.8	15.1	15.9	16.4	16.9
-3	87.5	85.3	84.5	83.4	15.3	16.0	16.5	17.0
2	96.3	93.9	92.8	91.7	15.4	16.2	16.7	17.2
7	106.0	103.2	102.3	101.0	15.5	16.3	16.8	17.3
12	118.3	116.2	115.5	114.7	15.7	16.5	17.0	17.5
17	131.1	128.2	127.4	126.3	15.9	16.7	17.2	17.7
22	142.9	140.3	138.8	137.2	16.1	16.9	17.4	17.9
27	154.1	151.3	150.0	148.6	16.4	17.3	17.8	18.3
32	165.5	162.4	161.2	159.6	16.5	17.4	17.9	18.4
37	180.9	177.6	175.7	174.5	16.8	17.7	18.2	18.7
42	196.5	191.9	189.8	188.2	17.0	17.9	18.4	18.9
47	213.3	209.1	207.0	205.4	17.1	18.0	18.5	19.0
52	228.9	224.2	221.4	219.8	17.4	18.3	18.8	19.3
57	243.4	237.7	235.6	233.0	17.8	18.8	19.3	19.8
62	261.9	255.7	252.6	250.0	20.0	21.1	21.6	22.1
67	279.6	272.0	268.9	265.3	20.1	21.2	21.7	22.2
72	298.5	291.1	287.9	283.8	20.4	21.5	22.0	22.6

Table 18. Heating capacity correction factors

% Variation of Nominal CFM	- 20	- 10	0	+ 10	+ 20
Total Gross Capacity Multiplier	0.96	0.98	1.0	1.01	1.02

Table 19. Auxiliary electric heat capacity

		Tota	Total <sup>(a)</sup>		Stag	ge 1	Stage 2	
	Unit	KW	MBh	No. of	KW	MBh	KW	MBh
Tons	Model No.	Input <sup>(b)</sup>	Output	Stages	Input <sup>(b)</sup>	Output	Input <sup>(b)</sup>	Output
		18.00	61.00	1	18.00	61.00	-	-
12½, 15	WS*150E3, E4, EW	36.00	123.00	2	18.00	61.00	18.00	61.00
	WS*180E3, E4, EW	54.00	184.00	2	36.00	123.00	18.00	61.00
		36.00	123.00	2	18.00	61.00	18.00	61.00
20	WS* 240E3, E4, EW	54.00	184.00	2	36.00	123.00	18.00	61.00
		72.00	246.00	2	36.00	123.00	36.00	123.00

<sup>(</sup>a) Heaters are rated at 240v,380v,480v and 600v. For other than rated voltage, CAP= (voltage/rated voltage)2 x rated cap. (b) For all input/output categories, does not include fan power or heat.

For other airflow conditions, see heating capacity correction factor Net Heating Capacity and Power Input include indoor fan heat at nominal CFM and 0.35 inch ESP. To obtain net heating at other conditions, subtract fan heat at this condition and add fan heat at new condition.

Heating capacities and powers are integrated to include the effects of defrost in the frost region.
 All heating capacities and power (kW) are at 70% OD relative humidity.

### **Performance Data**

Table 20. Electric heater voltage correction factors (applicable to auxiliary heat capacity)

Nominal	Distribution	Capacity		
Voltage	Voltage	Multiplier		
	208	0.75		
240	230	0.92		
	240	1.00		
	440	0.84		
480	460	0.94		
	480	1.00		
	540	0.81		
600	575	0.92		
	600	1.00		

Table 21. Air temperature rise across electric heaters (°F)

		12½ Ton 5000 CFM	15 Ton 6000 CFM	20 Ton 8000 CFM
ĸw	Stages	Three Phase WS*150E	Three Phase WS*180E	Three Phase WS*240E
9.00	1	-	-	-
17.30	1	-	-	-
18.00	1	11.4	9.5	-
27.00	2	-	-	-
36.00	2	23.0	19.0	14.2
54.00	2	34.1	28.4	21.3
72.00	2	-	-	28.5

Table 22. Electric heater temperature rise correction factors

% Variation From Nominal CFM	- 20	- 15	- 10	- 5	0	+5	+10	+15	+20
Temperature Rise Multiplier	1.25	1.17	1.11	1.05	1.00	0.95	0.91	0.87	0.83



### **Controls**


### **Field Installed Control Options**

### **Zone Sensors**

**Note:** Zone sensor required for units configured for Single Zone VAV indoor fan system control to enable Single Zone VAV functionality.


Zone Sensors are the building occupant's comfort control devices for units with ReliaTel:

### **Manual Changeover**




Heat, Cool or Off System Switch. Fan Auto or Off Switch. One temperature setpoint lever

# Manual/Automatic Changeover




Auto, Heat, Cool or Off System Switch. Fan Auto or Off Switch. Two temperature setpoint levers

# Manual/Automatic Changeover




Auto, Heat, Cool or Off System Switch. Fan Auto or Off Switch. Two temperature setpoint levers. Status Indication LED lights, System On, Heat, Cool, or Service.

## Manual/Automatic Changeover



Auto, Heat, Cool or Off System Switch. Fan Auto or Off Switch. Two temperature setpoint levers

### **Remote Sensor**




Sensor(s) available for all zone sensors to provide remote sensing capabilities

#### **RA Remote Sensor**

Return Air Remote Sensor which can be mounted in the return air duct to report return air temperature.



# Programmable Night Setback



Auto or manual changeover with seven-day programming. Keyboard selection of Heat, Cool, Fan, Auto, or On. All programmable sensors have System On, Heat, Cool, Service LED/indicators as standard. Night Setback Sensors have one (1) Occupied, one (1) Unoccupied, and one (1) Override program per day.

### Touchscreen Programmable Thermostat (2H/2C)




Two Heat/Two Cool programmable thermostat with touch screen digital display. Menu-driven programming. Effortless setup. Program each day separately with no need to copy multiple days. All programming can be done on one screen. Easy to read and use. Large, clear backlit digital display.

### CO<sub>2</sub> Sensor




The CO<sub>2</sub> sensor shall have the ability to monitor the concentration (parts per million, ppm) of CO<sub>2</sub> (Carbon Dioxide) in the air. As the CO<sub>2</sub> concentration changes, the outside air damper modulates to meet the current ventilation needs of the zone.

# Digital Display Programmable Thermostat (3H/2C)



Two Heat/Two Cool auto changeover digital display thermostat. 7-day programmable stat with night setback shall be available

# Digital Display Thermostat (3H/2C)



Three Heat, Two Cool auto changeover digital display thermostat.

### **Dual Thermistor Remote Zone Sensor**

This sensor will allow the customer to reduce the total number of remote sensors to obtain space temperature averaging. This sensor should be utilized with ReliaTel controls.

### **Room Remote Sensor**

Space Remote Sensor which can be mounted on the wall to report/control from a remote location in the space.



### **Electrical Data**

Table 23. Unit wiring

			Standard In	ndoor Motor	Oversize Indoor Fan Moto		
				Max Fuse Size or		Max Fuse Size or	
			Minimum Circuit		Minimum Circuit		
Tons	Unit Model #	Voltage Range	Ampacity	Breaker <sup>(a)</sup>	Ampacity	Breaker <sup>(a)</sup>	
	WS*150E3	187-253	67	80	73	90	
121/2	WS*150E4	414-506	32	40	35	40	
	WS*150EW	517-633	25	30	28	35	
	WS*180E3	187-253	73	90	79	100	
15	WS*180E4	414-506	36	45	39	50	
	WS*180EW	517-633	29	35	31	40	
	WS*240E3	187-253	113	150	124	150	
20	WS*240E4	414-506	53	70	59	70	
	WS*240EW	517-633	45	50	48	60	

<sup>(</sup>a) HACR type circuit breaker per NEC.

Table 24. Unit wiring with electric heat (single point connection) — standard refrigeration system (downflow and horizontal)

					Standar	d Indoor Motor	Oversize Indoor Motor		
Tons	Unit Model Number	Heater Model Number <sup>(a)</sup>	Heater kW Rating	Control Stages	MCA	Max Fuse Size or Max Circuit Breaker	MCA	Max Fuse Size or Max Circuit Breaker <sup>(b)</sup>	
		2	08/230 Volts	Three Pha	se				
		AYDHTRK318/AYHHTRM318	13.5/18.0	1	114/122	125/125	120/128	125/150	
121/2	WS*150E3	AYDHTRK336/AYHHTRM336	27.0/36.0	2	161/176	175/200	167/182	175/200	
		AYDHTRK354/AYHHTRM354	40.5/54.0	2	208/197	225/200	214/203	225/225	
		AYDHTRK318/AYHHTRM318	13.5/18.0	1	120/128	125/150	126/134	150/150	
15	WS*180E3	AYDHTRK336/AYHHTRM336	27.0/36.0	2	167/182	175/200	173/188	175/200	
		AYDHTRK354/AYHHTRM354	40.5/54.0	2	214/203	225/225	220/209	225/225	
		AYDHTRL336/AYHHTRN336	27.0/36.0	2	210/225	225/225	214/229	225/250	
20	WS*240E3	AYDHTRL354/AYHHTRN354	40.5/54.0	2	257/246	300/250	261/250	300/250	
		AYDHTRK372/AYHHTRN372	54.0/72.0	2	267/290	300/300	271/294	300/300	
			460 Volts Thr	ee Phase					
		AYDHTRK418/AYHHTRM418	18	1	60	60	63	70	
121/2	WS*150E4	AYDHTRK436/AYHHTRP436	36	2	87	90	90	90	
		AYDHTRK454/AYHHTRM454	54	2	97	100	100	100	
		AYDHTRK418/AYHHTRM418	18	1	65	70	67	70	
15	WS*180E4	AYDHTRK436/AYHHTRM436	36	2	91	100	94	100	
		AYDHTRK454/AYHHTRM454	54	2	101	110	104	110	
		AYDHTRL436/AYHHTRN436	36	2	108	110	112	125	
20	WS*240E4	AYDHTRL454/AYHHTRN454	54	2	118	125	122	125	
		AYDHTRK472/AYHHTRN472	72	2	140	150	144	150	



### **Electrical Data**

Table 24. Unit wiring with electric heat (single point connection) — standard refrigeration system (downflow and horizontal) (continued)

					Standar	d Indoor Motor	Oversiz	e Indoor Motor
Tons	Unit Model Number			Control Stages	MCA	Max Fuse Size or Max Circuit Breaker	MCA	Max Fuse Size or Max Circuit Breaker <sup>(b)</sup>
			575 Volts Thi	ee Phase				
-		AYDHTRKW18 (AYDHTRLW18) <sup>(a)</sup> /AYHHTRMW18 (AYHHTRPW18)	18	1	47	50	50	50
12½	WS*150EW	AYDHTRKW36/AYHHTRMW36 (AYHHTRRW36) <sup>(a)</sup>	36	2	69	70	72	80
		AYDHTRKW54/AYHHTRMW54	54	2	77	80	80	80
		AYDHTRKW18 (AYDHTRMW18) <sup>(a)</sup> /AYHHTRMW18 (AYHHTRQW18)	18	1	51	60	53	60
15	WS*180EW	AYDHTRKW36/AYHHTRMW36 (AYHHTRSW36) <sup>(a)</sup>	36	2	73	80	75	80
		AYDHTRKW54/AYHHTRMW54	54	2	81	90	83	90
		AYDHTRLW36/AYHHTRNW36	36	2	89	90	92	100
20	WS*240EW	AYDHTRLW54/AYHHTRNW54	54	2	97	100	100	100
		AYDHTRKW72/AYHHTRNW72	72	2	115	125	118	125

<sup>(</sup>a) Heater model numbers in parenthesis apply to units with an optional high SCCR rating. (b) Values do not include power exhaust accessory.

\* Indicates both downflow and horizontal units.

Table 25. Electrical characteristics - power exhaust accessory

Tons	Accessory Operating Voltage	Phase	НР	RPM	Amps FLA	LRA
	208-230	1	3/4	1040	6.6	13.5
12½, 15, 20	460	1	3/4	1040	3.2	8.4
	575	1	3/4	1040	2.1	5.2

Table 26. Electrical characteristics - evaporator fan motors - 60 cycle

-			Standard Evaporator Fan Motor						Oversized Evaporator Fan Motor						
						Am	nps					Am	nps		
Tons	Unit Model No.	No.	Volts	Phase	НР	FLA	LRA	No.	Volts	Phase	НР	FLA	LRA		
	WS*150E3	1	208-230	3	3.00	10.6	81.0	1	208-230	3	5.00	16.7	109.8		
121/2	WS*150E4	1	460	3	3.00	4.8	40.5	1	460	3	5.00	7.6	54.9		
	WS*150EW	1	575	3	3.00	3.9	31.0	1	575	3	5.00	6.1	41.6		
	WS*180E3	1	208-230	3	3.00	10.6	81.0	1	208-230	3	5.00	16.7	109.8		
15	WS*180E4	1	460	3	3.00	4.8	40.5	1	460	3	5.00	7.6	54.9		
	WS*180EW	1	575	3	3.00	3.9	31.0	1	575	3	5.00	6.1	41.6		
	WS*240E3	1	208-230	3	5.00	16.7	109.8	1	208-230	3	7.50	24.2	120.4		
20	WS*240E4	1	460	3	5.00	7.6	54.9	1	460	3	7.50	11.0	74.0		
	WS*240EW	1	575	3	5.00	6.1	41.6	1	575	3	7.50	9.0	60.0		

Table 27. Electrical characteristics - compressor motor and condenser motor - 60 cycle


				Compressor Motors					Condenser Fan Motors				
							Amp	os <sup>(a)</sup>				An	nps
Tons	Unit Model Number	No.	Volts	Phase	HP <sup>(b)</sup>	RPM	RLA	LRA	No.	Phase	HP	FLA	LRA
	WS*150E3	2	208-230	3	5.6	3450	22.4	149	2	3	0.5	2.7	9.65
121/2	WS*150E4	2	460	3	5.6	3450	10.6	75	2	3	0.5	1.35	4.82
	WS*150EW	2	575	3	5.6	3450	7.9/7.7	54	2	3	0.5	0.8	3.40
	WS*180E3	2	208-230	3	6.9	3450	25	164	2	3	0.5	2.7	9.65
15	WS*180E4	2	460	3	6.9	3450	12.5/12.2	100	2	3	0.5	1.35	4.82
	WS*180EW	2	575	3	6.9	3450	10.3/10.1	78	2	3	0.5	0.8	3.40
	WS*240E3	2	208-230	3	10.4	3450	39.1	267	2	3	1	3.8	16.42
20	WS*240E4	2	460	3	10.4	3450	17.3	142	2	3	1	1.8	7.7
	WS*240EW	2	575	3	10.4	3450	15.4	103	2	3	1	1.84	7.4

<sup>(</sup>a) For Compressor Motors and Condenser Fan Motors: Amp draw for each motor; multiply value by number of motors to determine total amps. (b) HP for each compressor.
\*Indicates both downflow and horizontal units.



# **Dimensional Data**

Figure 1. Heat pump models - 12½ - 20 tons



American Standard





Figure 2. Heat pump models - 12½ - 20 tons

Figure 3. Heat pump models - 121/2 - 20 tons



<sup>\*</sup> All dimensions are in inches/millimeters.

<sup>\*</sup> All dimensions are in inches/millimeters.







Figure 4. Heat pump models - 12½ - 20 tons

Figure 5. Heat pump models - 121/2 - 20 tons



<sup>\*</sup> All dimensions are in inches/millimeters.

<sup>\*</sup> Duct flanges mount 7-7/16" down inside the curb on the 1-1½ curb flanges. Roofcurb is intended for downflow use only. 
\* All dimensions are in inches/millimeters.



Downflow Condensate Location

R | W'' Horizontal Condensate Location

S | T | G Location

A | B | C | D

Figure 6. Downflow & horizontal condensate locations

Table 28. Heat pump units


									Condensate I	Drain Location
		Downflow Only						Condensate	Downflow	Horizontal
Tons	Α	В	С	D	F	G	Н	Drain Size	J	К
12½, 15, 20	26 7/16	28 3/4	19 15/16	4 1/4	4 1/4	76 5/16	68 11/16	1 NPT	26 3/4	5 3/8

Table 29. Swing clearances

Unit Model #	Α	В	С	D	E
WSD 150-240	29 1/2	56	38 1/2	18 1/2	N/A
WSH 150-240	29 1/2	N/A	38 1/2	18 1/2	14

Note: All dimensions are in inches.

TOP VIEW SHOWING THROUGH THE BASE ELECTRICAL UTILITY LOCATIONS AND ACCESS PANEL SWING CLEARANCES.



## **Dimensional Data**

Figure 7. Fresh air hood (horizontal units)




Figure 8. Fresh air hood (downflow units)




Figure 9. Power exhaust - downflow economizers




Figure 10. Power exhaust - downflow economizers - side view





Figure 11. Economizer - horizontal units



**Note:** When applying economizer to horizontal units, connected ductwork must be run full size to allow proper operation of economizer damper.

Figure 12. Economizer - downflow units




Table 30. Power exhaust dimensions

Unit Model #	Α	B <sup>(a)</sup>	C(p)
WS* 150-240	191⁄2	64¾	39

<sup>(</sup>a) Horizontal dimension only. Downflow economizer is width of end panel.

end panel.
(b) Power exhaust is applied on downflow economizer only.

# Weights

Table 31. Accessory net weights (lbs)

		Std Economizer		Low Leak Economizer	Outside Air Damper		Power		Oversized	High
Tons	Unit Model No.	Net	Ship	Net	Manual		Exhaust (b)	Roof Curb		Static Drive
12½, 15, 20	WSD150-240E	80	265	250	32	75	95	235	5	10
12½, 15, 20	WSH150-240E	65	210	220	32	75	-	ı	5	15

<sup>(</sup>a) Net weight should be added to unit weight when ordering factory installed economizer or oversize motor. (b) Downflow only.

Table 32. Electric heaters weights

Ī				Electric Heaters <sup>(a)(b)</sup>				
			All Zone	0 10 KH   20 00 KH   0 1 KH   72 KH			72 kW	
	Tons	Unit Model No.	Sensors	240/480V	240/480V	240/480V	240/480V	
İ	12½-20	WS*150E, 180E, 240E	1	28/22	33/27	40/32	43/34	


<sup>(</sup>a) For 600V heaters net weights are same as 480V heaters. (b) To estimate shipping weight add 5 lbs to net weight.

Table 33. Variable frequency drive weights

Motor Size	WSD150-240E	WSH150-240E		
3 <sup>(a)</sup> & 5 HP	32	34		
7.5 HP <sup>(b)</sup>	63	65		

<sup>(</sup>a) 3 HP motors not applicable to WS\*240E units.

Figure 13. Center of gravity



<sup>(</sup>b) WS\*240E units only.

Table 34. Maximum unit & corner weights (lbs) and center of gravity dimensions (ln.)

		Maximum Weights (Lbs)		Corner Weights (Lbs)				Center of Gravity (In.)		
Tons	Unit Model No.	Shipping	Net	Α	В	С	D	Length	Width	
121/2	WS*150E	2455	2024	647	524	385	468	55	35	
15	WS*180E	2459	2028	648	525	386	469	55	35	
20	WS*240E	2641	2198	717	575	403	502	54	35	

Table 35. Factory installed options (FIOPS) net weights (lbs)<sup>(a)(b)(c)</sup>

Accessory	Weight	Unit Model No.
	49	WS*150-180 standard size motor
High Efficiency Matera(d)	27	WS*240 standard size motor
High Efficiency Motors (d)	36	WS*150-180 oversized motor
	0	WS*240 oversized size motor
Hinged Doors	27	All WS* units
Powered Convenience Outlet	38	All WS* units
Through the Base Electrical	23	All WS* units
Unit Mounted Circuit Breaker	5	All WS* units except those with 54&72 kW heaters & 208/230V
Unit Mounted Circuit Breaker	10	All WS* units with 54&72 kW heaters & 208/230V
Unit Mounted Disconnect	5	All WS* units except those with 54&72 kW heaters & 208/230V
Unit Mounted Disconnect	10	All WS* units with 54&72 kW heaters & 208/230V
Smoke Detectors (Supply/Return)	5	All WS* units
Tool loos Hail Cooned	43	WS*150,180
Tool-less Hail Guard	51	WS*240
Stainless Steel Drain Pan	8.1	All WS* units

<sup>(</sup>a) Weights for FIOP accessories not listed are < 5 lbs.

**Note:** \* Indicates both downflow and horizontal units.

<sup>(</sup>b) Net weight should be added to unit weight when ordering factory installed accessories.

<sup>(</sup>c) See Table 31, p. 43 for standard factory installed economizer and oversized motors.
(d) Standard factory installed motors are already included in unit net and shipping weights. Values shown for high efficiency motors are in addition to the standard motor weight.



# **Jobsite Connections**


## Table 36. Zone sensors - typical number of wires

#### Zone Sensors

36113013	
Α	Manual Changeover
	Manual/Auto Changeover5
	Manual/Auto Changeover with Status Indication LED's10
	Programmable Night Setback with Status Indication LED's7

#### **Thermostats**

B 3 Power Wires + 1 Ground Wire (three phase) 2 Power Wires + 1 Ground Wire (single phase)



#### Notes:

- For specific wiring information, see the installation instructions.
- All wiring except power wires is low voltage.
- All customer-supplied wiring should be copper and must conform to NEC or CEC and local electrical codes.
- Wiring shown dotted is to be furnished and installed by the customer.
- Zone sensors are required for units configured for Single Zone VAV indoor fan system control
  in order to enable Single Zone VAV functionality.



# **Mechanical Specifications**

## General

The units shall be dedicated downflow or horizontal airflow. The operating range shall be between 115°F and 0°F in cooling as standard from the factory for all units. Cooling performance shall be rated in accordance with ARI testing procedures. All units shall be factory assembled, internally wired, fully charged with R-410A, and 100% run tested to check cooling operation, fan and blower rotation and control sequence, before leaving the factory. Wiring internal to the unit shall be colored and numbered for simplified identification. Units shall be UL listed and labeled, classified in accordance to UL 1995/C 22.2, 236-05 3<sup>rd</sup> Edition.

Packaged Rooftop units cooling, heating capacities, and efficiencies are AHRI certified within scope of AHRI Standard 340/360 (I-P) and ANSIZ21.47.

## Casing

Unit casing shall be constructed of zinc coated, heavy gauge, galvanized steel. Exterior surfaces shall be cleaned, phosphatized, and finished with a weather-resistant baked enamel finish. Unit's surface shall be tested 500 hours in a salt spray test in compliance with ASTM B117. Cabinet construction shall allow for all maintenance on one side of the unit. In order to ensure a water and air tight seal, service panels shall have lifting handles and no more than three screws to remove.

All exposed vertical panels and top covers in the indoor air section shall be insulated with a 1/2 inch, 1 pound density foil-faced, fire-resistant, permanent, odorless, glass fiber material. The base of the downflow unit shall be insulated with 1/2 inch, 1 pound density foil-faced, closed-cell material. The downflow unit's base pan shall have no penetrations within the perimeter of the curb other than the raised 11/8 inch high supply/return openings to provide an added water integrity precaution, if the condensate drain backs up. The base of the unit shall have provisions for forklift and crane lifting.

#### **Unit Top**

The top cover shall be one piece, or where seams exist, double hemmed and gasket sealed to prevent water leakage.

#### **Filters**

Two inch standard filters shall be factory supplied on all units. Optional two inch pleated MERV 8 and MERV 13 filters with filter removal tool shall be available.

#### Compressors

External high pressure cutout shall be provided on all 15 and 20 models. Low pressure switches shall be standard. All units shall have direct-drive, hermetic, scroll type compressors with centrifugal type oil pumps. Motor shall be suction gas-cooled and shall have a voltage utilization range of plus or minus 10% of nameplate voltage. Internal overloads shall be provided with the scroll compressors. Crankcase heaters shall be utilized with all scroll compressors.

## **Refrigerant Circuits**

Each refrigerant circuit shall have independent fixed orifice or thermostatic expansion devices, service pressure ports, and refrigerant line filter driers factory installed as standard. An area shall be provided for replacement suction line driers.

#### **Evaporator and Condenser Coils**

Internally finned, 5/16" copper tubes mechanically bonded to a configured aluminum plate fin shall be standard. Coils shall be leak tested at the factory to ensure the pressure integrity. All coils are pressure and leak tested at minimum of 450 psig. The completely assembled refrigerant system is leak tested at a minimum of 240 psig with a refrigerant and nitrogen mixture. All dual compressor units shall have intermingled evaporator coils. Sloped condensate drain pans are standard. Patent-pending 1+1+1 condenser coil, permanently gapped for easy cleaning is available.



#### **Outdoor Fans**

The outdoor fan shall be direct-drive, statically and dynamically balanced, draw-through in the vertical discharge position. The fan motor(s) shall be permanently lubricated and shall have built-in thermal overload protection.

#### Indoor Fan

Units above shall have belt driven, FC centrifugal fans with adjustable motor sheaves. Units with standard motors shall have an adjustable idler-arm assembly for quick-adjustment of fan belts and motor sheaves. All motors shall be thermally protected. Oversized motors shall be available for high static application. All indoor fan motors meet the U.S. Energy Policy Act of 1992 (EPACT).

#### **Controls**

Unit shall be completely factory- wired with necessary controls and contactor pressure lugs or terminal block for power wiring. Unit shall provide an external location for mounting a fused disconnect device. ReliaTel controls shall be provided for all 24-volt control functions. The resident control algorithms shall make all heating, cooling, and/or ventilating decisions in response to electronic signals from sensors measuring indoor and outdoor temperatures. The control algorithm maintains accurate temperature control, minimizes drift from set point, and provides better building comfort. A centralized control shall provide anti-short cycle timing and time delay between compressors to provide a higher level of machine protection.

#### **Defrost Controls**

Adaptive demand defrost shall be provided to permit defrost wherever coil icing conditions begin to significantly reduce unit capacity.

## **Discharge Line Thermostat**

A bi-metal element discharge line thermostat is installed as a standard option on the discharge line of each system. This standard option provides extra protection to the compressors against high discharge temperatures in case of loss of charge, extremely high ambient and other conditions which could drive the discharge temperature higher. Discharge line thermostat is wired in series with high pressure control. When the discharge temperature rises above the protection limit, the bi-metal disc in the thermostat switches to the off position, opening the 24 VAC circuit. When the temperature on the discharge line cools down, the bi-metal disc closes the contactor circuit, providing power to the compressor. When the thermostat opens the fourth time, the ReliaTel control must be manually reset to resume operation on that stage.

## **Phase Monitor**

The Phase Monitor is a 3 phase line monitor module that protects against phase loss, phase reversal and phase unbalance. It is intended to protect compressors from reverse rotation. It has an operating input voltage range of 190-600 VAC, and LED indicators for ON and FAULT. There are no field adjustments and the module will automatically reset from a fault condition.

## Variable Frequency Drive

Variable Frequency Drives are factory installed and tested to provide supply fan motor speed modulation. VFDs on the supply fan, as compared to inlet guide vanes or discharge dampers, are quieter, more efficient, and are eligible for utility rebates. All VFDs are designed to allow bypass if required. Bypass control will simply provide full nominal airflow in the event of drive failure.



## **Factory Installed Options**

#### **Black Epoxy Pre-Coated Coils**

The black epoxy coils have a thermoset vinyl coating that is bonded to the aluminum fin stock prior to the fin-stamping process. The pre-coated coils are an economical option for protection in mildly corrosive environments.

#### Condensate Overflow Switch

This option shall shut the unit down in the event that a clogged condensate drain line prevents proper condensate removal from the unit.

## Fault Detection & Diagnostics (FDD)

This offering meets the mandatory requirement of Title 24. This option provides detection of the following faults: Air temperature sensor failure/fault, not economizing when it should, economizing when it should not, damper not modulating, and excessive outdoor air. The FDD system shall be certified by the Energy Commission as meeting the requirements.

## **High Efficiency Motors**

This option is available with efficiency ratings from 86.5 up to 91.0. It is not available for all models.

## **High Short Circuit Current Rating**

Unit shall be provided with electrical subsystem that will withstand fault currents up to 65kA (208/230, 460 VAC) or 25kA (575 VAC) compliant with UL 1995 and NEC 440.4 (B). Each compressor circuit and the indoor fan shall have dedicated overcurrent protection. Three phase motors shall be protected by Class J time delay fuses. Single phase motors shall be protected by Class CC time delay fuses. All transformers shall also be protected with Class CC time delay fuses. Contactors shall be din rail mounted.

#### **Hinged Access Doors**

Sheet metal hinges are available on the Filter, Evaporator, ID Fan and Compressor/Control Access Doors. This option is available on all models.

#### **Horizontal Side Access with Circuit Breaker**

This option is a thermal magnetic, molded case, HACR Circuit Breaker with provisions for through the base electrical connections. The circuit breaker will be installed in a water tight enclosure in the unit with access through a swinging door. Factory wiring will be provided from the switch to the unit high voltage terminal block. The circuit breaker will provide overcurrent protection, be sized per NEC and UL guidelines, and be agency recognized by UL/CSA.

#### **Horizontal Side Access with Disconnect Switch**

Three-pole, molded case, disconnect switch with provisions for through the base electrical connections are available. The disconnect switch will be installed in the unit in a water-tight enclosure with access through a swinging door. Factory wiring will be provided from the switch to the unit high voltage terminal block. The switch will be UL/CSA agency recognized.

**Note:** The disconnect switch will be sized per NEC and UL guidelines but will not be used in place of unit overcurrent protection. This option is available on all models.

#### **Human Interface**

The Human Interface shall have a 5 inch color touchscreen display that conforms to FCC Part 15 Class B with an Ingress Protection Rating of IP24. The display text shall be readable by a person with 20/20 vision at a distance of 3 feet and 60° angle at lighting levels ranging from 100 lux - 25,000 lux. Also, the display shall operate at temperatures of -40° C to 70° C. Firmware and unit configurations shall be able to be restored via a USB storage device.



## Multi-Speed Indoor Fan System

Multi-speed indoor fan system is designed for use in applications for meeting the minimum requirement of CA Title 24. This system incorporates a multi-speed fan control to change the speed of the fan to 67% of full airflow based off of compressor stages.

## **Powered or Unpowered Convenience Outlet**

This option is a GFCI, 120v/15amp, 2 plug, convenience outlet, either powered or unpowered. When the convenience outlet is powered, a service receptacle disconnect will be available. The convenience outlet is powered from the line side of the disconnect or circuit breaker, and therefore will not be affected by the position of the disconnect or circuit breaker. This option can only be ordered when the Through the Base Electrical with either the Disconnect Switch, or Circuit Breaker, option is ordered. This option is available on all models.

## Single Zone VAV

SZVAV systems combine Trane application, control and system integration knowledge to exactly match fan speed with cooling and heating loads, regardless of the operating condition.

#### Stainless Steel Drain Pan

This option provides excellent corrosion and oxidation resistance. Drain pan shall be constructed of 304 stainless steel.

## Supply, Return and Plenum Air Smoke Detector

With this option installed, if smoke is detected, all unit operation will be shut down. Reset will be manual at the unit. Return Air Smoke Detectors require minimum allowable airflow when used with certain models. See the Installation, Operation, and Maintenance (IOM) manual for the models affected and the minimum allowable airflow required. This option is available on all downflow models. Supply and/or Return Detectors may not be used with the Plenum Smoke Detector.

## Through the Base Electrical with Circuit Breaker

This option is a thermal magnetic, molded case, HACR Circuit Breaker with provisions for through the base electrical connections. The circuit breaker will be installed in a water tight enclosure in the unit with access through a swinging door. Factory wiring will be provided from the switch to the unit high voltage terminal block. The circuit breaker will provide overcurrent protection, be sized per NEC and UL guidelines, and be agency recognized by UL/CSA.

## Through the Base Electrical with Disconnect Switch

Three-pole, molded case, disconnect switch with provisions for through the base electrical connections are available. The disconnect switch will be installed in the unit in a water-tight enclosure with access through a swinging door. Factory wiring will be provided from the switch to the unit high voltage terminal block. The switch will be UL/CSA agency recognized.

**Note:** The disconnect switch will be sized per NEC and UL guidelines but will not be used in place of unit overcurrent protection. This option is available on all models.

## **Through the Base Utilities Access**

An electrical service entrance shall be provided allowing electrical access for both control and main power connections inside the curb and through the base of downflow units, and through the front of the horizontal units. Option will allow for field installation of liquid-tight conduit and an external field-installed disconnect switch.

#### **Two-Inch Pleated Filters**

Two inch pleated MERV 8 or MERV 13 filters with filter removal tool shall be available on all models.

## **Mechanical Specifications**

## **Factory or Field Installed Options**

## **BACnet™ Communications Interface**

This option shall be provided to allow the unit to communicate directly with a generic open protocol BACnet MS/TP Network Building Automation System Controls.

#### **Barometric Relief**

This option shall provide a pressure operated damper for the purpose of space pressure equalization and be gravity closing to prohibit entrance of outside air during the equipment "off" cycle.

## Clogged Filter/Fan Failure Switch

A dedicated differential pressure switch is available to achieve active fan failure indication and/or clogged filter indication. These indications will be registered with either a zone sensor with status indication lights or an Integrated Comfort™ System.

#### **Differential Pressure Switches**

These options allow for individual fan failure and dirty filter indication. The fan failure switch will disable all unit functions and "flash" the Service LED on the zone sensor. The dirty filter switch will light the Service LED on the zone sensor and will allow continued unit operation.

## **Discharge Air Sensing Kit**

This kit provides true discharge air sensing in heating models. This sensor is a status indicator readable through Tracer™ or Tracker™. The kit is functional only with the ReliaTel Options Module.

#### **Economizer - Standard, Downflow**

The assembly includes fully modulating 0-100% motor and dampers, barometric relief, minimum position setting, preset linkage, wiring harness with plug, fixed dry bulb and spring return actuator. The barometric relief damper shall be standard with the downflow economizer and shall provide a pressure operated damper that shall be gravity closing and shall prohibit entrance of outside air during the equipment "off" cycle. Solid state enthalpy and differential enthalpy control shall be field-installed.

#### **Economizer - Low Leak, Downflow**

This accessory meets low leak requirements for ASHRAE 90.1, IECC, and CA Title 24 standards (3 cfm/ft^2@1" wg exterior air, 4 cfm/ft^2@1" wg return air). This option allows 100% outdoor air supply from 0-100% modulating dampers and is standard with barometric relief. It can be paired with powered exhaust for additional building pressure relief. This option can be paired with or without Fault Detection & Diagnostics (FDD) to meet current mandatory CA Title 24 requirements. Available on downflow units only. The economizers come with three control options, dry bulb and reference or comparative enthalpy (optional).

#### **Electric Heaters**

Electric heat modules shall be available for installation within the basic unit. Electric heater elements shall be constructed of heavy-duty nickel chromium elements internally delta connected for 240 volt, wye connected for 480 and 600 volt. Staging shall be achieved through ReliaTel. Each heater package shall have automatically reset high limit control operating through heating element contactors. All heaters shall be individually fused from the factory, where required, and shall meet all NEC and CEC requirements when properly installed. Power assemblies shall provide single-point connection. Electric heat modules shall be UL listed or CSA certified. If ordering the Through the Base Electrical option with an Electric Heater, the heater must be factory installed.



#### Frostat™

This option is to be utilized as a safety device. The Frostat opens when temperatures on the evaporator coil fall below 10°F. The temperature will need to rise to 50°F before closing. This option should be utilized in low airflow or high outside air applications.

## **Indoor Fan Motor Shaft Grounding Ring**

Shaft grounding rings are used on all VFD driven motors to provide a conductive discharge path away from the motor bearings to ground. Bearing Protection Ring shall be maintenance free circumferential ring of conductive micro fibers that discharges voltages to ground.

#### **Oversized Motors**

Oversized motors shall be available for high static applications.

#### Reference or Comparative Enthalpy

Reference Enthalpy is used to measure and communicate outdoor humidity. The unit receives and uses this information to provide improved comfort cooling while using the economizer. Comparative Enthalpy measures and communicates humidity for both outdoor and return air conditions and return air temperature. The unit receives and uses this information to maximize use of economizer cooling, and to provide maximum occupant comfort control. Reference or Comparative Enthalpy option shall be available when a factory or field installed Downflow Economizer is ordered. This option is available on all downflow models.

#### Tool-less Hail Guards

Tool-less, hail protection quality coil guards are available for condenser coil protection.

## Field Installed Options

## CO<sub>2</sub> Sensor

The  $CO_2$  sensor shall have the ability to monitor the concentration (parts per million, ppm) of  $CO_2$  (Carbon Dioxide) in the air. As the  $CO_2$  concentration changes, the outside air damper modulates to meet the current ventilation needs of the zone.

**Note:** Choose factory-installed CO<sub>2</sub> sensor wiring option to save time and ensure proper unit connections for the field installed CO<sub>2</sub> sensor kits.

#### **Digital Display Zone Sensor**

The Digital LCD (Liquid Crystal Display) zone sensor has the look and functionality of standard zone sensors. This sensor includes a digital display of set point adjustment and space temperature in °F (Fahrenheit) or °C (Celsius). Includes FAN and SYSTEM buttons (supports the service functions of the standard sensor). E-squared memory stores last programmed set points. Requires 24 VAC (Volts AC). This sensor should be utilized with ReliaTel™ controls.

## **Economizer - Standard, Horizontal**

The horizontal economizer shall contain the same features as the downflow economizer with the exception of barometric relief.

#### **Economizer - Low Leak, Downflow & Horizontal**

This accessory meets low leak requirements for ASHRAE 90.1, IECC, and CA Title 24 standards (3 cfm/ft^2@1" wg exterior air, 4 cfm/ft^2@1" wg return air). This option allows 100% outdoor air supply from 0-100% modulating dampers and is standard with barometric relief. It can be paired with powered exhaust for additional building pressure relief.



## **Mechanical Specifications**

#### **High Static Drive**

The high static drive option shall allow the standard motor on the  $12\frac{1}{2}$  and 15 ton units to operate with improved external static capabilities.

## **Manual Outside Air Damper**

The rain hood and screen shall provide up to 25% outside air.

### **Motorized Outside Air Dampers**

Manually set outdoor air dampers shall provide up to 50% outside air. Once set, outdoor air dampers shall open to set position when indoor fan starts. The damper shall close to the full closed position when indoor fan shuts down.

#### **Powered Exhaust**

The powered exhaust shall provide exhaust of return air, when using an economizer, to maintain better building pressurization.

#### **Roof Curb - Downflow**

The roof curb shall be designed to mate with the downflow unit and provide support and a water tight installation when installed properly. The roof curb design shall allow field-fabricated rectangular supply/return ductwork to be connected directly to the curb. Curb design shall comply with NRCA requirements. Curb shall be shipped knocked down for field assembly and shall include wood nailer strips.

#### Remote Potentiometer

The minimum position setting of the economizer shall be adjusted with this accessory.

#### **Ventilation Override Accessory**

With the Ventilation Override Accessory installed, the unit can be set to transition up to three different pre-programmed sequences for Smoke Purge, Pressurization, and Exhaust. The transition occurs when a binary input on the RTOM is closed (shorted). This would typically be a hard wired relay output from a smoke detector or fire control panel.

#### **Zone Sensors**

This option shall be provided to interface with Voyager units and shall be available in either manual, automatic, programmable with night setback, with system malfunction lights or remote sensor options.

**Note:** Zone sensors are required for units configured for Single Zone VAV indoor fan system control to enable Single Zone VAV functionality.



Ingersoll Rand (NYSE:IR) advances the quality of life by creating comfortable, sustainable and efficient environments. Our people and our family of brands-including Club Car®, Ingersoll Rand®, Thermo King® and Trane®-work together to enhance the quality and comfort of air in homes and buildings; transport and protect food and perishables; and increase industrial productivity and efficiency. We are a global business committed to a world of sustainable progress and enduring results.









ingersollrand.com





Globally Recognized. Industry Respected.

The AHRI Certified mark indicates Ingersoll Rand's participation in the AHRI Certification program. For verification of individual certified products, go to www.ahridirectory.org.

Ingersoll Rand has a policy of continuous product and product data improvement and reserves the right to change design and specifications without notice.

We are committed to using environmentally conscious print practices.