
spirax sarco

Stainless Steel Float & Thermostatic Steam Trap FT 46

The FT 46 is a stainless steel float trap designed for applications requiring continuous drainage of high condensate loads in filtered steam applications.

Model	FT 46 - 4.5	FT 46 - 10	FT 46 - 14	FT 46 - 21			
РМО	65 psig	145 psig	200 psig	300 psig			
Sizes	1", 1-1/2", 2"						
Connections	ANSI 150, 300						
Construction	AISI 316 Stainless Steel Body, Stainless Steel Internals						
Options	3/8" NPT Drain Cock Tapping						



1-1/2" and 2"

Construction Materials							
No.	Part	Material					
1	Body	Stainless Steel	AISI 316				
2	Cover Bolts	Stainless Steel	Class A2 Gr80				
	1"	M10 x 60 mm					
	1-1/2", 2"	M16 x 85 mm					
3	Cover Gasket	Stainless Steel					
4	Cover	Stainless Steel	AISI 316				
5	Valve Seat 1"	Stainless Steel					
	Main Valve Assembly	Stainless Steel					
	w/ Erosion Deflector						
	1-1/2", 2"						
6	Valve Seat Gasket 1"	Stainless Steel					
	Main Valve Assembly	Stainless Steel					
	Gasket 1-1/2", 2"						
7	Pivot Frame Assmebly	Stainless Steel					
	Set Screws 1"	M5 x 20 mm					
	Main Valve Assembly	Stainless Steel					
	Bolts 1-1/2"	M6 x 20 mm					
	Studs & Nuts 2"	M8 x 20 mm					
8	Ball Float & Lever	Stainless Steel					
9	Air Vent	Stainless Steel	<u> </u>				
11	Support Frame	Stainless Steel					
12	Pivot Frame	Stainless Steel					

Capacities

Refer to TIS 2.308

Typical Applications

Removal of filtered steam condensate from heating jackets, heat exchangers, large process vessels, steam filters, separators, and humidifiers.

Limiting Operating Conditions

Max. Operating Pressure (PMO) FT46-4.5: 65 psig (4.5 barg) FT46-10: 145 psig (10 barg) FT46-14: 200 psig (14 barg)

FT46-21: 300 psig (21 barg)

Max. Operating Temperature

45°F (25℃) of Superheat at all operating pressures

Pressure Shell Design Conditions


PMA 580 psig/0-248°F 40 barg/0-120℃ Max. allowable pressure 472 psig/464°F 32 barg/240 ℃ 21 barg/400℃ 304 psig/752°F **TMA**

Max. allowable temperature


752°F/0-304 psig 400 ℃/0-21 barg


TI-**2-318**-US 1.14

Stainless Steel Float & Thermostatic Steam Trap FT 46



Dimensions (nominal) in inches and millimeters								
Size/DN	Α	В	С	D	E	Weight		
1"	6.2	4.5	3.4	10.8 276	6.7	33 lb		
25	160	115	85		170	15 kg		
1-1/2"	9.0	4.8	4.5	12.7	7.9 200	72.8 lb		
40	230	130	115	326		33 kg		
2"	9.0	5.5	4.8	12.9	7.9 200	94.8 lb		
50	230	141	123	332		43 kg		





Installation

The trap msut be fitted with the direction of flow as indicated on the body, and with the float arm in a horizontal plane so that it rises and falls vertically. Full-flow isolating valves should be installed upstream and downstream of the trap.

Sample Specification


Float & Thermostatic traps for pharmaceutical sterile areas on plant or clean steam service shall have 316L stainless steel bodies and covers, and all internals, including float, main valve, head/seat, thermostatic air vent and air vent head/seat, shall be stainless steel. Connections shall be in-line horizontal. ANSI flanged Spirax Sarco Model FT 46.

Maintenance

This product can be maintained without disturbing the piping connections. Complete isolation from both supply and return line is required before any servicing is performed. The trap should be disassembled periodically for inspection and cleaning of the valve head and seat, operating mechanism and air vent.

Worn or damaged parts should be replaced using a complete main valve assembly and/or air vent assembly.

Complete installation and maintenance instructions are given in the IMI sheet, which accompanies the product.



TI-2-318-US 1.14

Telephone: (803) 714-2000 FAX (803) 714-2222