


# SPECIFICATION SERVICE SADDLE ALL STAINLESS DOUBLE BOLT MODEL 372




#### APPLICATIONS

- Typical Uses
  - Repair and restore damaged, broken, or torn out service connections or branch lines
  - Tapping branch connections on new or existing pipe
- Standard Pipe Sizes
  - 4" to 16" nominal
- Standard Taps
  - NPT: 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
  - CC/AWWA: 1/2", 3/4", 5/8", 1", 1-1/4", 1-1/2", 2"
  - BSP: 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"

See Smith-Blair catalog for available pipe diameter and tap size combinations as some combinations are not available

- Standard Width
  - 7.50"
- Type of Pipe
  - Carbon Steel, Stainless Steel, Ductile Iron, PVC, HDPE DR17 or thicker (with use of spring washers), Asbestos Cement, Copper, Aluminum
- Working Pressure
  - Up to 150 psi depending on **pipe size**, type of pipe, type of repair, pipe diameter, service conditions, and installation workmanship





# SPECIFICATION SERVICE SADDLE ALL STAINLESS DOUBLE BOLT MODEL 372

### MATERIALS

- Band
  - Type 304 Stainless Steel per ASTM A240
  - Band Thickness: 19 gauge
- Finger
  - Type 304 Stainless Steel per ASTM A240
  - Finger Thickness: 10 gauge
- Lug Bar
  - Type 304 Stainless Steel per ASTM A240
  - Lug Bar Thickness: 10 gauge
- Keeper Bar
  - Type 304 Stainless Steel per ASTM A240
  - Keeper Bar Thickness: 14 gauge
  - Solution annealed for increased corrosion resistance and strength
  - Helps pull clamp around the pipe and closes the clamp during installation
- Gasket
  - Nitrile (Buna-N) per ASTM D2000
  - Compounded to resist water, oil, natural gas, acids, alkalies, most (aliphatic) hydrocarbon fluids, and many other chemicals
  - Temperature range: -20°F to +180°F
  - Outlet gasket mated into recess of band
- Outlet
  - Type 304 Stainless Steel per ASTM A276
- Stud
  - Type 304 Stainless Steel per ASTM A276
  - Epoxy coated threads to prevent galling
  - 5/8"-11UNC x 7.00" long, Stud welded to Lug Bar; Rolled threads
- Nut
  - Type 304 Stainless Steel GR. 8 per ASTM A194
  - Fluoropolymer coated
  - 5/8"-11UNC, Heavy Hex Semi-Finished
- Washer
  - Type 304 Stainless Steel per ASTM A240
  - 5/8" Type A Plain
- Welding
  - Welds accomplished using qualified welders
  - GMAW and GTAW weld processes utilized



## SPECIFICATION SERVICE SADDLE ALL STAINLESS DOUBLE BOLT MODEL 372

### a xylem brand

### LISTINGS/STANDARDS

- Meets applicable portions of AWWA C230
- Certified to NSF/ANSI 61 and NSF/ANSI 372

#### OPTIONS

- Type 316 Stainless Steel band
- Type 316 Stainless Steel hardware with fluoropolymer coated nuts to prevent galling
- Alternative gasket material (e.g. Viton, EPDM, etc.)
- Spring washers for use of clamp on HDPE pipe

#### NOTES

- Spring washers are required when this product is used on DR17 or thicker HDPE pipe
- Xylem, Smith-Blair, SB stylized are registered trademarks of Xylem, Inc., or one of its subsidiaries.
- These product specifications were correct at the time of publication and are subject to change without notice.
- See the Smith-Blair website for part numbers and ordering information
- See the Smith-Blair website for warranty information
- See the Smith-Blair website for corrosion notice

4 - 16	PIPE SIZE	AND TA NOT A NOM	NOTES:	1.67 T/
	QUANTITY	AP SIZE COMB VAILABLE. NINAL CLAMP KEEPER		57 TYP
6.00	SIZE	BINATIONS SHOWN O		
N	QUANTITY	AS SOME O		
5/8" X 7.00"	STUD SIZE	AND TAP SIZE COMBINATIONS AS SOME COMBINATIONS ARE NOT AVAILABLE. 2. 4" NOMINAL CLAMP SHOWN OTHER SIZES SIMILAR. NOM. KEEPER BAR HARDWARE		1.91 TYP
5/8"	WASHER SIZE			
1-1/16"	SIZE	SOCKET		
1-1/2" 2"	1-1/4"	SIZE 1/2" 5/8"		
12 14	10 8	TAP CHART   03 04   06 07		
- 13	11	04 07 07		
5 <u>3</u>	54 54			
	SMITH-BLAIR, Inc.		TOLERANCES U.N.O. XX= ±.03 FRACTIONS= POSS FRACTIONS= DOTSCALE DWG.	SWITH-BLAIR
SPEC_372.DRW DWG. NO.	P/N N/A			
1 OF 1 SHEET REV.		6/22/15 EBOLT		