



SUBMITTAL INFORMATION

70 Series Coppersetter - (VBHC74-xxW-MM-44-NL style)



ANGLE BALL VALVE BY ANGLE CARTRIDGE DUAL CHECK VALVE (1" METER)

MALE IRON PIPE INLET BY MALE IRON PIPE OUTLET



Coppersetter Part Number

HEIGHT (INCHES)	APPROX. WT. LBS.	CATALOG NUMBER	✓ SUBMITTED ITEM(S)
15	11.0	VBHC74-15W-MM-44-NL	
18	11.3	VBHC74-18W-MM-44-NL	
21	11.6	VBHC74-21W-MM-44-NL	
24	13.2	VBHC74-24W-MM-44-NL	
27	13.5	VBHC74-27W-MM-44-NL	
30	13.8	VBHC74-30W-MM-44-NL	
33	14.1	VBHC74-33W-MM-44-NL	
36	14.4	VBHC74-36W-MM-44-NL	
39	14.7	VBHC74-39W-MM-44-NL	
42	15.0	VBHC74-42W-MM-44-NL	

Service Line Size

INLET	OUTLET
1" Male Iron Pipe	1" Male Iron Pipe

FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (UNS NO C89833)
- The product has the letters "NL" cast into the main body for proper identification
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B-62 and ASTM B-584, UNS NO C83600 - 85-5-5-5)
- Saddle Nuts hold the meter in place for tightening
- Bracing Eye is standard on all 70 Series Coppersetters
- Tie Bar is standard for 24" and taller Coppersetter heights (VBHC74 Series)
- Inlet and Outlet Service Line is Integral Male Iron Pipe Thread
- 1-1/8" O.D. Copper Risers provide more flow capacity
- All Ford Setters are assembled with lead-free solder
- Copper conforms to ASTM B-88, Copper Alloy #122
- ASSE 1024 approved Dual Check Valve

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443

Phone: 260-563-3171 / Fax: 800-826-3487

Overseas Fax: 260-563-0167

<http://www.fordmeterbox.com>

03/13/13

Submitted By: