



General Product Specification

Item No.	GPS348-10
-----------------	-----------

Date	6/12/2016
-------------	-----------

No. Pages	1
------------------	---

Product Description:

Style	Socks
Item Size (each)	3" x 4'
Color	Gray
Composition	100% Polypropylene
Structure	Spunbond outer sleeve filled with meltblown polypropylene chopped material
Technology	Meltblown
Absorbency	Universal (Hydrophilic)
Bonding	N/A

Intended Application	Universal (Hydrophilic) absorbent
-----------------------------	-----------------------------------

Absorbency Capacity	8.6 gallons per bale
----------------------------	----------------------

Packaging Description:

Packaging Configuration	case
Items Per Package	10 Socks/case
Container Type	box

Package Weight	10.0 lbs

Physical Properties:

Parameter	MBT Test Method	Units	Nominal	(+/-) Tolerance
Basis Weight	MBTTM001	LBS	10.0	2
Absorbency** (med Oil)	MBTTM012	GAL	8.6	4
3" Tensile Strength	MBTTM02	LBS	N/A	N/A
Color	N/A			

The above properties are “nominal” values used for process control when the product is produced and/or inspected. Performance “nominals” may vary depending upon the specific application, and/or environment being applied, stored, or shipped.

** The “Absorbency” spec and “MBTTM012” test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.

Attributes	Product will be free of foreign material contamination, rips, holes and tears.
Labeling	
Certification	Make no changes in basic process or composition without notifying customer.