


Slips & Drives



Standard Connectors For Rectangular Duct

Ridged and Leak-proof


- Standing S, Hemmed S, Drive Slip, and Standing Drive Slip
- Available in a variety of metals
- Available in a variety of gauges
- Hemmed S and Drive Slip available cut to length

Slips & Drives

Standard Connectors For Rectangular Duct

BASIC USE

These are the gold standard in the industry when it comes to rectangular ducts requiring a rigid, leak-proof connection.



* Reinforcing bar not included

DESCRIPTION

Ductmate offers Standing S and Standing Drive Cleat in a variety of metals and gauges. Our slips and drives are also available cut-to-length.

Slip & Drive System Part No. Key

Connector Type	Standing S Height	Alloy		Gauge
<ul style="list-style-type: none"> SS = Standing S HS = Hemmed S DS = Drive Slip SDS = Standing Drive Slip 	<ul style="list-style-type: none"> 1 = 1" .5 = 1/2" 1.625 = 1 1/2" 	<ul style="list-style-type: none"> GA = Galvanized GN = Galvannealed AZ = Aluminized AL = Aluminum 	<ul style="list-style-type: none"> S4 = 304 Stainless S6 = 316 Stainless PVC = PVC Coated BI = Black Iron 	<ul style="list-style-type: none"> 20 = 20 GA 22 = 22 GA 24 = 24 GA 26 = 26 GA 28 = 28 GA

Note: May not be available in all alloys

Packaging: 10' Lengths/100' Bundles

Hemmed S Slip, Drive Slip and 1/2" Standing S are also available in 5' lengths. Additional lead time and charges will be applied to all cut to length orders.

Weights Listed In Lbs/Ft

Gauges	1/2" Standing S	1" Standing S	1 1/2" Standing S	Hemmed S	Drive-Slip	Standing Drive Slip	Color Code
20 Ga.	N/A	0.78	0.79*	N/A	N/A	N/A	Yellow
22 Ga.	N/A	0.58	0.68*	N/A	N/A	0.46	Green
24 Ga.	0.41	0.55*	N/A	0.32*	0.19*	0.40	Orange
26 Ga.	0.35*	0.44	N/A	0.25*	0.15*	0.33	Blue
28 Ga.	N/A	N/A	N/A	0.23	0.12	N/A	Red

* Most popular gauges per connector

Note: N/A designates gauges not available

Cut to length Slips and Drives 24 and 26 Gauge

(100 Pieces Per Carton)


Hemmed Slip – 6" through 24" in 2" increments
(can be manufactured in 1" increments upon request)

Drive Slip – 6" through 26" in 2" increments
(can be manufactured in 1" increments upon request)


Straight end
(Hemmed S)



Straight end with 45° bevel
(Drive slip only)



Tabbed end with 45° bevel
(Drive slip only)



LIMITED PRODUCT WARRANTY

Ductmate warrants that Slips and Drives, when properly installed and maintained, will be free from defects in material and workmanship, and will comply with all written specifications made by Ductmate at the time of sale. Ductmate's warranty shall run for a period of one year from the date of manufacture.

Warranty Limitation

The warranty stated above is in lieu of all other warranties, express or implied, including but not limited to the implied warranties of MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Although Ductmate may have suggested the product, or provided written or oral advice to the Purchaser, it is the Purchaser's responsibility to test and determine the suitability of Slips and Drives, for the intended use and purpose, and Purchaser and/or its customer assumes all risk and liability whatsoever regarding such suitability.

Limitation of Liability

In the event of a breach of the above warranty, Ductmate's sole obligation, and Purchaser's sole and exclusive remedy, shall be, at Ductmate's option, repair or replacement of any defective products, or refund of an applicable portion of the purchase price. Ductmate shall have no liability for costs of removal or reinstallation of the product. The Purchaser agrees that no other remedy, including but not limited to loss of profits, loss sales, injury to person or property, or any other special, incidental or consequential damages, shall be available to the Purchaser for any claim arising out of this Agreement, regardless of whether such claim is made in contract or in tort, including strict liability in tort. In no event will Ductmate be obligated to pay damages to the Purchaser in any amount exceeding the purchase price that the Purchaser paid to Ductmate for the allegedly defective product.



Charleroi, PA

210 Fifth Street
Charleroi, PA 15022
800-245-3188
724-258-0500
FAX: 724-258-5494

Lodi, CA

810 S. Cluff Avenue
Lodi, CA 95240-9141
800-344-3270
209-333-4680
FAX: 209-333-4678

www.ductmate.com



This spec data is printed on paper that meets the Certified Fiber Sourcing requirements of the SFI program and contains 10% recycled content

Distributed By:



Ductmate is a proud member of the following organizations:

© Copyright Ductmate Industries, Inc. All rights reserved.

680 - 03/13