



UPS 43-100 F/SF



TM04 5464 4412

UPS 43-100 F/SF



TM04 6015 4709

Flow range:	0-65 gpm (0 - 14.8 m ³ /h)
Head range:	0-31 ft (0 - 9.5 m)
Motor:	2-pole, single-phase
Max. liquid temperature:	230 °F (110 °C)
Min. liquid temperature:	36 °F (2 °C)
Max. system pressure:	145 psi (10 bar)

Model	Speed	Volts	Amps	Watts	Hp	Capacitor
UPS 43-100 F/ SF	III	115	3.5	370	1/2	40 μF / 180 V
	II		3.1	335	1/2	40 μF / 180 V
	I		2.5	265	1/2	40 μF / 180 V
	III	208	1.7	350	1/2	10 μF / 400 V
	II		1.5	310	1/2	10 μF / 400 V
	I		1.2	250	1/2	10 μF / 400 V
	III	230	1.7	370	1/2	10 μF / 400 V
	II		1.5	335	1/2	10 μF / 400 V
	I		1.2	265	1/2	10 μF / 400 V

Approvals

UPS 43-100 F/SF

UPS 43-100 SF



Drinking Water System Components
In Accordance with NSF/ANSI 372

Model	Product number		Dimensions [inches (mm)]						Connection type and size	Shipping weight [lbs (kg)]
	115 V	208-230 V	A	B	C	D	E	F		
UPS 43-100 F	95906636	95906637	8.50 (216)	6.69 (170)	5.13 (130)	4.75 (121)	3.19 (81)	3.44 (87)	GF 40/43 flange (2) 1/2" dia. bolt holes	18.47 (8.4)
UPS 43-100 SF	95906638	95906639	8.50 (216)	6.69 (170)	5.13 (130)	4.75 (121)	3.19 (81)	3.44 (87)	GF 40/43 flange (2) 1/2" dia. bolt holes	18.47 (8.4)

Note: Dimensions in inches unless otherwise stated.