

## MM15TF/S

### FEATURES

- Integrated design, slim 15" width pairs well with other Wolf modules
- High-output 22,000 Btu burner sculpts its flame for perfect stir frying
- Automatic re-ignition system
- Innovative "two in one" grate for standard or wok cooking
- Seamless burner pan for easy clean-up
- Illuminated control panel
- Rigorously tested in our U.S. manufacturing facilities for decades of use
- Exceptional 24/7 support from our Customer Care team in Madison

### ACCESSORIES

- Filler Strip
- Filler Strip for Downdraft


Accessories available through an authorized Sub-Zero dealer.  
For local dealer information, visit [subzero-wolf.com/locator](http://subzero-wolf.com/locator).



**PRODUCT SPECIFICATIONS**


Model	MM15TF/S
Dimensions	15"W x 5"H x 21"D
Weight	30 lbs
Electrical Supply	120 VAC, 60 Hz
Electrical Service	15 amp dedicated circuit
Gas Supply	3/4" ID line
Gas Inlet	1/2" NPT male
Power Cord Length	6 Feet
Receptacle	3-prong grounding-type

**DIMENSIONS**




**ELECTRICAL**

**GAS**




**NOTE:** Dimensions in parenthesis are in millimeters unless otherwise specified


**STANDARD INSTALLATION**



COUNTERTOP CUT-OUT



SIDE VIEW



FRONT VIEW

**NOTE:** Shaded area above countertop indicates minimum clearance to combustible surfaces, combustible materials cannot be located within this area.