☐ HTVZDBLPV-WF (Platinum Vinyl, Less Refrigeration)

Versatile Bi-Level HTVZ Water Cooler Filtered, Pushbar Activated Models HTVZ8BLPV-WF, HTVZ8BLSS-WF and HTVZDBLPV-WF and HTVZDBLSS-WF

These units are replacing past models: HTV8BL-WF-Q-TTG HTV8BL WF-Q-TTG HTVBL-L/R-WF-TTG ☐ HTVZDBLSS-WF (Stainless Steel, Less Refrigeration) HTVBL-L/R-WF-TTG

Filtered Bi-Level Barrier-Free Cooler

GENERAL SPECIFICATIONS

☐ HTVZ8BLPV-WF (Platinum Vinyl)

☐ HTVZ8BLSS-WF (Stainless Steel)

MODELS:

Self-contained, electric refrigerated wall-mounted filtered water cooler easily accessible to physically challenged individuals. HTVZ8BL delivers 8 gph of 50°F drinking water at 90°F ambient air and 80°F inlet water. Model HTVZDBL delivers non-refrigerated drinking water. Shall include the WaterSentry® VII 1500-gallon capacity filter, certified to NSF/ANSI 42 and 53. Exclusive one-piece, Chrome-plated two-stream Double Bubbler™ with non-removable anti-squirt feature and integral hood. Automatic stream height regulator is located inside unit to prevent tampering. Includes self-closing, light touch front and side pushbar actuation with raised letters for the visually impaired. Type 300 series stainless steel cooler top, with satin finish resists stains. Contoured to insure proper drainage. The manufacturer shall certify the unit to meet the requirements of NSF/ANSI 61 and 372, UL 399 and CAN/CSA 22.2 No. 120.

STANDARD FEATURES

- Easy-Touch pushbar activation
- WaterSentry® VII 1500-gallon capacity Filtration System, certified to NSF/ANSI 42 & 53 (Lead, Class 1 Particulate, Chlorine, Taste & Odor)
- Extra deep basin minimizes splashing; with integral drain
- Exclusive one-piece, Chrome-plated two-stream Double Bubbler™ with non-removable anti-squirt feature and integral hood. It's integral hood insures a satisfying drink of water
- Valve with built-in flow regulator to provide constant stream from 20 to 105 psi water pressure
- *Versatile cooler design allows units to be installed either left-hand high and right-hand low or left-low and right high
- Finish options: Impact-resistant vinyl coating or stainless steel wrapper
- Rated for Indoor use

WATER INLET - 3/8" O.D. Tubing. DRAIN OUTLET - 1-1/2" tube outlet for 1-1/2" slip joint connection. Trap and service stop not included.

COOLING SYSTEM (Models HTVZ8BLPV-WF & HTVZ8BLSS-WF only)

- Compressor: Hermetically-sealed, reciprocating type, single phase. Sealed-in lifetime lubrication.
- Condenser: Fan cooled, copper tube with aluminum fins. Fan motor is permanently lubricated.
- Cooling Unit: Combination tube-tank type. Self-cleaning. Continuous copper tubing with stainless steel tank. Fully insulated with EPS foam that meets UL requirements for self-extinguishing material. EPS foam that meets UL requirements for self-extinguishing material.
- Refrigerant Control: Refrigerant R134a is controlled by accurately calibrated capillary tube.
- Temperature Control: Easily accessible enclosed adjustable thermostat is factory preset. Requires no adjustment other than for altitude requirements.





CONSTRUCTION

- · Stainless Steel basin with integral drain
- Galvanized structural steel cooler chassis provides structural integrity
- Cooler cabinet available as Platinum Vinyl Clad Steel or Stainless Steel (additional cost) construction
- Chrome-plated two-stream Double Bubbler™ with non-removable anti-squirt feature and integral hood.

REPLACEMENT FILTER:

55897C (Single)

WARRANTY

5 year limited warranty on the unit's refrigeration system. Electrical components and water system are warranted for 12 months from date of installation or 18 months from factory shipment, whichever date falls first.

CAPACITIES CHART						B	c UL us	CUSA	
Model	Voltage / Hertz	Chilling** Capacity	F.L. Amps	Rated Watts	Approx. Ship Wt.	ADA Compliant	UL399 and CAN/CSA 22.2 No. 120 Certified	NSF/ANSI 61 and 372 Certified	NSF/ANSI 42 and 53 Certified (Filter only)
HTVZ8BLPV-WF	115V / 60Hz	8.0 GPH	4.0	370	72 lbs.	•	•	•	•
HTVZ8BLSS-WF	115V / 60Hz	8.0 GPH	4.0	370	72 lbs.	•	•	•	•
HTVZDBLPV-WF	115V / 60Hz	_	1.0	120	49 lbs.	•	•	•	•
HTVZDBLSS-WF	115V / 60Hz	_	1.0	120	49 lbs.	•	•	•	•

^{**}Based on 80°F inlet water & 90°F ambient air temp for 50°F chilled drinking water.


NOTE: Continued product improvement makes specification sheets subject to change without notice. Color code of (PV) Platinum Vinyl and (SS) for Stainless Steel cooler wrapper.

Versatile Bi-Level HTVZ Water Cooler Filtered, Pushbar Activated Models HTVZ8BLPV-WF, HTVZ8BLSS-WF and HTVZDBLPV-WF and HTVZDBLSS-WF



Rated for Indoor Use Only

OPERATION OF QUICK CONNECT FITTINGS



PUSHING TUBE IN BEFORE PULLING IT OUT HELPS TO RELEASE TUBE NOTE: A service stop (not included) must be installed at the water inlet line.

NOTE: P-Trap (not supplied) to be installed per local building code.

OPERATING PRESSURES

Supply water 20 - 105 psi maximum. Minimum 40 psi supply line pressure required in special circumstances where both sides of bi-level are in use simultaneously to ensure adequate stream height. Use of water filter in this situation is not recommended.

STANDARD ROUGH-IN FOR LEFT-HAND HIGH SIDE

FRONT VIEW SIDE VIEW 18 3/8" 467mm 19" 483mm 6 3/8" 162mm HANGER BRACKET 9/32" DIA ((12)-2" 5lmm 2" 5lmm 38 I/2" 978mm ORIFICE HEIGHT 7/8" 22mm (ALT. LOCATION) PREFFERED 8 I/16" 205mm 33" 838mm ORIFICE HEIGHT FII TER 34 5/16" 872mm 24 1/2" 622mm D PREFFERED 31 5/16" 796mm RIM 22 |5/|6" 583mm 21 7/8" 556mm HEIGHT 19 7/16" 494mm 17 7/16" 443mm 483mm 13 15/16" 354mm 686mm 12 1/2" 318mm 5 3/4" 146mm ADA REQUIREMENT FINISHED FLOOR

REDUCE HEIGHT BY 3" FOR INSTALLATION OF CHILDREN'S ADA COOLER

LEGEND:

- A = Recommended Water Supply Location. Shut-off valve (not furnished) to accept 3/8" O.D. unplated copper tube. Up to 3" (76mm) maximum out from wall.
- B = Recommended Waste Outlet location. To accommodate 1-1/2" nominal drain. Drain stub 2" (51mm) out from wall.
- C = 1-1/2" Trap (not furnished).
- D = Electrical Supply (3) Wire Recessed Box Duplex Outlet.
- E = Insure proper ventilation by maintaining 6" (152mm) minimum clearance from cabinet louvers to wall.
- F = 7/16" (11mm) Bolt Holes for fastening to wall.
- **New Installations Must Use Ground Fault Circuit Interrupter (GFCI).

Halsey Taylor.

Job Name:	
Model:	Qty
Contact:	
Approval Signature:	
Notes:	


Page 2 Printed in the U.S.A

Versatile Bi-Level HTVZ Water Cooler Filtered, Pushbar Activated Models HTVZ8BLPV-WF, HTVZ8BLSS-WF and HTVZDBLPV-WF and HTVZDBLSS-WF



Rated for Indoor Use Only

OPERATION OF QUICK CONNECT FITTINGS



PUSHING TUBE IN BEFORE PULLING IT OUT HELPS TO RELEASE TUBE NOTE: A service stop (not included) must be installed at the water inlet line.


NOTE: P-Trap (not supplied) to be installed per local building code.

OPERATING PRESSURES

Supply water 20 - 105 psi maximum. Minimum 40 psi supply line pressure required in special circumstances where both sides of bi-level are in use simultaneously to ensure adequate stream height. Use of water filter in this situation is not recommended.

ALTERNATE ROUGH-IN FOR RIGHT-HAND HIGH SIDE

FRONT VIEW SIDE VIEW



REDUCE HEIGHT BY 3" FOR INSTALLATION OF CHILDREN'S ADA COOLER

LEGEND:

- A = Recommended Water Supply Location. Shut-off valve (not furnished) to accept 3/8" O.D. unplated copper tube. Up to 3" (76mm) maximum out from wall.
- B = Recommended Waste Outlet location. To accommodate 1-1/2" nominal drain. Drain stub 2" (51mm) out from wall.
- C = 1-1/2" Trap (not furnished).
- D = Electrical Supply (3) Wire Recessed Box Duplex Outlet.
- E = Insure proper ventilation by maintaining 6" (152mm) minimum clearance from cabinet louvers to wall.
- F = 7/16" (11mm) Bolt Holes for fastening to wall.
- **New Installations Must Use Ground Fault Circuit Interrupter (GFCI).

Halsey Taylor

Job Name:	
Model:	_ Qty
Contact:	
Approval Signature:	
Notes:	

Page 3 Printed in the U.S.A