


4.1

Shaded area indicates change Rev. 5-11


## Features Of All Styles Of Mueller® Bronze Saddles For O.D. Controlled PVC Pipe




- ☐ **Thick Tapping Boss** precision machined for a pressure tight connection that resists pull-out. Generous wrenching surfaces to provide sure grip while installing corporation valve.
- Silicon Bronze Screws for strength and corrosion resistance (also hinge pin on swing hinge style).
- □ Manufactured and Tested in accordance with all applicable parts of ANSI/AWWA C800–NSF 61 Certified.
- □ **Nitrile O-Ring Sealed** glued in place and confined in a groove to resist cold-flow or distortion and provide a pressure tight seal against the main.
- □ **Wide Strap** is specially shaped to fit the contour of the O.D. controlled plastic main and seal dependably without pipe distortion. Double-wide straps on saddles with 1-1/2" or 2" tapped outlets for added stability.

Rev. 8-15 Shaded area indicates change

Mueller® Bronze Service Saddles for cast iron, ductile iron, A-C pipe, & AWWA C900 PVC plastic pipe.





**Straps** – Silicon Bronze are flattened to provide increased gripping surface.304L stainless steel - for additional pipe support.\*

Rolled Strap Threads – for added strength.

Manufactured & Tested – in accordance with all applicable parts of ANSI/AWWA C800 - NSF 61 Certified.

Nitrile O-Ring Gasket – is cemented in place and confined in a retaining groove, for pressure tight seal on the main.

Body Curvature – designed to fit pipe accurately for secure clamping and uniform sealing pressure.





\*Stainless steel strap recommended for saddle used on PVC and AC pipe.

Mueller Ductile Iron Service Saddles for cast iron, ductile iron, steel, A-C pipe, & AWWA C900 PVC plastic pipe.

- Thick Tapping Boss precision machined for a pressure tight connection that resists pull-out.
- Heavy Body provides strength at critical stress points. Constructed of ASTM A536 ductile iron.
- □ **Straps** Forged alloy steel straps are zinc plated and are extra large and flattened to provide increased gripping surface. 304L Stainless steel - for additional pipe support.\*
  - **Nylon 11** fluidized bed applied, 10-12 mil thick coating is standard superior corrosion resistance, non-conductive, and unique capability to flex with saddle as it is tightened to conform to pipe OD.
- □ Rolled Strap Threads for added strength.
- Manufactured & Tested in accordance with all applicable parts of ANSI/AWWA C800 - NSF 61 Certified.
- Nitrile O-Ring Gasket is adhered in place and confined in a retaining groove, for pressure tight seal on the main.
- Body Curvature designed to fit pipe accurately for secure clamping and uniform sealing pressure.





<sup>\*</sup>Stainless steel strap recommended for saddle used on PVC and AC pipe.

# MUELLER® H-13000 & S-13000 SERIES BRONZE SERVICE SADDLES FOR C900 PVC PIPE



4.3

Shaded area indicates change Rev. 5-18

## Mueller® Service Saddles for AWWA C900 PVC pipe

- Outlet tapped with either AWWA taper (C.C.) or AWWA I.P.
   (F.I.P.T.) thread
- ☐ For use on cast iron O.D. PVC pipe made to ANSI/AWWA C900 standard
- □ 3/4" 2" tap sizes
- □ NSF 61 Certified
- □ 200 psi (1380 kPa/13 barg) maximum working pressure







H-13000 Series 2-piece 4"-8" mains; 3/4" to 1" tapping



H-13000 Series 2-piece 4"-8" mains; 1/2" or 2" tapping



H-13000 Series 2-piece 10" & 12" mains; 3/4" to 2" tapping

#### Mueller® Service Saddles for cast iron O.D. PVC pipe

Nominal				Тур	oe Of T	hread In S	ervice Sac	ddle Ou	tlet			
Main	AW	WA Tap	er Thre	ad (C.C.	)	Design	AWW	P.T)	Design			
Size	Catalog		Tapping Size				Catalog	Tapping Size				
	Number	3/4"	1"	1-1/2"	2"		number	3/4"	1"	1-1/2"	2"	
4"	S-13440	Х	Х	-	-		S-13490	Х	Х	-	-	
4"	H-13440	Х	Х	Х	Х		H-13490	Х	Х	Х	Х	
6"	S-13441	Х	Х	-	-		S-13491	Х	Х	-	-	
6"	H-13441	Х	Х	Х	Х		H-13491	Х	Х	Х	Х	
8"	S-13442	Х	Х	-	-	Two-piece	S-13492	Х	Х	-	-	Two-piece
8"	H-13442	Х	Х	Х	Χ		H-13492	Х	Х	Х	Х	
10"	H-13443	Х	Х	Х	Χ	1	H-13493	Х	Х	Х	Χ	
12"	H-13444	Х	Х	Х	Х		H-13494	Х	Х	Х	Х	

Machine	Service Saddle Tap Size								
Iwaciiiie	3/4"	1"	1-1/2"	2"					
E-5™ D-5™	X	X	X	X					
D-5™	X	X	X	X					
TRU-CUT™	X	X	-	-					
MEGA-CUT™	X	X	X	X					
PL-2™	X	Х	-	-					



## MUELLER® H-13000 & S-13000 SERIES BRONZE SERVICE SADDLES FOR IPS PVC PIPE

Rev. 5-11 Shaded area indicates change

## Mueller® Service Saddles for iron pipe size PVC pipe

- Outlet tapped with either AWWA taper (C.C.) or AWWA I.P.
   (F.I.P.T.) thread
- ☐ For use on IPS PVC pipe (O.D. controlled)
- □ 3/4" 2" tap sizes
- NSF 61 Certified
- 200 psi (1380 kPa/13 barg) maximum working pressure



S-13000 Series 2-piece hinged 2" to 8" mains; 3/4" to 1" tapping



H-13000 Series 2-piece 2" to 8" mains; 3/4" to 1" tapping



H-13000 Series 2-piece 4"-8" mains; 1-1/2" or 2" tapping



H-13000 Series 3-piece 10" & 12" mains; 3/4" to 1" tapping

#### Mueller Service Saddles for IPS PVC pipe

	Type Of T	hread In	Servic	e Saddle	Outlet							
Nominal	Al	WWA Ta <sub>l</sub>	per Thre	ead (C.C.)			AWV	Τ)				
Main Size	Catalog		Tappi	ng Size		Design	Catalog	atalog Tapping Size				Design
	Number	3/4"	1"	1-1/2"	2"		Number	3/4"	1"	1-1/2"	2"	
2"	S-13420	Х	Х	-	-		S-13470	Х	Х	-	-	
2"	H-13420	Х	Х	-	-		H-13470	Х	Х	-	-	
2-1/2"	S-13422	Х	Х	-	-		S-13472	Х	Х	-	-	
2-1/2"	H-13422	Х	Х	-	-		H-13472	Х	Х	-	-	1
3"	S-13425	Х	Х	-	-		S-13475	Х	Х	-	-	
3"	H-13425	Х	Х	-	-	T	H-13475	Х	Х	-	-	T
4"	S-13428	Х	Х	-	-	Two piece	S-13478	Х	Х	-	-	Two piece
4"	H-13428	Х	Х	Х	Χ		H-13478	Х	Х	Х	Χ	
6"	S-13431	Х	Х	-	-		S-13481	Х	Х	-	-	
6"	H-13431	Х	Х	Х	Х		H-13481	Х	Х	Х	Χ	
8"	S-13433	Х	Х	-	-		S-13483	Х	Х	-	-	
8"	H-13433	Х	Х	Х	Х	7	H-13483	Х	Х	Х	Х	
10"	H-13434	Х	Х	-	-	Three	H-13484	Х	Х	-	-	Three
12"	H-13435	Х	Х	-	-	piece	H-13485	Х	Х	-	-	piece

Machine	Service Saddle Tap Size								
wachine	3/4"	1"	1-1/2"	2"					
E-5 <sup>TM</sup>	X	X	X	X					
D-5™	X	X	X	X					
TRU-CUT™	X	X	-	-					
MEGA-CUT™	X	X	X	X					
PL-2™	X	X	-	-					

## MUELLER® BR1B SERIES BRONZE SERVICE SADDLES - SINGLE STRAP



4.5

Shaded area indicates change Rev. 9-18

### Mueller® Service Saddles for use on Cast Iron and Ductile Iron pipe

- □ Outlet tapped with either AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- ☐ For use on cast iron or ductile iron pipe
- □ 200 psig (1380 kPa/13.80) maximum working pressure
- □ Available in single strap designs
- □ Brass body
- ☐ Flattened silicon bronze straps
- □ Roll strap threads
- □ O-ring sealed outlet
- □ 1/2" thru 1" tap sizes
- ☐ Meets all applicable parts of ANSI/AWWA C800
- □ NSF 61 Certified



**BR 1 B Series** 

#### Mueller Service Saddles with Bronze Single Strap

Pipe O	.D. Range*		Kind and Size of	Pipe	Bronze S	Single S	traps			
			Cast or	Tap***	Base	Size of Tapping (accomplete catalog				
Inch	mm	A-C	Ductile Iron	Thread	Catainn	1/2"	5/8"	3/4"	1"	
4.74-5.32	120.4-135.1		4"	CC or IP	BR1B0474	050	062	075	100	
6.84-7.45	173.7-189.2	1	6"	CC or IP	BR1B0684	050	062	075	100	
8.99-9.67	228.3-245.6	**	8"	CC or IP	BR1B0899	050	062	075	100	
11.04-12.12	280.4-307.8	1	10"	CC or IP	BR1B1104	050	062	075	100	
13.14-14.58	333.8-370.3	1	12"	CC or IP	BR1B1314	050	062	075	100	

<sup>\*</sup>A-C pipe, classes 150-200 per ASTM C295 and AWWA C400 – actual O.D. of pipe being used must fall within the pipe O.D. range listed in the preceding charts. Centrifugally cast pipe, classes 50-250 per ANSI/AWWA C102/A21.2; ANSI/AWWA C106/A21.6; ANSI/AWWA C108/A21.8, and Federal specification WW-P-421. Ductile iron pipe, classes 50-56 per ANSI/AWWA C151/A21.51; Cast iron O.D. PVC plastic pipe per AWWA C900.

Machine	Service saddle tap size								
Machine	1/2"	5/8"	3/4"	1"					
E-5™ D-5™	X	X	X	X					
	-	-	X	X					
TRU-CUT™	-	-	X	X					
MEGA-CUT™	X	X	X	X					
PL-2	-	-	X	X					

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer, to make certain you select the proper clamp: 1) Determine the O.D. of the pipe at the point of saddle installation; 2) From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter.

\*\*\*CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)



## MUELLER® BR1S SERIES BRONZE **SERVICE SADDLES - SINGLE STRAP**

Rev. 8-15 Shaded area indicates change

#### Mueller® Service Saddles for use on A-C, cast iron, ductile iron, and AWWA C900 PVC plastic pipe

- Outlet tapped with either AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- ☐ For use on A-C pipe, cast iron or ductile iron pipe and C900 PVC pipe
- 200 psig (1380 kPa/13.80 bar) maximum working pressure
- Available in single strap designs
- □ Brass body
- 304L stainless steel straps
- Roll strap threads
- □ O-ring sealed outlet
- □ 1/2" thru 1" tap sizes
- Meets all applicable parts of ANSI/AWWA C800
- NSF 61 Certified



**BR 1 S Series** 

#### Mueller Service Saddles with Stainless Steel Single Strap

Pipe O.D	. Range*	K	ind and Size of P	ipe	Stair	nless Stee	l Single S	Straps			
			Coot on Ductile	T ***	Base			g (add to "Base" to talog number)			
Inch	mm	A-C	Cast or Ductile Iron, C900 PVC	Tap*** Thread	Catalog Number	1/2"	5/8"	3/4"	1"		
4.74-5.32	120.4-135.1		4"	CC or IP	BR1S0474	050	062	075	100		
6.84-7.45	173.7-189.2	1	6"	CC or IP	BR1S0684	050	062	075	100		
8.99-9.67	228.3-245.6	**	8"	CC or IP	BR1S0899	050	062	075	100		
11.04-12.12	280.4-307.8	]	10"	CC or IP	BR1S1104	050	062	075	100		
13.14-14.58	333.8-370.3		12"	CC or IP	BR1S1314	050	062	075	100		

<sup>\*</sup>A-C pipe, classes 150-200 per ASTM C295 and AWWA C400 – actual O.D. of pipe being used must fall within the pipe O.D. range listed in the preceding charts. Centrifugally cast pipe, classes 50-250 per ANSI/AWWA C102/A21.2; ANSI/AWWA C106/A21.6; ANSI/AWWA C108/A21.8, and Federal specification WW-P-421. Ductile iron pipe, classes 50-56 per ANSI/AWWA C151/A21.51; Cast iron O.D. PVC plastic pipe per AWWA C900.

\*\* The outside diameter of A-C pipe varies from manufacturer to manufacturer., to make certain you select the proper clamp: 1) Determine the O.D. of the pipe at the point of

#### These machines may be used with the service saddles illustrated on this page

Machine	Service saddle tap size								
Machine	1/2"	5/8"	3/4"	1"					
E-5™	X	X	X	X					
D-5™	-	-	X	X					
TRU-CUT™	-	-	X	X					
MEGA-CUT™	X	X	X	X					
PL-2	-	-	X	X					

saddle installation; 2) From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter. \*\*\*CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)

## MUELLER® BR2B SERIES BRONZE SERVICE SADDLES - DOUBLE STRAP



4.7

Shaded area indicates change Rev. 9-15

#### Mueller® Service Saddles for use on Cast Iron and Ductile Iron pipe

- Outlet tapped with either AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- ☐ For use on cast iron or ductile iron pipe and cast iron O.D.
- □ 200 psig (1380 kPa/14 barg) maximum working pressure
- Available in double strap designs
- Brass body
- ☐ Flattened silicon bronze straps
- □ Rolled strap threads
- □ O-ring sealed outlet
- □ 3/4" thru 2" tap sizes (1/2" and 5/8" some styles)
- ☐ Meets all applicable parts of ANSI/AWWA C800
- □ NSF 61 Certified



**BR 2 B Series** 

#### **Mueller Service Saddles with Bronze Double Straps**

Pipe O.D. R	ange*		Kind and Size of	f Pipe				Bronze Dou	ble Straps			
					Base	Size of Tapping (add to "Base" to complete catalog numb						er)
Inch	mm	A-C	Cast or Ductile Iron	r Iap^^^ ron Thread Catalog Number	Catalog	1/2"	5/8"	3/4"	1"	1-1/4"	1-1/2"	2"
4.74-5.32	120.4-135.1		4"	CC or IP	BR2B0474	050	062	075	100	-	-	-
4.74-5.10	120.4-129.5		4"	CC or IP	BR2B0474	-	-	-	-	125	150	200
5.10-5.40	129.5-137.1		4"	CC or IP	BR2B0510	-	-	-	-	125	150	200
6.84-7.45	173.7-189.2		6"	CC or IP	BR2B0684	050	062	075	100	125	150	200
8.99-9.67	228.4-245.6		8"	CC or IP	BR2B0899	050	062	075	100	125	150	200
11.04-12.12	280.4-307.8	**	10"	CC or IP	BR2B1104	050	062	075	100	125	150	200
13.14-14.58	333.8-370.3		12"	CC or IP	BR2B1314	050	062	075	100	125	150	200
15.22-16.88	386.6-428.7		14"	CC or IP	BR2B1522	-	-	075	100	-	150	200
17.32-19.19	439.9-487.4		16"	CC or IP	BR2B1732	-	-	075	100	-	150	200
18.00-19.50	457.2-495.3		18"	CC or IP	BR2B1800	-	-	075	100	125	150	200
20.00-21.60	508.0-548.6		20"	CC or IP	BR2B2000	-	-	075	100	125	150	200
24.00-25.80	609.6-655.3		24"	CC or IP	BR2B2400	-	-	075	100	125	150	200

<sup>\*</sup>A-C pipe, classes 150-200 per ASTM C295 and AWWA C400 – actual O.D. of pipe being used must fall within the pipe O.D. range listed in the preceding charts.

Centrifugally cast pipe, classes 50-250 per ANSI/AWWA C102/A21.2; ANSI/AWWA C106/A21.6; ANSI/AWWA C108/A21.8, and Federal specification WW-P-421. Ductile iron pipe, classes 50-56 per ANSI/AWWA C151/A21.51; Cast iron O.D. PVC plastic pipe per AWWA C900.

Machine	Service Saddle Tap Size											
wachine	1/2"	5/8"	3/4"	1"	1-1/4"	1-1/2"	2"					
E-5™	X	X	X	X	X	Х	X					
D-5™	-	-	X	Х	X	Х	X					
TRU-CUT™	-	-	X	Х	-	-	-					
MEGA-CUT™	X	X	Х	Х	X	Х	X					
PL-2™	-	-	X	X	-	-	-					

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer., to make certain you select the proper clamp: 1) Determine the O.D. of the pipe at the point of saddle installation; 2) From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter.

\*\*\*\*CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)



## MUELLER® BR2S & BR2W SERIES BRONZE SERVICE SADDLES - DOUBLE STRAP

Rev. 8-15 Shaded area indicates change

#### Mueller® Service Saddles for use on A-C, cast iron, ductile iron, and AWWA C900 PVC plastic pipe

- Outlet tapped with either AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- For use on A-C pipe, cast iron or ductile iron pipe and cast iron O.D. PVC pipe
- 200 psig (1380 kPa/14 barg) maximum working pressure
- Available in double strap designs
- Brass body
- 304L stainless steel straps
- Rolled strap threads
- O-ring sealed outlet
- 3/4" thru 2" tap sizes (1/2" and 5/8" some styles)
- Meets all applicable parts of ANSI/AWWA C800
- NSF 61 Certified





**BR 2 S Series** 

**BR 2 W Series** 

#### Mueller Service Saddles with Stainless Steel Double Straps

Pipe O.D. Ra	ange*		Kind and Size of	Pipe	Stainless Steel Double Straps							
			Cast or Ductile	Tap***	Base	Si	Size of Tapping (add to "Base" to complete catalog number)					er)
Inch	mm	A-C	Iron, C900 PVC	Thread	Catalog Number 1/2" 5/8"		3/4"	1"	1-1/4"	1-1/2"	2"	
4.74-5.32	120.4-135.1		4"	CC or IP	BR2S0474	050	062	075	100	-	-	-
4.74-5.10	120.4-129.5		4"	CC or IP	BR2S0474	-	-	-	-	125	150	200
5.10-5.40	129.5-137.1		4"	CC or IP	BR2S0510	-	-	-	-	125	150	200
6.84-7.45	173.7-189.2		6"	CC or IP	BR2S0684	050	062	075	100	125	150	200
8.99-9.67	228.4-245.6		8"	CC or IP	BR2S0899	050	062	075	100	125	150	200
11.04-12.12	280.4-307.8	**	10"	CC or IP	BR2S1104	050	062	075	100	125	150	200
13.14-14.58	333.8-370.3		12"	CC or IP	BR2S1314	050	062	075	100	125	150	200
15.22-16.88	386.6-428.7		14"	CC or IP	BR2S1522	-	-	075	100	-	150	200
17.32-19.19	439.9-487.4		16"	CC or IP	BR2S1732	-	-	075	100	-	150	200
18.00-19.50	457.2-495.3	1	18"	CC or IP	BR2W1800	-	-	075	100	125	150	200
20.00-21.60	508.0-548.6		20"	CC or IP	BR2W2000	-	-	075	100	125	150	200
24.00-25.80	609.6-655.3		24"	CC or IP	BR2W2400	-	-	075	100	125	150	200

<sup>\*</sup>A-C pipe, classes 150-200 per ASTM C295 and AWWA C400 – actual O.D. of pipe being used must fall within the pipe O.D. range listed in the preceding charts. Centrifugally cast pipe, classes 50-250 per ANSI/AWWA C102/A21.2; ANSI/AWWA C106/A21.6; ANSI/AWWA C108/A21.8, and Federal specification WW-P-421. Ductile iron pipe, classes 50-56 per ANSI/AWWA C151/A21.51; Cast iron O.D. PVC plastic pipe per AWWA C900.

#### These machines may be used with the service saddles illustrated on this page

Maahina		Service Saddle Tap Size											
Machine	1/2"	5/8"	3/4"	1"	1-1/4"	1-1/2"	2"						
E-5™	X	X	Х	X	Х	X	Х						
D-5™	-	-	Х	X	Х	X	Х						
TRU-CUT™	-	-	Х	X	-	-	-						
MEGA-CUT™	Х	X	Х	X	Х	Х	Х						
PL-2™	-	-	Х	Х	-	-	-						

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer., to make certain you select the proper clamp: 1) Determine the O.D. of the pipe at the point of saddle installation, 2) From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter. \*\*\*CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)

## MUELLER® DR1S SERIES DUCTILE IRON **SERVICE SADDLES - SINGLE STRAP**



Shaded area indicates change Rev. 8-15

#### Nylon Ductile Iron Service Saddles for use on cast iron, ductile iron, AWWA C900 PVC plastic, steel and A-C pipe

- Outlet tapped with AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- Single strap design rated at 250 psig (1725 kPa/17.25 bar) maximum working pressure
- ☐ ASTM A536 ductile iron body
- ☐ Body is Nylon 11 (10 -12 mil)
- □ 304L stainless steel strap
- □ Rolled strap threads
- □ Nitrile O-ring gasket
- □ 1/2" thru 2" tap sizes
- ☐ Meets all applicable parts of ANSI/AWWA C800
- □ NSF 61 Certified



**DR 1 S Series** 

#### Mueller® Service Saddles with Stainless Steel Single Strap

Pipe O.D	Pipe O.D. Range* Kind and Size of Pipe					Single Stainless Steel Strap						
			Std. Steel,	Cast Iron,	Tap***	Base	Size of	Tapping (	add to "Ba	se" to com	olete catalo	g number)
Inch	mm	A-C	IPS PVC	S Ductile Iron	Thread	Catalog Number	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"
2.35-2.50	59.7-63.5		2"	2"*	CC or IP	DR1S0235	050	075	100	-	-	-
2.85-2.91	72.4-73.9		2-1/2"	2-1/2"*	CC or IP	DR1S0285	050	075	100	-	-	-
3.56-4.00	90.5-101.6		3-1/2"	3"	CC or IP	DR1S0356	050	075	100	-	-	-
4.47-5.32	113.5-135.1	**	4"	4"	CC or IP	DR1S0447	050	075	100	125	150	200
6.59-7.37	167.4-187.2		6"	6"	CC or IP	DR1S0659	050	075	100	125	150	200
8.54-9.79	216.9-248.7		8"	8"	CC or IP	DR1S0854	050	075	100	125	150	200
10.64-12.12	270.3-307.8		10"	10"	CC or IP	DR1S1064	050	075	100	-	-	-
12.62-14.38	320.5-365.3		12"	12"	CC or IP	DR1S1262	050	075	100	-	-	-

<sup>\*</sup> Important—-carefully check the range of the saddle with the O.D. of the pipe being used.

#### These machines may be used with the service saddles illustrated on this page

Machine		Service Saddle Tap Size										
	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"						
E-5™	X	X	X	Х	X	X						
D-5™	-	X	X	Х	X	X						
TRU-CUT™	-	X	X	-	-	-						
MEGA-CUT™	X	X	X	X	X	X						
PL-2™	-	X	X	-	-	-						

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer, to make certain you select the proper clamp:

<sup>1)</sup> Determine the O.D. of the pipe at the point of saddle installation;

<sup>2)</sup> From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter.

<sup>\*\*\*</sup>CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)



## MUELLER® DR1A SERIES DUCTILE IRON **SERVICE SADDLES - SINGLE STRAP**

Rev. 4-14 Shaded area indicates change

#### Nylon Ductile Iron Service Saddles for use on cast iron, ductile iron, steel pipe

- Outlet tapped with either AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- Single strap design rated at 250 psig (1725 kPa/17.25 bar) maximum working pressure
- ASTM A536 ductile iron body
- Body is Nylon 11 (10 -12 mil)
- □ Forged alloy steel strap
- □ Rolled strap threads
- □ Nitrile O-ring gasket
- 1/2" thru 2" tap sizes
- Meets all applicable parts of ANSI/AWWA C800
- NSF 61 Certified



**DR 1 A Series** 

#### Mueller® Service Saddles with Single Alloy Strap

Pipe O.D	. Range*	Kind and Size of Pipe				Single Alloy Strap						
						Base	Size of	Tapping (	add to "Ba	se" to com	plete catalo	g number)
Inch	mm	A-C	Std. Steel	Cast Iron, Ductile Iron	Tap*** Thread	Catalog Number	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"
2.35-2.50	59.7-63.5		2"	2"*	CC or IP	DR1A0235	050	075	100	-	-	-
2.85-2.91	72.4-73.9		2-1/2"	2-1/2"*	CC or IP	DR1A0285	050	075	100	-	-	-
3.56-4.00	91.0-101.0		3-1/2"	3"	CC or IP	DR1A0356	050	075	100	-	-	-
4.47-5.32	113.5-135.1	**	4"	4"	CC or IP	DR1A0447	050	075	100	125	150	200
6.59-7.37	167.4-187.2		6"	6"	CC or IP	DR1A0659	050	075	100	125	150	200
8.54-9.79	216.9-248.7		8"	8"	CC or IP	DR1A0854	050	075	100	125	150	200
10.64-12.12	270.3-307.8		10"	10"	CC or IP	DR1A1064	050	075	100	-	-	-
12.62-14.38	320.5-365.3	1	12"	12"	CC or IP	DR1A1262	050	075	100	-	-	-

<sup>\*</sup> Important - carefully check the range of the saddle with the O.D. of the pipe being used.

#### These machines may be used with the service saddles illustrated on this page

M = = l= !	Service Saddle Tap Size										
Machine	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"					
E-5™	Х	X	X	X	X	X					
D-5™	-	X	X	X	X	X					
TRU-CUT™	-	X	X	-	-	-					
MEGA-CUT™	X	X	X	X	X	Х					
PL-2™	-	X	X	-	-	-					

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer, to make certain you select the proper clamp:

<sup>1)</sup> Determine the O.D. of the pipe at the point of saddle installation;

<sup>2)</sup> From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter

<sup>\*\*\*</sup>CC=AWWA Taper, IP=AWWA IP thread (F.I.P.T)

### **MUELLER® DR2A SERIES DUCTILE IRON** SERVICE SADDLES - DOUBLE STRAP



Shaded area indicates change Rev. 4-14

#### Nylon Ductile Iron Service Saddles for use on cast iron, ductile iron, steel pipe

- Outlet tapped with AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- Double strap design rated at 500 psig (3450 kPa/34.50 bar) maximum working pressure
- ☐ ASTM A536 ductile iron body
- Body is Nylon 11 (10 -12 mil)
- Forged alloy steel strap
- Rolled strap threads
- □ Nitrile O-ring gasket
- 1/2" thru 2" tap sizes
- ☐ Meets all applicable parts of ANSI/AWWA C800
- □ NSF 61 Certified



**DR 2 A Series** 

#### Mueller® Service Saddles with Double alloy strap Strap

Pipe O.D	. Range*	Kind and Size of Pipe				Double Steel Alloy Strap						
						Base	Size of	Tapping (	add to "Ba	se" to com	plete catalo	g number)
Inch	mm	A-C	Std. Steel	Cast Iron, Ductile Iron	Tap*** Thread	Catalog Number	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"
2.35-2.50	59.7-63.5		2"	2"*	CC or IP	DR2A0235	050	075	100	-	-	-
3.56-4.00	91.0-101.0		3-1/2"	3"	CC or IP	DR2A0356	050	075	100	-	-	-
4.47-5.32	113.5-135.1		4"	4"	CC or IP	DR2A0447	050	075	100	125	150	200
6.59-7.37	167.4-187.2		6"	6"	CC or IP	DR2A0659	050	075	100	125	150	200
8.54-9.79	216.9-248.7		8"	8"	CC or IP	DR2A0854	050	075	100	125	150	200
10.64-12.12	270.3-307.8	**	10"	10"	CC or IP	DR2A1064	050	075	100	125	150	200
12.62-14.38	320.5-365.3		12"	12"	CC or IP	DR2A1262	050	075	100	125	150	200
17.40-18.80	442.0-477.5		-	16"	CC or IP	DR2A1740	-	07	100	125	150	200
18.00-19.50	457.2-495.3		-	18"	CC or IP	DR2A1800	-	075	100	125	150	200
20.00-21.60	508.0-548.6		-	20"	CC or IP	DR2A2000	-	075	100	125	150	200
24.00-25.80	609.0-655.3		-	24"	CC or IP	DR2A2400	-	075	100	125	150	200

<sup>\*</sup> Important—-carefully check the range of the saddle with the O.D. of the pipe being used.

#### These machines may be used with the service saddles illustrated on this page

Machine	Service Saddle Tap Size											
wachine	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"						
E-5™	X	Х	X	X	Х	X						
D-5™	-	Х	X	X	Х	X						
TRU-CUT™	-	Х	X	-	-	-						
MEGA-CUT™	X	Х	X	X	Х	X						
PL-2™	-	X	X	-	-	-						

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer. To make certain you select the proper clamp:

<sup>1)</sup> Determine the O.D. of the pipe at the point of saddle installation;

<sup>2)</sup> From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter.

<sup>\*\*\*</sup>CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)



## MUELLER® DR2S SERIES DUCTILE IRON **SERVICE SADDLES - DOUBLE STRAP**

Rev. 8-15 Shaded area indicates change

#### Nylon Ductile Iron Service Saddles for use on cast iron, ductile iron AWWA C900 PVC plastic, steel and A-C pipe.

- ☐ Outlet tapped with AWWA taper (C.C.) or AWWA I.P. thread (F.I.P.T.)
- □ Double strap design rated at 500 psig (3450 kPa/34.50 bar) maximum working pressure
- ☐ ASTM A536 ductile iron body
- □ Body is Nylon 11 (10 -12 mil)
- ☐ 304L stainless steel strap
- □ Rolled strap threads
- □ Nitrile O-ring gasket
- □ 1/2" thru 2" tap sizes
- ☐ Meets all applicable parts of ANSI/AWWA C800
- NSF 61 Certified





**DR 2 S Series** 

**DR 2 W Series** 

#### Mueller® Service Saddles with Double stainless steel strap

Pipe O.D	). Range*	Kind and Size of Pipe				Double Stainless Steel Straps						
			Std.				Size of	Tapping (ad	d to "Base '	' to complet	e catalog n	umber)
Inch	mm	A-C	Steel IPS PVC	Cast Iron, Ductile Iron PVC C900	Tap*** Thread	Base Catalog Number	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"
2.35-2.50	59.7-63.5		2"	2"*	CC or IP	DR 2 S 0235	050	075	100	-	-	-
3.56-4.00	91.0-101.0		3-1/2"	3"	CC or IP	DR 2 S 0356	050	075	100	-	-	-
4.47-5.32	113.5-135.1		4"	4"	CC or IP	DR 2 S 0447	050	075	100	125	150	200
6.59-7.37	167.4-187.4		6"	6"	CC or IP	DR 2 S 0659	050	075	100	125	150	200
8.54-9.79	216.9-248.7		8"	8"	CC or IP	DR 2 S 0854	050	075	100	125	150	200
10.64-12.12	270.3-307.8	**	10"	10"	CC or IP	DR 2 S 1064	050	075	100	125	150	200
12.62-14.38	320.5-365.3		12"	12"	CC or IP	DR 2 S 1262	050	075	100	125	150	200
17.40-18.80	442.0-477.5		-	16"	CC or IP	DR 2 S 1740	-	075	100	125	150	200
18.00-19.50	457.2-495.3	1	-	18"	CC or IP	DR 2 W 1800	050	075	100	125	150	200
20.00-21.60	508.0-548.6		-	20"	CC or IP	DR 2 W 2000	050	075	100	125	150	200
24.00-25.80	609-655.3		-	24"	CC or IP	DR 2 W 2400	050	075	100	125	150	200

<sup>\*</sup> Important – carefully check the range of the saddle with the O.D. of the pipe being used.

#### These machines may be used with the service saddles illustrated on this page

Machina		Service Saddle Tap Size											
Machine	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"							
E-5™	X	X	X	X	X	X							
D-5™	-	X	X	X	X	X							
TRU-CUT™	-	X	X	-	-	-							
MEGA-CUT™	X	X	X	X	X	X							
PL-2™	-	X	X	-	-	-							

<sup>\*\*</sup> The outside diameter of A-C pipe varies from manufacturer to manufacturer. To make certain you select the proper clamp:

<sup>1)</sup> Determine the O.D. of the pipe at the point of saddle installation;

<sup>2)</sup> From the pipe O.D. range column of the above chart, choose a saddle that has a pipe O.D. range that includes the determined pipe diameter.

<sup>3)</sup> Ductile Iron Double Stainless Strap Saddles can be specifically sized for IPS PVC or C900.

<sup>\*\*\*</sup>CC=AWWA Taper; IP=AWWA IP thread (F.I.P.T)