



# CATALOG

LIGHT COMMERCIAL PRODUCTS



# Table of Contents

## Packaged Units 5

### Air Conditioners

|                                        |   |
|----------------------------------------|---|
| DSC (3 to 5 Tons – 14 SEER)            | 6 |
| DCC (6 Tons – Up to 15.5 IEER)         | 7 |
| DCC (7½ to 12½ Tons – Up to 13.4 IEER) | 8 |
| DCC (15 to 25 Tons – Up to 12.8 IEER)  | 9 |

### Heat Pumps

|                                        |    |
|----------------------------------------|----|
| DSH (3 to 5 Tons – 14 SEER)            | 10 |
| DCH (6 Tons – Up to 15.0 IEER)         | 11 |
| DCH (7½ to 12½ Tons – Up to 13.0 IEER) | 12 |

### Gas/Electric Units

|                                        |    |
|----------------------------------------|----|
| DSG (3 to 5 Tons – 14 SEER/80% AFUE)   | 13 |
| DCG (6 Tons – Up to 15.5 IEER)         | 14 |
| DCG (7½ to 12½ Tons – Up to 13.4 IEER) | 15 |
| DCG (15 to 25 Tons – Up to 12.6 IEER)  | 16 |

### Single-Phase Units

|                                             |    |
|---------------------------------------------|----|
| DTC/DTH/DTG (3 to 5 Tons – Up to 15.5 SEER) | 17 |
|---------------------------------------------|----|

### Three-Phase Units

|                                             |    |
|---------------------------------------------|----|
| DTC/DTH/DTG (3 to 5 Tons – Up to 15.0 SEER) | 18 |
|---------------------------------------------|----|

### M-Series

|                           |    |
|---------------------------|----|
| DP14CM (14 SEER)          | 19 |
| DP14HM (14 SEER)          | 20 |
| DP14GM (14 SEER/81% AFUE) | 21 |

## Split Systems 23

### Air Conditioners

|                                  |    |
|----------------------------------|----|
| DX13SA (3 to 5 Tons – 13 SEER )  | 24 |
| DX11SA (7½ & 10 Tons – 11.2 EER) | 25 |

### Heat Pumps

|                                |    |
|--------------------------------|----|
| DZ14SA (3 to 5 Tons – 14 SEER) | 26 |
| DZ11SA (7½ & 10 Tons – 11 EER) | 27 |

### Air Handlers

|     |    |
|-----|----|
| DAT | 28 |
|-----|----|

## Accessories 29

|                                                 |    |
|-------------------------------------------------|----|
| DSC / DSH / DSG Packaged Units (3 to 5 Tons)    | 30 |
| DCC / DCH / DCG Packaged Units (6 Tons)         | 32 |
| DCC / DCH / DCG Packaged Units (7½ to 12½ Tons) | 34 |
| DCC / DCG Packaged Units (15 to 25 Tons)        | 36 |
| DTC / DTH / DTG Packaged Unit (3 to 5 Tons)     | 38 |
| Light Commercial Packaged Units (DP14CM/HM/GM)  | 40 |
| Split Systems – Air Conditioners/Heat Pumps     | 42 |
| DSC / DSH (Heat Kit Match-Ups – 3 to 5 Tons)    | 43 |
| DTC / DTH (Heat Kit Match-Ups – 3 to 5 Tons)    | 45 |
| DCC / DCH (Heat Kit Match-Ups – 6 Tons)         | 46 |
| DCC / DCH (Heat Kit Match-Ups – 7½ to 12½)      | 47 |
| DCC (Heat Kit Match-Ups – 15 to 25 Tons)        | 49 |



# Packaged Units



# DSC – Single & Three-Phase Packaged Air Conditioners

## 3 to 5 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DSC Commercial Packaged Air Conditioners feature a high-efficiency scroll compressor, convertible airflow orientation, and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                |                                                                                                                                                                                                              |                                                                                                                                                                                                                                   |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» High-efficiency scroll compressors</li> <li>» Copper tube/aluminum fin coils</li> <li>» 24-volt terminal strip</li> </ul> | <ul style="list-style-type: none"> <li>» High-capacity, steel-cased filter drier</li> <li>» Convertible airflow orientation</li> <li>» Bottom utility entry</li> <li>» AHRI Certified; ETL Listed</li> </ul> | <ul style="list-style-type: none"> <li>» Built-in filter rack with standard 2" filters</li> <li>» Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish</li> <li>» Full perimeter rail; Curb fit</li> </ul> |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model            | Cooling Capacity |       | SEER/<br>EER | Voltage-<br>Phase | Electric<br>Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight<br>(lbs) |
|------------------|------------------|-------|--------------|-------------------|-----------------------|---------------------------------|---------------------------------|----------------------------------|-------|----------------------|
|                  | BTU/h            | CFM   |              |                   |                       | W"                              | D"                              | H"                               |       |                      |
| DSC036***3B***A* | 35,000           | 1,200 | 14.0 / 12.0  | 208/230-3         | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC036***4B***A* | 35,000           | 1,200 | 14.0 / 12.0  | 460-3             | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC036***7B***A* | 35,000           | 1,200 | 14.0 / 12.0  | 575-3             | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC036***1D***A* | 35,000           | 1,200 | 14.0 / 12.0  | 208/230-1         | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC036***3D***A* | 35,000           | 1,200 | 14.0 / 12.0  | 208/230-3         | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC048***3B***A* | 47,000           | 1,600 | 14.0 / 11.8  | 208/230-3         | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC048***4B***A* | 47,000           | 1,600 | 14.0 / 11.8  | 460-3             | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC048***7B***A* | 47,000           | 1,600 | 14.0 / 11.8  | 575-3             | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC048***1D***A* | 47,000           | 1,600 | 14.0 / 12.0  | 208/230-1         | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC048***3D***A* | 47,000           | 1,600 | 14.0 / 12.0  | 208/230-3         | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 590                  |
| DSC060***3B***A* | 58,000           | 1,800 | 14.0 / 11.6  | 208/230-3         | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC060***4B***A* | 58,000           | 1,800 | 14.0 / 11.6  | 460-3             | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC060***7B***A* | 58,000           | 1,800 | 14.0 / 11.6  | 575-3             | 10, 15, 20, 25        | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC060***1D***A* | 58,000           | 1,800 | 14.0 / 11.6  | 208/230-1         | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |
| DSC060***3D***A* | 58,000           | 1,800 | 14.0 / 11.6  | 208/230-3         | 10, 15, 20, 25        | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 595                  |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DCC – Three-Phase Packaged Air Conditioners

6 Tons



The Daikin DCC Commercial Packaged Air Conditioners feature a high-efficiency scroll compressor, convertible airflow orientation, and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                |                                                                                                                                                                                                              |                                                                                                                                                                                                                                   |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» High-efficiency scroll compressors</li> <li>» Copper tube/aluminum fin coils</li> <li>» 24-volt terminal strip</li> </ul> | <ul style="list-style-type: none"> <li>» High-capacity, steel-cased filter drier</li> <li>» Convertible airflow orientation</li> <li>» Bottom utility entry</li> <li>» AHRI Certified; ETL Listed</li> </ul> | <ul style="list-style-type: none"> <li>» Built-in filter rack with standard 2" filters</li> <li>» Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish</li> <li>» Full perimeter rail; Curb fit</li> </ul> |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model          | Cooling Capacity |       | SEER/<br>EER | Voltage-<br>Phase | Electric<br>Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight<br>(lbs) |
|----------------|------------------|-------|--------------|-------------------|-----------------------|---------------------------------|---------------------------------|----------------------------------|-------|----------------------|
|                | BTU/h            | CFM   |              |                   |                       | W"                              | D"                              | H"                               |       |                      |
| DCC072***3V*** | 70,000           | 2,250 | 11.3 / 15.4  | 208/230-3         | 10, 15, 20, 25        | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 665                  |
| DCC072***4V*** | 70,000           | 2,250 | 11.3 / 15.4  | 460-3             | 10, 15, 20, 25        | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 665                  |
| DCC072***7V*** | 70,000           | 2,250 | 11.3 / 15.5  | 575-3             | 10, 15, 20, 25        | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 665                  |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DCC – Three-Phase Packaged Air Conditioners

7½ to 12½ Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DCC Commercial Packaged Air Conditioners feature the chlorine-free refrigerant R-410A. Other features include a high-efficiency scroll compressor and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



## DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                        |                                                                                                                                                                                                                |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» High-efficiency scroll compressor</li> <li>» Copper tube/aluminum fin coils</li> <li>» Contactor with lugs</li> <li>» High-capacity, steel-cased filter drier</li> </ul> | <ul style="list-style-type: none"> <li>» Two-stage cooling</li> <li>» 24-volt terminal strip</li> <li>» Convertible airflow orientation</li> <li>» Easy to service</li> <li>» Built-in filter rack with standard 2" filters</li> </ul> | <ul style="list-style-type: none"> <li>» AHRI Certified; ETL Listed</li> <li>» Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish</li> <li>» Full perimeter rail; Curb fit</li> </ul> |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model          | Cooling Capacity |       | EER/<br>IEER | Voltage-<br>Phase | Electric<br>Heat (kW) | Dimensions                       |                                |                                | dB(A) | Ship Weight<br>(lbs) |
|----------------|------------------|-------|--------------|-------------------|-----------------------|----------------------------------|--------------------------------|--------------------------------|-------|----------------------|
|                | BTU/h            | CFM   |              |                   |                       | W"                               | D"                             | H"                             |       |                      |
| DCC090***3V*** | 88,000           | 3,000 | 11.3 / 13.0  | 208/230-3         | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 82    | 1085                 |
| DCC090***4V*** | 88,000           | 3,000 | 11.3 / 13.0  | 460-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 82    | 1085                 |
| DCC090***7V*** | 88,000           | 3,000 | 11.3 / 13.0  | 575-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 82    | 1085                 |
| DCC102***3V*** | 102,000          | 3,200 | 11.3 / 13.4  | 208/230-3         | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 83    | 1125                 |
| DCC102***4V*** | 102,000          | 3,200 | 11.3 / 13.4  | 460-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 83    | 1125                 |
| DCC102***7V*** | 102,000          | 3,200 | 11.3 / 13.4  | 575-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 83    | 1125                 |
| DCC120***3V*** | 116,000          | 3,500 | 11.3 / 13.0  | 208/230-3         | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 83    | 1125                 |
| DCC120***4V*** | 116,000          | 3,500 | 11.3 / 13.0  | 460-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 83    | 1125                 |
| DCC120***7V*** | 116,000          | 3,500 | 11.3 / 13.0  | 575-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 52 <sup>7</sup> / <sub>8</sub> | 83    | 1125                 |
| DCC150***3V*** | 144,000          | 3,900 | 11.0 / 12.2  | 208/230-3         | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 58 <sup>7</sup> / <sub>8</sub> | 83    | 1250                 |
| DCC150***4V*** | 144,000          | 3,900 | 11.0 / 12.2  | 460-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 58 <sup>7</sup> / <sub>8</sub> | 83    | 1250                 |
| DCC150***7V*** | 144,000          | 3,900 | 11.0 / 12.2  | 575-3             | 16,30,45              | 100 <sup>5</sup> / <sub>16</sub> | 61 <sup>3</sup> / <sub>4</sub> | 58 <sup>7</sup> / <sub>8</sub> | 83    | 1250                 |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DCC – Three-Phase Packaged Air Conditioners

15 to 25 Tons



The Daikin DCC Commercial Packaged Air Conditioners feature the chlorine-free refrigerant R-410A. Other features include a high-efficiency scroll compressor and easy access for servicing. These units are housed in a heavy-gauge, galvanized steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » High-efficiency scroll compressors
- » Copper tube/aluminum fin coils
- » Contactor with lugs
- » High-capacity, steel-cased filter drier
- » High -and low- pressure switches
- » Aluminum micro-channel indoor coil on 25-ton units
- » 24-volt terminal strip
- » Easy to service
- » 25-ton unit contains three outdoor fans
- » Built-in filter rack with standard 2" filters (convertible to 4" filters)
- » AHRI Certified; ETL Listed
- » Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish
- » Full perimeter rail

| Model          | Cooling Capacity |       | EER / IEER  | Voltage-Phase | Electric Heat (kW) | Dimensions |                   |     | dB(A) | Ship Weight (lbs) |
|----------------|------------------|-------|-------------|---------------|--------------------|------------|-------------------|-----|-------|-------------------|
|                | BTU/h            | CFM   |             |               |                    | W"         | D"                | H"  |       |                   |
| DCC180***3V*** | 180,000          | 6,000 | 11.0 / 12.8 | 208-230/3     | 30, 45, 60         | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2080              |
| DCC180***4V*** | 180,000          | 6,000 | 11.0 / 12.8 | 460/3         | 30, 45, 60         | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2080              |
| DCC180***7V*** | 180,000          | 6,000 | 11.0 / 12.8 | 575/3         | 30, 45, 60         | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2080              |
| DCC240***3V*** | 240,000          | 7,000 | 10.0 / 11.5 | 208-230/3     | 30, 45, 60, 75     | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2202              |
| DCC240***4V*** | 240,000          | 7,000 | 10.0 / 11.5 | 460/3         | 30, 45, 60, 75     | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2202              |
| DCC240***7V*** | 240,000          | 7,000 | 10.0 / 11.5 | 575/3         | 30, 45, 60, 75     | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2202              |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

| Model          | Cooling Capacity |       | EER / IEER  | Voltage-Phase | Electric Heat (kW) | Dimensions |                   |                   | dB(A) | Ship Weight (lbs) |
|----------------|------------------|-------|-------------|---------------|--------------------|------------|-------------------|-------------------|-------|-------------------|
|                | BTU/h            | CFM   |             |               |                    | W"         | D"                | H"                |       |                   |
| DCC300***3V*** | 290,000          | 8,200 | 10.2 / 11.8 | 208-230/3     | 30, 45, 60, 75     | 133½       | 88½ <sub>32</sub> | 53¾ <sub>32</sub> | 92    | 2387              |
| DCC300***4V*** | 290,000          | 8,200 | 10.2 / 11.8 | 460/3         | 30, 45, 60, 75     | 133½       | 88½ <sub>32</sub> | 53¾ <sub>32</sub> | 92    | 2387              |
| DCC300***7V*** | 290,000          | 8,200 | 10.2 / 11.8 | 575/3         | 30, 45, 60, 75     | 133½       | 88½ <sub>32</sub> | 53¾ <sub>32</sub> | 92    | 2387              |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DSH – Single & Three-Phase Packaged Heat Pumps

## 3 to 5 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DSH Commercial Packaged Heat Pumps feature the chlorine-free refrigerant R-410A. Other features include high-efficiency scroll compressors and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                   |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» High-efficiency scroll compressor</li> <li>» Copper tube/aluminum fin coils</li> <li>» Contactor with lugs</li> <li>» AHRI Certified; ETL Listed</li> </ul> | <ul style="list-style-type: none"> <li>» High-capacity, steel-cased filter drier</li> <li>» Bottom utility entry</li> <li>» 24-volt terminal strip</li> <li>» Convertible airflow orientation</li> <li>» Easy to service</li> </ul> | <ul style="list-style-type: none"> <li>» Built-in filter rack with standard 2" filters</li> <li>» Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish</li> <li>» Full perimeter rail; Curb fit</li> </ul> |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model            | Nominal Capacities <sup>1</sup> |       |         | SEER/<br>EER | Voltage-<br>Phase | Electric<br>Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight<br>(lbs) |
|------------------|---------------------------------|-------|---------|--------------|-------------------|-----------------------|---------------------------------|---------------------------------|----------------------------------|-------|----------------------|
|                  | Cooling                         | CFM   | Heating |              |                   |                       | W"                              | D"                              | H"                               |       |                      |
| DSH036***3B***A* | 36,000                          | 1,200 | 36,000  | 14 / 12      | 208/230-3         | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 605                  |
| DSH036***4B***A* | 36,000                          | 1,200 | 36,000  | 14 / 12      | 460-3             | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 605                  |
| DSH036***7B***A* | 36,000                          | 1,200 | 36,000  | 14 / 12      | 575-3             | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 605                  |
| DSH036***1D***A* | 36,000                          | 1,200 | 36,000  | 14 / 12      | 208/230-1         | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 605                  |
| DSH036***3D***A* | 36,000                          | 1,200 | 36,000  | 14 / 12      | 208/230-3         | 10, 15                | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 605                  |
| DSH048***3B***A* | 47,000                          | 1,600 | 45,500  | 14 / 12      | 208/230-3         | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 610                  |
| DSH048***4B***A* | 47,000                          | 1,600 | 45,500  | 14 / 12      | 460-3             | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 610                  |
| DSH048***7B***A* | 47,000                          | 1,600 | 45,500  | 14 / 12      | 575-3             | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 610                  |
| DSH048***1D***A* | 47,000                          | 1,600 | 45,000  | 14 / 12      | 208/230-1         | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 610                  |
| DSH048***3D***A* | 47,000                          | 1,600 | 45,000  | 14 / 12      | 208/230-3         | 10, 15, 18            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 610                  |
| DSH060***3B***A* | 60,000                          | 2,000 | 57,000  | 14 / 12      | 208/230-3         | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 675                  |
| DSH060***4B***A* | 60,000                          | 2,000 | 57,000  | 14 / 12      | 460-3             | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 675                  |
| DSH060***7B***A* | 60,000                          | 2,000 | 57,000  | 14 / 12      | 575-3             | 10, 15, 20, 25        | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 675                  |
| DSH060***1D***A* | 60,000                          | 2,000 | 57,000  | 14 / 12      | 208/230-1         | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 675                  |
| DSH060***3D***A* | 60,000                          | 2,000 | 57,000  | 14 / 12      | 208/230-3         | 10, 15, 20            | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 675                  |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DCH – Three-Phase Packaged Heat Pumps

6 Tons



The Daikin DCH Commercial Packaged Heat Pumps feature the chlorine-free refrigerant R-410A. Other features include high-efficiency scroll compressors and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » High-efficiency scroll compressor
- » Copper tube/aluminum fin coils
- » Contactor with lugs
- » AHRI Certified; ETL Listed
- » High-capacity, steel-cased filter drier
- » Bottom utility entry
- » 24-volt terminal strip
- » Convertible airflow orientation
- » Easy to service
- » Built-in filter rack with standard 2" filters
- » Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish
- » Full perimeter rail; Curb fit

| Model          | Nominal Capacities <sup>1</sup> |       |         | EER/<br>IEER | Voltage-<br>Phase | Electric<br>Heat (kW) | Dimensions |         |          | dB(A) | Ship Weight<br>(lbs) |
|----------------|---------------------------------|-------|---------|--------------|-------------------|-----------------------|------------|---------|----------|-------|----------------------|
|                | Cooling                         | CFM   | Heating |              |                   |                       | W"         | D"      | H"       |       |                      |
| DCH072***3V*** | 69,000                          | 2,250 | 69,000  | 11.2 / 15.0  | 208/230-3         | 10, 15, 20, 25        | 74 1/16    | 48 5/16 | 42 13/16 | 78    | 675                  |
| DCH072***4V*** | 69,000                          | 2,250 | 69,000  | 11.2 / 15.0  | 460-3             | 10, 15, 20, 25        | 74 1/16    | 48 5/16 | 42 13/16 | 78    | 675                  |
| DCH072***7V*** | 69,000                          | 2,250 | 69,000  | 11.1 / 15.0  | 575-3             | 10, 15, 20, 25        | 74 1/16    | 48 5/16 | 42 13/16 | 78    | 675                  |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DCH – Three-Phase Packaged Heat Pumps

7½ to 12½ Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DCH Commercial Packaged Heat Pumps feature high-efficiency scroll compressors, two-stage cooling, and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



## DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » High-efficiency scroll compressors
- » Two-stage cooling
- » Copper tube/aluminum fin coils
- » Contactor with lugs
- » High-capacity, steel-cased filter drier
- » 24-volt terminal strip
- » Convertible airflow orientation
- » Easy to service
- » Built-in filter rack with standard 2" filters
- » AHRI Certified; ETL Listed
- » Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish
- » Full perimeter rail; Curb fit

| Model          | Nominal Capacities <sup>1</sup> |       |         | EER/<br>IEER | Voltage-<br>Phase | Electric<br>Heat (kW) | Dimensions |         |         | Sound<br>Level<br>dB(A) | Ship Weight<br>(lbs) |
|----------------|---------------------------------|-------|---------|--------------|-------------------|-----------------------|------------|---------|---------|-------------------------|----------------------|
|                | Cooling                         | CFM   | Heating |              |                   |                       | W"         | D"      | H"      |                         |                      |
| DCH090***3V*** | 90,000                          | 3,000 | 90,000  | 11.5 / 12.8  | 208/230-3         | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1175                 |
| DCH090***4V*** | 90,000                          | 3,000 | 90,000  | 11.5 / 12.8  | 460-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1175                 |
| DCH090***7V*** | 90,000                          | 3,000 | 90,000  | 11.5 / 12.8  | 575-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1175                 |
| DCH102***3V*** | 102,000                         | 3,400 | 102,000 | 11.1 / 13.0  | 208/230-3         | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1310                 |
| DCH102***4V*** | 102,000                         | 3,400 | 102,000 | 11.1 / 13.0  | 460-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1310                 |
| DCH102***7V*** | 102,000                         | 3,400 | 102,000 | 11.1 / 13.0  | 575-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1310                 |
| DCH120***3V*** | 113,000                         | 3,500 | 116,000 | 11.1 / 12.6  | 208/230-3         | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1310                 |
| DCH120***4V*** | 113,000                         | 3,500 | 116,000 | 11.1 / 12.6  | 460-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1310                 |
| DCH120***7V*** | 113,000                         | 3,500 | 116,000 | 11.1 / 12.6  | 575-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 52 7/8" | 83                      | 1310                 |
| DCH150***3V*** | 140,000                         | 5,000 | 142,000 | 10.6 / 11.8  | 208/230-3         | 16,30,45              | 100 5/8"   | 61 3/4" | 58 7/8" | 83                      | 1350                 |
| DCH150***4V*** | 140,000                         | 5,000 | 142,000 | 10.6 / 11.8  | 460-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 58 7/8" | 83                      | 1350                 |
| DCH150***7V*** | 140,000                         | 5,000 | 142,000 | 10.6 / 11.8  | 575-3             | 16,30,45              | 100 5/8"   | 61 3/4" | 58 7/8" | 83                      | 1350                 |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



## DSG – Single & Three-Phase Packaged Gas/Electric

3 to 5 Tons

\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).



The Daikin DSG Commercial Packaged Gas/Electric Units feature the chlorine-free refrigerant R-410A. Other features include our dual-diameter tubular heat exchanger and a high-efficiency scroll compressor. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » Aluminized-steel tubular heat exchanger; stainless-steel heat exchanger optional
- » High-efficiency scroll compressor
- » Copper tube/aluminum fin coils
- » Contactor with lugs
- » High-capacity, steel-cased filter drier
- » 24-volt terminal strip
- » Easy to service and Convertible
- » Built-in filter rack with standard 2" filters
- » Bottom utility entry
- » AHRI Certified; ETL Listed
- » Complies with California Low NO<sub>x</sub> emissions standards
- » Full perimeter rail; Curb fit

| Model            | Nominal Capacities <sup>1</sup> |             |         | SEER/<br>EER | Voltage-<br>Phase | Dimensions                      |                                 |                                  | Sound<br>Level<br>dB(A) | Ship Weight<br>(lbs) |
|------------------|---------------------------------|-------------|---------|--------------|-------------------|---------------------------------|---------------------------------|----------------------------------|-------------------------|----------------------|
|                  | Cooling                         | Cooling CFM | Heating |              |                   | W"                              | D"                              | H"                               |                         |                      |
| DSG0360453B***A* | 35,000                          | 1,200       | 46,000  | 14.0 / 12.0  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 590                  |
| DSG0360454B***A* | 35,000                          | 1,200       | 46,000  | 14.0 / 12.0  | 460-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 590                  |
| DSG0360451D***A* | 36,000                          | 1,250       | 46,000  | 14.0 / 12.0  | 208/230-1         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 590                  |
| DSG0360453D***A* | 36,000                          | 1,250       | 46,000  | 14.0 / 12.0  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 590                  |
| DSG0360903B***A* | 35,000                          | 1,200       | 92,000  | 14.0 / 12.0  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 600                  |
| DSG0360904B***A* | 35,000                          | 1,200       | 92,000  | 14.0 / 12.0  | 460-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 600                  |
| DSG0360907B***A* | 35,000                          | 1,200       | 92,000  | 14.0 / 12.0  | 575-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 600                  |
| DSG0360901D***A* | 36,000                          | 1,250       | 92,000  | 14.0 / 12.0  | 208/230-1         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 600                  |
| DSG0360903D***A* | 36,000                          | 1,250       | 92,000  | 14.0 / 12.0  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 600                  |
| DSG0480903B***A* | 47,000                          | 1,600       | 92,000  | 14.0 / 11.8  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0480904B***A* | 47,000                          | 1,600       | 92,000  | 14.0 / 11.8  | 460-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0480901D***A* | 48,000                          | 1,600       | 92,000  | 14.0 / 12.0  | 208/230-1         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0480903D***A* | 48,000                          | 1,600       | 92,000  | 14.0 / 12.0  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0481153B***A* | 47,000                          | 1,600       | 115,000 | 14.0 / 11.8  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 640                  |
| DSG0481154B***A* | 47,000                          | 1,600       | 115,000 | 14.0 / 11.8  | 460-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 640                  |
| DSG0481157B***A* | 47,000                          | 1,600       | 115,000 | 14.0 / 11.8  | 575-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 640                  |
| DSG0481151D***A* | 48,000                          | 1,600       | 115,000 | 14.0 / 12.0  | 208/230-1         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 640                  |
| DSG0481153D***A* | 48,000                          | 1,600       | 115,000 | 14.0 / 12.0  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 640                  |
| DSG0600903B***A* | 58,000                          | 1,800       | 92,000  | 14.0 / 11.6  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0600904B***A* | 58,000                          | 1,800       | 92,000  | 14.0 / 11.6  | 460-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0600901D***A* | 58,000                          | 1,800       | 92,000  | 14.0 / 11.6  | 208/230-1         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0600903D***A* | 58,000                          | 1,800       | 92,000  | 14.0 / 11.6  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 635                  |
| DSG0601403B***A* | 58,000                          | 1,800       | 138,000 | 14.0 / 11.6  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 645                  |
| DSG0601404B***A* | 58,000                          | 1,800       | 138,000 | 14.0 / 11.6  | 460-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 645                  |
| DSG0601407B***A* | 58,000                          | 1,800       | 138,000 | 14.0 / 11.6  | 575-3             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 645                  |
| DSG0601401D***A* | 58,000                          | 1,800       | 138,000 | 14.0 / 11.6  | 208/230-1         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 645                  |
| DSG0601403D***A* | 58,000                          | 1,800       | 138,000 | 14.0 / 11.6  | 208/230-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>3</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78                      | 645                  |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DCG – Three-Phase Packaged Gas/Electric

## 6 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DCG Commercial Packaged Gas/Electric Units feature the chlorine-free refrigerant R-410A. Other features include our dual-diameter tubular heat exchanger and a high-efficiency scroll compressor. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » Aluminized-steel tubular heat exchanger; stainless-steel heat exchanger optional
- » High-efficiency scroll compressor
- » Copper tube/aluminum fin coils
- » Contactor with lugs
- » High-capacity, steel-cased filter drier
- » 24-volt terminal strip
- » Easy to service and Convertible
- » Built-in filter rack with standard 2" filters
- » Bottom utility entry
- » AHRI Certified; ETL Listed
- » Complies with California Low NOx emissions standards
- » Full perimeter rail; Curb fit

| Model          | Nominal Capacities <sup>1</sup> |             |         | EER/IEER    | Voltage-Phase | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------------|---------|-------------|---------------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | Cooling                         | Cooling CFM | Heating |             |               | W"                              | D"                              | H"                               |       |                   |
| DCG0721403V*** | 69,000                          | 2,250       | 138,000 | 11.2 / 15.5 | 208/230-3     | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 715               |
| DCG0721404V*** | 69,000                          | 2,250       | 138,000 | 11.2 / 15.5 | 460-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 715               |
| DCG0721407V*** | 69,000                          | 2,250       | 138,000 | 11.2 / 15.5 | 575-3         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 715               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DCG – Three-Phase Packaged Gas/Electric

7½ to 12½ Tons



The Daikin DCG Commercial Packaged Gas/Electric Units feature the chlorine-free refrigerant R-410A. Other features include our dual-diameter tubular heat exchanger and a high-efficiency scroll compressor. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » Aluminized-steel tubular heat exchanger; stainless-steel heat exchanger optional
- » High-efficiency scroll compressors
- » Two-stage cooling
- » Copper tube/aluminum fin coils

- » Contactor with lugs
- » High-capacity, steel-cased filter drier
- » 24-volt terminal strip
- » Easy to service and Convertible
- » Built-in filter rack with standard 2" filters

- » AHRI Certified; ETL Listed
- » Complies with California Low NO<sub>x</sub> emissions standards
- » Full perimeter rail; Curb fit

| Model          | Nominal Capacities <sup>1</sup> |       |         | EER/<br>IEER | Voltage-<br>Phase | Dimensions |         |         | dB(A) | Ship Weight<br>(lbs) |
|----------------|---------------------------------|-------|---------|--------------|-------------------|------------|---------|---------|-------|----------------------|
|                | Cooling                         | CFM   | Heating |              |                   | W"         | D"      | H"      |       |                      |
| DCG0902103V*** | 88,000                          | 3,000 | 210,000 | 11.3 / 13.0  | 208/230-3         | 100 5/8"   | 61 3/4" | 52 7/8" | 82    | 1175                 |
| DCG0902104V*** | 88,000                          | 3,000 | 210,000 | 11.3 / 13.0  | 460-3             | 100 5/8"   | 61 3/4" | 52 7/8" | 82    | 1175                 |
| DCG0902107V*** | 88,000                          | 3,000 | 210,000 | 11.3 / 13.0  | 575-3             | 100 5/8"   | 61 3/4" | 52 7/8" | 82    | 1175                 |
| DCG1022103V*** | 102,000                         | 3,200 | 210,000 | 11.3 / 13.4  | 208/230-3         | 100 5/8"   | 61 3/4" | 52 7/8" | 83    | 1215                 |
| DCG1022104V*** | 102,000                         | 3,200 | 210,000 | 11.3 / 13.4  | 460-3             | 100 5/8"   | 61 3/4" | 52 7/8" | 83    | 1215                 |
| DCG1022107V*** | 102,000                         | 3,200 | 210,000 | 11.3 / 13.4  | 575-3             | 100 5/8"   | 61 3/4" | 52 7/8" | 83    | 1215                 |
| DCG1202103V*** | 116,000                         | 3,500 | 210,000 | 11.3 / 12.8  | 208/230-3         | 100 5/8"   | 61 3/4" | 52 7/8" | 83    | 1215                 |
| DCG1202104V*** | 116,000                         | 3,500 | 210,000 | 11.3 / 12.8  | 460-3             | 100 5/8"   | 61 3/4" | 52 7/8" | 83    | 1215                 |
| DCG1202107V*** | 116,000                         | 3,500 | 210,000 | 11.3 / 12.8  | 575-3             | 100 5/8"   | 61 3/4" | 52 7/8" | 83    | 1215                 |
| DCG1502103V*** | 144,000                         | 3,900 | 210,000 | 10.8 / 12.0  | 208/230-3         | 100 5/8"   | 61 3/4" | 58 7/8" | 83    | 1340                 |
| DCG1502104V*** | 144,000                         | 3,900 | 210,000 | 10.8 / 12.0  | 460-3             | 100 5/8"   | 61 3/4" | 58 7/8" | 83    | 1340                 |
| DCG1502107V*** | 144,000                         | 3,900 | 210,000 | 10.8 / 12.0  | 575-3             | 100 5/8"   | 61 3/4" | 58 7/8" | 83    | 1340                 |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DCG – Three-Phase Packaged Gas/Electric

## 15 to 25 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DCG Commercial Packaged Gas/Electric Units feature the chlorine-free refrigerant R-410A. Other features include our innovative tubular heat exchanger and a high-efficiency scroll compressor. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                      |                                                                             |                                                      |
|--------------------------------------|-----------------------------------------------------------------------------|------------------------------------------------------|
| » R-410A chlorine-free refrigerant   | » High-capacity, steel-cased filter drier                                   | » AHRI Certified; ETL Listed                         |
| » Unique tubular heat exchanger      | » Built-in filter rack with standard 2" filters (convertible to 4" filters) | » Easy to service                                    |
| » High-efficiency scroll compressors | » High-and low- pressure switches                                           | » Full perimeter rail                                |
| » Copper tube/aluminum fin coils     |                                                                             | » Aluminum micro-channel indoor coil on 25-ton units |
| » Contactor with lugs                |                                                                             | » 25-ton unit contains three outdoor fans            |
| » 24-volt terminal strip             |                                                                             |                                                      |

| Model          | Nominal Capacities <sup>1</sup> |       |         | EER/IEER    | AFUE | Voltage-Phase | Dimensions |                   |     | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------|---------|-------------|------|---------------|------------|-------------------|-----|-------|-------------------|
|                | Cooling                         | CFM   | Heating |             |      |               | W"         | D"                | H"  |       |                   |
| DCG1803503V*** | 180,000                         | 5,600 | 350,000 | 10.8 / 12.6 | 80%  | 208-230/3     | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2198              |
| DCG1803504V*** | 180,000                         | 5,600 | 350,000 | 10.8 / 12.6 | 80%  | 460/3         | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2198              |
| DCG1803507V*** | 180,000                         | 5,600 | 350,000 | 10.8 / 12.6 | 80%  | 575/3         | 133½       | 88½ <sub>32</sub> | 50¾ | 88    | 2198              |
| DCG2404003V*** | 240,000                         | 7,000 | 400,000 | 9.8 / 11.3  | 80%  | 208-230/3     | 133½       | 88½ <sub>32</sub> | 50¾ | 88.3  | 2357              |
| DCG2404004V*** | 240,000                         | 7,000 | 400,000 | 9.8 / 11.3  | 80%  | 460/3         | 133½       | 88½ <sub>32</sub> | 50¾ | 88.3  | 2357              |
| DCG2404007V*** | 240,000                         | 7,000 | 400,000 | 9.8 / 11.3  | 80%  | 575/3         | 133½       | 88½ <sub>32</sub> | 50¾ | 88.3  | 2357              |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

| Model          | Nominal Capacities <sup>1</sup> |       |         | EER/IEER   | AFUE | Voltage-Phase | Dimensions |                   |                   | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------|---------|------------|------|---------------|------------|-------------------|-------------------|-------|-------------------|
|                | Cooling                         | CFM   | Heating |            |      |               | W"         | D"                | H"                |       |                   |
| DCG3004003V*** | 290,000                         | 8,200 | 400,000 | 9.8 / 11.4 | 80%  | 208-230/3     | 133½       | 88½ <sub>32</sub> | 53¾ <sub>32</sub> | 92.3  | 2523              |
| DCG3004004V*** | 290,000                         | 8,200 | 400,000 | 9.8 / 11.4 | 80%  | 460/3         | 133½       | 88½ <sub>32</sub> | 53¾ <sub>32</sub> | 92.3  | 2523              |
| DCG3004007V*** | 290,000                         | 8,200 | 400,000 | 9.8 / 11.4 | 80%  | 575/3         | 133½       | 88½ <sub>32</sub> | 53¾ <sub>32</sub> | 92.3  | 2523              |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DT Series – Single-Phase Packaged Units

3 to 5 Tons



The Daikin DT High-Efficiency Commercial Packaged Air Conditioners and Heat Pumps feature a high-efficiency scroll compressor, high-capacity steel-cased filter drier, and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » High-efficiency scroll compressor
- » Copper tube/aluminum fin coils
- » Contactor with lugs
- » High-capacity, steel-cased filter drier
- » 24-volt terminal strip
- » Convertible airflow orientation
- » Easy to service
- » Built-in filter rack with standard 2" filters
- » Heat Kits with single-point entry
- » AHRI Certified; ETL Listed
- » Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish
- » Full perimeter rail; Curb fit

### DTC Air Conditioners

| Model          | Cooling Capacity <sup>1</sup> |       | SEER / EER  | Voltage-Phase | Electric Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|-------------------------------|-------|-------------|---------------|--------------------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | BTU/h                         | CFM   |             |               |                    | W"                              | D"                              | H"                               |       |                   |
| DTC036***1D*** | 35,600                        | 1,200 | 15.5 / 13.0 | 208/230-1     | 10, 15             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 525               |
| DTC048***1D*** | 45,500                        | 1,600 | 15.0 / 12.0 | 208/230-1     | 10, 15, 18         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 560               |
| DTC060***1D*** | 59,000                        | 2,000 | 15.0 / 12.0 | 208/230-1     | 10, 15, 20         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 640               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

### DTH Heat Pumps

| Model          | Nominal Capacities <sup>1</sup> |       |         | SEER / EER  | Voltage-Phase | Electric Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------|---------|-------------|---------------|--------------------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | Cooling                         | CFM   | Heating |             |               |                    | W"                              | D"                              | H"                               |       |                   |
| DTH036***1D*** | 35,400                          | 1,200 | 34,800  | 15.0 / 12.0 | 208/230-1     | 10, 15             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 605               |
| DTH048***1D*** | 46,500                          | 1,600 | 44,500  | 15.0 / 12.0 | 208/230-1     | 10, 15, 18         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 610               |
| DTH060***1D*** | 59,500                          | 2,000 | 56,000  | 15.0 / 12.0 | 208/230-1     | 10, 15, 20         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 615               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

### DTG Gas/Electric

| Model          | Nominal Capacities <sup>1</sup> |       |         | SEER / EER  | Voltage-Phase | AFUE | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------|---------|-------------|---------------|------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | Cooling                         | CFM   | Heating |             |               |      | W"                              | D"                              | H"                               |       |                   |
| DTG0360451D*** | 35,600                          | 1,200 | 46,000  | 15.5 / 13.0 | 208/230 - 1   | 81%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 550               |
| DTG0360901D*** | 35,600                          | 1,200 | 92,000  | 15.5 / 13.0 | 208/230 - 1   | 81%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 560               |
| DTG0480901D*** | 45,500                          | 1,600 | 92,000  | 15.0 / 12.0 | 208/230 - 1   | 81%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 600               |
| DTG0481151D*** | 45,500                          | 1,600 | 115,000 | 15.0 / 12.0 | 208/230 - 1   | 81%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 597               |
| DTG0600901D*** | 59,000                          | 2,000 | 92,000  | 15.0 / 12.0 | 208/230 - 1   | 81%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 638               |
| DTG0601401D*** | 59,000                          | 2,000 | 138,000 | 15.0 / 12.0 | 208/230 - 1   | 81%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 655               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DT Series – Three-Phase Packaged Units

## 3 to 5 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DT High-Efficiency Commercial Packaged Air Conditioners and Heat Pumps feature a high-efficiency scroll compressor, high-capacity steel-cased filter drier, and easy access for servicing. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» High-efficiency scroll compressor</li> <li>» Copper tube/aluminum fin coils</li> <li>» Contactor with lugs</li> <li>» High-capacity, steel-cased filter drier</li> </ul> | <ul style="list-style-type: none"> <li>» 24-volt terminal strip</li> <li>» Convertible airflow orientation</li> <li>» Easy to service</li> <li>» Built-in filter rack with standard 2" filters</li> <li>» Heat Kits with single-point entry</li> </ul> | <ul style="list-style-type: none"> <li>» AHRI Certified; ETL Listed</li> <li>» Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish</li> <li>» Full perimeter rail; Curb fit</li> </ul> |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### DTC Air Conditioners

| Model          | Cooling Capacity <sup>1</sup> |       | SEER / EER  | Voltage-Phase | Electric Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|-------------------------------|-------|-------------|---------------|--------------------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | BTU/h                         | CFM   |             |               |                    | W"                              | D"                              | H"                               |       |                   |
| DTC036***3D*** | 36,000                        | 1,200 | 15.0 / 13.0 | 208/230 - 3   | 10, 15             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 529               |
| DTC048***3D*** | 47,000                        | 1,600 | 15.0 / 12.5 | 208/230 - 3   | 10, 15, 18         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 563               |
| DTC060***3D*** | 60,000                        | 2,000 | 15.0 / 12.5 | 208/230 - 3   | 10, 15, 20         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 575               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

### DTH Heat Pumps

| Model          | Nominal Capacities <sup>1</sup> |       |         | SEER / EER  | Voltage-Phase | Electric Heat (kW) | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------|---------|-------------|---------------|--------------------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | Cooling                         | CFM   | Heating |             |               |                    | W"                              | D"                              | H"                               |       |                   |
| DTH036***3D*** | 35,000                          | 1,200 | 32,800  | 15.0 / 13.0 | 208/230 - 3   | 10, 15             | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 548               |
| DTH048***3D*** | 47,000                          | 1,600 | 44,000  | 15.0 / 12.5 | 208/230 - 3   | 10, 15, 18         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 577               |
| DTH060***3D*** | 60,000                          | 2,000 | 55,000  | 15.0 / 12.5 | 208/230 - 3   | 10, 15, 20         | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 612               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

### DTG Gas/Electric

| Model          | Nominal Capacities <sup>1</sup> |       |         | SEER / EER  | Voltage-Phase | AFUE | Dimensions                      |                                 |                                  | dB(A) | Ship Weight (lbs) |
|----------------|---------------------------------|-------|---------|-------------|---------------|------|---------------------------------|---------------------------------|----------------------------------|-------|-------------------|
|                | Cooling                         | CFM   | Heating |             |               |      | W"                              | D"                              | H"                               |       |                   |
| DTG0360453D*** | 36,000                          | 1,200 | 46,000  | 15.0 / 13.0 | 208/230 - 3   | 80%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 553               |
| DTG0360903D*** | 36,000                          | 1,200 | 92,000  | 15.0 / 13.0 | 208/230 - 3   | 80%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 564               |
| DTG0480903D*** | 47,000                          | 1,600 | 92,000  | 15.0 / 12.5 | 208/230 - 3   | 80%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 599               |
| DTG0481153D*** | 47,000                          | 1,600 | 115,000 | 15.0 / 12.5 | 208/230 - 3   | 80%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 38 <sup>13</sup> / <sub>16</sub> | 78    | 597               |
| DTG0600903D*** | 60,000                          | 2,000 | 92,000  | 15.0 / 12.5 | 208/230 - 3   | 80%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 638               |
| DTG0601403D*** | 60,000                          | 2,000 | 138,000 | 15.0 / 12.5 | 208/230 - 3   | 80%  | 74 <sup>1</sup> / <sub>16</sub> | 48 <sup>5</sup> / <sub>16</sub> | 42 <sup>13</sup> / <sub>16</sub> | 78    | 655               |

<sup>1</sup> BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DP14CM – Three-Phase Packaged Air Conditioners

3 to 5 Tons



The Daikin DP14CM Commercial Packaged Air Conditioner provides energy-efficient cooling and cooling performance in one self-contained unit. This unit uses the chlorine-free refrigerant R-410A. The DP13CM is housed in a heavy-gauge, galvanized-steel cabinet that offers a high-quality, UV-resistant powder-paint finish and allows for a ground-level or rooftop mount.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » Energy-efficient compressor with internal relief valve
- » Fully charged R-410A system
- » EEM blower motor; PSC blower motor on 3-ton units
- » Copper tube/aluminum fin coils
- » Totally enclosed, permanently lubricated condenser fan motor
- » Electric heat kit available as a field-installed option
- » Convertible airflow — horizontal or downflow
- » Louvered condenser coil protection
- » Heavy-gauge galvanized-steel cabinet with attractive nickel gray powder-paint finish
- » Fully insulated air-handling compartment with convenient access panels

| Model        | Nominal Ratings      |       | SEER/<br>EER | Voltage-<br>Phase | Dimensions |    |     | dB(A) | Ship Weight<br>(lbs) |
|--------------|----------------------|-------|--------------|-------------------|------------|----|-----|-------|----------------------|
|              | Cooling <sup>1</sup> | CFM   |              |                   | W"         | D" | H"  |       |                      |
| DP14CM3643A* | 35,000               | 1,200 | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 34¾ | 80.1  | 365                  |
| DP14CM4843A* | 45,500               | 1,600 | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 81.7  | 435                  |
| DP14CM6043A* | 56,000               | 1,700 | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 80.2  | 458                  |

<sup>1</sup>Tons | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DP14HM – Three-Phase Packaged Heat Pumps

## 3 to 5 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DP14HM Commercial Packaged Heat Pump provides energy-efficient cooling and heating performance in one self-contained unit. This unit uses the chlorine-free refrigerant R-410A. This unit is housed in a heavy-gauge, galvanized-steel cabinet that offers a high-quality, UV-resistant powder-paint finish and allows for a ground-level or rooftop mount.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » Energy-efficient compressor with internal relief valve
- » Fully charged with R-410A chlorine-free refrigerant
- » EEM blower motor
- » Copper tube/aluminum fin coil
- » Convertible airflow — horizontal or downflow
- » Totally enclosed, permanently lubricated condenser fan motor
- » Electric heat kit available as a field-installed accessory
- » Heavy-gauge galvanized-steel cabinet
- » Attractive nickel gray powder-paint finish
- » Fully insulated blower compartment with convenient access panels
- » Louvered condenser coil protection
- » One footprint; two heights

| Model        | Nominal Capacities   |       |                      | SEER/<br>EER | Voltage-<br>Phase | Dimensions |    |     | dB(A) | Ship Weight<br>(lbs) |
|--------------|----------------------|-------|----------------------|--------------|-------------------|------------|----|-----|-------|----------------------|
|              | Cooling <sup>1</sup> | CFM   | Heating <sup>2</sup> |              |                   | W"         | D" | H"  |       |                      |
| DP14HM3643A* | 34,400               | 1,200 | 33,000               | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 34¾ | 81    | 400                  |
| DP14HM4843A* | 48,000               | 1,600 | 45,500               | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 79    | 475                  |
| DP14HM6043A* | 58,000               | 1,850 | 57,000               | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 80    | 495                  |

<sup>1</sup>Tons, <sup>2</sup>BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

## DP14GM – Three-Phase Packaged Gas/Electric

3 to 5 Tons



The Daikin DP14GM Commercial Packaged Gas/Electric Units feature the chlorine-free refrigerant R-410A. Other features include our corrosion-resistant tubular heat exchanger and an energy-efficient scroll compressor. These units are housed in a heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish.

PACKAGED UNITS

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » Energy-efficient compressor with internal relief valve
- » EEM blower motor; PSC blower motor on 3-ton units
- » Durable, corrosion-resistant aluminized-steel tubular heat exchanger
- » Fully charged R-410A system
- » Copper tube/aluminum fin coils
- » Gas valve for natural gas with easy conversion to propane
- » Direct-spark ignition system includes a microprocessor-based control for the entire ignition sequence
- » All blower operation and all safety circuits complete with self-diagnostics
- » All models comply with California Low NO<sub>x</sub> standards
- » ARI Certified; ETL Certified
- » Heavy-gauge, galvanized-steel cabinet with UV-resistant powder-paint finish
- » Fully insulated cabinet
- » One roof curb fits all units
- » One footprint; one height
- » Convenient access panels
- » Fits in a standard-size pick-up truck

| Model           | Nominal Capacities   |       |                      | SEER/<br>EER | Voltage-<br>Phase | Dimensions |    |     | dB(A) | Ship Weight<br>(lbs) |
|-----------------|----------------------|-------|----------------------|--------------|-------------------|------------|----|-----|-------|----------------------|
|                 | Cooling <sup>1</sup> | CFM   | Heating <sup>2</sup> |              |                   | W"         | D" | H"  |       |                      |
| DP14GM3608043A* | 35,000               | 1,200 | 80,000               | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 34¾ | 78    | 480                  |
| DP14GM4808043A* | 46,000               | 1,525 | 80,000               | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 80    | 545                  |
| DP14GM6108043A* | 56,500               | 1,750 | 80,000               | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 80    | 555                  |
| DP14GM6112043A* | 56,500               | 1,750 | 120,000              | 14.0 / 11.0  | 208/230-3         | 47         | 51 | 42¾ | 80    | 565                  |

<sup>1</sup>Tons, <sup>2</sup>BTU/h | Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.





# Split Systems & Air Handlers

# DX13SA – 13 SEER Air Conditioners

## 3 to 5 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DX13SA Three-Phase Air Conditioner uses the chlorine-free refrigerant R-410A and features operating sound levels that are among the best in the heating and cooling industry. With its 13 SEER rating, the DX13SA will help reduce energy consumption throughout the life of the system compared to lower SEER-rated equipment.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                |                                                                                                                                                                                                                                          |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» Energy-efficient compressor</li> <li>» Factory-installed filter drier</li> <li>» Copper tube/enhanced aluminum fin coil</li> <li>» Complies with ASHRAE Standard 90.1</li> </ul> | <ul style="list-style-type: none"> <li>» AHRI Certified; ETL Listed</li> <li>» Louvered sound control top design</li> <li>» Steel louver coil guard</li> <li>» Heavy-gauge galvanized-steel cabinet</li> </ul> | <ul style="list-style-type: none"> <li>» Attractive nickel gray powder-paint finish</li> <li>» Top and side maintenance access</li> <li>» Single-panel access to controls with space provided for field-installed accessories</li> </ul> |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model        | Cooling Capacity (BTU/h) | SEER | Voltage-Phase | Dimensions |     |     | Service Valve |          | dB(A) | Ship Weight (lbs) |
|--------------|--------------------------|------|---------------|------------|-----|-----|---------------|----------|-------|-------------------|
|              |                          |      |               | W"         | D"  | H"  | Liquid"       | Suction" |       |                   |
| DX13SA0363** | 36,000                   | 13.0 | 208/230-3     | 29"        | 29  | 28¾ | ⅞             | ¾        | 74    | 196               |
| DX13SA0364** | 36,000                   | 13.0 | 460-3         | 29"        | 29  | 28¾ | ⅞             | ¾        | 74    | 196               |
| DX13SA0483** | 48,000                   | 13.0 | 208/230-3     | 29"        | 29  | 36¼ | ⅞             | ⅞        | 76    | 190               |
| DX13SA0484** | 48,000                   | 13.0 | 460-3         | 29"        | 29  | 36¼ | ⅞             | ⅞        | 76    | 189               |
| DX13SA0603** | 60,000                   | 13.0 | 208/230-3     | 35½        | 35½ | 38¼ | ⅞             | ⅞        | 72    | 301               |
| DX13SA0604** | 60,000                   | 13.0 | 460-3         | 35½        | 35½ | 38¼ | ⅞             | ⅞        | 72    | 301               |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



## DX11SA – 11.2 EER Air Conditioners

7½ & 10 Tons

\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).



The Daikin DX11SA Commercial Air Conditioner cabinet features a powder-paint finish over heavy-gauge galvanized steel that provides premium durability and improved UV protection. Designed for ground-level or rooftop mount, the base pan elevates the unit above the slab to provide excellent water drainage and keep the coil away from debris that can collect inside the unit. The unit's attractive louvered metal guard protects the coil from damage and strengthens the unit.

### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- » R-410A chlorine-free refrigerant
- » Energy-efficient compressor with internal pressure relief valve
- » High-capacity, steel-cased filter drier
- » High-efficiency copper tube/aluminum fin coil High- and low-pressure switches
- » ARI Certified; ETL Listed
- » Louvered sound control top design
- » Steel louver coil guard protects coil from damage and adds strength to the unit
- » Bottom pan rails elevate unit above slab
- » Heavy-gauge galvanized-steel cabinet
- » Attractive nickel gray powder-paint finish

| Model        | Cooling Capacity (BTU/h) | EER / IEER  | Voltage-Phase | Dimensions |     |     | Service Valve |          | dB(A) | Ship Weight (lbs) |
|--------------|--------------------------|-------------|---------------|------------|-----|-----|---------------|----------|-------|-------------------|
|              |                          |             |               | W"         | D"  | H"  | Liquid"       | Suction" |       |                   |
| DX11SA0903** | 88,000                   | 11.2 / 11.5 | 208/230-3     | 35½        | 35½ | 37½ | ⅝             | 1⅜       | 84    | 315               |
| DX11SA0904** | 90,000                   | 11.2 / 11.5 | 460-3         | 35½        | 35½ | 37½ | ⅝             | 1⅜       | 84    | 315               |
| DX11SA1203** | 114,000                  | 11.2 / 11.5 | 208/230-3     | 35½        | 35½ | 41½ | ⅝             | 1⅜       | 84    | 334               |
| DX11SA1204** | 112,000                  | 11.2 / 11.5 | 460-3         | 35½        | 35½ | 41½ | ⅝             | 1⅜       | 84    | 334               |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DZ14SA – 14 SEER Heat Pumps

## 3 to 5 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin Commercial Heat Pump cabinet features a powder-paint finish over heavy-gauge galvanized steel that provides premium durability and improved UV protection. Designed for ground-level or rooftop mount, the base pan elevates the unit above the slab to provide excellent water drainage and keep the coil away from debris that can collect inside the heat pump. The unit's attractive louvered metal guard protects the coil from damage and strengthens the unit.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                                                                                                                                    |                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                        |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» Energy-efficient scroll compressor</li> <li>» Low-pressure switch</li> <li>» Liquid refrigerant return protection</li> <li>» Factory-installed, bi-flow liquid line filter drier</li> <li>» Copper tube/enhanced aluminum fin coil</li> </ul> | <ul style="list-style-type: none"> <li>» Reliable time-initiated, temperature-terminated defrost control</li> <li>» Contactor with lug connection</li> <li>» Ground lug connection</li> <li>» AHRI Certified; ETL Listed</li> <li>» Louvered sound control top design</li> <li>» Steel louver coil guard</li> </ul> | <ul style="list-style-type: none"> <li>» Heavy-gauge galvanized-steel cabinet</li> <li>» Attractive nickel gray powder-paint finish</li> <li>» Top and side maintenance access</li> <li>» Service ports and controls are accessible while unit is operating</li> </ul> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model        | Nominal Capacities (BTU/h) |         | SEER | Voltage-Phase | Dimensions |     |     | Service Valve |          | dB(A) | Ship Weight (lbs) |
|--------------|----------------------------|---------|------|---------------|------------|-----|-----|---------------|----------|-------|-------------------|
|              | Cooling                    | Heating |      |               | W"         | D"  | H"  | Liquid"       | Suction" |       |                   |
| DZ14SA0363** | 34,600                     | 32,800  | 14.0 | 208/230-3     | 29         | 29  | 32¼ | ¾             | 7/8      | 74    | 232               |
| DZ14SA0364** | 34,600                     | 32,800  | 14.0 | 460-3         | 29         | 29  | 32¼ | ¾             | 7/8      | 74    | 231               |
| DZ14SA0483** | 45,000                     | 44,500  | 14.0 | 208/230-3     | 29         | 29  | 34¼ | ¾             | 1½       | 76    | 235               |
| DZ14SA0484** | 45,000                     | 44,500  | 14.0 | 460-3         | 29         | 29  | 34¼ | ¾             | 1½       | 76    | 234               |
| DZ14SA0603** | 56,500                     | 59,000  | 14.0 | 208/230-3     | 35½        | 35½ | 34¼ | ¾             | 1½       | 75    | 262               |
| DZ14SA0604** | 56,500                     | 59,000  | 14.0 | 460-3         | 35½        | 35½ | 34¼ | ¾             | 1½       | 75    | 261               |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.



# DZ11SA – 11 EER Heat Pumps

7½ & 10 Tons

\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).



The Daikin DZ11SA Commercial Heat Pump cabinet features a powder-paint finish over heavy-gauge galvanized steel that provides premium durability and improved UV protection. Designed for ground-level or rooftop mount, the base pan elevates the unit above the slab to provide excellent water drainage and keep the coil away from debris that can collect inside the unit. The unit's attractive louvered metal guard protects the coil from damage and strengthens the unit.

## DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» R-410A chlorine-free refrigerant</li> <li>» Energy-efficient compressor with internal pressure relief valve</li> <li>» High-capacity, steel-cased, bi-flow heat pump filter drier</li> <li>» Discharge line muffler</li> <li>» Liquid refrigerant return protection</li> </ul> | <ul style="list-style-type: none"> <li>» Check flowrate heating mode expansion device</li> <li>» Low-pressure switch</li> <li>» Reliable, time-initiated, temperature-terminated defrost control</li> <li>» Brass liquid and suction line service valves</li> <li>» High-efficiency copper tube/aluminum fin coil</li> </ul> | <ul style="list-style-type: none"> <li>» ARI Certified; ETL Listed</li> <li>» Louvered sound control top design</li> <li>» Heavy-gauge galvanized-steel cabinet</li> <li>» Steel louver coil guard protects coil from damage and adds strength to the unit</li> <li>» Attractive nickel gray powder-paint finish</li> </ul> |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model       | Nominal Capacity (BTU/h) |         | EER  | Voltage-Phase | Dimensions |     |     | Service Valve |          | dB(A) | Ship Weight (lbs) |
|-------------|--------------------------|---------|------|---------------|------------|-----|-----|---------------|----------|-------|-------------------|
|             | Cooling                  | Heating |      |               | W"         | D"  | H"  | Liquid"       | Suction" |       |                   |
| DZ11SA0903A | 87,000                   | 82,000  | 11.0 | 208/230       | 35½        | 35½ | 37½ | ⅝             | 1⅜       | 84    | 334               |
| DZ11SA0904A | 87,000                   | 82,000  | 11.0 | 460           | 35½        | 35½ | 37½ | ⅝             | 1⅜       | 84    | 334               |
| DZ11SA1203A | 110,000                  | 100,000 | 11.0 | 208/230       | 35½        | 35½ | 41½ | ⅝             | 1⅜       | 84    | 383               |
| DZ11SA1204A | 110,000                  | 100,000 | 11.0 | 460           | 35½        | 35½ | 41½ | ⅝             | 1⅜       | 84    | 383               |

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

# DAT – Multi-Speed Upflow Air Handler

## 7½ & 10 Tons



\*Complete warranty details available from your local distributor or manufacturer's representative or at [www.daikincomfort.com](http://www.daikincomfort.com).

The Daikin DAT Multi-Speed, Multi-Position Air Handlers are suitable for upflow or left side horizontal installations to accompany your 7½ and 10-ton split-system units. These unit feature a fully insulated fiberglass blanket for quiet, efficient operation.



### DESIGNED FOR EXCEPTIONAL DURABILITY, ENERGY EFFICIENCY, AND OUTSTANDING PERFORMANCE.

- |                                                                                                                                                                                                                                                                                                    |                                                                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                 |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>» 10-ton model circuited for use with two 4 or 5-ton cooling-only or heat pump systems, or one 10-ton cooling-only or heat pump system</li> <li>» All models convertible to 460-3-60 from 208/230-3-60</li> <li>» Copper tube/aluminum fin coils</li> </ul> | <ul style="list-style-type: none"> <li>» Transformer and blower relay TXV control: 7½-ton unit has one (1); 10-ton unit has two (2) thermal expansion check valves</li> <li>» Draw-thru centrifugal blower is belt-driven for quiet, efficient operation</li> <li>» Heavy-gauge, reinforced, galvanized-steel cabinet</li> </ul> | <ul style="list-style-type: none"> <li>» Fully insulated with fiberglass blanket</li> <li>» Horizontal and vertical condensate pans</li> <li>» Built-in filter rack (2" filter included)</li> <li>» Entry on top of panel for both low and high voltages</li> <li>» Removable access panels make servicing of unit faster and easier</li> </ul> |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

| Model      | Nominal Cooling (BTU/h) | Electric Heat (kW) | CFM @ 0.3" ESP | Voltage-Phase | Dimensions |    |        | Service Valve |          | Ship Weight (lbs) |
|------------|-------------------------|--------------------|----------------|---------------|------------|----|--------|---------------|----------|-------------------|
|            |                         |                    |                |               | W"         | D" | H"     | Liquid"       | Suction" |                   |
| DAT09043** | 90,000                  | 15, 20, 30         | 3,000          | 208/240-3     | 48 1/8     | 24 | 60 1/2 | 3/8*          | 1 1/8*   | 430               |
| DAT09044** | 90,000                  | 15, 20, 30         | 3,000          | 460-3         | 48 1/8     | 24 | 60 1/2 | 3/8*          | 1 1/8*   | 430               |
| DAT12043** | 120,000                 | 15, 20, 30         | 4,000          | 208/240-3     | 48 1/8     | 24 | 60 1/2 | 3/8*          | 1 1/8*   | 430               |
| DAT12044** | 120,000                 | 15, 20, 30         | 4,000          | 460-3         | 48 1/8     | 24 | 60 1/2 | 3/8*          | 1 1/8*   | 430               |

\*For two refrigerant lines

Daikin North America LLC reserves the right to discontinue or change at any time specifications or designs without notice or without incurring obligations.

The background image is a full-page photograph of a modern architectural interior. It features a large, multi-story atrium with a glass and steel frame. The floor is highly reflective, showing clear reflections of the structural elements and a person walking in the distance. The lighting is bright, creating a high-contrast, blue-tinted scene. A semi-transparent dark grey rectangular box is positioned in the upper right quadrant, containing the word "Accessories" in white text.

# Accessories

# DSC/DSH/DSG Packaged Units

## 3 to 5 Tons

| Daikin Master Item #                                             | Description                                                                                                     | Fits Model Sizes | Field-Installed | Factory-Installed |
|------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>Curb</b>                                                      |                                                                                                                 |                  |                 |                   |
| 14CURB3672B                                                      | 14" Roof Curb                                                                                                   | 3-5 Tons         | ✓               |                   |
| 18CURB3672B                                                      | 18" Roof Curb                                                                                                   | 3-5 Tons         | ✓               |                   |
| 24CURB3672B                                                      | 24" Roof Curb                                                                                                   | 3-5 Tons         | ✓               |                   |
| GHRC-3672                                                        | Hurricane Restraint Clips                                                                                       | 3-5 Tons         | ✓               |                   |
| <b>Ultra Low-Leak Economizer &amp; Power Exhaust<sup>1</sup></b> |                                                                                                                 |                  |                 |                   |
| 1036609C                                                         | Ultra Low-Leak Downflow Economizer w/ Enthalpy                                                                  | 3-5 Tons         | ✓               | ✓                 |
| 1039609                                                          | Ultra Low-Leak Horizontal Economizer w/ Enthalpy                                                                | 3-5 Tons         | ✓               |                   |
| 104650921                                                        | Prop Power Exhaust 230v                                                                                         | 3-5 Tons         | ✓               |                   |
| 104650931                                                        | Prop Power Exhaust 460v                                                                                         | 3-5 Tons         | ✓               |                   |
| 104650941                                                        | Prop Power Exhaust 575v                                                                                         | 3-5 Tons         | ✓               |                   |
| <b>Low-Leak Economizer &amp; Power Exhaust<sup>2</sup></b>       |                                                                                                                 |                  |                 |                   |
| DDNECNJ3672C                                                     | Low-Leak Downflow Economizer                                                                                    | 3-5 Tons         | ✓               | ✓                 |
| DPE36722                                                         | Downflow Power Exhaust (208/230 Volt)                                                                           | 3-5 Tons         | ✓               |                   |
| DPE36724                                                         | Downflow Power Exhaust (460 Volt)                                                                               | 3-5 Tons         | ✓               |                   |
| DPE36727                                                         | Downflow Power Exhaust (575v)                                                                                   | 3-5 Tons         | ✓               |                   |
| DHZEENJ3672                                                      | Horizontal Economizer                                                                                           | 3-5 Tons         | ✓               |                   |
| DHPE36722                                                        | Horizontal Power Exhaust (208/230 Volt)                                                                         | 3-5 Tons         | ✓               |                   |
| DHPE36724                                                        | Horizontal Power Exhaust (460 Volt)                                                                             | 3-5 Tons         | ✓               |                   |
| DHPE36727                                                        | Horizontal Power Exhaust (575 Volt)                                                                             | 3-5 Tons         | ✓               |                   |
| <b>Downflow Accessories</b>                                      |                                                                                                                 |                  |                 |                   |
| D25FD3672                                                        | 25% Manual Fresh Air Damper                                                                                     | 3-5 Tons         | ✓               |                   |
| D25MFD3672                                                       | 25% Motorized Fresh Air Damper                                                                                  | 3-5 Tons         | ✓               |                   |
| DDNBBS3672                                                       | Burglar Bar Sleeves with Supply & Return                                                                        | 3-5 Tons         | ✓               |                   |
| DDNECNJ3672NR                                                    | Downflow Economizer <sup>2</sup> w/o Barometric Relief                                                          | 3-5 Tons         | ✓               |                   |
| DDNSQRD3616                                                      | Downflow Square-to-Round Adapter (16" Round)                                                                    | 3 tons           | ✓               |                   |
| DDNSQRD487218                                                    | Downflow Square-to-Round Adapter (18" Round)                                                                    | 4-5 tons         | ✓               |                   |
| <b>Horizontal Accessories</b>                                    |                                                                                                                 |                  |                 |                   |
| DBRD3672                                                         | Barometric Relief Damper                                                                                        | 3-5 Tons         | ✓               |                   |
| <b>Concentrics</b>                                               |                                                                                                                 |                  |                 |                   |
| CDK36                                                            | Concentric Duct Kit                                                                                             | 3 Ton            | ✓               |                   |
| CDK36515                                                         | Flush Mount Concentric Duct Kit w/ Filter                                                                       | 3 Ton            | ✓               |                   |
| CDK36530                                                         | Step Down Concentric Duct Kit                                                                                   | 3 Ton            | ✓               |                   |
| CDK36535                                                         | Step Down Concentric Duct Kit w/ Filter                                                                         | 3 Ton            | ✓               |                   |
| CDK4872                                                          | Concentric Duct Kit                                                                                             | 4-5 Ton          | ✓               |                   |
| CDK4872515                                                       | Flush Mount Concentric Duct Kit w/ Filter                                                                       | 4-5 Ton          | ✓               |                   |
| CDK4872530                                                       | Step Down Concentric Duct Kit                                                                                   | 4-5 Ton          | ✓               |                   |
| CDK4872535                                                       | Step Down Concentric Duct Kit w/ Filter                                                                         | 4-5 Ton          | ✓               |                   |
| <b>DDC Accessories<sup>3</sup></b>                               |                                                                                                                 |                  |                 |                   |
|                                                                  | DDC communicating controller (built-in BACnet® MS/TP)<br>includes Standard Room Sensor to be installed in field | 3-5 Tons         |                 | ✓                 |
| 10366D09C                                                        | DDC Ultra Low-Leak Downflow Economizer                                                                          | 3-5 Tons         | ✓               | ✓                 |
| 10396D09                                                         | DDC Ultra Low-Leak Horizontal Economizer                                                                        | 3-5 Tons         | ✓               |                   |
| 10465DDC                                                         | Power Exhaust kit used with DDC Ultra Low-Leak Economizer                                                       | 3-5 tons         | ✓               |                   |
| DLAKT01                                                          | Low-Ambient                                                                                                     | 3-5 Tons         | ✓               | ✓                 |
| LONKT01                                                          | LonWorks® card                                                                                                  | 3-5 Tons         | ✓               |                   |
| 3PMK01                                                           | Phase Monitor (3-Phase Only)                                                                                    | 3-5 Tons         | ✓               | ✓                 |
| DFSKT01                                                          | Dirty Filter Switch                                                                                             | 3-5 Tons         | ✓               |                   |
| <b>1 phase 208-230V Electric Heat Kits</b>                       |                                                                                                                 |                  |                 |                   |
| SPKT01                                                           | Single Point Wiring Kit 1 phase Heat Kits                                                                       | 3-5 Tons         | ✓               | ✓                 |
| EHK1-10                                                          | 10kw 208-230v 1ph Electric Heat Kit                                                                             | 3-5 Tons         | ✓               | ✓                 |
| EHK1-15                                                          | 15kw 208-230v 1ph Electric Heat Kit                                                                             | 3-5 Tons         | ✓               | ✓                 |
| EHK1-18                                                          | 18kw 208-230v 1ph Electric Heat Kit                                                                             | 4 tons           | ✓               | ✓                 |
| EHK1-20                                                          | 20kw 208-230v 1ph Electric Heat Kit                                                                             | 5 tons           | ✓               | ✓                 |
| <b>3 phase 208-230V Electric Heat Kits</b>                       |                                                                                                                 |                  |                 |                   |
| SPKT02                                                           | Single Point Wiring Kit 3 phase Heat Kits                                                                       | 3-5 Tons         | ✓               | ✓                 |
| EHK3-10                                                          | 10kw 208-230 3ph Electric Heat Kit                                                                              | 3-5 Tons         | ✓               | ✓                 |
| EHK3-15                                                          | 15kw 208-230 3ph Electric Heat Kit                                                                              | 3-5 Tons         | ✓               | ✓                 |

# DSC/DSH/DSG Packaged Units

3 to 5 Tons (cont.)

| Daikin Master Item #                   | Description                                                          | Fits Model Sizes | Field-Installed | Factory-Installed |
|----------------------------------------|----------------------------------------------------------------------|------------------|-----------------|-------------------|
| EHK3-18                                | 18kw 208-230 3ph Electric Heat Kit                                   | 4 tons           | √               | √                 |
| EHK3-20                                | 20kw 208-230 3ph Electric Heat Kit                                   | 5 tons           | √               | √                 |
| <b>3 phase 460V Electric Heat Kits</b> |                                                                      |                  |                 |                   |
| EHK4-10                                | 10kw 460v 3ph Electric Heat Kit                                      | 3-5 Tons         | √               | √                 |
| EHK4-15                                | 15kw 460v 3ph Electric Heat Kit                                      | 3-5 Tons         | √               | √                 |
| EHK4-18                                | 18kw 460v 3ph Electric Heat Kit                                      | 4 tons           | √               | √                 |
| EHK4-20                                | 20kw 460v 3ph Electric Heat Kit                                      | 5 tons           | √               | √                 |
| <b>3 phase 575V Electric Heat Kits</b> |                                                                      |                  |                 |                   |
| EHK7-10                                | 10kw 575v 3ph Electric Heat Kit                                      | 3-5 Tons         | √               | √                 |
| EHK7-15                                | 15kw 575v 3ph Electric Heat Kit                                      | 3-5 Tons         | √               | √                 |
| EHK7-18                                | 18kw 575v 3ph Electric Heat Kit                                      | 4 tons           | √               | √                 |
| EHK7-20                                | 20kw 575v 3ph Electric Heat Kit                                      | 5 tons           | √               | √                 |
| <b>High-Static Kits<sup>4</sup></b>    |                                                                      |                  |                 |                   |
| HSKTS036                               | High Static Kit - 230v & 460v                                        | DS*, 3 Ton       | √               | √                 |
| HSKTS048                               | High Static Kit - 230v & 460v                                        | DS*, 4 Ton       | √               | √                 |
| HSKTS060                               | High Static Kit - 230v & 460v                                        | DS*, 5 Ton       | √               | √                 |
| HSKTS036-7                             | High Static Kit - 575v                                               | DS*, 3 Ton       | √               | √                 |
| HSKTS048-7                             | High Static Kit - 575v                                               | DS*, 4 Ton       | √               | √                 |
| HSKTS060-7                             | High Static Kit - 575v                                               | DS*, 5 Ton       | √               | √                 |
| <b>Crankcase Heater Kits</b>           |                                                                      |                  |                 |                   |
| 0163R00002S                            | 40W 230V                                                             | 3 tons           | √               |                   |
| 0163R00031S                            | 40W 460V                                                             | 3 tons           | √               |                   |
| 0163R00032S                            | 40W 575V                                                             | 3 tons           | √               |                   |
| 0130L00017S                            | 70W 230V                                                             | 4 - 5 tons       | √               |                   |
| 0130L00018S                            | 70W 460V                                                             | 4 - 5 tons       | √               |                   |
| 0130L00019S                            | 70W 575V                                                             | 4 - 5 tons       | √               |                   |
| <b>High Efficiency Filters</b>         |                                                                      |                  |                 |                   |
| 0160L00203                             | High Efficiency MERV 13 Air Filter Nom. Size: 24x24x2; (Order Qty 1) | 3 tons           | √               |                   |
| 0160L00204                             | High Efficiency MERV 13 Air Filter Nom. Size: 14x20x2; (Order Qty 4) | 4 tons           | √               |                   |
| 0160L00205                             | High Efficiency MERV 13 Air Filter Nom. Size: 16x20x2; (Order Qty 4) | 5 tons           | √               |                   |
| <b>Misc Accessories</b>                |                                                                      |                  |                 |                   |
| HAILGD03D                              | Condenser Coil Hail Guard                                            | 3-5 tons         | √               |                   |
| HAILGD04D                              | Condenser Coil Hail Guard                                            | 5 tons DSH only  | √               |                   |
|                                        | Convenience Outlet: Non-Powered                                      | 3-5 tons         |                 | √                 |
|                                        | Convenience Outlet: Powered                                          | 3-5 tons         |                 | √                 |
|                                        | Disconnect Switch                                                    | 3-5 tons         |                 | √                 |
| LAKT11                                 | Low Ambient Kit, 208-230V - non-DDC                                  | 3-5 tons         | √               | √                 |
| LAKT13                                 | Low Ambient Kit, 460V - non-DDC                                      | 3-5 tons         | √               | √                 |
| LAKT14                                 | Low Ambient Kit, 575V - non-DDC                                      | 3-5 tons         | √               | √                 |
| 3PMNDK01                               | Phase Monitor - Non DDC                                              | 3-5 Ton          | √               | √                 |
|                                        | Smoke Detector (supply and/or return air)                            | 3-5 Ton          |                 | √                 |
|                                        | Hinged Panels                                                        | 3-5 Ton          |                 | √                 |
| FSK01A                                 | Freeze Stat Kit                                                      | 3-5 Ton          | √               |                   |
| IRKT-01                                | Isolation Relay Kit                                                  | 3-5 Ton          | √               |                   |
| LPM-07                                 | LP Conversion Kit (For DSG036045 unit only)                          | 3 Ton            | √               |                   |
| LPM-08                                 | LP Conversion Kit                                                    | 3-5 Ton          | √               |                   |
| 220-GX-01                              | Flue Extension Kit                                                   | 3-5 Ton          | √               |                   |
| HA036300                               | High Altitude Kit                                                    | 3-5 Ton          | √               |                   |

<sup>1</sup> Use Economizer & Power Exhaust listed within Ultra Low-Leak section

<sup>2</sup> Use Economizer & Power Exhaust listed within Low-Leak section

<sup>3</sup> For a full list of DDC accessories, please refer to DDC Controller Technical Guide manual (DK-DDC-TGD-01B)

<sup>4</sup> HSKT High-Static Kits are for use with standard single-speed belt-drive units only.

Note: Where multiple variations are available, the heaviest combination is listed.

# DCC/DCH/DCG Packaged Units

## 6 Tons

| Daikin Master Item #                                             | Description                                                                                                                 | Fits Model Sizes | Field-Installed | Factory-Installed |
|------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>Curb</b>                                                      |                                                                                                                             |                  |                 |                   |
| 14CURB3672B                                                      | 14" Roof Curb                                                                                                               | 6 tons           | ✓               |                   |
| 18CURB3672B                                                      | 18" Roof Curb                                                                                                               | 6 tons           | ✓               |                   |
| 24CURB3672B                                                      | 24" Roof Curb                                                                                                               | 6 tons           | ✓               |                   |
| GHRC-3672                                                        | Hurricane Restraint Clips                                                                                                   | 6 tons           | ✓               |                   |
| <b>Ultra Low-Leak Economizer &amp; Power Exhaust<sup>1</sup></b> |                                                                                                                             |                  |                 |                   |
| 1036609C                                                         | Ultra Low-Leak Downflow Economizer w/ Enthalpy                                                                              | 6 tons           | ✓               | ✓                 |
| 1039609                                                          | Ultra Low-Leak Horizontal Economizer w/ Enthalpy                                                                            | 6 tons           | ✓               |                   |
| 104650921                                                        | Prop Power Exhaust 230v                                                                                                     | 6 tons           | ✓               |                   |
| 104650931                                                        | Prop Power Exhaust 460v                                                                                                     | 6 tons           | ✓               |                   |
| 104650941                                                        | Prop Power Exhaust 575v                                                                                                     | 6 tons           | ✓               |                   |
| <b>Low-Leak Economizer &amp; Power Exhaust<sup>2</sup></b>       |                                                                                                                             |                  |                 |                   |
| DDNECNJ3672C                                                     | Low-Leak Downflow Economizer                                                                                                | 6 tons           | ✓               | ✓                 |
| DPE36722                                                         | Downflow Power Exhaust (208/230 Volt)                                                                                       | 6 tons           | ✓               |                   |
| DPE36724                                                         | Downflow Power Exhaust (460 Volt)                                                                                           | 6 tons           | ✓               |                   |
| DPE36727                                                         | Downflow Power Exhaust (575v)                                                                                               | 6 tons           | ✓               |                   |
| DHZEENJ3672                                                      | Horizontal Economizer                                                                                                       | 6 tons           | ✓               |                   |
| DHPE36722                                                        | Horizontal Power Exhaust (208/230 Volt)                                                                                     | 6 tons           | ✓               |                   |
| DHPE36724                                                        | Horizontal Power Exhaust (460 Volt)                                                                                         | 6 tons           | ✓               |                   |
| DHPE36727                                                        | Horizontal Power Exhaust (575 Volt)                                                                                         | 6 tons           | ✓               |                   |
| <b>Downflow Accessories</b>                                      |                                                                                                                             |                  |                 |                   |
| D25FD3672                                                        | 25% Manual Fresh Air Damper                                                                                                 | 6 tons           | ✓               |                   |
| D25MFD3672                                                       | 25% Motorized Fresh Air Damper                                                                                              | 6 tons           | ✓               |                   |
| DDNBBS3672                                                       | Burglar Bar Sleeves with Supply & Return                                                                                    | 6 tons           | ✓               |                   |
| DDNECNJ3672NR                                                    | Downflow Economizer <sup>2</sup> w/o Barometric Relief                                                                      | 6 tons           | ✓               |                   |
| DDNSQRD487218                                                    | Downflow Square-to-Round Adapter (18" Round)                                                                                | 6 tons           | ✓               |                   |
| <b>Horizontal Accessories</b>                                    |                                                                                                                             |                  |                 |                   |
| DBRD3672                                                         | Barometric Relief Damper                                                                                                    | 6 tons           | ✓               |                   |
| <b>Concentrics</b>                                               |                                                                                                                             |                  |                 |                   |
| CDK4872                                                          | Concentric Duct Kit                                                                                                         | 6 tons           | ✓               |                   |
| <b>DDC Accessories<sup>3</sup></b>                               |                                                                                                                             |                  |                 |                   |
|                                                                  | DDC communicating controller (built-in BACnet <sup>®</sup> MS/TP)<br>includes Standard Room Sensor to be installed in field | 6 tons           |                 | ✓                 |
| 10366D09C                                                        | DDC Ultra Low-Leak Downflow Economizer                                                                                      | 6 tons           | ✓               | ✓                 |
| 10396D09                                                         | DDC Ultra Low-Leak Horizontal Economizer                                                                                    | 6 tons           | ✓               |                   |
| 10465DDC                                                         | Power Exhaust kit used with DDC Ultra Low-Leak Economizer                                                                   | 6 tons           | ✓               |                   |
| DLAKT01                                                          | Low-Ambient                                                                                                                 | 6 tons           | ✓               | ✓                 |
| LONKT01                                                          | LonWorks <sup>®</sup> card                                                                                                  | 6 tons           | ✓               |                   |
| 3PMK01                                                           | Phase Monitor (3-Phase Only)                                                                                                | 6 tons           | ✓               | ✓                 |
| DFSKT01                                                          | Dirty Filter Switch                                                                                                         | 6 tons           | ✓               |                   |
| <b>3 phase 208-230V Electric Heat Kits</b>                       |                                                                                                                             |                  |                 |                   |
| SPKT02                                                           | Single Point Wiring Kit 3 phase Heat Kits                                                                                   | 6 tons           | ✓               | ✓                 |
| EHK3-10                                                          | 10kw 208-230 3ph Electric Heat Kit                                                                                          | 6 tons           | ✓               | ✓                 |
| EHK3-15                                                          | 15kw 208-230 3ph Electric Heat Kit                                                                                          | 6 tons           | ✓               | ✓                 |
| EHK3-18                                                          | 18kw 208-230 3ph Electric Heat Kit                                                                                          | 6 tons           | ✓               | ✓                 |
| EHK3-20                                                          | 20kw 208-230 3ph Electric Heat Kit                                                                                          | 6 tons           | ✓               | ✓                 |
| EHK3-25                                                          | 25kw 208-230 3ph Electric Heat Kit                                                                                          | 6 tons           | ✓               | ✓                 |
| <b>3 phase 460V Electric Heat Kits</b>                           |                                                                                                                             |                  |                 |                   |
| EHK4-10                                                          | 10kw 460v 3ph Electric Heat Kit                                                                                             | 6 tons           | ✓               | ✓                 |
| EHK4-15                                                          | 15kw 460v 3ph Electric Heat Kit                                                                                             | 6 tons           | ✓               | ✓                 |
| EHK4-18                                                          | 18kw 460v 3ph Electric Heat Kit                                                                                             | 6 tons           | ✓               | ✓                 |
| EHK4-20                                                          | 20kw 460v 3ph Electric Heat Kit                                                                                             | 6 tons           | ✓               | ✓                 |
| EHK4-25                                                          | 25kw 460v 3ph Electric Heat Kit                                                                                             | 6 tons           | ✓               | ✓                 |

# DCC/DCH/DCG Packaged Units

6 Tons (cont.)

| Daikin Master Item #                   | Description                                                          | Fits Model Sizes | Field-Installed | Factory-Installed |
|----------------------------------------|----------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>3 phase 575V Electric Heat Kits</b> |                                                                      |                  |                 |                   |
| EHK7-10                                | 10kw 575v 3ph Electric Heat Kit                                      | 6 tons           | ✓               | ✓                 |
| EHK7-15                                | 15kw 575v 3ph Electric Heat Kit                                      | 6 tons           | ✓               | ✓                 |
| EHK7-18                                | 18kw 575v 3ph Electric Heat Kit                                      | 6 tons           | ✓               | ✓                 |
| EHK7-20                                | 20kw 575v 3ph Electric Heat Kit                                      | 6 tons           | ✓               | ✓                 |
| EHK7-25                                | 25kw 575v 3ph Electric Heat Kit                                      | 6 tons           | ✓               | ✓                 |
| <b>High-Static Kits</b>                |                                                                      |                  |                 |                   |
| HSKTW072FI                             | High-Static Kit (230/460/575v)                                       | 6 tons           |                 | ✓                 |
| <b>Crankcase Heater Kits</b>           |                                                                      |                  |                 |                   |
| 0130L00017S                            | 70W 230V                                                             | 6 tons           | ✓               |                   |
| 0130L00018S                            | 70W 460V                                                             | 6 tons           | ✓               |                   |
| 0130L00019S                            | 70W 575V                                                             | 6 tons           | ✓               |                   |
| <b>High Efficiency Filters</b>         |                                                                      |                  |                 |                   |
| 0160L00205                             | High Efficiency MERV 13 Air Filter Nom. Size: 16x20x2; (Order Qty 4) | 6 tons           | ✓               |                   |
| <b>Misc Accessories</b>                |                                                                      |                  |                 |                   |
| HAILGD04D                              | Condenser Coil Hail Guard                                            | 6 tons           | ✓               |                   |
|                                        | Convenience Outlet: Non-Powered                                      | 6 tons           |                 | ✓                 |
|                                        | Convenience Outlet: Powered                                          | 6 tons           |                 | ✓                 |
|                                        | Disconnect Switch                                                    | 6 tons           |                 | ✓                 |
| HA-02                                  | High-Altitude Kit                                                    | 6 tons           | ✓               |                   |
| LAKT12                                 | Low Ambient Kit, 208-230V - non-DDC                                  | 6 tons           | ✓               | ✓                 |
| LAKT15                                 | Low Ambient Kit, 460V - non-DDC                                      | 6 tons           | ✓               | ✓                 |
| LAKT16                                 | Low Ambient Kit, 575V - non-DDC                                      | 6 tons           | ✓               | ✓                 |
| LPM-08                                 | LP Conversion Kit                                                    | 6 tons           | ✓               |                   |
| 3PMNDK01                               | Phase Monitor - Non DDC                                              | 6 tons           | ✓               | ✓                 |
|                                        | Smoke Detector (supply and/or return air)                            | 6 tons           |                 | ✓                 |
|                                        | Hinged Panels                                                        | 6 tons           |                 | ✓                 |

<sup>1</sup> Use Economizer & Power Exhaust listed within Ultra Low-Leak section

<sup>2</sup> Use Economizer & Power Exhaust listed within Low-Leak section

<sup>3</sup> For a full list of DDC accessories, please refer to DDC Controller Technical Guide manual (DK-DDC-TGD-01B)

Note: Where multiple variations are available, the heaviest combination is listed.

# DCC/DCH/DCG Packaged Units

7½ to 12½ Tons

| Daikin Master Item #                                             | Description                                                                                                     | Fits Model Sizes | Field-Installed | Factory-Installed |
|------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>Curb</b>                                                      |                                                                                                                 |                  |                 |                   |
| 14CURB90150                                                      | 14" Roof Curb                                                                                                   | 7½-12½ tons      | ✓               |                   |
| 18CURB90150                                                      | 18" Roof Curb                                                                                                   | 7½-12½ tons      | ✓               |                   |
| 24CURB90150                                                      | 24" Roof Curb                                                                                                   | 7½-12½ tons      | ✓               |                   |
| GHRC-90150                                                       | Hurricane Restraint Clips                                                                                       | 7½-12½ tons      | ✓               |                   |
| <b>Ultra Low-Leak Economizer &amp; Power Exhaust<sup>1</sup></b> |                                                                                                                 |                  |                 |                   |
| 1036610B                                                         | Ultra Low-Leak Horizontal Economizer w/ Dry Bulb                                                                | 7½-12½ tons      | ✓               |                   |
| 1039610B                                                         | Ultra Low-Leak Horizontal Economizer w/ Enthalpy                                                                | 7½-12½ tons      | ✓               |                   |
| 104651021                                                        | Prop Power Exhaust 230v                                                                                         | 7½-12½ tons      | ✓               |                   |
| 104651031                                                        | Prop Power Exhaust 460v                                                                                         | 7½-12½ tons      | ✓               |                   |
| 104651041                                                        | Prop Power Exhaust 575v                                                                                         | 7½-12½ tons      | ✓               |                   |
| <b>Low-Leak Economizer &amp; Power Exhaust<sup>2</sup></b>       |                                                                                                                 |                  |                 |                   |
| DDNECNJ90150B                                                    | Low-Leak Downflow Economizer                                                                                    | 7½-12½ tons      | ✓               | ✓                 |
| DPE901502                                                        | Downflow Power Exhaust (208/230v)                                                                               | 7½-12½ tons      | ✓               |                   |
| DPE901504                                                        | Downflow Power Exhaust (460v)                                                                                   | 7½-12½ tons      | ✓               |                   |
| DPE901507                                                        | Downflow Power Exhaust (575v)                                                                                   | 7½-12½ tons      | ✓               |                   |
| DHZECNJ90150                                                     | Horizontal Economizer                                                                                           | 7½-12½ tons      | ✓               |                   |
| DHPE901502                                                       | Horizontal Power Exhaust (208/230v)                                                                             | 7½-12½ tons      | ✓               |                   |
| DHPE901504                                                       | Horizontal Power Exhaust (460v)                                                                                 | 7½-12½ tons      | ✓               |                   |
| DHPE901507                                                       | Horizontal Power Exhaust (575v)                                                                                 | 7½-12½ tons      | ✓               |                   |
| <b>Downflow Accessories</b>                                      |                                                                                                                 |                  |                 |                   |
| D25FD90150                                                       | 25% Manual Fresh Air Damper                                                                                     | 7½-12½ tons      | ✓               |                   |
| D25MFD90150                                                      | 25% Motorized Fresh Air Damper                                                                                  | 7½-12½ tons      | ✓               |                   |
| DDNBBS90150                                                      | Burglar Bar Sleeves: includes Supply & Return                                                                   | 7½-12½ tons      | ✓               |                   |
| DDNECNJ90150NR                                                   | Low-Leak Downflow Economizer w/o Barometric Relief                                                              | 7½-12½ tons      | ✓               |                   |
| DDNSQRD9020                                                      | Downflow Square-to-Round Adapter 20" Round                                                                      | 7½ tons          | ✓               |                   |
| <b>Horizontal Accessories</b>                                    |                                                                                                                 |                  |                 |                   |
| DBRD3672                                                         | Horizontal Barometric Relief Damper (2 required)                                                                | 7½-12½ tons      | ✓               |                   |
| <b>Concentrics</b>                                               |                                                                                                                 |                  |                 |                   |
| CDK90102                                                         | Concentric Duct Kit                                                                                             | 7½-8½ tons       | ✓               |                   |
| CDK120                                                           | Concentric Duct Kit                                                                                             | 10 tons          | ✓               |                   |
| CDK150                                                           | Concentric Duct Kit                                                                                             | 12½ tons         | ✓               |                   |
| <b>3 phase 208-230V Electric Heat Kits</b>                       |                                                                                                                 |                  |                 |                   |
| EHK3-16                                                          | 16kw 208-230v 3ph Electric Heat Kit                                                                             | 7½-12½ tons      | ✓               | ✓                 |
| EHK3-30                                                          | 30kw 208-230v 3ph Electric Heat Kit                                                                             | 7½-12½ tons      | ✓               | ✓                 |
| EHK3-45                                                          | 45kw 208-230v 3ph Electric Heat Kit                                                                             | 7½-12½ tons      | ✓               | ✓                 |
| <b>3 phase 460V Electric Heat Kits</b>                           |                                                                                                                 |                  |                 |                   |
| EHK3-16                                                          | 16kw 460v 3ph Electric Heat Kit                                                                                 | 7½-12½ tons      | ✓               | ✓                 |
| EHK3-30                                                          | 30kw 460v 3ph Electric Heat Kit                                                                                 | 7½-12½ tons      | ✓               | ✓                 |
| EHK3-45                                                          | 45kw 460v 3ph Electric Heat Kit                                                                                 | 7½-12½ tons      | ✓               | ✓                 |
| <b>3 phase 575V Electric Heat Kits</b>                           |                                                                                                                 |                  |                 |                   |
| EHK3-16                                                          | 16kw 575v 3ph Electric Heat Kit                                                                                 | 7½-12½ tons      | ✓               | ✓                 |
| EHK3-30                                                          | 30kw 575v 3ph Electric Heat Kit                                                                                 | 7½-12½ tons      | ✓               | ✓                 |
| EHK3-45                                                          | 45kw 575v 3ph Electric Heat Kit                                                                                 | 7½-12½ tons      | ✓               | ✓                 |
| <b>DDC Accessories<sup>3</sup></b>                               |                                                                                                                 |                  |                 |                   |
|                                                                  | DDC communicating controller (built-in BACnet® MS/TP)<br>includes Standard Room Sensor to be installed in field | 7½-12½ tons      |                 | ✓                 |
| 10366D10B                                                        | DDC Ultra Low-Leak Downflow Economizer                                                                          | 7½-12½ tons      | ✓               | ✓                 |
| 10396D10                                                         | DDC Ultra Low-Leak Horizontal Economizer                                                                        | 7½-12½ tons      | ✓               |                   |
| 10465DDC                                                         | Power Exhaust kit used with DDC Ultra Low-Leak Economizer                                                       | 7½-12½ tons      | ✓               |                   |
| DLAKT03                                                          | Low-Ambient                                                                                                     | 7½-12½ tons      | ✓               | ✓                 |
| LONKT01                                                          | LonWorks® card                                                                                                  | 7½-12½ tons      | ✓               |                   |
| 3PMK01                                                           | Phase Monitor (3-Phase Only)                                                                                    | 7½-12½ tons      | ✓               | ✓                 |
| DFSKT01                                                          | Dirty Filter Switch                                                                                             | 7½-12½ tons      | ✓               |                   |

# DCC/DCH/DCG Packaged Units

7½ to 12½ Tons (cont.)

| Daikin Master Item #           | Description                                                          | Fits Model Sizes | Field-Installed | Factory-Installed |
|--------------------------------|----------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>High-Static Kits</b>        |                                                                      |                  |                 |                   |
| HSKTW120-3FIAC                 | High Static, Factory Installed (208/230v)                            | 10 tons AC       |                 | √                 |
| HSKTW120-4FIAC                 | High Static, Factory Installed (460v)                                | 10 tons AC       |                 | √                 |
| HSKTW120-7FIAC                 | High Static, Factory Installed (575v)                                | 10 tons AC       |                 | √                 |
| HSKTW120-3FIGAS                | High Static, Factory Installed (208/230v)                            | 10 tons Gas      |                 | √                 |
| HSKTW120-4FIGAS                | High Static, Factory Installed (460v)                                | 10 tons Gas      |                 | √                 |
| HSKTW120-7FIGAS                | High Static, Factory Installed (575v)                                | 10 tons Gas      |                 | √                 |
| HSKTW120-3FIHP                 | High Static, Factory Installed (208/230v)                            | 10 tons HP       |                 | √                 |
| HSKTW120-4FIHP                 | High Static, Factory Installed (460v)                                | 10 tons HP       |                 | √                 |
| HSKTW120-7FIHP                 | High Static, Factory Installed (575v)                                | 10 tons HP       |                 | √                 |
| HSKTW150-3FI                   | High Static, Factory Installed (230v)                                | 12½ tons         |                 | √                 |
| HSKTW150-4FI                   | High Static, Factory Installed (460v)                                | 12½ tons         |                 | √                 |
| HSKTW150AC-7FI                 | High Static, Factory Installed (575v)                                | 12½ tons AC/HP   |                 | √                 |
| <b>Crankcase Heater Kits</b>   |                                                                      |                  |                 |                   |
| 0130L00017S                    | 70W 230V                                                             | 7½-12½ tons      | √               |                   |
| 0130L00018S                    | 70W 460V                                                             | 7½-12½ tons      | √               |                   |
| 0130L00019S                    | 70W 575V                                                             | 7½-12½ tons      | √               |                   |
| <b>High Efficiency Filters</b> |                                                                      |                  |                 |                   |
| 0160L00205                     | High Efficiency MERV 13 Air Filter Nom. Size: 16x20x2; (Order Qty 4) | 7.5 tons         | √               |                   |
| 0160L00206                     | High Efficiency MERV 13 Air Filter Nom. Size: 16x24x2; (Order Qty 4) | 8.5 & 10 tons    | √               |                   |
| 0160L00202                     | High Efficiency MERV 13 Air Filter Nom. Size: 20x25x2; (Order Qty 4) | 12.5 tons        | √               |                   |
| <b>Misc Accessories</b>        |                                                                      |                  |                 |                   |
| HailGD02D                      | Condenser Coil Hail Guard                                            | 7½-10 tons       | √               |                   |
| HailGD05D                      | Condenser Coil Hail Guard                                            | 12½ tons         | √               |                   |
|                                | Convenience Outlet: Powered                                          | 7½-12½ tons      |                 | √                 |
|                                | Convenience Outlet: Non-Powered                                      | 7½-12½ tons      |                 | √                 |
|                                | Disconnect Switch (non-fused)                                        | 7½-12½ tons      |                 | √                 |
| LAKT17                         | Low-Ambient Kit, 208-230V - non-DDC                                  | 7½-8½ tons       | √               | √                 |
| LAKT18                         | Low-Ambient Kit, 460V - non-DDC                                      | 7½-8½ tons       | √               | √                 |
| LAKT19                         | Low-Ambient Kit, 575V - non-DDC                                      | 7½-8½ tons       | √               | √                 |
| LAKT20                         | Low-Ambient Kit, 208-230V - non-DDC                                  | 10-12½ tons      | √               | √                 |
| LAKT21                         | Low-Ambient Kit, 460V - non-DDC                                      | 10-12½ tons      | √               | √                 |
| LAKT22                         | Low-Ambient Kit, 575V - non-DDC                                      | 10-12½ tons      | √               | √                 |
| 3PMNDK01                       | Phase Monitor - Non DDC                                              | 7½-12½ tons      | √               | √                 |
|                                | Smoke Detector (supply and/or return air)                            | 7½-12½ tons      |                 | √                 |
|                                | Hinged Panels                                                        | 7½-12½ tons      |                 | √                 |
| HA036300                       | High-Altitude Kit                                                    | All Models       | √               |                   |
| LPKT36150                      | LP Kit                                                               | 7½-12½ tons      | √               |                   |
| 220-GX-002                     | Flue Extension Kit                                                   | 7½-12½ tons      | √               |                   |

<sup>1</sup> Use Economizer & Power Exhaust listed within Ultra Low-Leak section

<sup>2</sup> Use Economizer & Power Exhaust listed within Low-Leak section

<sup>3</sup> For a full list of DDC accessories, please refer to DDC Controller Technical Guide manual (DK-DDC-TGD-01B)

Note: Where multiple variations are available, the heaviest combination is listed.

# DCC/DCG Packaged Units

## 15 to 25 Tons

| Daikin Master Item #                                             | Description                                                                                                  | Fits Model Sizes | Field-Installed | Factory-Installed |
|------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>Curb</b>                                                      |                                                                                                              |                  |                 |                   |
| 14CURB180300                                                     | 14" Roof Curb                                                                                                | 15-25 tons       | ✓               |                   |
| 18CURB180300                                                     | 18" Roof Curb                                                                                                | 15-25 tons       | ✓               |                   |
| 24CURB180300                                                     | 24" Roof Curb                                                                                                | 15-25 tons       | ✓               |                   |
| GHRC-180300                                                      | Hurricane Restraint Clips                                                                                    | 15-25 tons       | ✓               |                   |
| <b>Ultra Low-Leak Economizer &amp; Power Exhaust<sup>1</sup></b> |                                                                                                              |                  |                 |                   |
| 1036611C                                                         | Ultra Low-Leak Downflow Economizer w/ Enthalpy                                                               | 15-25 tons       | ✓               | ✓                 |
| 104651121                                                        | Prop Power Exhaust 230v                                                                                      | 15-25 tons       | ✓               |                   |
| 104651131                                                        | Prop Power Exhaust 460v                                                                                      | 15-25 tons       | ✓               |                   |
| 104651141                                                        | Prop Power Exhaust 575v                                                                                      | 15-25 tons       | ✓               |                   |
| <b>Low-Leak Economizer &amp; Power Exhaust<sup>2</sup></b>       |                                                                                                              |                  |                 |                   |
| DDNECNJ180300B                                                   | Low-Leak Downflow Economizer                                                                                 | 15-25 tons       | ✓               | ✓                 |
| DPE1803002                                                       | Downflow Power Exhaust (208/230v)                                                                            | 15-25 tons       | ✓               |                   |
| DPE1803004                                                       | Downflow Power Exhaust (460v)                                                                                | 15-25 tons       | ✓               |                   |
| DPE1803007                                                       | Downflow Power Exhaust (575v)                                                                                | 15-25 tons       | ✓               |                   |
| DHZEENJ180300                                                    | Horizontal Economizer                                                                                        | 15-25 tons       | ✓               |                   |
| <b>Downflow Accessories</b>                                      |                                                                                                              |                  |                 |                   |
| D25FD180300                                                      | 25% Manual Fresh Air Damper                                                                                  | 15-25 tons       | ✓               |                   |
| D25MFD180300                                                     | 25% Motorized Fresh Air Damper                                                                               | 15-25 tons       | ✓               |                   |
| D50MFD180300                                                     | 50% Motorized Fresh Air Damper                                                                               | 15-25 tons       | ✓               |                   |
| DDNBB180300                                                      | Burglar Bar Sleeves with Supply and Return                                                                   | 15-25 tons       | ✓               |                   |
| <b>Horizontal Accessories</b>                                    |                                                                                                              |                  |                 |                   |
| HZCURB180300EDR                                                  | Horizontal Curb End Discharge Roofed In                                                                      | 15-25 tons       | ✓               |                   |
| HZCURB180300NSR                                                  | Horizontal Curb Non-Service Side Discharge Roofed In                                                         | 15-25 tons       | ✓               |                   |
| HZCURB180300SSR                                                  | Horizontal Curb Service Side Discharge Roofed In                                                             | 15-25 tons       | ✓               |                   |
| HZCURB180300EDS                                                  | Horizontal Curb End Discharge Slab Mount                                                                     | 15-25 tons       | ✓               |                   |
| HZCURB180300NSS                                                  | Horizontal Curb Non-Service Side Discharge Slab Mount                                                        | 15-25 tons       | ✓               |                   |
| HZCURB180300SSS                                                  | Horizontal Curb Service Side Discharge Slab Mount                                                            | 15-25 tons       | ✓               |                   |
| DHZE25FD180300                                                   | Horizontal Fresh Air Damper 25%                                                                              | 15-25 tons       | ✓               |                   |
| DHZRETPNL180300                                                  | Horizontal Return Panel                                                                                      | 15-25 tons       | ✓               |                   |
| <b>Concentrics</b>                                               |                                                                                                              |                  |                 |                   |
| CDK180                                                           | Concentric Duct Kit                                                                                          | 15 tons          | ✓               |                   |
| CDK240                                                           | Concentric Duct Kit                                                                                          | 20 tons          | ✓               |                   |
| CDK300                                                           | Concentric Duct Kit Flush Mount Diffuser                                                                     | 25 tons          | ✓               |                   |
| <b>DDC Accessories<sup>3</sup></b>                               |                                                                                                              |                  |                 |                   |
|                                                                  | DDC communicating controller (built-in BACnet® MS/TP) includes Standard Room Sensor to be installed in field | 15-25 tons       |                 | ✓                 |
| 10366D11B                                                        | DDC Ultra Low-Leak Downflow Economizer                                                                       | 15-25 tons       | ✓               | ✓                 |
| 10465DDC                                                         | Power Exhaust kit used with DDC Ultra Low-Leak Economizer                                                    | 15-25 tons       | ✓               |                   |
| DLAKT03                                                          | Low-Ambient                                                                                                  | 15-20 tons       | ✓               | ✓                 |
| LONKT01                                                          | LonWorks® card                                                                                               | 15-25 tons       | ✓               |                   |
| 3PMK01                                                           | Phase Monitor (3-Phase Only)                                                                                 | 15-25 tons       | ✓               | ✓                 |
| DFSKT02                                                          | Dirty Filter Switch                                                                                          | 15-25 tons       | ✓               |                   |

# DCC/DCG Packaged Units

15 to 25 Tons (cont.)

| Daikin Master Item #           | Description                                                          | Fits Model Sizes | Field-Installed | Factory-Installed |
|--------------------------------|----------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>High-Static Kits</b>        |                                                                      |                  |                 |                   |
| HSKTW180-3FI                   | High static, factory-installed, 230V                                 | 15 ton, AC only  |                 | ✓                 |
| HSKTW180-4FI                   | High static, factory-installed, 460V                                 | 15 ton, AC only  |                 | ✓                 |
| HSKTW180-7FI                   | High static, factory-installed, 575V                                 | 15 ton, AC only  |                 | ✓                 |
| HSKTW240-3FI                   | High static, factory-installed, 230V                                 | 20 ton           |                 | ✓                 |
| HSKTW240-4FI                   | High static, factory-installed, 460V                                 | 20 ton           |                 | ✓                 |
| HSKTW240-7FI                   | High static, factory-installed, 575V                                 | 20 ton           |                 | ✓                 |
| HSKTW300AC-FI                  | High static, factory-installed, 25 ton, all voltages                 | 25 ton, AC only  |                 | ✓                 |
| HSKTW300GAS-FI                 | High static, factory-installed, 25 ton, all voltages                 | 25 ton, Gas only |                 | ✓                 |
| <b>Crankcase Heater Kits</b>   |                                                                      |                  |                 |                   |
| 0130L00017S                    | 70W 230V                                                             | 15-20 tons       | ✓               |                   |
| 0130L00018S                    | 70W 460V                                                             | 15-20 tons       | ✓               |                   |
| 0130L00019S                    | 70W 575V                                                             | 15-20 tons       | ✓               |                   |
| 0130L00020S                    | 90W 230V                                                             | 25 tons          | ✓               |                   |
| 0130L00021S                    | 90W 460V                                                             | 25 tons          | ✓               |                   |
| 0130L00022S                    | 90W 575V                                                             | 25 tons          | ✓               |                   |
| <b>High Efficiency Filters</b> |                                                                      |                  |                 |                   |
| 0160L00202                     | High Efficiency MERV 13 Air Filter Nom. Size: 20x25x2; (Order Qty 6) | 15, 20 tons      | ✓               |                   |
| 0160L00201                     | High Efficiency MERV 13 Air Filter Nom. Size: 20x20x2; (Order Qty 8) | 25 tons          | ✓               |                   |
| <b>Misc Accessories</b>        |                                                                      |                  |                 |                   |
|                                | Convenience Outlet: Powered                                          | 15-25 tons       |                 | ✓                 |
|                                | Convenience Outlet: Non-Powered                                      | 15-25 tons       |                 | ✓                 |
|                                | Disconnect Switch (non-fused)                                        | 15-25 tons       |                 | ✓                 |
| LAKT23                         | Low-Ambient Kit, 208-230V - non-DDC                                  | 15-20 tons       | ✓               | ✓                 |
| LAKT24                         | Low-Ambient Kit, 460V - non-DDC                                      | 15-20 tons       | ✓               | ✓                 |
| LAKT25                         | Low-Ambient Kit, 575V - non-DDC                                      | 15-20 tons       | ✓               | ✓                 |
| LAKT05                         | Low-Ambient Kit (all voltages) - non-DDC                             | 25 tons          | ✓               | ✓                 |
| LPKT180300A                    | LP Conversion Kit                                                    | 15-25 tons       | ✓               |                   |
| 3PMNDK01                       | Phase Monitor - non-DDC                                              | 15-25 tons       | ✓               | ✓                 |
|                                | Smoke Detector (supply and/or return air)                            | 15-25 tons       |                 | ✓                 |
|                                | Hinged Panels                                                        | 15-25 tons       |                 | ✓                 |
| FSKT02A                        | Freeze Stat Kit <sup>1</sup>                                         | 25 tons          | ✓               |                   |
| HA036300                       | High-Altitude Kit                                                    | 15-25 tons       | ✓               |                   |
| LPKT180300A                    | LP Conversion Kit                                                    | 15-25 tons       | ✓               |                   |
| 220-GX-003                     | Flue Extension Kit                                                   | 15-25 tons       | ✓               |                   |

<sup>1</sup> Use Economizer & Power Exhaust listed within Ultra Low-Leak section

<sup>2</sup> Use Economizer & Power Exhaust listed within Low-Leak section

<sup>3</sup> For a full list of DDC accessories, please refer to DDC Controller Technical Guide manual (DK-DDC-TGD-01B)

<sup>4</sup> FSK02A is standard on 2 speed, V, models.

Note: Where multiple variations are available, the heaviest combination is listed.

# DTC/DTH/DTG Packaged Units

## 3 to 5 Tons

| Daikin Master Item #                                             | Description                                                                                                     | Fits Model Sizes | Field-Installed | Factory-Installed |
|------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>Curb</b>                                                      |                                                                                                                 |                  |                 |                   |
| 14CURB3672                                                       | 14" Roof Curb                                                                                                   | 3-5 tons         | ✓               |                   |
| 18CURB3672B                                                      | 18" Roof Curb                                                                                                   | 3-5 tons         | ✓               |                   |
| 24CURB3672B                                                      | 24" Roof Curb                                                                                                   | 3-5 tons         | ✓               |                   |
| GHRC-3672                                                        | Hurricane Restraint Clips                                                                                       | 3-5 tons         | ✓               |                   |
| <b>Ultra Low-Leak Economizer &amp; Power Exhaust<sup>1</sup></b> |                                                                                                                 |                  |                 |                   |
| 10-366-09C                                                       | Ultra Low-Leak Downflow Economizer w/ Enthalpy                                                                  | 3-5 Tons         | ✓               | ✓                 |
| 10-396-09                                                        | Ultra Low-Leak Horizontal Economizer w/ Enthalpy                                                                | 3-5 Tons         | ✓               |                   |
| 10-465-09-21                                                     | Prop Power Exhaust 230v                                                                                         | 3-5 Tons         | ✓               |                   |
| <b>Low-Leak Economizer &amp; Power Exhaust<sup>2</sup></b>       |                                                                                                                 |                  |                 |                   |
| DDNECNJ3672C                                                     | Low-Leak Downflow Economizer                                                                                    | 3-5 tons         | ✓               | ✓                 |
| DPE36722                                                         | Downflow Power Exhaust (208/230 Volt)                                                                           | 3-5 tons         | ✓               |                   |
| DHZEENJ3672                                                      | Horizontal Economizer                                                                                           | 3-5 tons         | ✓               |                   |
| DHPE36722                                                        | Horizontal Power Exhaust (208/230 Volt)                                                                         | 3-5 tons         | ✓               |                   |
| <b>Downflow Accessories</b>                                      |                                                                                                                 |                  |                 |                   |
| D25FD3672                                                        | 25% Manual Fresh Air Damper                                                                                     | 3-5 tons         | ✓               |                   |
| D25MFD3672                                                       | 25% Motorized Fresh Air Damper                                                                                  | 3-5 tons         | ✓               |                   |
| DDNBBS3672                                                       | Burglar Bar Sleeves with Supply & Return                                                                        | 3-5 tons         | ✓               |                   |
| DDNECNJ3672NR                                                    | Downflow Economizer <sup>2</sup> w/o Barometric Relief                                                          | 3-5 tons         | ✓               |                   |
| DDNSQRD3616                                                      | Downflow Square-to-Round Adapter (16" Round)                                                                    | 3 tons           | ✓               |                   |
| DDNSQRD487218                                                    | Downflow Square-to-Round Adapter (18" Round)                                                                    | 4-5 tons         | ✓               |                   |
| <b>Horizontal Accessories</b>                                    |                                                                                                                 |                  |                 |                   |
| DBRD3672                                                         | Horizontal Barometric Relief Damper                                                                             | 3-5 tons         | ✓               |                   |
| <b>Concentrics</b>                                               |                                                                                                                 |                  |                 |                   |
| CDK36                                                            | Concentric Duct Kit                                                                                             | 3 tons           | ✓               |                   |
| CDK4872                                                          | Concentric Duct Kit                                                                                             | 4-5 tons         | ✓               |                   |
| <b>1 phase 208-230V Electric Heat Kits</b>                       |                                                                                                                 |                  |                 |                   |
| SPKT01                                                           | Single Point Wiring Kit 1 phase Heat Kits                                                                       | 3-5 tons         | ✓               | ✓                 |
| EHK1-10                                                          | 10kw 208-230 1ph Electric Heat Kit                                                                              | 3-5 tons         | ✓               | ✓                 |
| EHK1-15                                                          | 15kw 208-230 1ph Electric Heat Kit                                                                              | 3-5 tons         | ✓               | ✓                 |
| EHK1-18                                                          | 18kw 208-230 1ph Electric Heat Kit                                                                              | 4 tons           | ✓               | ✓                 |
| EHK1-20                                                          | 20kw 208-230 1ph Electric Heat Kit                                                                              | 5 tons           | ✓               | ✓                 |
| <b>3 phase 208-230V Electric Heat Kits</b>                       |                                                                                                                 |                  |                 |                   |
| SPKT03                                                           | Single Point Wiring Kit 3 phase Heat Kits                                                                       | 3-5 tons         | ✓               | ✓                 |
| EHK3-10                                                          | 10kw 208-230 3ph Electric Heat Kit                                                                              | 3-5 tons         | ✓               | ✓                 |
| EHK3-15                                                          | 15kw 208-230 3ph Electric Heat Kit                                                                              | 3-5 tons         | ✓               | ✓                 |
| EHK3-18                                                          | 18kw 208-230 3ph Electric Heat Kit                                                                              | 4 tons           | ✓               | ✓                 |
| EHK3-20                                                          | 20kw 208-230 3ph Electric Heat Kit                                                                              | 5 tons           | ✓               | ✓                 |
| <b>DDC Accessories<sup>3</sup></b>                               |                                                                                                                 |                  |                 |                   |
|                                                                  | DDC communicating controller (built-in BACnet® MS/TP)<br>includes Standard Room Sensor to be installed in field | 3-5 tons         |                 | ✓                 |
| 10366D09C                                                        | DDC Ultra Low-Leak Downflow Economizer                                                                          | 3-5 tons         | ✓               | ✓                 |
| 10396D09                                                         | DDC Ultra Low-Leak Horizontal Economizer                                                                        | 3-5 tons         | ✓               |                   |
| 10465DDC                                                         | Power Exhaust kit used with DDC Ultra Low-Leak Economizer                                                       | 3-5 tons         | ✓               |                   |
| DLAKT01                                                          | Low-Ambient                                                                                                     | 3-5 tons         | ✓               | ✓                 |
| LONKT01                                                          | LonWorks® card                                                                                                  | 3-5 tons         | ✓               |                   |
| 3PMK01                                                           | Phase Monitor (3-Phase Only)                                                                                    | 3-5 tons         | ✓               | ✓                 |
| DFSKT01                                                          | Dirty Filter Switch                                                                                             | 3-5 tons         | ✓               |                   |

## DTC/DTH/DTG Packaged Units

3 to 5 Tons (cont.)

| Daikin Master Item #           | Description                                                          | Fits Model Sizes | Field-Installed | Factory-Installed |
|--------------------------------|----------------------------------------------------------------------|------------------|-----------------|-------------------|
| <b>Crankcase Heater Kits</b>   |                                                                      |                  |                 |                   |
| 0163R00002S                    | 40W 230V                                                             | 3 tons           | √               |                   |
| 0130L00017S                    | 70W 230V                                                             | 4 - 5 tons       | √               |                   |
| <b>High Efficiency Filters</b> |                                                                      |                  |                 |                   |
| 0160L00203                     | High Efficiency MERV 13 Air Filter Nom. Size: 24x24x2; (Order Qty 1) | 3 tons           | √               |                   |
| 0160L00204                     | High Efficiency MERV 13 Air Filter Nom. Size: 14x20x2; (Order Qty 4) | 4 tons           | √               |                   |
| 0160L00205                     | High Efficiency MERV 13 Air Filter Nom. Size: 16x20x2; (Order Qty 4) | 5 tons           | √               |                   |
| <b>Misc Accessories</b>        |                                                                      |                  |                 |                   |
| HAILGD03D                      | Condenser Coil Hail Guard                                            | 3-5 tons         | √               |                   |
| HAILGD04D                      | Condenser Coil Hail Guard                                            | 5 tons           | √               |                   |
|                                | Convenience Outlet: Non-Powered                                      | 3-5 tons         |                 | √                 |
|                                | Convenience Outlet: Powered                                          | 3-5 tons         |                 | √                 |
| HA036300                       | High Altitude Kit                                                    | 3-5 tons         | √               |                   |
| LPM-07                         | LP Conversion Kit (DTG036045 only)                                   | 3 tons           | √               |                   |
| LPM-08                         | LP Conversion Kit (DTG units only)                                   | 3-5 tons         | √               |                   |
| LAKT11                         | Low Ambient Kit, 208-230V - non-DDC                                  | 3-4 tons         | √               | √                 |
| LAKT12                         | Low Ambient Kit, 208-230V - non-DDC                                  | 5 tons           | √               | √                 |
| 3PMNDK01                       | Phase Monitor (3-Phase Only) - Non DDC                               | 3-5 tons         | √               | √                 |
|                                | Smoke Detector (supply and/or return air)                            | 3-5 tons         |                 | √                 |
|                                | Hinged Panels                                                        | 3-5 tons         |                 | √                 |
| 220-GX-001                     | Flue Extension Kit                                                   | 3-5 tons         | √               |                   |

<sup>1</sup> Use Economizer & Power Exhaust listed within Ultra Low-Leak section

<sup>2</sup> Use Economizer & Power Exhaust listed within Low-Leak section

<sup>3</sup> For a full list of DDC accessories, please refer to DDC Controller Technical Guide manual (DK-DDC-TGD-01B)

Note: Where multiple variations are available, the heaviest combination is listed.

# Light Commercial Packaged Units

## DP14CM/DP14HM

| Accessory Item # | Description                                                    | Fits Chassis Size |
|------------------|----------------------------------------------------------------|-------------------|
| 20464501NGK      | Horizontal Duct Cover                                          | Medium            |
| 20464502NGK      | Horizontal Duct Cover                                          | Large             |
| CDK36            | Concentric Kit                                                 | Medium            |
| CDK4872          | Concentric Kit                                                 | Large             |
| DDNECNJPCHMM     | Downflow Economizer                                            | Medium            |
| DDNECNJPCHML     | Downflow Economizer                                            | Large             |
| DDNIFRPCHMM      | Downflow Internal Filter Rack                                  | Medium            |
| DDNIFRPCHML      | Downflow Internal Filter Rack                                  | Large             |
| DHZECNJPGCHM     | Horizontal Economizer                                          | Medium            |
| DHZECNJPGCHL     | Horizontal Economizer                                          | Large             |
| DPHFRA           | External Horizontal Filter Rack                                | All Sizes         |
| DDN25FDPGCHMM    | 25% Manual Downflow Fresh Air Damper                           | Medium            |
| DDN25FDPGCHML    | 25% Manual Downflow Fresh Air Damper                           | Large             |
| DHZ25FDPGCHMM    | 25% Manual Horizontal Fresh Air Damper                         | Medium            |
| DHZ25FDPGCHML    | 25% Manual Horizontal Fresh Air Damper                         | Large             |
| DDN25MFDPGCHMM   | 25% Motorized Downflow Fresh Air Damper                        | Medium            |
| DDN25MFDPGCHML   | 25% Motorized Downflow Fresh Air Damper                        | Large             |
| DHZ25MFDPGCHMM   | 25% Motorized Horizontal Fresh Air Damper                      | Medium            |
| DHZ25MFDPGCHML   | 25% Motorized Horizontal Fresh Air Damper                      | Large             |
| OT/EHR18-60      | Outdoor Thermostat & Emergency Heat Relay Kit                  | All Sizes         |
| OT18-60A         | Outdoor Thermostat Kit w/ Lockout Stat                         | All Sizes         |
| D14CRBPGCHMA     | Roof Curb                                                      | All Sizes         |
| SQRPG101/102     | Square-to-Round Adapter w/16" Round for Downflow Application   | Medium            |
| SQRPG103         | Square-to-Round Adapter w/18" Round for Downflow Application   | Large             |
| SQRPGH101/102    | Square-to-Round Adapter w/16" Round for Horizontal Application | Medium            |
| SQRPGH103        | Square-to-Round Adapter w/18" Round for Horizontal Application | Large             |

| Accessory Item # | Description                                                    | Fits Chassis Size  |
|------------------|----------------------------------------------------------------|--------------------|
| 20464501NGK      | Horizontal Duct Cover                                          | Medium             |
| 20464502NGK      | Horizontal Duct Cover                                          | Large              |
| CDK36            | Concentric Kit                                                 | Medium             |
| CDK4872          | Concentric Kit                                                 | Large              |
| DDNECNJPGMM      | Downflow Economizer                                            | Medium             |
| DDNECNJPGML      | Downflow Economizer                                            | Large              |
| DDNIFRPGMM       | Downflow Internal Filter Rack (with economizer)                | Medium             |
| DDNIFRPGA        | Downflow Internal Filter Rack (no economizer)                  | All Sizes          |
| DHZECNJPGCHM     | Horizontal Economizer                                          | Medium             |
| DHZECNJPGCHL     | Horizontal Economizer                                          | Large              |
| DPHFRA           | External Horizontal Filter Rack                                | All Sizes          |
| DHZIFRPGCHA      | Internal Horizontal Filter Rack                                | All Sizes          |
| DDN25FDPGCHMM    | 25% Manual Downflow Fresh Air Damper                           | Medium             |
| DDN25FDPGCHML    | 25% Manual Downflow Fresh Air Damper                           | Large              |
| DHZ25FDPGCHMM    | 25% Manual Horizontal Fresh Air Damper                         | Medium             |
| DHZ25FDPGCHML    | 25% Manual Horizontal Fresh Air Damper                         | Large              |
| DDN25MFDPGCHMM   | 25% Motorized Downflow Fresh Air Damper                        | Medium             |
| DDN25MFDPGCHML   | 25% Motorized Downflow Fresh Air Damper                        | Large              |
| DHZ25MFDPGCHMM   | 25% Motorized Horizontal Fresh Air Damper                      | Medium             |
| DHZ25MFDPGCHML   | 25% Motorized Horizontal Fresh Air Damper                      | Large              |
| HA036300         | High-Altitude Kit                                              | All Sizes          |
| LPM-07           | LP Conversion Kit (Single-Stage Models)                        | 3 and 4 ton models |
| LPM-08           | LP Conversion Kit (Two-Stage Models)                           | 5 ton models       |
| OTDFPKG-01       | Outdoor Thermostat with Housing                                | All Sizes          |
| D14CRBPGCHMA     | Roof Curb                                                      | All Sizes          |
| SQRPG101/102     | Square-to-Round Adapter w/16" Round for Downflow Application   | Medium             |
| SQRPG103         | Square-to-Round Adapter w/18" Round for Downflow Application   | Large              |
| SQRPGH101/102    | Square-to-Round Adapter w/16" Round for Horizontal Application | Medium             |
| SQRPGH103        | Square-to-Round Adapter w/18" Round for Horizontal Application | Large              |

# Split Systems

## Air Conditioners/Heat Pumps

### Air Conditioners

| Item #              | Description                        |
|---------------------|------------------------------------|
| ABK-20              | Anchor Bracket Kit <sup>^</sup>    |
| ASC-01              | Anti-Short Cycle Kit               |
| FSK01A <sup>1</sup> | Freeze Protection Kit <sup>2</sup> |
| LSK01A <sup>2</sup> | Liquid Line Solenoid Kit           |
| LAKT01              | Low-Ambient Kit                    |
| 0163R00002          | Crankcase heater                   |
| 0163R00003          | Crankcase heater                   |
| 0163R00004          | Crankcase Heater                   |
| OY18-60A            | Outdoor Thermostat                 |
| TX3N4 <sup>2</sup>  | TXV Kit                            |
| TX5N4 <sup>2</sup>  | TXV Kit                            |

<sup>^</sup> Contains 20 brackets; four brackets needed to anchor unit to pad

<sup>1</sup> Installed on indoor coil

<sup>2</sup> Field-installed, non-bleed, expansion valve kit — Condensing units and heat pumps with reciprocating compressors require the use of start-assist components when used in conjunction with an indoor coil using a non-bleed thermal expansion valve refrigerant metering device or liquid line solenoid kit. The TXV should always be sized based on the tonnage of the outdoor unit.

### Heat Pumps

| Item #                | Description                     |
|-----------------------|---------------------------------|
| 0130R00000S           | Low-pressure Switch Kit         |
| ABK-20                | Anchor Bracket Kit <sup>^</sup> |
| ASC-01                | Anti-Short Cycle Kit            |
| AFE18-60A             | All-fuel Kit                    |
| LAKT-01               | Low-Ambient Kit                 |
| FSK01A <sup>1</sup>   | Freeze Protection Kit           |
| OT18-60A <sup>2</sup> | Outdoor Thermostat              |
| OT/EHR18-60           | Emergency Heat Relay kit        |
| TX3N4 <sup>2</sup>    | TXV Kit                         |
| TX5N4 <sup>2</sup>    | TXV Kit                         |

<sup>^</sup> Contains 20 brackets; four brackets needed to anchor unit to pad

<sup>1</sup> Installed on indoor coil

<sup>2</sup> Required for heat pump applications where ambient temperatures fall below 0°F with 50% or higher relative humidity.

# DSC/DSH Packaged Unit Heat Kit Match-Ups

3 to 5 Tons

## DSC — Heat Kit Usage

### Single-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DSC036***1D*** | 24.7 / 24.7 | 40 / 40   | ---         | ---                       |
| EHK1-10        | 48.2 / 55.2 | 50 / 60   | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK1-15        | 70.8 / 81.2 | 80 / 90   | 11.3 / 15.0 | 1400-1440 CFM             |
| DSC048***1D*** | 29.0 / 29.0 | 45 / 45   | ---         | ---                       |
| EHK1-10        | 48.6 / 55.6 | 50 / 60   | 7.5 / 10.0  | 1400-1800 CFM             |
| EHK1-15        | 71.3 / 81.6 | 80 / 90   | 11.3 / 15.0 | 1575-1800 CFM             |
| EHK1-18        | 84.8 / 97.3 | 90 / 100  | 13.5 / 18.0 | 1575-1800 CFM             |
| DSC060***1D*** | 41.3 / 41.3 | 60 / 60   | ---         | ---                       |
| EHK1-10        | 53.8 / 60.8 | 60 / 70   | 7.5 / 10.0  | 1750-2250 CFM             |
| EHK1-15        | 76.4 / 86.8 | 80 / 90   | 11.3 / 15.0 | 1750-2250 CFM             |
| EHK1-20        | 98.9 / 113  | 100 / 125 | 15.0 / 20.0 | 1850-2250 CFM             |

### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP     | kW*         | Recommended Airflow Range |
|----------------|-------------|---------|-------------|---------------------------|
| DSC036***3D*** | 16.9 / 16.9 | 25 / 25 | ---         | ---                       |
| EHK3-10        | 29.1 / 33.1 | 30 / 35 | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK3-15        | 42.2 / 48.2 | 45 / 50 | 11.3 / 15.0 | 1400-1440 CFM             |
| DSC036***3B*** | 17.9 / 17.9 | 25 / 25 | ---         | ---                       |
| EHK3-10        | 30.3 / 34.3 | 35 / 35 | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK3-15        | 43.4 / 49.4 | 45 / 50 | 11.3 / 15.0 | 1400-1440 CFM             |
| DSC048***3D*** | 20.6 / 20.6 | 30 / 30 | ---         | ---                       |
| EHK3-10        | 29.5 / 33.5 | 35 / 35 | 7.5 / 10.0  | 1400-1800 CFM             |
| EHK3-15        | 42.6 / 48.6 | 45 / 50 | 11.3 / 15.0 | 1575-1800 CFM             |
| EHK3-18        | 50.4 / 57.6 | 60 / 60 | 13.5 / 18.0 | 1575-1800 CFM             |
| DSC048***3B*** | 21.2 / 21.2 | 30 / 30 | ---         | ---                       |
| EHK3-10        | 30.3 / 34.3 | 35 / 35 | 7.5 / 10.0  | 1400-1800 CFM             |
| EHK3-15        | 43.4 / 49.4 | 45 / 50 | 11.3 / 15.0 | 1575-1800 CFM             |
| EHK3-18        | 51.1 / 58.4 | 60 / 60 | 13.5 / 18.0 | 1575-1800 CFM             |
| DSC060***3D*** | 28.3 / 28.3 | 40 / 40 | ---         | ---                       |
| EHK3-10        | 34.6 / 38.6 | 40 / 40 | 7.5 / 10.0  | 1750 - 2250 CFM           |
| EHK3-15        | 47.8 / 53.8 | 50 / 60 | 11.3 / 15.0 | 1750 - 2250 CFM           |
| EHK3-20        | 60.6 / 68.6 | 70 / 70 | 15.0 / 20.0 | 1850 - 2250 CFM           |
| DSC060***3B*** | 24.6 / 24.6 | 40 / 40 | ---         | ---                       |
| EHK3-10        | 30.0 / 34.0 | 40 / 40 | 7.5 / 10.0  | 1750 - 2250 CFM           |
| EHK3-15        | 43.1 / 49.1 | 45 / 50 | 11.3 / 15.0 | 1750 - 2250 CFM           |
| EHK3-20        | 56.0 / 64.0 | 60 / 70 | 15.0 / 20.0 | 1850 - 2250 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DSH — Heat Kit Usage

### Single-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DSH036***1D*** | 24.7 / 24.7 | 40 / 40   | ---         | ---                       |
| EHK1-10        | 69.8 / 76.8 | 70 / 80   | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK1-15        | 92.4 / 103  | 100 / 110 | 11.3 / 15.0 | 1400-1440 CFM             |
| DSH048***1D*** | 29.1 / 29.1 | 45 / 45   | ---         | ---                       |
| EHK1-10        | 74.2 / 81.2 | 80 / 90   | 7.5 / 10.0  | 1400-1800 CFM             |
| EHK1-15        | 96.9 / 107  | 100 / 110 | 11.3 / 15.0 | 1575-1800 CFM             |
| EHK1-18        | 110 / 123   | 110 / 125 | 13.5 / 18.0 | 1575-1800 CFM             |
| DSH060***1D*** | 40.2 / 40.2 | 60 / 60   | ---         | ---                       |
| EHK1-10        | 85.3 / 92.3 | 90 / 100  | 7.5 / 10.0  | 1750-2250 CFM             |
| EHK1-15        | 108 / 118   | 110 / 125 | 11.3 / 15.0 | 1750-2250 CFM             |
| EHK1-20        | 130 / 144   | 150 / 150 | 15.0 / 20.0 | 1850-2250 CFM             |

### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP     | kW*         | Recommended Airflow Range |
|----------------|-------------|---------|-------------|---------------------------|
| DSH036***3D*** | 16.9 / 16.9 | 25 / 25 | ---         | ---                       |
| EHK3-10        | 42.9 / 46.9 | 45 / 50 | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK3-15        | 56.0 / 62.0 | 60 / 70 | 11.3 / 15.0 | 1400-1440 CFM             |
| DSH036***3B*** | 17.9 / 17.9 | 25 / 25 | ---         | ---                       |
| EHK3-10        | 43.9 / 47.9 | 45 / 50 | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK3-15        | 57.0 / 63.0 | 60 / 70 | 11.3 / 15.0 | 1400-1440 CFM             |
| DSH048***3D*** | 20.6 / 20.6 | 30 / 30 | ---         | ---                       |
| EHK3-10        | 46.6 / 50.6 | 50 / 60 | 7.5 / 10.0  | 1400-1800 CFM             |
| EHK3-15        | 59.8 / 65.8 | 60 / 70 | 11.3 / 15.0 | 1575-1800 CFM             |
| EHK3-18        | 67.5 / 74.8 | 70 / 80 | 13.5 / 18.0 | 1575-1800 CFM             |
| DSH048***3B*** | 21.2 / 21.2 | 30 / 30 | ---         | ---                       |
| EHK3-10        | 47.2 / 51.2 | 50 / 60 | 7.5 / 10.0  | 1400-1800 CFM             |
| EHK3-15        | 60.4 / 66.4 | 70 / 70 | 11.3 / 15.0 | 1575-1800 CFM             |
| EHK3-18        | 68.1 / 75.4 | 70 / 80 | 13.5 / 18.0 | 1575-1800 CFM             |
| DSH060***3D*** | 29.1 / 29.1 | 45 / 45 | ---         | ---                       |
| EHK3-10        | 55.1 / 59.1 | 60 / 60 | 7.5 / 10.0  | 1750-2250 CFM             |
| EHK3-15        | 68.2 / 74.2 | 70 / 80 | 11.3 / 15.0 | 1750-2250 CFM             |
| EHK3-20        | 81.1 / 89.1 | 90 / 90 | 15.0 / 20.0 | 1850-2250 CFM             |
| DSH060***3B*** | 25.5 / 25.5 | 40 / 40 | ---         | ---                       |
| EHK3-10        | 51.5 / 55.5 | 60 / 60 | 7.5 / 10.0  | 1750-2250 CFM             |
| EHK3-15        | 64.6 / 70.6 | 70 / 80 | 11.3 / 15.0 | 1750-2250 CFM             |
| EHK3-20        | 77.5 / 85.5 | 80 / 90 | 15.0 / 20.0 | 1850-2250 CFM             |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

# DSC/DSH Packaged Unit Heat Kit Match-Ups

## 3 to 5 Tons (cont.)

### DSC — Heat Kit Usage

#### Three-Phase Units @ 480V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DSC036***4B*** | 9.6  | 15  | ---  | ---                       |
| EHK4-10        | 17.1 | 20  | 10.0 | 1250-1350 CFM             |
| EHK4-15        | 24.6 | 25  | 15.0 | 1400-1440 CFM             |
| DSC048***4B*** | 10.0 | 15  | ---  | ---                       |
| EHK4-10        | 17.1 | 20  | 10.0 | 1400-1800 CFM             |
| EHK4-15        | 24.6 | 25  | 15.0 | 1575-1800 CFM             |
| EHK4-18        | 29.3 | 30  | 18.0 | 1575-1800 CFM             |
| DSC060***4B*** | 11.9 | 15  | ---  | ---                       |
| EHK4-10        | 16.9 | 20  | 10.0 | 1750 - 2250 CFM           |
| EHK4-15        | 24.4 | 25  | 15.0 | 1750 - 2250 CFM           |
| EHK4-20        | 31.9 | 35  | 20.0 | 1850 - 2250 CFM           |

#### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DSC036***7B*** | 7.6  | 15  | ---  | ---                       |
| EHK7-10        | 15.4 | 20  | 10.0 | 1250-1350 CFM             |
| EHK7-15        | 21.8 | 25  | 15.0 | 1400-1440 CFM             |
| DSC048***7B*** | 8.3  | 15  | ---  | ---                       |
| EHK7-10        | 15.4 | 20  | 10.0 | 1400-1800 CFM             |
| EHK7-15        | 21.8 | 25  | 15.0 | 1575-1800 CFM             |
| EHK7-18        | 25.5 | 30  | 18.0 | 1575-1800 CFM             |
| DSC060***7B*** | 8.9  | 15  | ---  | ---                       |
| EHK7-10        | 14.0 | 15  | 10.0 | 1750-2250 CFM             |
| EHK7-15        | 20.4 | 25  | 15.0 | 1750-2250 CFM             |
| EHK7-20        | 26.5 | 30  | 20.0 | 1850-2250 CFM             |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

### DSH — Heat Kit Usage

#### Three-Phase Units @ 480V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DSH036***4B*** | 9.6  | 15  | ---  | ---                       |
| EHK4-10        | 24.6 | 25  | 10.0 | 1250-1350 CFM             |
| EHK4-15        | 32.1 | 35  | 15.0 | 1400-1440 CFM             |
| DSH048***4B*** | 10.0 | 15  | ---  | ---                       |
| EHK4-10        | 25.0 | 25  | 10.0 | 1400-1800 CFM             |
| EHK4-15        | 32.5 | 35  | 15.0 | 1575-1800 CFM             |
| EHK4-18        | 37.1 | 40  | 18.0 | 1575-1800 CFM             |
| DSH060***4B*** | 12.3 | 20  | ---  | ---                       |
| EHK4-10        | 27.3 | 30  | 10.0 | 1750-2250 CFM             |
| EHK4-15        | 34.8 | 35  | 15.0 | 1750-2250 CFM             |
| EHK4-20        | 42.3 | 45  | 20.0 | 1850-2250 CFM             |

#### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DSH036***7B*** | 7.6  | 15  | ---  | ---                       |
| EHK7-10        | 20.1 | 25  | 10.0 | 1400-1475 CFM             |
| EHK7-15        | 26.5 | 30  | 15.0 | 1575-1650 CFM             |
| DSH048***7B*** | 8.3  | 15  | ---  | ---                       |
| EHK7-10        | 20.8 | 25  | 10.0 | 1400-1800 CFM             |
| EHK7-15        | 27.2 | 30  | 15.0 | 1575-1800 CFM             |
| EHK7-18        | 30.9 | 35  | 18.0 | 1575-1800 CFM             |
| DSH060***7B*** | 9.2  | 15  | ---  | ---                       |
| EHK7-10        | 21.7 | 25  | 10.0 | 1750-2250 CFM             |
| EHK7-15        | 28.1 | 30  | 15.0 | 1750-2250 CFM             |
| EHK7-20        | 34.2 | 35  | 20.0 | 1850-2250 CFM             |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

# DTC/DTH Packaged Unit Heat Kit Match-Ups

3 to 5 Tons

## DTC — Heat Kit Usage

### Single and Three Phase Units @ 208 / 240V

| Model          | MCA         | MOP     | kW*         | Recommended Airflow Range |
|----------------|-------------|---------|-------------|---------------------------|
| DTC036***1D*** | 22.9 / 22.9 | 35 / 35 | ---         | ---                       |
| EHK1-10        | 50.0 / 57.0 | 50 / 60 | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK1-15        | 72.6 / 83.0 | 80 / 90 | 11.3 / 15.0 | 1250-1440 CFM             |
| DTC036***3D*** | 16.5 / 16.5 | 25 / 25 | ---         | ---                       |
| EHK3-10        | 30.9 / 34.9 | 35 / 35 | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK3-15        | 44.0 / 50.0 | 45 / 50 | 11.3 / 15.0 | 1250-1440 CFM             |

|                |             |          |             |               |
|----------------|-------------|----------|-------------|---------------|
| DTC048***1D*** | 33.1 / 33.1 | 50 / 50  | ---         | ---           |
| EHK1-10        | 53.8 / 60.8 | 60 / 70  | 7.5 / 10.0  | 1400-1800 CFM |
| EHK1-15        | 76.4 / 86.8 | 80 / 90  | 11.3 / 15.0 | 1575-1800 CFM |
| EHK1-18        | 89.9 / 102  | 90 / 110 | 13.5 / 18.0 | 1575-1800 CFM |
| DTC048***3D*** | 24.7 / 24.7 | 35 / 35  | ---         | ---           |
| EHK3-10        | 34.6 / 38.6 | 35 / 40  | 7.5 / 10.0  | 1400-1800 CFM |
| EHK3-15        | 47.8 / 53.8 | 50 / 60  | 11.3 / 15.0 | 1575-1800 CFM |
| EHK3-18        | 55.5 / 62.8 | 60 / 70  | 13.5 / 18.0 | 1575-1800 CFM |

|                |             |           |             |               |
|----------------|-------------|-----------|-------------|---------------|
| DTC060***1D*** | 40.2 / 40.2 | 60 / 60   | ---         | ---           |
| EHK1-10        | 53.8 / 60.8 | 60 / 70   | 7.5 / 10.0  | 1750-2250 CFM |
| EHK1-15        | 76.4 / 86.8 | 80 / 90   | 11.3 / 15.0 | 1750-2250 CFM |
| EHK1-20        | 98.9 / 113  | 100 / 125 | 15.0 / 20.0 | 1850-2250 CFM |
| DTC060***3D*** | 28.8 / 28.8 | 40 / 40   | ---         | ---           |
| EHK3-10        | 34.6 / 38.6 | 40 / 40   | 7.5 / 10.0  | 1750-2250 CFM |
| EHK3-15        | 47.8 / 53.8 | 50 / 60   | 11.3 / 15.0 | 1750-2250 CFM |
| EHK3-20        | 60.6 / 68.6 | 70 / 70   | 15.0 / 20.0 | 1850-2250 CFM |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DTH — Heat Kit Usage

### Single and Three Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DTH036***1D*** | 22.9 / 22.9 | 35 / 35   | ---         | ---                       |
| EHK1-10        | 68.1 / 75.1 | 70 / 80   | 7.5 / 10.0  | 1250-1350 CFM             |
| EHK1-15        | 90.7 / 101  | 100 / 110 | 11.3 / 15.0 | 1250-1440 CFM             |
| DTH036***3D*** | 16.5 / 16.5 | 25 / 25   | ---         | ---                       |
| EHK3-10        | 42.5 / 46.5 | 45 / 50   | 7.5 / 10.0  | 1250 - 1350 CFM           |
| EHK3-15        | 55.6 / 61.6 | 60 / 70   | 11.3 / 15.0 | 1250-1440 CFM             |

|                |             |           |             |                 |
|----------------|-------------|-----------|-------------|-----------------|
| DTH048***1D*** | 33.1 / 33.1 | 50 / 50   | ---         | ---             |
| EHK1-10        | 78.3 / 85.3 | 80 / 90   | 7.5 / 10.0  | 1400-1800 CFM   |
| EHK1-15        | 101 / 111   | 110 / 125 | 11.3 / 15.0 | 1575-1800 CFM   |
| EHK1-18        | 114 / 127   | 125 / 150 | 13.5 / 18.0 | 1575-1800 CFM   |
| DTH048***3D*** | 24.7 / 24.7 | 35 / 35   | ---         | ---             |
| EHK3-10        | 50.7 / 54.7 | 60 / 60   | 7.5 / 10.0  | 1400 - 1800 CFM |
| EHK3-15        | 63.9 / 69.9 | 70 / 70   | 11.3 / 15.0 | 1575 - 1800 CFM |
| EHK3-18        | 71.6 / 78.9 | 80 / 80   | 13.5 / 18.0 | 1575 - 1800 CFM |

|                |             |           |             |                 |
|----------------|-------------|-----------|-------------|-----------------|
| DTH060***1D*** | 40.2 / 40.2 | 60 / 60   | ---         | ---             |
| EHK1-10        | 85.3 / 92.3 | 100 / 100 | 7.5 / 10.0  | 1750-2250 CFM   |
| EHK1-15        | 108 / 118   | 110 / 125 | 11.3 / 15.0 | 1750-2250 CFM   |
| EHK1-20        | 130 / 144   | 150 / 150 | 15.0 / 20.0 | 1850-2250 CFM   |
| DTH060***3D*** | 29.1 / 29.1 | 45 / 45   | ---         | ---             |
| EHK3-10        | 55.1 / 59.1 | 60 / 60   | 7.5 / 10.0  | 1750 - 2250 CFM |
| EHK3-15        | 68.2 / 74.2 | 70 / 80   | 11.3 / 15.0 | 1750 - 2250 CFM |
| EHK3-20        | 81.1 / 89.1 | 90 / 90   | 15.0 / 20.0 | 1850 - 2250 CFM |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

# DCC/DCH Packaged Unit Heat Kit Match-Ups

## 6 Tons

### DCC — Heat Kit Usage

#### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP     | kW*         | Recommended Airflow Range |
|----------------|-------------|---------|-------------|---------------------------|
| DCC072***3V*** | 30.0 / 30.0 | 45 / 45 | ---         | ---                       |
| EHK3-10        | 33.5 / 37.5 | 45 / 45 | 7.5 / 10.0  | 2,100 - 2,700 CFM         |
| EHK3-15        | 46.6 / 52.6 | 50 / 60 | 11.3 / 15.0 | 2,100 - 2,700 CFM         |
| EHK3-20        | 59.5 / 67.5 | 60 / 70 | 15.0 / 20.0 | 2,100 - 2,700 CFM         |
| EHK3-25        | 72.6 / 82.6 | 80 / 90 | 18.8 / 25.0 | 2,100 - 2,700 CFM         |

#### Three-Phase Units @ 480V

|                |      |    |      |                   |
|----------------|------|----|------|-------------------|
| DCC072***4V*** | 14.3 | 20 | ---  | ---               |
| EHK4-10        | 18.6 | 20 | 10.0 | 2,100 - 2,700 CFM |
| EHK4-15        | 26.1 | 30 | 15.0 | 2,100 - 2,700 CFM |
| EHK4-20        | 33.6 | 35 | 20.0 | 2,100 - 2,700 CFM |
| EHK4-25        | 41.3 | 45 | 25.0 | 2,100 - 2,700 CFM |

#### Three-Phase Units @ 575V

|                |      |    |      |                   |
|----------------|------|----|------|-------------------|
| DCC072***7V*** | 11   | 15 | ---  | ---               |
| EHK7-10        | 15.5 | 20 | 10.0 | 2,100 - 2,700 CFM |
| EHK7-15        | 21.9 | 25 | 15.0 | 2,100 - 2,700 CFM |
| EHK7-20        | 28   | 30 | 20.0 | 2,100 - 2,700 CFM |
| EHK7-25        | 34.4 | 35 | 25.0 | 2,100 - 2,700 CFM |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

### DCH — Heat Kit Usage

#### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DCH072***3V*** | 30.0 / 30.0 | 45 / 45   | ---         | ---                       |
| EHK3-10        | 56.0 / 60.0 | 60 / 70   | 7.5 / 10.0  | 2,100 - 2,700 CFM         |
| EHK3-15        | 69.1 / 75.1 | 70 / 80   | 11.3 / 15.0 | 2,100 - 2,700 CFM         |
| EHK3-20        | 82.0 / 90.0 | 90 / 90   | 15.0 / 20.0 | 2,100 - 2,700 CFM         |
| EHK3-25        | 95.1 / 105  | 100 / 110 | 18.8 / 25.0 | 2,100 - 2,700 CFM         |

#### Three-Phase Units @ 480V

|                |      |    |      |                   |
|----------------|------|----|------|-------------------|
| DCH072***4V*** | 14.3 | 20 | ---  | ---               |
| EHK4-10        | 29.3 | 30 | 10.0 | 2,100 - 2,700 CFM |
| EHK4-15        | 36.8 | 40 | 15.0 | 2,100 - 2,700 CFM |
| EHK4-20        | 44.3 | 45 | 20.0 | 2,100 - 2,700 CFM |
| EHK4-25        | 52   | 60 | 25.0 | 2,100 - 2,700 CFM |

#### Three-Phase Units @ 575V

|                |      |    |      |                   |
|----------------|------|----|------|-------------------|
| DCH072***7V*** | 11   | 15 | ---  | ---               |
| EHK7-10        | 23.5 | 25 | 10.0 | 2,100 - 2,700 CFM |
| EHK7-15        | 29.9 | 30 | 15.0 | 2,100 - 2,700 CFM |
| EHK7-20        | 36   | 40 | 20.0 | 2,100 - 2,700 CFM |
| EHK7-25        | 42.4 | 45 | 25.0 | 2,100 - 2,700 CFM |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

# DCC/DCH Packaged Unit Heat Kit Match-Ups

7½ to 12½ Tons

## DCC — Heat Kit Usage

### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DCC090***3V*** | 38.4 / 38.4 | 50 / 50   | ---         | ---                       |
| EHK3-16        | 46.6 / 52.6 | 50 / 60   | 11.3 / 15.0 | 3000-3375 CFM             |
| EHK3-30        | 85.4 / 97.4 | 90 / 100  | 22.5 / 29.9 | 3000-3375 CFM             |
| EHK3-45        | 125 / 143   | 125 / 150 | 33.7 / 44.9 | 3000-3375 CFM             |
| DCC102***3V*** | 41.4 / 41.4 | 50 / 50   | ---         | ---                       |
| EHK3-16        | 46.6 / 52.6 | 50 / 60   | 11.3 / 15.0 | 3400 - 3825 CFM           |
| EHK3-30        | 85.4 / 97.4 | 90 / 100  | 22.5 / 29.9 | 3400 - 3825 CFM           |
| EHK3-45        | 125 / 143   | 125 / 150 | 33.7 / 44.9 | 3400 - 3825 CFM           |
| DCC120***3V*** | 46.3 / 46.3 | 60 / 60   | ---         | ---                       |
| EHK3-16        | 47.1 / 53.1 | 60 / 60   | 11.3 / 15.0 | 3,500-4,500 CFM           |
| EHK3-30        | 85.9 / 97.9 | 90 / 100  | 22.5 / 29.9 | 3,500-4,500 CFM           |
| EHK3-45        | 125 / 143   | 125 / 150 | 33.7 / 44.9 | 4,000-4,500 CFM           |
| DCC150***3V*** | 63.6 / 63.6 | 80 / 80   | ---         | ---                       |
| EHK3-16        | 63.6 / 63.6 | 80 / 80   | 11.3 / 15.0 | 4,000-5,600 CFM           |
| EHK3-30        | 89.3 / 101  | 90 / 110  | 22.5 / 29.9 | 4,300-5,600 CFM           |
| EHK3-45        | 128 / 146   | 150 / 150 | 33.7 / 44.9 | 4,500-5,600 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DCC — Heat Kit Usage

### Three-Phase Units @ 480V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC090***4V*** | 18   | 20  | ---  | ---                       |
| EHK4-16        | 26.1 | 30  | 15.0 | 3000-3375 CFM             |
| EHK4-30        | 48.6 | 50  | 29.9 | 3000-3375 CFM             |
| EHK4-45        | 71.1 | 80  | 44.9 | 3000-3375 CFM             |
| DCC102***4V*** | 18.6 | 20  | ---  | ---                       |
| EHK4-16        | 26.1 | 30  | 15.0 | 3400 - 3825 CFM           |
| EHK4-30        | 48.6 | 50  | 29.9 | 3400 - 3825 CFM           |
| EHK4-45        | 71.1 | 80  | 44.9 | 3400 - 3825 CFM           |
| DCC120***4V*** | 22.2 | 25  | ---  | ---                       |
| EHK4-16        | 26.3 | 30  | 15.0 | 3,500-4,500 CFM           |
| EHK4-30        | 48.8 | 50  | 29.9 | 3,500-4,500 CFM           |
| EHK4-45        | 71.3 | 80  | 44.9 | 4,000-4,500 CFM           |
| DCC150***4V*** | 29.8 | 40  | ---  | ---                       |
| EHK4-16        | 29.8 | 40  | 15.0 | 4,000-5,600 CFM           |
| EHK4-30        | 50.4 | 60  | 29.9 | 4,300-5,600 CFM           |
| EHK4-45        | 72.9 | 80  | 44.9 | 4,500-5,600 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DCH — Heat Kit Usage

### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DCH090***3V*** | 38.4 / 38.4 | 50 / 50   | ---         | ---                       |
| EHK3-16        | 77.5 / 83.5 | 80 / 90   | 11.3 / 15.0 | 3000-3375 CFM             |
| EHK3-30        | 116 / 128   | 125 / 150 | 22.5 / 29.9 | 3000-3375 CFM             |
| EHK3-45        | 155 / 173   | 175 / 175 | 33.7 / 44.9 | 3000-3375 CFM             |
| DCH102***3V*** | 41.4 / 41.4 | 50 / 50   | ---         | ---                       |
| EHK3-16        | 80.5 / 86.5 | 90 / 90   | 11.3 / 15.0 | 3400 - 3825 CFM           |
| EHK3-30        | 119 / 131   | 125 / 150 | 22.5 / 29.9 | 3400 - 3825 CFM           |
| EHK3-45        | 158 / 176   | 175 / 200 | 33.7 / 44.9 | 3400 - 3825 CFM           |
| DCH120***3V*** | 46.3 / 46.3 | 60 / 60   | ---         | ---                       |
| EHK3-16        | 85.4 / 91.4 | 90 / 100  | 11.3 / 15.0 | 3,500-4,500 CFM           |
| EHK3-30        | 124 / 136   | 125 / 150 | 22.5 / 29.9 | 3,500-4,500 CFM           |
| EHK3-45        | 163 / 181   | 175 / 200 | 33.7 / 44.9 | 4,000-4,500 CFM           |
| DCH150***3V*** | 63.6 / 63.6 | 80 / 80   | ---         | ---                       |
| EHK3-16        | 103 / 109   | 110 / 110 | 11.3 / 15.0 | 4,000-5,600 CFM           |
| EHK3-30        | 142 / 154   | 150 / 175 | 22.5 / 29.9 | 4,300-5,600 CFM           |
| EHK3-45        | 181 / 199   | 200 / 200 | 33.7 / 44.9 | 4,500-5,600 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DCH — Heat Kit Usage

### Three-Phase Units @ 480V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCH090***4V*** | 18   | 20  | ---  | ---                       |
| EHK4-16        | 40.5 | 45  | 15.0 | 3000-3375 CFM             |
| EHK4-30        | 63   | 70  | 29.9 | 3000-3375 CFM             |
| EHK4-45        | 85.5 | 90  | 44.9 | 3000-3375 CFM             |
| DCH102***4V*** | 18.6 | 20  | ---  | ---                       |
| EHK4-16        | 41.1 | 45  | 15.0 | 3400 - 3825 CFM           |
| EHK4-30        | 63.6 | 70  | 29.9 | 3400 - 3825 CFM           |
| EHK4-45        | 86.1 | 90  | 44.9 | 3400 - 3825 CFM           |
| DCH120***4V*** | 22.2 | 25  | ---  | ---                       |
| EHK4-16        | 44.7 | 45  | 15.0 | 3,500-4,500 CFM           |
| EHK4-30        | 67.2 | 70  | 29.9 | 3,500-4,500 CFM           |
| EHK4-45        | 89.7 | 90  | 44.9 | 4,000-4,500 CFM           |
| DCH150***4V*** | 29.8 | 40  | ---  | ---                       |
| EHK4-16        | 52.3 | 60  | 15.0 | 4,000-5,600 CFM           |
| EHK4-30        | 74.8 | 80  | 29.9 | 4,300-5,600 CFM           |
| EHK4-45        | 97.3 | 100 | 44.9 | 4,500-5,600 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

# DCC/DCH Packaged Unit Heat Kit Match-Ups

7½ to 12½ Tons (cont.)

## DCC — Heat Kit Usage

### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC090***7V*** | 13.3 | 15  | ---  | ---                       |
| EHK7-16        | 21.9 | 25  | 15.0 | 3000-3375 CFM             |
| EHK7-30        | 40.5 | 45  | 29.9 | 3000-3375 CFM             |
| EHK7-45        | 59.4 | 60  | 44.9 | 3000-3375 CFM             |
| DCC102***7V*** | 17.1 | 20  | ---  | ---                       |
| EHK7-16        | 21.9 | 25  | 15.0 | 3400 - 3825 CFM           |
| EHK7-30        | 40.5 | 45  | 29.9 | 3400 - 3825 CFM           |
| EHK7-45        | 59.4 | 60  | 44.9 | 3400 - 3825 CFM           |
| DCC120***7V*** | 16.6 | 20  | ---  | ---                       |
| EHK7-16        | 21.9 | 25  | 15.0 | 3,500-4,500 CFM           |
| EHK7-30        | 40.5 | 45  | 29.9 | 3,500-4,500 CFM           |
| EHK7-45        | 59.4 | 60  | 44.9 | 4,000-4,500 CFM           |
| DCC150***7V*** | 22.1 | 25  | ---  | ---                       |
| EHK7-16        | 23.3 | 25  | 15.0 | 4,000-5,600 CFM           |
| EHK7-30        | 41.9 | 45  | 29.9 | 4,300-5,600 CFM           |
| EHK7-45        | 60.8 | 70  | 44.9 | 4,500-5,600 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DCH — Heat Kit Usage

### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCH090***7V*** | 13.3 | 15  | ---  | ---                       |
| EHK7-16        | 32.2 | 35  | 15.0 | 3000-3375 CFM             |
| EHK7-30        | 50.8 | 60  | 29.9 | 3000-3375 CFM             |
| EHK7-45        | 69.7 | 70  | 44.9 | 3000-3375 CFM             |
| DCH102***7V*** | 17.1 | 20  | ---  | ---                       |
| EHK7-16        | 35.9 | 40  | 15.0 | 3400 - 3825 CFM           |
| EHK7-30        | 54.6 | 60  | 29.9 | 3400 - 3825 CFM           |
| EHK7-45        | 73.4 | 80  | 44.9 | 3400 - 3825 CFM           |
| DCH120***7V*** | 16.6 | 20  | ---  | ---                       |
| EHK7-16        | 35.5 | 40  | 15.0 | 3,500-4,500 CFM           |
| EHK7-30        | 54.1 | 60  | 29.9 | 3,500-4,500 CFM           |
| EHK7-45        | 73   | 80  | 44.9 | 4,000-4,500 CFM           |
| DCH150***7V*** | 22.1 | 25  | ---  | ---                       |
| EHK7-16        | 41   | 45  | 15.0 | 4,000-5,600 CFM           |
| EHK7-30        | 59.6 | 60  | 29.9 | 4,300-5,600 CFM           |
| EHK7-45        | 78.5 | 80  | 44.9 | 4,500-5,600 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

# DCC Packaged Unit Heat Kit Match-Ups

15 to 25 Tons

## DCC — Heat Kit Usage

### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DCC180***3V*** | 71.4 / 71.4 | 90 / 90   | ---         | ---                       |
| EHK3-31        | 86.4 / 98.0 | 90 / 100  | 21.6 / 28.8 | 5250 - 6750 CFM           |
| EHK3-46        | 124 / 141   | 125 / 150 | 32.4 / 43.2 | 5250 - 6750 CFM           |
| EHK3-60        | 161 / 150   | 175 / 175 | 43.3 / 57.6 | 5250 - 6750 CFM           |

### Three-Phase Units @ 480V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC180***4V*** | 34.3 | 45  | ---  | ---                       |
| EHK4-31        | 48.6 | 50  | 28.8 | 5250 - 6750 CFM           |
| EHK4-46        | 70.4 | 80  | 43.2 | 5250 - 6750 CFM           |
| EHK4-60        | 74.7 | 80  | 57.6 | 5250 - 6750 CFM           |

### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC180***7V*** | 25.7 | 30  | ---  | ---                       |
| EHK7-31        | 40.5 | 45  | 28.8 | 5250 - 6750 CFM           |
| EHK7-46        | 58.6 | 60  | 43.2 | 5250 - 6750 CFM           |
| EHK7-60        | 62.2 | 70  | 57.6 | 5250 - 6750 CFM           |

### Three-Phase Units @ 208 / 240V

| Model          | MCA         | MOP       | kW*         | Recommended Airflow Range |
|----------------|-------------|-----------|-------------|---------------------------|
| DCC240***3V*** | 96.4 / 96.4 | 125 / 125 | ---         | ---                       |
| EHK3-31        | 96.4 / 104  | 125 / 125 | 21.6 / 28.8 | 7200 - 8500 CFM           |
| EHK3-46        | 130 / 148   | 150 / 150 | 32.4 / 43.2 | 7201 - 8500 CFM           |
| EHK3-75        | 168 / 191   | 200 / 225 | 54.1 / 72.0 | 7203 - 8500 CFM           |

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC240***4V*** | 43.5 | 50  | ---  | ---                       |
| EHK3-46        | 73.3 | 80  | 43.2 | 7201 - 8500 CFM           |
| EHK3-75        | 94.9 | 110 | 72   | 7203 - 8500 CFM           |

### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC240***7V*** | 35   | 45  | ---  | ---                       |
| EHK3-31        | 42.6 | 45  | 28.8 | 7200 - 8500 CFM           |
| EHK3-46        | 60.8 | 70  | 43.2 | 7201 - 8500 CFM           |
| EHK3-60        | 64.3 | 70  | 57.6 | 7202 - 8500 CFM           |
| EHK3-75        | 78.8 | 90  | 72   | 7203 - 8500 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## DCC — Heat Kit Usage

### Three-Phase Units @ 208 / 240V

| Model          | MCA       | MOP       | kW*         | Recommended Airflow Range |
|----------------|-----------|-----------|-------------|---------------------------|
| DCC300***3V*** | 133 / 133 | 175 / 175 | ---         | ---                       |
| EHK3-31        | 133 / 133 | 175 / 175 | 21.6 / 28.8 | 7200 - 8500 CFM           |
| EHK3-46        | 139 / 156 | 175 / 175 | 32.4 / 43.2 | 7201 - 8500 CFM           |
| EHK3-60        | 176 / 165 | 200 / 175 | 43.3 / 57.6 | 7202 - 8500 CFM           |
| EHK3-75        | 176 / 199 | 200 / 225 | 54.1 / 72.0 | 7203 - 8500 CFM           |

### Three-Phase Units @ 480V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC300***4V*** | 53.8 | 70  | ---  | ---                       |
| EHK3-31        | 55.9 | 70  | 28.8 | 7200 - 8500 CFM           |
| EHK3-46        | 77.6 | 80  | 43.2 | 7201 - 8500 CFM           |
| EHK3-60        | 81.9 | 90  | 57.6 | 7202 - 8500 CFM           |
| EHK3-75        | 99.2 | 110 | 72   | 7203 - 8500 CFM           |

### Three-Phase Units @ 575V

| Model          | MCA  | MOP | kW*  | Recommended Airflow Range |
|----------------|------|-----|------|---------------------------|
| DCC300***7V*** | 42.9 | 50  | ---  | ---                       |
| EHK3-31        | 46.4 | 50  | 28.8 | 7200 - 8500 CFM           |
| EHK3-46        | 64.5 | 70  | 43.2 | 7201 - 8500 CFM           |
| EHK3-60        | 68.1 | 80  | 57.6 | 7202 - 8500 CFM           |
| EHK3-75        | 82.6 | 100 | 72   | 7203 - 8500 CFM           |

\* Electric Heater kW rating: Rated at 240v for 208-230v units; 480v for 460v units

## Notes

## Notes



### About Daikin:

**DAIKIN**

Daikin Industries, Ltd. (DIL) is a global Fortune 1000 company which celebrated its 90th anniversary in May 2014. The company is recognized as one of the largest HVAC (Heating, Ventilation, Air Conditioning) manufacturers in the world. DIL is primarily engaged in developing indoor comfort systems and refrigeration products for residential, commercial and industrial applications. Its consistent success is derived, in part, from a focus on innovative, energy-efficient and premium quality indoor climate and comfort management solutions.

### Additional Information

Before purchasing this appliance, read important information about its estimated annual energy consumption, yearly operating cost, or energy efficiency rating that is available from your retailer.

Visit [www.daikincomfort.com](http://www.daikincomfort.com)

*Daikin* and its design are trademarks owned by Daikin.

**DAIKIN**

Our continuing commitment to quality products may mean a change in specifications without notice.

© 2018 **DAIKIN NORTH AMERICA LLC** · Houston, Texas · USA · [www.daikincomfort.com](http://www.daikincomfort.com) or [www.daikinac.com](http://www.daikinac.com)