



SPECIFICATIONS

Product Description: **DUCTING, 12" (30.4cm) DIAMETER**

Part Number: 9550-15, 9550-25 Style: RETRACTABLE

GENERAL DESCRIPTION:

This product is lightweight, retractable and designed for maximum air handling capabilities. Dual direction flow with minimum friction loss.

CONSTRUCTION:

- Vinyl and polyester materials
- Single-Ply
- PVC Coated
- Temperature Range: -20°F to 180°F (-28.8°C to 82.2°C)
- Retractable, Non-collapsible design
- Class 1 hard drawn spring steel wire helix
- Meets ASTM 227 Specs.
- Yellow color with black weather-strip
- Fastening cuffs at both ends



AVAILABLE:

Part No.	Diameter In. (cm)	Length Ft. (m)	End Straps	Weight Lbs. (Kg)
9550-15	12" (30.4 cm)	15' (4.57 m)	Dual	14 lbs. (6.3 kg)
9550-25	12" (30.4 cm)	25' (7.62 m)	Dual	22 lbs. (9.8 kg)

ACCESSORIES:

Part No.	Ducting Size	Description	
9509-03	12" (30.4 cm)	Reduces 12" (30.4cm) blower to 8" (20.3cm) ducting (use only with 9509-50 blower)	
9550-01	12" (30.4 cm)	Duct to Duct Connector, with raised lip	
9600-36	12" (30.4 cm)	Storage Rack for 12" (30.4cm) Ducting, up to 25' (7.62m) Ducting	
9600-45	12" (30.4 cm)	Storage Bag	

1360 Shiloh Church Road Piedmont, SC 29673 864-846-8740 800-622-3530 FAX: 800-362-7231 <u>www.allegrosafety.com</u>

Rev E 11-20-12