



SPECIFICATIONS

Product Description: **DUCTING,**
Part Number: **9650-15, 9650-25**
Style: **20" RETRACTABLE**

GENERAL DESCRIPTION:

This product is lightweight, retractable and designed for maximum air handling capabilities. Dual direction flow with minimum friction loss.

CONSTRUCTION:

- Vinyl and polyester materials
- Single-ply
- PVC coated
- Temperature range: -20°F to 180°F
- Retractable, non-collapsible design.
- Class 1 hard drawn spring steel wire helix
- Steel wire meets ASTM 227 Specs.
- Yellow color with black weather-strip
- Fastening cuffs at both ends



AVAILABLE:

Part No.	Diameter	Length	End-Straps
9650-15	20" (50.8 cm)	15' (4.57 m)	Dual
9650-25	20" (50.8 cm)	25' (7.62 m)	Dual

ACCESSORIES:

Part No.	Ducting Size	Description
9650-01	20" (50.8 cm)	Duct to Duct Connector, with raised lip
9600-45	20" (50.8 cm)	Storage Bag