



**MCR
SAFETY**

6528S

Supported / Dipped gloves Specification Sheet

PRODUCT DESCRIPTION:

Best bang for your buck. PVC offers unmatched performance at an affordable cost. Double dipped PVC coated gloves provide excellent protection. Glove lengths from knit wrist to 18" provide different levels of protection. The 6528S is an industry standard black double dipped, sandy finish, interlock lined glove with a gauntlet cuff. Glove is 18" in length.

FEATURES:

- PVC
- Black Double Dipped
- Interlock
- Sandy Finish
- 18 inch

APPLICATIONS:

Agriculture, Dairy, Farming, Janitorial, Material Handling, Sanitation, Petrochemical industries



TECHNICAL DATA FOR: 6528S


Material Group	Supported	Overall Length	18 in.
Product Type	Supported / Dipped gloves		
Glove Size	Large		
Material	PVC		
Grade	Industrial Grade		
Lining	Interlock		
Thumb Style	Wing		
Made In	China,USA		



MCR
SAFETY

6528S

Supported / Dipped gloves Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6528S	Large	15.000	5	N/A	48.282 lb.	8.047

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved