



MCR
SAFETY

9786

Predalite

Supported / Dipped gloves
Specification Sheet

PRODUCT DESCRIPTION:

00014

FEATURES:


- Light Nitrile Palm Coated
- Interlock Lining
- PVC Safety Cuff
- CE Score 3111
- Treated with Actifresh

APPLICATIONS:

Food, Oil and Gas Industry, Carpentry, Construction,
Landscaping

TECHNICAL DATA FOR: 9786L

Series	Predalite	Overall Length	11 in.
Material Group	Supported	EN 388 : CE Score - Abrasion	4
Product Type	Supported / Dipped gloves	EN 388 : CE Score - Cut	1
Glove Size	Large	EN 388 : CE Score - Tear	2
Material	Nitrile	EN 388 : CE Score - Puncture	1
Grade	Premium		
Lining	Interlock		
Thumb Style	Straight		
Made In	Sri Lanka,Pakistan		



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
----------	-------	----	----	----	-------------	------------



MCR
SAFETY

9786

Predalite

Supported / Dipped gloves
Specification Sheet

Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9786L	Large	10.826	4.720	N/A	38.436 lb.	3.203
9786XL	X - Large	11.024	4.960	N/A	39.156 lb.	3.263
9786M	Medium	10.433	4.330	N/A	32.700 lb.	2.725
9786S	Small	10.237	4.090	N/A	30.420 lb.	2.535

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved