

Residential Atmospheric Vent Fan Assist Gas Water Heater



Photo is of RG2F40S6N

FEATURING: 1











- **High Efficiency Blower**—Pulls air through a tightly restricted baffle system resulting in increased water heater efficiency ratings.
 - Ten Foot Power Cord-Included (120 VAC).
- Bradford White ICON System®—Intelligent gas control with spark to pilot ignition system eliminates the constant burning pilot. This results in savings of pilot gas during standby periods (120 VAC).
 - Enhanced Performance—Proprietary algorithms provide enhanced First Hour Rating and tighter temperature differential.
 - Advanced Temperature Control System—Microprocessor constantly monitors and controls burner operation to maintain consistent and accurate water temperature levels.
 - Intelligent Diagnostics—An exclusive green LED light prompts the installer during start-up and provides ten different diagnostic codes to assist in troubleshooting.
 - Pilot On Indication Flashing green LED provides positive indication that pilot is on.
 - Separate Immersed Thermowell—High-strength advanced polymer composite
 thermowell provides isolation between electric temperature sensor and surrounding
 water. No need to drain the tank when removing gas valve.
- Advanced ScreenLok® Technology Flame Arrestor Design Flame arrestor is designed to prevent ignition of flammable vapors outside of the water heater.
- Flammable Vapor Sensor Electronic sensor prevents burner operation if flammable vapors are detected.
- Maintenance-Free—No regular cleaning of air inlet openings or flame arrestor is required under normal conditions.
- Sight Window Offers a view into the combustion chamber to observe the operation of the pilot and burner.
- Vitraglas® Lining with Microban®—An exclusively engineered enamel formula that provides superior tank protection from the corrosive effects of water; and with Microban® antimicrobial product protection to help prevent the growth of bacteria, mold and mildew on the surface of the tank lining.
- Factory-Installed Hydrojet® Total Performance System—Sediment reducing device that also increases first hour rating of hot water while minimizing temperature build-up in tank.
- Insulation System—2" (51mm) Non-CFC foam insulation covers the sides and top of the tank, reducing heat loss. This results in less energy consumption, improved efficiencies, and jacket rigidity.
- Pedestal Base.
- Water Connections 3/4" (19mm) NPT factory-installed true dielectric fittings extend water heater life and simplify water line connections.
- Factory-Installed Heat Traps—Design incorporates a flexible disk that reduces heat loss in piping and eliminates the potential for noise generation.
- Protective Anode Rod.
- 3x4 "Snap Lock" Draft Diverter—Allows either 3" (76mm) or 4" (102mm) vent connections.
- T&P Relief Valve—Installed.
- Low Restrictive Brass Drain Valve Durable tamper proof design.
- NOx Emissions Less than 40 ng/J.











copy of the warranty included with the heater.

Microban® antimicrobial product protection helps prevent the growth of bacteria, mold and mildew that may affect the product. The built-in antimicrobial properties do not protect users or others from disease-causing organisms. Microban® is a registered trademark of Microban Products Company.

For products installed in USA, Canada, and Puerto Rico. Some states do not allow limitations on warranties. See complete

Residential Atmospheric Vent Fan Assist Gas Water Heater

Fan Assist Models

NATURAL GAS AND LIQUID PROPANE GAS

Meet or exceed ASHRAE 90.1b (current standard) C.E.C. Listed 78% Recovery Efficiency

Model Number	Nominal Gal. Capacity		DOE Rated Storage			First Hour Rating	Uniform Energy Factor	Recovery at 90°F Rise*			Model Number		Nominal Liter Capacity	DOE Rated Storage			First Hour Rating	Uniform Energy Factor	y 50°C Rise* r		
	U.S. Gal.	lmp. Gal.	Volume Gal.	BTU/Hr. Input	LP BTU/Hr. Input	Gal.		U.S. GPH	lmp. GPH	LP U.S. GPH	LP Imp. GPH				Volume Liters	kW Input	LP kW Input	Liters		Liters/ Hour	LP Liters/ Hour
RG2F40S6N	40	33	38	38,000	38,000	75	0.70	41	33	40	33	RG2F40S	6N	151	144	11.1	11.1	284	0.70	155	151
RG2F50S6N	50	42	48	38,000	38,000	76	0.68	41	33	40	33	RG2F50S	6N	189	182	11.1	11.1	288	0.68	155	151
Model		Α		В		C	D			Ε,		F		G	Н		J	M		S	Approx.

Number	Floor to Exhaust Conn. in.	Jacket Dia. in.	Vent Size in.	Floor to T&P Conn. in.	Floor to Gas Conn. in.	Floor to Top of Heater in.	Floor to Water Conn. in.	Depth in.	C/L of Water Conn. in.	Water Conn. NPT in.	Gas Conn. Size in.	Shipping Weight
RG2F40S6N	541/4	22	3 or 4	40	13	47	477/8	257/8	8	3/4	1/2	150
RG2F50S6N	55 ¹ / ₄	24	3 or 4	405/8	13	48	487/8	277/8	8	3/4	1/2	176
Model Number	A Floor to Exhaust Conn.	B Jacket Dia.	C Vent Size	D Floor to T&P Conn.	E Floor to Gas Conn.	F Floor to Top of Heater	G Floor to Water Conn.	H Depth	J C/L of Water Conn.	M Water Conn. NPT	S Gas Conn. Size	Approx. Shipping Weight

mm. mm mm. mm. mm. mm. mm mm. mm. mm. RG2F40S6N 1378 559 76 or 102 1016 330 1194 1216 657 203 19 13 68 1403 1032 RG2F50S6N 610 76 or 102 330 1219 1241 708 203 13 80 19


Propane models feature a Titanium Stainless Steel propane burner. For Propane (LP) models change suffix "N" to "X".

For 10 year models, change suffix from "6" to "10".

Based on manufacturer's rated recovery efficiency.

120V, 60Hz., 1 Amp.

Uniform Energy Factor and First Hour Rating is based on the latest AHRI directory listings.



General:

Meets NAECA Requirements.

All gas water heaters are certified at 300 PSI test pressure (2068 kPa) and 150 PSI working pressure (1034 kPa). All potable water connections are 3/4" NPT (19mm) on 8" (203mm) centers. All models design-certified by CSA International (formerly AGA/CGA), ANSI Z21.10.1 and peak performance rated.

Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.

Suitable for Water (Potable) Heating and Space Heating. Toxic chemicals, such as those used for boiler treatment, shall NEVER be introduced into the potable side of this system. The potable side may NEVER be connected to any existing heating system or component(s) previously used with a non-potable water heating appliance.





Sales: 800-523-2931 ■ Fax 215-641-1612

24/7 Technical Support: 800-334-3393

Email techserv@bradfordwhite.com

Products made by Bradford White are manufactured in the United States using the finest raw materials and components from around the world.