
CSBXXXX SWAY BRACE FITTING

EG F	-inish*	Service Pipe Size		
Part Number	Article Number	NPS (in)	mm**	
CSB0100	404516	1	25	
CSB0125	404517	1-1/4	32	
CSB0150	404518	1-1/2	38	
CSB0200	404519	2	50	
CSB0250	404520	2-1/2	65	
CSB0300	404521	3	80	
CSB0400	404522	4	100	
CSB0500	404523	5	125	
CSB0600	404524	6	150	
CSB0800	404525	8	200	
CSB1000	404526	10	250	




Sway Brace assemblies are intended to be installed in accordance with NFPÁ®-13 and the manufacturer's installation instructions.


The required type, number, and size of fasteners used for the structure attachment fitting shall be in accordance with NFPA-13.

*Part numbers and article numbers are for EG only. Other coatings available. Contact customer service for availability.

**Metric pipe sizes are not UL listed.



Installation Angle from Vertical



- RNING:
 Pentair products shall be installed and used only as indicated in Pentair product instruction sheets and training materials. Instruction sheets are available at www.erico.pentair.com and from your Pentair customer service representative.

 PENTAIR products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.

 All instructions must be completely followed to ensure proper and safe installation and performance.

 Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

 Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.

 All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose. other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:
a. Conformance to all governing codes.
b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified

c. Using appropriate industry standard hardware as noted above.

All governing codes and regulations and those required by the job site must be observed.

All ways use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.



UL® Loads (Listed for Sway Braces) lbs (N)							
EG Finish*	Lateral						
Part Number	Youngstown Tube Fire Flow	Bull Moose Eddy Flow	Wheatland Mega Flow	Sch 10 Service Pipe	Sch 40 Service Pipe		
CSB0100	N/A	N/A	N/A	2,765 (12,299)	2,765 (12,299)		
CSB0125	N/A	2,765 (12,299)	2,765 (12,299)	2,765 (12,299)	2,765 (12,299)		
CSB0150							
CSB0200							
CSB0250	2,765 (12,299)						
CSB0300							
CSB0400							
CSB0500	N/A	N/A	N/A	2,765 (12,299)	2,765 (12,299)		
CSB0600	N/A	N/A	2,765 (12,299)	2,765 (12,299)	2,765 (12,299)		
CSB0800	N/A	N/A	N/A	2,765 (12,299)	2,765 (12,299)		
CSB1000	N/A	N/A	N/A	2800 (12,455)	2800 (12,455)		

	U	JL® Loads (Listed for	Sway Braces) lbs (N)				
EG Finish*	Longitudinal							
Part Number	Youngstown Tube Fire Flow	Bull Moose Eddy Flow	Wheatland Mega Flow	Sch 10 Service Pipe	Sch 40 Service Pipe			
CSB0100	N/A	N/A	N/A	1,600 (7,117)	1,600 (7,117)			
CSB0125	N/A	1,000 (4,448) 1,000 (4,448)		1,000 (4,448)	1,000 (4,448)			
CSB0150	1,600 (7,117)							
CSB0200	0.045 (0.000)							
CSB0250	2,015 (8,963)							
CSB0300	2,100 (9,341)							
CSB0400	2,600 (11,565)	2,600 (11,565) 2,600 (11,565		2,600 (11,565)	2,600 (11,565)			
CSB0500	N/A	N/A	N/A	2,600 (11,565)	2,600 (11,565)			
CSB0600	N/A	N/A	2,600 (11,565)	2,600 (11,565)	2,600 (11,565)			
CSB0800	N/A	N/A	N/A	2,600 (11,565)	2,600 (11,565)			
CSB1000	N/A N/A		N/A	2,800 (12,455)	2,800 (12,455)			

A) UL Listed for use with Lightwall Service Pipe, Schedule 10, and Schedule 40 Service Pipe, for use with 1 to 2 NPS Schedule 40 brace pipe.

B) *Part numbers and article numbers are for EG only. Other coatings available. Contact customer service for availability.



PENTAIR

CFS544_B

EG Finish*		Sonvice	Dino Sizo	F	M® Horizontal	Load Ratings Ib	s (N)	
Part Number Orientation to Sprinkler Pipe	Service Pipe Size		Installation Angle				Pipe Schdule	
	Inch	mm	30° - 44°	45° - 59°	60° - 74°	75° - 90°	1	
CSB0100		1	25	1,490 (6,628)	2,110 (9,386)	2,580 (11,476)	2,900 (12,900)	
CSB0125		1 - 1/4	32	1,380 (6,139)	1,960 (8,719)	2,400 (10,676)	2,690 (11,966)	
CSB0150		1 - 1/2	40					
CSB0200		2	50					
CSB0250		2 - 1/2	65	1,440 (6,405)	2,030 (9,030)	2,490 (11,076)	2,790 (12,411)	
CSB0300	Lateral	3	85		1,970 (8,763)	2,420 (10,765)	2,710 (12,055)	
CSB0400		4	100	1,390 (6,183)				
CSB0500		5	125					
CSB0600		6	150	1,460 (6,494)	2,060 (9,163)	2,520 (11,210)	2,830 (12,588)	
CSB0800		8	200	1,330 (5,916)	1,880 (8,363)	2,300 (10,231)	2,580 (11,476)	- LW, 10, 40
CSB1000		10	250	1,330 (3,716)	1,000 (0,363)			
CSB0100		1	25	1,290 (5,738)	1,240 (5,516)	1,260 (5,605)	1,400 (6,228)	
CSB0125		1 - 1/4	32		1,240 (3,310)			
CSB0150		1 - 1/2	40	1,200 (5,338)	1,860 (8,274)	2 190 (0 (07)	2.250 (10.009)	
CSB0200		2	50		1 000 (0 00 ()	2,180 (9,697)	2,250 (10,008)	
CSB0250		2 - 1/2	65	1,320 (5,872)	1,820 (8,096)		2,500 (11,121)	
CSB0300	Longitudinal	3	80		300 (5,783) 1,790 (7,962)	0.100 (0.740)		
CSB0400		4	100	1,300 (5,783)		1,790 (7,962) 2,190 (9,742)	2 /20 /11 /00	
CSB0500		5	125				2,630 (11,699)	
CSB0600	1	6	150	1,410 (6,272)	1,950 (8,674)		2,680 (11,921)	
CSB0800		8	200	1 400 (4 000) 1 000 (0 5 (1)	1 000 /0 5411	2,350 (10,453)	0 / 40 /11 7 /01)
CSB1000		10	250	1,400 (6,228)	1,920 (8,541)		2,640 (11,743)	

Notes:


- A) FM approved when used with 1", 1-1/4" or 2" (DN25, DN32, DN40, DN50) NPS Schedule 40, GB/T 3091, EN 10255 (Heavy), AS 1074 (Heavy) or JIS G3454 brace pipe.
- B) Load rátings for Schedule 40 above may also be applied to AS 1074 (Heavy), GB/T 3091, EN 10255 (Heavy) and JIS G3454 pipe.
- C) Load ratings for Schedule 40 above may also be applied to AS 1074 (Meduim), GB/T 3091, EN 10255 (Medium or Heavy), JIS G3452, FM approved Thinwall, and Schedule 40 pipes unless otherwise indicated.
- D) Load ratings for LW above refers to FM Approved Lightwall Pipe, commonly referred to as "Schedule 7". These ratings may also be applied to A1074 Lightwall, EN 10255 L, EN 10220, and GB/T 8163 pipe unless otherwise specified.
- E) Load ratings for "0.188 wall" above may be applied to any thicker walled pipe unless otherwise specified.
- F) *Part numbers and article numbers are for EG only. Other coatings available. Contact customer service for availability.






CFS544_B

#1



Insert brace pipe and drop clamp over service pipe

#2



Tighten nuts until head snaps off






Note: Alternate torque between nuts evenly




Tighten set screw until

CSBXXXX is a Sway Brace Fitting to be combined with a CADDY brand Structural Attachment Fitting and "Bracing Pipe" to form a complete bracing assembly.

Sway Braces shall be installed in accordance with NFPA®-13.







Pentair, CADDY, ERICO CADWELD, ERICO CRITEC, ERICO, ERIFLEX, and LENTON are owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

