

For Residential and Commercial Applications

| | | | |
|----------------|--|----------------------|--|
| Job Name | | Engineer / Architect | |
| Job Location | | Wholesaler | |
| Submittal Date | | Contractor | |

PLB100X/111X/113X 1/4 Turn Angle Stop – Compression x Compression

Use: For use only in potable water distribution systems, hot and cold, in accessible locations only

Part Listing:

| | | |
|--------------------------|-----------|---|
| <input type="checkbox"/> | PLB100X B | 1/2" nom compression x 3/8" OD compression, chrome plated, bulk |
| <input type="checkbox"/> | PLB100X P | 1/2" nom compression x 3/8" OD compression, chrome plated, bagged |
| <input type="checkbox"/> | PLB113X P | 1/2" nom compression x 3/8" OD compression w/loose key, chrome plated, bagged |
| <input type="checkbox"/> | PLB111X P | 1/2" nom compression x 1/4" OD compression, chrome plated, bagged |



MATERIAL SPECIFICATIONS

| | |
|---------------------------|-------------------------------|
| Body | Low lead brass, chrome plated |
| Stem | Low lead brass |
| Ball | Low lead brass, chrome plated |
| Seats | PTFE |
| O-ring | NBR |
| Handle | ABS, chrome plated |
| Handle Screw | Stainless steel |
| Compression Nut | Brass, chrome plated |
| Compression Sleeve | Brass |
| Adaptor | Low lead brass, chrome plated |

Operating Specifications

| Temperature | Pressure |
|---------------------------|-----------------|
| Intermittent 40° - 140° F | 125 PSI maximum |

This specification and all information contained herein is the confidential and exclusive property of Brasscraft Manufacturing Company, and shall not be disclosed to others without the written consent of Brasscraft Mfg. Co. This specification must be returned to Brasscraft Mfg. Co. if requested.





400.276 PLB100X/111X/113X 1/4 Turn Angle Stop-Comp Outlet REV 12/18

PLUMBSHOP®

©2018 Brasscraft Manufacturing Company

PLB100X/111X/113X 1/4 Turn Angle Stop – Compression x Compression

| PART DIMENSIONS (Inches) | | | | | | |
|--------------------------|--------|--------|--------|--------|--------|--------|
| Model | DIM. A | DIM. B | DIM. C | DIM. D | DIM. E | DIM. F |
| PLB100X | 2.02 | 1.77 | 2.34 | 1.12 | 1.22 | .94 |
| PLB111X | 2.02 | 1.77 | 2.34 | 1.12 | 1.22 | .94 |
| PLB113X | 1.63 | 1.12 | 2.44 | 1.12 | 1.22 | 2.35 |



Listings & Certifications:

- IAPMO listed to ASME A112.18.1 / CSA B125.1 (File #8425)
- IAPMO listed to NSF / ANSI 372 for No-Lead (File #8427)
- IAPMO listed to NSF61 (File #N-8426)



This specification and all information contained herein is the confidential and exclusive property of Brasscraft Manufacturing Company, and shall not be disclosed to others without the written consent of Brasscraft Mfg. Co. This specification must be returned to Brasscraft Mfg. Co. if requested.

400.276 PLB100X/111X/113X 1/4 Turn Angle Stop-Comp Outlet REV 12/18

PLUMBSHOP®

©2018 Brasscraft Manufacturing Company